


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MAX. BUNDLE DIA.	PACKAGE QTY.	"L" LENGTH +/- .3" [ 7 ]
MLT2EH-LP	2" [ 51 ]	50	11.8" [ 300 ]
MLT4EH-LP	4" [ 102 ]	50	17.1" [ 434 ]
MLT6EH-LP	6" [ 152 ]	50	23.4" [ 594 ]
MLT8EH-LP	8" [ 203 ]	50	29.7" [ 754 ]
MLT10EH-LP	10" [ 254 ]	50	35.9" [ 912 ]
MLT12EH-Q	12" [ 305 ]	25	42.2" [ 1072 ]



- NOTES:
1. APPLICATION TOOLS - ST2MT, RT2HT, RT2HTN & PBTMT
  2. MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2670 NEWTONS) WHEN TESTED ON A 3" MANDREL.
  3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
  4. TOLERANCES:  
 .XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
 .X = ±.03 [ .8 ]    ANGLES = ±2°
  5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED  
EDGES ALONG  
STRAP BODY

SECTION A - A  
SCALE: 4x

REV					DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE					
											<b>METAL LOCKING TIE EXTRA HEAVY DUTY 304 STAINLESS STEEL</b>					
											CUSTOMER DRAWING					
											ITEM REVISION NAME <b>N41155BS/04</b>					
											DATASET FILE NAME <b>N41155BS_DC/04A</b>					
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]					
											.x ± .03 [ .8 ]    .xxx ± .010 [ .25 ] .xx ± .02 [ .5 ]    ANGLES ± 5 °					
											THIRD ANGLE PROJECTION					
											MATERIAL: <b>SEE NOTES</b>					
											DRAWING NUMBER: <b>N41155BS_DC</b>					
04A	02/13	JAMB	SKB	RGRO					UPDATE DRAWING TO NEW PANDUIT TITLE BLOCK AND PANDUIT LOGO REMOVED APPLICATION TOOL ST3MT, ADDED ST2MT TOOL	SSECN01028	DRAWN BY <b>JAMB</b>	DATE <b>01/04</b>	CHK <b>DPN</b>	SCALE <b>2:1</b>	SHT 1 OF 1	SIZE <b>A</b>
03A	2/12	MIM	RGRO	---					NOTE 3: METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	----						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[MLT2EH-LP](#) [MLT4EH-LP](#) [MLT8EH-LP](#) [MLT10EH-LP](#)