

Features

Regulated Converters

- 30W in a 1"x1" case
- 4:1 wide input voltage range
- 2kVDC/1min isolation
- IEC/EN62638-1 certified
- Efficiency over 90%
- OVP, OLP, OTP, UVLO
- +110°C max. case temperature



REC30E-Z

30 Watt

1" x 1"

Single & Dual Output



IEC62368-1 2nd Edition certified
 IEC/EN62368-1 3rd Edition certified
 EN55032 compliant
 CB-Report

Description

The REC30E-Z series are high power density, wide input voltage range 30W DC/DC converters in an industry standard 1"x1" case size. Despite their small size, the REC30E-Z converters are fully specified devices with output currents up to 7 amps, over 90% efficiency, no minimum load, 2000VDC/1min isolation, tight regulation, and low ripple/noise figures. The outputs are also fully protected against over-temperature, short circuits, overcurrent, and overvoltage, and the single output version offers a ±10% trim range. These converters will find industrial applications where board space is at a premium.

Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. (1) [%]	max. Capacitive Load (2) [µF]
REC30E-243.3SZ	9 - 36	3.3	7000	88.5	10000
REC30E-2405SZ	9 - 36	5	6000	89	7200
REC30E-2412SZ	9 - 36	12	2500	90	1200
REC30E-2415SZ	9 - 36	15	2000	90.5	1000
REC30E-2424SZ	9 - 36	24	1250	90.5	380
REC30E-2412DZ	9 - 36	±12	±1250	89	±750
REC30E-2415DZ	9 - 36	±15	±1000	90	±500
REC30E-483.3SZ	18 - 75	3.3	7000	88	10000
REC30E-4805SZ	18 - 75	5	6000	90	7200
REC30E-4812SZ	18 - 75	12	2500	90.5	1200
REC30E-4815SZ	18 - 75	15	2000	90.5	1000
REC30E-4824SZ	18 - 75	24	1250	91	380
REC30E-4812DZ	18 - 75	±12	±1250	90.5	±750
REC30E-4815DZ	18 - 75	±15	±1000	91	±500

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load

Model Numbering



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Typ.	Max.
Internal Input Filter				Pi type
Input Voltage Range	nom. Vin= 24VDC	9VDC	24VDC	36VDC
	nom. Vin= 48VDC	18VDC	48VDC	75VDC
Input Surge Voltage	nom. Vin= 24VDC		50VDC	
	nom. Vin= 48VDC		100VDC	
Under Voltage Lockout (UVLO)	nom. Vin= 24VDC	DC-DC ON	7.5VDC	
		DC-DC OFF	16VDC	
	nom. Vin= 48VDC	DC-DC ON	9VDC	
		DC-DC OFF	18VDC	
Input Current	nom. Vin= 24VDC		1500mA	
	nom. Vin= 48VDC		690mA	
Quiescent Current				10mA
Output Voltage Trimming	single output		±10%	
Minimum Load			0%	
Start-up time			30ms	
ON/OFF CTRL	DC-DC ON		Open or $3.5\text{VDC} < V_{CTRL} < 15\text{VDC}$	
	DC-DC OFF		Short or $0\text{VDC} < V_{CTRL} < 1.2\text{VDC}$	
Input Current of CTRL Pin	DC-DC OFF		2mA	
Internal Operating Frequency	REC30E-243.3SZ, REC30E-483.3SZ		300kHz	
	REC30E-24xxS(D)Z		400kHz	
	REC30E-48xxS(D)Z		370kHz	
	REC30E-4815SZ, REC30E-2415DZ		430kHz	
Output Ripple and Noise ⁽³⁾	20MHz BW		75mVp-p	

Notes:


Note3: Measurements are made with a 0.1µF MLCC across output (low ESR)

Efficiency vs. Load

REC30E-243.3SZ



REC30E-2405SZ




continued on next page


Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)

Efficiency vs. Load


REC30E-2424SZ




REC30E-2415DZ



REC30E-4812SZ




REC30E-4812DZ



OUTPUT VOLTAGE TRIMMING

The REC30E-Z converters offer the feature of trimming the output voltage over a certain range around the nominal value by using external trim resistors. The values for the external trim resistors shown in the below examples are according to standard E96 values; therefore, the specified voltage may slightly vary.



continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

OUTPUT VOLTAGE TRIMMING

V_{out_nom} = nominal output voltage [VDC]
 V_{out_set} = trimmed output voltage [VDC]
 ΔV_{out} = output voltage change [%]
 V_{ref} = reference voltage [VDC]
 R_{up} = external trim up resistor [Ω]
 R_{down} = external trim down resistor [Ω]
 R_1, R_2, R_3 = internal resistors [Ω]
 k_u = trim up factor []
 k_d = trim down factor []

Vout _{nom}	R ₁ [Ω]	R ₂ [Ω]	R ₃ [Ω]	V _{ref} [VDC]
3.3VDC	16k6	10k	52k3	1.25
5VDC	10k		35k7	2.5
12VDC	38k		48k7	
15VDC	50k1		64k9	
24VDC	86k		73k2	

$$k_u = \left[\frac{V_{ref}}{(V_{out} + \Delta V_{out}) - V_{ref}} \right] * R_1 = k\Omega$$

$$R_{up} = \left[\frac{k_u * R_2}{R_2 - k_u} \right] - R_3 = k\Omega$$

$$k_d = \left[\frac{(V_{out} + \Delta V_{out}) - V_{ref}}{V_{ref}} \right] * R_2 = k\Omega$$

$$R_{down} = \left[\frac{k_d * R_1}{R_1 - k_d} \right] - R_3 = k\Omega$$

Trim Up: Vout_{set} = 26.4VDC

Vout_{nom} = 24V, ΔV_{out} = 2.4V (10%)

$$k_u = \left[\frac{2.5V}{(24V + 2.4V) - 2.5V} \right] * 86k\Omega = 8k995\Omega$$

$$R_{up} = \left[\frac{8.995k\Omega * 10k\Omega}{10k\Omega - 8.995k\Omega} \right] - 73.2k\Omega = 16k4\Omega$$

Trim down: Vout_{set} = 21.6VDC

Vout_{nom} = 24V, ΔV_{out} = -2.4V (-10%)

$$k_d = \left[\frac{[24V + (-2.4V)] - 2.5V}{2.5V} \right] * 10k\Omega = 76k4\Omega$$

$$R_{down} = \left[\frac{76.4k\Omega * 86k\Omega}{86k\Omega - 76.4k\Omega} \right] - 73.2k\Omega = 611k2\Omega$$

REGULATIONS

Parameter	Condition		Value
Output Accuracy			±1.0% typ.
Line Regulation	low line to high line, full load	Single	±0.2% typ.
		Dual	±0.5% typ.
Load Regulation	0% to 100% load	Single	0.2% typ.
		Dual	1.0% typ.
Cross Regulation	asymmetrical load 25% / 100%		±0.5% typ.
Transient Response Recovery Time	25% load step change (75% - 100%)		250µs

PROTECTIONS

Parameter	Type		Value
Short Circuit Protection (SCP)			continuous, auto recovery
Over Load Protection (OLP)	hiccup mode	nom. Vin= 24VDC	170% of rated I _{OUT}
		nom. Vin= 48VDC	190% of rated I _{OUT}
Over Temperature Protection (OTP)	automatic restart after cool down		115°C

continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Type		Value
Over Voltage Protection (OVP)	internal clamping	REC30E-xx3.3SZ	5.3VDC min.
		REC30E-xx05SZ	6.2VDC min.
		REC30E-xx12SZ	15VDC min.
		REC30E-xx15SZ	18VDC min.
		REC30E-xx24SZ	30VDC min.
		REC30E-xx12DZ	±15VDC min.
		REC30E-xx15DZ	±18VDC min.
Isolation Voltage ⁽⁴⁾	I/P to O/P	1 minute	2kVDC
Isolation Resistance	V _{ISO} = 500VDC		1GΩ min.
Isolation Capacitance			2400pF max.

Notes:

Note4: For repeat Hi-Pot testing, reduce the time and/or the test voltage

ENVIRONMENTAL


Parameter	Condition		Value
Operating Temperature Range ⁽⁵⁾	refer to "Derating Graph"		-40°C to +105°C
Maximum Case Temperature			110°C
Temperature Coefficient			0.02%/K max.
Thermal Impedance	0.1m/s, horizontal		15.9K/W
Operating Altitude			5000m
Operating Humidity	non-condensing		5% - 95% RH max.
Pollution Degree			PD2
Vibration			according to MIL-HDBK-202G
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	560 x 10 ³ hours

Notes:


Note5: Test PCB: Eurocard 160x100mm 105µm copper, double layer horizontal

Derating Graph
(@chamber)

REC30E-2405SZ



REC30E-4812SZ



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


SAFETY AND CERTIFICATIONS

Certificate Type (Safety)	Report / File Number	Standard
Audio/Video, information and communication technology equipment - Part1: Safety requirements 2nd Edition (CB Scheme)	2207062-CB	IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements 2nd Edition		EN62368-1:2014+A11:2017
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition (CB Scheme)	2207062-1-CB	IEC62368-1:2018 3rd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition		EN IEC 62368-1:2020+A11:2020
RoHS2		RoHS-2011/65/EU + AM-2015/863


EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment – Emission Requirements	without external components	EN55032:2015+A11:2020, Class A
	see filter below	EN55032:2015+A11:2020, Class B

EMC Filtering Suggestions according to EN55032

REC30E-24xxS(D)Z



REC30E-48xxS(D)Z



Component List Class B

MODEL	C1	L1	C2	C3	C4
REC30E-24xxS(D)Z	4.7µF	10µH	4.7µF	2200pF	2200pF
REC30E-48xxS(D)Z		32µH			






DIMENSION AND PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	case	nickel plated metal enclosure (UL94 V-2)
	baseplate	plastic (UL94 V-2)
	potting	silicone, (UL94 V-0)
	PCB	FR4, (UL94 V-1)
Dimension (LxWxH)		25.4 x 25.4 x 10.0mm
Weight		17g typ.

continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Dimension Drawing (mm)



Pinning Information

Pin #	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	CTRL	CTRL
4	-Vout	-Vout
5	Trim	COM
6	+Vout	+Vout

Tolerance:
x.x = ±0.5mm
x.xx = ±0.25mm

PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	260.0 x 28.5 x 20.8mm
Packaging Quantity		8pcs
Storage Temperature Range		-55°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

[REC30E-2405SZ](#) [REC30E-2412DZ](#) [REC30E-2412SZ](#) [REC30E-2415DZ](#) [REC30E-2415SZ](#) [REC30E-2424SZ](#)
[REC30E-243.3SZ](#) [REC30E-4805SZ](#) [REC30E-4812DZ](#) [REC30E-4812SZ](#) [REC30E-4815DZ](#) [REC30E-4815SZ](#)
[REC30E-4824SZ](#) [REC30E-483.3SZ](#)