






ISS.	AMEND	DATE
1	ISSUED	22/06/23

**DUAL MOUNT**  
CAN BE FRONT OR REAR MOUNTED



PLAIN HOLE VARIANTS  
'X' VERSION Ø2.5  
'X1' VERSION Ø3.2



**Material:**

1. RJ12 In-Line Coupler: PC/ABS, UL94 V-0 Black
2. RJ12 In-Line Coupler Contact: Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.
3. PCB: FR4, UL94 V-0
4. FT Frame: Polyamide UL 94V-2
5. Operating Temperatures: Min -10°C Max +60°C

3x HOLE VARIANTS  
Ø3.2mm CSK 90° x Ø5.85  
'X' PLAIN Ø2.5 HOLES  
'X1' PLAIN Ø3.2 HOLES

VARIANTS	
PART NO.	HOLE DETAILS
CP30724	HOLE Ø3.2 x CSK 90° x Ø5.85
CP30724X	PLAIN HOLE Ø2.5
CP30724X1	PLAIN HOLE Ø3.2

**RoHS**  
COMPLIANT

**TOLERANCE**  
NO DEC. PLACE ±  
1 DEC. PLACE ±  
2 DEC. PLACE ±  
HOLE Ø ±  
ANGLES ±  
UNLESS OTHERWISE STATED

DO NOT SCALE

**Cliff Electronic Components Ltd.**  
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,  
Redhill, Surrey, RH1 2PF, England, UK  
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: See Notes

FINISH: See Notes

DRAWN: T.I.O

APPROVED: D.P.I

TITLE: DUAL MOUNT SLIM FT CAT3 RJ12 6P6C

DRWG. No. **CP30724**

FORM: A4DRWGf