


Application Tooling Specification Sheet



Order No. 63891-9000

FEATURES

Mini-Mac Applicator


- Directly adapts to most automatic wire processing machines
- Applicator designed to industry standard mounting and shut height 135.80mm (5.346")
- Quick set-up time; plus the crimp height, track and feed adjustments can be set without removing the applicator from the press
- Fine adjustment allows users to achieve target with little effort by adjusting in increments of .015mm (.0006") for conductor crimp height and .063mm (.0025") for insulation height
- Independent adjustment rings allow users to quickly adjust the conductor or insulation crimp height without affecting each other.

SCOPE

Revision: B

Products: Sabre™ Male Flat Blade Crimp Terminal, 18 AWG.

Terminal Series No			Order No.	Wire Size		Insulation Diameter		Strip Length	
Terminal Series No.		renninai	AWG	mm²	mm	In.	mm	ln.	
42170	43178-1001	43178-1002	43178-1003	18	0.80	2.36-3.30	.093130	3.96-5.54	.156218
43178	43178-5001	43178-5002	43178-5003						



CRIMP SPECIFICATIONS

Terr	Terminal Series No.	Bell n	nouth	Cut-off Tab	Maximum	Conductor Brush	
	Terminal Series No.	mm	ln.	mm	ln.	mm	ln.
	43178	0.25-1.00	.010039	0.50	.019	1.50	.059

	Bend up Bend down Degree		Twist Roll		Punch Width (Ref)				Seam	
Terminal Series No.					Conductor		Insulation			
					mm	In	mm	In	Seam shall not be open	
43178	3	3	4	8	3.20	.126	4.30	.169	and no wire allowed out of the crimping area	

After crimping, the conductor profile should measure the following.


	Terminal Series No.		Size	Crimp	Pull Force Minimum		
		AWG	mm ²	mm	In.	N	Lb.
ĺ	43178	18	0.80	1.78-1.88	.070074	88.9	20.0

Tool Qualification Notes:

- 1. Pull Force should be measured with no influence from the insulation crimp.
- 2. The above specifications are guidelines to an optimum crimp..

PARTS LIST

	Mini-Mac Applicator 63891-9000									
ltem	Order No	Engineering No.	Description	Quantity						
	Perishable Tooling									
	63891-9070	63891-9070	Tool Kit (All "Y" Items)	REF						
1	11-18-5413	60842A106	Conductor Punch	1 Y						
2	63445-3262	63445-3262	Conductor Anvil	1 Y						
3	11-18-5419	60843A108	Insulation Punch	1 Y						
4	63445-4322	63445-4322	Insulation Anvil	1 Y						
5	63443-0047	63443-0047	Front Cut-Off Plunger	1 Y						
6	63443-0012	63443-0012	Cut-off Plunger Retainer	1 Y						
	•	Other	Components							
7	11-18-5442	60843A123	Front Cover	1						
8	63443-0009	63443-0009	Scrap Shield	1						
9	63443-0021	63443-0021	Lower Tooling Key	1						
10	63443-0090	63443-0090	Wire Stop	1						
11	63443-6121	63443-6121	Rear Cover	1						
12	63700-0539	63700-0539	Heavy Duty Cut-off Plunger Spring	1						
13	63803-5118	63803-5118	Conductor Bushing	1						
14	63830-3005	63830-3005	Tooling Washer	1						
15	63830-3006	63830-3006	Front Plunger Striker	1						
16	63830-4002	63830-4002	Anvil Mount	1						
	Frame									
17	63801-3201	63801-3201	Тор	1						
18	63801-3282	63801-3282	Base	1						
19	63801-6550	63801-6550	Track	1						
			ardware							
20	N/A	N/A	M3 by 6 Long SHCS	2**						
21	N/A	N/A	M4 by 6 Long SHCS	2**						
22	N/A	N/A	M4 by 8 Long BHCS	4**						
23	N/A	N/A	M4 by 12 Long BHCS	2**						
24	N/A	N/A	M4 by 25 Long SHCS	2**						
25	N/A N/A		M5 by 12 Long SHCS	1**						
26	N/A	N/A	M8 by 20 Long BHCS	1**						
27	N/A	N/A	3MM by 6 Long Roll Pin	1**						
**	** Available from an industrial supply company such as MSC (1-800-645-7270).									



NOTES

- 1. Molex recommends an extra perishable tooling kit be maintained at your facility.
- 2. Verify tooling alignment by manually cycling the press and applicator before crimping under power. Check that all screws are tight.
- 3. Slugs, terminals, dirt, and oil should be kept clear of work area.
- 4. Wear safety glasses at all times.
- 5. For recommended maintenance refer to the Mini-Mac Manual.

CAUTION: This applicator should only be used in a press with a shut height of 135.80 mm (5.346"). Tooling damage could result at a lower setting

CAUTION: To prevent injury, never operate this applicator without the guards supplied with the press or wireprocessing machine in place. Reference the press or wire processing manufacturer's instruction manual.

CAUTION: Molex crimp specifications are valid only when used with Molex terminals, applicators and tooling.

Contact Information

For more information on Molex application tooling please contact Molex at 1-800-786-6539.

Visit our Web site at http://www.molex.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex: 63891-9070