




**Part Number :** [764955107](#)

**Product Description :** Impact 85 Ohm Plus 4 Pair RAM Signal Module, Right Guided, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free

**Series Number :** 76495

**Status :** Active

**Product Category :** Backplane Connectors



---

## Documents & Resources

### Drawings

[Drawing 764955107\\_sd.pdf](#)

[Packaging Design Drawing PK-70873-041-001.pdf](#)

### 3D Models and Design Files

[3D Model 764955107\\_stp.zip](#)

[Electrical Model Document EE-76495-0002-001.pdf](#)

[S-Parameter Model SP-76495-0002-001.zip](#)

[Symbol Footprint Data SYM-76495-5107-001.zip](#)

### Specifications

[Application Specification AS-76060-990-001.pdf](#)

[Product Specification PS-170540-999-001.pdf](#)

[Product Specification PS-45499-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS

- REACH SVHC

- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Backplane Connectors
Series	76495
Description	Impact 85 Ohm Plus 4 Pair RAM Signal Module, Right Guided, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free
Application	Coplanar
Component Type	Right Angle Male
Product Family	Impact Backplane Connector and Cable Assembly System
Product Name	Impact
UPC	887191367842

### Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	85Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

### Physical

Circuits (Loaded)	120
-------------------	-----

Circuits (maximum)	120
Color - Resin	Gray
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	20.129/g
Number of Columns	10
Number of Pairs	4
Number of Rows	12
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	1.20mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Pitch - Mating Interface	1.35mm, 1.90mm
Pitch - Termination Interface	1.35mm, 1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

#### Mates With / Use With

##### Mates with Part(s)

Description	Part Number
-------------	-------------

Impact 85 Ohm Plus 4 Pair Right- Angle Daughtercards	<u>170340</u>
---	---------------

---

---

This document was generated on Mar 24, 2024