# Product data sheet Characteristics

## ZCKS1H29

limit switch body ZCKS - 1NC+1NO - snap action - M20





#### Main

Main		
Range of product	OsiSense XC	
Series name	Standard format	
Product or component type	Limit switch body	
Device short name	ZCKS	
Body type	Fixed	
Product compatibility	XCKS	-
Associated head	ZCKD019 ZCKD02 ZCKD05 ZCKD06 ZCKD08 ZCKD31 ZCKD33 ZCKD34 ZCKD34 ZCKD39 ZCKD41 ZCKD55 ZCKD49 ZCKD55 ZCKD55 ZCKD59 ZCKD59	
Pady material	ZCKD029 Plastic	
Body material		
Cable entry	1 entry tapped for M20 x 1.5 cable gland	
Number of poles	2	
Contacts type and composition	1 NC + 1 NO	
Contact operation	Snap action	
Number of steps	1 1 position	
Contacts material	Silver plated contacts	
		P

## Complementary

Local display	Without		
Electrical connection	Screw-clamp terminals, clamping capacity: 1 x 0.342 x 1.5 mm²		
Positive opening	With		
Minimum actuation speed	0.01 m/min		
[le] rated operational current	3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A		
[Ithe] conventional enclosed thermal current	10 A		
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 contact block 300 V conforming to UL 508 contact block 500 V degree of pollution 3 conforming to IEC 60947-1 contact block		
Resistance across terminals	0.25 mOhm conforming to IEC 60255-7 category 3		
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60664 6 kV conforming to IEC 60947-1		
Short-circuit protection	10 A by gG cartridge fuse		
Electrical durability	5000000 cycles, DC-13 120 V, 7 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 24 V, 13 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 9 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C		
Width	40 mm		
Height	73 mm		
Depth	36 mm		
Product weight	0.08 kg		
Terminals description ISO n°1	(11-12)NC (21-22)NC		

#### Environment

IP degree of protection	IP65
IK degree of protection	IK03
Ambient air temperature for operation	-2570 °C for standard environment
Ambient air temperature for storage	-4070 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Green Premium product	
Compliant - since 1008 - Schneider Electric declaration of conformity	
Schneider Electric declaration of conformity	
Reference not containing SVHC above the threshold	
Reference not containing SVHC above the threshold	
Available	
Product environmental	
Available	
End of life manual	

#### Contractual warranty

Warranty period	18 months	