

Rundstecker isoliert Prises cylindriques isol. Pin connectors insulated

UL-No. E330536 mit Stützhülse

Werkstoff:
MS sn = Messing verzinkt

Temperaturbeständigkeit:
PVC -10°C bis +50°C

Strombelastbarkeit:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.

avec douille-support

Matière:
MS sn = laiton étamé

Résistant à une température de:
PVC -10°C à +50°C


Intensité admissible:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.




with extra support-sleeve


Material:
MS sn = tin-plated brass




Temperature range:
PVC -10°C up to +50°C

Current carrying capacity:
0.5 – 1.0 mm²/10A max.
1.5 – 2.5 mm²/15A max.
4.0 – 6.0 mm²/25A max.



| PVC | | | | | | | |
|-----------------|-------|---------------------------------------|---|---|---------|----------|---------------------------------|
| mm ² | AWG | für Stecker pour fiche for plug | Farbe Couleur Colour | Artikelnummer Numéro d'article Part-No. | L mm | øD mm | Werkzeuge Outils Toolings |
| 0.5-1 | 22-18 | Ø 4.0 mm |  | 3915 | 23 | 1.7 | 3974n, 3986c, 3986n, 3986s |
| 1.5-2.5 | 16-14 | Ø 5.0 mm |  | 3916 | 23 | 2.3 | |
| 4-6 | 12-10 | Ø 5.0 mm |  | 3917 | 25 | 3.4 | |



| PVC | | | | | | | |
|-----------------|-------|---------------------------------------|---|---|---------|----------|---------------------------------|
| mm ² | AWG | für Stecker pour fiche for plug | Farbe Couleur Colour | Artikelnummer Numéro d'article Part-No. | L mm | øD mm | Werkzeuge Outils Toolings |
| 0.5-1 | 22-18 | Ø 4.0 mm |  | 3920 | 21.5 | 1.7 | 3974n, 3986c, 3986n, 3986s |
| 1.5-2.5 | 16-14 | Ø 5.0 mm |  | 3921 | 21.5 | 2.3 | |
| 4-6 | 12-10 | Ø 5.0 mm |  | 3922 | 24 | 3.4 | |