

## Type TL Series

### Type TL Series



Tyco are pleased to offer this unique High Power, metal chip resistor for current sensing positions. It has a special metal resistive element and suitable barrier layers beneath the solder to prolong terminal life. Following the developments by semiconductor manufacturers in the production of a range of IC's for battery charge management and low voltage power supplies, the TL Series satisfies the demand for a low ohmic shunt resistor to act as a current sensor. It has particular applications in the automotive industry for sensing in EMU's.

### Key Features

- Up to 1 Watt at 70°C
- Supplied on Tape
- Ideal for Current Detection
- Wide Value Range R001 to 1R0 Possible
- Fully Automated Manufacture
- 12:06, 20:10 and 25:12 Packages Available
- Available in Distribution

### Characteristics - Electrical


	1206	2010	2512
Resistance Value Range:	R003-R20	R003-R50	R001-R50
Resistance Tolerance:	± 1%		
Power Rating:	Up to 1 watt at 70°C derating to zero at 170°C		
Operating Temperature:	-65°C to +170°C		
Inductance:	< 5 NanoHenries		
T.C.R.	±75ppm/°C (R007-R20/R50)		

### Characteristics - Mechanical

Body Construction:	Fully Welded Element
Terminations:	100% Tin
Coating:	Epoxy


### Power Derating Curve

Type	Power Rating
TL2B	0.25 Watts
TL2H*	0.5 Watts
TL3A	1.0 Watts



For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with this curve.

### Dimensions



Type	L	W	H	D
TL2B	3.2	1.6	0.6	0.5
TL2H*	5.1	2.5	0.6	0.5
TL3A	6.4	3.2	0.6	0.8

### How to Order

TL	3A	R015	F	TE
<b>Common Part</b>	<b>Power Ratings</b>	<b>Resistance Value</b>	<b>Tolerance</b>	<b>Packaging</b>
TL - Standard Part	2B - 12:06 *2H - 20:10 3A - 25:12	0.005 ohm (5 milli ohm) R005  0.015 ohm (15 milli ohms) R015  0.047 ohm (47 milli ohms) R047	F - ±1%	TE - 4000 per Reel  TDG - 2000 per Reel (2512 only)

\* - 20:10 available by special request. Minimum Orders of 10000 pcs to apply

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[TL3AR068FTDG](#) [TL2BR022FTE](#) [TL2BR033FTE](#) [TL2BR018FTE](#) [TL2BR051FTE](#) [TL2BR075FTE](#) [TL2BR015FTE](#)  
[TL2BR10FTE](#) [TL2BR047FTE](#) [TL3AR082FTDG](#) [TL3AR005FTDG](#) [TL3AR018FTDG](#) [TL3AR027FTDG](#) [TL3AR22FTDG](#)  
[TL3AR039FTDG](#) [TL3AR006FTDG](#) [TL3AR025FTDG](#) [TL3AR004FTDG](#) [TL3AR003FTDG](#) [TL2BR068FTE](#)  
[TL3AR051FTDG](#) [TL2BR01FTE](#) [TL3AR10FTDG](#) [TLRS157560ER0005FTDG](#) [TLR3A20KR003FTDG](#)  
[TLR3A20DR0015FTDG](#) [TLR3A10DR0005FTDG](#) [TLR3A10DR001FTDG](#) [TLR3A10DR00075FTDG](#)