



R13-112



Rating
16A 125V AC 10A 250V AC
Contact resistance
50mΩ Max
Insulation resistance
DC 500V 100MΩ Min
Dielectric strength
AC 1500V 1 minute
Cut-out




FEATURES

- * MATERIAL: Frame is nylon (UL flame: 94V-2). Terminals are silver plated brass.
- * Illuminated actuators are molded in PC, available with red, amber, green, blue and white colors.
- * Snap-in mounting, easy to install switch into panel.
- * Except lever type actuator (AP, BP, CP, DP, LP), watertight cover is optional.
- * Standard dimension of housing height is 14.5mm, if look for shorter height, please refer to page 1-57, item R13-208 with housing height 12.0mm.
- * R13-112B9 & R13-112B9F: The LED is built with PCB for shifting to AC rating application.
- * Watertight cover is optional.



Cut-out for X8 ROCKER



































ROCKER			
A,B,BF C,D,E, F,G,H, I		A5	
A2 E2 F2		LP	
A2B		A8,B8 B8F C8,D8 F8,E8	
B2 B2F		B9 B9F	
L		AP BP CP DP	



Ordering number instruction

R13-112 -

FUNCTION					TERMINAL
Different button (按鈕不同)					<div style="display: flex; align-items: center; gap: 10px;"> 0 2 ☐ .187" SQ </div>
A  2P SPST OFF ON	A 2  2P SPST OFF ON	A 5  2P SPST OFF ON (Gloss Finish)	A P  2P SPST OFF ON	A 2 B  2P SPST OFF ON	<div style="display: flex; align-items: center; gap: 10px;"> 0 9 ☐ PC </div> <div style="font-size: 12px; color: red; text-align: center;">A/C/D/E/F/G/H/I</div>
Illuminated / Different button (帶燈/按鈕不同)					<div style="display: flex; align-items: center; gap: 10px;"> 1 2 ☐ SO </div> <div style="font-size: 12px; color: red; text-align: center;">A/C/D/E/F/G/H/I/L</div>
B  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B 2  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B 9  3P SPST (W/O Lens) (LED) 125VAC 33KΩ / 250VAC 150KΩ	B 1 0  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B P  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	
Momentary / Illuminated / Different button (彈回/帶燈/按鈕不同)					
B F  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B 2 F  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B 9 F  3P SPST (W/O Lens) (LED) 125VAC 33KΩ / 250VAC 150KΩ			
Different position / Different button (動作特性不同/按鈕不同)					
C  3P SPDT ON	C P  3P SPDT ON	D  3P SPDT ON OFF ON	D P  3P SPDT ON OFF ON		
Momentary (彈回)					
E  2P SPST (OFF) ON	F  2P SPST OFF (ON)	G  3P SPDT (ON) ON	H  3P SPDT (ON) OFF ON	I  3P SPDT (ON) OFF (ON)	
Independent circuit / Different button (獨立迴路/按鈕不同)					
L  4P SPST (LED) OFF ON	L P  4P SPST (LED) OFF ON	L F  4P SPST (LED) OFF (ON)			
Watertight (防水)					
A 8  2P SPST OFF ON	B 8  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	B 8 F  3P SPST (NEON) 125VAC 33KΩ / 250VAC 150KΩ	C 8  3P SPDT ON	D 8  3P SPDT ON OFF ON	F 8  2P SPST OFF (ON)
E 8  2P SPST (OFF) ON					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-112BW-02-BRR-N1](#)