

Emergency Stop Switches

X6 Series



Excellent safety and design. The shortest depth behind the panel in its class.









• See website for details on approvals and standards.







Excellent safety

Third-generation

Reverse Energy Structure

IDEC's unique Reverse Energy Structure, achieved as a result of in-depth failure analysis of emergency stop switches, has resulted in this innovative emergency stop switch.

X6 series emergency stop switches provide the highest level of safety, because the unibody design eliminates the possibility of the contact bocks falling off the switch

Only 19.5 mm depth behind the panel

The short depth behind the panel reduces the required mounting space.

Depth: 30% reduction Volume: 70% reduction

(Compared with conventional emergency stop switches) Thus equipment and control panels can be made much smaller.



*1: Solder terminal. Solder/tab terminal: 23.9mm

Unparalleled design

The smooth button is ideal for applications that require utmost cleanliness, such as food processing machines or semiconductor manufacturing equipment. Also suitable for applications requiring a sleek design of emergency stop switches, such as medical equipment.










ø30 mm Button Arrow Marked

ø40 mm Button ø40 mm Button

Arrow Marked

Prevents dust build-up

The smooth and ridge-less button surface prevents dust built-up, and is also easy to clean.





Conventional Operator

Interfaces

Sensors

Two ways to reset, two button sizes, two wiring methods.

The X6 emergency stop switch can be reset either by pulling or turning. The button is available in ø30 mm and ø40 mm sizes. In addition to a red button, a yellow button is also available as a stop switch. Solder terminals and solder/tab terminals are available.

Two ways to reset







Turn to reset

Two connection methods



Solder Terminal



Solder/Tab Terminal #110

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies LED Illumination

Controllers

Operator

AUTO-ID

XA XW

XN

APEM

Switches &

Pilot Lights

Enabling Switches Safety Products Explosion Proof Terminal Blocks

> Circuit Protectors

Power Supplies

LED Illumination

Controllers

Operator

Sensors

AUTO-ID

XA

XW

XN

SEMI

Control Boxes

Ø16 X6 Series Emergency Stop Switches (Unibody)

Third-generation emergency stop switch with Reverse Energy Structure Smallest in its class

- Two button sizes-ø30mm and ø40mm
- Two ways of resetting —pulling and turning.
- Safety lock mechanism (IEC 60947-5-5; 6.2)
- Direct opening action (IEC 60947-5-5; 5.2, IEC 60947-5-1, Annex K)
- Degree of protection: IP65 (IEC60529)



Standards and Specifications

Contact Ratings

Rated Insulation Voltage (Ui) 250V Rated Thermal Current (Ith) 5A Rated Operating Voltage (Ue) 30V 125V 250V Resistive Load Rated Operating Current 3A (AC-12)Main Contacts 50/60 Hz Inductive Load 1.5A 0.75A (AC-15) Resistive Load 0.2A 2A 0.4A (DC-12) DC Inductive Load 0.22A 0.1A (DC-13)Minimum applicable load: 5V AC/DC, 1 mA (reference value)

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (May vary depending on the operating conditions and load)
- Operational current represents the classification by making and breaking currents (IEC 60947-5-1).

Note:

TÜV/CCC rating: UL rating:

AC-15 0.75A/250V, DC-13 1A/30V Standard Duty AC 0.75A/250V Standard Duty DC 1A/30V

Specifications

Applicable Standards	IEC 60947-5-1, EN 60947-5-1 IEC 60947-5-5 (Note), EN 60947-5-5 (Note) JIS C8201-5-1, JIS C8201-5-5, UL508 CSA C22.2 No.14, GB14048.5		
Operating Temperature	-25 to +60°C (no freezing)		
Operating Humidity	45 to 85% RH (no condensation)		
Storage Temperature	-45 to +80°C (no freezing)		
Operating Force	Push to lock: 10.5N Pull to reset: 8.8N Turn to reset: 0.17 N·m		
Minimum Force Required for Direct Opening Action	40N		
Minimum Operator Stroke Required for Direct Opening Action	4.5 mm		
Maximum Operator Stroke	4.5 mm		
Contact Resistance	$50 \text{ m}\Omega$ maximum (initial value)		
Insulation Resistance	100 MΩ minimum (500V DC megger)		
Overvoltage Category	II		
Impulse Withstand Voltage	2.5 kV		
Pollution Degree	3		
Operation Frequency	900 operations/hour		
Shock Resistance	Operation extremes: 150 m/s ² Damage limits: 1000 m/s ²		
Vibration Resistance	Operation extremes: 10 to 500 Hz amplitude 0.35 mm, acceleration 50 m/s² Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s²		
Mechanical Life	100,000 operations minimum		
Electrical Life	100,000 operations minimum		
Degree of Protection	IP65 (IEC 60529)		
Short-circuit Protection	250V/10A fuse (Type aM IEC 60269-1/IEC 60269-2)		
Conditional Short-circuit Current	1000A		
Terminal Style	Solder terminal, Solder/tab terminal #110		
Recommended Tightening Torque for Locking Ring	0.88 N·m		
Applicable Wire Size	1.25 mm² maximum (AWG16 maximum)		
Terminal Soldering Condition	310 to 350°C, within 3 seconds		
Weight (approx.)	ø30mm button: 13g ø40mm button: 16g		

Pushlock Pull/Turn Reset Switch (Solder Terminal)

Unmarked

Pushlock Pull/Turn Reset Switch

Package quantity: 1

T USHIOCK T UII/ TUTTI NESEL SWILCH			rackaye quantity. I
Shape	Main Contact (NC)	Par	t No.
Snape	Walli Guillagi (NG)	Solder Terminal	Solder/tab Terminal #110
ø30mm Mushroom	1NC	AB6E-3BV01PRH	AB6E-3BV01PTRH
	2NC	2NC AB6E-3BV02PRH	AB6E-3BV02PTRH
ø40mm Mushroom	1NC	AB6E-4BV01PRH	AB6E-4BV01PTRH
	2NC	AB6E-4BV02PRH	AB6E-4BV02PTRH

Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.

Arrow Marked

Pushlock Pull/Turn Reset Switch

Package quantity: 1

r usinock r un/ rum neset switch		_	rackage quality. I	
Shape	Main Contact (NC)	Par	t No.	
Snape	iviaiii Goittact (ivo)	Solder Terminal	Solder/tab Terminal #110	
ø30mm Mushroom	1NC	AB6E-3BV01PRM	AB6E-3BV01PTRM	
	2NC	AB6E-3BV02PRM	AB6E-3BV02PTRM	
ø40mm Mushroom	1NC	AB6E-4BV01PRM	AB6E-4BV01PTRM	
2NC		AB6E-4BV02PRM	AB6E-4BV02PTRM	

[•] Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.

APEM Switches & Pilot Lights Control Boxes Enabling Switches Safety Products **Explosion Proof** Terminal Blocks Relays & Sockets Circuit Protectors Power Supplies

LED Illumination


Controllers

Operator Sensors AUTO-ID


> XA XWXN

ø16 X6 Series Emergency Stop Switches (Unibody)

Dimensions



Mounting Hole Layout



The values shown on the left are the minimum dimensions for mounting with other ø16 mm pushbuttons. For other control units of different sizes and styles, determine the values according to dimensions, operation, and wiring.

	Х	Υ
ø30 mm Button	40 mm min.	40mm min.
ø40 mm Button	50 mm min.	50mm min.

• See D-047 for accessories and replacement parts.

Terminal Arrangement (Bottom View)

All dimensions in mm.



1NC: Terminals located near the TOP marking


Safety Precautions

- Turn off power to the X6 series units before installation, removal, wiring, maintenance, and inspection, Failure to turn power off may cause electrical shocks or fire hazard.
- For wiring, use wires of proper size to meet the voltage and current requirements and solder properly. Improper soldering may cause overheating and create fire hazards.

Instructions

Panel Mounting

Remove the locking ring from the operator and check that the rubber gasket is in place. Insert the operator from panel front into the panel hole. Face the side with the projection upward, and tighten the locking ring using the locking ring wrench MT-001.





Notes for Panel Mounting

Using the locking ring wrench MT-001, tighten the locking ring to a torque of 0.88 N·m. Do not use pliers. Do not apply excessive force. otherwise the locking ring will become damaged.

Wiring

- 1. Applicable wire size is 1.25 mm² maximum.
- 2. Solder the terminals using a soldering iron at 310 to 350°C for 3 seconds maximum. Do not use flow or dip soldering. SnAgCu type lead-free solder is recommended. Make sure that the soldering iron touches the terminals only, not plastic parts. Do not apply external force such as bending the terminals or applying tensile force on the
- 3. Use a non-corrosive rosin flux. To prevent the flux from entering the switch while soldering, face the terminals downward.





- 4. Because the terminal spacing is narrow, use protective tubes or heat shrinkable tubes to avoid burning the wire sheath or short cir-
- 5. Apply force on the terminals in the vertical direction to the panel only, otherwise the terminals will be damaged.

Notes for Solder/tab terminal #110

- 1. Use quick connect of #110 and 0.5mm tab thickness.
- 2. To prevent short-circuit between different poles, use protective tubes or heat shrink tubes.
- 3. Apply force on the terminals in the vertical direction to the panel only, otherwise the terminals will be damaged.

Contact Bounce

When the button is reset by pulling or turning, the NC contacts will bounce. When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).

Handling

Do not expose the switch to excessive shock and vibrations, otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



APEM

Switches &

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies LED Illumination

Controllers

Operator

Interfaces

Sensors

AUTO-ID

XA XW

XN

SFMI

Emergency Stop Switches

X Series



High level of safety with Safe **Break Action and Reverse** Energy Structure.















• See website for details on approvals and standards.

Series	Туре	Features
440 VA O	Unibody	Small, unibody emergency stop switches. Only 19.5mm behind panel.
ø16 XA Series	With Removable Contact	ø16 mm, 4-contact Emergency Stop Switch. Round form types also available.
ø22 XW Series	Standard Bezel	Four different terminal styles. Can be used on FB series control station
Ø22 AW Series	Mechanincal Indicator	Mechanical indicator on the operator body shows the contact status - green when NC contacts are closed - reducing maintenance work.
	Plastic Bezel	ø60mm jumbo mushroom, and LED push-on models available.
ø30 XN Series	Flush Bezel	Stylish design. Projects only 21mm from the panel.
	Padlockable	Padlockable models can be locked using padlocks when latched. Prevents unauthorized resetting.


APEM Switches & Pilot Lights

Control Boxes

Enabling

Switches Safety Products

Saves space



ø16 XA (w/ removable contact block)

Prevents dust build-up



NC contact OFF

NC contact ON

The round form button design is ideal for use on consumer equipment. The smooth and ridge-less button surface prevents dust build-up, and is also to clean

Normal/latched status can be checked from a distance with the mechanical indicator function.

Reduces maintenance work and improves operation efficiency.

ø22 XW (Mechanical Indicator)

Terminal Blocks Relays & Sockets

Explosion Proof

Circuit Protectors

Power Supplies LED Illumination

Controllers

Operator

Interfaces

Sensors

AUTO-ID

X6

SEMI


ø30 XN (Padlockable)

Prevents unauthorized resetting using padlocks


The padlockable emergency stop switches are push-to-lock, turn/pull-to-reset emergency stop switches. Installing the padlock(s) on latched emergency stop switches prevents unauthorized resetting.



Multiple padlocks can be installed by using a hasp



The mechanical indicator on the operator body shows the normal/latched status (green: normal).



APEM

Switches & Pilot Lights

Control Boxes

Enabling

Switches

Safety Products

Explosion Proof

Terminal Blocks

LED Illumination

Controllers

Operator Interfaces Sensors AUTO-ID

X6

XW

XN

SEMI

Circuit Protectors Power Supplies

ø16 XA Series Emergency Stop Switches (Unibody)

Small, unibody emergency stop switches suitable for equipment with small mounting space. Requires only $\emptyset 16mm \times 19.5mm$ for installation.

- ø29mm and ø40mm mushroom operators
- Degree of protection IP65 and IP40 (IEC 60529)
- Dark red (Munsell 5R4/12) and bright red (Munsell 7.5R4.5/14) colors for operators of emergency stop switches.
- Gold plated silver contacts.
- Push-to-lock, pull or turn-to-reset operator
- Safety lock mechanism (IEC 60947-5-5, 6.2)
- Direct opening action mechanism (IEC 60947-5-5, 5.2, IEC60947-5-1, Annex K)



Standards and Specifications

Contact Ratings

Rated Insulation Voltage (Ui)			250V	
Thermal Current (Ith)		5A		
ng Voltage (Ue)	30V	125V	250V
AC	Resistive Load (AC-12)	_	5A	3A
50/60Hz	Inductive Load (AC-15)	_	3A	1.5A
DC	Resistive Load (DC-12)	2A	0.4A	0.2A
Inductive Load (DC-13)	1A	0.22A	0.1A	
Contact Material			d plated si	lver
	nt (lth) g Voltage (Ue AC 50/60Hz	nt (lth) AC 50/60Hz Resistive Load (AC-12) Inductive Load (AC-15) Resistive Load (AC-12) Inductive Load (DC-12) Inductive Load (DC-13)	nt (Ith) ag Voltage (Ue) AC 50/60Hz Inductive Load (AC-12) Resistive Load (AC-15) Resistive Load (DC-12) Inductive Load (DC-13) 1A	The first of the

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (May vary depending on the operating conditions and load.)
- The rated operating currents are measured at resistive/inductive loads as specified in IEC 60947-5-1.

Specifications

Applicable Standards	IEC 60947-5-1, EN 60947-5-1 IEC 60947-5-5, EN 60947-5-5 JIS C8201-5-1, UL508, CSA C22.2 No.14 GB14048.5	
Operating Temperature	-25 to +60°C (no freezing)	
Storage Temperature	-45 to +80°C (no freezing)	
Operating Humidity	45 to 85% RH (no condensation)	
Operating Force	Push-to-lock: 10.5N Pull to reset: 10N Turn to reset: 0.16 N·m	
Minimum Force Required for Direct Opening Action	40N	
Minimum Operator Stroke Required for Direct Opening Action	4.0 mm	
Maximum Operator Stroke	4.5 mm	
Contact Resistance	50 mΩ maximum (initial value)	
Insulation Resistance	100 MΩ minimum (500V DC megger)	
Overvoltage Category	II	
Impulse Withstand Voltage	2.5 kV	
Pollution Degree	3	
Operating Frequency	900 operations/hour	
Shock Resistance	Operating extremes: 150 m/s ² Damage limits: 1000 m/s ²	
Vibration Resistance	Operating extremes: 10 to 500 Hz, amplitude 0.35mm, acceleration 50 m/s² Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s²	
Durability	Mechanical: 250,000 Electrical: 100,000 250,000 (24V AC/DC, 100mA)	
Degree of Protection	IP65, IP40 (IEC 60529)	
Short-circuit Protection	250V/10A fuse (Type aM IEC 60269-1/IEC 60269-2)	
Conditional Short-circuit Current	1000A	
Terminal Style	Solder terminal, Solder/tab #110 terminal	
Recommended Tightening Torque for Locking Ring	0.88 N·m	
Applicable Wire Size	1.25 mm² maximum (AWG16 maximum)	
Terminal Soldering Condition	310 to 350°C, within 3 seconds	
Weight (approx.)	ø29mm mushroom: 14g ø40mm mushroom: 17g	

D-015


Pushlock Pull/Turn Reset (Solder Terminal)

XA Series

Shape	Contact		t No.	① Operator Color
Snape	Contact	IP40 (contact part: black)	IP65 (contact part: yellow)	Code
ø29mm Mushroom	1NC	XA1E-BV3U01K①	XA1E-BV3U01①	
	2NC	XA1E-BV3U02K①	XA1E-BV3U02①	R: red
ø40mm Mushroom	1NC	XA1E-BV4U01K①	XA1E-BV4U01 ①	RH: bright red
	2NC	XA1E-BV4U02K①	XA1E-BV4U02①	

[•] Solder/tab #110 terminal is also available. Specify "T" before ① in the Ordering No. $\text{XA1E-BV3U02KR} \rightarrow \text{XA1E-BV3U02K}\underline{\text{T}}R$

Dimensions













ø29 mm Mushroom ø40 mm Mushroom


All dimensions in mm.

Terminal Arrangement (Bottom View)



1NC: Termimals on top

Mounting Hole Layout



• The values shown on the left are the minimum dimensions for mounting with other ø16 mm pushbut-tons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring.

	Х	Y
ø29mm Mushroom	40 mm r	ninimum
ø40mm Mushroom	50 mm r	ninimum

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets Circuit

Protectors

Power Supplies

LED Illumination

Controllers Operator

Interfaces

Sensors

AUTO-ID

Х6

XW

XN

APEM

Switches &

Pilot Lights

Enabling Switches

Control Boxes

Safety Products

Terminal Blocks

Relays & Sockets

Circuit
Protectors

Power Supplies

LED Illumination

Controllers

Operator

Sensors

Х6

XW XN SEMI

Ø16 XA Series Emergency Stop Switches (w/Removable Contact Block)

Compact size - only 27.9 mm deep behind the panel. Reliable "Safe break action."

- The depth behind the panel is only 27.9 mm for 1 to 4 contacts, both on illuminated and non-illuminated.
- IDEC's original "Safe break action" ensures that the contacts open when the contact block is detached from the operator.
- 1 to 4NC main contacts and 1NO monitor contact
- Push-to-lock, Pull or Turn-to-reset operator
- Direct opening action mechanism (IEC 60947-5-5, 5.2, IEC60947-5-1, Annex K)
- Safety lock mechanism (IEC 60947-5-5, 6.2)
- Degree of protection IP65 (IEC 60529)
- Gold plated silver contacts.
- Two operator sizes: ø29 and ø40 mm
- Dark red (Munsell 5R4/12) or bright red (Munsell 7.5R4.5/14) colors are available for the operator of non-illuminated emergency stop switches.



Standards and Specifications

Contact Ratings

NC main contacts (black) /NO monitor contact (blue)

Rate	Rated Insulation Voltage (Ui)			300V (il	luminated pa	art: 60V)
Rate	Rated Thermal Current (Ith)			5A		
Rate	ed Operating	Voltage (Ue)	30V	125V	250V
	AC 50/60	Resistive Load (AC-12)	_	3A	3A	
	Main	Hz	Inductive Load (AC-15)	_	1.5A	1.5A
ırrent	Contacts	DC	Resistive Load (DC-12)	2A	0.4A	0.2A
ting Cu		DC	Inductive Load (DC-13)	1A	0.22A	0.1A
Rated Operating Current			Resistive Load (AC-12)	-	1.2A	0.6A
Rateo			Inductive Load (AC-14)	-	0.6A	0.3A
	Contacts		Resistive Load (DC-12)	2A	0.4A	0.2A
	50		Inductive Load (DC-13)	1A	0.22A	0.1A
Con	Contact Material			Go	ld plated silv	/er

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (Operating area may vary according to the operating conditions and load types.)
- The rated operating currents are measured at resistive/inductive load types specified in IEC 60947-5-1.

Illumination Ratings

Rated Voltage	Operating Voltage	Rated Current
24V AC/DC	24V AC/DC ±10%	11 mA

Specifications

Applicable Standards	IEC60947-5-1, EN60947-5-1 IEC60947-5-5, EN60947-5-5, JIS C8201-5-1, UL991, NFPA79, UL508, CSA C22.2 No.14, GB14048.5
Operating Temperature	-25 to +60°C (no freezing) Illuminated: -25 to +55°C (no freezing)
Storage Temperature	-45 to +80°C
Operating Humidity	45 to 85% RH (no condensation)
Operating Force	Push to lock: 10.5N Pull to reset: 10N Turn to reset: 0.16 N·m
Minimum Force Required for Direct Opening Action	60N
Minimum Operator Stroke Required for Direct Opening Action	4.0 mm
Maximum Operator Stroke	4.5 mm
Contact Resistance	$50 \text{ m}\Omega$ maximum (initial value)
Insulation Resistance	100 MΩ minimum (500V DC megger)
Overvoltage Category	II.
Impulse Withstand Voltage	2.5 kV
Pollution Degree	3 (inside LED unit: 2)
Operation Frequency	900 operations/hour
Shock Resistance	Operating extremes: 150 m/s ² Damage limits: 1000 m/s ²
Vibration Resistance	Operating extremes: 10 to 500 Hz, amplitude 0.35 mm acceleration 50 m/s ² Damage limits: 10 to 500 Hz, amplitude 0.35 mm acceleration 50 m/s ²
Mechanical Life	250,000 operations minimum
Electrical Life	100,000 operations min 250,000 operations min (24V AC/DC, 100 mA)
Degree of Protection	IP65 (IEC60529)
Short-circuit Protection	250V/10A fuse (Type aM, IEC60269-1/IEC60269-2)
Conditional Short-circuit Current	1000A
Terminal Style	Solder terminal, PC board terminal
Recommended Tightening Torque for Locking Ring	0.88 N·m
Connectable Wire	1.25 mm² maximum (AWG16 maximum)
Soldering Conditions	310 to 350°C, 3 seconds maximum
Weight	ø29 mm: 23g, ø40 mm: 28g

Pushlock Pull/Turn Reset (Solder Terminal/PC Board Terminal)

Non-illuminated

Chana	NC Main	NO Monitor	tor Part No.		Operator
Shape	Contact	Contact	Solder Terminal	PC Board Terminal	Color Code
ø29mm Mushroom	1NC	_	XA1E-BV301①	XA1E-BV301V①	
	2NC	_	XA1E-BV302①	XA1E-BV302V①	
	3NC	_	XA1E-BV303①	XA1E-BV303V①	
	4NC	_	XA1E-BV304①	XA1E-BV304V①	
	1NC	1NO	XA1E-BV311①	XA1E-BV311V①	
	2NC	1NO	XA1E-BV312①	XA1E-BV312V①	
	3NC	1NO	XA1E-BV313①	XA1E-BV313V①	R: Dark red RH: Bright
ø40mm Mushroom	1NC	_	XA1E-BV401①	XA1E-BV401V①	red
	2NC	_	XA1E-BV402①	XA1E-BV402V①	
	3NC	_	XA1E-BV403①	XA1E-BV403V①	
	4NC	_	XA1E-BV404①	XA1E-BV404V①	
	1NC	1NO	XA1E-BV411①	XA1E-BV411V①	
	2NC	1NO	XA1E-BV412①	XA1E-BV412V①	
	3NC	1NO	XA1E-BV413①	XA1E-BV413V①	

- Specify a color code in place of ① in the Part No.
- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- Terminal cover (XA9Z-VL2) is ordered separately.
- For EMO Switches, see D-052.

Illuminated

Chana	NC Main	NO Monitor	Part	No.	Operator
Shape	Contact	Contact Contact	Solder Terminal	PC Board Terminal	Color
ø29mm Mushroom	1NC	_	XA1E-LV301Q4R	XA1E-LV301Q4VR	
	2NC	_	XA1E-LV302Q4R	XA1E-LV302Q4VR	1
	3NC	_	XA1E-LV303Q4R	XA1E-LV303Q4VR	1
	4NC	_	XA1E-LV304Q4R	XA1E-LV304Q4VR	1
	1NC	1NO	XA1E-LV311Q4R	XA1E-LV311Q4VR	1
	2NC	1NO	XA1E-LV312Q4R	XA1E-LV312Q4VR	1
	3NC	1NO	XA1E-LV313Q4R	XA1E-LV313Q4VR	Dorly rod only
40mm Mushroom	1NC	_	XA1E-LV401Q4R	XA1E-LV401Q4VR	Dark red only
	2NC	_	XA1E-LV402Q4R	XA1E-LV402Q4VR	1
	3NC	_	XA1E-LV403Q4R	XA1E-LV403Q4VR	1
	4NC	_	XA1E-LV404Q4R	XA1E-LV404Q4VR	1
	1NC	1NO	XA1E-LV411Q4R	XA1E-LV411Q4VR	1
	2NC	1NO	XA1E-LV412Q4R	XA1E-LV412Q4VR	7
	3NC	1NO	XA1E-LV413Q4R	XA1E-LV413Q4VR	1

- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- Terminal cover (XA9Z-VL2) is ordered separately.

Switches & Pilot Lights Control Boxes Enabling Switches Safety Products **Explosion Proof** Terminal Blocks Relays & Sockets Circuit Protectors Power Supplies LED Illumination Controllers

APEM

Operator

Sensors AUTO-ID

Х6

XWXN

ø16 XA Series Emergency Stop Switches (w/Removable Contact Block)

Dimensions

Non-illuminated

APEM
Switches &
Pilot Lights
Control Boxes

Emergency Stop Switches Enabling

Switches
Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit
Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces


Sensors


AUTO-ID


X6 XA


XW XW


SEMI













Illuminated







PC Board Layout (Bottom View)

PC Board Terminal


Non-Illuminated



Illuminated




Panel Cut-out




All dimensions in mm.

Mounting Hole Layout



	X	Υ
ø29mm Mushroom	40 mm minimum	
ø40mm Mushroom	50 mm r	ninimum

 The values shown above are the minimum dimensions for mounting with other ø16 mm pushbuttons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.




LED Unit Internal Circuit

Terminal Arrangement (Bottom View)

Non-illuminated


NC main contacts (black) only NC main contacts (black): Terminals 1-2



1NC: Terminals on right 2NC: Terminals on right and left 3NC: Terminals on right, left, and top


Illuminated

NC main contacts only (black) NC main contacts(black): Terminals 1-2



1NC: Terminals on right 2NC: Terminals on right and left 3NC: Terminals on right, left, and top With NO monitor contacts (blue)


NC main contacts (black): Terminals 1-2 NO monitor contacts (blue): Terminals 3-4



1NC: Terminals on top 2NC: Terminals on right and left

With NO monitor contacts (blue)

NC main contacts (black): Terminals 1-2 NO monitor contacts (blue): Terminals 3-4



1NC: Terminals on top

2NC: Terminals on right and left

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit

Protectors

Power Supplies

LED Illumination

Controllers

Sensors

AUTO-ID

Х6

XW

XN

APEM

Switches &

Pilot Lights

Enabling

Switches

Safety Products

Terminal Blocks

Circuit

Protectors
Power Supplies

LED Illumination

Controllers

Operator

Sensors

AUTO-ID

X6

XW

XN

SEMI

Control Boxes

Ø16 XA Series Emergency Stop Switches Round Form (w/Removable Contact Blocks)

Smooth Round Form Buttons

- IDEC's unique Reverse Energy Structure
- Depth behind the panel: 27.9mm
- Arrow marked and unmarked buttons.
- The smooth button is ideal for applications that require utmost cleanliness. Prevents dust built-up, and is also easy to clean.
- Two reset operations pushlock pull or turn reset.
- · Gold plated silver contacts.
- Direct opening action (IEC60947-5-5:5.2, IEC60947-5-1, Annex K)
- Safety lock mechanism (IEC60947-5-5:6.2)
- Degree of protection IP65 (IEC60529)



Standards and Specifications

Contact Ratings

NC main contacts (black) /NO monitor contact (blue)

300V (illuminated part: 60V) Rated Insulation Voltage (Ui) Rated Thermal Current (Ith) 5A Rated Operating Voltage (Ue) 30V 125V 250V Resistive Load 3A 3A (AC-12) 50/60 Inductive Load 1.5A 1.5A Main (AC-15)Contacts Resistive Load 2A 0.4A 0.2A (DC-12)DC Inductive Load 1A 0.22A 0.1A (DC-13) Resistive Load 1.2A 0.6A AC (AC-12) 50/60 Inductive Load 0.6A 0.3A Monitor (AC-14) Contacts Resistive Load 2A 0.4A 0.2A (DC-12)DC Inductive Load 1A 0.22A 0.1A (DC-13)Contact Material Gold plated silver

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (Operating area may vary according to the operating conditions and load types.)
- The rated operating currents are measured at resistive/inductive load types specified in IEC 60947-5-1.

Illumination Ratings

Rated Voltage	Operating Voltage	Rated Current
24V AC/DC	24V AC/DC ±10%	11 mA

Specifications

Applicable Standards	IEC60947-5-1, EN60947-5-1 IEC60947-5-5, EN60947-5-5, JIS C8201-5-1, UL991, NFPA79, UL508, CSA C22.2 No.14, GB14048.5				
Operating	-25 to +60°C (no freezing)				
Temperature	Illuminated: -25 to +55°C (no freezing)				
Storage Temperature	-45 to +80°C				
Operating Humidity	45 to 85% RH (no condensation)				
Operating Force	Push to lock: 10.5N Pull to reset: 10N Turn to reset: 0.16 N·m				
Minimum Force Required for Direct Opening Action	60N				
Minimum Operator Stroke Required for Direct Opening Action	4.0 mm				
Maximum Operator Stroke	4.5 mm				
Contact Resistance	50 mΩ maximum (initial value)				
Insulation Resistance	100 MΩ minimum (500V DC megger)				
Overvoltage Category	II				
Impulse Withstand Voltage	2.5 kV				
Pollution Degree	3 (inside LED unit: 2)				
Operation Frequency	900 operations/hour				
Shock Resistance	Operating extremes: 150 m/s ² Damage limits: 1000 m/s ²				
Vibration Resistance	Operating extremes: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s² Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s²				
Mechanical Life	250,000 operations minimum				
Electrical Life	100,000 operations min 250,000 operations min (24V AC/DC, 100 mA)				
Degree of Protection	IP65 (IEC60529)				
Short-circuit Protection	250V/10A fuse (Type aM, IEC60269-1/IEC60269-2)				
Conditional Short-circuit Current	1000A				
Terminal Style	Solder terminal, PC board terminal				
Recommended Tightening Torque for Locking Ring	0.88 N·m				
Connectable Wire	1.25 mm² maximum (AWG16 maximum)				
Soldering Conditions	310 to 350°C, 3 seconds maximum				
Weight	ø30 mm: 23g, ø40 mm: 28g				

For more information, visit http://eu.idec.com

APEM Switches & Pilot Lights Control Boxes

Enabling Switches

Pushlock Pull/Turn Reset (Solder Terminal)

Non-illuminated

			Part No. (Ordering Part No.)		
Shape	NC Main Contact NO Monitor Contact		Unmarked	Arrow Marked	
ø30 Mushroom	3NC	-	XA1E-BV3T03RH	XA1E-BV3T03RM	
	4NC	-	XA1E-BV3T04RH	XA1E-BV3T04RM	
	1NC	1NO	XA1E-BV3T11RH	XA1E-BV3T11RM	
	2NC	1NO	XA1E-BV3T12RH	XA1E-BV3T12RM	
	3NC	1NO	XA1E-BV3T13RH	XA1E-BV3T13RM	
ø40 Mushroom	3NC	_	XA1E-BV4T03RH	XA1E-BV4T03RM	
	4NC	-	XA1E-BV4T04RH	XA1E-BV4T04RM	
	1NC	1NO	XA1E-BV4T11RH	XA1E-BV4T11RM	
	2NC	1NO	XA1E-BV4T12RH	XA1E-BV4T12RM	
	3NC	1NO	XA1E-BV4T13RH	XA1E-BV4T13RM	

- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- 1NC and 2NC contacts also available.
- Terminal cover (XA9Z-VL2) is ordered separately.
- For PC board terminals, add "V" in front of "R" in the part number. Example: XA1E-BV3T03RH => XA1E-BV3T03VRH

Illuminated

			Part No. (Orde	ering Part No.)
Shape	NC Main Contact	NO Monitor Contact	Unmarked	Arrow Marked
ø30 Mushroom	1NC	-	XA1E-LV3T01Q4R	XA1E-LV3T01Q4RM
	2NC	-	XA1E-LV3T02Q4R	XA1E-LV3T02Q4RM
	3NC	-	XA1E-LV3T03Q4R	XA1E-LV3T03Q4RM
	4NC	-	XA1E-LV3T04Q4R	XA1E-LV3T04Q4RM
	1NC	1NO	XA1E-LV3T11Q4R	XA1E-LV3T11Q4RM
	2NC	1NO	XA1E-LV3T12Q4R	XA1E-LV3T12Q4RM
	3NC	1NO	XA1E-LV3T13Q4R	XA1E-LV3T13Q4RM
ø40 Mushroom	1NC	-	XA1E-LV4T01Q4R	XA1E-LV4T01Q4RM
	2NC	-	XA1E-LV4T02Q4R	XA1E-LV4T02Q4RM
	3NC	-	XA1E-LV4T03Q4R	XA1E-LV4T03Q4RM
	4NC	-	XA1E-LV4T04Q4R	XA1E-LV4T04Q4RM
	1NC	1NO	XA1E-LV4T11Q4R	XA1E-LV4T11Q4RM
	2NC	1NO	XA1E-LV4T12Q4R	XA1E-LV4T12Q4RM
	3NC	1NO	XA1E-LV4T13Q4R	XA1E-LV4T13Q4RM

- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- Terminal cover (XA9Z-VL2) is ordered separately.
- For PC board terminals, add "V" in front of "R" in the part number. Example: XA1E-LV3T01Q4R => XA1E-LV3T01Q4VR

Safety Products **Explosion Proof** Terminal Blocks Circuit Protectors Power Supplies LED Illumination Controllers Operator Interfaces Sensors AUTO-ID Х6 XWXN

APEM

Switches & Pilot Lights Control Boxes

> Enabling Switches

Safety Products

Terminal Blocks

Relays & Sockets

Circuit
Protectors

Power Supplies


LED Illumination


Operator Interfaces Sensors


AUTO-ID

ø16 XA Series Emergency Stop Switches Round Form (w/Removable Contact Blocks)


Dimensions








ø30 Mushroom





ø40 Mushroom

Х6


XW

XN

Terminal Arrangement (Bottom View)

Non-illuminated

NC main contacts (black) only NC main contacts (black): Terminals 1-2




1NC: Terminals on right

2NC: Terminals on right and left

3NC: Terminals on right, left, and top

With NO monitor contacts (blue) NC main contacts (black): Terminals 1-2 NO monitor contacts (blue): Terminals 3-4




1NC: Terminals on top

2NC: Terminals on right and left

Illuminated

NC main contacts only (black) NC main contacts(black): Terminals 1-2




1NC: Terminals on right

2NC: Terminals on right and left

3NC: Terminals on right, left, and top


With NO monitor contacts (blue) NC main contacts (black): Terminals 1-2 NO monitor contacts (blue):Terminals 3-4



1NC: Terminals on top

2NC: Terminals on right and left


Mounting Hole Layout



	Х	Υ	
ø29mm Mushroom	40 mm minimum		
ø40mm Mushroom	50 mm minimum		

 The values shown above are the minimum dimensions for mounting with other ø16 mm pushbuttons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.

LED Unit Internal Circuit




Safety Precautions

- Turn off power to the XA series emergency stop switch before starting installation, removal, wiring, maintenance, and inspection of the relays. Failure to turn power off may cause electrical shock or fire hazard.
- Use the LED unit removal tool when replacing the LED unit to avoid burn on your hands.
- Use wires of the proper size to meet the voltage and current requirements, and solder the wires correctly. If soldering is incomplete, the wire may heat during operation, causing fire hazard.

Instructions

Removing the Contact Block

First unlock the operator button. While pushing up the white bayonet ring, using a small screwdriver (width: 2.5 to 3 mm) if necessary, turn the contact block counterclockwise and pull out. Do not exert excessive force when using a screwdriver, otherwise the bayonet ring may be damaged.




Notes for Removing the Contact Block

- 1. When the contact block is removed, the monitor contact (NO contact) is closed
- 2. While removing the contact block, do not exert excessive force, otherwise the switch may be damaged.

Panel Mounting

Remove the locking ring from the operator and check that the rubber gasket is in place. Insert the operator from panel front into the panel hole. Face the side with the anti-rotation protrusion on the operator upward, and tighten the locking ring.




Notes for Panel Mounting


To mount the XA emergency stop switches onto a panel, tighten the locking ring to a tightening torque of 0.88 N·m maximum using ring wrench MT-001. Do not use pliers. Do not exert excessive force, otherwise the locking ring may be damaged.

Installing the Contact Block

First turn the bayonet ring to the unlocked position.



Align the small **\(\Lambda \)** marking on the edge of the operator base with the TOP marking on the contact block. Press the contact block onto the operator and turn the contact block clockwise until the bayonet ring clicks.




Notes for Installing the Contact Block

Check that the contact block is securely installed on the operator. When the emergency stop switch is properly assembled, the bayonet ring is in $_{
m XN}$ place as shown below.



Removing the LED Unit (Contact Block)

Pull out the LED unit while squeezing the latches on the LED unit using the LED unit removal tool (MT-101).



APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks Relays & Sockets

Circuit

Protectors Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID

X6

SFMI

Installing the LED Unit (with Removable Contact Block)

Align the to of the LED unit with the TOP marking on the contact block. Push the LED unit into the contact block.



Solder the terminal at a temperature of 310 to 350°C within 3 seconds using a soldering iron. Sn-Aq-Cu type is recommended when

using lead-free solder. When soldering, do not touch the enabling

switch with the soldering iron. Also ensure that no tensile force is applied to the terminal. Do not bend the terminal or apply excessive

3. Use a non-corrosive rosin flux. To prevent the flux from entering the

Because the terminal spacing is narrow, use protective tubes or heat shrinkable tubes to avoid burning of wire coating or short circuit.

2. Because the terminal spacing is narrow, use protective tubes or heat

3. Do not apply force on the terminals in the direction other than vertical to the mounting panel, otherwise the terminals will be damaged.

switch while soldering, face the terminals downward.

shrinkable tubes of 0.5mm minimum in thickness.

1. Use #110 receptacles for 0.5mm-thick tabs.

1. The applicable wire size is 1.25 mm² maximum.

ches

Wiring

Enabling Switches

APEM

Switches & Pilot Lights

Control Boxes

Safety Products

Explosion Proof

Expression 1 rees

Terminal Blocks
Relays & Sockets

Circuit

Protectors
Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID

PC Board Terminal

force to the terminal.


Solder/Tab Terminal #110

 When mounting a contact block on a PC board, provide sufficient rotating space for the PC board when installing and removing the contact block.

When mounting an XA emergency stop switch on a PC board, make sure that the operator is securely installed.

About PC Board and Circuit Design


- 1. Use PC boards made of glass epoxy copper-clad laminated sheets of 1.6 mm in thickness, with double-sided through hole.
- PC boards and circuits must withstand rated voltage and current, including the instantaneous current and voltage at switching.
- The minimum applicable load is 5V AC/DC, 1 mA. This value may vary according to the operating environment and load.
- 4. Within the 2.8* mm areas shown in the figure below, terminals touch the PC board, resulting in possible short circuit on the printed circuit. When designing a PC board pattern, take this possibility into consideration.



Installing Insulation Terminal Cover

To install the terminal cover (XA9Z-VL2), align the TOP marking on the terminal cover with TOP marking on the contact block, and press the terminal cover toward the contact block.

Note: For wiring, insert the wires into the holes in the terminal cover before soldering.




Contact Bounce

When the button is reset by pulling or turning, the NC main contacts will bounce. When pressing the button, the NO monitor contacts will bounce. When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).

Nameplate

When anti-rotation is not required, remove the projection from the nameplate using pliers.



Handling

Do not expose the switch to excessive shock and vibration, otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



LED Illumination

Controllers

Sensors AUTO-ID

X6 XΑ

XN SFMI

Ø22 XW Series Emergency Stop Switches

ø22 mm, 4-contact Emergency Stop Switch. Compact size—only 37.1 mm deep behind the panel (screw terminal style 48.7 mm with terminal cover). Reliable "Safe break action."

- The depth behind the panel is only 37.1 mm for 1 to 4 contacts (screw terminal style 48.7 mm with terminal cover).
- The same depth behind the panel for illuminated and non-illuminated switches.
- IDEC's original "Safe break action" ensures that the contacts open when the contact block is detached from the operator.
- 1 to 4NC main contacts and 1 or 2NO monitor contact
- Push-to-lock, Pull or Turn-to-reset operator
- Direct opening action mechanism (IEC60947-5-5, 5.2, IEC60947-5-1, Annex K)
- Safety lock mechanism (IEC60947-5-5, 6.2)
- Degree of protection IP65, IP67 (IEC60529)
- Durable, gold plated silver contacts.
- Screw terminal style is finger-safe (IP20).
- Two operator sizes: ø40 and ø60 mm
- Dark red (Munsell 5R4/12) or bright red (Munsell 7.5R4.5/14) colors are available for the non-illuminated operator.
- Push-ON illumination available (operator size: ø60)
- Connector style available to reduce wiring time and wiring mistakes.



Standards and Specifications

Contact Ratings

(NC main contacts/NO monitor contact)

			Screw Terminal		250V		
Rated Insulation		ulation Solder Terminal			2007		
Volt	Voltage (Ui)		PC Board Terminal		300V		
			Connector		125V		
Rat	ed Thermal (Current (Ith)		5A (co	nnector style	: 2.5A)	
Rat (Ue	ed Operating)	Voltage		30V 125V 250V (Note 3)			
	Contacts	AC	Resistive Load (AC-12)	-	5A (Note 1)	3A	
urrent		50/60 Hz	Inductive Load (AC-15)	ı	3A (Note 2)	1.5A	
g C		DC	Resistive Load (DC-12)	2A	0.4A	0.2A	
atin		DC	Inductive Load (DC-13)	1A	0.22A	0.1A	
Oper		AC	Resistive Load (AC-12)	ı	1.2A	0.6A	
ated	Monitor Contacts		Inductive Load (AC-14)	-	0.6A	0.3A	
2		DC	Resistive Load (DC-12)	2A	0.4A	0.2A	
		DC	Inductive Load (DC-13)	1A	0.22A	0.1A	
Co	Contact Material			Go	old plated silv	er	

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (Operating area depends on the operating conditions and load types.)
- The rated operating currents are measured at resistive/inductive load types specified in JIS C8201-5-1.

Note 1: Solder terminal/PC board terminal: 3A, Connector: 2.5A

Note 2: Solder terminal/PC board terminal: 1.5A

Note 3: Except for connector style.

Illumination Ratings

Rated Voltage	Operating Voltage	Rated Current
24V AC/DC	24V AC/DC ±10%	15 mA

Note: An LED lamp is built into the contact block and cannot be replaced.

Specifications

	IEC60947-5-1, EN60947-5-1 IEC60947-5-5 (Note), EN60947-5-5					
Applicable Standards	JIS C8201-5-1, UL508, UL991, NFPA79,					
	CSA C22.2 No. 14, GB14048.5					
Operating Temperature	Non-illuminated: -25 to +60°C (no freezing) LED illuminated: -25 to +55°C (no freezing)					
Storage Temperature	-45 to +80°C					
Operating Humidity	45 to 85% RH (no condensation)					
	Push to lock: 32N					
Operating Force	Pull to reset: 21N					
	Turn to reset: 0.27 N·m					
Minimum Force Required for Direct Opening Action	80N					
Minimum Operator Stroke						
Required for Direct Opening Action	4.0 mm					
Maximum Operator Stroke	4.5 mm					
Maximum operator stroke						
Contact Resistance	50 mΩ maximum (initial value) Connector style: 30 mΩ (Note)					
Insulation Resistance	100 M Ω minimum (500V DC megger)					
Overvoltage Category	II					
Impulse Withstand Voltage	2.5 kV					
Pollution Degree	3 (connector style: 2)					
Operation Frequency	900 operations/hour					
Shock Resistance	Operating extremes: 150 m/s ² Damage limits: 150 m/s ²					
	Operating extremes: 10 to 500 Hz, amplitude 0.35 mm,					
Vibration Resistance	acceleration 50 m/s ²					
	Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s ²					
Mechanical Life	250,000 operations minimum					
	100,000 operations minimum					
Electrical Life	250,000 operations minimum (24V AC/DC, 100 mA)					
	Panel front: IP65, IP67 (IEC 60529)					
Degree of Protection	Terminal Protection: IP20 (screw terminal, when using XW9Z-VL2MF)					
Short-circuit Protection	250V/10A fuse (Type aM, IEC60269-1/IEC60269-2)					
Conditional	1000A					
Short-circuit Current						
Terminal Style	Solder terminal, PC board terminal,					
	M3 screw terminal, Connector					
Recommended Tightening Torque for	2.0 N·m					
Locking Ring	2.0 19 111					
Looning rining	Screw terminal: 0.75 to 1.25 mm² (AWG18 to 16)					
Connectable Wire	Solder terminal / PC board terminal:					
Connectable wire	1.25 mm² maximum (AWG16 maximum)					
	Connector style: 0.3 to 0.85 mm² (AWG22 to 18)					
Soldering Conditions	310 to 350°C, 3 seconds maximum					
Recommended	0.6 to 1.0 N·m					
Tightening Torque for Terminal Screw	ט.ט נט זייט טייט טייט טייט טייט טייט טייט					
Weight	ø40 mm: 72g ø60 mm: 81g					
Note: When connecting the applicable connector to a 1m wire of 0.3 mm ² (AWG22).						



APEM
Switches &
Pilot Lights
Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit

Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces Sensors AUTO-ID

> X6 XA

XN

SEMI

XW Series Emergency Stop Switches

Non-illuminated Pushlock Pull / Turn Reset (Screw Terminal)

Shape	NC Main	NO Monitor	Par	t No.	①Operator
Silape	Contact	Contact	IP20	w/Terminal Cover	Color Code
ø40mm Mushroom	1NC	_	XW1E-BV401MF①	XW1E-BV401M①	
	2NC	_	XW1E-BV402MF①	XW1E-BV402M①	
a special section of the section of	3NC	_	XW1E-BV403MF①	XW1E-BV403M①	
	4NC	_	XW1E-BV404MF①	XW1E-BV404M①	
	1NC	1NO	XW1E-BV411MF①	XW1E-BV411M①	
	2NC	1NO	XW1E-BV412MF①	XW1E-BV412M①	
	3NC	1NO	XW1E-BV413MF①	XW1E-BV413M①	
	2NC	2N0	XW1E-BV422MF①	XW1E-BV422M①	R: Dark red
ø60mm Mushroom	1NC	_	XW1E-BV501MF①	XW1E-BV501M①	RH: Bright red
	2NC	_	XW1E-BV502MF①	XW1E-BV502M①	
	3NC	_	XW1E-BV503MF①	XW1E-BV503M①	
	4NC	_	XW1E-BV504MF①	XW1E-BV504M①	
	1NC	1NO	XW1E-BV511MF①	XW1E-BV511M①	
	2NC	1NO	XW1E-BV512MF①	XW1E-BV512M①	
	3NC	1NO	XW1E-BV513MF①	XW1E-BV513M①	
	2NC	2N0	XW1E-BV522MF①	XW1E-BV522M①	

- Specify a color code in place of ① in the Part No.
- IP20 types can be connected to solid wires only.
- For EMO Switches, see D-052.

Non-illuminated Pushlock Pull/Turn Reset (Solder Terminal/PC Board Terminal)

Chana	NC Main	NO Monitor	Par	①Operator	
Shape	Contact	Contact	Solder Terminal	PC Board Terminal	Color Code
ø40mm Mushroom	1NC	_	XW1E-BV401①	XW1E-BV401V①	
	2NC		XW1E-BV402①	XW1E-BV402V①	
	3NC	_	XW1E-BV403①	XW1E-BV403V①	
	4NC	_	XW1E-BV404①	XW1E-BV404V①	R: Dark red
	1NC	1NO	XW1E-BV411①	XW1E-BV411V①	RH: Bright red
	2NC	1NO	XW1E-BV412①	XW1E-BV412V①	
	3NC	1NO	XW1E-BV413①	XW1E-BV413V①	
	2NC	2N0	XW1E-BV4221	_	

- \bullet Specify a color code in place of $\textcircled{\scriptsize 1}$ in the Part No.
- Terminal cover (XA9Z-VL2) is ordered separately.

Pushlock Pull/Turn Reset (Connector)

Pusillock Pull/Turil Reset (Conflet	(101)			
Shape	NC Main Contact	NO Monitor Contact	Part No.	①Operator Color Code
ø40mm Mushroom				
	3NC	_	XW1E-BV403V①-BC	R: Dark red RH: Bright red

- Specify a color code in place of ① in the Part No.
- See D-036 for applicable connectors.

XW Series Emergency Stop Switches

LED Illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Chana	Illumination	Rated	NC Main	NO Monitor	Part No.		
Shape	IIIuIIIIIauoii	Voltage	Contact	Contact	IP20	w/Terminal Cover	
ø40mm Mushroom			1NC	_	XW1E-LV401Q4MFR	XW1E-LV401Q4MR	
and the same of th			2NC	_	XW1E-LV402Q4MFR	XW1E-LV402Q4MR	
	LED	24V AC/DC	3NC	_	XW1E-LV403Q4MFR	XW1E-LV403Q4MR	
			4NC	_	XW1E-LV404Q4MFR	XW1E-LV404Q4MR	
			1NC	1NO	XW1E-LV411Q4MFR	XW1E-LV411Q4MR	
			2NC	1NO	XW1E-LV412Q4MFR	XW1E-LV412Q4MR	
			3NC	1NO	XW1E-LV413Q4MFR	XW1E-LV413Q4MR	
			2NC	2N0	XW1E-LV422Q4MFR	XW1E-LV422Q4MR	

- The operator color is red only.
- IP20 types can be connected to solid wires only.

LED Illuminated Pushlock Pull/Turn Reset (Solder Terminal/PC Board Terminal)

Chana	Illumination	Rated	NC Main	NO Monitor	Part No.		
Shape	Illullillauoli	Voltage	Contact	Contact	Solder Terminal	PC Board Terminal	
ø40mm Mushroom			1NC	_	XW1E-LV401Q4R	XW1E-LV401Q4VR	
		24V AC/DC	2NC	_	XW1E-LV402Q4R	XW1E-LV402Q4VR	
	LED		3NC	_	XW1E-LV403Q4R	XW1E-LV403Q4VR	
			4NC	_	XW1E-LV404Q4R	XW1E-LV404Q4VR	
The state of the s			1NC	1NO	XW1E-LV411Q4R	XW1E-LV411Q4VR	
			2NC	1NO	XW1E-LV412Q4R	XW1E-LV412Q4VR	
			3NC	1NO	XW1E-LV413Q4R	XW1E-LV413Q4VR	
			2NC	2N0	XW1E-LV422Q4R	_	

- The operator color is red only.
- Terminal cover (XA9Z-VL2) is ordered separately.

Push-ON LED Illuminated Pushlock Pull/Turn Reset (Screw Terminal)

01		Rated	NC Main	NO Monitor	Part No.	
Shape	Illumination	Voltage	Contact	Contact	IP20	w/Terminal Cover
ø40mm Mushroom LED	LED	24V	3NC	_	XW1E-TV403Q4MFR	XW1E-TV403Q4MR
	LED	AC/DC	2NC	1NO	XW1E-TV412Q4MFR	XW1E-TV412Q4MR

- The operator color is red only.
- Push-ON is illuminated when the operator is latched, and turns off when reset.
- IP20 types can be connected to solid wires only.

Push-ON LED Illuminated Pushlock Pull/Turn Reset (Connector)

don on the manimated racinock rail/rain neset (connector)									
Shape	Illumination	Rated Voltage	NC Main Contact	NO Monitor Contact	Part No.				
ø40mm Mushroom	LED	24V AC/DC	ЗNC	_	XW1E-TV403Q4VR-BC				

- The operator color is red only.
- Push-ON is illuminated when the operator is latched, and turns off when reset. See D-036 for applicable connectors.

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks Relays & Sockets

Circuit Protectors

Power Supplies LED Illumination

Controllers Operator

Sensors

AUTO-ID

Х6

XΑ

XN

APEM
Switches &
Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Controllers

Operator
Interfaces

Protectors
Power Supplies

Sensors

AUTO-ID


XA

XN


ø22 XW Series Emergency Stop Switches

Dimensions (Non-Illuminated)


Screw Terminal (IP20)



Screw Terminal (w/terminal cover)



Solder Terminal and PC Board Terminal



All dimensions in mm.

D-029

APEM Switches & Pilot Lights Control Boxes

Enabling Switches

Safety Products **Explosion Proof** Terminal Blocks

Relays & Sockets

Power Supplies

LED Illumination

Controllers Operator Interfaces

Sensors AUTO-ID


Circuit

Protectors

Dimensions (Illuminated)


Screw Terminal (IP20) LED Illuminated


ø40mm Operator




Panel Thickness 0.8 to 6


Screw Terminal (w/terminal cover) **LED Illuminated** ø40mm Operator






Solder Terminal and PC Board Terminal LED Illuminated ø40mm Operator


















Х6 XΑ


XN

SEMI

Dimensions (Connector Style)

Non-illuminated / LED Push-ON ø40mm Operator





36.1 31.4 (when unlocked)

For applicable connectors, see D-036.

All dimensions in mm.

APEM

Switches &

Pilot Lights


Enabling Switches

Control Boxes

Safety Products

Terminal Blocks


Mounting Hole Layout



	Х	Y	
Screw Terminal	70 mm minimum		
Solder/PC Board Terminal	50 mm minimum		
Connector Style	50 mm minimum	70 mm minimum	

• The values shown above are the minimum dimensions for mounting with other ø22mm pushbuttons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.

LED Internal Circuit



Terminal Arrangement (Bottom View)

Screw Terminal Non-illuminated

4

NC main contacts only NC main contacts

Terminals 1-2

TOP Relays & Sockets *1 *2 **⋤**₩ Circuit <u>~</u> Protectors

<u>-</u>

Power Supplies LED Illumination

> Operator Interfaces

> > Sensors

AUTO-ID

Х6

XΑ

XN

SEMI


Terminals on right 2NC: Terminals on right and Controllers

Terminals on right, left,

With 1NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts: Terminals 3-4

> *1 *2 ,[= ₽'n Lef 42

1NC: Terminals on top 2NC: Terminals on right and left With 2NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts Terminals 3-4



Screw Terminal Illuminated

NC main contacts only NC main contacts: Terminals 1-2

TOF *1 *2

1NC: Terminals on right 2NC: Terminals on right and

3NC: Terminals on right, left,

Terminals 1-2 NO monitor contacts *1 *2

With 1NO monitor contacts

NC main contacts

4= 2 1NC: Terminals on top

2NC: Terminals on right and left

NO monitor contacts: TOP

With 2NO monitor contacts

NC main contacts:

X1

Screw Terminal Illuminated Push-ON

NC main contacts: Terminals 1-2




Terminals 1-2 NO monitor contacts TOP *3 *4 ıp 7₹


Х2

With 1NO monitor contacts

NC main contacts:

Terminal Marking Development





• On solder terminal and PC board terminal, the contact block is marked with contact codes (NC main contact 1-2: black, NO monitor contact 3-4: blue).

Solder Terminal / PC Board Terminal Non-illuminated

NC main contacts:

NC main contacts only NC main contacts: Terminals 1-2

> TOP Right

Terminals on right Terminals on right and

Terminals on right, left, and top

Terminals 1-2 NO monitor contacts Terminals 3-4 TOF 2

With 1NO monitor contacts

Lef Righ Terminals on top

1NC: Terminals on right and With 2NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts Terminals 3-4



Solder Terminal only

Solder Terminal / PC Board Terminal Illuminated

NC main contacts only

NC main contacts: Terminals 1-2

Terminals on right Terminals on right and

and top


Terminals on right, left,

With 1NO monitor contacts NC main contacts Terminals 1-2 NO monitor contacts Terminals 3-4

4


1NC: Terminals on top 2NC: Terminals on right and left

With 2NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts: Terminals 3-4




Solder Terminal only

Connector Style Non-illuminated



Connector Style Push-ON




For applicable connectors, see D-036.

All dimensions in mm.

Ø22 XW Series Emergency Stop Switches (Mechanical Indicator)

High level of safety with Safe Break Action. Mechanical indicator on the operator body shows the contact status - green when NC contacts are closed - reducing the maintenance work.

- IDEC's original "Safe Break Action" and "Reverse Energy Structure" ensure the safety of operator and system, when the switch is damaged due to excessive shocks.
- The mechanical indicator on the operator body shows the normal/ latched status (green: normal), Reduces maintenance work and improves operation efficiency.
- Illuminated model also available (same size as non-illuminated)
- The depth behind the panel is only 46.4 mm (w/terminal cover).
- 1 to 4NC main contacts and 1 or 2NO monitor contact
- · Push-to-lock, Pull or Turn-to-reset operator
- Direct opening action mechanism (IEC 60947-5-5, 5.2, IEC 60947-5-1, Annex K)
- Safety lock mechanism (IEC 60947-5-5, 6.2)
- Degree of protection: IP65 (IEC 60529)
- Durable, gold plated silver contacts.
- Finger-safe structure (IP20)
- UL NISD category



Standards and Specifications

Contact Ratings

(NC main contacts/NO monitor contact)

Rated Insulation Voltage (Ui)			Screw Terminal	250V		
Rate	ed Thermal C	urrent (Ith)			5A	
Rated Operating Voltage (Ue)				30V	125V	250V
	Main Contacts Monitor Contacts Monitor Contacts AC 50/60 Hz AC 50/60 Hz	Resistive Load (AC-12)	-	5A	3A	
l Ħ		Inductive Load (AC-15)	-	3A	1.5A	
Curr		DC	Resistive Load (DC-12)	2A	0.4A	0.2A
ting			Inductive Load (DC-13)	1A	0.22A	0.1A
pera		AC	Resistive Load (AC-12)	-	1.2A	0.6A
ted 0	Monitor	50/60 Hz	Inductive Load (AC-14)	-	0.6A	0.3A
Rai	문 Contacts	D0	Resistive Load (DC-12)	2A	0.4A	0.2A
		DC	Inductive Load (DC-13)	1A	0.22A	0.1A
Conf	Contact Material				ld plated sil	ver

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (Operating area depends on the operating conditions and load types.)
- The rated operating currents are measured at resistive/inductive load types specified in JIS C8201-5-1.

Illumination Ratings

Rated Voltage	Operating Voltage	Rated Current
24V AC/DC	24V AC/DC ±10%	15 mA

Note: An LED lamp is built into the contact block and cannot be replaced.

Specifications

Applicable Standards	IEC60947-5-5, EN60947-5-5 JIS C8201-5-1, UL508, UL991, NFPA79, EN418 CSA C22.2 No. 14, GB14048.5
Operating Temperature	Non-illuminated: -25 to +60°C (no freezing) LED illuminated: -25 to +55°C (no freezing)
Storage Temperature	-45 to +80°C (no freezing)
Operating Humidity	45 to 85% RH (no condensation)
Operating Force	Push to lock: 32N Pull to reset: 21N Turn to reset: 0.27 N·m
Minimum Force Required for Direct Opening Action	80N
Minimum Operator Stroke Required for Direct Opening Action	4.0 mm
Maximum Operator Stroke	4.5 mm
Contact Resistance	50 m $Ω$ maximum (initial value)
Insulation Resistance	100 MΩ minimum (500V DC megger)
Overvoltage Category	II
Impulse Withstand Voltage	2.5 kV
Pollution Degree	3
Operation Frequency	900 operations/hour
Shock Resistance	Operating extremes: 150 m/s² Damage limits: 1000 m/s²
Vibration Resistance	Operating extremes:10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s² Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s²
Mechanical Life	250,000 operations minimum
Electrical Life	100,000 operations minimum 250,000 operations minimum (24V AC/DC, 100 mA)
Degree of Protection	Panel front: IP65 (IEC 60529) Terminal Protection: IP20 (screw terminal, when using XW9Z-VL2MF)
Short-circuit Protection	250V/10A fuse (Type aM, IEC60269-1/IEC60269-2)
Conditional Short-circuit Current	1000A
Terminal Style	M3 screw terminal
Recommended Tightening Torque for Locking Ring	2.0 N·m
Connectable Wire	0.75 to 1.25 mm ² (AWG18 to 16)
Recommended Tightening Torque for Terminal Screw	0.6 to 1.0 N·m

APEM

Switches &

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Sensors

AUTO-ID

X6 XΑ

XN

SFMI

APEM
Switches &
Pilot Lights
Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Circuit
Protectors

Power Supplies

LED Illumination

Controllers

Operator

Sensors AUTO-ID

ø22 XW Series Emergency Stop Switches (Mechanical Indicator)

Non-illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Package quantity: 1

Shape	NC Main NO Monitor		Part	Button Color	
2	Contact	Contact	IP20	w/Terminal Cover	Code
ø38 mushroom with	1NC	_	XW1E-BV4TG01MFR	XW1E-BV4TG01MR	
mechanical indicator	2NC	_	XW1E-BV4TG02MFR	XW1E-BV4TG02MR	
	3NC	_	XW1E-BV4TG03MFR	XW1E-BV4TG03MR	
	4NC	_	XW1E-BV4TG04MFR	XW1E-BV4TG04MR	P (rod)
	1NC	1NO	XW1E-BV4TG11MFR	XW1E-BV4TG11MR	R (red)
	2NC	1NO	XW1E-BV4TG12MFR	XW1E-BV4TG12MR	
	3NC	1NO	XW1E-BV4TG13MFR	XW1E-BV4TG13MR	
	2NC	2N0	XW1E-BV4TG22MFR	XW1E-BV4TG22MR	

- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- IP20 types can be connected to solid wires only.

Illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Package quantity: 1

Shape	Illumi-	Rated	NC Main	NO Monitor	Part	Button	
	nation	Voltage	Contact	Contact	IP20	w/Terminal Cover	Color Code
ø38 mushroom with			1NC	_	XW1E-LV4TG01Q4MFR	XW1E-LV4TG01Q4MR	
mechanical indicator			2NC	_	XW1E-LV4TG02Q4MFR	XW1E-LV4TG02Q4MR	
	1 (FI) 1 -	24V AC/DC	3NC	_	XW1E-LV4TG03Q4MFR	XW1E-LV4TG03Q4MR	
			4NC	_	XW1E-LV4TG04Q4MFR	XW1E-LV4TG04Q4MR	R (red)
			1NC	1NO	XW1E-LV4TG11Q4MFR	XW1E-LV4TG11Q4MR	n (ieu)
			2NC	1NO	XW1E-LV4TG12Q4MFR	XW1E-LV4TG12Q4MR	
			3NC	1NO	XW1E-LV4TG13Q4MFR	XW1E-LV4TG13Q4MR	
			2NC	2N0	XW1E-LV4TG22Q4MFR	XW1E-LV4TG22Q4MR	

- Pushlock pull/turn reset switches are locked when pressed, and reset when pulled or turned clockwise.
- IP20 types can be connected to solid wires only.
- LED lamp is not removable.


X6 XA

XN

Dimensions

Screw Terminal (IP20)

Screw Terminal (w/terminal cover)



All dimensions in mm.

Circuit Protectors Power Supplies

LED Illumination Controllers

Operator Interfaces

Sensors


AUTO-ID

Х6 XΑ

XN

SEMI


Mounting Hole Layout



	Х	Υ
Screw Terminal	70 mm minimum	

. The values shown above are the minimum dimensions for mounting with other ø22mm emergency stop switches. For other emergency stop switches of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.

LED Internal Circuit



Terminal Arrangement (Bottom View)

Screw Terminal Non-illuminated

NC main contacts only NC main contacts: Terminals With 1NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts: Terminals 3-4


With 2NO monitor contacts NC main contacts: Terminals 1-2 NO monitor contacts: Terminals 3-4








Terminals on right, left, and top









T0P

*1


*2


Terminals on right, left and top

Screw Terminal Illuminated

NC main contacts only With 1NO monitor contacts NC main contacts: NC main contacts: Terminals 1-2 Terminals 1-2

NO monitor contacts: Terminals 3-4






Terminals 1-2 NO monitor contacts: Terminals 3-4

With 2NO monitor contacts

NC main contacts:



\triangle

Safety Precautions

- Turn off power to the XW series emergency stop switch before starting installation, removal, wiring, maintenance, and inspection of the relays. Failure to turn power off may cause electrical shock or fire hazard.
- For wiring, use wires of the proper size to meet the voltage and current requirements. Tighten the M3 terminal screw to a tightening torque of 0.6 to 1.0 N·m. Failure to tighten the terminal screws may cause overheating and fire.

APEM

Switches & Pilot Lights

Control Boxes

Stop Switches

Enabling

Switches
Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers
Operator

Interfaces

AUTO-ID

Х6

XA


XN

SEMI

Instructions

Removing the Contact Block

First unlock the operator button. Grab the bayonet ring \odot and pull back the bayonet ring until the latch pin clicks ②, then turn the contact block counterclockwise and pull out ③.




Notes for removing the contact block

- When the contact block is removed, the monitor contact (NO contact) is closed.
- While removing the contact block, do not exert excessive force, otherwise the switch may be damaged.
- An LED lamp is built into the contact block for illuminated pushbuttons. When removing the contact block, pull the contact block straight to prevent damage to the LED lamp. If excessive force is exerted, the LED lamp may be damaged and fail to light.

Panel Mounting

Remove the locking ring from the operator and check that the rubber gasket is in place. Insert the operator from panel front into the panel hole. Face the side without thread on the operator with TOP marking upward, and tighten the locking ring.




Notes for panel mounting

When mounting the operator onto a panel, use the optional locking ring wrench (MW9Z-T1) to tighten the locking ring. Tightening torque must not exceed 2.0 N·m. Do not use pliers. Excessive tightening will damage the locking ring. Use a nameplate for emergency stop switches (with anti-rotation function) when mounting onto a panel. Use an anti-rotation ring (HW9Z-RL) if a nameplate is not used. (Mechanical indicator types have a projection on the operator so an anti-rotation ring is not required.)


Installing the Contact Block

First unlock the operator button. Align the small ▼ marking on the edge of the operator with the small ▲ marking on the yellow bayonet ring. Hold the contact block, not the bayonet ring. Press the contact block onto the operator and turn the contact block clockwise until the bayonet ring clicks.



Notes for installing the contact block

Make sure that the bayonet ring is in the locked position. Check that the two projections on the bayonet ring are securely in place.



Wiring

Solder Terminal

- 1. The applicable wire size is 1.25 mm² maximum.
- Solder the terminal at a temperature of 310 to 350°C within 3 seconds using a soldering iron. Sn-Ag-Cu type is recommended when using lead-free solder. When soldering, do not touch the enabling switch with the soldering iron. Also ensure that no tensile force is applied to the terminal. Do not bend the terminal or apply excessive force to the terminal.
- 3. Use a non-corrosive rosin flux.
- Because the terminal spacing is narrow, use protective tubes or heat shrinkable tubes to avoid burning of wire coating or short circuit


PC Board Terminal

- When mounting a contact block on a PC board, provide sufficient rotating space for the PC board when installing and removing the contact block.
- When mounting an XW emergency stop switch on a PC board, make sure that the operator is securely installed.
- 3. Do not solder by flow soldering. Otherwise, damage may be caused.

Instructions

About PC Board and Circuit Design

- 1. Use PC boards made of glass epoxy copper-clad laminated sheets of 1.6 mm in thickness, with double-sided through hole.
- 2. PC boards and circuits must withstand rated voltage and current, including the instantaneous current and voltage at switching.
- 3. The minimum applicable load is 5V AC/DC, 1 mA. This value may vary according to the operating environment and load.
- 4. Within the 2.8* mm areas shown in the figure below, terminals touch the PC board, resulting in possible short circuit on the printed circuit. When designing a PC board pattern, take this possibility into consideration.



Screw Terminal

Applicable Crimping Terminals Solid Wire Ring Termina Spade Terminal 6.0 max ø1.2 max. ø3.2 min. 6.2 max 3.0 max 4.7 to 5.9 Crimping Terminal Crimpino Insulating Tube Terminal Insulating Tube Only solid wires can he used for IP20 units

- 1. Wire thickness: 0.75 to 1.25 mm2 (AWG18 to 16)
- Be sure to install an insulating tube on the crimping terminal.
- 2. Tighten the M3 terminal screw to a tightening torque of 0.6 to 1.0 N·m.

Connector

- 1. Connector shape
 - Tyco Electronics, D-2000 series Part No. 1376009-1 (tab header, board mount)
- Applicable connectors (to be supplied by user)
 - Tyco Electronics, D-2000 series Part No. 1-1318119-4 (receptacle housing)
 - Tyco Electronics, D-2000 series Part No. 1318107-1 (receptacle contact)
- 3. To prepare correct receptacles for the connector, read the instruction sheet and catalog of Tyco Electronics and understand the installation and wiring method.
- 4. Fasten the cable so that the connector is not pulled. Otherwise the switch may be deformed and damaged, causing malfunction or operation failure.

Installing & Removing Terminal Covers

XA9Z-VL2 (Terminal Cover for Solder Terminals)


To install the terminal cover, align the TOP marking on the terminal cover with TOP marking on the contact block, and press the terminal cover toward the contact block.




Note: For wiring, insert the wires into the holes in the terminal cover before soldering.

XW9Z-VL2M (Terminal Cover for Screw Terminals)

To install the terminal cover, align the TOP marking on the terminal cover with the TOP marking on the contact block. Place the two projections on the bottom side of the contact block into the slots in the terminal cover. Press the terminal cover toward the contact block.




To remove the terminal cover, pull out the two latches on the top side of the terminal cover. Do not exert excessive force to the latches, otherwise the latches may break.



XW9Z-VL2MF (IP20 Protection Terminal Cover)

To install the IP20 protection cover, align the TOP marking on the cover with the TOP marking on the contact block, and press the cover toward the contact block.



- 1. Once installed, the XW9Z-VL2MF cannot be removed.
- 2. The XW9Z-VL2MF cannot be installed after wiring.
- 3. With the XW9Z-VL2MF installed, crimping terminals cannot be used. Use solid
- 4. Make sure that the XW9Z-VL2MF is securely installed. IP20 cannot be achieved when installed loosely, and electric shocks may occur.

APEM

Switches 8 Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers Operator

Interfaces

Sensors

AUTO-ID

X6

XΑ

XN

SFMI

Instructions

Contact Bounce

When the button is reset by pulling or turning, the NC main contacts will bounce. When pressing the button, the NO monitor contacts will bounce.

When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).

LED Illuminated Switches

An LED lamp is built into the contact block and cannot be replaced.

Installing the Anti-rotation Ring HW9Z-RL


Align the side without thread on the operator with TOP marking, the small \triangle marking on the anti-rotation ring, and the recess on the mounting panel.



* Not required for mechanical indicator types.


Nameplate or Switch Guard

When anti-rotation is not required, remove the projection from the nameplate or switch guard using pliers. Mechanical indicator types have projections on the operator. Make sure to remove the projection on the nameplate or switch guard.



Handling

Do not expose the switch to excessive shocks and vibrations, otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



APEM
Switches &

Pilot Lights
Control Boxes

Emergeno

Stop Switches

Enabling

Switches
Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors AUTO-ID

Х6

XA

XN

Ø30 XN Series Emergency Stop Switches

ø30 mm, 4-contact Emergency Stop Switch. Padlockable and flush bezel are available.

- Padlockable, flush bezel, ø60mm jumbo mushroom, illuminated, LED push-on are available.
- IDEC's original "Safe break action" and reverse energy structure ensure the highest level of safety.
- Safety lock mechanism (IEC 60947-5-5, 6.2)
- Direct opening action mechanism (IEC 60947-5-5, 5.2, IEC60947-5-1, Annex K)
- Short depth behind the panel only 47.7 mm for 4-contact, illuminated (flush bezel: 60.4 mm, padlockable: 61.4 mm)
- Padlockable can be locked using padlocks when latched (main contact: OFF). The rugged aluminum diecast shroud allows for installing a maximum of 20 padlocks using a hasp (total weight: 1500g maximum).
- Gold plated silver contacts.
- Red (Munsell 5R4/12) or bright red (Munsell 7.5R4.5/14) colors are available.



Standards and Specifications

Contact Ratings

NC main contacts/NO monitor contacts

INC	IIIaiii cui	IIIaulo/IV	J IIIUIIIIUI GUIILA	เบเอ											
Rat	ed Insulation	Voltage (Ui)			250V										
Rat	ed Thermal (Current (Ith)		5A											
Rat	ed Operating	Voltage (Ue)		30V	125V	250V									
	AC	Resistive Load (AC-12)	-	5A	3A										
	Main	50/60 Hz Inductive Load (AC-15)		-	3A	1.5A									
rrent	Contacts	Contacts	DC	Resistive Load (DC-12)	2A	0.4A	0.2A								
ting Cu	ting Cu	БС	Inductive Load (DC-13)	1A	0.22A	0.1A									
d Opera	DC DC AC 50/60 Hz	Resistive Load (AC-12)	ı	1.2A	0.6A										
Rate	Monitor	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz	Inductive Load (AC-14)	-	0.6A	0.3A
	Contacts	DC	Resistive Load (DC-12)	2A	0.4A	0.2A									
		DC	Inductive Load (DC-13)	1A	0.22A	0.1A									
Cor	ntact Materia	I		Go	old plated Silv	ver									

- Minimum applicable load: 5V AC/DC, 1 mA (reference value) (May vary depending on the operating conditions and load types.)
- The rated operating currents are measured at resistive/inductive load types specified in IEC 60947-5-1.

Illumination Ratings (LED)

Rated Voltage	Operating Voltage	Rated Current
24V AC/DC	24V AC/DC ±10%	15 mA

Note: An LED lamp is built into the contact block and cannot be replaced.

Specifications

Applicable Standards	IEC60947-5-1, EN60947-5-1 IEC60947-5-5, EN60947-5-5 JIS C8201-5-1, UL508, UL991, NFPA79 CSA C22.2 No. 14, GB14048.5
Operating Temperature	Non-illuminated: -25 to +60°C (no freezing) Illuminated: -25 to +55°C (no freezing)
Storage Temperature	-45 to +80°C
Operating Humidity	45 to 85% RH (no condensation)
Minimum Force Required for Direct Opening Action	80N
Minimum Operator Stroke Required for Direct Opening Action	4.0 mm
Maximum Operator Stroke	4.5 mm
Contact Resistance	50 mΩ maximum (initial value)
Insulation Resistance	100 MΩ minimum (500V DC megger)
Overvoltage Category	
Impulse Withstand Voltage	2.5 kV
Pollution Degree	3
Operating Frequency	900 operations/hour
Shock Resistance	Operating extremes: 150 m/s² Damage limits: 1000 m/s²
Vibration Resistance	Operating extremes: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s ² Damage limits: 10 to 500 Hz, amplitude 0.35 mm, acceleration 50 m/s ²
Durability (at 900 operations/h, on-duration 40%)	Mechanical: 250,000 operations minimum 100,000 operations minimum 250,000 operations minimum (24V AC/DC, 100 mA)
Degree of Protection	Operator: IP65 (IEC60529) Terminal: IP20 (when XW9Z-VL2MF is installed)
Short-circuit Protection	250V/10A fuse (Type aM, IEC60269-1/IEC60269-2)
Conditional Short-circuit Current	1000A
Terminal Style	M3 screw terminal
Recommended Tightening Torque for Terminal Screw	0.6 to 1.0 N·m
Recommended Tightening Torque for Locking Ring	2.5 N·m
Applicable Wire Size	0.75 to 1.25 mm² (AWG18 to 16)
Total Weight of a Hasp and Padlocks	1500g maximum (padlockable)
Reinforced Insulation (IEC 60664-1)	Between live part and metal bezel (flush bezel, padlockable)
Weight	83g (XN1E-LV404Q4MR) 93g (XN1E-BV504MR) 89g (XN5E-LV404Q4MR) 120g (XN4E-LL404Q4MR)

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Sensors

AUTO-ID

X6

XΑ

XW

APEM
Switches &
Pilot Lights
Control Boxes

Enabling
Switches
Safety Products
Explosion Proof
Terminal Blocks
Relays & Sockets
Circuit
Protectors
Power Supplies
LED Illumination

Controllers

Operator Interfaces

Sensors AUTO-ID

> XA XW

SEMI

XN Series Emergency Stop Switches

Plastic Bezel

Non-illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Chana	NC Main	NO Monitor	Part N	lo.	①Operator
Shape	Contact	Contact	IP20 Fingersafe Terminal	w/Terminal Cover	Color Code
ø40mm Mushroom	1NC	_	XN1E-BV401MF①	XN1E-BV401M1	
	2NC	_	XN1E-BV402MF①	XN1E-BV402M1	
	3NC	_	XN1E-BV403MF①	XN1E-BV403M1	
	4NC	_	XN1E-BV404MF①	XN1E-BV404M1	
	1NC	1NO	XN1E-BV411MF①	XN1E-BV411M①	
	2NC	1NO	XN1E-BV412MF①	XN1E-BV412M1	
	3NC	1NO	XN1E-BV413MF①	XN1E-BV413M①	
	2NC	2N0	XN1E-BV422MF①	XN1E-BV422M1	R: Red
ø60mm Jumbo Mushroom	1NC	_	XN1E-BV501MF①	XN1E-BV501M①	RH: Bright red
	2NC	_	XN1E-BV502MF①	XN1E-BV502M①	
	3NC	_	XN1E-BV503MF①	XN1E-BV503M①	
	4NC	_	XN1E-BV504MF①	XN1E-BV504M①	
	1NC	1NO	XN1E-BV511MF①	XN1E-BV511M①	
	2NC	1NO	XN1E-BV512MF①	XN1E-BV512M①	
	3NC	1NO	XN1E-BV513MF①	XN1E-BV513M①	
	2NC	2N0	XN1E-BV522MF①	XN1E-BV522M①	

- \bullet Specify a color code in place of $\textcircled{\scriptsize 1}$ in the Part No.
- Only solid wires can be used on the IP20 fingersafe terminal switches.

Illuminated Pushlock Pull/Turn Reset (Screw Terminal)

		Rated Voltage	NC Main Contact	NO Monitor Contact	Part	Operator	
Shape	Illumination				IP20 Fingersafe Terminal	w/Terminal Cover	Operator Color
ø40mm Mushroom			1NC	_	XN1E-LV401Q4MFR	XN1E-LV401Q4MR	
			2NC	_	XN1E-LV402Q4MFR	XN1E-LV402Q4MR	
			3NC	_	XN1E-LV403Q4MFR	XN1E-LV403Q4MR	
	LED	24V	4NC	_	XN1E-LV404Q4MFR	XN1E-LV404Q4MR	Red only
	LED	AC/DC	1NC	1NO	XN1E-LV411Q4MFR	XN1E-LV411Q4MR	ried offig
			2NC	1NO	XN1E-LV412Q4MFR	XN1E-LV412Q4MR	
			3NC	1NO	XN1E-LV413Q4MFR	XN1E-LV413Q4MR	01Q4MR 02Q4MR 03Q4MR 04Q4MR 11Q4MR 12Q4MR 13Q4MR
			2NC	2N0	XN1E-LV422Q4MFR	XN1E-LV422Q4MR	

• Only solid wires can be used on the IP20 fingersafe terminal switches.

Illuminated Push-ON Pushlock Pull/Turn Reset (Screw Terminal)

Shape		Rated	NC Main Contact	NO Monitor Contact	Part	Operator	
	Illiimination	Voltage			IP20 Fingersafe Terminal	w/Terminal Cover	Operator Color
ø40mm Mushroom			2NC	_	XN1E-TV402Q4MFR	XN1E-TV402Q4MR	
LED	24V AC/DC	3NC	_	XN1E-TV403Q4MFR	XN1E-TV403Q4MR	Red only	
			2NC	1NO	XN1E-TV412Q4MFR	XN1E-TV412Q4MR	

- Push-ON is illuminated when the operator is latched, and turns off when reset.
- Only solid wires can be used on the IP20 fingersafe terminal switches.

Flush Bezel

Non-illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Shape	NC Main	NO Monitor	Part	Operator	
Silape	Contact	Contact	IP20 Fingersafe Terminal	w/Terminal Cover	Color Code
ø40mm Mushroom	1NC	_	XN5E-BV401MF①	XN5E-BV401M①	
	2NC		XN5E-BV402MF①	XN5E-BV402M①	
	3NC		XN5E-BV403MF①	XN5E-BV403M①	
	4NC		XN5E-BV404MF①	XN5E-BV404M①	R: Red
	1NC	1NO	XN5E-BV411MF①	XN5E-BV411M①	RH: Bright red
	2NC	1NO	XN5E-BV412MF①	XN5E-BV412M①	
	3NC	1NO	XN5E-BV413MF①	XN5E-BV413M①	
	2NC	2N0	XN5E-BV422MF①	XN5E-BV422M①	

- Specify a color code in place of ① in the Part No.
- Only solid wires can be used on the IP20 fingersafe terminal switches.

Illuminated Pushlock Pull/Turn Reset (Screw Terminal)

Shape		Datad	Rated NC Main Voltage Contact		Part	Operator	
	Illumination				IP20 Fingersafe Terminal	w/Terminal Cover	Operator Color
ø40mm Mushroom			1NC	_	XN5E-LV401Q4MFR	XN5E-LV401Q4MR	
			2NC	_	XN5E-LV402Q4MFR	XN5E-LV402Q4MR	
			3NC	_	XN5E-LV403Q4MFR	XN5E-LV403Q4MR	
	LED	24V	4NC	_	XN5E-LV404Q4MFR	XN5E-LV404Q4MR	Red only
LED	LED	AC/DC	1NC	1NO	XN5E-LV411Q4MFR	XN5E-LV411Q4MR	neu only
			2NC	1NO	XN5E-LV412Q4MFR	XN5E-LV412Q4MR	
			3NC	1NO	XN5E-LV413Q4MFR	XN5E-LV413Q4MR	
			2NC	2N0	XN5E-LV422Q4MFR	XN5E-LV422Q4MR	

[•] Only solid wires can be used on the IP20 fingersafe terminal switches.

Illuminated Push-ON Pushlock Pull/Turn Reset (Screw Terminal)

		Rated	NC Main	NO Monitor	Part	No.	- Operator Color
Shape	Illumination	Voltage	Contact	Contact	IP20 Fingersafe Terminal	w/Terminal Cover	
Ø40mm Mushroom	Omm Mushroom LED		2NC	_	XN5E-TV402Q4MFR	XN5E-TV402Q4MR	
		24V AC/DC	3NC	_	XN5E-TV403Q4MFR	XN5E-TV403Q4MR	Red only
			2NC	1NO	XN5E-TV412Q4MFR	XN5E-TV412Q4MR	

- Push-ON is illuminated when the operator is latched, and turns off when reset.
- Only solid wires can be used on the IP20 fingersafe terminal switches.

APEM Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks Relays & Sockets Circuit Protectors

Power Supplies LED Illumination

Controllers

Sensors

AUTO-ID

Х6 XA XW

Enabling Switches Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit
Protectors

Power Supplies

LED Illumination

Controllers

Operator

Sensors AUTO-ID

X6

XW

SEMI

XN Series Emergency Stop Switches

Padlockable

Non-illuminated Pushlock Turn Reset (Padlockable) (Screw Terminal)

Shape	NC Main	NO Monitor	Part	Operator	
Silape	Contact Contact		IP20 Fingersafe Terminal	w/Terminal Cover	Color
ø44mm Mushroom	1NC	_	XN4E-BL401MFRH	XN4E-BL401MRH	
	2NC	_	XN4E-BL402MFRH	XN4E-BL402MRH	
	3NC	_	XN4E-BL403MFRH	XN4E-BL403MRH	
	4NC	_	XN4E-BL404MFRH	XN4E-BL404MRH	Bright red only
9	1NC	1NO	XN4E-BL411MFRH	XN4E-BL411MRH	bright red only
	2NC	1NO	XN4E-BL412MFRH	XN4E-BL412MRH	
	3NC	1NO	XN4E-BL413MFRH	XN4E-BL413MRH	
	2NC	2N0	XN4E-BL422MFRH	XN4E-BL422MRH	

- Only solid wires can be used on the IP20 fingersafe terminal switches.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See D-050.

Illuminated Pushlock Turn Reset (Padlockable) (Screw Terminal)

		Datad	NC Main	NO Monitor	Part	No.	Omereter	
Shape	Illumination	Rated Voltage	Contact	Contact	IP20 Fingersafe Terminal	w/Terminal Cover	Operator Color	
ø44mm Mushroom			1NC	_	XN4E-LL401Q4MFR	XN4E-LL401Q4MR		
				2NC	_	XN4E-LL402Q4MFR	XN4E-LL402Q4MR	
			3NC	_	XN4E-LL403Q4MFR	XN4E-LL403Q4MR		
	LED	24V	4NC	_	XN4E-LL404Q4MFR	XN4E-LL404Q4MR	Red only	
	LED	AC/DC	1NC	1NO	XN4E-LL411Q4MFR	XN4E-LL411Q4MR	neu only	
			2NC	1NO	XN4E-LL412Q4MFR	XN4E-LL412Q4MR		
			3NC	1NO	XN4E-LL413Q4MFR	XN4E-LL413Q4MR		
			2NC	2N0	XN4E-LL422Q4MFR	XN4E-LL422Q4MR		


- Only solid wires can be used on the IP20 fingersafe terminal switches.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See D-050.

LED Push-ON Pushlock Turn Reset (Padlockable) (Screw Terminal)


			Dotod	NC Main	NO Monitor	Part	No.	Operator	
	Shape	Illumination	Rated Voltage	NC Main Contact	Contact	IP20 Fingersafe Terminal	w/Terminal Cover	Color	
	ø44mm Mushroom								
-	-			2NC	_	XN4E-TL402Q4MFR	XN4E-TL402Q4MR		
		LED	24V AC/DC	3NC	_	XN4E-TL403Q4MFR	XN4E-TL403Q4MR	Red only	
				2NC	1NO	XN4E-TL412Q4MFR	XN4E-TL412Q4MR		

- \bullet Push-ON is illuminated when the operator is latched, and turns off when reset.
- \bullet Only solid wires can be used on the IP20 fingersafe terminal switches.
- Padlocks and hasps are not supplied with the emergency stop switches and must be ordered separately. See D-050.

Dimensions



Panel Cut-out



M3 Terminal

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID

Panel Cut-out

Locking Ring

M3 Terminal

Х6

XA

XW

SEMI

APEM Switches &

Pilot Lights

Enabling Switches Safety Products Explosion Proof

Terminal Blocks Relays & Sockets Circuit Protectors Power Supplies LED Illumination Controllers Operator

> Sensors AUTO-ID


> > Х6 XΑ XW

SEMI

Control Boxes

Dimensions

Flush Bezel Non-Illuminated IP20 Fingersafe w/Terminal Cover Locking Ring Locking Ring M3 Terminal Screws



All dimensions in mm.

For more information, visit http://eu.idec.com

^{*1)} Make sure that the panel cut-out is as shown in the drawing as the operator has a projection for anti-rotation.

APEM

Switches & Pilot Lights

Control Boxes


Enabling Switches

Safety Products **Explosion Proof**


Terminal Blocks Relays & Sockets Circuit Protectors

Dimensions


Padlockable Non-Illuminated IP20 Fingersafe




w/Terminal Cover




Illuminated/Push-ON IP20 Fingersafe



w/Terminal Cover






Power Supplies LED Illumination

> Controllers Operator

> > Sensors

AUTO-ID




	Х	Y	
Plastic Bezel	70 mm minimum		
Flush Bezel	70 mm minimum		

*1) Make sure that the panel cut-out is as shown in the drawing as the operator has a projection for anti-rotation.

- The values shown above are the minimum dimensions for mounting with other ø30 mm pushbuttons. For other control units of different sizes and styles, determine the values according to the dimensions, operation, and wiring convenience.
- For padlockable, determine the values according to the size and number of padlocks and hasp.

LED Unit Internal Circuit



Х6

XΑ XW

SEMI

Enabling

Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Power Supplies

LED Illumination

Controllers

Operator

Interfaces

Sensors

Х6

XA XW

SEMI

Circuit Protectors

Terminal Arrangement

Terminal Arrangement (Bottom View)

Non-illuminated NC main contacts only




1NC: Terminals on right 2NC: Terminals on right and left

Terminals on right, left, and top

With 1NO monitor contact *1 *2 *2 Right *2 * *4 *3

> 1NC: Terminals on top 2NC: Terminals on right and left

With 2NO monitor contacts *3 *4 Right *4 *3



Applicable Crimping Terminal

· Be sure to install an insulating tube on the crimping terminal.

Spade Terminal


4.7 to 5.9


4.7 to 5.9

Insulation Tube

Wire

Push-0N






2NC: Terminals on right and left Terminals on right,

left, and top

Contact With 1NO monitor 1-2: NC main contact (black)

Right

3-4: NO monitor contact (blue) Contact Number (1-4) Starting with the contact clockwise direction.




With 2NO monitor

*3 *4

contacts

Illuminated





1NC: Terminals on right 2NC: Terminals on right and left

Terminals on right, left, and top

With 1NO monitor contact

contact

*3 *4

LED 7

34

X1 X2



1NC: Terminals on top 2NC: Terminals on right and left

Solid Wire

Ring Terminal



. Only solid wire can be used for IP20.


• See D-050 for accessories and replacement parts.

All dimensions in mm.

Operating Instructions

Removing the Contact Block

First unlock the operator button. Grab the yellow bayonet ring ① and pull back the bayonet ring until the latch pin clicks ②, then turn the contact block counterclockwise and pull out 3.




Notes for removing the contact block

- 1. Do not attempt to remove the contact block while the operator is latched, otherwise the switch may be damaged.
- 2. When the contact block is removed, the monitor contact (NO contact)
- 3. While removing the contact block, do not use excessive force, otherwise the switch may be damaged.
- 4. An LED lamp is built into the contact block for illuminated pushbuttons. When removing the contact block, pull the contact block straight to prevent damage to the LED lamp. If excessive force is used, the LED lamp may be damaged and fail to light.

Panel Mounting


Remove the locking ring from the operator and check that the rubber gasket is in place. Insert the operator from panel front into the panel hole. Face the side without thread on the operator with TOP marking upward, and tighten the locking ring using ring wrench XN9Z-T1 or TWST-T1 to a torque of 2.5 N·m maximum.



When using a nameplate When using a nameplate HNAV-□, break the projection from the nameplate using pliers.

Installing the Contact Block

First unlock the operator button. Align the small ▼ marking on the edge of the operator with the small A marking on the yellow bayonet ring. Hold the contact block, not the bayonet ring. Press the contact block onto the operator and turn the contact block clockwise until the bayonet ring clicks.



Notes for installing the contact block

- 1. Do not attempt to install the contact block when the operator is latched, otherwise the switch may be damaged.
- 2. Make sure that the bayonet ring is in the locked position.

Installing & Removing Terminal Covers

XW9Z-VL2M

To install the terminal cover, align the TOP marking on the terminal cover with the TOP marking on the contact block. Place the two projections on the bottom side of the contact block into the slots in the terminal cover. Press the terminal cover toward the contact block.

To remove the terminal cover, pull out the two latches on the top side of the terminal cover. Do not exert excessive force to the latches, otherwise the latches may break.

IP20 Fingersafe Terminal Cover XW9Z-VL2MF

To install the IP20 fingersafe terminal cover, align the TOP marking on the cover with the TOP marking on the contact block, and press the cover toward the contact block.

Notes:

- 1. Once installed, the XW9Z-VL2MF cannot be removed.
- 2. With the XW9Z-VL2MF installed, crimping terminals cannot be used. Use solid wires.
- 3. The XW9Z-VL2MF cannot be installed after wiring.
- 4. Make sure that the XW9Z-VL2MF is securely installed. IP20 cannot be achieved when installed loosely, and electric shocks may occur.

Notes for Operation

When using the XN emergency stop switches in safety-related part of a control system, observe safety standards and regulations of the relevant country or region. Also be sure to perform a risk assessment before operation.

Wiring

Tighten the M3 terminal screws to a torque of 0.6 to 1.0 N·m.

Contact Bounce


When the button is reset by pulling or turning, the NC main contacts will bounce. When pressing the button, the NO monitor contacts will

When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).


LED Illuminated Switches


An LED lamp is built into the contact block and cannot be replaced.

Do not expose the switch to excessive shocks and vibrations, for example by operating the switch with tools. Otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



TOP Marking (Pull)





APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products **Explosion Proof**

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies LED Illumination

Controllers

Operator

Sensors

AUTO-ID

X6

XΑ XW

SFMI

Enabling
Switches
Safety Products
Explosion Proof
Terminal Blocks
Relays & Sockets
Circuit
Protectors
Power Supplies
LED Illumination
Controllers
Operator
Interfaces
Sensors
AUTO-ID

Accessories and Replacement Parts (ø16 X6/XA Series Emergency Stop Switches)

Package quantity: 1

Description & Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks	
Ring Wrench	Metal (nickel-plated brass)	MT-001	MT-001	1	Used to tighten the locking ring when installing the XA emergency stop switch onto a panel.	
Locking Ring	Polyamide	XA9Z-LN	XA9Z-LNPN10	10	• Black	
Terminal Cover	PBT	XA9Z-VL2	XA9Z-VL2PN02	2	White Used for solder terminals. Also applicable to the XW series.	
LED Unit	For Solder Terminal	XA9Z-LED2R	XA9Z-LED2R		Replacement LED unit for illumi-	
600	For PC Board Terminal XA9Z-LED2V		XA9Z-LED2VR XA9Z-LED2VR		nated (for XA series only).	
LED Unit Removal Tool	Stainless Steel	MT-101	MT-101	·	Used for removing the LED unit.	

Nameplates (for ø16 X6/XA Emergency Stop Switches)

Package quantity: 1

Description	Legend	Part No.	Material	Plate Color	Legend Color
For a 20mm Operator	(blank)	HAAV-0		Valley	Black
For ø30mm Operator	EMERGENCY STOP	HAAV-27	Dolyamida		
F 140 0	(blank)	HAAV4-0	Polyamide	Yellow	DIACK
For ø40mm Operator	EMERGENCY STOP	HAAV4-27			

[•] Cannot be used with a switchguard.


For ø30mm Operator

SEMI

0435 076

• Panel thickness when using the nameplate: 0.5 to 2 mm

For ø40mm Operator



Enabling Switches Safety Products **Explosion Proof**

Relays & Sockets Circuit Protectors Power Supplies LED Illumination Controllers Operator

Sensors AUTO-ID

SEMI

Accessories (ø22 XW Series Emergency Stop Switches)

Description & Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks
Ring Wrench	Metal (nickel-plated brass) (weight: approx. 150g)	MW9Z-T1	MW9Z-T1	1	Used to tighten the locking ring when installing the XW emergency stop switch onto a panel. 110 0
Anti-rotation Ring	Ring: Polyamide Gasket: Nitryl rubber	HW9Z-RL	HW9Z-RLPN10	10	The anti-rotation ring is used for preventing the operator from turning. Top
Terminal Cover	РВТ	XA9Z-VL2	XA9Z-VL2PN02	2	White Used for solder terminals.
Terminal Cover	PPE	XW9Z-VL2M	XW9Z-VL2MPN02	2	Black Used for screw terminals. Attached to IP20 protection cover units.
IP20 Protection Cover	Polyamide	XW9Z-VL2MF	XW9Z-VL2MFPN02	2	Black Used on terminals for IP20 finger protection. Only solid wires can be used. The IP20 protection cover cannot be removed once installed.
Ring Adapter	Rubber on metal base	XW9Z-A30E	XW9Z-A30EPN02	2	Yellow panel surface Used for installing XW1E emergency stop switches in ø30mm mounting hole. Can be used for XW1E emergency stop switches only. IP65 protection. Cannot be used with nameplates. Panel thickness when mounted: 0.8 to 3.0 mm Adapter Washer *(*: A or B) Note 1: Adapter washer thickness (t) A = 1.2 mm B = 0.8 mm Panel Mounting Adapter Gasket Adapter Gasket Adapter Washer A Adapter Washer B Panel Adapter Gasket Adapter Washer A Adapter Washer B

- XW emergency stop switches of screw terminal are provided with a terminal cover.
- All dimensions in mm.

Nameplate (for ø22 Emergency Stop Switches)

Description	Legend	Part No.	Ordering No.	Package Quantity	Material	Plate Color	Legend Color
For a 10mm Operator	(blank)	HWAV-0-Y	HWAV-0-Y		Polyamide	Yellow	Black
For ø40mm Operator	EMERGENCY STOP	HWAV-27-Y	HWAV-27-Y		Folyamile		
	(blank)	HWAV5-0	HWAV5-0		DDT		
For ø60mm Operator	EMERGENCY STOP	HWAV5-27			PBT		
	EMERGENCY STOP	HWAV5F-27	HWAV5F-27PN10	10	PET film sticker		

APEM
Switches &
Pilot Lights

Control Boxes

Stop Switches

Enabling Switches Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers


Operator Interfaces

Sensors

AUTO-ID


Dimensions

For ø40mm Operator




• Panel thickness when using the nameplate: 0.8 to 4.5 mm

For ø60mm Operator



• Panel thickness when using the nameplate: 0.8 to 4 mm

Sticker Nameplate for ø60mm Operator



All dimensions in mm.

Maintenance Parts (for ø22 Emergency Stop Switches)

Description & Shape	Material	Part No.	Ordering No.	Package Quantity	Dimensions (mm)
Locking Ring Ø28.4 H5 M22 P1	Polyamide (black)	HW9Z-LN	HW9Z-LNPN05	5	Cannot be used on XW Series (mechanical indicator)
Washer	Nityl rubber	HW9Z-WM	HW9Z-WMPN10	10	10.5 02.6 0 = 0.15
Locking Ring ø27.8 t=5.0	Polyamide	CW9Z-LN	CW9Z-LNPN05	5	For use on XW Series (mechanical indicator) only.

X6 XA XW XN SEMI

Enabling Switches Safety Products **Explosion Proof** Terminal Blocks Relays & Sockets Circuit Protectors Power Supplies LED Illumination Controllers Operator Interfaces Sensors AUTO-ID

SEMI

Accessories and Replacement Parts (for ø30 XN Series Emergency Stop Switches)

Name & Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks
Terminal Cover	PPE	XW9Z-VL2M	XW9Z-VL2MPN02	2	Black Used for screw terminals. Attached to IP20 protection cover units.
IP20 Fingersafe Terminal Cover	Polyamide	XW9Z-VL2MF	XW9Z-VL2MFPN02	2	Black Used to change terminal cover to IP20 fingersafe terminal. Only solid wires can be used. Once installed, IP20 terminal cover cannot be removed.
Ring Wrench	Brass	XN9Z-T1	XN9Z-T1	1	Used to tighten the locking ring when installing the XN emergency stop switch onto a panel. 90 90
Ring Wrench	Steel Trivalent chromate plating	TWST-T1	TWST-T1	1	Used to tighten the locking ring when installing the XN emergency stop switch onto a panel. Output Company to the company to th

- The XN series emergency stop switches are supplied with either terminal cover or IP20 fingersafe terminal cover.
- · Padlocks and hasps are not supplied and must be ordered separately.

Nameplates (for ø30 Emergency Stop Switches)

Description & Shape	Legend	Part No.	Package Quantity	Dimensions (mm)
	(blank)	HNAV-0	4	Polyamide Mounting panel thickness XN4E-□L4: 1.0 to 4.5 mm XN□E-□V4: 1.0 to 3.5 mm
	EMERGENCY STOP	HNAV-27	l	430 1.5 1.0

Plate color: Yellow (Munsell 2.5Y 8/10 or equivalent), Legend: Black

Padlock and Hasp


Padlocks and hasps of the following specifications can be used with padlockable emergency stop switches.

Padlock Size

a	b	С	d
7 mm maximum	7 mm maximum 19 mm minimum		15 mm minimum (Note)

Note: When the padlock is installed from the side of the bezel, dimension d requires a minimum of 6 mm. When the padlock is installed from the front of the button, dimension d requires a minimum of 15 mm.

Recommended Hasp



Maker	Part No.
PANDUIT CORP.	PSL-HD3 PSL-1A
Master Lock® Company LLC	420, 421

Use only padlocks or hasps that satisfy the specifications shown on the left. The maximum total weight for padlocks and hasps is 1500g. Make sure that the total weight does not exceed 1500g, otherwise the XN emergency stop switch may be damaged.

Make sure that locking and unlocking of the padlock and hasp do not interfere with other devices.

Padlocks and hasps are available from the following manufacturers.

Manufacturer	URL		
PANDUIT CORP.	http://www.panduit.com/		
Master Lock® Company LLC	http://www.masterlock.com/		

Emergency Stop Guard for Machinery (Protective Shroud)

If the safety requirements of ISO13850:2015 4.3.2 or 4.5 is satisfied, the switchguard can be used safely by combining IDEC's switchguard and emergency stop switch, which is approved by TÜV Rheinland in ISO13850:2015 to be used as protective shroud with emergency stop switch.

APEM

Switches & Pilot Lights

Control Boxes

Stop Switches

Enabling

Switches
Safety Products

Explosion Proof

Terminal Blocks

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID

XA XW

SEMI

In the past, emergency stop switches with switch guards (same definition as the term "protective shroud" used in standards) could not be used on machine tools or food processing machines in compliance with ISO/IEC standards.

However, in the latest revision, the use of a protective shroud is permitted with conditions. This is because the "Prevention of unintended actuation of an emergency stop device" was added as a safety requirement and the definition of a protective shroud is as below.

ISO13850:2015 3.7 protective shroud (protective shroud)

mechanincal measure provided to reduce the possibility of unintended actuation of an emergency stop device.

Protective shroud can be used under the following conditions:

ISO13850:2015 4.5 Prevention of unintended acuation of an emergency stop device

The emergency stop device shall be designed to avoid unintended actuation.

The actuation of the emergency stop device shall not be impaired.

To prevent unintended actuation of the emergency stop device some precautions can be taken, e.g.:

- locate the emergency stop device away from foreseeable heavily trafficked areas,
- select the type of emergency stop device,
- select appropriate size or shape of the emergency stop device, or
- mount the emergency stop device within a recessed surface of the surrounding control panel.

The use of a protective shroud around the emergency stop device should be avoided, except when necessary to prevent unintended actuation and other measures are not practicable.

For emergency stop devices intended to be acutated by the hand the measures against unintended actuation shall not impede or hinder actuation with the palm of the hand, from any foreseeable position of the machine operator and others who could need to actuate them.

For details on protective shroud, see D-055.

Enabling Switches

Safety Products

Explosion Proof

SEMI EMO Switch Guards

SEMI Emergency Off (EMO) Switches

ø16mm XA Series EMO Switches (Solder Terminal) (Pushlock Turn Reset Switch)

Package Quantity: 1

Shape	NC Main Contact	NO Monitor Contact	Part No.
ø40mm Mushroom	1NC	_	XA1E-BV401RH-EM0
	2NC	_	XA1E-BV402RH-EMO
EMO	3NC	_	XA1E-BV403RH-EMO
	4NC	_	XA1E-BV404RH-EMO
	1NC	1NO	XA1E-BV411RH-EMO
	2NC	1NO	XA1E-BV412RH-EMO
	3NC	1NO	XA1E-BV413RH-EMO

- Button color is bright red (RH).
- For detailed specifications and instructions, see website.

ø22mm XW Series EMO Switch (Pushlock Turn Reset Switch)

Package Quantity: 1

Terminal Blocks Relays & Sockets Circuit Protectors Power Supplies

Package Quantity: 1

LED Illumination Controllers

Operator

Sensors

AUTO-ID

Х6 XΑ

XW

XN

Chana	NC Main Contact	NO Manitar Cantact	Part No.		
Shape	NC Main Contact	NO Monitor Contact	IP20 Fingersafe Terminal	w/Terminal Cover	
ø40mm Mushroom	1NC	_	XW1E-BV401MFRH-EM0	XW1E-BV401MRH-EM0	
and the	2NC	_	XW1E-BV402MFRH-EM0	XW1E-BV402MRH-EM0	
The same of the sa	3NC	_	XW1E-BV403MFRH-EM0	XW1E-BV403MRH-EM0	
	4NC	_	XW1E-BV404MFRH-EM0	XW1E-BV404MRH-EM0	
-VO	1NC	1NO	XW1E-BV411MFRH-EM0	XW1E-BV411MRH-EMO	
	2NC	1NO	XW1E-BV412MFRH-EM0	XW1E-BV412MRH-EMO	
	3NC	1NO	XW1E-BV413MFRH-EM0	XW1E-BV413MRH-EMO	
	2NC	2N0	XW1E-BV422MFRH-EM0	XW1E-BV422MRH-EM0	

- Button color is bright red (RH).
- For detailed specifications and instructions, see website.

ø22mm HW Series EMO Switches (Screw Terminal) (Pushlock Turn Reset Switch)

Shape	Contact Arrangement	Part No.	Button Color	
ø40mm	1NC	HW1B-V401R-EM0		
Mushroom	1NO-1NC	HW1B-V411R-EMO		
EMO	2NC	HW1B-V402R-EM0	Red only	
Lie	2NO-2NC	HW1B-V422R-EM0		

· For detailed specifications and instructions, see website

FB Series Control Boxes

ø22mm HW Series EMO Switch

Package Quantity: 1

W_L	p22mm mw ochos Lino Switch							
III m	Shape		NO	Part	No.			
ination			IVIODITOR	Without SEMI Switch Guard	With SEMI Switch Guard			
Non	HW Series EMO Switch (Pushlock Turn Reset)	1NC		FB1W-HW1B-V401R-EM0-Y0	FB1W-HW1B-V401R-EM0-Y□			
n-illuminated		2NC	_	FB1W-HW1B-V402R-EM0-Y0	FB1W-HW1B-V402R-EM0-Y□			
ated		1NC	1NO	FB1W-HW1B-V411R-EMO-Y0	FB1W-HW1B-V411R-EM0-Y□			

ø22mm XW Series FMO Switch

Package Quantity: 1

VLL	ZZZIIIII XVV OSITOS LINO OVITOTI								
■		NC Main	NO	Part	No.				
Illumination	Shape	Contact	Monitor Contact	Without SEMI Switch Guard	With SEMI Switch Guard				
П	ø22mm XW Series Emergency	1NC	_	FB1W-XW1E-BV401MRH-EM0-Y0	FB1W-XW1E-BV401MRH-EMO-Y□				
	Stop Switch 2NC Pulhlock Pull/Turn Reset 3NC	2NC		FB1W-XW1E-BV402MRH-EM0-Y0	FB1W-XW1E-BV402MRH-EM0-Y□				
무		_	FB1W-XW1E-BV403MRH-EM0-Y0	FB1W-XW1E-BV403MRH-EM0-Y□					
		4NC	_	FB1W-XW1E-BV404MRH-EM0-Y0	FB1W-XW1E-BV404MRH-EM0-Y□				
≣	illuminated	1NC	1N0	FB1W-XW1E-BV411MRH-EM0-Y0	FB1W-XW1E-BV411MRH-EMO-Y□				
ate		2NC	1N0	FB1W-XW1E-BV412MRH-EM0-Y0	FB1W-XW1E-BV412MRH-EMO-Y□				
12	E10	3NC	1N0	FB1W-XW1E-BV413MRH-EM0-Y0	FB1W-XW1E-BV413MRH-EMO-Y□				
		2NC	2N0	FB1W-XW1E-BV422MRH-EM0-Y0	FB1W-XW1E-BV422MRH-EMO-Y□				

Note: Insert a code of SEMI switch guard in place of ☐ in Part No. (2: HW9Z-KG3, 3: HW9Z-KG4) HW9Z-KG3 and HW9Z-KG4 are compliant with SEMI S2. See D-055 for details.

Safety Products

Relays & Sockets Circuit Protectors

Power Supplies

LED Illumination

Controllers Operator

Interfaces Sensors

AUTO-ID

Х6 XΑ


XW

XN


SEMI EMO Switch Guards

Dimensions


ø16mm XA Series EMO Switches




ø22mm XW Series EMO Switches



ø22mm HW Series EMO Switches






- For 1NC contact, the contact block will mount on the opposite side.
- See B-227 for wiring.
- · Integrated terminal cover

Recommended Tightening Torque Number of Wires

	Unit		Wire	Number of Wires	Recommended Tightening Torque (N·m)	Terminal Screw
		Crimpi	ng Terminal	2	1.0 to 1.3	
	HW-U Contact Block	Solid Wire	ø0.5 to 1.6mm (AWG14 to 22)	2	1.0 to 1.3	
		Solid Wile	ø1.7 to 2.0mm (AWG12)	1	1.2 to 1.3	M3.5
		Stranded	0.3 to 2.0mm ² Stranded (AWG14 to 22)		1.0 to 1.3	
		Wire	2.1 to 3.5mm ² (AWG12)	1	1.2 to 1.3	

FB Series Control Box


ø22mm XW Series EMO Switches



All dimensions in mm.

FB Series Control Box

ø22mm HW Series EMO Switches




ø22mm HW Series EMO Switches +


SEMI Switch Guard (HW9Z-KG4)

4-M4 Tapping Screw Holes for Rear Mounting (Depth: 10mm) 2-Front Mounting Holes EMO Switch Cover Mounting Screws Switch Guard 15.5 Cover 2-ø21.3 Knockout Box Base

ø22mm HW Series EMO Switches + SEMI Switch Guard (HW9Z-KG3)



SEMI Switch Guard (HW9Z-KG3)



ø22mm XW Series EM0 Switches +



Relays & Sockets

LED Illumination


Controllers Operator Interfaces

Sensors AUTO-ID

Circuit

Protectors Power Supplies

ø22mm XW Series EMO Switches + SEMI Switch Guard (HW9Z-KG4)



Enabling Switches Safety Products **Explosion Proof** Terminal Blocks Relays & Sockets Circuit Protectors **Power Supplies** The combination of IDEC's EMO switch guards and emergency stop switches are approved by TÜV Rheinland for compliance with SEMI S2 standards

SEMI S2-compliant Combinations

EMO Switch Guard	Applicable Emergency Stop Switches					
XA9Z-KG1 XA1E-BV4****-EMO (①), XA1E-BV3 (②), XA1E-LV3 (③), XA1E-BV4 (③), XA1E-LV4 (③)						
HW9Z-KG3	XW1E-BV4***-EMO (4), XW1E-BV4 (5), XW1E-LV4 (5), XW1E-TV4 (5), HW1B-V3 (6), HW1B-V4 (7), HW1B-X4 (8), HW1B-Y2 (9)					
HW9Z-KG4	XW1E-BV4****-EMO (10), XW1E-BV4 (11), XW1E-LV4 (11), XW1E-TV4 (11), XW1E-BV5 (12) HW1B-V3 (13), HW1B-V4 (14), HW1E (15), HW1B-X4 (16), HW1B-Y2 (17)					
HW9Z-KG5	XW1E-BV4****-EMO (®), XW1E-BV4 (®), XW1E-LV4 (®), XW1E-TV4 (®), XW1E-BV5 (@), HW1B-V3 (@), HW1B-V4 (@), HW1B-Y2 (©)					

XA9Z-KG1	HW9Z-KG
2	5
EMO 3	





HW9Z-KG5

LED Illumination

Controllers Operator

Sensors

AUTO-ID

Х6 XA

> XW XN

Note:

In the past, emergency stop switches with switch guards (same definition as the term "protective shroud" used in standards) could not be used on machine tools or food processing machines in compliance with ISO/IEC standards.

However, following the revision of standards in 2015, a protective shroud can now be used under certain conditions.

About SEMI


SEMI is an international industry association whose member companies produce materials, equipment, and related technology for manufacturing semiconductor, flat panel display (FPD), and micro-electromechanical systems (MEMS) products. The SEMI safety guideline was published for the semiconductor industry and it is observed with the same importance as standards.

SEMI S2-0706, 12.1 describes as follows; "The equipment should have an 'emergency off' (EMO) circuit. The EMO actuator (e.g., button), when activated, should place the equipment into a safe shutdown condition, without generating any additional hazard to personnel or the facility." Because the semiconductor environment involves solvents and chemicals in many cases, some of which are toxic, interrupting the power source may cause secondary accidents. SEMI safety guideline requires the installation of an emergency off switch which disconnects only the part responsible for the hazardous situation, and maintains the functions of safety-related devices (e.g., smoke detectors, gas/water leak detectors, pressure measurement devices, etc.).

Emergency off buttons should be located or guarded to minimize accidental activation (SEMI S2-0706, 12.5.1). The emergency off button should be red and mushroom shaped. A yellow background for the EMO should be provided (SEMI S2-0706, 12.3).

- Location of EMO switches on semiconductor manufacturing equipment Acceptance criteria: controls should not be located above 1638 mm (64.5 in.) or below 838 mm (33 in.) (SEMI S8-0705, 9.1.2).
- No operation or regularly scheduled maintenance location should require more than 3 m (10 feet) travel to an EMO button (S2-0706, 12.5.2).





For more information, visit http://eu.idec.com

Enabling Switches Safety Products **Explosion Proof**

Relays & Sockets Circuit Protectors Power Supplies LED Illumination Controllers Operator

Sensors AUTO-ID

Х6 XA XW XN

SEMI S2 Compliant Switch Guards

Switch Guards Package Quantity: 1								
Series	Description & Shape	SEMI S2	ISO 13850	Part No.	Applicable Switches (*1)	Remarks		
ø16mm XA Series	ø16 mm EMO Switch Guard	0	0	XA9Z-KG1	XA1E-BV3 XA1E-BV4 XA1E-LV3 XA1E-LV4	SEMI S2 compliant (The combination of IDEC's emergency stop switches and EMO switch guards are approved by TÜV Rheinland for compliance with SEMI S2 standard.) ISO 13850 compliant.		
	ø22 mm EMO Switch Guard	0	_	HW9Z-KG1	XW1E-BV4 XW1E-LV4 XW1E-TV4 HW1B-V3 HW1B-V4 HW1B-X4 HW1B-Y2 HW1E-BV4 HW1E-LV4	SEMI S2-0703, 12.5.1 compliant. Widely used switch guard in many applications.		
	ø22 mm EMO Switch Guard	0	_	HW9Z-KG2	XW1E-BV4 XW1E-IV4 XW1E-TV4 HW1B-V3 HW1B-V4 HW1B-X4 HW1B-Y2 HW1E-BV4 HW1E-LV4	SEMI S2-0703, 12.5.1 compliant. SEMATECH Application Guide for SEMI S2-93, 12.4. compliant. The round shape is effective to prevent inadvertent operation from any direction.		
	ø22 mm EMO Switch Guard	0	0	HW9Z-KG3	XW1E-BV4 XW1E-LV4 XW1E-TV4 HW1B-V3 HW1B-V4 HW1B-X4 HW1B-Y2	SEMI S2 compliant (The combination of IDEC's emergency stop switches and EMO switch guards are approved by TÜV Rheinland for compliance with SEMI S2 standard.) ISO 13850 compliant. The smallest switch guard for ø22 series switches. Can be installed on FB control boxes.		
ø22mm HW/XW Series	ø22 mm EMO Switch Guard	0	0	HW9Z-KG4	XW1E-BV4 XW1E-BV5 XW1E-LV4 XW1E-TV4 HW1B-V3 HW1B-V4 HW1B-X4 HW1B-X4 HW1B-Y2 HW1E-BV4 HW1E-LV4	SEMI S2 compliant (The combination of IDEC's emergency stop switches and EMO switch guards are approved by TÜV Rheinland for compliance with SEMI S2 standard.) ISO 13850 compliant. SEMATECH Application Guide for SEMI S2-93, 12.4. compliant. Narrower than HW9ZKG5. Saves more space. Can be installed on FB control boxes. Available in white.		
	ø22 mm EMO Switch Guard	0	0	HW9Z-KG5	XW1E-BV4 XW1E-LV4 XW1E-TV4 XW1E-BV5 HW1B-V3 HW1B-V4 HW1B-X4 HW1B-Y2 HW1E-BV4 HW1E-LV4	SEMI S2 compliant (The combination of IDEC's emergency stop switches and EMO switch guards are approved by TÜV Rheinland for compliance with SEMI S2 standard.) ISO 13850 compliant. SEMATECH Application Guide for SEMI S2-93, 12.4. compliant. A nameplate can be installed. Available in white.		

[•] Material: polyamide (PA6), degree of protection: IP65 (IEC 60529)

^{*1)} For details on applicable emergency stop switches, see D-052.

Safety Products

Explosion Proof

Power Supplies

LED Illumination

Controllers Operator

Interfaces

Sensors

AUTO-ID

XA XW XW


SEMI S2 Compliant Switch Guards


Dimensions


XA9Z-KG1


HW9Z-KG1

All dimensions in mm.










HW9Z-KG3


Terminal Blocks

Relays & Sockets

Circuit
Protectors








• Panel thickness: 1.2 to 4.0 mm (1.2 to 2.6 mm when using an HWAV nameplate)

Panel Cut-out

ø16mm



ø22mm


The * 1.7 $_0^{+0.2}$ recess is for preventing rotation and not necessary when anti-rotation is not used.

The * 3.2 $^{+0.2}_{0}$ recess is for preventing rotation and not necessary when anti-rotation is not used.

 When anti-rotation is not required or when the panel cut-out does not have anti-rotation recess, remove the projection using pliers.




Note: The height of the applicable switch and guard will be 3 mm or less as shown in the diagram on the right.



To tighten the locking ring, use locking ring wrench MT-100 and tighten to a torque of 0.88 N·m.

ø22 mm



To tighten the locking ring, use locking ring wrench MW9Z-T1 and tighten to a torque of 2.0 N·m.

APEM

Switches & Pilot Lights

Control Boxes

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit

Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID


EMO Sticker



Part No.: HW9Z-EMO-NPP

Color: Yellow (red legend)Package

Quantity: 10



Nameplate (for ø22 mm Emergency Stop Switches)

Name	Legend	Part No.	Remarks		
For ø40mm Mushroom	EMERGENCY OFF	HWAV-74-Y	Nameplate color: yellow Legend color: black	OFF 1.5	

Х6 XA XW XN