


## SB® 120 Connectors

Up to 240 Amps



Like the other Multipole connectors, the SB® 120 offers color-coded mechanically keyed housings. Keys can be used to identify and separate different circuits, or prevent users from accidentally cross mating different voltages. Wires sizes from 10 to 1 AWG (5.3 to 42.4 mm<sup>2</sup>) are held in the second smallest SB® housing.

- **Extended Range Contacts Expand Wire Size up to 1 AWG (42.4 mm<sup>2</sup>)**

*Allows UL rated currents up to 240 amps*

- **Chemical Resistant Housing Option**

*Extends temperature range down to -40°C, while offering enhanced UV and chemical resistance*

- **Panel Mounting Grooves**

*With use of mounting clamps, can be easily mounted through panels*

## SB® 120 ORDERING INFORMATION

### SB® 120 Standard Housings

The second to smallest SB® housings work with wire contacts up to 1 AWG (42.4 mm<sup>2</sup>) as well as busbar contacts. Genderless design mates with itself. Mechanical keys are color-coded.

Description	Part Numbers	
Minimum Quantity	250	50
Red	6810G3-BK	6810G3
Gray	6810G1-BK	6810G1
Blue	6810G2-BK	6810G2

### SB® 120 Chemical Resistant (CR) Housings



Same features as the Standard SB® 120 but molded in a chemical resistant PBT/PC blend. Suitable for use to -40°C.

Description	Part Numbers	
Minimum Quantity	250	50
Red	P6810G3-BK	P6810G3
Gray	P6810G1-BK	P6810G1

### SB® 120 Silver Plated Wire Contacts

Silver plated contacts offer superior electrical performance and durability up to 10,000 mating cycles. See reducing bushings in accessory section for smaller wires.

AWG	mm <sup>2</sup>	Mating Force	Loose Piece Part Numbers			Dimensions			
						- A -		- B -	
					inches	mm	inches	mm	
Minimum Quantity			600	500	50				
1	42.4	Low	1323G1-BK	-	1323G1	0.47	11.94	0.39	9.91
2	33.6	High	-	1319-BK	1319	0.44	11.18	0.34	8.64
4	21.1	High	-	1319G4-BK	1319G4	0.44	11.18	0.29	7.37
6	13.3	High	-	1319G6-BK	1319G6	0.44	11.18	0.22	5.59




## SB® 120 Silver Plated Busbar Contacts

Use 2 busbar contacts per housing to provide a quick disconnect input or output busbar connection. Busbar contacts are for mating with wire contacts only. Part number 120BBS includes lock nuts. Locknuts must be ordered separately for B01997P1.



Type	Thread	Mating Force	Loose Piece Part Numbers		
Minimum Quantity					
Busbar	10 to 24	High	1,000	300	20
Lock Nut	10 to 24	-	H1216P8	-	-

See Busbar contact drawing on website for further detail.



## SB® 120 CONNECTOR TEMPERATURE CHARTS - Temperature rise charts are based on a 25°C ambient temperature.

Current - Temperature Derating per IEC 60512-5-2 Test 5B



## SB® 120 CONNECTOR SPECIFICATIONS

MECHANICAL		
<b>Wire Size Range</b>	<b>AWG</b>	<b>mm<sup>2</sup></b>
Wire Contacts with Bushings	10 to 1	5.3 to 42.4
<b>Max. Wire Insulation Diameter</b>	<b>in.</b>	<b>mm</b>
	0.600	15.240
<b>Operating Temperature <sup>2</sup></b>	<b>°F</b>	<b>°C</b>
Standard	-4° to 221°	-20° to 105°
Chemical Resistant	-40 to 221°	-40° to 105°
<b>Mating Cycles No Load by Plating</b>	<b>Silver (Ag)</b>	
Wire and Busbar Contacts	10,000	
<b>Avg. Mating / Unmating Force</b>	<b>Lbf.</b>	<b>N</b>
Wire-to-Wire	20	89
<b>Min. Contact / Spring Retention Force</b>	<b>Lbf.</b>	<b>N</b>
	75	333.6

MATERIALS	
<b>Housing</b>	
Standard Plastic Resin	Polycarbonate
Chem. Resistant Resin	Polycarbonate / PBT blend
Contact Retention Spring	Stainless Steel
<b>Housing Flammability Rating</b>	
UL94	V-0
Glow Wire	960°C (GWFI) / 800°C (GWIT)
<b>Wire &amp; Busbar Contacts</b>	
Base	Copper Alloy
Plating	Silver
<b>Contact Termination Methods</b>	
Crimp <sup>3</sup>	Wire Contacts
Hand Solder	Wire Contacts
Wrench / Socket	Busbar Contacts Only

Specifications continued on next page

## ELECTRICAL

<b>Current Rating Amperes <sup>1</sup></b>	<b>UL 1977</b>	<b>CSA</b>
Wire-to-Wire (1 AWG)	240	130
Wire-to-Busbar (2 AWG)	120	
<b>Voltage Rating AC/DC</b>		
UL 1977	600	
<b>Dielectric Withstanding Voltage</b>		
Volts AC	2,200	
<b>Avg. Mated Contact Resistance Milliohms <sup>1</sup></b>		
5 1/2" of 2 AWG Wire	0.136	
<b>Hot Plug Current Rating Amperes - Wire &amp; Busbar</b>		
250 cycles at 120V DC	60A	



NOTE 1: See IEC 60664-1 for working voltage.

NOTE 2: Amp ratings are stated per position and based on all positions being fully loaded.

1 - Based on: 105°C rated or better cable of the largest size. Properly calibrated Anderson Power™ recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.

2 - Limited by the thermal properties of the connector plastic housing.


3 - Use Anderson Power™ recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.

## SB® 120 ACCESSORIES

### Mounting Clamp for SB® 120

Mounting clamps can be used for fastening a SB® 120 series housings to a panel. Fastening hardware not included.

Description	Part Number
Minimum Quantity	20 sets of 2
Panel Mount Bracket	1467G1



### Cable Clamps \*

Durable metal cable clamps securely hold cables to prevent accidental strain or pulls from dislodging wire or contacts from the housing. Cable clamps are recommended for solder terminated wires.

Description	Cable Size		Part Numbers
	Min / Max Inches O.D.	Min / Max mm O.D.	
Minimum Quantity			50
Bolt on for Discrete Conductor	0.70 to 0.23	17.7 to 5.8	981G1
Bolt on for Bundled Conductor	0.73 to 0.29	18.5 to 7.3	981G2

\* Torque value 21 (in lbs) / 2.4 (Nm) NOTE: For assembly of clamp to housing only

## IEC INFORMATION

ATTRIBUTES	SB®120
<b>AMP Rating AC/DC</b>	120
<b>Voltage Rating AC/DC (Steady State)</b>	400 V AC/DC (Operational)
<b>Breaking Capacity - AMP Rating / Cycles</b>	120 Amp / 10 Cycles
<b>Voltage Rating (Breaking Capacity)</b>	220 VDC
<b>Finger Safety - Mated Only</b>	IEC 60529- IP20
<b>Wire Size Tested</b>	50 mm <sup>2</sup>
<b>Contact Series Tested</b>	1323
<b>Climatic Testing Cold, Heat &amp; MFG)</b>	IEC 60512 Test-11j, 11i & 11g
<b>Cycle Life</b>	IEC 60512 Test 9a- 5,000 Cycles
<b>Mechanical Strength Impact</b>	IEC 60512-5 @ 29.5 Inches - Dropped 8 Times
<b>Temperature Range</b>	-20°C to 105°C -4°F to 221°F

Connector Series	Configurations	Creepage / Clearance per IEC 60950-1	Material Group
SB® 120	Unmated	4.10 mm	IIIa
	Mated	4.10 mm	


## PROTECTION

### Touch Safety with Wire Contacts

IEC 60529 IP10 unmated

### Environmental Sealing with Boots

IEC 60529 IP64



The given wire O.D. information is an estimate.

Cable clamps should be evaluated for performance with the actual wire to be used.


### “A” Frame Handle for SB® 120 \*

Handle makes mating and unmating the connector easier. The non-conductive gray plastic material is strong and safe. Machine screws and locknuts included.

Description	Part Number
Minimum Quantity	200
Gray “A” Handle & Hardware	997G1

\* Torque value 21 (in - lbs) / 2.4 (Nm)

NOTE: For assembly of clamp to housing only




### “T” Handle \*

The “T” handle makes mating and unmating the connector easier. The non-conductive red plastic material is strong and safe. (2) Self tapping screws are used to secure the handle to the connector housing.

Description	Part Numbers	
Minimum Quantity	1,000	50
Red “T” Handle + Hardware Bag	-	SB120-HDL-RED
Red “T” Handle Only	113899P1	-
#8 x 7/8” Screw (Order 2 Per Handle)	H1120P43	-

\* Torque value 21 (in - lbs) / 2.4 (Nm)


NOTE: For assembly of clamp to housing only



### Dust Cover

Prevents dust and dirt from entering the mating interface of the connector when unmated. NOTE: Not a Hermetic Seal.

Description	Part Numbers	
Minimum Quantity	100	50
Dust Cover with Lanyard Strap, Black	B02019P1	134G4




### SB® 120 Environmental Boots

Environmental Boots provide water, dirt, chemical and UV protection for SB® 120 connectors. The durable boots shield the connectors from water and dirt to IP64 in both the mated and unmated condition.

Description	Part Numbers	
Minimum Quantity	250	25
SB® 120 Environmental Boot, Load	3-6035P1-BK	3-6035P1
SB® 120 Environmental Boot, Source	3-6034P1-BK	3-6034P1


Dimensions					
- A -		- B -		- C -	
in.	mm	in.	mm	in.	mm
7.9	201	2.8	71	8.0	203



### Silver Plated Reducing Bushings

Use with contact part number 1319-BK to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

Contact Barrel Size		Wire Size		Part Numbers			Dimensions - ID -	
AWG	mm²	AWG	mm²				inches	mm
Minimum Quantity				2,000	1,000	100		
2	33.6	4	21.1	5919-BK	-	5919	0.28	7.11
2	33.6	6	13.3	-	5920-BK	5920	0.23	5.84
2	33.6	10 to 8	5.2 to 8.3	5921-BK	-	5921	0.18	4.57



# SB® Tooling Information

Wire Size		Loose Piece Part Number	Loose Piece Contact Crimp Tools								
AWG	mm <sup>2</sup>		Silver Plating	Hand Tool	OR	Pneumatic Tool	+	Die	+	Locator	Number of Crimps
<b>SB® 120</b>											
1	42.4	1323G1	1368 Series		1387G1		1388G3		1389G4	Single	
2	33.6	1319					1388G4				
4	21.1	1319G4									
6	13.3	1319G6									

NOTE: See website for the most current information.

All Data Subject to Change Without Notice 2024-0002 DS-SB120 REV 8 **Your Best Connection™**

Anderson™ will use reasonable efforts to include accurate and up-to-date content in the data sheet. All product information contained in the data sheet including ordering information, illustrations, specifications, and dimensions, are believed to be reliable as of the date of publishing, but is subject to change without notice. Anderson™ makes no warranty or representation as to its accuracy. Content in the data sheet may contain technical inaccuracies, typographical errors and may be changed or updated without notice. Anderson™ may also make improvements and/or changes to the products and/or to the programs described in the content at any time without notice. Current sales drawings and specifications are available upon request.

©2024 Anderson Power Products, Inc. All rights reserved. A®, Anderson Power Products®, SB®, are registered trademarks of Anderson Power Products, Inc. Anderson™, Anderson Power™, Anderson Power™ logo and Your Best Connection™ are trademarks of Anderson Power Products, Inc.



**HEADQUARTERS:** Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T: +1 978-422-3800 F: +1 978-422-0128 • **EUROPE:** Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 520203 • **GERMANY:** IDEAL® Industries Germany GmbH, Esslinger Strasse 7, D – 70771 Leinfelden-Echterdingen, T: +49 (0) 711 – 997606666 • **ASIA / PACIFIC:** IDEAL® Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036 • **INDIA:** IDEAL® INDUSTRIES India Private Limited, 229-230, SPAZEDGE, Tower B, Sector 47, Sohna Road, Gurgaon – 122018, Haryana, India T: +(91) 956-0075905 T: +(91) 124-4495101 • **CHINA:** IDEAL® Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, PR. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218 • [www.ideal-industries.in](http://www.ideal-industries.in) • [www.andersonpower.com](http://www.andersonpower.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[120BBS](#) [1323G1](#) [1323G1-BK](#) [5919](#) [5920](#) [5920-BK](#) [113899P1](#) [134G4](#) [1467G1](#) [6810G1](#) [6810G1-BK](#) [6810G2](#)  
[6810G2-BK](#) [6810g3](#) [6810G3-BK](#) [981G1](#) [981G2](#) [P6810G1](#) [P6810G1-BK](#) [P6810G3](#) [P6810G3-BK](#) [SB120-HDL-RED](#)  
[1388G3](#) [1389G4](#) [B02019P1](#) [3-6034P1](#) [3-6035P1](#) [3-6034P1-BK](#) [3-6035P1-BK](#) [B01997P1](#) [H1216P8](#) [H1120P43](#)