





WOLF MINI AND MICRO TORCHES

ATEX Directive
94/9/EC Compliant



- ATEX Directive Compliant
- IECEx Scheme Certified
- T4/T5 temperature class
- Ultra small size
- Lightweight, ergonomic design
- Proven impact resistance
- Single handed switching
- Switch protection shroud
- Integral pen style pocket clip
- IP67 water and dust tight



IECEx

The Wolf range of Mini and Micro Torches, certified for use in potentially explosive atmospheres, use high-tech light sources to give impressive performance with a compact size. Designed for easy storage in a pocket, they are the perfect torch for any application where a small size is critical.

All four models are compliant with the 94/9/EC ATEX 'Explosive Atmospheres' Directive and certified to IECEx for use in potentially explosive gas, vapour or mist atmospheres, where a T4 or T5 temperature class permits. The three models with LED light sources; the M-10 Micro, the M-40 Mini and M-60 Mini are approved as Category 1 equipment for use in Zones 0, 1 and 2, whilst the

M-20 Xenon Mini is approved as Category 2 equipment for use in Zones 1 and 2.

The M-10 Micro has a single white 5mm 'Nichia' LED light source and is powered by four alkaline LR44 'button cells', giving an impressive beam with a two hour duration from a very compact size. The M-20 Mini uses a Xenon filament bulb powered by two LR03 'AAA' cells, giving an excellent narrow beam of light with good range and up to 2.5 hours duration. The M-40 Mini has a cluster of three white 5mm 'Nichia' LEDs, and the M-60 Mini uses a single 1 watt Luxeon LED giving a remarkable light output; both products are powered by three alkaline LR1 'N' cells giving up to ten hours of usable light.

The Mini and Micro Torch Range have an ergonomic design and are constructed from high quality thermoplastic resin, with excellent impact and chemical resistance. The polycarbonate lens has been set-back within the lens ring to minimise risk of damage. All models have a lanyard hole, an integral pocket clip for secure retention and to prevent roll on a flat surface, and a push-button for single handed switching, which is shrouded to guard against accidental operation. Additionally all models are certified IP67, sealed against water and dust ingress.

Mini and Micro torches are supplied with cells, the M-10 Micro is supplied with a neck cord for added convenience.

Wolf Mini and Micro Torch Range					
Technical Specification					
Model	M-10		M-20		M-60
Description	LED Micro Torch		Xenon Mini Torch		LED Mini Torch
Code	II 1 G Ex ia IIC T5 (Ta=50°C) IP67		II 2 G Ex ib IIC T4 IP67		II 1 G Ex ia IIC T4 (Ta=50°C) IP67
Apparatus standards	EN60079-0, EN50020 / IEC60070-0, IEC60079-11				
Type of protection	"ia/ib" Intrinsic Safety				
Area of classification (Gases)	Zones 0, 1 & 2		Zones 1 & 2		Zones 0, 1 & 2
Temp. classification (Gases)	T5				T4
Ambient temperature	-20°C to + 50°C		-20°C to + 40°C		-20°C to + 50°C
Certificate	Baseefa06ATEX0084 IECEx BAS 06.0023				
Enclosure	Impact resistant thermoplastic, electrostatic non-hazardous				
Lens	Polycarbonate				
Beam type	Medium Spot		Narrow Spot		Medium Spot
Light source:	Pt. no.	-		M-201	-
	Type	1x5mm LED White (Nichia)		Xenon filled filament bulb	3 x 5mm LED White (Nichia)
	Rating	-		2.3V 0.3A	1 Watt
	Output	18 cd		15 lm	3 x 18 cd
	Life	25,000 hrs		30 hrs	25,000 hours
Power source:	Pt. no.	M-102 (4 pack)		M-202 (2 pack)	M-402 (3 pack)
	Type	LR44 primary cells to IEC60086		LR03 primary cells to IEC60086	LR1 primary cells to IEC60086
	Volts	4 x 1.5V		2 x 1.5V	3 x 1.5V
Light duration	up to 2 hrs		up to 2.3 hrs		up to 10 hrs
Ingress protection	IP67 to EN60529:1992				
Weight (incl. cells)	25g		60g		

Note: All information has been gathered under laboratory conditions, the user must regard the values given as approximate. The Company reserves the right to alter product specifications without prior notice.

WOLF SAFETY LAMP COMPANY
Saxon Road Works, Sheffield S8 0YA, England
Tel: +44 114 255 1051 Fax: +44 114 255 7988
E-mail: info@wolf-safety.co.uk Website: www.wolf-safety.co.uk

