


Item no.: 233-510
 Product description: PCB terminal strip 2 solder pins/pole 10-pole Pin spacing 2.54 mm / 0.1 in with push-button



Produkt kann von Bild abweichen / product may differ

Packing unit 180 4*45 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	3.99 g
Color	orange
No. of connection Points	10
No. of potentials	10
pole count	10
Height	15.5 mm
Height	0.61 in
Width	27.7 mm
Width	1.091 in
Depth	13.9 mm
Depth	0.547 in
Pin spacing from	2.54 mm
Pin spacing from	0.1 in
Rating based on	IEC/EN 60664-1
Overvoltage category EN I	III
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV

Current intensity EN
Overvoltage category EN II
Pollution degree

6 A
II
2



Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Overvoltage category EN III	III
Degree of pollution	3
Rated voltage EN	63 V
Rated surge voltage	2.5 kV
Nominal current	6 A
Connection method	CAGE CLAMP®CONNECTION
Cross section [mm²]	0.08 - 0.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 0.5 mm²
Wiring method	fine-stranded
Cross section [mm²]	0 - 0.25 mm²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm²]	0 - 0.25 mm²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Strip length from [inch]	0.2 in
Strip length up to [inch]	0.24 in



Conductor entry angle to the PCB (degrees)	30 °
Solder pin length [mm]	4 mm
Solder pin width A [mm]	0.5 mm
Solder pin width B [mm]	0.75 mm
Diameter of drilled hole [mm]	1.1 mm
Tolerance of drilled hole diameter [mm]	0.1 mm
Material group	I
Insulating material	PA 6.6
Temperature stability	-60 °C to +105 °C
Flammability category, based on UL 94	0V
Clamping spring material	Nickel-chromium spring steel (CrNi)
Contact material	Electrolytic copper (Ecu)
Contact plating	tin-plated



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
233-510	ABS	04-HG469925/1-PDA	250	4	0,08-0,5
233-510	BV	11915/A0	250	6	0,08-0,5
233-510	CSA	154112-1465035	150	4	28-20
233-510	DNV	E-9215	250	4	0,08-0,5
233-510	GL	17296-00HH	250	4	0,08-0,5
233-510	KEMA	90.6212.01/02	250	6	0,08-0,5
233-510	RMR	11130002	250	4	0,08-0,5
233-510	UR	E45172	150	4	18-28

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected