

15mmx15mm LIGHT BAR

Part Number: DE/4GD

GREEN


Features

- •UNIFORM LIGHT EMITTING AREA.
- •EASILY MOUNTED ON P.C. BOARDS OR INDUSTRY STANDARD SOCKETS.
- •FLUSH MOUNTABLE.
- •EXCELLENT ON/OFF CONTRAST.
- •CAN BE USED WITH PANELS AND LEGEND MOUNTS.
- •MECHANICALLY RUGGED.
- ●I.C. COMPATIBLE.
- ●RoHS COMPLIANT.

Description

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions & Internal Circuit Diagram



Notes:

1. All dimensions are in millimeters (inches), Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted.

2. Specifications are subject to change without notice.





SPEC NO: DSAE0577 REV NO: V.6 DATE: MAR/08/2007 PAGE: 1 OF 3
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: D.M.LIU

Kingbright

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) [2] @ 10mA Min. Typ.		Viewing Angle [1]
					2 θ 1/2
DE/4GD	GREEN (GaP)	GREEN DIFFUSED	12	52	120°

Notes:

- 1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.
- 2. Luminous Intensity / Luminous Flux: +/-15%.

Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD [1]	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
V _F [2]	Forward Voltage	Green	2.2	2.5	V	IF=20mA
lr	Reverse Current	Green		10	uA	VR = 5V

Notes:

- 1. Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.

Absolute Maximum Ratings at Ta=25°C


Parameter	Green	Units		
Power dissipation	62.5	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3 Seconds			

Notes

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.

SPEC NO: DSAE0577 REV NO: V.6 DATE: MAR/08/2007 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: D.M.LIU

Kingbright



SPEC NO: DSAE0577 REV NO: V.6 DATE: MAR/08/2007 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: D.M.LIU