ne<mark>x</mark>peria

Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <u>http://www.nxp.com</u>, <u>http://www.philips.com/</u> or <u>http://www.semiconductors.philips.com/</u>, use <u>http://www.nexperia.com</u>

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use **salesaddresses@nexperia.com** (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia



TL431 family Adjustable precision shunt regulator Rev. 5 – 01 September 2015

Product data sheet

1. Product profile

1.1 General description

Three-terminal shunt regulator family with an output voltage range between V_{ref} and 36 V, to be set by two external resistors.

- The TL431xDBZR types feature an enhanced stability area with a very low load capacity requirement.
- The TL431xFDT types offer an enhanced stability area and a higher ElectroMagnetic Interference (EMI) ruggedness, for example, for Switch Mode Power Supply (SMPS) applications.
- The TL431xSDT types are designed for standard requirements and linear applications.

Reference	Temperature rang	ge (T _{amb})		Pinning
voltage tolerance (V _{ref})	0 °C to 70 °C	–40 °C to 85 °C	–40 °C to 125 °C	configuration (see <u>Table 3</u>)
2 %	TL431CDBZR	TL431IDBZR	TL431QDBZR	normal pinning
			TL431FDT	normal pinning
			TL431MFDT	mirrored pinning
			TL431SDT	normal pinning
			TL431MSDT	mirrored pinning
1 %	1 % TL431ACDBZR TL431AIDBZR		TL431AQDBZR	normal pinning
			TL431AFDT	normal pinning
			TL431AMFDT	mirrored pinning
			TL431ASDT	normal pinning
			TL431AMSDT	mirrored pinning
0.5 %	TL431BCDBZR	TL431BIDBZR	TL431BQDBZR	normal pinning
			TL431BFDT	normal pinning
			TL431BMFDT	mirrored pinning
			TL431BSDT	normal pinning
			TL431BMSDT	mirrored pinning

Table 1. Product overview



Adjustable precision shunt regulator

1.2 Features and benefits

- Programmable output voltage up to 36 V
- Three different reference voltage tolerances:
 - Standard grade: 2 %
 - A-Grade: 1 %
 - B-Grade: 0.5 %
- Typical temperature drift: 6 mV (in a range of 0 °C up to 70 °C)
- Low output noise
- Typical output impedance: 0.2 Ω
- Sink current capability: 1 mA to 100 mA
- AEC-Q100 qualified (grade 1)

1.3 Applications

- Shunt regulator
- Precision current limiter
- Precision constant current sink
- Isolated feedback loop for Switch Mode Power Supply (SMPS)

1.4 Quick reference data

Table 2. Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{KA}	cathode-anode voltage		V _{ref}	-	36	V
Ι _K	cathode current		1	-	100	mA
V _{ref}	reference voltage	$V_{KA} = V_{ref};$ $I_K = 10 \text{ mA};$ $T_{amb} = 25 \text{ °C}$				
	Standard-Grade (2 %)		2440	2495	2550	mV
	A-Grade (1 %)		2470	2495	2520	mV
	B-Grade (0.5 %)		2483	2495	2507	mV

Adjustable precision shunt regulator

2. Pinning information

Table 3.	Pinning			
Pin	Symbol	Description	Simplified outline	Graphic symbol
Normal p	inning: All ty	pes without MFDT and MSD	T ending	
1	k	cathode		DEE
2	REF	reference		REF
3	а	anode		a — }] — k 006aab355
Mirrored	pinning: All t	ypes with MFDT and MSDT	ending	
1	REF	reference		DEE
2	k	cathode		REF
3	а	anode		a →∑ k 006aab355

TL431 family Product data sheet

Adjustable precision shunt regulator

3. Ordering information

Table 4. Orde	ring inforn	nation	
Type number	Package		
	Name	Description	Version
TL431CDBZR	-	plastic surface-mounted package; 3 leads	SOT23
TL431IDBZR			
TL431QDBZR			
TL431FDT			
TL431MFDT			
TL431SDT			
TL431MSDT			
TL431ACDBZR			
TL431AIDBZR			
TL431AQDBZR			
TL431AFDT			
TL431AMFDT			
TL431ASDT			
TL431AMSDT			
TL431BCDBZR			
TL431BIDBZR			
TL431BQDBZR			
TL431BFDT			
TL431BMFDT			
TL431BSDT			
TL431BMSDT			

Table 4. Ordering information

TL431 family Product data sheet

Adjustable precision shunt regulator


4. Marking

Table 5. Marking	codes		
Type number	Marking code ^[1]	Type number	Marking code ^[1]
TL431CDBZR	CA*	TL431ASDT	RL*
TL431IDBZR	CB*	TL431AMSDT	LQ*
TL431QDBZR	CC*	TL431BCDBZR	CG*
TL431FDT	AR*	TL431BIDBZR	CH*
TL431MFDT	AU*	TL431BQDBZR	CJ*
TL431SDT	RM*	TL431BFDT	AT*
TL431MSDT	LR*	TL431BMFDT	AW*
TL431ACDBZR	CD*	TL431BSDT	MA*
TL431AIDBZR	CE*	TL431BMSDT	MB*
TL431AQDBZR	CF*	-	-
TL431AFDT	AS*	-	-
TL431AMFDT	AV*	-	-

[1] * = placeholder for manufacturing site code.

5. Functional diagram

The TL431 family comprises a range of 3-terminal adjustable shunt regulators, with specified thermal stability over applicable automotive and commercial temperature ranges. The output voltage may be set to any value between V_{ref} (approximately 2.5 V) and 36 V with two external resistors (see Figure 8). These devices have a typical output impedance of 0.2 Ω . Active output circuitry provides a very sharp turn-on characteristic, making these devices excellent replacements for Zener diodes in many applications like on-board regulation, adjustable power supplies and switching power supplies.



TL431 family Product data sheet

Adjustable precision shunt regulator


Limiting values 6.

Symbol	Parameter	Conditions		Min	Max	Unit
V _{KA}	cathode-anode voltage			-	37	V
I _K	cathode current			-100	150	mA
I _{ref}	reference current			-0.05	10	mA
P _{tot}	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C$	<u>[1]</u>	-	350	mW
			[2]	-	580	mW
			[3]	-	950	mW
Tj	junction temperature			-	150	°C
T _{amb}	ambient temperature					
	TL431XCDBZR			0	+70	°C
	TL431XIDBZR			-40	+85	°C
	TL431XQDBZR TL431XFDT TL431XSDT			-40	+125	°C
T _{stg}	storage temperature			-65	+150	°C

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for anode 1 cm².

Device mounted on a ceramic PCB, Al₂O₃, standard footprint. [3]



Adjustable precision shunt regulator

Table 7.ESD maximum ratings

$T_{amb} = 25$	$^{\circ}\!$				
Symbol	Parameter	Conditions	Min	Max	Unit
V _{ESD}	electrostatic discharge voltage	MIL-STD-883 (human body model)	-	4	kV

7. Recommended operating conditions

Table 8.	Operating conditions				
Symbol	Parameter	Conditions	Min	Max	Unit
V _{KA}	cathode-anode voltage		V _{ref}	36	V
I _K	cathode current		1	100	mA

8. Thermal characteristics

						-	
Symbol	Parameter	Conditions		Min	Тур	Max	Unit
R _{th(j-a)} thermal resistance from junction to ambient		in free air	<u>[1]</u>	-	-	360	K/W
		[2]	-	-	216	K/W	
		[3]	[3]	-	-	132	K/W
R _{th(j-sp)}	thermal resistance from junction to solder point		<u>[4]</u>	-	-	50	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for anode 1 cm².

[3] Device mounted on a ceramic PCB, Al₂O₃, standard footprint.

[4] Soldering point of anode.

Adjustable precision shunt regulator

9. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
	Grade (2 %):					
	ZR; TL431IDBZR; TL431QDI	BZR; TL431FDT; TL431MFDT; T	L431SDT; TI	L431MSDT		
V _{ref}	reference voltage	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$	2440	2495	2550	mV
ΔV_{ref}	reference voltage variation	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$				
	TL431CDBZR	$T_{amb} = 0 \ ^{\circ}C \ to \ 70 \ ^{\circ}C$	-	6	16	mV
	TL431IDBZR	$T_{amb} = -40 \ ^{\circ}C \ to \ 85 \ ^{\circ}C$	-	14	34	mV
	TL431QDBZR TL431FDT TL431MFDT TL431SDT TL431MSDT	$T_{amb} = -40 \text{ °C to } 125 \text{ °C}$				
$\Delta V_{ref} / \Delta V_{KA}$	reference voltage variation	I _K = 10 mA				
	to cathode-anode voltage	ΔV_{KA} = 10 V to V _{ref}	-	-1.4	-2.7	mV/V
	variation ratio	ΔV_{KA} = 36 V to 10 V	-	-1	-2	mV/V
I _{ref}	reference current	I _K = 10 mA; R1 = 10 kΩ; R2 = open	-	2	4	μA
ΔI_{ref}	reference current variation	$I_{K} = 10 \text{ mA};$ R1 = 10 kΩ; R2 = open				
	TL431CDBZR	T _{amb} = 0 °C to 70 °C	-	0.4	1.2	μA
	TL431IDBZR	T _{amb} = −40 °C to 85 °C	-	0.8	2.5	μA
	TL431QDBZR TL431FDT TL431MFDT TL431SDT TL431MSDT	T _{amb} = −40 °C to 125 °C				
K(min)	minimum cathode current	V _{KA} = V _{ref}	-	0.4	1	mA
off	off-state current	V _{KA} = 36 V; V _{ref} = 0	-	0.1	1	μA
Z _{KA}	dynamic cathode-anode impedance	I_{K} = 1 mA to 100 mA; V_{KA} = V_{ref} ; f < 1 kHz	-	0.2	0.5	Ω
A-Grade (1 TL431ACD	,	AQDBZR; TL431AFDT; TL431A	MFDT: TL431	ASDT: TL43	31AMSDT	
V _{ref}	reference voltage	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$	2470	2495	2520	mV
۷ _{ref}	reference voltage variation	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$				
	TL431ACDBZR	$T_{amb} = 0 \ ^{\circ}C \text{ to } 70 \ ^{\circ}C$	-	6	16	mV
	TL431AIDBZR	$T_{amb} = -40 \text{ °C to } 85 \text{ °C}$	-	14	34	mV
	TL431AQDBZR TL431AFDT TL431AMFDT TL431ASDT TL431AMSDT	$T_{amb} = -40 \text{ °C to } 125 \text{ °C}$				
$\Delta V_{ref} / \Delta V_{KA}$	reference voltage variation	I _K = 10 mA				
	to cathode-anode voltage	$\Delta V_{KA} = 10 \text{ V to } V_{ref}$	-	-1.4	-2.7	mV/V
	variation ratio	$\Delta V_{KA} = 36 \text{ V to } 10 \text{ V}$		-1	-2	mV/V

Product data sheet

Adjustable precision shunt regulator

Table	10.	Ch	arad	cteristi	cs	continued	
-	~ -	~~					

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I _{ref}	reference current	I _K = 10 mA; R1 = 10 kΩ; R2 = open	-	2	4	μA
ΔI_{ref}	reference current variation	I _K = 10 mA; R1 = 10 kΩ; R2 = open				
	TL431ACDBZR	T _{amb} = 0 °C to 70 °C	-	0.4	1.2	μA
	TL431AIDBZR	$T_{amb} = -40 \text{ °C to } 85 \text{ °C}$	-	0.8	2.5	μA
	TL431AQDBZR TL431AFDT TL431AMFDT TL431ASDT TL431AMSDT	T _{amb} = −40 °C to 125 °C				
I _{K(min)}	minimum cathode current	$V_{KA} = V_{ref}$				
	TL431ACDBZR	T _{amb} = 0 °C to 70 °C	-	0.4	0.6	mA
	TL431AIDBZR	$T_{amb} = -40 \text{ °C to } 85 \text{ °C}$				
	TL431AQDBZR TL431AFDT TL431AMFDT TL431ASDT TL431AMSDT	T _{amb} = −40 °C to 125 °C				
I _{off}	off-state current	V _{KA} = 36 V; V _{ref} = 0	-	0.1	0.5	μA
Z _{KA}	dynamic cathode-anode impedance	$I_{K} = 1 \text{ mA to } 100 \text{ mA};$ $V_{KA} = V_{ref}; f < 1 \text{ kHz}$	-	0.2	0.5	Ω
B-Grade (0 TL431BCD		BQDBZR; TL431BFDT; TL431B	MFDT; TL43 [°]	1BSDT; TL4:	31BMSDT	I
V _{ref}	reference voltage	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$	2483	2495	2507	mV
∆V _{ref}	reference voltage variation	$V_{KA} = V_{ref}$; $I_K = 10 \text{ mA}$				
	TL431BCDBZR	T _{amb} = 0 °C to 70 °C	-	6	16	mV
	TL431BIDBZR	$T_{amb} = -40 \ ^{\circ}C \text{ to } 85 \ ^{\circ}C$	-	14	34	mV
	TL431BQDBZR TL431BFDT TL431BMFDT TL431BSDT TL431BMSDT	$T_{amb} = -40 \text{ °C to } 125 \text{ °C}$				
$\Delta V_{ref} / \Delta V_{KA}$	reference voltage variation	I _K = 10 mA				
	to cathode-anode voltage variation ratio	ΔV_{KA} = 10 V to V _{ref}	-	-1.4	-2.7	mV/V
		ΔV_{KA} = 36 V to 10 V	-	-1	-2	mV/V
I _{ref}	reference current	$I_{K} = 10 \text{ mA};$ R1 = 10 kΩ; R2 = open	-	2	4	μA

Downloaded from Arrow.com.


Adjustable precision shunt regulator

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
ΔI _{ref}	reference current variation	$I_K = 10 \text{ mA};$ R1 = 10 kΩ; R2 = open				
	TL431BCDBZR	$T_{amb} = 0 \ ^{\circ}C \text{ to } 70 \ ^{\circ}C$	-	0.4	1.2	μA
	TL431BIDBZR	$T_{amb} = -40 \ ^{\circ}C \text{ to } 85 \ ^{\circ}C$	-	0.8	2.5	μA
	TL431BQDBZR TL431BFDT TL431BMFDT TL431BSDT TL431BMSDT	T _{amb} = -40 °C to 125 °C				
I _{K(min)}	minimum cathode current	$V_{KA} = V_{ref}$				
	TL431BCDBZR	$T_{amb} = 0 \ ^{\circ}C \text{ to } 70 \ ^{\circ}C$	-	0.4	0.6	mA
	TL431BIDBZR	$T_{amb} = -40 \text{ °C to } 85 \text{ °C}$				
	TL431BQDBZR TL431BFDT TL431BMFDT TL431BSDT TL431BMSDT	T _{amb} = -40 °C to 125 °C				
l _{off}	off-state current	V _{KA} = 36 V; V _{ref} = 0	-	0.1	0.5	μA
Z _{KA}	dynamic cathode-anode impedance	$I_{K} = 1 \text{ mA to } 100 \text{ mA};$ $V_{KA} = V_{ref}$; f < 1 kHz	-	0.2	0.5	Ω


Table 10. Characteristics ...continued

TL431 family Product data sheet

TL431 family




TL431 family




TL431 family


Adjustable precision shunt regulator



TL431 family




TL431 family



TL431 family


Adjustable precision shunt regulator



TL431 family Product data sheet


All information provided in this document is subject to legal disclaimers.

TL431 family




TL431 family

Adjustable precision shunt regulator




TL431 family

Adjustable precision shunt regulator




Adjustable precision shunt regulator

10. Application information




TL431 family



TL431 family Product data sheet

Adjustable precision shunt regulator




11. Test information

11.1 Quality information


This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q100 - Failure mechanism based stress test qualification for integrated circuits, and is suitable for use in automotive applications.

12. Package outline



Adjustable precision shunt regulator

13. Soldering



TL431 family Product data sheet

Adjustable precision shunt regulator

14. Revision history

Table 11. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
TL431_FAM v.5	20150901	Product data sheet	-	TL431_FAM v.4
Modifications:	• Figure 18: Ca	pacitor value corrected		
TL431_FAM v.4	20110630	Product data sheet	-	TL431_FAM v.3
TL431_FAM v.3	20101105	Product data sheet	-	TL431_FAM v.2
TL431_FAM v.2	20100120	Product data sheet	-	TL431_FAM v.1
TL431_FAM v.1	20090806	Product data sheet	-	-

Adjustable precision shunt regulator

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications - This NXP

Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Product data sheet

Adjustable precision shunt regulator

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Adjustable precision shunt regulator

17. Contents

1	Product profile 1
1.1	General description 1
1.2	Features and benefits 2
1.3	Applications 2
1.4	Quick reference data 2
2	Pinning information 3
3	Ordering information 4
4	Marking 5
5	Functional diagram 5
6	Limiting values 6
7	Recommended operating conditions 7
8	Thermal characteristics 7
9	Characteristics 8
10	Application information 20
11	Test information 22
11.1	Quality information 22
12	Package outline 22
13	Soldering 23
14	Revision history 24
15	Legal information 25
15.1	Data sheet status 25
15.2	Definitions
15.3	Disclaimers
15.4	Trademarks
16	Contact information 26
17	Contents 27

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP Semiconductors N.V. 2015.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 01 September 2015 Document identifier: TL431 family