

Search within category **GO**

BUY NOW

DESIGN / INSTALL



PLT1M-M60

Pan-Ty® locking tie, miniature cross section, 3.9 (99mm) length, flame retardant nylon 6.6, black.

Specs

Packaging Details

Tools

Documents

★ Add to Favorites

🛒 Add to BOM

Material	Nylon 6.6
Color	Black
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Environment	Indoor
Maximum Installation Temperature (°F)	32
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Maximum Operating Temperature (°C)	100
Maximum Operating Temperature (°F)	212
Cross Section	Miniature
Locking Style	Locking
Continuous Use Temperature Range	-76°F (-60°C) - 212°F (100°C)
Plenum-Rated	No
Tool	GTS-E, GS2B, PTS, PPTS, STS2
Thickness In (mm)	0.04 (1.1)
Bundle Diameter Range In. (mm)	0.06 (1.5) - 0.87 (22.0)
CE Compliant	Yes
CSA Certified	No
Mil. Std. Part Number	NA
UL 62275 Compliant (Type 1, 11)	No
UL 62275 Compliant (Type 2, 21)	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Application	General
Maximum Bundle Diameter (In.)	0.87
Operating Temperature	-76°F (-60°C) - 212°F (100°C)
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.

Thickness (mm)	1.1
UV Resistant	0
Width In (mm)	0.09 (2.5)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)