

Cyclone water separator with float drain


Technical characteristics

Max operating pressure: 16 bar

Temperature: +1°C to +65°C

Construction: Anodised Aluminium

Equipped with: Automatic float drain



A (mm)	B (mm)	C (mm)	D (mm)	Female thread (BSPP)	Flow rate (m ³ /h)	Parts Numbers
187	88	20	60	G 1/2	155	SPC 155
257	88	20	80	G 3/4	235	SPC 235
263	125	32	100	G 1	365	SPC 365
461	125	32	140	G 1 1/2	770	SPC 770
684	163	43	520	G 2	1280	SPC 1280