

# LQM31PN1R0M00#

“#” indicates a package specification code.


Size Code 3216 (1206) in mm (in inch), 0.95mm max. Thickness



< List of part numbers with package codes >

LQM31PN1R0M00L      LQM31PN1R0M00B

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	3000
B	Bulk(Bag)	1000

Mass (typ.)	
1 piece	0.024g

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LQM31PN1R0M00#

“#” indicates a package specification code.

## Specifications

L size	3.2±0.2mm
W size	1.6±0.2mm
T size	0.85±0.1mm
Size code inch (mm)	1206 (3216)
Inductance	1μH±20%
Inductance Test Frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	1200mA
Max. of DC resistance	0.15Ω
Class of magnetic shield	Ferrite Core
Self resonance frequency (min.)	60MHz
DC Resistance Intermediate Values	0.12Ω±25%
Operating Temperature Range	-55°C to 125°C
Series	LQM31PN_00

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# LQM31PN1R0M00#

“#” indicates a package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




■ LQM31PN1R0M00 L



■ LQM31PN1R0M00 Q



■ LQM31PN1R0M00 |Z|




■ LQM31PN1R0M00 L-Current 20degC

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LQM31PN1R0M00#

“#” indicates a package specification code.



**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.