


Datasheet

# 2.5" SATA SSD

## 3TE7 series

- 2.5" SATA Slim SATA III solution for industrial field
- High IOPS
- iSMART disk health monitoring
- iPower Guard for protecting unstable start up and shut down.
- iData Guard for abnormal power failure



## Introduction

Innodisk 2.5" SATA SSD 3TE7 is SATA III 6.0 Gb/s flash based disk, which adopts latest SATA III NAND controller with Innodisk's exclusive L<sup>3</sup> FW architecture. The upgraded L<sup>3</sup> FW architecture, combining Innodisk signature 4K mapping algorithm L<sup>2</sup> FW architecture with powerful LDPC technology, makes 3TE7 series have outstanding high IOPS, better data integrity and extended lifespan through reducing the bad block number happening. Built-in thermal sensor, and iData Guard ensure data integrity and reliability of 2.5" SATA SSD 3TE7 for industrial applications.

# 2.5" SATA SSD

## 3TE7 series


### Diagram

Contact us for more information about the 2.5" SATA SSD 3TE7.

Innodisk is a service-driven provider of industrial embedded flash and DRAM storage products and technologies, with a focus on the industrial/embedded, aerospace and defense, and cloud computing industries.

\* DES25-XXXDK1XX%X (=%1 or A)

\* DES25-XXXDK1XX%X (=%3 or C)



### Specifications

Interface	SATA III
Flash Type	3D TLC
Capacity	32GB~2TB
Max. Channels	4
Sequential R/W (MB/sec, max.)*	550 / 520 MB/s
4KB Random (QD32) R/W (IOPS)**	82,000/74,000
Max. Power Consumption	3.3W
Thermal Sensor	√
External DRAM Buffer	-
H/W Write Protect	-
ATA Security	√
S.M.A.R.T.	√
Dimension (WxLxH)	69.8 X 100.0 X 7.0 mm
Environment	Vibration: 20G @7~2000Hz Shock: 1500G @ 0.5ms Storage Temperature: -40°C ~ +85°C MTBF: 3 million hours
* Performance based on CrystalDiskMark 6.0.2 with file size 1000MB	

#### Headquarters (Taiwan)

5F., No.237, Sec. 1, Datong Rd., Xizhi Dist., New Taipei City, Taiwan (R.O.C.)  
Tel: +886-2-77033000  
Email: sales@innodisk.com

#### Branch Offices:

USA  
[usasales@innodisk.com](mailto:usasales@innodisk.com)  
+1-510-770-9421  
Europe  
[eusales@innodisk.com](mailto:eusales@innodisk.com)  
+31-40-3045-400  
Japan  
[jpsales@innodisk.com](mailto:jpsales@innodisk.com)  
+81-3-6667-0161  
China  
[sales\\_cn@innodisk.com](mailto:sales_cn@innodisk.com)  
+86-755-21673689  
[www.innodisk.com](http://www.innodisk.com)

© 2021 Innodisk Corporation.  
All right reserved. Specifications are subject to change without prior notice.

### Ordering Information (Please refer to TPS for detail)

20210730

Operation Temp.	32GB	64GB	128GB	256GB	512GB	1TB	2TB
Standard Grade (0°C ~ +70°C)	DES25-32GDK1EC3SF	DES25-64GDK1EC3DF	DES25-A28DK1%C3QF DES25-A28DK1%C*DF	DES25-B56DK1%C*QF	DES25-C12DK1%C*QF	DES25-01TDK1%C*QF	DES25-02TDK1%C*QF
Industrial Grade (-40°C ~ +85°C)	DES25-32GDK1EW3SF	DES25-64GDK1EW3DF	DES25-A28DK1%W3QF DES25-A28DK1%W3DF	DES25-B56DK1%W*QF	DES25-C12DK1%W*QF	DES25-01TDK1%W*QF	DES25-02TDK1%W*QF

%: E: 64 layers 3D TLC; G: 96 layers 3D TLC; K: 112 layers 3D TLC  
\*. PCB version control

**innodisk**

[www.innodisk.com](http://www.innodisk.com)