
# **F95 Audio Series**

# **Conformal Coated Chip Optimized for Audio Applications**







Single-side electrodes (Both electrodes at bottom side only)

## **FEATURES**

- · Compliant to the RoHS3 directive 2015/863/EU
- Rich Sound in the Bass Register and Clear Sound
- Materials are Strictly Selected to Achieve High Level Sound
- F95 Series has No Lead-Frame and No Vibration Factor
- Low ESR, Low ESL
- 100% Surge Current Tested
- Line Up Miniature Size and High Capacitance, Necessary to Mobile Design
- SMD Conformal
- Small and High CV

## **APPLICATIONS**

- · Mobile Audio Player
- Smartphone
- Mobile Phone
- Wireless Microphone System





# **MARKING**







<u></u>	
<i>)</i> <b>J</b> 8	
$-\mathcal{T}$	

Capacitance

## **CASE DIMENSIONS:**

## millimeters (inches)

Code	EIA Code	EIA Metric	L	W	Н	A	В	С	D*
В	1411	3528-20	3.50±0.20 (0.138±0.008)	2.80±0.20 (0.110±0.008)	1.80±0.20 (0.071±0.008)	0.80±0.30 (0.031±0.012)	1.20±0.30 (0.047±0.012)	1.10±0.30 (0.043±0.012)	0.20 (0.008)
s	1306	3216-12	3.20±0.30 (0.126±0.012)	1.60±0.30 (0.063±0.012)	1.00±0.20 (0.039±0.008)	0.80±0.30 (0.031±0.012)	1.20±0.30 (0.047±0.012)	0.80±0.30 (0.031±0.012)	0.20 (0.008)
Т	1411	3527-12	3.50±0.20 (0.138±0.008)	2.70±0.20 (0.106±0.008)	1.00±0.20 (0.039±0.008)	0.80±0.20 (0.031±0.008)	1.20±0.20 (0.047±0.008)	1.10±0.20 (0.043±0.012)	0.20 (0.008)

<sup>\*</sup>D dimension only for reference

μF	68	100	150	220	330	470	680
code	W7	A8	E8	J8	N8	S8	W8

## **HOW TO ORDER**



227

**Capacitance Code** pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

M **Tolerance** K=±10%

M=±20%

S Case

Size

See

table

above

**Packaging** See Tape & Reel Packaging Section

AM<sub>1</sub> **AUDIO** 

Series

Code

02

Single Face Electrode

### **TECHNICAL SPECIFICATIONS**

Category Temperature Range:	-55 to +125°C
Rated Temperature:	+85°C
Capacitance Tolerance:	±20%, ±10% at 120Hz
Dissipation Factor:	Refer to next page
ESR 100kHz:	Refer to next page
Leakage Current:	Refer to next page
	Provided that:
	After 1 minute's application of rated voltage, leakage current at 85°C
	10 times or less than 20°C specified value.
	After 1 minute's application of rated voltage, leakage current at 125°C
	12.5 times or less than 20°C specified value.
Capacitance Change By Temperature	+15% Max. at +125°C
	+10% Max. at +85°C
	-10% Max. at -55°C

# **F95 Audio Series**



# **Conformal Coated Chip Optimized for Audio Applications**

# **CAPACITANCE AND RATED VOLTAGE RANGE** (LETTER DENOTES CASE SIZE)

Capac	itance	Rated Voltage					
μF	Code	4V (0G)	6.3V (0J)	10V (1A)			
68	686	S	S	В			
100	107	S	S/T	В			
150	157	S					
220	227	S/T	В				
330	337	Т	В				
470	477	В					
680	687						

Released ratings

Please contact to your local KYOCERA AVX sales office when these series are being designed in your application.

## **RATINGS & PART NUMBER REFERENCE**

Part Number	Case Capacitance	Rated DCL	DF O 10011-	ESR	100kHz RMS Current (mA)			*1	MSL		
Part Number	Size	· (μF)	Voltage (V)	(μΑ)	@ 120Hz (%)	@ 100kHz (Ω)	25°C	85°C	125°C	ΔC/C (%)	IVISL
	4 Volt										
F950G686#SAAM1Q2	S	68	4	2.7	10	0.8	274	246	110	*	3
F950G107#SAAM1Q2	S	100	4	4.0	14	0.8	274	246	110	*	3
F950G157#SAAM1Q2	S	150	4	6.0	22	0.8	274	246	110	±15	3
F950G227#SAAM1Q2	S	220	4	8.8	30	0.8	274	246	110	±15	3
F950G227#TAAM1Q2	Т	220	4	8.8	25	0.6	365	329	146	*	3
F950G337#TAAM1Q2	T	330	4	13.2	40	0.8	316	285	126	±20	3
F950G477#BAAM1Q2	В	470	4	18.8	40	0.4	461	415	184	±20	3
					6.3 V	olt					
F950J686#SAAM1Q2	S	68	6.3	4.3	14	0.9	258	232	103	*	3
F950J107#SAAM1Q2	S	100	6.3	6.3	20	0.9	258	232	103	±15	3
F950J107#TAAM1Q2	Т	100	6.3	6.3	14	0.6	365	329	146	*	3
F950J227#BAAM1Q2	В	220	6.3	13.9	30	0.4	461	415	184	*	3
F950J337#BAAM1Q2	В	330	6.3	20.8	35	0.6	376	339	151	±20	3
	10 Volt										
F951A686#BAAM1Q2	В	68	10	6.8	12	0.4	461	415	184	*	3
F951A107#BAAM1Q2	В	100	10	10.0	14	0.4	461	415	184	*	3

<sup>\*1:</sup> ΔC/C Marked "\*"

Item	All Case (%)
Damp Heat	±10
Temperature cycles	±5
Resistance soldering heat	±5
Surge	±5
Endurance	±10

#: "M" for  $\pm 20\%$  tolerance, "K" for  $\pm 10\%$  tolerance. Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

# **F95 Audio Series**



# **Conformal Coated Chip Optimized for Audio Applications**

## **QUALIFICATION TABLE**


TEST	Audio F95 series (Temperature range -55°C to +125°C)
1521	Condition
Damp Heat (Steady State)	At 40°C, 90 to 95% R.H., 500 hours (No voltage applied) Capacitance Change
Temperature Cycles	At -55°C / +125°C, 30 minutes each, 5 cycles Capacitance Change
Resistance to Soldering Heat	10 seconds reflow at 260°C, 5 seconds immersion at 260°C. Capacitance Change
Surge	After application of surge voltage in series with a $33\Omega$ resistor at the rate of 30 seconds ON, 30 seconds OFF, for 1000 successive test cycles at 85°C, capacitors shall meet the characteristic requirements in the table above.  Capacitance Change
Endurance	After 2000 hours' application of rated voltage 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change
Shear Test	After applying the pressure load of 5N for 10±1 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode.
Terminal Strength	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of substrate so that the substrate may bend by 1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.

#### SOLID ELECTROLYTIC CAPACITOR ROADMAP

#### CONDUCTIVE CONVENTIONAL NIOBIUM **POLYMER TANTALUM** OXIDE **TC Series** N Series T Series T Cx F Series F Series F38 Fxx $MnO_2$ MnO<sub>2</sub> CATHODE Polymer DIELECTRIC Ta205 Ta, 0, Nb<sub>2</sub>O<sub>5</sub> ANODE Niobium Tantalum Tantalum Oxide **FIVE CAPACITOR CONSTRUCTION STYLES** J-lead Undertab TAC microchip® Conforma Hermetic

#### **SERIES LINE UP:**

CONVENTIONAL SMD MnO<sub>2</sub>



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## **KYOCERA AVX:**

F951A106MPAAQ2 F951C226MQAAQ2 F951D106KSAAQ2 F951C226MAAAQ2 F950G107MSAAQ2 F950G227MTAAQ2 F951D225MPAAQ2 F951E225MPAAQ2 F950G157MPAAQ2 F950J107MTAAM1Q F950J107MTAAM1Q2 F951C106MQAAQ2 F950J476MPAAQ2 F950G337MAAAQ2 F950G337MBAAQ2 F950J686MSAAM1Q F951A686MBAAM1Q2 F951C106MAAAQ2 F950G227MTAAM1Q F951E475KQAAQ2 F950G107MAAAQ2 F951A476MBAAQ2 F951A107MBAAM1Q2 F951D106MSAAQ2 F951C156MAAAQ2 F951C475MPAAQ2 F950G157MSAAM1Q2 F950G157MBAAQ2 F951A336MSAAQ2 F951A226KQAAQ2 F950J107MAAAM1Q2 F950J686MAAAM1Q F950J336MPAAQ2 F951D106KBAAQ2 F950G227MBAAQ2 F950G157MSAAM1Q F951C156KAAAQ2 F951A106MRAAQ2 F950G107MPAAQ2 F950J227MBAAM1Q2 F951A226MPAAQ2 F950J107MPAAQ2 F951A336MAAAQ2 F950J686MAAAM1Q2 F951A107MBAAM1Q F950G227KBAAQ2 F951E475KAAAQ2 F951A226KAAAQ2 F950G337MTAAM1Q2 F950J107MTAAQ2 F950J227MBAAQ2 F951D106MBAAQ2 F950G227MAAAM1Q2 F951D106KAAAQ2 F951E106MAAAQ2 F951C156MSAAQ2 F951A336MPAAQ2 F951A476MSAAQ2 F951E475MSAAQ2 F950J107MAAAQ2 F951C336MBAAQ2 F950G337KAAAQ2 F951A226MAAAQ2 F950G337MTAAM1Q F951E106KAAAQ2 F950G227MSAAQ2 F951E225MRAAQ2 F951V105MPAAQ2 F951D106MAAAQ2 F951D475MAAAQ2 F951C336MTAAQ2 F950G686MSAAM1Q F950J226MRAAQ2 F950G227KTAAQ2 F951A226MQAAQ2 F951A226MSAAQ2 F950G477MBAAQ2 F951A107MTAAQ2 F950J227MBAAM1Q F951C226KAAAQ2 F951C106MSAAQ2 F951A107KAAAQ2 F950G686MSAAM1Q2 F951V475MBAAQ2 F950G107MSAAM1Q F951C226MBAAQ2 F951A336MQAAQ2 F951V105MSAAQ2 F950J107KQAAQ2 F951A476MTAAQ2 F950G337MBAAM1Q2 F950J686MPAAQ2 F950G477KBAAQ2 F951V475KBAAQ2 F951E105MRAAQ2 F950G227MAAAQ2 F950G337MBAAM1Q F950G227MQAAQ2 F950G337MTAAQ2 F951A107MBAAQ2