




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 1021 – 3256 CMA

Stud Size: 1/4

Features

Product Type Features

Shape Description	RING-001
Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.026 g
----------------	---------

Contact Features

Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

--	--



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	1021 – 3256 CMA
Stud Diameter	6.5 mm [.256 in]
Tongue Thickness	.6 mm [.023 in]
Product Length	25.7 mm [1.01 in]
Barrel Inside Diameter	1.4 mm, 2.67 mm [.055 in] [.105 in]
Compatible Insulation Diameter (Max)	3.1 mm [.122 in]
Compatible Insulation Diameter Range	1.78 – 3.05 mm [.075 – .122 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 444155-2  
RING TONGUE 1-5 MM2 0.6  
ELECTRO TPBR

TE Part # 444151-2  
RING TONGUE 2.5-4.0 MM2 0.81  
ELECTROTPBR

TE Part # 7-2150711-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-  
110F160F

TE Part # 881000-1  
RING TONGUE 2.5/4.0 MM2 BR

TE Part # 2150711-2  
OCEAN\_2.0\_Applicator-E-110F160F-  
REA

Customers Also Bought

TE Part #1SNA356101R0200  
DBT17-GN

TE Part #7-1879233-7  
SMW5 150R 5%

TE Part #966067-6  
FER,WIRE,PL SLV,75/18,L10,GREY,LP

TE Part #MD24-12  
Dir,Mini,Fixed,NF 2400-2485MHz,  
11dBi,BW6





TE Part #1318384-4

025 40POS CAP ASSY H TIN



TE Part #2176378-1

RQ 0805 10R 0.1% 10PPM 5K RL



TE Part #3-1879377-4

CRGH0805 5% 22R 0.33W



TE Part #4-2176070-2

3521 510R 1% 2W

TE Part #1SNA356103R0400

DBT112-GN



TE Part #NB09524001

ATUM-16/4-0-SP

Documents

Product Drawings

RING TONGUE 0.5 /1.5 MM2 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_626030-2\_D\_c-626030-2-d.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_626030-2\_D\_c-626030-2-d.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_626030-2\_D\_c-626030-2-d.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English