45 V, 500 mA NPN general-purpose transistors Rev. 7 — 18 June 2018

Product data sheet

Product profile 1

1.1 General description

NPN general-purpose transistors in a small SOT23 Surface-Mounted Device (SMD) plastic package.

Table 1. Product overview

Type number	Package	Package I				
	Nexperia	JEDEC	JEITA			
BC817	SOT23	TO-236AB	-	BC807		
BC817-16					BC807-16	
BC817-25				BC807-25		
BC817-40				BC807-40		

1.2 Features and benefits

- High current
- Three current gain selections
- AEC-Q101 qualified

1.3 Applications

· General-purpose switching and amplification



45 V, 500 mA NPN general-purpose transistors

1.4 Quick reference data

Table 2. Quick reference data

T_{amb} = 25 °C unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V _{CEO}	collector-emitter voltage	open base		-	-	45	V
l _C	collector current			-	-	500	mA
I _{CM}	peak collector current	single pulse; t _p ≤ 1 ms		-	-	1	А
h _{FE}	BC817	V _{CE} = 1 V; I _C = 100 mA	[1]	100	-	600	
	BC817-16		[1]	100	-	250	
	BC817-25		[1]	160	-	400	
	BC817-40		[1]	250	-	600	

[1] pulsed; $t_p \le 300 \ \mu s$; $\delta \le 0.02$

2 Pinning information

Table 3. Pinning				
Pin	Symbol	Description	Simplified outline	Graphic symbol
SOT23		·		·
1	В	base		
2	E	emitter	3	C
3	С	collector		в
) E
				sym123

3 Ordering information

Table 4. Ordering information

Type number	Package					
	Name	Description	Version			
BC817	TO-236AB	Plastic surface-mounted package; 3 leads	SOT23			
BC817-16						
BC817-25						
BC817-40						

BC817_SER Product data sheet

45 V, 500 mA NPN general-purpose transistors

Marking 4

Table 5. Marking						
Type number		Marking code				
BC817	[1]	6D%				
BC817-16	[1]	6A%				
BC817-25	[1]	6B%				
BC817-40	[1]	6C%				

[1] % = placeholder for manufacturing site code


Limiting values 5

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CBO}	collector-base voltage	open emitter	open emitter		50	V
V _{CEO}	collector-emitter voltage	open base		-	45	V
V _{EBO}	emitter-base voltage	open collector		-	5	V
I _C	collector current			-	500	mA
I _{CM}	peak collector current	single pulse; $t_p \le 1 \text{ ms}$		-	1	А
I _{BM}	peak base current	single pulse; $t_p \le 1 \text{ ms}$	single pulse; $t_p \le 1 \text{ ms}$ -		200	mA
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[1] [2]	-	250	mW
			[3] [2]	-	345	mW
Tj	junction temperature			-	150	°C
T _{amb}	ambient temperature			-65	150	°C
T _{stg}	storage temperature			-65	150	°C

Device mounted on an FR4 Printed-Circuit-Board (PCB); single-sided copper; tin-plated and standard footprint.
 Valid for all available selection groups.
 Device mounted on an FR4 Printed-Circuit-Board (PCB); single-sided copper; tin-plated; mounting pad for collector 1 cm².



45 V, 500 mA NPN general-purpose transistors

Thermal characteristics 6


Table 7. Thermal characteristics

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
R _{th(j-a)}	· · · · · · · · , · · · ·	in free air	[1] [2]	-	-	500	K/W
	to ambient		[3] [2]	-	-	362	K/W

[1] Device mounted on an FR4 Printed-Circuit-Board (PCB); single-sided copper; tin-plated and standard footprint.

Valid for all available selection groups.

[2] Valid for all available selection groups.
 [3] Device mounted on an FR4 Printed-Circuit-Board (PCB); single-sided copper; tin-plated; mounting pad for collector 1 cm².



45 V, 500 mA NPN general-purpose transistors

Characteristics 7


Table 8. Characteristics

T_{amb} = 25 °C unless otherwise specified.


Symbol	Parameter	Conditions		Min	Тур	Мах	Unit
V _{(BR)CBO}	collector-base breakdown voltage	I _C = 100 μΑ; I _E = 0 Α		50	-	-	V
V _{(BR)CEO}	collector-emitter breakdown voltage	I _C = 10 mA; I _B = 0 A		45	-	-	V
V _{(BR)EBO}	emitter-base breakdown voltage	I _E = 100 μΑ; I _C = 0 Α		5	-	-	V
I _{CBO}	collector-base	V _{CB} = 20 V; I _E = 0 A		-	-	100	nA
	cut-off current	V _{CB} = 20 V; I _E = 0 A; T _j = 150 °C		-	-	5	μA
I _{EBO}	emitter-base cut-off current	V _{EB} = 5 V; I _C = 0 A		-	-	100	nA
h _{FE}	DC current gain						
	BC817	V _{CE} = 1 V; I _C = 100 mA	[1]	100	-	600	
	BC817-16	V _{CE} = 1 V; I _C = 100 mA	[1]	100	-	250	
	BC817-25	V _{CE} = 1 V; I _C = 100 mA	[1]	160	-	400	
	BC817-40	V _{CE} = 1 V; I _C = 100 mA	[1]	250	-	600	
h _{FE}	DC current gain	V _{CE} = 1 V; I _C = 500 mA	[1]	40	-	-	
V _{CEsat}	collector-emitter saturation voltage	I _C = 500 mA; I _B = 50 mA	[1]	-	-	700	mV
V _{BE}	base-emitter voltage	V _{CE} = 1 V; I _C = 500 mA	[1] [2]	-	-	1.2	V
f _T	transition frequency	V _{CE} = 5 V; I _C = 10 mA; f = 100 MHz		100	-	-	MHz
C _c	collector capacitance	V _{CB} = 10 V; I _E = i _e = 0 A; f = 1 MHz		-	3	-	pF

6/15


BC817 series



BC817 series



BC817 series



45 V, 500 mA NPN general-purpose transistors


8 Test information

8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - Stress test qualification for discrete semiconductors, and is suitable for use in automotive applications.


9 Package outline

Table 9. Package outline



45 V, 500 mA NPN general-purpose transistors

10 Soldering



BC817_SER
Product data sheet

45 V, 500 mA NPN general-purpose transistors

11 Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes		
BC817 v.7	20180618	Product data sheet	-	BC817_BC817W_BC337 v.6		
Modifications:	Nexperia. • Legal text • Removed • Added Fig Fig 2. and • Graphs in • Added se	s have been adapted to the new basic types: BC327 and BC807 g 1. Power derating curves in se I Fig 3. in section "Thermal char section "Characteristics" are so ctions 8 "Test information" and s Section "Packing information"	stics" are sorted in new order. nation" and 9 "Soldering".			
BC817_BC817W_BC337 v.6	20091117	Product data sheet	-	BC817_BC817W_BC337 v.5		
BC817_BC817W_BC337 v.5	20050221	Product data sheet	CPCN200302007F CPCN200405006F	BC817 v.4; BC817W_SER v.4; BC337 v.3		
BC817 v.4	20040116	Product Specification	-	BC817 v.3		
BC817W_SER v.4	20040225	Product Specification	-	BC817W_SER v.3		
BC337 v.3	19990415	Product Specification	_	BC337 338 CNV v.2		

45 V, 500 mA NPN general-purpose transistors

12 Legal information

12.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

12.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification - The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

12.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Suitability for use in automotive applications - This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk

BC817 SER **Product data sheet**

45 V, 500 mA NPN general-purpose transistors

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

BC817 series

45 V, 500 mA NPN general-purpose transistors

Contents

Product profile	
General description	1
Features and benefits	1
Applications	1
Quick reference data	2
Pinning information	2
Ordering information	2
Marking	3
Limiting values	
Thermal characteristics	5
Characteristics	6
Test information	10
Quality information	10
Package outline	
Soldering	11
Revision history	12
Legal information	
	General description Features and benefits Applications Quick reference data Pinning information Ordering information Marking Limiting values Thermal characteristics Characteristics Test information Quality information Package outline Soldering Revision history

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2018.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 18 June 2018 Document identifier: BC817_SER