

NLC453232T-220K-PF



Applications	Commercial Grade	
Feature	No Directivity Wire Wound Wire Wound Ferrite Core	
Series Type	NLC453232	
Status	Production (Not Recommended for New Design) Recommended Alternate Part No. : Contact	
Brand	TDK	



	Size	
Length(L)	4.50mm ±0.30mm	
Width(W)	3.20mm ±0.20mm	
Thickness Height	3.20mm ±0.20mm	
Recommended Land Pattern (A)	1.50mm Nom.	
Recommended Land Pattern (B)	3.00mm Nom.	
Recommended Land Pattern (C)	2.80mm Nom.	

Electrical Characteristics		
Inductance	22μH ±10% at 2.52MHz	
Rated Current	370mA	
DC Resistance [Typ.]		
DC Resistance [Max.]	900mΩ	
Self Resonant Frequency [Min.]	18MHz	
Self Resonant Frequency [Typ.]		
Q [Min.]	10	
Q [Typ.]		

Other			
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105°C		
	Wave (Flow)		
Soldering Method	Reflow		
	Iron Soldering		
AEC-Q200	No		
Packing	Blister (Plastic)Taping [180mm Reel]		
Package Quantity	500pcs		
Weight	0.18g		

[!] Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.


[!] All specifications are subject to change without notice.





NLC453232T-220K-PF





Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)














[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.







NLC453232T-220K-PF



Associated Images





[!] Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.