

INTERCONNECTS

SERIES 351 • 2,54 GRID INTERCONNECT HEADERS • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3

- Series 351 interconnect header strips come in three lengths with 0,46 dia. pluggable solder tails at one end and 0,64 dia. pins at the other. Please see series:
351...003 uses pin #5503
351...004 uses pin #5504
351...005 uses pin #5505
- 0,46 pluggable solder tails are available at both ends. Please see series:
351...009 uses pin #5509
351...010 uses pin #5510
351...011 uses pin #5511
See pages 212 and 214 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 351...003	0,46 / 0,64 Dia. Solder Tails
	351-10-1- <u> </u> -00-003000	↑ Specify number of pins 01-64
FIG. 2	Series 351...009	0,46 / 0,46 Dia. Solder Tails
	351-10-1- <u> </u> -00-009000	↑ Specify number of pins 01-64
FIG. 2	Series 351...004	0,46 / 0,64 Dia. Solder Tails
	351-10-1- <u> </u> -00-004000	↑ Specify number of pins 01-64
FIG. 3	Series 351...010	0,46 / 0,46 Dia. Solder Tails
	351-10-1- <u> </u> -00-010000	↑ Specify number of pins 01-64
FIG. 3	Series 351...005	0,46 / 0,64 Dia. Solder Tails
	351-10-1- <u> </u> -00-005000	↑ Specify number of pins 01-64
FIG. 3	Series 351...011	0,46 / 0,46 Dia. Solder Tails
	351-10-1- <u> </u> -00-011000	↑ Specify number of pins 01-64



XX=Plating Code
See Below

For
Electrical, Mechanical
& Environmental Data,
See page 264

SPECIFY PLATING CODE XX=	10 ◆			
Pin Plating	0,25µm Au			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[351-10-164-00-011000](#) [351-10-164-00-009000](#) [351-10-164-00-005000](#) [351-10-164-00-004000](#) [351-10-164-00-003000](#) [351-10-132-00-011000](#) [351-10-132-00-009000](#) [351-10-132-00-005000](#) [351-10-132-00-004000](#) [351-10-132-00-003000](#) [351-10-120-00-009000](#) [351-10-120-00-004000](#) [351-10-120-00-003000](#) [351-10-110-00-004000](#) [351-10-112-00-004000](#)