



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|-----------------|
| L | 23mm MAX |
| T | 23mm MAX |
| H | 14.5mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 10mm +/-0.5mm |
| S1 | 18.5mm +/-0.5mm |
| Wire Size | 0.3mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Tray |
| Packaging Quantity | 420 |
| Component Weight | 13 g |

General Information

| | |
|---------------|---|
| Series | SSR21NV-M/NH-M |
| Style | Through-Hole |
| Features | High Performance, High Impedance, Strong Inductance |
| RoHS | Yes |
| Miscellaneous | 65 (K) Temperature Rise Max. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|----------------|
| Voltage AC | 250 VAC |
| Inductance | 68 mH (10 kHz) |
| Current | 800 mA |
| Temperature Range | -25/+120°C |
| DC Resistance | 800 mOhms |