

AC30V Series

Technical Specifications

Overloads

- Heavy Duty Ratings; 150 % for 30 s, 180 % for 0.5 s
- Normal Duty Ratings; 110 % for 30 s, 180 % of heavy duty FLC for 0.5 s

Output Frequency

- 0.5 - 1500 Hz dependant upon switching frequency

Operating Range

- Heavy Duty Ratings; 0 - 45 °C
- Normal Duty Ratings; 0 - 40 °C
Derate from temperatures above to 50 °C max.
- Altitude up to 2000 m ASL
Derate above 1000 m

Environment

- Conformally coated to 3C3 and 3C4 for Hydrogen Sulphide (H₂S) as standard
- Optional Internal EMC filter meets requirements of EN61800-3 C2 1st environment
- Integral DC choke above 2.2 kW reduces harmonics to within limits set by EN61000-3-12

Switching Frequency

- Output switching frequencies up to 12 kHz

Dynamic Braking

- Each drive is fitted with an internal dynamic brake switch 100 % continuously rated

Inputs/Outputs


- Analogue Inputs 2; (1 - ±10 V), (1 - ±10 V) or (0-20 mA)
 - Analogue Outputs 2; (1 - 0-10 V or 0-20 mA), (1 - ±10 V)
 - Digital Inputs 3; Nominal 24 VDC
 - Digital Inputs/Outputs 4; Nominal 24 VDC
 - Relay Outputs 2; Volt free relay contacts, 3 A at 230 VAC max.
 - Reference Supplies +10 VDC (10 mA max) -10 VDC (10 mA max) +24 VDC (140 mA max)
- Safe Torque Off (STO)**
- STO connection in accordance with EN13849 to PLe Cat 3 and SIL3 to EN61800-5-2

Optional Equipment


- Communications Modules
 - CANopen
 - CC Link
 - DeviceNet
 - EtherCAT
 - Modbus TCP/IP
 - PROFIBUS
 - PROFINET
 - EtherCAT
 - BACnet IP
 - ControlNet
 - DeviceNet
 - BACnet MSTP
- I/O Expansion Module providing;
 - 6 Digital I/O; user configurable
 - 2 Relay outputs 3 A at 230 VAC
 - 3 Analogue inputs ±10 V
 - Real time clock
 - Thermistor Input

Standards


- AC30V series meets the following standards when installed in accordance with the relevant product manual.
- CE marked to EN61800-5-1 (Safety, Low Voltage)
- CE marked to EN61800-3 (EMC)
- NTRL listed to US safety standard UL508C
- NTRL listed to Canadian standard C22.2#14



Frame D



Frame E



Frame F

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates, Dubai
Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, Wiener Neustadt
Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt
Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles
Tel: +32 (0)67 280 900
parker.belgium@parker.com

BY – Belarus, Minsk
Tel: +375 17 209 9399
parker.belarus@parker.com

CH – Switzerland, Etoy
Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens
Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budapest
Tel: +36 23 885 470
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty
Tel: +7 7272 505 800
parker.easteurope@parker.com

NL – The Netherlands, Oldenzaal
Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Asker
Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev
Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

US – USA, Cleveland
Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

CN – China, Shanghai
Tel: +86 21 2899 5000

HK – Hong Kong
Tel: +852 2428 8008

IN – India, Mumbai
Tel: +91 22 6513 7081-85

JP – Japan, Tokyo
Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul
Tel: +82 2 559 0400

MY – Malaysia, Shah Alam
Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

SG – Singapore
Tel: +65 6887 6300

TH – Thailand, Bangkok
Tel: +662 186 7000-99

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos
Tel: +55 800 727 5374

CL – Chile, Santiago
Tel: +56 2 623 1216

MX – Mexico, Apodaca
Tel: +52 81 8156 6000



Ratings									
380-480 (±10 %) VAC Supplies Three Phase									
Normal Duty				Heavy Duty					
kW	hp	Output Current A _{rms}		kW	hp	Output Current A _{rms}		Frame	
		400 VAC	480 VAC			400 VAC	480 VAC		
1.1	1.5	3.5	3.0	0.75	1	2.5	2.1	D	
1.5	2	4.5	3.4	1.1	1.5	3.5	3.0	D	
2.2	3	5.5	4.8	1.5	2	4.5	3.4	D	
3	4	7.5	5.8	2.2	3	5.5	4.8	D	
4	5	10	7.6	3	4	7.5	5.8	D	
5.5	7.5	12	11	4	5	10	7.6	D	
7.5	10	16	14	5.5	7.5	12	11	E	
11	15	23	21	7.5	10	16	14	E	
15	20	32	27	11	15	23	21	F	
18	25	38	36	15	20	32	27	F	

Dimensions (all dimensions are in millimeters)			
Frame	H	W	D
D	286	100	255
E	333	125	255
F	383	150	255

We reserve the right to change the product specification without prior notice

We reserve the right to make technical changes. The data correspond to the technical state at the time of printing.
© 2012 Parker Hannifin Corporation. All rights reserved. 192-300020N3 October 2012



EMEA Product Information Centre
Free phone: 00 800 27 27 5374
(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)
US Product Information Centre
Toll-free number: 1-800-27 27 537
www.parker.com

Your local authorized Parker distributor



ENGINEERING YOUR SUCCESS.

aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding

AC30V Variable Speed Drive

For the Control of Pump, Fan and General Purpose Applications

0.75 - 18.5 kW

AC30V Series AC Drive - Engineered for Flexibility, Simplicity and Reliability

0.75 - 18.5 kW

AC30V drive has been designed to provide users with exceptional levels of control for pump, fan and general purpose applications. Its flexible and highly modular construction enables a wide range of communications and I/O modules to be easily added as required.


The AC30V has been designed with simplicity in mind, but this doesn't compromise its functionality. Integrated macros for a range of applications and PLC functionality enable more capable users to create sophisticated control that would previously have required a separate PLC.

Designed for operation in environment class 3C3 and 3C4 for (H₂S) as standard, temperatures up to 50 °C with optional integrated EMC filter to C2 1st environment and DC choke to reduce line harmonics.



Engineered for all environments

- Conformally coated as standard allowing the drive to be used in both Classes 3C3 and 3C4 for Hydrogen Sulphide gas (H₂S) at a concentration of 25 ppm for 1200 hours. It is also compliant to both Classes 3C1 (rural) and 3C2 (urban) for all nine defined substances in table 4 in EN60271-3-3
- Internal EMC filter options up to C2 1st environment for use in commercial buildings
- CE marked to EN61800-5-1 and NTRL listed to UL508C and C22.2#14
- DC chokes above 2.2 kW reduce harmonics to below IEC/EN61000-3-12 limits
- Complies with the RoHS substances restrictions in accordance with EC Directive 2011/65/EU
- Automatic restarting and power ride through functions compensate against unstable power supplies



Engineered cooling improves reliability

- Intelligent design minimises force ventilation requirements
- Removable fan improves maintainability
- Isolated power stack cooling path reduces contamination of control electronics

Unobstructed access to power and dynamic brake terminals

- Terminal covers removable with drive in-situ
- Dynamic brake switch fitted as standard

Suitable for harsh environments

- AC30V is conformally coated as standard and meets the requirements of environment classes 3C1, 3C2 (all defined substances) plus 3C3 and 3C4 for Hydrogen Sulphide (H₂S)

Suited to all environments

- Internal EMC filter options up to C2 1st environment for use in commercial buildings
- CE marked to EN61800-5-1 and NTRL listed to UL508C and C22.2#14
- DC chokes above 2.2 kW reduce harmonics to below IEC/EN61000-3-12 limits

Compact footprint, chassis or through-panel mounting

- Multi-position feet with keyhole slots for ease of mounting
- Reduced heat radiation allows side-by-side mounting

IEC61131 PLC functionality included

- The included PLC functionality enables AC30V to take greater control of its surrounding and in some instances removes the need for an external PLC altogether

Ethernet connectivity and inbuilt diagnostic web pages

- Inbuilt web pages allow AC30V to be interrogated over the onboard Ethernet and Modbus TCP/IP connection

Simplified configuration and data storage with SD cards

- SD card simplifies firmware updates and allows drive configuration and data to be stored

Intuitive and easy to use, multi-function graphical keypad

- Remote mountable and easy to use tactile keypad makes drive setup and operation simple

Field-fittable communications

- Seamless integration into automation systems



Expandable I/O capabilities

- A range of option modules expand AC30V to accommodate application specific I/O
- Spring clamp terminals reduce installation time and risk of loose connections

Safe-Torque-Off (STO) for safety critical applications

- Protecting users and machinery against unexpected motor start-up in accordance with EN13849-1 at PLe Cat3 or SIL 3 to EN61800-5-2

Engineered for energy-savings

Pumps and fans are frequently oversized for the application they are used in and often consume significantly more power than needed. Matching motor speeds to varying demands reduces energy consumption, extends mechanical life and most importantly, saves money. AC30V is the perfect drive to achieve this with integrated energy monitoring functionality and enhanced efficiency.

Engineered for all motors

The AC30V offers effective and affordable control of either AC induction motors or permanent magnet (PMAC) servo motors.

PMAC motors offer additional benefits over standard AC induction motors

- Up to 10 % more energy saving
- Up to 75 % smaller

Engineered for performance

Graphical keypad
The tactile IP55 keypad can be mounted either on the drive itself or remotely and provides access to all drive functions. The backlit LCD display can present information in any one of a number of different languages, or even in your own custom language with your own user-defined units.

Simple setup wizard and macros
Integrated quick start wizards means you don't have to be an expert to configure the drive within minutes. Dedicated macros and integrated function blocks simplify the creation of specific motor control applications.

Communications options
AC30V supports a host of popular fieldbus communication networks as well as having Ethernet and Modbus TCP as standard.

I/O option modules
Functionality can be extended with the addition of an optional I/O module. These include real time clock, thermistor and expanded analogue and digital I/O.