



CMOS/ 1.8V/ 2.5×2.0mm



RoHS Compliant

Features

- Miniature ceramic package
2.5 (L) × 2.0 (W) × 0.7 (H) mm (Typ.)
- High Stability Output Frequency
±10×10⁻⁶ (-10 to +70°C)
±15×10⁻⁶ (-40 to +85°C)
- CMOS output
- Supply voltage V_{CC}=1.8V
Low Power Supply Consumption

Applications

- Wi-Fi, Bluetooth* etc.
- * Bluetooth* is a registered trademarks of Bluetooth SIG Inc.

How to Order

KC2520C 40.000 C 1 □ E 00
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series
- ② Output Frequency
- ③ Output Type (CMOS)
- ④ Supply Voltage (1.8V)
- ⑤ Frequency Tolerance (See Table 1)
- ⑥ Symmetry/ INH Function (45/ 55%)
- ⑦ Individual Specification (STD Specification is "00")

Packaging (Tape & Reel 2000 pcs./ reel)

Table 1

Code	Freq. Tol.	Operating Temperature Range (°C)	Note
	× 10 ⁻⁶		
Y	±10	-10 to +70	Please contact us for available frequencies.
K	±20	-40 to +85	Standard specifications
L	±15		


Specifications

Item	Symbol	Conditions	Min.	Max.	Units
Output Frequency Range	f _o		1.5	54	MHz
Frequency Tolerance	f _{tol}	Initial tolerance, Operating temperature range, Rated power supply voltage change, Aging (1 year @25°C), Shock and vibration	Temp.: -40 to +85°C Temp.: -40 to +85°C Temp.: -10 to +70°C	-15 +15 +10	×10 ⁻⁶
Storage Temperature Range	T _{stg}		-55	+125	°C
Operating Temperature Range	T _{use}		-10	+70	°C
Max. Supply Voltage	—		-0.3	+4.0	V
Supply Voltage	V _{CC}		+1.6	+2.0	V
Current Consumption (Maximum Loaded)	I _{CC}	CL≤15pF	1.5≤f _o <24MHz 24≤f _o ≤54MHz	4 4.5	mA
Stand-by Current	I _{std}		—	5	μA
Symmetry	SYM	@50% V _{CC}	45	55	%
Rise/ Fall Time (10% V _{CC} to 90% V _{CC} Maximum Loaded)	Tr/ Tf		—	4	ns
Low Level Output Voltage	V _{OL}	I _{OL} =4mA	—	10% V _{CC}	V
High Level Output Voltage	V _{OH}	I _{OH} =-4mA	90% V _{CC}	—	V
CMOS Load	L _{CMOS}	CMOS Output	—	15	pF
Input Voltage Range	V _{IN}		0	V _{CC}	V
Low Level Input Voltage	V _{IL}		—	30% V _{CC}	V
High Level Input Voltage	V _{IH}		70% V _{CC}	—	V
Disable Time	t _{dis}		—	100	ns
Enable Time	t _{ena}		—	5	ms
Start-up Time	t _{str}	@Minimum operating voltage to be 0 sec.	—	10	ms
1 Sigma Jitter	J _{Sigma}	Measured with Wavecrest SIA-3000	—	8	ps
Peak to Peak Jitter	J _{PK-PK}		—	80	ps

Note: All electrical characteristics are defined at the maximum load and operating temperature range.
Please contact us for inquiry about operating temperature range, available frequencies and other conditions.


Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KYOCERA AVX:

[KC2520B27.0000C20E00](#) [KC2520B48.0000C10E00](#) [KC2520B27.0000C10E00](#) [KC2520B25.0000C10E00](#)
[KC2520B24.0000C10E00](#) [KC2520B14.3182C10E00](#) [KC2520B24.5760C10E00](#) [KC2520B25.0000C1GE00](#)
[KC2520B33.3333C1GE00](#) [KC2520B4.09600C1GE00](#) [KC2520B48.0000C1GE00](#) [KC2520B7.37280C1GE00](#)
[KC2520B25.0000C2GE00](#) [KC2520B27.0000C2GE00](#) [KC2520B33.3333C2GE00](#) [KC2520B48.0000C2GE00](#)
[KC2520B12.0000C10E00](#) [KC2520B14.7456C1GE00](#) [KC2520B33.3333C1GESH](#) [KC2520B50.0000C1FE00](#)
[KC2520B50.0000C1GE00](#) [KC2520B66.6667C1GE00](#) [KC2520B16.0000C20EME](#) [KC2520C38.4000C1LE00](#)
[KC2520B16.0000C10E00](#) [KC2520B30.0000C10E00](#) [KC2520B40.0000C10E00](#) [KC2520B50.0000C10E00](#)
[KC2520C26.0000C1LE00](#) [KC2520C26.0000C1YE00](#) [KC2520C38.4000C1YE00](#) [KC2520C40.0000C1LE00](#)
[KC2520B7.37280C2GE00](#) [KC2520B4.09600C2GE00](#) [KC2520B80.0000C1GE00](#) [KC2520B10.0000C1GE00](#)
[KC2520B3.68640C1GE00](#) [KC2520B20.0000C1GE00](#) [KC2520B60.0000C1GE00](#) [KC2520B14.3182C1GE00](#)
[KC2520B16.0000C1GE00](#) [KC2520B30.0000C1GE00](#) [KC2520B8.00000C1GE00](#) [KC2520B49.1520C1GE00](#)
[KC2520B40.0000C1GE00](#) [KC2520B4.00000C1GE00](#) [KC2520B24.0000C1GE00](#) [KC2520B12.0000C1GE00](#)
[KC2520B19.2000C1GE00](#) [KC2520B6.00000C1GE00](#) [KC2520B1.84320C1GE00](#) [KC2520B16.3840C1GE00](#)
[KC2520C24.0000C1LE00](#) [KC2520B27.0000C1GE00](#) [KC2520C40.0000C1YE00](#) [KC2520C24.0000C1YE00](#)
[KC2520C16.3840C1KE00](#)