

## SSR21NV-M031900

Aliases (UALM21V0319000)

KEMET, SSR21NV-M/NH-M, AC Line Filters, Common Mode, 190 mH



Click [here](#) for the 3D model.

### Dimensions

L	22mm MAX
T	16mm MAX
H	27mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.2mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	450
Component Weight	14.5 g

### General Information

Series	SSR21NV-M/NH-M
Style	Through-Hole
Features	High Performance, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	45 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	190 mH (10 kHz)
Current	300 mA
Temperature Range	-25/+120°C
DC Resistance	2.9 Ohms