TECHNICAL DATA

Version 13

AT175 Polycoated Cloth Tape

General Description

A polycloth extruded gloss tape with a white pressure sensitive, aggressive adhesive.

- Easy unwind and very easy tear
- Good abrasion resistance
- Very high tack
- Clean peel
- Water resistant finish
- Writable surface
- · Conformable to awkward shapes
- Non-corrosive adhesive
- Wide colour range



Technical Details

Typical Values

Thickness 0.23mm

Breaking Load 32 N/cm

Elongation 24%

Adhesion

Steel 5.5 N/cm

Self 3.5 N/cm

Moisture Vapour Permeability 20g/m₂/24 hrs

Water Extract

pH. 60 to 8.0

Chloride Max 0.01% as NaCl

Sulphate Max 0.01% as Na₂SO₄

RoHS compliant Yes

Service Temperature -50 °C to +80 °C

Application Temperature +10 °C to +45 °C

Storage Temperature +12 °C to +25 °C

NOT

Except where indicated otherwise, the figures stated are average values and should not be regarded as MAXIMUM or MINIMUM values for specification purposes. The Company reserves the right to improve products and any change in specification will result in a re-issue of the relevant 'Technical Data Sheet'. Customers should satisfy themselves that the tape is suitable for their requirements whether after such modifications or otherwise. Please check that you have the latest issue of the 'Technical Data Sheet'. All slitting and length tolerances are to British Standards. Before use the customer is advised to consult the Health & Safety Data Sheet produced by the company for this product, which is available on request.

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.





AFERA

Association des Fabricants Européens de Rubans Auto-Adhésifs.

Adding more to adhesive tape

Advance Tapes International Limited Westmoreland Avenue Thurmaston Leicester LE4 8PH

England

Tel. +44 (0)116 251 0191 Fax. +44 (0)116 265 2046 contact@advancetapes.com



www.advancetapes.com Q05026