

# PIN RECEPTACLES

FOR .032" - .046" DIAMETER PINS

<p><b>0359</b> 0359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p><b>0358</b> 0358-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p><b>0360</b> 0360-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>	<p><b>0343</b> 0343-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>
<p><b>0356</b> 0356-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel See page 194.11 for Tape &amp; Reel details</p>	<p><b>6659</b> 6659-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole</p>	<p><b>0347</b> 0347-0-15-XX-34-XX-10-0 Solder mount in .120 min. mounting hole</p>	<p><b>0329</b> 0329-0-15-XX-34-XX-10-0 Solder mount in .075 min. mounting hole. "Knock out" bottom</p>
<p><b>0814</b> 0814-0-15-XX-34-XX-04-0 Solder mount in .082 min. mounting hole</p>	<p><b>5059</b> 5059-0-15-XX-34-XX-04-0 Press-fit in .090 mounting hole</p>	<p><b>8360</b> 8360-0-15-XX-34-XX-10-0 Press-fit in .087 mounting hole</p>	<p><b>9359</b> 9359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole</p>

**SPECIFICATIONS:**

**Shell Material:** Brass Alloy 360, 1/2 Hard  
**Contact Material:** Beryllium Copper Alloy 172, HT  
**Dimensions:** Inches  
**Tolerances On:** Lengths: ±.005  
 Diameters: ±.002  
 Angles: ±2°



**ORDER CODE: XXXX - X - XX - XX - 34 - XX - XX - 0**

**BASIC PART #**

**SPECIFY SHELL FINISH:**

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

**SELECT CONTACT:**

**#34 CONTACT (DATA ON PAGE 258)**

(For alternate contact choices, see group E on page 248)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mill-Max:

[8360-0-15-01-34-01-10-0](#) [6659-0-15-01-34-01-10-0](#) [6659-0-15-01-34-27-10-0](#) [0359-0-15-80-34-80-10-0](#) [0360-0-15-15-34-27-10-0](#) [0329-0-15-15-34-27-10-0](#) [0329-0-15-01-34-27-10-0](#) [0360-0-15-01-34-27-10-0](#) [0814-0-15-01-34-01-04-0](#) [0814-0-15-01-34-27-04-0](#) [0360-0-15-01-34-01-10-0](#) [0359-0-15-01-34-01-10-0](#) [0358-0-15-01-34-01-10-0](#) [0356-0-15-01-34-01-10-0](#) [0356-0-15-01-34-27-10-0](#) [0347-0-15-01-34-01-10-0](#) [0347-0-15-01-34-27-10-0](#) [0343-0-15-01-34-01-10-0](#) [0343-0-15-01-34-27-10-0](#) [0329-0-15-01-34-01-10-0](#) [6659-0-15-80-34-80-10-0](#) [6659-0-15-80-34-27-10-0](#) [0343-0-15-15-34-27-10-0](#) [0347-0-15-15-34-27-10-0](#) [0356-0-15-15-34-27-10-0](#) [0359-0-15-15-34-27-10-0](#) [0814-0-15-15-34-27-04-0](#) [6659-0-15-15-34-27-10-0](#) [0360-0-15-00-00-00-10-0](#) [0347-0-15-00-00-00-10-0](#) [0359-0-15-00-00-00-10-0](#) [0358-0-15-00-00-00-10-0](#) [6659-0-15-00-00-00-10-0](#) [5059-0-15-00-00-00-04-0](#) [8360-0-15-00-00-00-10-0](#) [0329-0-15-00-00-00-10-0](#) [0356-0-15-00-00-00-10-0](#) [0343-0-15-00-00-00-10-0](#) [0814-0-15-00-00-00-04-0](#) [0359-0-15-01-34-14-10-0](#) [0358-0-15-80-34-14-10-0](#) [0360-0-15-80-34-14-10-0](#) [0347-0-15-80-34-14-10-0](#) [0329-0-15-01-34-14-10-0](#) [0347-0-15-01-34-14-10-0](#) [0358-0-15-01-34-14-10-0](#) [0814-0-15-80-34-14-04-0](#) [0359-0-15-80-34-14-10-0](#) [0329-0-15-80-34-14-10-0](#) [0356-0-15-80-34-14-10-0](#) [0814-0-15-01-34-14-04-0](#) [0356-0-15-01-34-14-10-0](#) [0343-0-15-80-34-14-10-0](#) [0343-0-15-01-34-14-10-0](#) [0360-0-15-01-34-14-10-0](#) [0343-0-15-15-34-14-10-0](#) [0814-0-15-15-34-14-04-0](#) [8360-0-15-80-34-14-10-0](#) [6659-0-15-80-34-14-10-0](#) [5059-0-15-15-34-14-04-0](#) [9359-0-15-01-34-14-10-0](#) [5059-0-15-80-34-14-04-0](#) [6659-0-15-01-34-14-10-0](#) [8360-0-15-01-34-14-10-0](#) [9359-0-15-80-34-14-10-0](#) [5059-0-15-01-34-14-04-0](#)