

# 1.8V Low-Power Push-Pull Output Comparator

#### **Features**

- Propagation Delay at 1.8 V<sub>DD</sub>:
  - 56 ns (typical) high-to-low
  - 49 ns (typical) low-to-high
- Low Quiescent Current: 100 μA (typical)
- Input Offset Voltage: ±3 mV (typical)
- Rail-to-Rail Input:  $V_{SS} 0.3V$  to  $V_{DD} + 0.3V$
- · CMOS/TTL-Compatible Output
- Wide Supply Voltage Range: 1.8V to 5.5V
- · Available in Single, Dual and Quad
- · Packages: SC70, SOT-23, SOIC, MSOP, TSSOP

#### **Typical Applications**

- · Laptop Computers
- · Mobile Phones
- · Handheld Electronics
- · RC Timers
- · Alarm and Monitoring Circuits
- · Window Comparators
- Multivibrators


#### **Design Aids**

- · Microchip Advanced Part Selector (MAPS)
- · Analog Demonstration and Evaluation Boards
- · Application Notes

#### **Related Devices**

• Open-Drain Output: MCP6566/6R/6U/7/9

#### **Typical Application**




#### **Description**

The Microchip Technology Inc. MCP6561/1R/1U/2/4 families of CMOS/TTL-compatible comparators are offered in single, dual and quad configurations.

These comparators are optimized for low-power 1.8V, single-supply applications with greater than rail-to-rail input operation. The internal input hysteresis eliminates output switching due to internal input noise voltage, reducing current draw. The push-pull output of the MCP6561/1R/1U/2/4 family supports rail-to-rail output swing and interfaces with CMOS/TTL logic. The output toggle frequency can reach a typical of 4 MHz while limiting supply current surges and dynamic power consumption during switching.

This family operates with a single-supply voltage of 1.8V to 5.5V, while drawing less than 100 µA/comparator of quiescent current (typical).

### **Package Types**



NOTES:

# 1.0 ELECTRICAL CHARACTERISTICS

### 1.1 Absolute Maximum Ratings†

$V_{DD} - V_{SS}$	
All Other Inputs and OutputsV <sub>SS</sub>	
Difference Input voltage	V <sub>DD</sub> – V <sub>SS</sub>
Output Short-Circuit Current	±25 mA
Current at Input Pins	±2 mA
Current at Output and Supply Pins	±50 mA
Storage Temperature	65°C to +150°C
Ambient Temp. with Power Applied	40°C to +125°C
Junction Temp	+150°C
ESD Protection on All Pins (HBM/MM).	≥ 4 kV/300V

- Notice: Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.
- †† See Section 4.1.2 "Input Voltage and Current Limits".

#### **DC CHARACTERISTICS**

Electrical Characteristics: Unless otherwise indicated:  $V_{DD}$  = +1.8V to +5.5V,  $V_{SS}$  = GND,  $T_A$  = +25°C,  $V_{IN}$ + =  $V_{DD}$ /2,  $V_{IN}$ - =  $V_{SS}$ ,  $R_I$  = 10 kΩ to  $V_{DD}$ /2 (see Figure 1-1).

$R_L = 10 \text{ k}\Omega$ to $V_{DD}/2$ (see Figure 1-1	$R_{\rm L} = 10 \text{ k}\Omega$ to $V_{\rm DD}/2$ (see Figure 1-1).								
Parameters	Symbol	Min	Тур	Max	Units	Conditions			
Power Supply									
Supply Voltage	$V_{DD}$	1.8	_	5.5	V				
Quiescent Current per Comparator	IQ	60	100	130	μA	I <sub>OUT</sub> = 0			
Power Supply Rejection Ratio	PSRR	63	70	_	dB	V <sub>CM</sub> = V <sub>SS</sub>			
Input									
Input Offset Voltage	Vos	-10	±3	+10	mV	V <sub>CM</sub> = V <sub>SS</sub> (Note 1)			
Input Offset Drift	$\Delta V_{OS}/\Delta T$	_	±2	_	μV/°C	V <sub>CM</sub> = V <sub>SS</sub>			
Input Offset Current	Ios	_	±1	_	pА	V <sub>CM</sub> = V <sub>SS</sub>			
Input Bias Current	I <sub>B</sub>	_	1	_	pА	$T_A = +25^{\circ}C, V_{IN} = V_{DD}/2$			
		_	60	_	pА	$T_A = +85^{\circ}C, V_{IN} = V_{DD}/2$			
			1500	5000	pА	$T_A = +125$ °C, $V_{IN}$ -= $V_{DD}/2$			
Input Hysteresis Voltage	V <sub>HYST</sub>	1.0		5.0	mV	V <sub>CM</sub> = V <sub>SS</sub> (Notes 1, 2)			
Input Hysteresis Linear Temp. Co.	TC <sub>1</sub>		10	_	μV/°C				
Input Hysteresis Quadratic Temp. Co.	TC <sub>2</sub>	_	0.3	_	μV/°C <sup>2</sup>				
Common-Mode Input Voltage	V <sub>CMR</sub>	$V_{SS} - 0.2$	_	V <sub>DD</sub> + 0.2	V	V <sub>DD</sub> = 1.8V			
Range		V <sub>SS</sub> - 0.3	_	V <sub>DD</sub> + 0.3	V	V <sub>DD</sub> = 5.5V			
Common-Mode Rejection Ratio	CMRR	54	66	_	dB	$V_{CM} = -0.3V$ to $V_{DD} + 0.3V$ , $V_{DD} = 5.5V$			
		50	63	_	dB	$V_{CM} = V_{DD}/2$ to $V_{DD} + 0.3V$ , $V_{DD} = 5.5V$			
		54	65	_	dB	$V_{CM} = -0.3V \text{ to } V_{DD}/2, V_{DD} = 5.5V$			
Common-Mode Input Impedance	Z <sub>CM</sub>		10 <sup>13</sup>   4	_	$\Omega    pF$				
Differential Input Impedance	Z <sub>DIFF</sub>	_	10 <sup>13</sup>   2	_	$\Omega    pF$				
Push-Pull Output									
High-Level Output Voltage	V <sub>OH</sub>	V <sub>DD</sub> – 0.7	_	_	V	$I_{OUT} = -3 \text{ mA/-8 mA with } V_{DD} = 1.8 \text{V}/5.5 \text{V}$ (Note 3)			
Low-Level Output Voltage	V <sub>OL</sub>	_	_	0.6	V	$I_{OUT} = 3 \text{ mA/8 mA with } V_{DD} = 1.8 \text{V}/5.5 \text{V}$ (Note 3)			
Short-Circuit Current	I <sub>SC</sub>		±30	_	mA	Note 3			
Output Pin Capacitance	C <sub>OUT</sub>		8		pF				

Note 1: The input offset voltage is the center of the input referred trip points. The input hysteresis is the difference between the input referred trip points.

- 2:  $V_{HYST}$  at different temperatures is estimated using  $V_{HYST}$  (T<sub>A</sub>) =  $V_{HYST}$  @ +25°C + (T<sub>A</sub> 25°C) TC<sub>1</sub> + (T<sub>A</sub> 25°C)<sup>2</sup> TC<sub>2</sub>.
- 3: Limit the output current to the absolute maximum rating of 50 mA.

### **AC CHARACTERISTICS**

Electrical Characteristics: Unless otherwise indicated:  $V_{DD}$  = +1.8V to +5.5V,  $V_{SS}$  = GND,  $T_A$  = +25°C,  $V_{IN}$ + =  $V_{DD}$ /2,  $V_{IN}$ - =  $V_{SS}$ ,  $R_L$  = 10 kΩ to  $V_{DD}$ /2 and  $C_L$  = 25 pF (see Figure 1-1).

Parameters	Symbol	Min	Тур	Max	Units	Conditions
Propagation Delay						
High-to-Low,100 mV Overdrive	t <sub>PHL</sub>	_	56	80	ns	$V_{CM} = V_{DD}/2, V_{DD} = 1.8V$
		_	34	80	ns	$V_{CM} = V_{DD}/2, V_{DD} = 5.5V$
Low-to-High, 100 mV Overdrive	t <sub>PLH</sub>	_	49	80	ns	$V_{CM} = V_{DD}/2, V_{DD} = 1.8V$
		_	47	80	ns	$V_{CM} = V_{DD}/2, V_{DD} = 5.5V$
Skew <sup>(1)</sup>	t <sub>PDS</sub>	_	±10	_	ns	
Output						
Rise Time	t <sub>R</sub>	_	20	_	ns	
Fall Time	t <sub>F</sub>	_	20	_	ns	
Maximum Toggle Frequency	f <sub>TG</sub>	_	4	_	MHz	V <sub>DD</sub> = 5.5V
		_	2	_	MHz	V <sub>DD</sub> = 1.8V
Input Voltage Noise <sup>(2)</sup>	E <sub>NI</sub>	_	350	_	μV <sub>P-P</sub>	10 Hz to 10 MHz

**Note 1:** Propagation delay skew is defined as:  $t_{PDS} = t_{PLH} - t_{PHL}$ .


2: ENI is based on SPICE simulation.

### **TEMPERATURE SPECIFICATIONS**

<b>Electrical Characteristics:</b> Unless otherwise indicated: V <sub>DD</sub> = +1.8V to +5.5V and V <sub>SS</sub> = GND.								
Parameters	Symbol	Min	Тур	Max	Units	Conditions		
Temperature Ranges								
Specified Temperature Range	T <sub>A</sub>	-40	_	+125	°C			
Operating Temperature Range	T <sub>A</sub>	-40	_	+125	°C			
Storage Temperature Range	T <sub>A</sub>	-65	_	+150	°C			
Thermal Package Resistances								
Thermal Resistance, 5-Lead SC70	$\theta_{JA}$	_	331	_	°C/W			
Thermal Resistance, 5-Lead SOT-23	$\theta_{JA}$	_	220.7	_	°C/W			
Thermal Resistance, 8-Lead SOIC	$\theta_{JA}$	_	149.5	_	°C/W			
Thermal Resistance, 8-Lead MSOP	$\theta_{JA}$	_	211	_	°C/W			
Thermal Resistance, 14-Lead SOIC	$\theta_{JA}$	_	95.3	_	°C/W			
Thermal Resistance, 14-Lead TSSOP	$\theta_{JA}$	_	100	_	°C/W			

# 1.2 Test Circuit Configuration

This test circuit configuration is used to determine the AC and DC specifications.



**FIGURE 1-1:** AC and DC Test Circuit for the Push-Pull Output Comparators.

NOTES:

#### 2.0 TYPICAL PERFORMANCE CURVES

**Note:** The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.




FIGURE 2-1: Input Offset Voltage.





FIGURE 2-2: Input Offset Voltage Drift.



**FIGURE 2-3:** Input vs. Output Signal, No Phase Reversal.




FIGURE 2-4: Input Hysteresis Voltage.




FIGURE 2-5: Input Hysteresis Voltage Drift – Linear Temp. Co. (TC1).




FIGURE 2-6: Input Hysteresis Voltage Drift – Quadratic Temp. Co. (TC2).

**Note:** Unless otherwise indicated:  $V_{DD}$  = +1.8V to +5.5V,  $V_{SS}$  = GND,  $T_A$  = +25°C,  $V_{IN}$ + =  $V_{DD}$ /2,  $V_{IN}$ - = GND,  $R_L$  = 10 k $\Omega$  to  $V_{DD}$ /2 and  $C_L$  = 25 pF.






FIGURE 2-7: Temperature.


Input Offset Voltage vs.




**FIGURE 2-8:** Input Offset Voltage vs. Common-Mode Input Voltage.



**FIGURE 2-9:** Input Offset Voltage vs. Common-Mode Input Voltage.



**FIGURE 2-10:** Input Hysteresis Voltage vs. Temperature.



**FIGURE 2-11:** Input Hysteresis Voltage vs. Common-Mode Input Voltage.





FIGURE 2-12: Input Hysteresis Voltage vs. Common-Mode Input Voltage.



**FIGURE 2-13:** Input Offset Voltage vs. Supply Voltage vs. Temperature.







FIGURE 2-14: Quiescent Current.




**FIGURE 2-15:** Quiescent Current vs. Common-Mode Input Voltage.




**FIGURE 2-16:** Input Hysteresis Voltage vs. Supply Voltage vs. Temperature.




**FIGURE 2-17:** Quiescent Current vs. Supply Voltage vs. Temperature.



**FIGURE 2-18:** Quiescent Current vs. Common-Mode Input Voltage.



**FIGURE 2-19:** Quiescent Current vs. Toggle Frequency.



**FIGURE 2-20:** Output Headroom vs. Output Current.




FIGURE 2-21: Low-to-High and High-to-Low Propagation Delays.





FIGURE 2-22: Short-Circuit Current vs. Supply Voltage vs. Temperature.



**FIGURE 2-23:** Output Headroom vs. Output Current.




FIGURE 2-24: Low-to-High and High-to-Low Propagation Delays.







FIGURE 2-25: Propagation Delay Skew.




**FIGURE 2-26:** Propagation Delay vs. Supply Voltage.



**FIGURE 2-27:** Propagation Delay vs. Common-Mode Input Voltage.



**FIGURE 2-28:** Propagation Delay vs. Temperature.



**FIGURE 2-29:** Propagation Delay vs. Input Overdrive.







FIGURE 2-30: Propagation Delay vs. Common-Mode Input Voltage.




**FIGURE 2-31:** Propagation Delay vs. Capacitive Load.




**FIGURE 2-32:** Input Bias Current vs. Input Voltage vs. Temperature.



**FIGURE 2-33:** Common-Mode Rejection Ratio and Power Supply Rejection Ratio vs. Temperature.



**FIGURE 2-34:** Power Supply Rejection Ratio (PSRR).



**FIGURE 2-35:** Common-Mode Rejection Ratio (CMRR).






FIGURE 2-36: Common-Mode Rejection Ratio (CMRR).



**FIGURE 2-37:** Output Jitter vs. Input Frequency.



**FIGURE 2-38:** Input Offset Current and Input Bias Current vs. Temperature.




FIGURE 2-39: Input Offset Current and Input Bias Current vs. Common-Mode Input Voltage vs. Temperature.

NOTES:

#### 3.0 PIN DESCRIPTIONS

Descriptions of the pins are listed in Table 3-1.

TABLE 3-1: PIN FUNCTION TABLE

MCP6561	MCP6561R	MCP6561U	MCP6562	MCP6564		
SC70, SOT-23	SOT-23	SOT-23	MSOP, SOIC	SOIC, TSSOP	Symbol	Description
1	1	4	1	1	OUT, OUTA	Digital Output (Comparator A)
4	4	3	2	2	V <sub>IN</sub> -, V <sub>INA</sub> -	Inverting Input (Comparator A)
3	3	1	3	3	V <sub>IN</sub> +, V <sub>INA</sub> +	Noninverting Input (Comparator A)
5	2	5	8	4	$V_{DD}$	Positive Power Supply
_	_	_	5	5	V <sub>INB</sub> +	Noninverting Input (Comparator B)
_	_	_	6	6	V <sub>INB</sub> -	Inverting Input (Comparator B)
_	_	_	7	7	OUTB	Digital Output (Comparator B)
_	_	_	_	8	OUTC	Digital Output (Comparator C)
_	_	_	_	9	V <sub>INC</sub> -	Inverting Input (Comparator C)
_	_	_	_	10	V <sub>INC</sub> +	Noninverting Input (Comparator C)
2	5	2	4	11	V <sub>SS</sub>	Negative Power Supply
_	_	_	_	12	V <sub>IND</sub> +	Noninverting Input (Comparator D)
_	_	_	_	13	V <sub>IND</sub> -	Inverting Input (Comparator D)
_	_	_	_	14	OUTD	Digital Output (Comparator D)

#### 3.1 Analog Inputs

The comparator noninverting and inverting inputs are high-impedance CMOS inputs with low bias currents.

#### 3.2 Digital Outputs

The comparator outputs are CMOS push-pull, digital outputs. They are designed to be compatible with CMOS and TTL logic, and are capable of driving heavy DC or capacitive loads.

## 3.3 Power Supply ( $V_{SS}$ and $V_{DD}$ )

The positive power supply pin ( $V_{DD}$ ) is 1.8V to 5.5V higher than the negative power supply pin ( $V_{SS}$ ). For normal operation, the other pins are at voltages between  $V_{SS}$  and  $V_{DD}$ .

Typically, these parts are used in a single (positive) supply configuration. In this case,  $V_{SS}$  is connected to ground and  $V_{DD}$  is connected to the supply.  $V_{DD}$  will need a local bypass capacitor (typically 0.01  $\mu F$  to 0.1  $\mu F$ ) within 2 mm of the  $V_{DD}$  pin. These pins can share a bulk capacitor with nearby analog parts (within 100 mm), but it is not required.

NOTES:

#### 4.0 APPLICATION INFORMATION

The MCP6561/1R/1U/2/4 families of push-pull output comparators are fabricated on Microchip's state-of-the-art CMOS process. They are suitable for a wide range of high-speed applications requiring low-power consumption.

#### 4.1 Comparator Inputs

#### 4.1.1 NORMAL OPERATION

The input stage of these families of devices uses three differential input stages in parallel: one operates at low input voltages, one at high input voltages and one at middle input voltages. With this topology, the input voltage range is 0.3V above  $V_{DD}$  and 0.3V below  $V_{SS}$ , while providing low offset voltage throughout the Common-mode range. The input offset voltage is measured at both  $V_{SS} - 0.3 V$  and  $V_{DD} + 0.3 V$  to ensure proper operation.

The MCP6561/1R/1U/2/4 families have internally set hysteresis  $V_{HYST}$  that is small enough to maintain input offset accuracy and large enough to eliminate output chattering caused by the comparator's own input noise voltage,  $E_{NI}$ . Figure 4-1 depicts this behavior. Input offset voltage ( $V_{OS}$ ) is the center (average) of the (input referred) low-high and high-low trip points. Input hysteresis voltage ( $V_{HYST}$ ) is the difference between the same trip points.




FIGURE 4-1: The MCP6561/1R/1U/2/4 Comparators' Internal Hysteresis Eliminates Output Chatter Caused by Input Noise Voltage.

# 4.1.2 INPUT VOLTAGE AND CURRENT LIMITS

The ESD protection on the inputs can be depicted as shown in Figure 4-2. This structure was chosen to protect the input transistors, and to minimize input bias current ( $I_B$ ). The input ESD diodes clamp the inputs when they try to go more than one diode drop below  $V_{SS}$ . They also clamp any voltages that go too far above  $V_{DD}$ . Their breakdown voltage is high enough to allow normal operation and low enough to bypass ESD events within the specified limits.




FIGURE 4-2: Simplified Analog Input ESD Structures.

In order to prevent damage and/or improper operation of these amplifiers, the circuits they are in must limit the currents (and voltages) at the  $V_{IN}^+$  and  $V_{IN}^-$  pins (see Section 1.1 "Absolute Maximum Ratings†" at the beginning of Section 1.0 "Electrical Characteristics"). Figure 4-3 shows the recommended approach to protecting these inputs. The internal ESD diodes prevent the input pins ( $V_{IN}^+$  and  $V_{IN}^-$ ) from going too far below ground, and the resistors,  $R_1$  and  $R_2$ , limit the possible current drawn out of the input pin. Diodes,  $D_1$  and  $D_2$ , prevent the input pin ( $V_{IN}^+$  and  $V_{IN}^-$ ) from going too far above  $V_{DD}$ . When implemented as shown, resistors,  $R_1$  and  $R_2$ , also limit the current through  $D_1$  and  $D_2$ .




FIGURE 4-3: Protecting the Analog Inputs.

It is also possible to connect the diodes to the left of the resistors,  $\mathsf{R}_1$  and  $\mathsf{R}_2.$  In this case, the currents through the diodes,  $\mathsf{D}_1$  and  $\mathsf{D}_2,$  need to be limited by some other mechanism. The resistor then serves as an inrush current limiter; the DC current into the input pins ( $\mathsf{V}_{\mathsf{IN}}+$  and  $\mathsf{V}_{\mathsf{IN}}-$ ) should be very small.

A significant amount of current can flow out of the inputs when the Common-mode voltage ( $V_{CM}$ ) is below ground ( $V_{SS}$ ); see Figure 2-32. Applications that are high-impedance may need to limit the usable voltage range.

#### 4.1.3 PHASE REVERSAL

The MCP6561/1R/1U/2/4 comparator families use CMOS transistors at the input. They are designed to prevent phase inversion when the input pins exceed the supply voltages. Figure 2-3 shows an input voltage exceeding both supplies with no resulting phase inversion.

#### 4.2 Push-Pull Output

The push-pull output is designed to be compatible with CMOS and TTL logic, while the output transistors are configured to give rail-to-rail output performance. They are driven with circuitry that minimizes any switching current (shoot-through current from supply-to-supply) when the output is transitioned from high-to-low or from low-to-high (see Figure 2-15 and Figure 2-18 for more information).

#### 4.3 Externally Set Hysteresis

Greater flexibility in selecting hysteresis (or input trip points) is achieved by using external resistors. Hysteresis reduces output chattering when one input is slowly moving past the other. It also helps in systems where it is best not to cycle between high and low states too frequently (e.g., air conditioner thermostatic control). Output chatter also increases the dynamic supply current.

#### 4.3.1 NONINVERTING CIRCUIT

Figure 4-4 shows a noninverting circuit for singlesupply applications using just two resistors. The resulting hysteresis diagram is shown in Figure 4-5.





FIGURE 4-4: Noninverting Circuit with Hysteresis for Single Supply.



**FIGURE 4-5:** Hysteresis Diagram for the Noninverting Circuit.

The trip points for Figure 4-4 and Figure 4-5 are:

### **EQUATION 4-1:**

$$\begin{split} V_{TLH} &= V_{REF} \bigg( I + \frac{R_I}{R_F} \bigg) - V_{OL} \bigg( \frac{R_I}{R_F} \bigg) \\ V_{THL} &= V_{REF} \bigg( I + \frac{R_I}{R_F} \bigg) - V_{OH} \bigg( \frac{R_I}{R_F} \bigg) \end{split}$$

Where:

 $V_{TLH}$  = Trip Voltage from Low-to-High  $V_{THL}$  = Trip Voltage from High-to-Low

#### 4.3.2 INVERTING CIRCUIT

Figure 4-6 shows an inverting circuit for single supply using three resistors. The resulting hysteresis diagram is shown in Figure 4-7.




FIGURE 4-6: Inverting Circuit with Hysteresis.




FIGURE 4-7: Hysteresis Diagram for the Inverting Circuit.

In order to determine the trip voltages ( $V_{THL}$  and  $V_{TLH}$ ) for the circuit shown in Figure 4-6,  $R_2$  and  $R_3$  can be simplified to the Thevenin equivalent circuit with respect to  $V_{DD}$ , as shown in Figure 4-8.




FIGURE 4-8: Thevenin Equivalent Circuit.

Where:

$$R_{23} = \frac{R_2 R_3}{R_2 + R_3}$$

$$V_{23} = \frac{R_3}{R_2 + R_3} \times V_{DD}$$

Using this simplified circuit, the trip voltage can be calculated using the following equation:

#### **EQUATION 4-2:**

$$\begin{split} V_{THL} &= V_{OH} \!\! \left( \! \frac{R_{23}}{R_{23} + R_F} \! \right) + V_{23} \!\! \left( \! \frac{R_F}{R_{23} + R_F} \! \right) \\ V_{TLH} &= V_{OL} \!\! \left( \! \frac{R_{23}}{R_{23} + R_F} \! \right) + V_{23} \!\! \left( \! \frac{R_F}{R_{23} + R_F} \! \right) \end{split}$$

Where:

 $V_{TLH}$  = Trip Voltage from Low-to-High  $V_{THL}$  = Trip Voltage from High-to-Low

Figure 2-20, and Figure 2-23 can be used to determine typical values for  $V_{OH}$  and  $V_{OL}$ .

### 4.4 Bypass Capacitors

With this family of comparators, the power supply pin ( $V_{DD}$  for single supply) should have a local bypass capacitor (i.e., 0.01  $\mu F$  to 0.1  $\mu F$ ) within 2 mm for good edge rate performance.

#### 4.5 Capacitive Loads

Reasonable capacitive loads (e.g., logic gates) have little impact on propagation delay (see Figure 2-31). The supply current increases with increasing toggle frequency (Figure 2-19), especially with higher capacitive loads. The output slew rate and propagation delay performance will be reduced with higher capacitive loads.

#### 4.6 PCB Surface Leakage

In applications where low input bias current is critical, PCB (Printed Circuit Board) surface leakage effects need to be considered. Surface leakage is caused by humidity, dust or other contamination on the board. Under low humidity conditions, a typical resistance between nearby traces is  $10^{12}\Omega$ . A 5V difference would cause 5 pA of current to flow. This is greater than the MCP6561/1R/1U/2/4 families' bias current at +25°C (1 pA, typical).

The easiest way to reduce surface leakage is to use a guard ring around sensitive pins (or traces). The guard ring is biased at the same voltage as the sensitive pin. An example of this type of layout is shown in Figure 4-9.




FIGURE 4-9: Example Guard Ring Layout for Inverting Circuit.

- Inverting Configuration (Figures 4-6 and 4-9):
  - a) Connect the guard ring to the noninverting input pin (V<sub>IN</sub>+). This biases the guard ring to the same reference voltage as the comparator (e.g., V<sub>DD</sub>/2 or ground).
  - b) Connect the inverting pin (V<sub>IN</sub>-) to the input pad without touching the guard ring.
- Noninverting Configuration (Figure 4-4):
  - a) Connect the noninverting pin (V<sub>IN</sub>+) to the input pad without touching the guard ring.
  - b) Connect the guard ring to the inverting input pin (V<sub>IN</sub>-).

#### 4.7 PCB Layout Technique

When designing the PCB layout, it is critical to note that analog and digital signal traces are adequately separated to prevent signal coupling. If the comparator output trace is at close proximity to the input traces, then large output voltage changes from V<sub>SS</sub> to V<sub>DD</sub>, or visa versa, may couple to the inputs and cause the device output to oscillate. To prevent such oscillation, the output traces must be routed away from the input pins. The SC70 and SOT-23 are relatively immune because the output pin OUT (Pin 1) is separated by the power pin  $V_{DD}/V_{SS}$  (Pin 2) from the input pin +IN (as long as the analog and digital traces remain separated throughout the PCB). However, the pinouts for the dual and quad packages (SOIC, MSOP, TSSOP) have OUT and -IN pins (Pins 1 and 2) close to each other. The recommended layout for these packages is shown in Figure 4-10.




FIGURE 4-10: Recommended Layout.

#### 4.8 Unused Comparators

An unused amplifier in a quad package (MCP6564) should be configured as shown in Figure 4-11. This circuit prevents the output from toggling and causing crosstalk. It uses the minimum number of components and draws minimal current (see Figure 2-15 and Figure 2-18).




FIGURE 4-11: Unused Comparators.

### 4.9 Typical Applications

#### 4.9.1 PRECISE COMPARATOR

Some applications require higher DC precision. An easy way to solve this problem is to use an amplifier (such as the MCP6291) to gain-up the input signal before it reaches the comparator. Figure 4-12 shows an example of this approach.




FIGURE 4-12: Precise Inverting Comparator.

#### 4.9.2 WINDOWED COMPARATOR

Figure 4-13 shows one approach to designing a windowed comparator. The AND gate produces a logic '1' when the input voltage is between  $V_{RB}$  and  $V_{RT}$  (where  $V_{RT} > V_{RB}$ ).




FIGURE 4-13: Windowed Comparator.

#### 4.9.3 BISTABLE MULTIVIBRATOR

A simple bistable multivibrator design is shown in Figure 4-14.  $V_{REF}$  needs to be between the power supplies ( $V_{SS}$  = GND and  $V_{DD})$  to achieve oscillation. The output duty cycle changes with  $V_{REF}$ 




FIGURE 4-14: Bistable Multivibrator.

NOTES:

#### 5.0 DESIGN AIDS

# 5.1 Microchip Advanced Part Selector (MAPS)

MAPS is a software tool that helps semiconductor professionals efficiently identify Microchip devices that fit a particular design requirement. Available at no cost from the Microchip website at <a href="https://www.microchip.com/maps">www.microchip.com/maps</a>, the MAPS is an overall selection tool for Microchip's product portfolio that includes Analog, Memory, MCUs and DSCs. Using this tool you can define a filter to sort features for a parametric search of devices and export side-by-side technical comparison reports. Helpful links are also provided for data sheets, purchase and sampling of Microchip parts.

# 5.2 Analog Demonstration and Evaluation Boards

Microchip offers a broad spectrum of Analog Demonstration and Evaluation Boards that are designed to help you achieve faster time to market. For a complete listing of these boards and their corresponding user's guides and technical information, visit the Microchip website at <a href="https://www.microchip.com/analogtools">www.microchip.com/analogtools</a>. Three of our boards that are especially useful are:

- 8-Pin SOIC/MSOP/TSSOP/DIP Evaluation Board, P/N SOIC8EV
- 14-Pin SOIC/TSSOP/DIP Evaluation Board, P/N SOIC14EV
- 5/6-Pin SOT23 Evaluation Board, P/N VSUPEV2

#### 5.3 Application Notes

The following Microchip Application Note is available on the Microchip website at <a href="https://www.microchip.com">www.microchip.com</a> and is recommended as a supplemental reference resource:


 AN895, "Oscillator Circuits For RTD Temperature Sensors", DS00895


NOTES:

#### 6.0 PACKAGING INFORMATION

#### 6.1 **Package Marking Information**

5-Lead SC-70 (MCP6561)





5-Lead SOT-23 (MCP6561, MCP6561R, MCP6561U)



Device	Code			
MCP6561T	WBNN			
MCP6561RT	WANN			
MCP6561UT	WKNN			
Note: Applies to 5-Lead SOT-23				





8-Lead MSOP (MCP6562)





8-Lead SOIC (150 mil) (MCP6562)





Legend: XX...X Customer-specific information

Year code (last digit of calendar year) ΥY Year code (last 2 digits of calendar year) WW Week code (week of January 1 is week '01') NNN Alphanumeric traceability code


(e3) Pb-free JEDEC designator for Matte Tin (Sn)

This package is Pb-free. The Pb-free JEDEC designator (@3) can be found on the outer packaging for this package.


Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

## **Package Marking Information (Continued)**

14-Lead SOIC (150 mil) (MCP6564)



14-Lead TSSOP (MCP6564)



Example:





Example:



## 5-Lead Plastic Small Outline Transistor (LT) [SC70]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-061-LT Rev E Sheet 1 of 2

Note:

## 5-Lead Plastic Small Outline Transistor (LT) [SC70]

For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	Limits	MIN	NOM	MAX
Number of Pins	N		5	
Pitch	е		0.65 BSC	
Overall Height	Α	0.80 - 1.10		
Standoff	A1	0.00 - 0.1		
Molded Package Thickness	A2	0.80	1	1.00
Overall Length	D		2.00 BSC	
Overall Width	Е		2.10 BSC	
Molded Package Width	E1		1.25 BSC	
Terminal Width	b	0.15 - 0.40		
Terminal Length	Ĺ	0.10 0.20 0.46		
Lead Thickness	С	0.08	-	0.26

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.
  3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-061-LT Rev E Sheet 2 of 2

## 5-Lead Plastic Small Outline Transistor (LT) [SC70]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



### RECOMMENDED LAND PATTERN

	Units	MILLIMETERS		
Dimension	Dimension Limits		NOM	MAX
Contact Pitch	Е	0.65 BSC		
Contact Pad Spacing	С		2.20	
Contact Pad Width	Х			0.45
Contact Pad Length	Υ			0.95
Distance Between Pads	G	1.25		
Distance Between Pads	Gx	0.20		·


#### Notes:


Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2061-LT Rev E

# 5-Lead Plastic Small Outline Transistor (OT) [SOT23]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-091-OT Rev F Sheet 1 of 2

### 5-Lead Plastic Small Outline Transistor (OT) [SOT23]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS				
Dimension	Limits	MIN	NOM	MAX	
Number of Pins	N		5		
Pitch	е		0.95 BSC		
Outside lead pitch	e1		1.90 BSC		
Overall Height	Α	0.90	-	1.45	
Molded Package Thickness	A2	0.89	-	1.30	
Standoff	A1	ı	-	0.15	
Overall Width	E	2.80 BSC			
Molded Package Width	E1		1.60 BSC		
Overall Length	D		2.90 BSC		
Foot Length	L	0.30	-	0.60	
Footprint	L1	0.60 REF			
Foot Angle	ф	0°	-	10°	
Lead Thickness	С	0.08	-	0.26	
Lead Width	b	0.20	-	0.51	

#### Notes:

- Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side.
- 2. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-091-OT Rev F Sheet 2 of 2

# 5-Lead Plastic Small Outline Transistor (OT) [SOT23]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е			
Contact Pad Spacing	С		2.80	
Contact Pad Width (X5)	Х			0.60
Contact Pad Length (X5)	Υ			1.10
Distance Between Pads	G	1.70		
Distance Between Pads	GX	0.35		
Overall Width	Z			3.90

#### Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2091-OT Rev F

### 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-111C Sheet 1 of 2

### 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]

For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS				
Dimension	Limits	MIN	NOM	MAX	
Number of Pins	N		8		
Pitch	е		0.65 BSC		
Overall Height	Α	ı	-	1.10	
Molded Package Thickness	A2	0.75	0.85	0.95	
Standoff	A1	0.00	-	0.15	
Overall Width	E	4.90 BSC			
Molded Package Width	E1	3.00 BSC			
Overall Length	D		3.00 BSC		
Foot Length	L	0.40	0.60	0.80	
Footprint	L1	0.95 REF			
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.08	-	0.23	
Lead Width	b	0.22	-	0.40	

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.
  3. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-111C Sheet 2 of 2

### 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е	0.65 BSC		
Contact Pad Spacing	С		4.40	
Overall Width	Z			5.85
Contact Pad Width (X8)	X1			0.45
Contact Pad Length (X8)	Y1			1.45
Distance Between Pads	G1	2.95		
Distance Between Pads	GX	0.20		

#### Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2111A

# 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm (.150 ln.) Body [SOIC]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing No. C04-057-SN Rev E Sheet 1 of 2

# 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm (.150 ln.) Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension	Dimension Limits		NOM	MAX	
Number of Pins	N		8		
Pitch	е		1.27 BSC		
Overall Height	Α	-	-	1.75	
Molded Package Thickness	A2	1.25	-	1	
Standoff §	A1	0.10	-	0.25	
Overall Width	Е	6.00 BSC			
Molded Package Width	E1	3.90 BSC			
Overall Length	D	4.90 BSC			
Chamfer (Optional)	h	0.25 - 0.50		0.50	
Foot Length	L	0.40	-	1.27	
Footprint	L1	1.04 REF			
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.17	-	0.25	
Lead Width	b	0.31	-	0.51	
Mold Draft Angle Top	α	5°	-	15°	
Mold Draft Angle Bottom	β	5°	-	15°	

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- 3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.


5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-057-SN Rev E Sheet 2 of 2  $\,$ 

Note:

# 8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm Body [SOIC]

For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



## RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е		1.27 BSC	
Contact Pad Spacing	С		5.40	
Contact Pad Width (X8)	X1			0.60
Contact Pad Length (X8)	Y1			1.55

### Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2057-SN Rev E

# 14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing No. C04-065-SL Rev D Sheet 1 of 2

## 14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Pins	N		14	
Pitch	е		1.27 BSC	
Overall Height	Α	-	-	1.75
Molded Package Thickness	A2	1.25	-	1
Standoff §	A1	0.10	-	0.25
Overall Width	Е	6.00 BSC		
Molded Package Width	E1	3.90 BSC		
Overall Length	D	8.65 BSC		
Chamfer (Optional)	h	0.25 - 0.50		0.50
Foot Length	L	0.40 - 1.27		1.27
Footprint	L1	1.04 REF		
Lead Angle	Θ	0°	-	1
Foot Angle	$\varphi$	0°	-	8°
Lead Thickness	С	0.10 - 0.25		0.25
Lead Width	b	0.31	-	0.51
Mold Draft Angle Top	α	5°	-	15°
Mold Draft Angle Bottom	β	5°	-	15°

### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- 3. Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-065-SL Rev D Sheet 2 of 2  $\,$ 

# 14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



## RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е		1.27 BSC	
Contact Pad Spacing	С		5.40	
Contact Pad Width (X14)	Х			0.60
Contact Pad Length (X14)	Υ			1.55

#### Notes


1. Dimensioning and tolerancing per ASME Y14.5M  $\,$ 

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2065-SL Rev D

# 14Lead Thin Shrink Small Outline Package [ST] 4.4 mm Body [TSSOP]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-087 Rev D Sheet 1 of 2

# 14Lead Thin Shrink Small Outline Package [ST] 4.4 mm Body [TSSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Un	its	N	IILLIMETER	S
	Dimension Lim	its	MIN	NOM	MAX
Number of Terminals	N			14	
Pitch	е	:		0.65 BSC	
Overall Height	А	\	_	_	1.20
Standoff	A.	1	0.05	-	0.15
Molded Package Thickness	A:	2	0.80	1.00	1.05
Overall Length	D	)	4.90	5.00	5.10
Overall Width E			6.40 BSC		
Molded Package Width	E.	1	4.30	4.40	4.50
Terminal Width	b	)	0.19	-	0.30
Terminal Thickness	С	;	0.09		0.20
Terminal Length	L	.	0.45	0.60	0.75
Footprint L1		1	1.00 REF		
Lead Bend Radius	R	1	0.09		ı
Lead Bend Radius	R	2	0.09	_	_
Foot Angle	θ	1	0°	_	8°
Mold Draft Angle	θ2	2	_	12° REF	
Mold Draft Angle	θ	3	_	12° REF	_

### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-087 Rev D Sheet 2 of 2

# 14Lead Thin Shrink Small Outline Package [ST] 4.4 mm Body [TSSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



## RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	Е		0.65 BSC	
Contact Pad Spacing	С		5.90	
Contact Pad Width (Xnn)	Х			0.45
Contact Pad Length (Xnn)	Υ			1.45
Contact Pad to Contact Pad (Xnn)	G	0.20		

#### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2087 Rev D

## APPENDIX A: REVISION HISTORY

## Revision E (March 2020)

The following is the list of modifications:

 Updated package drawings for the 5-lead SC-70 and 14-lead TSSOP packages in Section 6.0 "Packaging Information".

## **Revision D (October 2019)**

The following is the list of modifications:

 Updated Section 6.0 "Packaging Information".

## Revision C (February 2013)

The following is the list of modifications:

- 1. Added the Analog Input (V<sub>IN</sub>) parameter in Section 1.0 "Electrical Characteristics".
- 2. Updated the package drawing section.

## **Revision B (August 2009)**

The following is the list of modifications:

- 1. Added MCP6561U throughout the document.
- 2. Updated package drawing section.

## Revision A (March 2009)

· Original Release of this Document.

# MCP6561/1R/1U/2/4

NOTES:

# PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. – X	/ <u>/xx</u>	Examples:
Device Tempe Ran	<u> </u>	a) MCP6561T-E/LT: Tape and Reel, Extended Temperature, 5-Lead SC70 Package.
Device:	MCP6561T: Single Comparator (Tape and Reel) (SC70, SOT-23)	b) MCP6561T-E/OT: Tape and Reel, Extended Temperature, 5-Lead SOT-23 Package.
	MCP6561RT: Single Comparator (Tape and Reel) (SOT-23 only)  MCP6561UT: Single Comparator (Tape and Reel) (SOT-23 only)  MCP6562: Dual Comparator	a) MCP6561RT-E/OT: Tape and Reel, Extended Temperature, 5-Lead SOT-23 Package.
	MCP6562T: Dual Comparator (Tape and Reel) MCP6564: Quad Comparator MCP6564T: Quad Comparator (Tape and Reel)	a) MCP6561UT-E/OT: Tape and Reel, Extended Temperature, 5-Lead SOT-23 Package.
Temperature Range:	E = -40°C to +125°C	a) MCP6562-E/MS: Extended Temperature, 8-Lead MSOP Package.
Package:	LT = Plastic Small Outline Transistor (SC70), 5-Lead OT = Plastic Small Outline Transistor (SOT-23), 5-Lead	b) MCP6562-E/SN: Extended Temperature, 8-Lead SOIC Package.
	MS = Plastic Micro Small Outline Transistor (MSOP), 8-Lead SN = Plastic Small Outline Transistor (SOIC), 8-Lead ST = Plastic Thin Shrink Small Outline Transistor (TSSOP),	a) MCP6564T-E/SL: Tape and Reel, Extended Temperature, 14-Lead SOIC Package.
	14-Lead SL = Plastic Small Outline Transistor (SOIC), 14-Lead	b) MCP6564T-E/ST: Tape and Reel, Extended Temperature, 14-Lead TSSOP Package.

# MCP6561/1R/1U/2/4

NOTES:

#### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our
  knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data
  Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, Anyln, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MulttrRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2009-2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-5713-8

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



# **Worldwide Sales and Service**

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address:

www.microchip.com

**Atlanta** Duluth, GA

Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983 Indianapolis

Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

**China - Shanghai** Tel: 86-21-3326-8000

**China - Shenyang** Tel: 86-24-2334-2829

**China - Shenzhen** Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan

Tel: 86-27-5980-5300 China - Xian

Tel: 86-29-8833-7252 **China - Xiamen** Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

**Germany - Garching** Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

Germany - Karlsruhe Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Microchip:

<u>MCP6562-E/MS</u> <u>MCP6562-E/SN</u> <u>MCP6562T-E/MS</u> <u>MCP6562T-E/SN</u> <u>MCP6564-E/SL</u> <u>MCP6564-E/SL</u> <u>MCP6564-E/ST</u> <u>MCP6564T-E/ST</u> <u>MCP6561UT-E/OT</u> <u>MCP6561RT-E/OT</u> <u>MCP6561T-E/LT</u> <u>MCP6561T-E/OT</u> <u>MCP6562-E/MC</u> MCP6564A-E/ML MCP6562A-E/MF MCP6562A-E/UN