COMPLIANT

HALOGEN FREE



Vishay General Semiconductor

High Current Density Surface Mount Schottky Barrier Rectifiers



DESIGN SUPPORT TOOLS

click logo to get started



PRIMARY CHARACTERISTICS				
I _{F(AV)}	12 A			
V _{RRM}	20 V, 30 V			
I _{FSM}	280 A			
E _{AS}	20 mJ			
V _F at I _F = 12 A	0.38 V			
T _J max.	150 °C			
Package	SMPC (TO-277A)			
Circuit configuration	Single			

FEATURES

- Very low profile typical height of 1.1 mm
- · Ideal for automated placement
- · Guardring for overvoltage protection
- · Low forward voltage drop, low power losses
- · High efficiency
- · Low thermal resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

MECHANICAL DATA

Case: SMPC (TO-277A)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3_X - halogen-free, RoHS-compliant and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,....)

Terminals: matte tin plated leads, solderable J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SS12P2L	SS12P3L	UNIT	
Device marking code		S122	S123		
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	V	
Maximum average forward rectified current (fig. 1)	I _{F(AV)}	12		Α	
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I _{FSM}	280		А	
Non-repetitive avalanche energy at $I_{AS} = 2.0 \text{ A}$, $T_{J} = 25 ^{\circ}\text{C}$	E _{AS}	20		mJ	
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150		°C	



www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT	
Maximum instantaneous forward voltage	I _F = 6 A	T _A = 25 °C	V _F ⁽¹⁾	0.41	-	V	
	I _F = 12 A			0.48	0.56		
	I _F = 6 A	T _A = 125 °C		0.30	-		
	I _F = 12 A			0.38	0.46		
Maximum reverse current	Rated V _R	T _A = 25 °C	I _R ⁽²⁾	150	1000	μΑ	
	nateu v _R	T _A = 125 °C		59	120	mA	
Typical junction capacitance	4.0 V, 1 MHz		CJ	930	1	pF	

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width \leq 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	SS12P2L SS12P3L		UNIT		
Typical thermal resistance	R ₀ JA ⁽¹⁾	60		°C/W		
Typical thermal resistance	$R_{ hetaJL}$	3		O/ VV		

Note

(1) Units mounted on recommended PCB 1 oz. pad layout

ORDERING INFORMATION (Example)							
PREFERRED P/N	UNIT WEIGHT (g)	PACKAGE CODE	BASE QUANTITY	DELIVERY MODE			
SS12P3L-M3/86A	0.10	86A	1500	7" diameter plastic tape and reel			
SS12P3L-M3/87A	0.10	87A	6500	13" diameter plastic tape and reel			
SS12P3LHM3_A/H ⁽¹⁾	0.10	Н	1500	7" diameter plastic tape and reel			
SS12P3LHM3_A/I (1)	0.10	I	6500	13" diameter plastic tape and reel			

Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance



Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

<u>SS12P3LHM3/86A</u> <u>SS12P2L-M3/86A</u> <u>SS12P2L-M3/87A</u> <u>SS12P2LHM3/86A</u> <u>SS12P2LHM3/87A</u> <u>SS12P3LHM3/87A</u> <u>SS12P3LHM3/87A</u> <u>SS12P3LHM3_A/I</u> <u>SS12P3LHM3_A/I</u>