




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/18/06	
A		REDRAWN	10/17/11	



Positions: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24
 A = .165 [4.20] X No. of Spaces per row
 B = .165 [4.20] X No. of Positions per row+ .055 [1.40]

WIRE SIZE	CIRCUITS			
AWG	2	4~6	8~10	12~24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A

SPECIFICATIONS:
 Material:
 Insulator: Nylon 66, rated UL 94V-2
 Insulator color: Natural
 Electrical:
 Operating voltage: 600 VAC max
 Current rating: / Circuit (See Chart)
 Insulation resistance: 1000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1500 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES: .10 ±.10 ØXX ±.015
 .XX ±.020 ØXXX ±.015
 .XXX ±.015

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710
WIRE TO WIRE CONNECTOR HOUSING
 FEMALE, 4.2MM PITCH

DRAWN	SS	8/18/06	SIZE	PART NO.	REV.
CHECKED			X	DMH-XX	A
APPROVED			REF:	S00123T	
			SCALE:	NIS	SHEET 1 OF 1