



DATA SHEET

SK32 thru S310

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

VOLTAGE 20 to 100 Volts **CURRENT** 3.0 Amperes

SMC/DO-214AB


Unit: inch (mm)

FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- Low profile package
- Built-in strain relief
- Metal to silicon rectifier. majority carrier conduction
- Low power loss,high efficiency
- High surge capacity
- For use in low voltage high frequency inverters, free wheeling, and polarity protection applications
- Pb free product are available : Pb free 99% Sn abovecan meet Rohs environment substance directive request

MECHANICAL DATA

Case: JEDEC DO-214AB molded plastic
 Terminals:Solder plated, solderable per MIL-STD-202G, Method 208
 Polarity: Color band denotes positive end (cathode)
 Standard packaging: 16mm tape (EIA-481)
 Weight: 0.007 ounce, 210mg



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
 Resistive or inductive load.

PARAMETER	SYMBOL	SK32	SK33	SK34	SK35	SK36	SK38	SK39	S310	UNITS
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	80	90	100	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	56	64	70	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	80	90	100	V
Maximum Average Forward Current .375"(9.5mm) lead length at TL=75°C	I _{AV}	3.0								A
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load(JEDEC method)	I _{FSM}	100								A
Maximum Forward Voltage at 3.0A (Note 1)	V _F	0.50			0.75		0.85			V
Maximum DC Reverse Current TA=25°C at Rated DC Blocking Voltage TA=100°C	I _R					0.5 20				mA
Maximum Thermal Resistance (Note 2)	R _{θJL} R _{θJA}					20 75				°C / W
Operating Junction Temperature Range	T _J					-55 to +125				°C
Storage Temperature Range	T _{STG}					-55 to +150				°C

NOTES:

1. Pulse Test with PW =300µsec, 1% Duty Cycle.
2. Mounted on P.C. Board with 8.0mm² (.013mm thick) copper pad areas.



RATING AND CHARACTERISTIC CURVES




Fig.1- FORWARD CURRENT DERATING CURVE




Fig.2- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- MAXIMUM NON - REPETITIVE SURGE CURRENT