

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)

32_MMBX-SMA-50-1/119_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
MMBX	plug (male)	HUBER+SUHNER-MMBX
SMA	plug (male)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	SUCOPRO Plating
Body	Copper Beryllium Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body		SUCOPRO Plating
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	12.4 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 2.5 GHz	32 dB	1.05
2.5 GHz ... 6 GHz	30 dB	1.06

COAXIAL ADAPTER, MMBX, 50 Ohm, plug / plug (male / male)

32_MMBX-SMA-50-1/119_N

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
6 GHz ... 12.4 GHz	16 dB	1.35

Mechanical data	
Weight	0.003 kg
Mating cycles	500

Environmental data	
Operation temperature	-55 °C ... 155°C

Ordering Information Table		
Item number	Item description	Packaging type
23004934	32_MMBX-SMA-50-1/119_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2312 / Date of publication: 26.11.2023 / uncontrolled copy