

PIC16(L)F18326/18346

Full-Featured, 14/20 Low Pin Count Microcontrollers with XLP

Description

PIC16(L)F18326/18346 microcontrollers feature analog, core independent peripherals and communication peripherals, combined with eXtreme Low Power (XLP) for a wide range of general purpose and low-power applications. The Peripheral Pin Select (PPS) functionality enables pin mapping when using the digital peripherals (CLC, CWG, CCP, PWM and communications) to add flexibility to the application design.

Core Features

- C Compiler Optimized RISC Architecture
- Operating Speed:
- DC 32 MHz clock input
- 125 ns minimum instruction cycle
- Interrupt Capability
- 16-Level Deep Hardware Stack
- Up to Four 8-bit Timers
- Up to Three 16-bit Timers
- Low-Current Power-on Reset (POR)
- Power-up Timer (PWRTE)
- Brown-out Reset (BOR) Option
- Low-Power BOR (LPBOR) Option
- Extended Watchdog Timer (WDT) with Dedicated On-Chip Oscillator for Reliable Operation
- Programmable Code Protection

Memory

- · 28 Kbytes Program Flash Memory
- 2 KB Data SRAM Memory
- 256B of EEPROM
- · Direct, Indirect, and Relative Addressing Modes

Operating Characteristics

- Operating Voltage Range:
 - 1.8V to 3.6V (PIC16LF18326/18346)
 - 2.3V to 5.5V (PIC16F18326/18346)
- Temperature Range:
 - Industrial: -40°C to 85°C
 - Extended: -40°C to 125°C

eXtreme Low-Power (XLP) Features

- Sleep Mode: 40 nA @ 1.8V, typical
- Watchdog Timer: 250 nA @ 1.8V, typical
- Secondary Oscillator: 300 nA @ 32 kHz
- Operating Current:
 - 8 μA @ 32 kHz, 1.8V, typical
 - 37 μA/MHz @ 1.8V, typical

Power-Saving Functionality

- Idle Mode: Ability to Put the CPU Core to Sleep While Internal Peripherals Continue Operating from the System Clock
- Doze Mode: Ability to Run the CPU Core Slower Than the System Clock Used by the Internal Peripherals
- · Sleep Mode: Lowest Power Consumption
- Peripheral Module Disable (PMD): Peripheral Power Disable Hardware Module to Minimize Power Consumption of Unused Peripherals

Digital Peripherals

- Configurable Logic Cell (CLC):
 - Four CLCs
 - Integrated combinational and sequential logic
- Complementary Waveform Generator (CWG):
 - Two CWGs
 - Rising and falling edge dead-band control
 - Full-bridge, half-bridge, 1-channel drive
 - Multiple signal sources
- Capture/Compare/PWM (CCP) Modules:
 - Four CCPs
 - 16-bit resolution for Capture/Compare modes
 10-bit resolution for PWM mode
- Pulse-Width Modulators (PWM):
 - Two 10-bit PWMs
- Numerically Controlled Oscillator (NCO):
 - Precision linear frequency generator (@50% duty cycle) with 0.0001% step size of source input clock
 - Input Clock: 0 Hz < F_{NCO} < 32 MHz
 - Resolution: F_{NCO}/2²⁰
- Serial Communications:
- EUSART
 - RS-232, RS-485, LIN compatible
 - Auto-Baud Detect, auto-wake-up on start
- Host Synchronous Serial Port (MSSP)
 - SPI
 - I²C, SMBus, PMBus™ compatible
- Data Signal Modulator (DSM):
 - Modulates a carrier signal with digital data to create custom carrier synchronized output waveforms

- Up to 18 I/O Pins:
 - Individually programmable pull-ups
 - Slew rate control
 - Interrupt-on-change with edge-select
 - Input level selection control (ST or TTL)
 - Digital open-drain enable
- Peripheral Pin Select (PPS):
 - I/O pin remapping of digital peripherals
- Timer Modules:
 - Timer0:
 - 8/16-bit timer/counter
 - Synchronous or asynchronous operation
 - Programmable prescaler/postscaler
 - Time base for capture/compare function
 - Timer1/3/5 with gate control:
 - 16-bit timer/counter
 - Programmable internal or external clock sources
 - Multiple gate sources
 - Multiple gate modes
 - Time base for capture/compare function
 - Timer2/4/6:
 - 8-bit timers
 - Programmable prescaler/postscaler
 - Time base for PWM function

Analog Peripherals

- 10-Bit Analog-to-Digital Converter (ADC):
 - 17 external channels
 - Conversion available during Sleep
- Comparator:
 - Two comparators
 - Fixed Voltage Reference at non-inverting input(s)
 - Comparator outputs externally accessible
- 5-Bit Digital-to-Analog Converter (DAC):
 - 5-bit resolution, rail-to-rail
 - Positive Reference Selection
 - Unbuffered I/O pin output
 - Internal connections to ADCs and comparators
- Voltage Reference:
 - Fixed Voltage Reference with 1.024V, 2.048V and 4.096V output levels Flexible Oscillator Structure
- High-Precision Internal Oscillator:
 - Software-selectable frequency range up to 32 MHz
 - ±1% at nominal 4 MHz calibration point
- 4x PLL with External Sources
- Low-Power Internal 31 kHz Oscillator (LFINTOSC)
- External Low-Power 32 kHz Crystal Oscillator (SOSC)
- External Oscillator Block with:
 - Three Crystal/Resonator modes up to 20 MHz
 - Three External Clock modes up to 20 MHz
 - Fail-Safe Clock Monitor
 - Detects clock source failure
 - Oscillator Start-up Timer (OST)
 - Ensures stability of crystal oscillator sources

Device	Data Sheet Index	Program Memory (KB)	Program Memory (KW)	EEPROM (B)	RAM (B)	I/OS ⁽¹⁾	10-bit ADCs	Comparators	5-bit DAC	Timers 0/1/2	CCP/PWM	CWG	EUSART	IdS	I ² C	CLC	NCO	Sdd	ICD ⁽²⁾
PIC16(L)F18313	(A)	3.5	2	256	256	6	5	1	1	1/1/1	2/2	1	1	1	1	2	1	Y	Ι
PIC16(L)F18323	(A)	3.5	2	256	256	12	11	2	1	1/1/1	2/2	1	1	1	1	2	1	Y	Ι
PIC16(L)F18324	(B)	7	4	256	512	12	11	2	1	1/3/3	4/2	2	1	1	1	4	1	Y	1
PIC16(L)F18325	(C)	14	8	256	1K	12	11	2	1	1/3/3	4/2	2	1	2	2	4	1	Y	Ι
PIC16(L)F18326	(D)	28	16	256	2K	12	11	2	1	1/3/3	4/2	2	1	2	2	4	1	Y	1
PIC16(L)F18344	(B)	7	4	256	512	18	17	2	1	1/3/3	4/2	2	1	1	1	4	1	Y	Ι
PIC16(L)F18345	(C)	14	8	256	1K	18	17	2	1	1/3/3	4/2	2	1	2	2	4	1	Y	1
PIC16(L)F18346	(D)	28	16	256	2K	18	17	2	1	1/3/3	4/2	2	1	2	2	4	1	Y	

Data Sheet Index: (Unshaded devices are described in this document.)

B:	DS40001800	PIC16(L)F18324/18344 Data Sheet,Full-Featured, Low Pin Count Microcontrollers with XLP
----	------------	--

C:	DS40001795	PIC16(L)F18325/18345 Data Sheet,Full-Featured, Low Pin Count Microcontrollers with XLP
----	------------	--

D: DS40001839 PIC16(L)F18326/18346 Data Sheet,Full-Featured, Low Pin Count Microcontrollers with XLP

Note: For other small form-factor package availability and marking information, visit http://www.microchip.com/packaging or contact the local sales office.

Pin Diagrams




FIGURE 2: 16-PIN UQFN/QFN/VQFN (4x4)






FIGURE 3: 20-PIN PDIP, SOIC, SSOP





Pin Allocation Tables

z

6

TABLE 2:

DS40001839F-page 6

I/O ⁽²⁾	14-Pin PDIP/SOIC/TSSOI	16-Pin UQFN/QFN/VQFN	ADC	Reference	Comparator	NCO	DAC	MSD	Timers	ССР	MWG	CWG	dssm	EUSART	CLC	CLKR	Interrupt	Pull-up	Basic
RA0	13	12	ANA0	_	C1IN0+	_	DAC1OUT	_	_	_	_	_	SS2 ⁽¹⁾		_	_	IOC	Y	ICDDAT/ ICSPDAT
RA1	12	11	ANA1	VREF+	C1IN0- C2IN0-	_	DAC1REF+	_	_	_	_	_	_		_	_	IOC	Y	ICDCLK/ ICSPCLK
RA2	11	10	ANA2	VREF-	_	-	DAC1REF-	_	тоскі ⁽¹⁾	CCP3 ⁽¹⁾	_	CWG1IN ⁽¹⁾ CWG2IN ⁽¹⁾	-		_		INT ⁽¹⁾ IOC	Y	_
RA3	4	3	_	_	_	_	_	_	_	_	_	_	_		_	_	IOC	Y	MCLR VPP
RA4	3	2	ANA4	_	_		_	_	T1G ⁽¹⁾ SOSCO	_	_	_			_	_	IOC	Y	CLKOUT OSC2
RA5	2	1	ANA5	_	_	_	_	_	T1CKI ⁽¹⁾ SOSCIN SOSCI		_	_	_	-	CLCIN3 ⁽¹⁾	_	IOC	Y	CLKIN OSC1
RC0	10	9	ANC0	_	C2IN0+		_	_	T5CKI ⁽¹⁾	_		_	SCK1 ⁽¹⁾ SCL1 ^(1,3,4)	l	_		IOC	Y	_
RC1	9	8	ANC1	_	C1IN1- C2IN1-		_	_	_	CCP4 ⁽¹⁾		_	SDI1 ⁽¹⁾ SDA1 ^(1,3,4)	l	CLCIN2 ⁽¹⁾	_	IOC	Y	_
RC2	8	7	ANC2	_	C1IN2- C2IN2-		_	MDCIN1 ⁽¹⁾	_	_		_			_	_	IOC	Y	_
RC3	7	6	ANC3	_	C1IN3- C2IN3-		_	MDMIN ⁽¹⁾	T5G ⁽¹⁾	CCP2 ⁽¹⁾		_	SS1 ⁽¹⁾		CLCIN0 ⁽¹⁾	_	IOC	Y	_
RC4	6	5	ANC4	_	_		_	_	T3G ⁽¹⁾	_		_	SCK2 ⁽¹⁾ SCL2 ^(1,3,4)	I	CLCIN1 ⁽¹⁾	_	IOC	Y	—
RC5	5	4	ANC5	_	—		-	MDCIN2 ⁽¹⁾	Т3СКІ ⁽¹⁾	CCP1 ⁽¹⁾	—	-	SDI2 ⁽¹⁾ SDA2 ^(1,3,4)	RX ⁽¹⁾	—	_	IOC	Y	—
VDD	1	16	_	_	_	-	_	—	_	_	_	_	_		_	_	_	_	Vdd

1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers.

14/16-PIN ALLOCATION TABLE (PIC16(L)F18326)

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers.

3: These peripheral functions are bidirectional. The output pin selections must be the same as the input pin selections.

4: These pins are configured for I²C logic levels; clock and data signals may be assigned to any of these pins. Assignments to the other pins (e.g., RA5) will operate, but logic levels will be standard TTL/ ST as selected by the INLVL register.

Note

TABLE 2: 14/16-PIN ALLOCATION TABLE (PIC16(L)F18326) (CONTINUED)

IADLI					-00411						-,								
I/O ⁽²⁾	14-Pin PDIP/SOIC/TSSOP	16-Pin UQFN/QFN/VQFN	ADC	Reference	Comparator	NCO	DAC	WSQ	Timers	ССР	WMd	CWG	ASSM	EUSART	OLC	CLKR	Interrupt	Pull-up	Basic
Vss	14	13	_		_		_		—	—		_			—	—	-	_	Vss
		_	_	_	C10UT	NCO1		DSM	TMR0	CCP1	PWM5	CWG1A CWG2A	SDA1 ⁽³⁾ SDA2 ⁽³⁾	СК	CLC10UT	CLKR		Ι	—
OUT ⁽²⁾	_	_	_	l	C2OUT		_		_	CCP2	PWM6	CWG1B CWG2B	SCL1 ⁽³⁾ SCL2 ⁽³⁾	DT	CLC2OUT	_	_	_	_
001-	-	_	_	_	_	_	_		_	CCP3		CWG1C CWG2C	SDO1 SDO2	ТΧ	CLC3OUT	_	_	_	_
	_	_	_	_	_	_	_	_	_	CCP4	-	CWG1D CWG2D	SCK1 SCK2	-	CLC4OUT	_	-	_	_

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers.

3: These peripheral functions are bidirectional. The output pin selections must be the same as the input pin selections.

4: These pins are configured for I²C logic levels; clock and data signals may be assigned to any of these pins. Assignments to the other pins (e.g., RA5) will operate, but logic levels will be standard TTL/ ST as selected by the INLVL register.

1/O ⁽²⁾	20-Pin PDIP/SOIC/SSOI	20-Pin UQFN/QFN/VQFI	ADC	Reference	Comparator	NCO	DAC	MSD	Timers	ССР	MWd	CWG	ASSM	EUSART	CLC	CLKR	Interrupt	Pull-up	Basic
RA0	19	16	ANA0	I	C1IN0+	—	DAC1OUT	—	-	—	—	—	—	_	—		IOC	Y	ICDDAT ICSPDAT
RA1	18	15	ANA1	VREF+	C1IN0- C2IN0-	_	DAC1REF+	_	_	_	_	_	SS2	_	—	_	IOC	Y	ICDCLK ICSPCLK
RA2	17	14	ANA2	VREF-	_	_	DAC1REF-	_	T0CKI ⁽¹⁾	CCP3 ⁽¹⁾	_	CWG1IN ⁽¹⁾ CWG2IN ⁽¹⁾	—	_	CLCIN0 ⁽¹⁾	_	IOC INT ⁽¹⁾	Y	_
RA3	4	1	_	_	_	_	_	_	_	_	_	_	—	_	_	_	IOC	Y	MCLR VPP
RA4	3	20	ANA4	_	_	_	_	_	T1G ⁽¹⁾ T3G ⁽¹⁾ T5G ⁽¹⁾ SOSCO	CCP4 ⁽¹⁾	_	_	_	_	_	_	IOC	Y	CLKOUT OSC2
RA5	2	19	ANA5	_	_	_	_	_	T1CKI ⁽¹⁾ T3CKI ⁽¹⁾ T5CKI ⁽¹⁾ SOSCIN SOSCI	_	_	_	_	_	_	_	IOC	Y	CLKIN OSC1
RB4	13	10	ANB4		_	_	—	_	_	_	_	_	SDI1 ⁽¹⁾ SDA1 ^(1,3,4)		CLCIN2 ⁽¹⁾		IOC	Y	_
RB5	12	9	ANB5	_	_	_	_	_	_	_	_	_	SDI2 ⁽¹⁾ SDA2 ^(1,3,4)	RX ⁽¹⁾	CLCIN3 ⁽¹⁾	_	IOC	Y	_
RB6	11	8	ANB6	_	_	_	_	_	_	_	_	_	SCK1 ⁽¹⁾ SCL1 ^(1,3,4)	_	_	_	IOC	Y	_
RB7	10	7	ANB7		_	_	—	_	_	_	_	_	SCK2 ⁽¹⁾ SCL2 ^(1,3,4)		—		IOC	Y	_
RC0	16	13	ANC0		C2IN0+		_							_			IOC	Y	
RC1	15	12	ANC1		C1IN1- C2IN1-	—		—	_	—	—	—	—	_	—		IOC	Y	—
RC2	14	11	ANC2	-	C1IN2- C2IN2-	_	_	MDCIN1 ⁽¹⁾		_	_	_	_		_		IOC	Υ	_

TABLE 3: 20-PIN ALLOCATION TABLE (PIC16(L)F18346)

N

6

All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. 2:

3: These peripheral functions are bidirectional. The output pin selections must be the same as the input pin selections.

4: These pins are configured for I²C logic levels; clock and data signals may be assigned to any of these pins. Assignments to other pins (e.g., RA5) will operate, but logic levels will be standard TTL/ST as selected by the INLVL register.

5.	-		-			- ((-)			,									
20-Pin PDIP/SOIC/SSOP	20-Pin UQFN/QFN/VQFN	ADC	Reference	Comparator	NCO	DAC	WSQ	Timers	ССР	PWM	CWG	MSSP	EUSART	CLC	CLKR	Interrupt	Pull-up	Basic
7	4	ANC3	I	C1IN3- C2IN3-	—	_	MDMIN ⁽¹⁾	—	CCP2 ⁽¹⁾	_	_	—	—	CLCIN1 ⁽¹⁾	—	IOC	Y	_
6	3	ANC4	_	_	—	_	_	_	_	_	_	—	_	_	_	IOC	Y	_
5	2	ANC5	_	_	_	_	MDCIN2 ⁽¹⁾	_	CCP1 ⁽¹⁾	_	_	—	_	_	_	IOC	Y	_
8	5	ANC6	_	_		_	_	_	_	_		SS1 ⁽¹⁾	_	_	—	IOC	Y	_
9	6	ANC7	-	—	—	—	—	_	_	_	_	—	_	—	—	IOC	Y	_
1	18	—	_	—	_	_	_	_	—	—	_	—	—	—	—	—	—	Vdd
20	17	—		_	_	—	_	_	—	_		—	—	_	—	-	-	Vss
—	—	_		C1OUT	NCO1	—	DSM	TMR0	CCP1	PWM5	CWG1A CWG2A	SDO1 SDO2	DT	CLC1OUT	CLKR	_	_	—
	_	_	I	C2OUT	—	—	_	—	CCP2	PWM6	CWG1B CWG2B	SCK1 SCK2	СК	CLC2OUT	—		_	—
—	_	_	I	—	—	_	_	—	CCP3	_	CWG1C CWG2C	SCL1 ⁽³⁾ SCL2 ⁽³⁾	ТΧ	CLC3OUT	—	_	_	—
	Ι		-	—	—	_	—	—	CCP4	Ι	CWG1D CWG2D	SDA1 ⁽³⁾ SDA2 ⁽³⁾	_	CLC4OUT	_	Ι	_	—
	r r r r r r r r	Solution Solution 30-5 30-5 30 30-5 <t< td=""><td>Ng Ng Ng OSS/OIG 0 0 0 0 0 7 4 ANC3 6 3 ANC4 5 2 ANC5 8 5 ANC6 9 6 ANC7 1 18 20 17 </td><td>AG NL AG Set set</td><td>Add Na Add Second Second</td><td>AG NL AG Setter and and and and and and and and and and</td><td>OS NUC OC SUC SUC</td><td>OS NAŬ SO SO</td><td>OS NH DAIN DA Set and an and an and and and and and and a</td><td>7 4 ANC3 $-$ C1IN3- C2IN3- $-$ MDMIN⁽¹⁾ $-$ CCP2⁽¹⁾ 6 3 ANC4 $-$</td><td>Number of the second second</td><td>Add Number of the second second</td><td>No. No. No.<td>OSS OSCO BAD SCO DS AD C N S SCO SCO SCO SCO SCO SCO SCO SCO SCO S</td><td>OSS OS OS</td><td>OSS MA X <thx< th=""> X X X</thx<></td><td>Mark A</td><td>OSS/DIGATION OR SO OR OR OR OR SO SO</td></td></t<>	Ng Ng Ng OSS/OIG 0 0 0 0 0 7 4 ANC3 6 3 ANC4 5 2 ANC5 8 5 ANC6 9 6 ANC7 1 18 20 17	AG NL AG Set set	Add Na Add Second Second	AG NL AG Setter and	OS NUC OC SUC SUC	OS NAŬ SO SO	OS NH DAIN DA Set and an and an and and and and and and a	7 4 ANC3 $-$ C1IN3- C2IN3- $ -$ MDMIN ⁽¹⁾ $-$ CCP2 ⁽¹⁾ 6 3 ANC4 $ -$	Number of the second	Add Number of the second	No. No. <td>OSS OSCO BAD SCO DS AD C N S SCO SCO SCO SCO SCO SCO SCO SCO SCO S</td> <td>OSS OS OS</td> <td>OSS MA X <thx< th=""> X X X</thx<></td> <td>Mark A</td> <td>OSS/DIGATION OR SO OR OR OR OR SO SO</td>	OSS OSCO BAD SCO DS AD C N S SCO SCO SCO SCO SCO SCO SCO SCO SCO S	OSS OS OS	OSS MA X <thx< th=""> X X X</thx<>	Mark A	OSS/DIGATION OR SO OR OR OR OR SO SO

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers.

3: These peripheral functions are bidirectional. The output pin selections must be the same as the input pin selections.

4: These pins are configured for I²C logic levels; clock and data signals may be assigned to any of these pins. Assignments to other pins (e.g., RA5) will operate, but logic levels will be standard TTL/ST as selected by the INLVL register.

Table of Contents

1.0	Device Overview	12
2.0	Guidelines for Getting Started With PIC16(L)F183XX Microcontrollers	
3.0	Enhanced Mid-Range CPU	
4.0	Memory Organization	
5.0	Device Configuration	
6.0	Resets	
7.0	Oscillator Module	
8.0	Interrupts	
9.0	Power-Saving Operation Modes	
10.0		
11.0	o	
12.0	I/O Ports	
14.0		
15.0	Interrupt-on-Change	172
16.0	Fixed Voltage Reference (FVR)	179
17.0	Temperature Indicator Module	182
18.0	Comparator Module	184
	Pulse-Width Modulation (PWM)	
20.0	Complementary Waveform Generator (CWG) Module	199
21.0	Configurable Logic Cell (CLC)	221
22.0	Analog-to-Digital Converter (ADC) Module	
23.0		
24.0	5-bit Digital-to-Analog Converter (DAC1) Module	
25.0		
	Timer0 Module	
	Timer2/4/6 Module	
	Capture/Compare/PWM Modules	
	Host Synchronous Serial Port (MSSPx) Module	
	Enhanced Universal Synchronous Asynchronous Receiver Transmitter (EUSART1)	
	Reference Clock Output Module	
	In-Circuit Serial Programming™ (ICSP™)	
34.0	5	
	Electrical Specifications	
	Development Support	
	Packaging Information	
	endix A: Data Sheet Revision History	
	Microchip WebSite	
	omer Change Notification Service	
	omer Support	
Produ	uct Identification System	

TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, contact the Marketing Communications Department via E-mail at **docerrors@microchip.com**. We welcome your feedback.

Most Current Data Sheet

To obtain the most up-to-date version of this data sheet, register at our Worldwide Website at:

http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS30000000A is version A of document DS30000000).

Errata

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, check with one of the following:

- Microchip's Worldwide Website; http://www.microchip.com
- Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include literature number) you are using.

Customer Notification System

Register on our website at www.microchip.com to receive the most current information on all of our products.

1.0 DEVICE OVERVIEW


The PIC16(L)F18326/18346 devices are described within this data sheet. PIC16(L)F18326 are available in 14-pin PDIP, SOIC, TSSOP and 16-pin UQFN/QFN/VQFN packages. PIC16(L)F18346 are available in 20-pin PDIP, SOIC, SSOP, UQFN and QFN/VQFN packages. See Section 38.0 "Packaging Information" for further packaging information. Figure 1-1 shows a block diagram of the PIC16(L)F18326/18346 devices. Table 1-2 shows the pinout descriptions.

Reference Table 1-1 for peripherals available per device.

TABLE 1-1: DEVICE PERIPHERAL SUMMARY

SUMMAR	•		
Peripheral		PIC16(L)F18326	PIC16(L)F18346
Analog-to-Digital Converter (ADC)		٠	٠
Temperature Indicator		•	٠
Digital-to-Analog Converter (DAC)			
	DAC1	•	٠
Fixed Voltage Reference (FVR)			
	ADCFVR	•	٠
	CDAFVR	•	٠
Digital Signal Modulator (DSM)			
	DSM1	•	•
Numerically Controlled Oscillator (NC	O)		
	NCO1	٠	٠
Capture/Compare/PWM (CCP) Modul	es		
	CCP1	٠	٠
	CCP2	•	٠
	CCP3	•	•
	CCP4	•	٠
Comparators			
	C1	•	٠
	C2	•	٠
Complementary Waveform Generator (CWG)		
	CWG1	•	٠
	CWG2	•	٠
Configurable Logic Cell (CLC)			
	CLC1	•	•
	CLC2	•	٠
	CLC3	•	٠
	CLC4	•	٠
Enhanced Universal Synchronous/Asy ter (EUSART)	nchronous Receiv	er/Tran	ismit-
	EUSART1	•	٠
Host Synchronous Serial Port (MSSP)		
	MSSP1	•	٠
	MSSP2	•	٠
Pulse-Width Modulator (PWM)	1		
	PWM5	•	٠
	PWM6	•	٠
Timers (TMR)	1		
	TMR0	٠	٠
	TMR1	•	٠
	TMR2	•	٠
	TMR3	•	٠
	TMR4	•	•
	TMR4 TMR5	•	•

PIC16(L)F18326/18346



Name	Function Input Type Output Type			Description
RA0/ANA0/C1IN0+/DAC1OUT/	RA0	TTL/ST	CMOS	General purpose I/O.
SS2 ⁽¹⁾ / ICDDAT/ICSPDAT	ANA0	AN	—	ADC Channel A0 input.
	C1IN0+	AN	—	Comparator C1 positive input.
	DAC1OUT	_	AN	Digital-to-Analog Converter output.
	SS2	TTL/ST	—	Client Select 2 input.
	ICDDAT	TTL/ST	CMOS	In-Circuit Debug Data I/O.
	ICSPDAT	TTL/ST	CMOS	ICSP™ Data I/O.
RA1/ANA1/VREF+/C1IN0-/	RA1	TTL/ST	CMOS	General purpose I/O.
C2IN0-/DAC1REF+/ ICDCLK/	ANA1	AN	—	ADC Channel A1 input.
ICSPCLK	VREF+	AN	—	ADC positive voltage reference input.
	C1IN0-	AN	—	Comparator C1 negative input.
	C2IN0-	AN	_	Comparator C2 negative input.
	DAC1REF+	—	AN	Digital-to-Analog Converter positive reference input.
	ICDCLK	TTL/ST	CMOS	In-Circuit Debug Clock I/O.
	ICSPCLK	TTL/ST	CMOS	ICSP Clock I/O.
RA2/ANA2/VREF-/ DAC1REF-/	RA2	TTL/ST	CMOS	General purpose I/O.
T0CKI ⁽¹⁾ / CCP3 ⁽¹⁾ /CWG1IN ⁽¹⁾ / CWG2IN ⁽¹⁾ /INT ⁽¹⁾	ANA2	AN		ADC Channel A2 input.
CWG2IN\`'/INT\''	VREF-	AN	—	ADC negative voltage reference input.
	DAC1REF-	_	AN	Digital-to-Analog Converter negative reference input.
	TOCKI	TTL/ST	—	TMR0 Clock input.
	CCP3	TTL/ST	CMOS	Capture/Compare/PWM 3 input.
	CWG1IN	TTL/ST	—	Complementary Waveform Generator 1 input.
	CWG2IN	TTL/ST	—	Complementary Waveform Generator 2 input.
	INT	TTL/ST		External interrupt input.
RA3/MCLR/Vpp	RA3	TTL/ST	CMOS	General purpose I/O.
	MCLR	TTL/ST	—	Master Clear with internal pull-up.
	VPP	HV		Programming voltage.
RA4/ANA4/T1G ⁽¹⁾ / SOSCO/	RA4	TTL/ST	CMOS	General purpose I/O.
CLKOUT/OSC2	ANA4	AN	—	ADC Channel A4 input.
	T1G	ST	—	TMR1 gate input.
	SOSCO	_	XTAL	Secondary Oscillator connection.
	CLKOUT	—	CMOS	Fosc/4 output.
	OSC2	—	XTAL	Crystal/Resonator (LP, XT, HS modes).

TABLE 1-2:PIC16(L)F18326 PINOUT DESCRIPTION

 Legend:
 AN = Analog input or output
 CMOS = CMOS compatible input or output
 OD
 = Open-Drain

 TTL = TTL compatible input
 ST
 = Schmitt Trigger input with CMOS levels
 I²C
 = Schmitt Trigger input with I²C

 HV = High Voltage
 XTAL
 = Crystal levels
 I
 I
 I

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-1.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input	Output Type	Description
	Function	Туре	Output Type	Description
RA5/ANA5/T1CKI ⁽¹⁾ / SOSCIN/	RA5	TTL/ST	CMOS	General purpose I/O.
SOSCI/ CLCIN3 ⁽¹⁾ /CLKIN/ OSC1	ANA5	AN	—	ADC Channel A5 input.
USCI	T1CKI	TTL/ST	—	TMR1 Clock input.
	SOSCIN	TTL/ST	—	Secondary Oscillator input connection.
	SOSCI	XTAL	—	Secondary Oscillator connection.
	CLCIN3	TTL/ST	—	Configurable Logic Cell 3 input.
	CLKIN	TTL/ST	—	External clock input.
	OSC1	XTAL	—	Crystal/Resonator (LP, XT, HS modes).
RC0/ANC0/C2IN0+/ T5CKI(1)/	RC0	TTL/ST	CMOS	General purpose I/O.
SCK1 ⁽¹⁾ / SCL1 ^(1,3)	ANC0	AN	—	ADC Channel C0 input.
	C2IN0+	AN	—	Comparator C2 positive input.
	T5CKI	TTL/ST	—	TMR5 Clock input.
	SCK1	TTL/ST	CMOS	SPI Clock 1.
	SCL1	I ² C	OD	I ² C Clock 1.
RC1/ANC1/C1IN1-/C2IN1-/	RC1	TTL/ST	CMOS	General purpose I/O.
CCP4 ⁽¹⁾ /SDI1 ⁽¹⁾ /SDA1 ^(1,3) / CLCIN2 ⁽¹⁾	ANC1	AN		ADC Channel C1 input.
CLCIN2.	C1IN1-	AN	—	Comparator C1 negative input.
	C2IN1-	AN	—	Comparator C2 negative input.
	CCP4	TTL/ST	CMOS	Capture/Compare/PWM 4 input.
	SDI1	TTL/ST	CMOS	SPI Data input 1.
	SDA1	l ² C	OD	I ² C Data 1.
	CLCIN2	TTL/ST	—	Configurable Logic Cell 2 input.
RC2/ANC2/C1IN2-/C2IN2-/	RC2	TTL/ST	CMOS	General purpose I/O.
MDCIN1 ⁽¹⁾	ANC2	AN	—	ADC Channel C2 input.
	C1IN2-	AN	—	Comparator C1 negative input.
	C2IN2-	AN	—	Comparator C2 negative input.
	MDCIN1	TTL/ST	—	Modular Carrier input 1.
RC3/ANC3/C1IN3-/C2IN3-/	RC3	TTL/ST	CMOS	General purpose I/O.
MDMIN ⁽¹⁾ /T5G ⁽¹⁾ / CCP2 ⁽¹⁾ / SS1 ⁽¹⁾ /CLCIN0 ⁽¹⁾	ANC3	AN	—	ADC Channel C3 input.
SSINUCLUINO	C1IN3-	AN	—	Comparator C1 negative input.
	C2IN3-	AN	_	Comparator C2 negative input.
	MDMIN	TTL/ST	_	Modular Source input.
	T5G	TTL/ST	_	TMR5 gate input.
	CCP2	TTL/ST	CMOS	Capture/Compare/PWM 2 input.
	SS1	TTL/ST	—	Client Select 1 input.

 TABLE 1-2:
 PIC16(L)F18326 PINOUT DESCRIPTION (CONTINUED)

 Legend: AN = Analog input or output
 CMOS=CMOS compatible input or output
 OD
 = Open-Drain

 TTL = TTL compatible input
 ST
 = Schmitt Trigger input with CMOS levels
 I²C
 = Schmitt Trigger input with I²C

 HV = High Voltage
 XTAL
 = Crystal levels
 I
 I
 I
 I

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-1.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
RC4/ANC4/T3G ⁽¹⁾ / SCK2 ⁽¹⁾ /	RC4	TTL/ST	CMOS	General purpose I/O.
SCL2 ^(1,3) / CLCIN1 ⁽¹⁾	ANC4	AN	—	ADC Channel C4 input.
	T3G	TTL/ST	—	TMR3 gate input.
	SCK2	TTL/ST	CMOS	SPI Clock 2.
	SCL2	l ² C	OD	I ² C Clock 2.
	CLCIN1	TTL/ST	—	Configurable Logic Cell 1 input.
RC5/ANC5/MDCIN2 ⁽¹⁾ /	RC5	TTL/ST	CMOS	General purpose I/O.
T3CKI ⁽¹⁾ /CCP1 ⁽¹⁾ /SDI2 ⁽¹⁾ / SDA2 ^(1,3) /RX ⁽¹⁾ /DT	ANC5	AN	—	ADC Channel C5 input.
SDA2 ⁽¹⁾ /RX ⁽¹ /DT	MDCIN2	TTL/ST	—	Modular Carrier input 2.
	T3CKI	TTL/ST	—	TMR3 Clock input.
	CCP1	TTL/ST	CMOS	Capture/Compare/PWM 1 input.
	SDI2	TTL/ST	CMOS	SPI Data 2.
	SDA2	l ² C	OD	I ² C Data 2.
	RX	TTL/ST	CMOS	EUSART asynchronous input.
	DT	TTL/ST	CMOS	EUSART synchronous data output.
Vdd	Vdd	Power	—	Positive supply.
Vss	Vss	Power	_	Ground reference.

TABLE 1-2: PIC16(L)F18326 PINOUT DESCRIPTION (CONTINUED)

Legend: AN = Analog input or output CMOS=CMOS compatible input or output = Open-Drain OD TTL = TTL compatible input ST = Schmitt Trigger input with CMOS levels I^2C = Schmitt Trigger input with I^2C

XTAL = Crystal levels

HV = High Voltage Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-1.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
)UT ⁽²⁾	C1	—	CMOS	Comparator C1 output.
	C2	_	CMOS	Comparator C2 output.
	NCO1	_	CMOS	Numerically Controlled Oscillator output.
	DSM	_	CMOS	Digital Signal Modulator output.
	TMR0	_	CMOS	TMR0 clock output.
	CCP1	_	CMOS	Capture/Compare/PWM 1 output.
	CCP2	_	CMOS	Capture/Compare/PWM 2 output.
	CCP3	_	CMOS	Capture/Compare/PWM 3 output.
	CCP4	_	CMOS	Capture/Compare/PWM 4 output.
	PWM5	_	CMOS	Pulse-Width Modulator 5 output.
	PWM6	_	CMOS	Pulse-Width Modulator 6 output.
	CWG1A	_	CMOS	Complementary Waveform Generator 1 output A.
	CWG2A	_	CMOS	Complementary Waveform Generator 2 output A
	CWG1B	_	CMOS	Complementary Waveform Generator 1 output B
	CWG2B	_	CMOS	Complementary Waveform Generator 2 output B
	CWG1C	_	CMOS	Complementary Waveform Generator 1 output C
	CWG2C	_	CMOS	Complementary Waveform Generator 2 output C
	CWG1D	_	CMOS	Complementary Waveform Generator 1 output D
	CWG2D	—	CMOS	Complementary Waveform Generator 2 output D
	SDA1 ⁽³⁾	l ² C	OD	I ² C data output.
	SDA2 ⁽³⁾	l ² C	OD	I ² C data output.
	SCL1 ⁽³⁾	l ² C	OD	I ² C clock output.
	SCL2 ⁽³⁾	l ² C	OD	I ² C clock output.
	SDO1	_	CMOS	SPI1 data output.
	SD02	_	CMOS	SPI2 data output.
	SCK1	_	CMOS	SPI1 clock output.
	SCK2	_	CMOS	SPI2 clock output.
	TX/CK	_	CMOS	Asynchronous TX data/synchronous clock output
	DT	_	CMOS	EUSART synchronous data output.
	CLC1OUT	_	CMOS	Configurable Logic Cell 1 source output.
	CLC2OUT	_	CMOS	Configurable Logic Cell 2 source output.
	CLC3OUT	_	CMOS	Configurable Logic Cell 3 source output.
	CLC4OUT	_	CMOS	Configurable Logic Cell 4 source output.
	CLKR	_	CMOS	Clock Reference output.

TABLE 1-2: PIC16(L)F18326 PINOUT DESCRIPTION (CONTINUED)

 Legend:
 AN = Analog input or output
 CMOS=CMOS compatible input or output
 OD = Open-Drain

 TTL = TTL compatible input
 ST = Schmitt Trigger input with CMOS levels
 I²C = Schmitt Trigger input with I²C

 HV = High Voltage
 XTAL = Crystal levels

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-1.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
RA0/ANA0/C1IN0+/DAC1OUT/	RA0	TTL/ST	CMOS	General purpose I/O.
ICDDAT/ICSPDAT	ANA0	AN	_	ADC Channel A0 input.
	C1IN0+	AN	_	Comparator C1 positive input.
	DAC1OUT	_	AN	Digital-to-Analog Converter output.
	ICDDAT	TTL/ST	CMOS	In-Circuit Debug Data I/O.
	ICSPDAT	TTL/ST	CMOS	ICSP™ Data I/O.
RA1/ANA1/VREF+/C1IN0-/	RA1	TTL/ST	CMOS	General purpose I/O.
C2IN0-/ DAC1REF+/SS2 ⁽¹⁾)/	ANA1	AN	_	ADC Channel A1 input.
ICDCLK/ ICSPCLK	VREF+	AN	_	ADC positive voltage reference input.
	C1IN0-	AN	_	Comparator C1 negative input.
	C2IN0-	AN	_	Comparator C2 negative input.
	DAC1REF+	AN	_	Digital-to-Analog Converter positive reference input.
	SS2	TTL/ST	_	Client Select 2 input.
	ICDCLK	TTL/ST	CMOS	In-Circuit Debug Clock I/O.
	ICSPCLK	TTL/ST	CMOS	ICSP Clock I/O.
RA2/ANA2/VREF-/ DAC1REF-/	RA2	TTL/ST	CMOS	General purpose I/O.
T0CKI ⁽¹⁾ / CCP3 ⁽¹⁾ /CWG1IN ⁽¹⁾ /	ANA2	AN	_	ADC Channel A2 input.
CWG2IN ⁽¹⁾ /CLCIN0 ⁽¹⁾ / INT ⁽¹⁾	VREF-	AN	_	ADC negative voltage reference input.
	DAC1REF-	AN	_	Digital-to-Analog Converter negative reference input.
	T0CKI	TTL/ST	_	TMR0 Clock input.
	CCP3	TTL/ST	CMOS	Capture/Compare/PWM 3 input.
	CWG1IN	TTL/ST	_	Complementary Waveform Generator 1 input.
	CWG2IN	TTL/ST	_	Complementary Waveform Generator 2 input.
	CLCIN0	TTL/ST	_	Configurable Logic Cell 0 input.
	INT	TTL/ST	_	External interrupt input.
RA3/MCLR/VPP	RA3	TTL/ST	CMOS	General purpose I/O.
	MCLR	TTL/ST	_	Master Clear with internal pull-up.
	Vpp	HV	_	Programming voltage.
RA4/ANA4/T1G(1)/T3G ⁽¹⁾ /	RA4	TTL/ST	CMOS	General purpose I/O.
T5G ⁽¹⁾ /SOSCO/CCP4 ⁽¹⁾ /	ANA4	AN	_	ADC Channel A4 input.
CLKOUT/OSC2	T1G	TTL/ST	_	TMR1 gate input.
	T3G	TTL/ST	_	TMR3 gate input.
	T5G	TTL/ST	_	TMR5 gate input.
	SOSCO	_	XTAL	Secondary Oscillator connection.
	CCP4	TTL/ST	CMOS	Capture/Compare/PWM 4 input.
	CLKOUT		CMOS	Fosc/4 output.
	OSC2	_	XTAL	Crystal/Resonator (LP, XT, HS modes).

TABLE 1-3: PIC16(L)F18346 PINOUT DESCRIPTION

 Legend:
 AN
 = Analog input or output
 CMOS= CMOS compatible input or output
 OD
 = Open-Drain

 TTL
 = TTL compatible input
 ST
 = Schmitt Trigger input with CMOS levels
 I²C
 = Schmitt Trigger input with I²C

 HV
 = High Voltage
 XTAL
 = Crystal levels
 I²C
 = Schmitt Trigger input with I²C

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-2.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
RA5/ANA5/T1CKI ⁽¹⁾ / T3CKI ⁽¹⁾ /	RA5	TTL/ST	CMOS	General purpose I/O.
T5CKI ⁽¹⁾ / SOSCIN/SOSCI/ CLKIN/OSC1	ANA5	AN	_	ADC Channel A5 input.
CLKIN/OSC1	T1CKI	TTL/ST	_	TMR1 Clock input.
	T3CKI	TTL/ST	_	TMR3 Clock input.
	T5CKI	TTL/ST	_	TMR5 Clock input.
	SOSCIN	TTL/ST	_	Secondary Oscillator input connection.
	SOSCI	XTAL	_	Secondary Oscillator connection.
	CLKIN	TTL/ST	_	External clock input.
	OSC1	XTAL	_	Crystal/Resonator (LP, XT, HS modes).
RB4/ANB4/SDI1 ⁽¹⁾ / SDA1 ^(1,3) /	RB4	TTL/ST	CMOS	General purpose I/O.
CLCIN2 ⁽¹⁾	ANB4	AN	_	ADC Channel B4 input.
	SDI1	TTL/ST	CMOS	SPI Data input 1.
	SDA1	I ² C	OD	I ² C Data 1.
	CLCIN2	TTL/ST	_	Configurable Logic Cell 2 input.
RB5/ANB5/SDI2 ⁽¹⁾ / SDA2 ^(1,3) /	RB5	TTL/ST	CMOS	General purpose I/O.
RX ⁽¹⁾ /DT/CLCIN3 ⁽¹⁾	ANB5	AN		ADC Channel B5 input.
	SDI2	TTL/ST	CMOS	SPI Data input 2.
	SDA2	l ² C	OD	I ² C Data 2.
	RX	TTL/ST	CMOS	EUSART asynchronous input.
	DT	TTL/ST	CMOS	EUSART synchronous data output.
	CLCIN3	TTL/ST	—	Configurable Logic Cell 3 input.
RB6/ANB6/SCK1 ⁽¹⁾ / SCL1 ^(1,3)	RB6	TTL/ST	CMOS	General purpose I/O.
	ANB6	AN	_	ADC Channel B6 input.
	SCK1	TTL/ST	CMOS	SPI Clock 1.
	SCL1	l ² C	OD	I ² C Clock 1.
RB7/ANB7/SCK2 ⁽¹⁾ / SCL2 ^(1,3)	RB7	TTL/ST	CMOS	General purpose I/O.
	ANB7	AN		ADC Channel B7 input.
	SCK2	TTL/ST	CMOS	SPI Clock 2.
	SCL2	l ² C	OD	I ² C Clock 2.
RC0/ANC0/C2IN0+	RC0	TTL/ST	CMOS	General purpose I/O.
	ANC0	AN	_	ADC Channel C0 input.
	C2IN0+	AN	_	Comparator C2 positive input.
RC1/ANC1/C1IN1-/C2IN1-	RC1	TTL/ST	CMOS	General purpose I/O.
	ANC1	AN	_	ADC Channel C1 input.
	C1IN1-	AN	_	Comparator C1 negative input.
	C2IN1-	AN	_	Comparator C2 negative input.
RC2/ANC2/C1IN2-/C2IN2-/	RC2	TTL/ST	CMOS	General purpose I/O.
MDCIN1 ⁽¹⁾	ANC2	AN	_	ADC Channel C2 input.
	C1IN2-	AN	_	Comparator C1 negative input.
	C2IN2-	AN	_	Comparator C2 negative input.
	MDCIN1	TTL/ST	_	Modular Carrier input 1.

TABLE 1-3: PIC16(L)F18346 PINOUT DESCRIPTION (CONTINUED)

Legend: AN = Analog input or output CMOS= CMOS compatible input or output OD = Open-Drain

TTL = TTL compatible input ST = Schmitt Trigger input with CMOS levels I^2C = Schmitt Trigger input with I^2C HV = High Voltage XTAL = Crystal levels

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-2.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
RC3/ANC3/C1IN3-/C2IN3-/	RC3	TTL/ST	CMOS	General purpose I/O.
MDMIN ⁽¹⁾ / CCP2 ⁽¹⁾ /CLCIN1 ⁽¹⁾ /	ANC3	AN	_	ADC Channel C3 input.
	C1IN3-	AN		Comparator C1 negative input.
	C2IN3-	AN		Comparator C2 negative input.
	MDMIN	TTL/ST		Modular Source input.
	CCP2	TTL/ST	CMOS	Capture/Compare/PWM 2 input.
	CLCIN1	TTL/ST	_	Configurable Logic Cell 1 input.
RC4/ANC4	RC4	TTL/ST	CMOS	General purpose I/O.
	ANC4	AN		ADC Channel C4 input.
RC5/ANC5/MDCIN2 ⁽¹⁾ / CCP1 ⁽¹⁾	RC5	TTL/ST	CMOS	General purpose I/O.
	ANC5	AN		ADC Channel C5 input.
	MDCIN2	TTL/ST		Modular Carrier input 2.
	CCP1	TTL/ST	CMOS	Capture/Compare/PWM 1 input.
RC6/ANC6/SS1 ⁽¹⁾	RC6	TTL/ST	CMOS	General purpose I/O.
	ANC6	AN		ADC Channel C6 input.
	SS1	TTL/ST		Client Select 1 input.
RC7/ANC7	RC7	TTL/ST	CMOS	General purpose I/O.
	ANC7	AN		ADC Channel C7 input.
VDD	Vdd	Power	-	Positive supply.
Vss	Vss	Power	_	Ground reference.

TABLE 1-3: PIC16(L)F18346 PINOUT DESCRIPTION (CONTINUED)

Legend: AN = Analog input or output CMOS= CMOS compatible input or output OD = Open-Drain

TTL = TTL compatible input ST = Schmitt Trigger input with CMOS levels I^2C = Schmitt Trigger input with I^2C HV = High Voltage XTAL = Crystal levels

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-2.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

Name	Function	Input Type	Output Type	Description
OUT ⁽²⁾	C1	—	CMOS	Comparator C1 output.
	C2	—	CMOS	Comparator C2 output.
	NCO1	_	CMOS	Numerically Controlled Oscillator output.
	DSM	—	CMOS	Digital Signal Modulator output.
	TMR0	—	CMOS	Timer0 clock output.
	CCP1	—	CMOS	Capture/Compare/PWM 1 output.
	CCP2	—	CMOS	Capture/Compare/PWM 2 output.
	CCP3	—	CMOS	Capture/Compare/PWM 3 output.
	CCP4	_	CMOS	Capture/Compare/PWM 4 output.
	PWM5	_	CMOS	Pulse-Width Modulator 5 output.
	PWM6	_	CMOS	Pulse-Width Modulator 6 output.
	CWG1A	_	CMOS	Complementary Waveform Generator 1 output A.
	CWG2A	_	CMOS	Complementary Waveform Generator 2 output A.
	CWG1B	_	CMOS	Complementary Waveform Generator 1 output B.
	CWG2B	_	CMOS	Complementary Waveform Generator 2 output B.
	CWG1C	_	CMOS	Complementary Waveform Generator 1 output C.
	CWG2C	_	CMOS	Complementary Waveform Generator 2 output C.
	CWG1D	_	CMOS	Complementary Waveform Generator 1 output D.
	CWG2D	_	CMOS	Complementary Waveform Generator 2 output D.
	SDA1 ⁽³⁾	l ² C	OD	I ² C data output.
	SDA2 ⁽³⁾	l ² C	OD	I ² C data output.
	SCL1 ⁽³⁾	l ² C	OD	I ² C clock output.
	SCL2 ⁽³⁾	l ² C	OD	I ² C clock output.
	SDO1		CMOS	SPI1 data output.
	SD02	_	CMOS	SPI2 data output.
	SCK1	_	CMOS	SPI1 clock output.
	SCK2	_	CMOS	SPI2 clock output.
	TX/CK	_	CMOS	Asynchronous TX data/synchronous clock output.
	DT	—	CMOS	EUSART synchronous data output.
	CLC1OUT		CMOS	Configurable Logic Cell 1 source output.
	CLC2OUT	_	CMOS	Configurable Logic Cell 2 source output.
	CLC3OUT	_	CMOS	Configurable Logic Cell 3 source output.
	CLC4OUT	_	CMOS	Configurable Logic Cell 4 source output.
	CLKR	_	CMOS	Clock Reference output.

TABLE 1-3: PIC16(L)F18346 PINOUT DESCRIPTION (CONTINUED)

Legend:AN= Analog input or outputCMOS=CMOS compatible input or outputOD= Open-DrainTTL= TTL compatible inputST= Schmitt Trigger input with CMOS levels I^2C = Schmitt Trigger input with I^2C

HV = High Voltage XTAL = Crystal levels

Note 1: Default peripheral input. Input can be moved to any other pin with the PPS input selection registers. See Register 13-2.

2: All pin outputs default to PORT latch data. Any pin can be selected as a digital peripheral output with the PPS output selection registers. See Register 13-2.

2.0 GUIDELINES FOR GETTING STARTED WITH PIC16(L)F183XX MICROCONTROLLERS

2.1 Basic Connection Requirements

Getting started with the PIC16(L)F183XX family of 8-bit microcontrollers requires attention to a minimal set of device pin connections before proceeding with development.

The following pins must always be connected:

- All VDD and Vss pins (see Section 2.2 "Power Supply Pins")
 MCLR pin (when configured for external
- operation)

(see Section 2.3 "Master Clear (MCLR) Pin")

These pins must also be connected if they are being used in the end application:

- ICSPCLK/ICSPDAT pins used for In-Circuit Serial Programming[™] (ICSP[™]) and debugging purposes (see Section 2.4 "ICSP[™] Pins")
- OSC1 and OSC2 pins when an external oscillator source is used


(see Section 2.5 "External Oscillator Pins")

Additionally, the following pins may be required:

• VREF+/VREF- pins are used when external voltage reference for analog modules is implemented

The minimum mandatory connections are shown in Figure 2-1.





2.2 Power Supply Pins

2.2.1 DECOUPLING CAPACITORS

The use of decoupling capacitors on every pair of power supply pins (VDD and VSS) is required. All VDD and VSS pins must be connected. None can be left floating.

Consider the following criteria when using decoupling capacitors:

- Value and type of capacitor: A 0.1 μF (100 nF), 10-25V capacitor is recommended. The capacitor must be a low-ESR device, with a resonance frequency in the range of 200 MHz and higher. Ceramic capacitors are recommended.
- Placement on the printed circuit board: The decoupling capacitors need to be placed as close to the pins as possible. It is recommended to place the capacitors on the same side of the board as the device. If space is constricted, the capacitor can be placed on another layer on the PCB using a via; however, ensure that the trace length from the pin to the capacitor is no greater than 0.25 inch (6 mm).
- Handling high-frequency noise: If the board is experiencing high-frequency noise (upward of tens of MHz), add a second ceramic type capacitor in parallel to the above described decoupling capacitor. The value of the second capacitor can be in the range of 0.01 μ F to 0.001 μ F. Place this second capacitor next to each primary decoupling capacitor. In high-speed circuit designs, consider implementing a decade pair of capacitances as close to the power and ground pins as possible (e.g., 0.1 μ F in parallel with 0.001 μ F).
- **Maximizing performance:** On the board layout from the power supply circuit, run the power and return traces to the decoupling capacitors first, and then to the device pins. This ensures that the decoupling capacitors are first in the power chain. Equally important is to keep the trace length between the capacitor and the power pins to a minimum, thereby reducing PCB trace inductance.

2.2.2 TANK CAPACITORS

On boards with power traces running longer than six inches in length, it is suggested to use a tank capacitor for integrated circuits, including microcontrollers, to supply a local power source. The value of the tank capacitor may be determined based on the trace resistance that connects the power supply source to the device, and the maximum current drawn by the device in the application. In other words, select the tank capacitor so that it meets the acceptable voltage sag at the device. Typical values range from 4.7 μ F to 47 μ F.

2.3 Master Clear (MCLR) Pin

The MCLR pin provides three specific device functions:

- Device Reset (when MCLRE = 1)
- Digital input pin (when MCLRE = 0)
- Device Programming and Debugging

If programming and debugging are not required in the end application then either set the MCLRE Configuration bit to '1' and use the pin as a digital input or clear the MCLRE Configuration bit and leave the pin open to use the internal weak pull-up. The addition of other components, to help increase the application's resistance to spurious Resets from voltage sags, may be beneficial. A typical configuration is shown in Figure 2-1. Other circuit designs may be implemented, depending on the application's requirements.

During programming and debugging, the resistance and capacitance that can be added to the pin must be considered. Device programmers and debuggers drive the \overline{MCLR} pin. Consequently, specific voltage levels (VIH and VIL) and fast signal transitions must not be adversely affected. Therefore, the programmer \overline{MCLR}/VPP output will need to be connected directly to the pin so that R1 isolates the capacitor, C1 from the \overline{MCLR} pin during programming and debugging operations.

Any components associated with the $\overline{\text{MCLR}}$ pin must be placed within 0.25 inch (6 mm) of the pin.

2.4 ICSP[™] Pins

The ICSPCLK and ICSPDAT pins are used for In-Circuit Serial ProgrammingTM (ICSPTM) and debugging purposes. It is recommended to keep the trace length between the ICSP connector and the ICSP pins on the device as short as possible. If the ICSP connector is expected to experience an ESD event, a series resistor is recommended, with the value in the range of a few tens of ohms, not to exceed 100 Ω .

Pull-up resistors, series diodes and capacitors on the ICSPCLK and ICSPDAT pins are not recommended as they will interfere with the programmer/debugger communications to the device. If such discrete components are an application requirement, they must be isolated from the programmer by resistors between the application and the device pins or removed from the circuit during programming. Alternatively, refer to the AC/DC characteristics and timing requirements information in the respective device Flash programming specification for information on capacitive loading limits, and pin input voltage high (VIH) and input low (VIL) requirements.

For device emulation, ensure that the "Communication Channel Select" (i.e., ICSPCLK/ICSPDAT pins), programmed into the device, matches the physical connections for the ICSP to the Microchip debugger/ emulator tool.

For more information on available Microchip development tools connection requirements, refer to **Section 37.0 "Development Support"**.

2.5 External Oscillator Pins

Many microcontrollers have options for at least two oscillators: a high-frequency primary oscillator and a low-frequency secondary oscillator (refer to **Section 7.0 "Oscillator Module"** for details).

The oscillator circuit must be placed on the same side of the board as the device. Place the oscillator circuit close to the respective oscillator pins with no more than 0.5 inch (12 mm) between the circuit components and the pins. The load capacitors must be placed next to the oscillator itself, on the same side of the board.

Use a grounded copper pour around the oscillator circuit to isolate it from surrounding circuits. The grounded copper pour must be routed directly to the MCU ground. Do not run any signal traces or power traces inside the ground pour. Also, if using a two-sided board, avoid any traces on the other side of the board where the crystal is placed.

Layout suggestions are shown in Figure 2-2. In-line s may be handled with a single-sided layout that completely encompasses the oscillator pins. With fine-pitch s, it is not always possible to completely surround the pins and components. A suitable solution is to tie the broken guard sections to a mirrored ground layer. In all cases, the guard trace(s) must be returned to ground.


In planning the application's routing and I/O assignments, ensure that adjacent PORT pins, and other signals in close proximity to the oscillator, are benign (i.e., free of high frequencies, short rise and fall times, and other similar noise).


For additional information and design guidance on oscillator circuits, refer to these Microchip Application Notes, available at the corporate website (www.microchip.com):

- AN826, "Crystal Oscillator Basics and Crystal Selection for rfPIC™ and PICmicro[®] Devices"
- AN849, "Basic PICmicro[®] Oscillator Design"
- AN943, "Practical PICmicro[®] Oscillator Analysis and Design"
- AN949, "Making Your Oscillator Work"

2.6 Unused I/Os

Unused I/O pins may be configured as outputs and driven to a logic low state. Alternatively, connect a 1 k Ω to 10 k Ω resistor to Vss on unused pins and drive the output logic low.






3.0 ENHANCED MID-RANGE CPU

This family of devices contains an enhanced mid-range 8-bit CPU core. The CPU has 48 instructions. Interrupt capability includes automatic context saving. The hardware stack is 16-levels deep and has Overflow and Underflow Reset capability. Direct, Indirect, and

FIGURE 3-1: CORE BLOCK DIAGRAM

Relative Addressing modes are available. Two File Select Registers (FSRs) provide the ability to read program and data memory.

- · Automatic Interrupt Context Saving
- · 16-level Stack with Overflow and Underflow
- File Select Registers
- Instruction Set



3.1 Automatic Interrupt Context Saving

During interrupts, certain registers are automatically saved in shadow registers and restored when returning from the interrupt. This saves stack space and user code. See **Section 8.5 "Automatic Context Saving"** for more information.

3.2 16-Level Stack with Overflow and Underflow

These devices have a hardware stack memory 15 bits wide and 16 words deep. A Stack Overflow or Underflow will set the appropriate bit (STKOVF or STKUNF) in the PCON register, and if enabled, will cause a software Reset. See Section 4.4 "Stack" for more details.

3.3 File Select Registers

There are two 16-bit File Select Registers (FSR). FSRs can access all file registers, program memory, and data EEPROM, which allows one Data Pointer for all memory. When an FSR points to program memory, there is one additional instruction cycle in instructions using INDF to allow the data to be fetched. General purpose memory can now also be addressed linearly, providing the ability to access contiguous data larger than 80 bytes. There are also new instructions to support the FSRs. See Section 4.5 "Indirect Addressing" for more details.

3.4 Instruction Set

There are 48 instructions for the enhanced mid-range CPU to support the features of the CPU. See **Section 34.0 "Instruction Set Summary**" for more details.

4.0 MEMORY ORGANIZATION

These devices contain the following types of memory:

- Program Memory
 - Configuration Words
 - Device ID
 - Revision ID
 - User ID
 - Program Flash Memory
- Data Memory
 - Core Registers
 - Special Function Registers
 - General Purpose RAM
 - Common RAM
- Data EEPROM

The following features are associated with access and control of program memory and data memory:

- PCL and PCLATH
- Stack
- Indirect Addressing
- NVMREG Access

4.1 **Program Memory Organization**

The enhanced mid-range core has a 15-bit program counter capable of addressing 32K x 14 program memory space. Table 4-1 shows the memory sizes implemented. Accessing a location above these boundaries will cause a wrap-around within the implemented memory space. The Reset vector is at 0000h and the interrupt vector is at 0004h (see Figure 4-1).

TABLE 4-1: DEVICE SIZES AND ADDRESSES

Device	Program Memory Size (Words)	Last Program Memory Address
PIC16(L)F18326/18346	16384	3FFFh

FIGURE 4-1: PROGRAM MEMORY MAP AND STACK FOR PIC16(L)F18326/18346

	PC<14:0>	
RETUR	L, CALLW N, RETLW Dt, RETFIE	
	Stack Level 0	1
	Stack Level 1	
	Stack Level 15	
	Reset Vector	0000h
	•	
C	Interrupt Vector	0004h
On-chip Brogrom	D	0005h
Program	Page 0-3	3FFFh
, , , , , , , , , , , , , , , , , , ,		4000h
	Rollover to Page 0	
	:	
	Rollover to Page 0	7FFFh

4.1.1 READING PROGRAM MEMORY AS DATA

There are three methods of accessing constants in program memory. The first method is to use tables of RETLW instructions. The second method is to set an FSR to point to the program memory. The third method is to use the NVMCON registers to access the program memory.

4.1.1.1 RETLW Instruction

The RETLW instruction can be used to provide access to tables of constants. The recommended way to create such a table is shown in Example 4-1.

EXAMPLE 4-1:	RETLW INSTRUCTION
constants	
BRW	;Add Index in W to
	;program counter to
	;select data
RETLW DATA0	;Index0 data
RETLW DATA1	;Index1 data
RETLW DATA2	
RETLW DATA3	
my_function	
; LOTS OF CO	DE
MOVLW DA	TA_INDEX
call constants	5
; THE CONSTAN	NT IS IN W

The BRW instruction makes this type of table very simple to implement. If the code must remain portable with previous generations of microcontrollers, the computed GOTO method must be used because the BRW instruction is not available in some devices, such as the PIC16F6XX, PIC16F7XX, PIC16F8XX, and PIC16F9XX devices.

4.1.1.2 Indirect Read with FSR

The program memory can be accessed as data by setting bit 7 of an FSRxH register and reading the matching INDFx register. The MOVIW instruction will place the lower eight bits of the addressed word in the W register. Writes to the program memory cannot be performed via the INDF registers. Instructions that read the program memory via the FSR require one extra instruction cycle to complete. Example 4-2 demonstrates accessing the program memory via an FSR.

The HIGH directive will set bit 7 if a label points to a location in the program memory.

EXAMPLE 4-2: ACCESSING PROGRAM MEMORY VIA FSR

constants					
RETLW	DATAO		;Index0	data	
RETLW	DATA1		;Index1	data	
RETLW	DATA2				
RETLW	data3				
my_functi	on				
; LO:	IS OF COD)E			
MOVLW	LOW CO	nstan	ts		
MOVWF	FSR1L				
MOVLW	HIGH C	onsta	nts		
MOVWF	FSR1H				
MOVIW	0[FSR1]			
;THE PROG	RAM MEMOR	RY IS	IN W		

4.1.1.3 NVMREG Access

The NVMREG interface allows read/write access to all locations accessible by the FSRs, User ID locations, and EEPROM. The NVMREG interface also provides read-only access to Device ID, Revision ID, and Configuration data. See **Section 11.4** "NVMREG Access" for more information.

4.2 Data Memory Organization


The data memory is partitioned into 32 memory banks with 128 bytes in each bank. Each bank consists of (Figure 4-2):

- 12 core registers
- Special Function Registers (SFR)
- Up to 80 bytes of General Purpose RAM (GPR)
- 16 bytes of common RAM

4.2.1 BANK SELECTION

The active bank is selected by writing the bank number into the Bank Select Register (BSR). Unimplemented memory will read as '0'. All data memory can be accessed either directly (via instructions that use the file registers) or indirectly via the two File Select Registers (FSR). See Section 4.5 "Indirect Addressing" for more information. Data memory uses a 12-bit address. The upper five bits of the address define the Bank address and the lower seven bits select the registers/RAM in that bank.

FIGURE 4-2: BANKED-MEMORY PARTITIONING



4.2.2 CORE REGISTERS

The core registers contain the registers that directly affect basic operation. The core registers occupy the first 12 addresses of every data memory bank (addresses x00h/x80h through x0Bh/x8Bh). These registers are listed below in Table 4-2. For detailed information, see Table 4-4.

TABLE 4-2: CORE REGISTERS

Addresses	BANKx
x00h or x80h	INDF0
x01h or x81h	INDF1
x02h or x82h	PCL
x03h or x83h	STATUS
x04h or x84h	FSR0L
x05h or x85h	FSR0H
x06h or x86h	FSR1L
x07h or x87h	FSR1H
x08h or x88h	BSR
x09h or x89h	WREG
x0Ah or x8Ah	PCLATH
x0Bh or x8Bh	INTCON

4.2.2.1 STATUS Register

The STATUS register, shown in Register 4-1, contains:

- The arithmetic status of the ALU
- The Reset status

1' = Bit is set

The STATUS register can be the destination for any instruction, like any other register. If the STATUS register is the destination for an instruction that affects the Z, DC or C bits, then the write to these three bits is disabled. These bits are set or cleared according to the device logic. Furthermore, the TO and PD bits are not writable. Therefore, the result of an instruction with the STATUS register as destination may be different than intended.

REGISTER 4-1: STATUS: STATUS REGISTER

'0' = Bit is cleared

For example, CLRF STATUS will clear the upper three bits and set the Z bit. This leaves the STATUS register as '000u u1uu' (where u = unchanged).

It is recommended, therefore, that only BCF, BSF, SWAPF and MOVWF instructions are used to alter the STATUS register, because these instructions do not affect any Status bits. For other instructions not affecting any Status bits (Refer to Section 4.0 "Memory Organization").

Note 1: The <u>C and DC</u> bits operate as Borrow and Digit Borrow out bits, respectively, in subtraction.

U-0	U-0	U-0	R-1/q	R-1/q	R/W-0/u	R/W-0/u	R/W-0/u		
_	_	_	ТО	PD	Z	DC ⁽¹⁾	C ⁽¹⁾		
bit 7			•			•	bit 0		
Legend:									
R = Readable bitW = Writable bitU = Unimplemented bit, read as '0'									
u = Bit is unchar	nged	x = Bit is unkr	-n/n = Value at POR and BOR/Value at all other Resets						

q = Value depends on condition

bit 7-5	Unimplemented: Read as '0'
bit 4	TO: Time-Out bit
	1 = After power-up, CLRWDT instruction or SLEEP instruction 0 = A WDT Time-out occurred
bit 3	PD: Power-Down bit
	1 = After power-up or by the CLRWDT instruction 0 = By execution of the SLEEP instruction
bit 2	Z: Zero bit
	 1 = The result of an arithmetic or logic operation is zero 0 = The result of an arithmetic or logic operation is not zero
bit 1	DC: Digit Carry/Digit Borrow bit (ADDWF, ADDLW, SUBLW, SUBWF instructions) ⁽¹⁾
	 1 = A carry-out from the 4th low-order bit of the result occurred 0 = No carry-out from the 4th low-order bit of the result
bit 0	C: Carry/Borrow bit ⁽¹⁾ (ADDWF, ADDLW, SUBLW, SUBWF instructions) ⁽¹⁾
	1 = A carry-out from the Most Significant bit of the result occurred
	0 = No carry-out from the Most Significant bit of the result occurred
Note 1:	For Borrow, the polarity is reversed. A subtraction is executed by adding the two's complement of the

Note 1: For Borrow, the polarity is reversed. A subtraction is executed by adding the two's complement of the second operand. For rotate (RRF, RLF) instructions, this bit is loaded with either the high-order or low-order bit of the source register.

4.2.3 SPECIAL FUNCTION REGISTERS

The Special Function Registers are registers used by the application to control the desired operation of peripheral functions in the device. The Special Function Registers occupy the 20 bytes after the core registers of every data memory bank (addresses x0Ch/x8Ch through x1Fh/x9Fh), with the exception of banks 27, 28, and 29 (PPS and CLC registers). The registers associated with the operation of the peripherals are described in the appropriate peripheral chapter of this data sheet.

4.2.4 GENERAL PURPOSE RAM

There are up to 80 bytes of GPR in each data memory bank. The general purpose RAM can be accessed in a non-banked method via the FSRs. This can simplify access to large memory structures. See **Section 4.5.2 "Linear Data Memory"** for more information.

4.2.5 COMMON RAM

There are 16 bytes of common RAM accessible from all banks.

4.2.6 DEVICE MEMORY MAPS

The memory maps for PIC16(L)F18326/18346 are as shown in Table 4-4.

IADLE	4-3. C	PECIAL	FUNCT		JUSIER			NS 0-31		AINROJ [®]				
Bank Offset	Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets			
All Bank	s													
000h	INDF0	Addressing physical re		n uses conte	ents of FSR0	H/FSR0L to	address dat	ta memory (i	not a	XXXX XXXX	XXXX XXXX			
001h	INDF1		ressing this location uses contents of FSR1H/FSR1L to address data memory (not a xxxx xxxx xxxx xxxx xxxx xxxx xxxx											
002h	PCL	Program C	ounter (PC)	Least Signif	icant Byte					0000 0000	0000 0000			
003h	STATUS		_	_	TO	PD	Z	DC	С	1 1000	q quuu			
004h	FSR0L	Indirect Da	ta Memory A	Address 0 Lo	w Pointer					0000 0000	uuuu uuuu			
005h	FSR0H	Indirect Da	ta Memory A	Address 0 Hi	gh Pointer					0000 0000	0000 0000			
006h	FSR1L	Indirect Da	ta Memory A	Address 1 Lo	w Pointer					0000 0000	uuuu uuuu			
007h	FSR1H	Indirect Da	ta Memory A	Address 1 Hi	gh Pointer					0000 0000	0000 0000			
008h	BSR	_	_	_	BSR4	BSR3	BSR2	BSR1	BSR0	0 0000	0 0000			
009h	WREG	Working R	egister							0000 0000	uuuu uuuu			
00Ah	PCLATH	_	Write Buffe	rite Buffer for the upper 7 bits of the Program Counter -000 0000 -000 000										
00Bh	INTCON	GIE	PEIE		_	_	_	_	INTEDG	001	001			

TABLE 4-3: SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (ALL BANKS)⁽¹⁾

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: These registers can be accessed from any bank.

TABLE	4-4: SPE	CIAL F			UMMARY B	ANKS 0-31						
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 0												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	cifics				
00Ch	PORTA		_	—	RA5	RA4	RA3	RA2	RA1	RA0	xx xxxx	uu uuuu
00Dh	PORTB	X —		•	•	Unimple	emented	•	•	•	—	
		— X	RB7	RB6	RB5	RB4	—	—	_	—	XXXX	uuuu
00Eh	PORTC	X —	—	—	RC5	RC4	RC3	RC2	RC1	RC0	xx xxxx	uu uuuu
		— X	RC7	RC6	RC5	RC4	RC3	RC2	RC1	RC0	XXXX XXXX	นนนน นนนเ
00Fh	—	—				Unimple	emented		-		_	—
010h	PIR0		_	_	TMR0IF	IOCIF	_	_	_	INTF	000	000
011h	PIR1		TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	0000 0000	0000 0000
012h	PIR2		TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	0000 0000	0000 0000
013h	PIR3		OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF	0000 0000	0000 0000
014h	PIR4		CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	0000 0000	0000 0000
015h	TMR0L				•	TMR0I	L<7:0>	•	•	•	XXXX XXXX	XXXX XXXX
016h	TMR0H					TMR0	H<7:0>				1111 1111	1111 1111
017h	T0CON0		T0EN		TOOUT	T016BIT		TOOUT	PS<3:0>		0-00 0000	0-00 0000
018h	T0CON1			T0CS<2:0>		TOASYNC		TOCKF	°S<3:0>		0000 0000	0000 0000
019h	TMR1L					TMR1I	L<7:0>				XXXX XXXX	นนนน นนนเ
01Ah	TMR1H					TMR1	H<7:0>				XXXX XXXX	นนนน นนนเ
01Bh	T1CON		TMR1CS	6<1:0>	T1CK	PS<1:0>	T1SOSC	T1SYNC	_	TMR10N	0000 00-0	uuuu uu-i
01Ch	T1GCON		TMR1GE	T1GPOL	T1GTM	T1GSPM	T1GGO/ DONE	T1GVAL	T1GS	S<1:0>	0000 0x00	uuuu uxui
01Dh	TMR2			•		TMR2	2<7:0>	•	•		0000 0000	0000 0000
01Eh	PR2					PR2<	<7:0>				1111 1111	1111 1111
01Fh	T2CON		—		T2OU	TPS<3:0>		TMR2ON	T2CKF	PS<1:0>	-000 0000	-000 0000

 Legend:
 x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

 Note
 1:
 Only on PIC16F18326/18346.

2: Register accessible from both User and ICD Debugger.

TABLE 4-4: SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 1												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				

08Ch TRISA — — TRISA5 TRISA4 — TRISA2 TRISA1 TRISA0	11 -111	11 -111
		11 111
08Dh TRISB X — Unimplemented	—	—
- X TRISB7 TRISB6 TRISB5 TRISB4	1111	1111
08Eh TRISC X – – – TRISC5 TRISC4 TRISC3 TRISC2 TRISC1 TRISC0	11 1111	11 1111
– X TRISC7 TRISC6 TRISC5 TRISC4 TRISC3 TRISC2 TRISC1 TRISC0	1111 1111	1111 1111
08Fh — — Unimplemented	—	—
090h PIE0 TMR0IE IOCIE INTE	000	000
091h PIE1 TMR1GIE ADIE RCIE TXIE SSP1IE BCL1IE TMR2IE TMR1IE	0000 0000	0000 0000
092h PIE2 TMR6IE C2IE C1IE NVMIE SSP2IE BCL2IE TMR4IE NCO1IE	0000 0000	0000 0000
093h PIE3 OSFIE CSWIE TMR3GIE TMR3IE CLC4IE CLC3IE CLC2IE CLC1IE	0000 0000	0000 0000
094h PIE4 CWG2IE CWG1IE TMR5GIE TMR5IE CCP4IE CCP3IE CCP2IE CCP1IE	0000 0000	0000 0000
095h — — Unimplemented	—	—
096h — — Unimplemented	—	—
097h WDTCON — — WDTPS<4:0> SWDTEN	01 0110	01 0110
098h — — Unimplemented	—	—
099h — — Unimplemented	—	—
09Ah — — Unimplemented	—	—
09Bh ADRESL ADRES<7:0>	XXXX XXXX	uuuu uuuu
09Ch ADRESH ADRES<9:8>	XXXX XXXX	uuuu uuuu
09Dh ADCON0 GO/DONE ADON	0000 0000	0000 0000
09Eh ADCON1 ADFM ADCS<2:0> — ADNREF ADPREF<1:0>	0000 -000	0000 -000
09Fh ADACT — — — ADACT<4:0>	0 0000	0 0000

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', x = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

2: Register accessible from both User and ICD Debugger.

TABLE	<u>4-4: SPE</u>	CIAL F	UNCTION RE	EGISTER S	UMMARY B	ANKS 0-31 (CONTINUE	<u>)</u>				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 2												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
10Ch	LATA		_	_	LATA5	LATA4		LATA2	LATA1	LATA0	xx -xxx	uu -uuu
10Dh	LATB	X —				Unimple	mented				—	
		— X	LATB7	LATB6	LATB5	LATB4	—	—	—	—	XXXX	uuuu
10Eh	LATC	X —	—	—	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0	xx xxxx	uu uuuu
		— X	LATC7	LATC6	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0	XXXX XXXX	นนนน นนนน
10Fh	—	—				Unimple	emented				—	_
110h	—	—				Unimple	mented				—	_
111h	CM1CON0		C10N	C10UT		C1POL		C1SP	C1HYS	C1SYNC	00-0 -100	00-0 -100
112h	CM1CON1		C1INTP	C1INTN		C1PCH<2:0>			C1NCH<2:0>		0000 0000	0000 0000
113h	CM2CON0		C2ON	C2OUT		C2POL		C2SP	C2HYS	C2SYNC	00-0 -100	00-0 -100
114h	CM2CON1		C2INTP	C2INTN		C2PCH<2:0>			C2NCH<2:0>		0000 0000	0000 0000
115h	CMOUT		—	—	_	—	_	—	MC2OUT	MC1OUT	00	00
116h	BORCON		SBOREN		_	—	_	—	—	BORRDY	1q	uu
117h	FVRCON		FVREN	FVRRDY	TSEN	TSRNG	CDAFV	′R<1:0>	ADFV	R<1:0>	0q00 0000	0q00 0000
118h	DACCON0		DAC1EN	—	DAC10E	—	DAC1PS	SS<1:0>	_	DAC1NSS	0-0- 00-0	0-0- 00-0
119h	DACCON1			—	_			DAC1R<4:0>			0 0000	0 0000
11Ah to		_				Unimple	mented				_	_

Unimplemented

OUNTRADY DANIZO A AA (OONTINULED)

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Legend:

Only on PIC16F18326/18346. Note 1:

Register accessible from both User and ICD Debugger. 2:

_

11Fh

TABLE 4-4:	SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)
------------	--

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 3												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
18Ch	ANSELA		-	_	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	xx -xxx	uu -uuu
18Dh	ANSELB	X —				Unimple	emented				—	—
		— X	ANSB7	ANSB6	ANSB5	ANSB4	_	—	_	_	xxxx	uuuu
18Eh	ANSELC	Х	—	—	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	xx xxxx	uu uuuu
		— X	ANSC7	ANSC6	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	XXXX XXXX	uuuu uuuu
18Fh	—	—				Unimple	emented				—	_
190h	—	—				Unimple	emented				—	
191h	—	—				Unimple	emented				—	_
192h	—	—				Unimple	emented				_	_
193h	—	—				Unimple	emented				—	_
194h	—	-				Unimple	emented				—	_
195h	—	—				Unimple	emented				—	
196h	—	—				Unimple	emented				—	—
197h	VREGCON ⁽¹⁾		—	—			—	—	VREGPM	Reserved	01	01
198h	—	—				Unimple	emented				—	—
199h	RC1REG					RC1RE	G<7:0>				0000 0000	0000 0000
19Ah	TX1REG					TX1RE					0000 0000	0000 0000
19Bh	SP1BRGL					SP1BR					0000 0000	0000 0000
19Ch	SP1BRGH				1	SP1BR0	1		I	1	0000 0000	0000 0000
19Dh	RC1STA		SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	0000 000x	0000 000x
19Eh	TX1STA		CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TMRT	TX9D	0000 0010	0000 0010

PIC16(L)F18326/18346

19Fh

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

SCKP

BRG16

WUE

ABDEN

01-0 0-00 01-0 0-00

Note 1: Only on PIC16F18326/18346.

BAUD1CON

2: Register accessible from both User and ICD Debugger.

ABDOVF

RCIDL

TABLE	4-4: SPE	CIAL F	UNCTION RE	EGISTER SI	UMMARY B	ANKS 0-31 (CONTINUE))				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 4												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
20Ch	WPUA			_	WPUA5	WPUA4	WPUA3	WPUA2	WPUA1	WPUA0	00 0000	00 0000
20Dh	WPUB	X —				Unimple	mented				-	—
		— X	WPUB7	WPUB6	WPUB5	WPUB4				—	0000	0000
20Eh	WPUC	X —	-	_	WPUC5	WPUC4	WPUC3	WPUC2	WPUC1	WPUC0	00 0000	00 0000
		— X	WPUC7	WPUC6	WPUC5	WPUC4	WPUC3	WPUC2	WPUC1	WPUC0	0000 0000	0000 0000
20Fh	—	—				Unimple	emented				—	—
210h	_	-				Unimple	emented				_	—
211h	SSP1BUF					SSP1Bl	JF<7:0>				XXXX XXXX	uuuu uuuu
212h	SSP1ADD					SSP1AD)D<7:0>				0000 0000	0000 0000
213h	SSP1MSK					SSP1MS	SK<7:0>				1111 1111	1111 1111
214h	SSP1STAT		SMP	CKE	D/A	Р	S	R/W	UA	BF	0000 0000	0000 0000
215h	SSP1CON1		WCOL	SSPOV	SSPEN	CKP		SSPM	1<3:0>		0000 0000	0000 0000
216h	SSP1CON2		GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	0000 0000	0000 0000
217h	SSP1CON3		ACKTIM	PCIE	SCIE	BOEN	SDAHT	SBCDE	AHEN	DHEN	0000 0000	0000 0000
218h	—	—				Unimple	mented				_	
219h	SSP2BUF					SSP2BL	JF<7:0>				XXXX XXXX	uuuu uuuu
21Ah	SSP2ADD					SSP2AD)D<7:0>				0000 0000	0000 0000
21Bh	SSP2MSK					SSP2MS	SK<7:0>				1111 1111	1111 1111
21Ch	SSP2STAT		SMP	CKE	D/A	Р	S	R/W	UA	BF	0000 0000	0000 0000
21Dh	SSP2CON1		WCOL	SSPOV	SSPEN	CKP		SSPM	1<3:0>		0000 0000	0000 0000
21Eh	SSP2CON2		GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	0000 0000	0000 0000
21Fh	SSP2CON3		ACKTIM	PCIE	SCIE	BOEN	SDAHT	SBCDE	AHEN	DHEN	0000 0000	0000 0000

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

Note 1:

2: Register accessible from both User and ICD Debugger.

1 (CONTINUED)
;-

IADLL	•••	• • • • •			•			- /				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 5												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
28Ch	ODCONA		_	_	ODCA5	ODCA4		ODCA2	ODCA1	ODCA0	00 -000	00 -000
28Dh	ODCONB	X —				Unimple	mented				—	—
		— X	ODCB7	ODCB6	ODCB5	ODCB4	_	—		_	0000	0000
28Eh	ODCONC	X —	—	-	ODCC5	ODCC4	ODCC3	ODCC2	ODCC1	ODCC0	00 0000	00 0000
		— X	ODCC7	ODCC6	ODCC5	ODCC4	ODCC3	ODCC2	ODCC1	ODCC0	0000 0000	0000 0000
28Fh	—	—	Unimplemented								_	-
290h	—		Unimplemented								—	_
291h	CCPR1L		CCPR1<7:0>									XXXX XXXX
292h	CCPR1H					CCPR1	<15:8>				XXXX XXXX	XXXX XXXX
293h	CCP1CON		CCP1EN	_	CCP1OUT	CCP1FMT		CCP1MC	DE<3:0>		0-x0 0000	0-x0 0000
294h	CCP1CAP		<u> </u>					CCP1C	TS<3:0>		0000	xxxx
295h	CCPR2L					CCPR2	2<7:0>				XXXX XXXX	XXXX XXXX
296h	CCPR2H				•	CCPR2	<15:8>				XXXX XXXX	XXXX XXXX
297h	CCP2CON		CCP2EN	_	CCP2OUT	CCP2FMT		CCP2MC	DE<3:0>		0-x0 0000	0-x0 0000
298h	CCP2CAP			_		_		CCP2C	TS<3:0>		0000	xxxx
299h	—		Unimplemented								—	_
29Ah	—	—	Unimplemented								—	_
29Bh	—		Unimplemented								—	_
29Ch	—		Unimplemented								—	_
29Dh	—		Unimplemented								—	
29Eh	—		Unimplemented								—	_
29Fh	CCPTMRS		C4TSEL	<1:0>	C3TSE	C3TSEL<1:0> C2TSEL<1:0> C1TSEL<1:0>						0101 0101

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

2: Register accessible from both User and ICD Debugger.

TABLE	4-4: SPE	CIAL F	UNCTION RE	GISTER S	UMMARY B	ANKS 0-31 (CONTINUE	D)				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 6												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
30Ch	SLRCONA		—	—	SLRA5	SLRA4	—	SLRA2	SLRA1	SLRA0	11 -111	11 -11
30Dh	SLRCONB	X —				Unimple	emented				—	—
		— X	SLRB7	SLRB6	SLRB5	SLRB4	—	_	—	—	1111	1111
30Eh	SLRCONC	X —	—	—	SLRC5	SLRC4	SLRC3	SLRC2	SLRC1	SLRC0	11 1111	11 111
		— X	SLRC7	SLRC6	SLRC5	SLRC4	SLRC3	SLRC2	SLRC1	SLRC0	1111 1111	1111 111
30Fh	-	-				Unimple	emented				—	—
310h	_	—				Unimple	emented				—	
311h	CCPR3L					CCPR	3<7:0>				XXXX XXXX	XXXX XXXX
312h	CCPR3H					CCPR3	<15:8>				XXXX XXXX	XXXX XXX
313h	CCP3CON		CCP3EN	—	CCP3OUT	CCP3FMT		CCP3MC	DE<3:0>		0-x0 0000	0-x0 0000
314h	CCP3CAP		—	—	—	—		CCP3C	TS<3:0>		0000	xxx:
315h	CCPR4L					CCPR	4<7:0>				XXXX XXXX	XXXX XXX
316h	CCPR4H		CCPR4<15:8> xxxx xxxx xxxx xxxx xxxx									
317h	CCP4CON		CCP4EN	—	CCP4OUT	P4OUT CCP4FMT CCP4MODE<3:0> 0-x0 0000 0-x0 0000						
318h	CCP4CAP		—	—	—	—		CCP4C	TS<3:0>		0000	xxx:
319h to 31Fh	_	-	Unimplemented									

 Legend:
 x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

 Note
 1:
 Only on PIC16F18326/18346.

 Legend:

TABLE 4-4:	SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)
------------	--

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 7												
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
38Ch	INLVLA			—	INLVLA5	INLVLA4	INLVLA3	INLVLA2	INLVLA1	INLVLA0	11 1111	11 1111
38Dh	INLVLB	X —				Unimple	emented				—	—
		— X	INLVLB7	INLVLB6	INLVLB5	INLVLB4	_			_	1111	1111
38Eh	INLVLC	X —	—	—	INLVLC5	INLVLC4	INLVLC3	INLVLC2	INLVLC1	INLVLC0	11 1111	11 1111
		— X	INLVLC7	INLVLC6	INLVLC5	INLVLC4	INLVLC3	INLVLC2	INLVLC1	INLVLC0	1111 1111	1111 1111
38Fh	—	— Unimplemented								—	_	
390h	—	—		Unimplemented								_
391h	IOCAP		—	—	IOCAP5	IOCAP4	IOCAP3	IOCAP2	IOCAP1	IOCAP0	00 0000	00 0000
392h	IOCAN		—	—	IOCAN5	IOCAN4	IOCAN3	IOCAN2	IOCAN1	IOCAN0	00 0000	00 0000
393h	IOCAF		_	—	IOCAF5	IOCAF4	IOCAF3	IOCAF2	IOCAF1	IOCAF0	00 0000	00 0000
394h	IOCBP	X —				Unimple	emented				—	-
		— X	IOCBP7	IOCBP6	IOCBP5	IOCBP4	—	—	—	—	0000	0000
395h	IOCBN	X —				Unimple	emented				—	-
		— X	IOCBN7	IOCBN6	IOCBN5	IOCBN4	—	—	—	—	0000	0000
396h	IOCBF	X —				Unimple	mented		_		—	—
		— X	IOCBF7	IOCBF6	IOCBF5	IOCBF4	—	—	—	—	0000	0000
397h	IOCCP	X —		—	IOCCP5	IOCCP4	IOCCP3	IOCCP2	IOCCP1	IOCCP0	00 0000	00 0000
		— X	IOCCP7	IOCCP6	IOCCP5	IOCCP4	IOCCP3	IOCCP2	IOCCP1	IOCCP0	0000 0000	0000 0000
398h	IOCCN	X —	_	—	IOCCN5	IOCCN4	IOCCN3	IOCCN2	IOCCN1	IOCCN0	00 0000	00 0000
		— X	IOCCN7	IOCCN6	IOCCN5	IOCCN4	IOCCN3	IOCCN2	IOCCN1	IOCCN0	0000 0000	0000 0000
399h	IOCCF	X —	—	—	IOCCF5	IOCCF4	IOCCF3	IOCCF2	IOCCF1	IOCCF0	00 0000	00 0000
		— X	IOCCF7	IOCCF6	IOCCF5	IOCCF4	IOCCF3	IOCCF2	IOCCF1	IOCCF0	0000 0000	0000 0000

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

TABLE 4-4: SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)

								-,				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 7	Bank 7											
					CPU CORE RI	EGISTERS; see	Table 4-2 for spe	ecifics				
39Ah	CLKRCON		CLKREN	—	—	CLKRD	C<1:0>		CLKRDIV<2:0>		01 0000	01 0001
39Bh	—	—				Unimple	mented				—	-
39Ch	MDCON		MDEN		_	MDOPOL	MDOUT	_	_	MDBIT	00 00	00 00
39Dh	MDSRC		_		_	_	MDMS<3:0> xxxx 0 uu					
39Eh	MDCARH		_	MDCHPOL	MDCHSYNC	_		MDCH	1<3:0>		-xx- xxxx	-uu- uuuu
39Fh	MDCARL		—	MDCLPOL	MDCLSYNC	_	MDCL<3:0> -xx- xxxx -uu- uuuu					

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

TABLE 4	4-4: SPE	CIAL FL	JNCTION RE		UMMARY B	ANKS 0-31 (CONTINUE	D)			
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR

Bank 8

CPU CORE REGISTERS; see Table 4-2 for specifics

PIC16(L)F18326/18346

Value on

all other

Resets

10.01												
40Ch to 410h	-	—				Unimple	emented				-	-
411h	TMR3L					XXXX XXXX	uuuu uuuu					
412h	TMR3H					TMR3H	H<7:0>				XXXX XXXX	uuuu uuuu
413h	T3CON		TMR3CS	6<1:0>	T3CKF	PS<1:0>	T3SOSC	T3SYNC	—	TMR3ON	0000 00-0	uuuu uu-u
414h	T3GCON		TMR3GE	MR3GE T3GPOL T3GTM T3GSPM T3GGO/ DONE T3GVAL T3GSS<1:0>						0000 0x00	uuuu uxuu	
415h	TMR4					TMR4	<7:0>				0000 0000	0000 0000
416h	PR4					PR4<	<7:0>				1111 1111	1111 1111
417h	T4CON		_		T4OU	TPS<3:0>		TMR4ON	T4CKF	°S<1:0>	-000 0000	-000 0000
418h	TMR5L					TMR5I	_<7:0>				XXXX XXXX	uuuu uuuu
419h	TMR5H					TMR5H	H<7:0>				XXXX XXXX	uuuu uuuu
41Ah	T5CON		TMR5CS	S<1:0>	T5CKF	PS<1:0>	T5SOSC	T5SYNC	—	TMR5ON	0000 00-0	uuuu uu-u
41Bh	T5GCON		TMR5GE	T5GPOL	T5GTM	T5GSPM	T5GGO/ DONE	T5GVAL	T5GS	S<1:0>	00x0 0x00	uuuu uxuu
41Ch	TMR6			TMR6<7:0>								0000 0000
41Dh	PR6			PR6<7:0>								1111 1111
41Eh	T6CON									PS<1:0>	-000 0000	-000 0000
41Fh	—	_	Unimplemented								_	_

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

TABLE	ABLE 4-4: SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)											
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 9	Bank 9											
48Ch to												
497h						•						
498h	NCO1ACCL					NCO1A0	CC<7:0>				0000 0000	0000 0000
499h	NCO1ACCH					NCO1AC	C<15:8>				0000 0000	0000 0000
49Ah	NCO1ACCU		—	—	—	—		NCO1AC	C<19:16>		0000	0000
49Bh	NCO1INCL					NCO1IN	IC<7:0>				0000 0001	0000 0001
49Ch	NCO1INCH			NCO1INC<15:8> 0000 0000 0000 0000								
49Dh	NCO1INCU		_	_	_	0000 0000						
49Eh	NCO1CON		N1EN	_	N1OUT	N1POL	_	—	_	N1PFM	0-000	0-000
49Fh	NCO1CLK		1	N1PWS<2:0>	•	—	—	_	N1CK	S<1:0>	00000	00000

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Legend:

Note 1: Only on PIC16F18326/18346.

I	TABLE	4-4: SPE	CIAL FU	NCTION RE		UMMARY B	ANKS 0-31 (CONTINUE	D)		
	Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit

Bank 10-11

Dalik I	-11												
					CPU CORE RI	EGISTERS; see	Table 4-2 for spe	ecifics					
50Ch to 51Fh	_	—				Unimple	emented				-	—	
58Ch to 59Fh	_	—		Unimplemented									
Bank 12	Bank 12												
60Ch	_	—		Unimplemented									
60Dh		—		Unimplemented									
60Eh	_	—		Unimplemented									
60Fh	_	—				Unimple	emented				_	—	
610h	—	—		Unimplemented									
611h	_	—		Unimplemented									
612h	_	—		Unimplemented									
613h		—				Unimple	emented				_	—	
614h	_	—				Unimple	emented				_	—	
615h	_	—				Unimple	emented				_	_	
616h	_	—				Unimple	mented				_	_	
617h	PWM5DCL		PWM5DC	<1:0>	—	_	_	_	—	—	xx	uu	
618h	PWM5DCH					PWM5D)C<9:2>				XXXX XXXX	uuuu uuuu	
619h	PWM5CON		PWM5EN	—	PWM5OUT	PWM5POL	—	—	—	—	0-00	0-00	
61Ah	PWM6DCL		PWM6DC	PWM6DC<1:0>									
61Bh	PWM6DCH			PWM6DC<9:2> xxxx xxxx uuuu uuu									
61Ch	PWM6CON		PWM6EN	—	PWM6OUT	PWM6POL	—	—	—	—	0-00	0-00	
61Dh to 61Eh	_	—		Unimplemented — —									
61Fh	PWMTMRS		_	P6TSEL<1:0> P5TSEL<1:0> 0101 0101									
Lawards						te di un e di e e fot						•	

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

> Register accessible from both User and ICD Debugger. 2:

Value on

all other Resets

Value on: POR, BOR

Bit 0

TABLE	4-4: SPEC	IAL F	UNCTION RE	GISTER S	JMMARY B	ANKS 0-31 (CONTINUED	D)					
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets	
Bank 1	3												
	CPU CORE REGISTERS; see Table 4-2 for specifics												
68Ch	_	_				Unimple	mented				_	_	
68Dh	—	_		Unimplemented									
68Eh	—	_				Unimple	mented				_	_	
68Fh	—					Unimple	mented				—	_	
690h	—	_				Unimple	mented				—	—	
691h	CWG1CLKCON		—	_	—	—	—	_		CS	0	0	
692h	CWG1DAT		—	—	—	—		DAT	<3:0>		0000	0000	
693h	CWG1DBR		—	_			DBR<	<5:0>			00 0000	00 0000	
694h	CWG1DBF		—	_		•	DBF<	<5:0>			00 0000	00 0000	
695h	CWG1CON0		EN	LD		_	_		MODE<2:0>		00000	00000	
696h	CWG1CON1		—	_	IN		POLD	POLC	POLB	POLA	x- 0000	x- 0000	
697h	CWG1AS0		SHUTDOWN	_	0001 01	0001 01							
698h	CWG1AS1		_	—	—	AS4E	AS0E	0 0000	0 0000				
699h	CWG1STR		OVRD	OVRC	OVRB	OVRA	STRD	STRC	STRB	STRA	0000 0000	0000 0000	
69Ah to 69Fh	-	_		Unimplemented									

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Legend:

Only on PIC16F18326/18346. Note 1:

IADLE	4-4. OI LO						CONTINUEL)					
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets	
Bank 1	4												
	-				CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics					
70Ch	—	—				_	_						
70Dh	—	_				Unimple	mented				_	_	
70Eh	—	—				Unimple	mented				_	_	
70Fh	—	—				Unimple	mented				—	-	
710h	—	_				Unimple	mented				_	_	
711h	CWG2CLKCON			_	—	_	_	—	—	CS	0	(
712h	CWG2DAT		_	—	—	—		DAT	<3:0>		0000	000	
713h	CWG2DBR		_	—			DBR	<5:0>			00 0000	00 0000	
714h	CWG2DBF			—			DBF<	<5:0>			00 0000	00 000	
715h	CWG2CON0		EN	LD	—	—	—		MODE<2:0>		00000	0000	
716h	CWG2CON1			-	IN	_	POLD	POLC	POLB	POLA	x- 0000	x- 000	
717h	CWG2AS0		SHUTDOWN	REN	LSBE		0001 01	0001 01-					
718h	CWG2AS1			_	—	AS4E	AS3E	AS2E	AS1E	AS0E	0 0000	0 0000	
719h	CWG2STR		OVRD	OVRC	OVRB	STRA	0000 0000	0000 0000					
71Ah to 71Fh	_	—		Unimplemented — —									

PIC16(L)F18326/18346

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

TABLE	4-4: SPE	CIAL F	UNCTION R	EGISTER SI	UMMARY B	BANKS 0-31 (CONTINUE	D)					
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets	
Banks	15-16												
							Table 4.0 fee and	alfina					
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics					
78Ch to 79FH	_	-		Unimplemented									
80Ch to 81Fh	_	-				Unimple	mented				_	_	
Bank 1	7												
88Ch	—	—				Unimple	emented				—	_	
88Dh	—	—				Unimple	emented				—	—	
88Eh	—	—				Unimple	mented				—	—	
88Fh						Unimple	mented				_	—	
890h	_	—				Unimple	mented					_	
891h	NVMADRL			_		NVMAD	R<7:0>				0000 0000	0000 000	
892h	NVMADRH		_				NVMADR<14:8	>			1000 0000	1000 0000	
893h	NVMDATL					NVMDA	\T<7:0>				0000 0000	0000 000	
894h	NVMDATH		_				NVMDA	T<13:8>			00 0000	00 0000	
895h	NVMCON1		—	NVMREGS	LWLO	FREE	WRERR	WREN	WR	RD	-000 x000	-000 q000	
896h	NVMCON2					NVM	CON2				0000 0000	0000 0000	
897h	_	—				Unimple	emented				_	—	
898h	—	—	Unimplemented										
899h	—	—	Unimplemented										
89Ah	—	—		—	—								
89Bh	PCON0		STKOVF	STKUNF	_	RWDT	RMCLR	RI	POR	BOR	00-1 110q	qq-q qqu	
89Ch to 89Fh	-	-		Unimplemented									

x = unknown, u = unchanged, g = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346.

Legend: Note 1:

2:

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7 Bit 6 Bit 5 Bit 4 Bit 3 Bit 2 Bit 1 Bit 0								Value on: POR, BOR	Value on all other Resets
Bank 1	8											
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
90Ch	—	_		Unimplemented								
90Dh	—	_				Unimple	mented				_	_
90Eh	_	—				Unimple	mented				—	_
90Fh	_					Unimple	emented				—	
910h	_	—				Unimple	mented				—	-
911h	PMD0		SYSCMD	FVRMD	_	_	_	NVMMD	CLKRMD	IOCMD	00000	0000
912h	PMD1		NCOMD	TMR6MD	TMR5MD	TMR4MD	TMR3MD	TMR2MD	TMR1MD	TMR0MD	0000	000
913h	PMD2		_	DACMD	ADCMD	_	—	CMP2MD	CMP1MD	—	-000-	-000
914h	PMD3		CWG2MD	CWG1MD	PWM6MD	PWM5MD	CCP4MD	CCP3MD	CCP2MD	CCP1MD	-00000	-0000
915h	PMD4		_	_	UART1MD	_		MSSP2MD	MSSP1MD	—	00-	00
916h	PMD5		_	_	_	CLC4MD	CLC3MD	CLC2MD	CLC1MD	DSMMD	000	00
917h	—					Unimple	mented				—	
918h	CPUDOZE		IDLEN	DOZEN	ROI	DOE	_		DOZE<2:0>		000000	00000
919h	OSCCON1				NOSC<2:0>			NDIV	<3:0>		-qqq 0000	-qqq 000
91Ah	OSCCON2		_		COSC<2:0>			CDIV	<3:0>		-qqq 0000	-qqq 000
91Bh	OSCCON3		CSWHOLD	SOSCPWR	SOSCBE	ORDY	NOSCR	—		—	0000 0	0000 0
91Ch	OSCSTAT1		EXTOR	HFOR	—	LFOR	SOR	ADOR	—	PLLR	qq-q qq-q	dd-d dd-
91Dh	OSCEN		EXTOEN	HFOEN	—	LFOEN	SOSCEN	ADOEN		_	00-0 00	00-0 00-
91Eh	OSCTUNE		_	_			10 0000	10 000				
91Fh	OSCFRQ		—	—	—	—		HFFR	Q<3:0>		qqq	qq

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

Note 1:

TABLE 4	4-4:	SPE	CIAL FU	NCTION RE	EGISTER S	UMMARY B	ANKS 0-31 (CONTINUE	D)					
Address		Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets	
Banks 1	19-27													
						CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics					
98Ch to 9EFh			-				Unimple	mented				_	_	
A0Ch to A6Fh	_		_		Unimplemented									
A8Ch to AEFh	_		_				Unimple	emented				_	_	
B0Ch to B6Fh			—				Unimple	emented				_	_	
B8Ch to BEFh	_		_				Unimple	emented				_	_	
C0Ch to C6Fh	_		_				Unimple	emented				_	—	
C8Ch to CEFh	_		—		Unimplemented									
D0Ch to D6Fh	_		—		Unimplemented — –									
D8Ch to DEFh	_		—				Unimple	mented				_	—	

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

Note 1:

TABLE 4-4:	SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)
------------	--

IADLL	+ + . 01 L						CONTINUEL	5)							
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets			
Bank 28	}														
					CPU CORE R	EGISTERS; see	Table 4-2 for sp	ecifics							
E0Ch	_	_				Unimple	emented				—	—			
E0Dh	_	-				Unimple	emented				_				
E0Eh	_	_			Unimplemented — —										
E0Fh	PPSLOCK		—	—	—	—	—	—	—	PPSLOCKED	0	0			
E10h	INTPPS		—	_	—			INTPPS<4:0>			0 0010	u uuuu			
E11h	TOCKIPPS		—	_	—			T0CKIPPS<4:0>			0 0010	u uuuu			
E12h	T1CKIPPS		—	_	—			T1CKIPPS<4:0>			0 0101	u uuuu			
E13h	T1GPPS		—	—	—				0 0100	u uuuu					
E14h	CCP1PPS		—	_	—				1 0011	u uuuu					
E15h	CCP2PPS		—	_	—				1 0101	u uuuu					
E16h	CCP3PPS		—	_	—				0 0010	u uuuu					
E17h	CCP4PPS	X —	—	—	—			CCP4PPS<4:0>			1 0001	u uuuu			
		— X	—	_	—			CCP4PPS<4:0>			0 0100	u uuuu			
E18h	CWG1PPS		—	—	—			CWG1PPS<4:0>			0 0010	u uuuu			
E19h	CWG2PPS		—	—	—			CWG2PPS<4:0>			0 0010	u uuuu			
E1Ah	MDCIN1PPS		—	—	—		N	IDCIN1PPS<4:0	>		1 0010	u uuuu			
E1Bh	MDCIN2PPS		_	_	_		N	IDCIN2PPS<4:0	>		1 0101	u uuuu			
E1Ch	MDMINPPS		_	—	—		Ν	MDMINPPS<4:0>			1 0011	u uuuu			
E1Dh	SSP2CLKPPS	Х —	_	—	—		S	SP2CLKPPS<4:0	>		1 0100	u uuuu			
		— X	_	_	_		S	SP2CLKPPS<4:0	>		0 1111	u uuuu			
E1Eh	SSP2DATPPS	X —	—	—	-	SSP2DATPPS<4:0>1 0101u uuuu									
		— X	—	_	_		S	SP2DATPPS<4:0	>		0 1101	u uuuu			
E1Fh	SSP2SSPPS	X —	—	—	—			SP2SSPPS<4:0			0 0000	u uuuu			
		— X	—	_	_										
E20h	SSP1CLKPPS	Х —	_	—	_	── SSP1CLKPPS<4:0>1 0000u uuuu									
		— X	—	—	—										

PIC16(L)F18326/18346

 ${\scriptstyle \circledcirc}$ 2016-2022 Microchip Technology Inc. and its subsidiaries

Legend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value or all other Resets			
Bank 28															
					CPU CORE R	EGISTERS; see	Table 4-2 for sp	ecifics							
E21h SSF	P1DATPPS	X —	—	—	_		S	SP1DATPPS<4:(>		1 0001	u uuu			
		— X	—	_	-		S	SP1DATPPS<4:(>		0 1100	u uuu			
E22h SSF	P1SSPPS	X —	—	—	_		S	SSP1SSPPS<4:0	>		1 0011	u uuu			
		— X	—	_	-		S	SSP1SSPPS<4:0	>		1 0100	u uu			
E23h —		—				Unimple	emented				—	_			
E24h RXF	PPS	X —	—	—	_			RXPPS<4:0>			1 0101	u uu			
		— X	—	—			RXPPS<4:0>								
E25h TXP	PPS	X —	—	-				TXPPS<4:0>			1 0100	u uu			
		— X	_	—	_		TXPPS<4:0>								
E26h —		—				Unimple	Unimplemented								
E27h —		—				Unimple	emented				_	_			
E28h CLC	IN0PPS	X —	_				(CLCIN0PPS<4:0>	`		1 0011	u uu			
		— X	_	—	_		(CLCIN0PPS<4:0>	•		0 0010	u uu			
E29h CLC	IN1PPS	X —	_	_			(CLCIN1PPS<4:0>	`		0 0100	u uu			
		— X	—	—	—		(CLCIN1PPS<4:0>	`		1 0011	u uu			
E2Ah CLC	IN2PPS	X —	_	_			(CLCIN2PPS<4:0>	`		1 0001	u uu			
		— X	—	_	_			CLCIN2PPS<4:0>			0 1100	u uu			
E2Bh CLC	CIN3PPS	X —	_	—	_		(CLCIN3PPS<4:0>	>		0 0101	u uu			
		— X	_	—	_			CLCIN3PPS<4:0>	>		0 1101	u uu			
E2Ch T3C	KIPPS	X —	_	—	_	T3CKIPPS<4:0> T3CKIPPS<4:0>						u uu			
		— X	-	-	—				0 0101	u uu					
E2Dh T3G	SPPS	X —	_	—	_		1 0001	u uu							
		— X	—	—	—			T3GPPS<4:0>			1 0100	u uu			
E2Eh T5C	KIPPS	X —	-	—	_			T5CKIPPS<4:0>			1 0001	u uu			
		— X	_	—	_			T5CKIPPS<4:0>			0 0101	u uu u uu			
E2Fh T5G	PPS	X —	_	_	_		T5GPPS<4:0>								

T5GPPS<4:0>

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

_

Note 1:

Register accessible from both User and ICD Debugger. 2:

Х

PIC16(L)F18326/18346

---1 0100 ---u uuuu

Address	Name	PIC16(L)F18326	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 29	9											
					CPU CORE R	EGISTERS; see	Table 4-2 for spo	ecifics				
E8Dh	—	_		Unimplemented							_	_
E8Eh	—	_				Unimple	mented				_	_
E8Fh	—	_				Unimple	mented				_	_
E90h	RA0PPS		—	—	—		RA0PPS<4:0>					u uuuu
E91h	RA1PPS		_	—	—			RA1PPS<4:0>			0 0000	u uuuu
E92h	RA2PPS		_	—	—		RA2PPS<4:0>				0 0000	u uuuu
E93h	—	_				Unimplemented					_	—
E94h	RA4PPS		—	—	—			RA4PPS<4:0>			0 0000	u uuuu
E95h	RA5PPS		_	—	—			RA5PPS<4:0>			0 0000	u uuuu
E96h	—	_				Unimple	mented				_	—
E97h	—	-				Unimple	mented				-	—
E98h	—	_				Unimple	mented				_	—
E99h	—	—				Unimple	emented				_	_
E9Ah	—	—				Unimple	emented				—	—
E9Bh	—	—				Unimple	emented				_	—
E9Ch	RB4PPS	X –	-		_	Unimple	emented				_	—
		— X	_		_			RB4PPS<4:0>			0 0000	u uuuu
E9Dh	RB5PPS	Х –	-			Unimple	mented				-	—
		— X	_	—	_			RB5PPS<4:0>			0 0000	u uuuu
E9Eh	RB6PPS	Х –	-			Unimple	mented				-	—
		— X	_	_	_			RB6PPS<4:0>			0 0000	u uuuu
E9Fh	RB7PPS	Х –	-			Unimple	mented				_	_
		— X	_	_	—			RB7PPS<4:0>			0 0000	u uuuu

gend: x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'.

Note 1: Only on PIC16F18326/18346.

Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 2	9											
					CPU CORE RI	EGISTERS; see	Table 4-2 for spe	ecifics				
	1											
EA0h	RCOPPS		—	—	—			RC0PPS<4:0>			0 0000	u uuuu
EA1h	RC1PPS		—	—	—			RC1PPS<4:0>			0 0000	u uuuu
EA2h	RC2PPS		—	—	—			RC2PPS<4:0>			0 0000	u uuuu
EA3h	RC3PPS		_	—	_			RC3PPS<4:0>			0 0000	u uuuu
EA4h	RC4PPS		_	_	_			RC4PPS<4:0>			0 0000	u uuuu
EA5h	RC5PPS		_	_	_			RC5PPS<4:0>			0 0000	u uuuu
											—	—
EA6h	KCOFF3											
EA6h	NCOFF 3	— X	_	—	—			RC6PPS<4:0>			0 0000	u uuuu
EA6h EA7h	RC7PPS	— X X —	_	—	—	Unimple		RC6PPS<4:0>			0 0000	u uuuu

PIC16(L)F18326/18346

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Legend:

Only on PIC16F18326/18346. Note 1:

TABLE 4-4:	SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)
------------	--

Address		PIC16(L)F18326		Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 3	0											
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
F0Ch	_	_		Unimplemented						_	_	
F0Dh	_	_				Unimple	mented				_	
F0Eh	_	_				Unimple	mented				_	
F0Fh	CLCDATA		_	_	_	_	MLC4OUT	MLC3OUT	MLC2OUT	MLC1OUT	0000	00
F10h	CLC1CON		LC1EN	—	LC10UT	LC1INTP	LC1INTN		LC1MODE<2:0>	>	0-00 0000	0-00 00
F11h	CLC1POL		LC1POL	—	—	—	LC1G4POL	LC1G3POL	LC1G2POL	LC1G1POL	0 xxxx	0 uu
F12h	CLC1SEL0		_	—			LC1D1	S<5:0>			xx xxxx	uu uu
F13h	CLC1SEL1			—			LC1D2	S<5:0>			xx xxxx	uu uu
F14h	CLC1SEL2			—			LC1D3	S<5:0>			xx xxxx	uu uu
F15h	CLC1SEL3			—			LC1D4	S<5:0>			xx xxxx	uu uu
F16h	CLC1GLS0		LC1G1D4T	LC1G1D4N	LC1G1D3T	LC1G1D3N	LC1G1D2T	LC1G1D2N	LC1G1D1T	LC1G1D1N	****	uuuu uu
F17h	CLC1GLS1		LC1G2D4T	LC1G2D4N	LC1G2D3T	LC1G2D3N	LC1G2D2T	LC1G2D2N	LC1G2D1T	LC1G2D1N	XXXX XXXX	uuuu uu
F18h	CLC1GLS2		LC1G3D4T	LC1G3D4N	LC1G3D3T	LC1G3D3N	LC1G3D2T	LC1G3D2N	LC1G3D1T	LC1G3D1N	XXXX XXXX	uuuu uu
F19h	CLC1GLS3		LC1G4D4T	LC1G4D4N	LC1G4D3T	LC1G4D3N	LC1G4D2T	LC1G4D2N	LC1G4D1T	LC1G4D1N	XXXX XXXX	uuuu uu
F1Ah	CLC2CON		LC2EN	—	LC2OUT	LC2INTP	LC2INTN		LC2MODE<2:0>	>	0-00 0000	0-00 00
F1Bh	CLC2POL		LC2POL	_	—	_	LC2G4POL	LC2G3POL	LC2G2POL	LC2G1POL	0 xxxx	0 uu
F1Ch	CLC2SEL0		—	—			LC2D1	S<5:0>			xx xxxx	uu uu
F1Dh	CLC2SEL1		—	—			LC2D2	S<5:0>			xx xxxx	uu uu

LC2D3S<5:0>

LC2D4S<5:0>

PIC16(L)F18326/18346

--xx xxxx

--xx xxxx

--uu uuuu

--uu uuuu

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

_

_

Note 1:

CLC2SEL2

CLC2SEL3

2: Register accessible from both User and ICD Debugger.

_

TABLE	4-4: SPEC	CIAL F	UNCTION RE	GISTER SU	JMMARY B	ANKS 0-31 (CONTINUE	D)				
Address	Name	PIC16(L)F18326 PIC16(L)F18346	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 3	0											
					CPU CORE R	EGISTERS; see	Table 4-2 for spe	ecifics				
F20h	CLC2GLS0		LC2G1D4T	LC2G1D4N	LC2G1D3T	LC2G1D3N	LC2G1D2T	LC2G1D2N	LC2G1D1T	LC2G1D1N	XXXX XXXX	uuuu uuuu
F21h	CLC2GLS1		LC2G2D4T	LC2G2D4N	LC2G2D3T	LC2G2D3N	LC2G2D2T	LC2G2D2N	LC2G2D1T	LC2G2D1N	XXXX XXXX	uuuu uuuu
F22h	CLC2GLS2		LC2G3D4T	LC2G3D4N	LC2G3D3T	LC2G3D3N	LC2G3D2T	LC2G3D2N	LC2G3D1T	LC2G3D1N	XXXX XXXX	uuuu uuuu
F23h	CLC2GLS3		LC2G4D4T	LC2G4D4N	LC2G4D3T	LC2G4D3N	LC2G4D2T	LC2G4D2N	LC2G4D1T	LC2G4D1N	XXXX XXXX	uuuu uuuu
F24h	CLC3CON		LC3EN	—	LC3OUT	LC3OUT LC3INTP LC3INTN LC3MODE<2:0>					0-00 0000	0-00 0000
F25h	CLC3POL		LC3POL	—		_	LC3G4POL	LC3G3POL	LC3G2POL	LC3G1POL	0 xxxx	0 uuuu
F26h	CLC3SEL0		_	—		LC3D1S<5:0>					xx xxxx	uu uuuu
F27h	CLC3SEL1		_	_			LC3D2	S<5:0>			xx xxxx	uu uuuu
F28h	CLC3SEL2		_	—			LC3D3	S<5:0>			xx xxxx	uu uuuu
F29h	CLC3SEL3		_	_			LC3D4	S<5:0>			xx xxxx	uu uuuu
F2Ah	CLC3GLS0		LC3G1D4T	LC3G1D4N	LC3G1D3T	LC3G1D3N	LC3G1D2T	LC3G1D2N	LC3G1D1T	LC3G1D1N	**** ****	uuuu uuuu
F2Bh	CLC3GLS1		LC3G2D4T	LC3G2D4N	LC3G2D3T	LC3G2D3N	LC3G2D2T	LC3G2D2N	LC3G2D1T	LC3G2D1N	XXXX XXXX	uuuu uuuu
F2Ch	CLC3GLS2		LC3G3D4T	LC3G3D4N	LC3G3D3T	LC3G3D3N	LC3G3D2T	LC3G3D2N	LC3G3D1T	LC3G3D1N	**** ****	uuuu uuuu
F2Dh	CLC3GLS3		LC3G4D4T	LC3G4D4N	LC3G4D3T	LC3G4D3N	LC3G4D2T	LC3G4D2N	LC3G4D1T	LC3G4D1N	**** ****	uuuu uuuu
F2Eh	CLC4CON		LC4EN	_	LC4OUT	LC4INTP	LC4INTN		LC4MODE<2:0>	•	0-00 0000	0-00 0000
F2Fh	CLC4POL		LC4POL	_		_	LC4G4POL	LC4G3POL	LC4G2POL	LC4G1POL	0 xxxx	0 uuuu
F30h	CLC4SEL0			_			LC4D1	S<5:0>			xx xxxx	uu uuuu
F31h	CLC4SEL1		_	_			LC4D2	S<5:0>			xx xxxx	uu uuuu
F32h	CLC4SEL2		_	_			LC4D3	S<5:0>			xx xxxx	uu uuuu
F33h	CLC4SEL3		_	_			LC4D4	S<5:0>			xx xxxx	uu uuuu
F34h	CLC4GLS0		LC4G1D4T	LC4G1D4N	LC4G1D3T	LC4G1D3N	LC4G1D2T	LC4G1D2N	LC4G1D1T	LC4G1D1N	XXXX XXXX	uuuu uuuu
F35h	CLC4GLS1		LC4G2D4T	LC4G2D4N	LC4G2D3T	LC4G2D3N	LC4G2D2T	LC4G2D2N	LC4G2D1T	LC4G2D1N	XXXX XXXX	uuuu uuuu
F36h	CLC4GLS2		LC4G3D4T	LC4G3D4N	LC4G3D3T	LC4G3D3N	LC4G3D2T	LC4G3D2N	LC4G3D1T	LC4G3D1N	XXXX XXXX	uuuu uuuu
F37h	CLC4GLS3		LC4G4D4T	LC4G4D4N	LC4G4D3T	LC4G4D3N	LC4G4D2T	LC4G4D2N	LC4G4D1T	LC4G4D1N	XXXX XXXX	uuuu uuuu

x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

Note 1:

1	TABLE 4	1-4:	SPECIAL FUNCTION REGISTER SUMMARY BANKS 0-31 (CONTINUED)								
			5	346							

Name	<u>PIC16(L)F183</u> PIC16(L)F183	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Value on: POR, BOR	Value on all other Resets
Bank 31 — only accessible from Debug Executive, unless otherwise specified											
CPU CORE REGISTERS; see Table 4-2 for specifics											
_			Unimplemented —					—	—		
STATUS_SHAD		_	_	—	—	—	Z	DC	С	xxx	uuu
WREG_SHAD				Worki	ing Register Norn	nal (Non-ICD) Sh	adow			XXXX XXXX	uuuu uuuu
BSR_SHAD		—	_	_		Bank Select Reg	ister Normal (No	on-ICD) Shadow		x xxxx	u uuuu
PCLATH_SHAD		—		Progra	am Counter Latch	High Register No	ormal (Non-ICD)	Shadow		-xxx xxxx	-uuu uuuu
FSR0L_SHAD			Indi	rect Data Memo	ory Address 0 Lov	v Pointer Normal	(Non-ICD) Shad	ow		XXXX XXXX	uuuu uuuu
FSR0H_SHAD			Indi	rect Data Memo	ory Address 0 Higl	h Pointer Normal	(Non-ICD) Shad	ow		XXXX XXXX	uuuu uuuu
FSR1L_SHAD			Indi	rect Data Memo	ory Address 1 Lov	v Pointer Normal	(Non-ICD) Shad	ow		XXXX XXXX	uuuu uuuu
FSR1H_SHAD			Indi	rect Data Memo	ory Address 1 Higl	h Pointer Normal	(Non-ICD) Shad	ow		XXXX XXXX	uuuu uuuu
_	—				Unimple	mented				—	—
STKPTR		_	_	_		Cu	rrent Stack point	ter		x xxxx	1 1111
TOSL					Top of Stac	k Low byte				XXXX XXXX	XXXX XXXX
TOSH		_			To	p of Stack High b	oyte			-xxx xxxx	-xxx xxxx
			Image: matrix of the secure of the secur	Image: marked bit is a construct of the security of the secu	Image: Simple from Debug Executive, unless otherwise specified CPU CORE R STATUS_SHAD Image: Simple from Debug Executive, unless otherwise specified STATUS_SHAD Image: Debug Executive, unless otherwise specified VREG_SHAD Image: Debug Executive, unless otherwise specified VREG_SHAD Image: Debug Executive, unless otherwise specified STKPT Image: Debug Executive, unless otherwise specified STKPTR Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified STKPTR Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified FSR0L_SHAD Image: Debug Executive, unless otherwise specified Image: Debug Executive, unless otherwise specified FSR1L_SHAD	only accessible from Debug Executive, unless otherwise specified only accessible from Debug Executive, unless otherwise specified CPU CORE REGISTERS; see STATUS_SHAD WREG_SHAD BSR_SHAD PCLATH_SHAD PCLATH_SHAD FSROL_SHAD Indirect Data Memory Address 0 Low FSROH_SHAD Indirect Data Memory Address 1 Low FSR1L_SHAD Indirect Data Memory Address 1 Low FSR1H_SHAD Indirect Data Memory Address 1 Low FSR1H_SHAD TOP of Stace	Image: model of the matrix	- only accessible from Debug Executive, unless otherwise specified only accessible from Debug Executive, unless otherwise specified CPU CORE REGISTERS; see Table 4-2 for specifics only accessible from Debug Executive, unless otherwise specified CPU CORE REGISTERS; see Table 4-2 for specifics STATUS_SHAD onloceton STATUS_SHAD onloceton WREG_SHAD onloceton BSR_SHAD onloceton PCLATH_SHAD onloceton STROL_SHAD onloceton FSROL_SHAD onloceton STROL_SHAD onloceton Indirect Data Memory Address 0 Low Pointer Normal (Non-ICD) Shad FSR1L_SHAD onloceton Indirect Data Memory Address 1 Low Pointer Normal (Non-ICD) Shad FSR1H_SHAD onloceton Onlinect Data Memory Address 1 Low Pointer Normal (Non-ICD) Shad Indirect	Image: Status_Shap Image: S	Image: Second secon	Image: model of the model


x = unknown, u = unchanged, q = depends on condition, - = unimplemented, read as '0', r = reserved. Shaded locations unimplemented, read as '0'. Only on PIC16F18326/18346. Legend:

Note 1:

4.3 PCL and PCLATH

The Program Counter (PC) is 15 bits wide. The low byte comes from the PCL register, which is a readable and writable register. The high byte (PC<14:8>) is not directly readable or writable and comes from PCLATH. On any Reset, the PC is cleared. Figure 4-3 shows the five situations for the loading of the PC.

FIGURE 4-3: LOADING OF PC IN DIFFERENT SITUATIONS



4.3.1 MODIFYING PCL

Executing any instruction with the PCL register as the destination simultaneously causes the Program Counter PC<14:8> bits (PCH) to be replaced by the contents of the PCLATH register. This allows the entire contents of the program counter to be changed by writing the desired upper seven bits to the PCLATH register. When the lower eight bits are written to the PCL register, all 15 bits of the program counter will change to the values contained in the PCLATH register.

4.3.2 COMPUTED GOTO

A computed GOTO is accomplished by adding an offset to the program counter (ADDWF PCL). When performing a table read using a computed GOTO method, care must be exercised if the table location crosses a PCL memory boundary (each 256-byte block). Refer to Application Note AN556, *Implementing a Table Read* (DS00556).

4.3.3 COMPUTED FUNCTION CALLS

A computed function CALL allows programs to maintain tables of functions and provide another way to execute state machines or look-up tables. When performing a table read using a computed function CALL, care must be exercised if the table location crosses a PCL memory boundary (each 256-byte block).

If using the CALL instruction, the PCH<2:0> and PCL registers are loaded with the operand of the CALL instruction. PCH<6:3> is loaded with PCLATH<6:3>.

The CALLW instruction enables computed calls by combining PCLATH and \overline{W} to form the destination address. A computed CALLW is accomplished by loading the \overline{W} register with the desired address and executing CALLW. The PCL register is loaded with the value of \overline{W} and PCH is loaded with PCLATH.

4.3.4 BRANCHING

The branching instructions add an offset to the PC. This allows relocatable code and code that crosses page boundaries. There are two forms of branching, BRW and BRA. The PC will have incremented to fetch the next instruction in both cases. When using either branching instruction, a PCL memory boundary may be crossed.

If using BRW, load the \overline{W} register with the desired unsigned address and execute BRW. The entire PC will be loaded with the address PC + 1 + \overline{W} .

If using BRA, the entire PC will be loaded with PC + 1 + the signed value of the operand of the BRA instruction.

4.4 Stack

All devices have a 16-level x 15-bit wide hardware stack (refer to Figure 4-4 through Figure 4-7). The stack space is not part of either program or data space. The PC is PUSHed onto the stack when CALL or CALLW instructions are executed or an interrupt causes a branch. The stack is POPed in the event of a RETURN, RETLW or a RETFIE instruction execution. PCLATH is not affected by a PUSH or POP operation.

The stack operates as a circular buffer and does not cause a Reset when either a Stack Overflow or Underflow occur if the STVREN bit is programmed to '0' (Configuration Words). This means that after the stack has been PUSHed sixteen times, the seventeenth PUSH overwrites the value that was stored from the first PUSH. The eighteenth PUSH overwrites the second PUSH (and so on). The STKOVF and STKUNF flag bits will be set on an Overflow/Underflow, regardless of whether the Reset is enabled.

If the STVREN bit in Configuration Words is programmed to '1', the device will be Reset if the stack is PUSHed beyond the sixteenth level or POPed beyond the first level, setting the appropriate bits (STKOVF or STKUNF, respectively) in the PCON register.

Note 1:	There are no instructions/mnemonics
	called PUSH or POP. These are actions
	that occur from the execution of the
	CALL, CALLW, RETURN, RETLW and
	RETFIE instructions or the vectoring to
	an interrupt address.

4.4.1 ACCESSING THE STACK

The stack is accessible through the TOSH, TOSL and STKPTR registers. STKPTR is the current value of the Stack Pointer. TOSH:TOSL register pair points to the TOP of the stack. Both registers are read/writable. TOS is split into TOSH and TOSL due to the 15-bit size of the PC. To access the stack, adjust the value of STKPTR, which will position TOSH:TOSL, then read/write to TOSH:TOSL. STKPTR is five bits to allow detection of Overflow and Underflow.

Note:	Care must be taken when modifying the
	STKPTR while interrupts are enabled.

During normal program operation, CALL, CALLW and Interrupts will increment STKPTR while RETLW, RETURN, and RETFIE will decrement STKPTR. At any time, STKPTR can be read to see how much stack is left. The STKPTR always points at the currently used place on the stack. Therefore, a CALL or CALLW will increment the STKPTR and then write the PC, and a return will unload the PC and then decrement the STKPTR.

Reference Figure 4-4 through Figure 4-7 for examples of accessing the stack.


FIGURE 4-4: ACCESSING THE STACK EXAMPLE 1

	STKPTR = 0x1F Stack Reset Disabled (STVREN = 0)
[∨] 0x0E	
0x0D	
0x0C	
0x0B	
Axoa	
0x09	Initial Stack Configuration:
0x08	After Reset, the stack is empty. The empty stack is initialized so the Stack
0x07	Pointer is pointing at 0x1F. If the Stack Overflow/Underflow Reset is enabled, the
0x06	TOSH/TOSL registers will return '0'. If the Stack Overflow/Underflow Reset is
0x05	disabled, the TOSH/TOSL registers will
0x04	— return the contents of stack address 0x0F.
0x03	
0x02	
0x01	
0x00	
TOSH:TOSL 0x1F 0x0000	STKPTR = 0x1F Stack Reset Enabled (STVREN = 1)

PIC16(L)F18326/18346

JRE 4-5: ACC	CESSING TH	E STA		2
				_
		0x0F		
		0x0E		
		0x0D		
		0x0C		
		0x0B		
		0x0A		
		0x09		This figure shows the stack configuration
		0x08		after the first CALL or a single interrupt. If a RETURN instruction is executed, the
		0x07		return address will be placed in the Program Counter and the Stack Pointer
		0x06		decremented to the empty state (0x1F).
		0x05		
		0x04		
		0x03		
		0x02		-
	4	0x01		
TOSH:TOSL		0x00	Return Address	STKPTR = 0x00
	CESSING TH	E STA		3
	CESSING TH	ſ		3
	CESSING TH	0x0F	CK EXAMPLE	3
		0x0F 0x0E	CK EXAMPLE	3 3
		0x0F 0x0E 0x0D		3 3
		0x0F 0x0E 0x0D 0x0D	ACK EXAMPLE	After seven CALLS or six CALLS and an
		0x0F 0x0E 0x0D 0x0D 0x0C 0x0B	CK EXAMPLE	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions
		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A		After seven CALLS or six CALLS and an interrupt, the stack looks like the figure
		0x0F 0x0E 0x0D 0x0C 0x0C 0x0B 0x0A 0x09		After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses
		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x09 0x08		After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x0A 0x09 0x08 0x07		After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.
		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x09 0x08 0x07 0x06	Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x0A 0x09 0x08 0x07 0x06 0x05	Return Address Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x09 0x08 0x07 0x06	Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x09 0x08 0x07 0x06 0x05 0x04	Return Address Return Address Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x04 0x03 0x05 0x04 0x03	Return Address Return Address Return Address Return Address Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.
JRE 4-6: ACC		0x0F 0x0E 0x0D 0x0C 0x0B 0x0A 0x09 0x08 0x07 0x06 0x05 0x04 0x03 0x02	Return Address Return Address Return Address Return Address Return Address Return Address	After seven CALLS or six CALLS and an interrupt, the stack looks like the figure on the left. A series of RETURN instructions will repeatedly place the return addresses into the Program Counter and pop the stack.

PIC16(L)F18326/18346




4.5 Indirect Addressing

The INDFn registers are not physical registers. Any instruction that accesses an INDFn register actually accesses the register at the address specified by the File Select Registers (FSR). If the FSRn address specifies one of the two INDFn registers, the read will return '0' and the write will not occur (though Status bits may be affected). The FSRn register value is created by the pair FSRnH and FSRnL.

The FSR registers form a 16-bit address that allows an addressing space with 65536 locations. These locations are divided into four memory regions:


- · Traditional/Banked Data Memory
- Linear Data Memory
- Program Flash Memory
- EEPROM

INDIRECT ADDRESSING PIC16(L)F18326/18346



4.5.1 TRADITIONAL/BANKED DATA MEMORY

The traditional data memory is a region from FSR address 0x000 to FSR address 0xFFF. The addresses correspond to the absolute addresses of all SFR, GPR and common registers.




4.5.2 LINEAR DATA MEMORY

The linear data memory is the region from FSR address 0x2000 to FSR address 0x29AF. This region is a virtual region that points back to the 80-byte blocks of GPR memory in all the banks.

Unimplemented memory reads as 0x00. Use of the linear data memory region allows buffers to be larger than 80 bytes because incrementing the FSR beyond one bank will go directly to the GPR memory of the next bank.

The 16 bytes of common memory are not included in the linear data memory region.

FIGURE 4-10: LINEAR DATA MEMORY MAP




4.5.3 DATA EEPROM MEMORY

The EEPROM memory can be read or written through the NVMCON register interface (see Section 11.2 "Data EEPROM"). However, to make access to the EEPROM easier, read-only access to the EEPROM contents are also available through indirect addressing via an FSR. When the MSP of the FSR (ex: FSRxH) is set to 0x70, the lower 8-bit address value (in FSRxL) determines the EEPROM location that may be read via the INDF register). In other words, the EEPROM address range 0x00-0xFF is mapped into the FSR address space between 0x7000 and 0x70FF. Writing to the EEPROM cannot be accomplished via the FSR/INDF interface. Reads from the EEPROM through the FSR/INDF interface will require one additional instruction cycle to complete.

4.5.4 PROGRAM FLASH MEMORY

To make constant data access easier, the entire Program Flash Memory is mapped to the upper half of the FSR address space. When the MSB of FSRnH is set, the lower 15 bits are the address in program memory which will be accessed through INDF. Only the lower eight bits of each memory location are accessible via INDF. Writing to the Program Flash Memory cannot be accomplished via the FSR/INDF interface. All instructions that access Program Flash Memory via the FSR/INDF interface will require one additional instruction cycle to complete.

FIGURE 4-11: PROGRAM FLASH MEMORY MAP



5.0 DEVICE CONFIGURATION

Device configuration consists of Configuration Words, Code Protection and Device ID.

5.1 Configuration Words

There are several Configuration Word bits that allow different oscillator and memory protection options. These are implemented as Configuration Word 1 at 8007h, Configuration Word 2 at 8008h, Configuration Word 3 at 8009h, and Configuration Word 4 at 800Ah.

Note:	The DEBUG bit in Configuration Words is
	managed automatically by device
	development tools including debuggers
	and programmers. For normal device
	operation, this bit must be maintained as a
	'1'.

5.2 Register Definitions: Configuration Words

	R 5-1: CONF			SCILLATOR		11.4	D/D 4
		R/P-1	U-1	R/P-1	U-1	U-1	R/P-1
		FCMEN	—	CSWEN	—	—	CLKOUTEN
		bit 13					bit
U-1	R/P-1	R/P-1	R/P-1	U-1	R/P-1	R/P-1	R/P-1
	RSTOSC2	RSTOSC1	RSTOSC0		FEXTOSC2	FEXTOSC1	FEXTOSC0
bit 7							bit
Legend:							
R = Readable bit P = Programmable bit U = Unimplemented bit, read as '1'							
'0' = Bit is c	leared	'1' = Bit is set		n = Value wh	en blank or afte	r Bulk Erase	
bit 13		Safe Clock Mo		bit			
		SCM timer ena					
bit 12		SCM timer disa					
	-	ted: Read as '					
bit 11		ck Switch Enat riting to NOSC		allowed			
					l by user softwa	are	
bit 10-9		 0 = OFF The NOSC and NDIV bits cannot be changed by user software Unimplemented: Read as '1' 					
bit 8	CLKOUTEN: Clock Out Enable bit						
				bit is ignored;	otherwise:		
				I/O or oscillato	r function on OS		
	0 = ON CL	KOUI functio					
				Fosc/4 clock a	ppears at OSC2	2	
	Unimplemen	ted: Read as '	1'		ppears at OSC2	2	
bit 7 bit 6-4	Unimplemen RSTOSC<2:0	ted: Read as ' >: Power-up D	1')efault Value fo	or COSC bits			loor ooffwara
	Unimplemen RSTOSC<2:0 This value is t	ted: Read as ' ⊳: Power-up D he Reset defa	1')efault Value fo ult value for C	or COSC bits OSC, and sele	cts the oscillato		user software
	Unimplemen RSTOSC<2:0	ted: Read as ' >: Power-up E he Reset defa x EXTOSC	1' Default Value fo ult value for C operating per	or COSC bits	cts the oscillato		user software
	Unimplemen RSTOSC<2:0 This value is t 111 = EXT1	ted: Read as ' >: Power-up D he Reset defar X EXTOSC T1 HFINTOS rved	1' Default Value fo ult value for C operating per SC (1 MHz)	or COSC bits OSC, and sele	cts the oscillato		user software
	Unimplement RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN	ted: Read as ' >: Power-up E he Reset defa x EXTOSC T1 HFINTOS rved T LFINTOS	1' Default Value fo ult value for C operating per SC (1 MHz) SC	or COSC bits OSC, and sele	cts the oscillato		user software
	Unimplement RSTOSC<2:0 This value is the set of the set	ted: Read as ' >: Power-up E he Reset defa x EXTOSC T1 HFINTOS ved T LFINTOS SOSC (3	1' Default Value fo ult value for C operating per SC (1 MHz)	or COSC bits OSC, and sele	cts the oscillato		user software
	Unimplement RSTOSC<2:0 This value is the second sec	ted: Read as ' >: Power-up E he Reset defa X EXTOSC T1 HFINTOS Ved T LFINTOS SOSC (3 Ved	1 [°] Default Value for C operating per SC (1 MHz) SC 2.768 kHz)	or COSC bits OSC, and sele FEXTOSC<2:	cts the oscillato 0> bits	r first used by t	user software
	Unimplement RSTOSC<2:0 This value is the second sec	ted: Read as ' >: Power-up E he Reset defa X EXTOSC T1 HFINTOS ved T LFINTOS SOSC (3 ved X EXTOSC	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL;	or COSC bits OSC, and sele FEXTOSC<2:	cts the oscillato	r first used by t	user software
bit 6-4	Unimplemen RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN	ted: Read as ' >: Power-up E he Reset defa X EXTOSC T1 HFINTOS Ved T LFINTOS SOSC (3 Ved	¹ ' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz)	or COSC bits OSC, and sele FEXTOSC<2:	cts the oscillato 0> bits	r first used by t	user software
	Unimplemen RSTOSC<2:0 This value is to 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplemen	ted: Read as ' >: Power-up D he Reset defair X EXTOSC T1 HFINTOS Ved T LFINTOS SOSC (3 Ved X EXTOSC T32 HFINTOS ted: Read as '	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1'	or COSC bits OSC, and sele FEXTOSC<2:	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplemen RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplemen FEXTOSC<2:	ted: Read as ' >: Power-up D he Reset defair X EXTOSC T1 HFINTOS Ved T LFINTOS SOSC (3 Ved X EXTOSC T32 HFINTOS ted: Read as '	1' Default Value for Co operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' External Osc	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper-	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplement RSTOSC<2:0 This value is to 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplement FEXTOSC<2: 111 = ECH 110 = ECM	ted: Read as ' >: Power-up E he Reset defai X EXTOSC II HFINTOS Ved II LFINTOS SOSC (3 Ved X EXTOSC III HFINTOS ted: Read as ' 0>: FEXTOSC EC (External C EC (External C	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' External Osc Clock) above 8 Clock) for 100	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper- illator Mode Se MHz kHz to 8 MHz	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplement RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplement FEXTOSC<2: 111 = ECH 110 = ECM 101 = ECL	ted: Read as ' >: Power-up E he Reset defairs X EXTOSC T1 HFINTOS rved T LFINTOS SOSC (3 rved X EXTOSC T32 HFINTOS ted: Read as ' 0>: FEXTOSC EC (External C EC (External C	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' External Osc Clock) above 8 Clock) for 100 Clock) below 1	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper- illator Mode Se MHz kHz to 8 MHz	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplement RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplement FEXTOSC<2: 111 = ECH 110 = ECM 101 = ECL 100 = OFF	ted: Read as ' >: Power-up D he Reset defair X EXTOSC T1 HFINTOS ved T LFINTOS SOSC (3 ved X EXTOSC T32 HFINTOS ted: Read as ' 0>: FEXTOSC EC (External C EC (External C Oscillator not c	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' External Osc Clock) above 8 Clock) for 100 Clock) below 1	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper- illator Mode Se MHz kHz to 8 MHz	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplement RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplement FEXTOSC<2: 111 = ECH 110 = ECM 101 = ECL 100 = OFF 011 = Unimplement	ted: Read as ' >: Power-up E he Reset defai X EXTOSC T1 HFINTOS ved T LFINTOS SOSC (3 ved X EXTOSC T32 HFINTOS ted: Read as ' 0>: FEXTOSC EC (External C EC (External C Oscillator not c olemented	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' External Osc Clock) above 8 Clock) for 100 Clock) below 1 enabled	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper- illator Mode Se MHz kHz to 8 MHz 00 kHz	cts the oscillato 0> bits ating per FEXT	r first used by t	user software
bit 6-4 bit 3	Unimplemen RSTOSC<2:0 This value is t 111 = EXT1 110 = HFIN 101 = Reset 100 = LFIN 011 = SOSC 010 = Reset 001 = EXT4 000 = HFIN Unimplemen FEXTOSC<2: 111 = ECH 110 = ECM 101 = ECL 100 = OFF 011 = Unimplemen 010 = HS	ted: Read as ' >: Power-up E he Reset defai X EXTOSC T1 HFINTOS Ved T LFINTOS SOSC (3 Ved X EXTOSC T32 HFINTOS ted: Read as ' 0>: FEXTOSC EC (External C EC (External C CScillator not e olemented HS (Crystal os	1' Default Value for C operating per SC (1 MHz) SC 2.768 kHz) with 4x PLL; SC (32 MHz) 1' C External Osc Clock) above 8 Clock) for 100 Clock) below 1 enabled scillator) above	or COSC bits OSC, and sele FEXTOSC<2: EXTOSC oper- illator Mode Se MHz kHz to 8 MHz 00 kHz	cts the oscillato 0> bits ating per FEXT election bits	r first used by t	user software

REGISTER	R 5-2: CON	FIGURATION	WORD 2: S	UPERVISOR	S		
		R/P-1	R/P-1	R/P-1	U-1	R/P-1	U-1
		DEBUG	STVREN	PPS1WAY	_	BORV	_
		bit 13		•		•	bit 8
		-					
R/P-1	R/P-1	R/P-1	U-1	R/P-1	R/P-1	R/P-1	R/P-1
BOREN1	BOREN0	LPBOREN	_	WDTE1	WDTE0	PWRTE	MCLRE
bit 7							bit 0
Legend:							
R = Readabl	e bit	P = Programma	able bit	U = Unimpleme	ented bit, read as	; '1'	
'0' = Bit is cle	eared	'1' = Bit is set		n = Value wher	h blank or after B	ulk Erase	
bit 13		igger Enable bit ⁽¹					
				SPCLK and ICSI SPCLK and ICSF	•		
bit 12		k Overflow/Unde			DAT are dedicat		Jei
DIL 12		tack Overflow or					
	0 = OFF S	tack Overflow or	Underflow will n	ot cause a Reset			
bit 11		SLOCK One-Wa	•				
		he PPSLOCKED lear/set cycle) bit can be cle	ared and set on	ly once; PPS re	gisters remain lo	ocked after one
		,	bit can be set a	nd cleared repea	tedly (subiect to t	the unlock seaue	nce)
bit 10		ed: Read as '1'					,
bit 9	•	out Reset Voltag	e Selection bit ⁽²⁾	1			
	1 = LOW	Brown-out Rese	et voltage (VBOR)	set to 1.9V on L	F, and 2.45V on	F devices	
	0 = HIGH		et voltage (VBOR)				
1.11.0	-		commended for (operation at or ab	ove 16 MHz.		
bit 8	-	ed: Read as '1'					
bit 7-6		Brown-out Rese Brown-out Rese) is set by the BC	RV bit		
	11 = ON			SBOREN bit is ig			
	10 = SLEEP			/hile running, disa		BOREN bit is igr	ored
	01 = SBOREN 00 = OFF		eset is enabled a	according to SBO	REN		
bit 5		w-Power BOR E					
bit 0		LPBOR is disable					
	0 = ON U	LPBOR is enable	ed				
bit 4	Unimplement	ed: Read as '1'					
bit 3-2		Vatchdog Timer					
	11 = ON 10 = SLEEP		abled; SWDTEN	is ignored	in Sleen/Idle: SV	VDTEN is ignored	Ч
	01 = SWDTEN			WDTEN bit in the			u .
	00 = OFF		abled; SWDTEN		-		
bit 1		er-up Timer Enab	le bit				
		WRT is disabled WRT is enabled					
bit 0							
DILU	If LVP = 1:	er Clear (MCLR)	Enable bit				
	RA3 pin function	on is MCLR.					
	$\frac{\text{If LVP} = 0}{1}$		5				
		ICLR pin is MCLI		unction			
Note 1:	The DEBUG bit in (•	•		device developm	nent tools includir	na debuaaers
	and programmers.	-	-	• •	•		.9 402499013
	See VBOR paramet		•				

REGISTER 5-2: CONFIGURATION WORD 2: SUPERVISORS

REGISTER	001	IGURATION					
		R/P-1	U-1	U-1	U-1	U-1	U-1
		LVP ⁽¹⁾	—	_			
		bit 13					bit 8
U-1	U-1	U-1	U-1	U-1	U-1	R/P-1	R/P-1
—	—	—	—	—	—	WRT1	WRT0
bit 7							bit 0
Legend:							
R = Readal	ble bit	P = Programn	nable bit	U = Unimplem	nented bit, read	l as '1'	
'0' = Bit is cleared '1' = Bit is set n = Value when blank or after Bulk Erase							
bit 13	LVP: Low-Vol	ltage Programn	ning Enable bit	(1)			
				enabled. MC	LR/VPP pin f	unction is M	CLR. MCLRE
		onfiguration bit			•		
				d for programm	ing.		
bit 12-2	Unimplemen	ted: Read as '					
bit 1-0		Jser NVM Self-		n bits			
		Write protectio					
				ed, 0200h to 3F	,		
			•	ed, 2000h to 3F	•		
				ed, no address			
	WRI applies	only to the self-	write feature o	f the device; wr	riting through IC	JSP™ is never	protected.
Note 1:	The LVP bit canno	ot be programn	ned to '0' when	Programming	mode is entere	d via LVP.	

REGISTER 5-3: CONFIGURATION WORD 3: MEMORY

REGISTER 5-4:	CONFIGURATION WORD 4: CODE PROTECTION

		U-1	U-1	U-1	U-1	U-1	U-1
		_	—	_	_	_	_
		bit 13					bit 8
U-1	U-1	U-1	U-1	U-1	U-1	R/P-1	R/P-1
_	—	_	_	—	—	CPD	CP
bit 7							bit 0
Logondy							

Legend:		
R = Readable bit	P = Programmable bit	U = Unimplemented bit, read as '1'
'0' = Bit is cleared	'1' = Bit is set	n = Value when blank or after Bulk Erase

bit 13-2 Unimplemented: Read as '1'

bit 1	1 = OFF	EEPROM Memory Code Protection bit Data EEPROM code protection disabled Data EEPROM code protection enabled
bit 0	1 = OFF	am Memory Code Protection bit Program Memory code protection disabled Program Memory code protection enabled

5.3 Code Protection

Code protection allows the device to be protected from unauthorized access. Program memory protection and data memory are controlled independently. Internal access to the program memory is unaffected by any code protection setting.

5.3.1 PROGRAM MEMORY PROTECTION

The entire program memory space is protected from external reads and writes by the \overline{CP} bit in Configuration Words. When $\overline{CP} = 0$, external reads and writes of program memory are inhibited and a read will return all '0's. The CPU can continue to read program memory, regardless of the protection bit settings. Self-write writing the program memory is dependent upon the write protection setting. See Section 5.4 "Write Protection" for more information.

5.3.2 DATA MEMORY PROTECTION

The entire data EEPROM are protected from external reads and writes by the CPD bit in the Configuration Words. When CPD = 0, external reads and writes of EEPROM memory are inhibited and a read will return all '0's. The CPU can continue to read and write EEPROM memory, regardless of the protection bit settings.

5.4 Write Protection

Write protection allows the device to be protected from unintended self-writes. Applications, such as boot loader software, can be protected while allowing other regions of the program memory to be modified.

The WRT<1:0> bits in Configuration Words define the size of the program memory block that is protected.

5.5 User ID

Four memory locations (8000h-8003h) are designated as ID locations where the user can store checksum or other code identification numbers. These locations are readable and writable during normal execution. See Section 11.4.7 "NVMREG EEPROM, User ID, Device ID and Configuration Word Access" for more information on accessing these memory locations. For more information on checksum calculation, see the "PIC16(L)F183XX Memory Programming Specification" (DS40001738).

5.6 Device ID and Revision ID

The 14-bit Device ID word is located at 8006h and the 14-bit Revision ID is located at 8005h. These locations are read-only and cannot be erased or modified. See **Section 11.4** "**NVMREG Access**" for more information on accessing these memory locations.

Development tools, such as device programmers and debuggers, may be used to read the Device ID and Revision ID.

PIC16(L)F18326/18346

Register Definitions: Device and Revision 5.7

REGISTER 5-5:	DE	DEVID: DEVICE ID REGISTER							
		R	R	R	R	R	R		
			DEV<13:8>						
		bit 13					bit 8		
R	R	R	R	R	R	R	R		
			DEV	<7:0>					
bit 7							bit 0		

Legend:

R = Readable bit

'1' = Bit is set '0' = Bit is cleared

bit 13-0 DEV<13:0>: Device ID bits

Device	DEVID<13:0> Values				
PIC16F18326	11 0000 1010 0100 (30A4)				
PIC16LF18326	11 0000 1010 0110 (30A6)				
PIC16F18346	11 0000 1010 0101 (30A5)				
PIC16LF18346	11 0000 1010 0111 (30A7)				

REGISTER 5-6: REVID: REVISION ID REGISTER

R-1	R-0	R	R	R	R
REV<13:8>					
bit 13					bit 8

R	R	R	R	R	R	R	R	
	REV<7:0>							
bit 7							bit 0	

Legend:	
R = Readable bit	
'1' = Bit is set	'0' = Bit is cleared

bit 13-0 REV<13:0>: Revision ID bits

Note: The upper two bits of the Revision ID Register will always read '10'.

6.0 RESETS


There are multiple ways to reset this device:

- Power-On Reset (POR)
- Brown-Out Reset (BOR)
- Low-Power Brown-Out Reset (LPBOR)
- MCLR Reset
- WDT Reset
- RESET instruction
- · Stack Overflow
- · Stack Underflow
- Programming mode exit

To allow VDD to stabilize, an optional Power-up Timer can be enabled to extend the Reset time after a BOR or POR event.

A simplified block diagram of the on-chip Reset circuit is shown in Figure 6-1.

FIGURE 6-1: SIMPLIFIED BLOCK DIAGRAM OF ON-CHIP RESET CIRCUIT



6.1 Power-on Reset (POR)

The POR circuit holds the device in Reset until VDD has reached an acceptable level for minimum operation. Slow rising VDD, fast operating speeds or analog performance may require greater than minimum VDD. The PWRT, BOR or MCLR features can be used to extend the start-up period until all device operation conditions have been met.

6.2 Brown-out Reset (BOR)

The BOR circuit holds the device in Reset while VDD is below a selectable minimum level. Between the POR and BOR, complete voltage range coverage for execution protection can be implemented.

The Brown-out Reset module has four operating modes controlled by the BOREN<1:0> bits in Configuration Words. The four operating modes are:

- · BOR is always on
- BOR is off when in Sleep
- BOR is controlled by software
- BOR is always off

Refer to Table 6-1 for more information.

The Brown-out Reset voltage level is selectable by configuring the BORV bit in Configuration Words.

A VDD noise rejection filter prevents the BOR from triggering on small events. If VDD falls below VBOR for a duration greater than parameter TBORDC, the device will reset, and the BOR bit of the PCON0 register will be cleared, indicating that a Brown-out Reset condition occurred. See Figure 6-2 for more information.

BOREN<1:0>	SBOREN	Device Mode	BOR Mode	Instruction Execution upon: Release of POR or Wake-up from Sleep
11	X	X	Active	In these specific cases, "Release of POR" and "Wake-up from Sleep", there is no delay in start-up. The BOR ready flag, (BORRDY = 1), will be set before the CPU is ready to execute instructions because the BOR circuit is forced on by the BOREN<1:0> bits.
10	Х	Awake	Active	Waits for release of BOR (BORRDY = 1)
		Sleep	Disabled	BOR ignored when asleep
01	1	X	Active	In these specific cases, "Release of POR" and "Wake-up from Sleep", there is no delay in start-up. The BOR Ready flag, (BORRDY = 1), will be set before the CPU is ready to execute instructions because the BOR circuit is forced on by the BOREN<1:0> bits
	0	Х	Disabled	Begins immediately (BORRDY = x)
00	Х	Х	Disabled	

TABLE 6-1: BOR OPERATING MODES

6.2.1 BOR IS ALWAYS ON

When the BOREN bits of Configuration Words are programmed to '11', the BOR is always on. The device start-up will be delayed until the BOR is ready and VDD is higher than the BOR threshold.

BOR protection is active during Sleep. The BOR does not delay wake-up from Sleep.

6.2.2 BOR IS OFF IN SLEEP

When the BOREN bits of Configuration Words are programmed to '10', the BOR is on, except in Sleep. The device start-up will be delayed until the BOR is ready and VDD is higher than the BOR threshold.

BOR protection is not active during Sleep, but device wake-up will be delayed until the BOR can determine that VDD is higher than the BOR threshold. The device wake-up will be delayed until the BOR is ready.

6.2.3 BOR CONTROLLED BY SOFTWARE

When the BOREN bits of Configuration Words are programmed to '01', the BOR is controlled by the SBOREN bit of the BORCON register. The device wake from Sleep is not delayed by the BOR Ready condition or the VDD level only when the SBOREN bit is cleared in software and the device is starting up from a non POR/BOR Reset event.

BOR protection begins as soon as the BOR circuit is ready. The status of the BOR circuit is reflected in the BORRDY bit of the BORCON register. BOR Protection is unchanged by Sleep




FIGURE 6-2: BROWN-OUT SITUATIONS

6.2.4 BOR ALWAYS OFF

When the BOREN bits of Configuration Word 2 are programmed to '00', the BOR is always disabled. In the configuration, setting the SWBOREN bit will have no affect on BOR operation.

6.3 Low-Power Brown-out Reset (LPBOR)

The Low-Power Brown-Out Reset (LPBOR) circuit provides alternative protection against Brown-out conditions. When VDD falls below the LPBOR threshold, the device is held in Reset. When this occurs, the BOR bit of the PCON0 register is cleared to indicate that a Brown-out Reset occurred. The BOR bit will be cleared when either the BOR or the LPBOR circuitry detects a BOR condition. The LPBOR feature can be used with or without BOR enabled.

When used while BOR is enabled, the LPBOR can be used as a secondary protection circuit in case the BOR circuit fails to detect the BOR condition. Additionally, when BOR is enabled except while in Sleep (BOREN<1:0> = 10), the LPBOR circuit will hold the device in Reset while VDD is lower than the LPBOR threshold, and will also re-arm the POR. (see Figure 35-11 for LPBOR Reset voltage levels).

When used without BOR enabled, the LPBOR circuit provides a single Reset trip point with the benefit of reduced current consumption.

6.3.1 ENABLING LPBOR

The LPBOR is controlled by the LPBOR bit of Configuration Words. When the device is erased, the LPBOR module defaults to disabled.

6.3.1.1 LPBOR Module Output

The output of the LPBOR module is a signal indicating whether or not a Reset is to be asserted. This signal is OR'd together with the Reset signal of the BOR module to provide the generic BOR signal, which goes to the PCON register and to the power control block.

6.4 MCLR

The $\overline{\text{MCLR}}$ is an <u>optional</u> external input that can reset the device. The $\overline{\text{MCLR}}$ function is controlled by the MCLRE bit of Configuration Words and the LVP bit of Configuration Words (Table 6-2).

 TABLE 6-2:
 MCLR CONFIGURATION

MCLRE	LVP	MCLR
0	0	Disabled
1	0	Enabled
x	1	Enabled

6.4.1 MCLR ENABLED

When MCLR is enabled and the pin is held low, the device is held in Reset. The MCLR pin is connected to VDD through an internal weak pull-up.

The device has a noise filter in the $\overline{\text{MCLR}}$ Reset path. The filter will detect and ignore small pulses.

Note: A Reset does not drive the MCLR pin low.

6.4.2 MCLR DISABLED

When MCLR is disabled, the pin functions as a general purpose input and the internal weak pull-up is under software control. See Section 12.2 "PORTA Registers" for more information.

6.5 Watchdog Timer (WDT) Reset

The Watchdog Timer generates a Reset if the firmware does not issue a CLRWDT instruction within the time-out period. The \overline{TO} and \overline{PD} bits in the STATUS register as well as the RWDT bit in the PCON register, are changed to indicate the WDT Reset. See Section 10.0 "Watchdog Timer (WDT)" for more information.

6.6 RESET Instruction

A RESET instruction will cause a device Reset. The \overline{RI} bit in the PCON register will be set to '0'. See Table 6-4 for default conditions after a RESET instruction has occurred.

6.7 Stack Overflow/Underflow Reset

The device can reset when the Stack Overflows or Underflows. The STKOVF or STKUNF bits of the PCON register indicate the Reset condition. These Resets are enabled by setting the STVREN bit in Configuration Words. See **Section 4.4 "Stack"** for more information.

6.8 Programming Mode Exit

Upon exit of Programming mode, the device will behave as if a device Reset had just occurred.

6.9 Power-up Timer

The Power-up Timer provides a nominal 64 ms time-out on POR or Brown-out Reset.

The device is held in Reset as long as PWRT is active. The PWRT delay allows additional time for the VDD to rise to an acceptable level. The Power-up Timer is enabled by clearing the PWRTE bit in Configuration Words.

The Power-up Timer starts after the release of the POR and BOR.

For additional information, refer to Application Note *AN607*, *Power-up Trouble Shooting* (DS00607).

6.10 Start-up Sequence


Upon the release of a POR or BOR, the following must occur before the device will begin executing:

- 1. Power-up Timer runs to completion (if enabled).
- 2. MCLR must be released (if enabled).
- 3. Oscillator start-up timer runs to completion (if required for oscillator source).

The total time out will vary based on oscillator configuration and Power-up Timer Configuration. See Section 7.0, Oscillator Module for more information.

The Power-up Timer and oscillator start-up timer run independently of MCLR Reset. If MCLR is kept low long enough, the Power-up Timer will expire. Upon bringing MCLR high, the device will begin execution after ten Fosc cycles (see Figure 6-3). This is useful for testing purposes or to synchronize more than one device operating in parallel.

FIGURE 6-3: RESET START-UP SEQUENCE



6.11 Determining the Cause of a Reset

Upon any Reset, multiple bits in the STATUS and PCON registers are updated to indicate the cause of the Reset. Table 6-3 and Table 6-4 show the Reset conditions of these registers.

STKOVF	STKUNF	RWDT	RMCLR	RI	POR	BOR	то	PD	Condition
0	0	1	1	1	0	х	1	1	Power-on Reset
0	0	1	1	1	0	х	0	х	Illegal, $\overline{\text{TO}}$ is set on $\overline{\text{POR}}$
0	0	1	1	1	0	х	х	0	Illegal, PD is set on POR
0	0	u	1	1	u	0	1	1	Brown-out Reset
u	u	0	u	u	u	u	0	u	WDT Reset
u	u	u	u	u	u	u	0	0	WDT Wake-up from Sleep
u	u	u	u	u	u	u	1	0	Interrupt Wake-up from Sleep
u	u	u	0	u	u	u	u	u	MCLR Reset during Normal Operation
u	u	u	0	u	u	u	1	0	MCLR Reset during Sleep
u	u	u	u	0	u	u	u	u	RESET Instruction Executed
1	u	u	u	u	u	u	u	u	Stack Overflow Reset (STVREN = 1)
u	1	u	u	u	u	u	u	u	Stack Underflow Reset (STVREN = 1)

TABLE 6-3: RESET STATUS BITS AND THEIR SIGNIFICANCE

TABLE 6-4: RESET CONDITION FOR SPECIAL REGISTERS
--

Condition	Program Counter	STATUS Register	PCON0 Register
Power-on Reset	0000h	1 1000	00 110x
MCLR Reset during Normal Operation	0000h	u uuuu	uu Ouuu
MCLR Reset during Sleep	0000h	1 Ouuu	uu Ouuu
WDT Reset	0000h	0 uuuu	uu-0 uuuu
WDT Wake-up from Sleep	PC + 1	0 Ouuu	uu-u uuuu
Brown-out Reset	0000h	1 1000	00-1 11u0
Interrupt Wake-up from Sleep	PC + 1 ⁽¹⁾	1 Ouuu	uu-u uuuu
RESET Instruction Executed	0000h	u uuuu	uu-u u0uu
Stack Overflow Reset (STVREN = 1)	0000h	u uuuu	lu-u uuuu
Stack Underflow Reset (STVREN = 1)	0000h	u uuuu	ul-u uuuu

Legend: u = unchanged, x = unknown, - = unimplemented bit, reads as '0'.

Note 1: When the wake-up is due to an interrupt and Global Enable (GIE) bit is set, the return address is pushed on the stack and PC is loaded with the interrupt vector (0004h) after execution of PC + 1.

R/W-1/u	R/W-0-0	U-0	U-0	U-0	U-0	U-0	R-q/u	
SBOREN ⁽¹⁾	Reserved	—	_	_	—	_	BORRDY	
bit 7		- -					bit 0	
Legend:								
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unknow		iown	-n/n = Value at POR and BOR/Value at all other Re					
'1' = Bit is set		'0' = Bit is clea	ared	q = Value de	pends on conditi	on		

REGISTER 6-1: BORCON: BROWN-OUT RESET CONTROL REGISTER

bit 7	SBOREN: Software Brown-out Reset Enable bit ⁽¹⁾
	If BOREN <1:0> in Configuration Words ≠ 01:
	SBOREN is read/write, but has no effect on the BOR.
	If BOREN <1:0> in Configuration Words = 01:
	1 = BOR Enabled
	0 = BOR Disabled
bit 6	Reserved: Bit must be maintained as '0'
bit 5-1	Unimplemented: Read as '0'
bit 0	BORRDY: Brown-out Reset Circuit Ready Status bit
	1 = The Brown-out Reset circuit is active

0 = The Brown-out Reset circuit is inactive

Note 1: BOREN<1:0> bits are located in Configuration Words.

6.12 Power Control (PCON) Register

The Power Control (PCON) register contains flag bits to differentiate between a:

- Power-on Reset (POR)
- Brown-out Reset (BOR)
- RESET Instruction Reset (RI)
- MCLR Reset (RMCLR)
- Watchdog Timer Reset (RWDT)
- Stack Underflow Reset (STKUNF)
- Stack Overflow Reset (STKOVF)

The PCON0 register bits are shown in Register 6-2.

Hardware will change the corresponding register bit during the Reset process; if the Reset was not caused by the condition, the bit remains unchanged (Table 6-4).

Software can reset the bit to the Inactive state after the restart (hardware will not reset the bit).

Software may also set any PCON bit to the Active state, so that user code may be tested, but no Reset action will be generated.

6.13 Register Definitions: Power Control

R/W/HS-0/q	R/W/HS-0/q	U-0	R/W/HC-1/q	R/W/HC-1/q	R/W/HC-1/q	R/W/HC-q/u	R/W/HC-q/u
STKOVF	STKUNF	—	RWDT	RMCLR	RI	POR	BOR
bit 7			•			•	bit (
Legend:							
HC = Bit is clea	ared by hardwa	ire		HS = Bit is se	et by hardware		
R = Readable I	oit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is uncha	anged	x = Bit is unk	nown	-m/n = Value	at POR and BC	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is cle	ared	q = Value dep	pends on condit	ion	
bit 7		Overflow occur	red	has been clea	ired by firmware		
bit 6	 0 = A Stack Overflow has not occurred or has been cleared by firmware STKUNF: Stack Underflow Flag bit 1 = A Stack Underflow occurred 0 = A Stack Underflow has not occurred or has been cleared by firmware 						
bit 5	Unimplemen	ted: Read as '	0'				
bit 4	RWDT: Watchdog Timer Reset Flag bit 1 = A Watchdog Timer Reset has not occurred or set to '1' by firmware 0 = A Watchdog Timer Reset has occurred (cleared by hardware)						
bit 3	RMCLR: MCLR Reset Flag bit $1 = A \overline{MCLR}$ Reset has not occurred or set to '1' by firmware $0 = A \overline{MCLR}$ Reset has occurred (cleared by hardware)						
bit 2	 RI: RESET Instruction Flag bit 1 = A RESET instruction has not been executed or set to '1' by firmware 0 = A RESET instruction has been executed (cleared by hardware) 						
bit 1	POR: Power-on Reset Status bit 1 = No Power-on Reset occurred						
bit 0	 0 = A Power-on Reset occurred (must be set in software after a Power-on Reset occurs) BOR: Brown-out Reset Status bit 1 = No Brown-out Reset occurred 0 = A Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset or Brown-out Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software after a Power-on Reset occurred (must be set in software af						

REGISTER 6-2: PCON0: POWER CONTROL REGISTER 0

TABLE 6-5: SUMMARY OF REGISTERS ASSOCIATED WITH RESET	S
---	---

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
BORCON	SBOREN	_			—			BORRDY	76
PCON0	STKOVF	STKUNF	_	RWDT	RMCLR	RI	POR	BOR	77
STATUS	_	_	_	TO	PD	Z	DC	С	30
WDTCON			WDTPS<4:0> SW			SWDTEN	121		

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by Resets.

7.0 OSCILLATOR MODULE

7.1 Overview

The oscillator module has a wide variety of clock sources and selection features that allow it to be used in a wide range of applications while maximizing performance and minimizing power consumption. Figure 7-1 illustrates a block diagram of the oscillator module.

Clock sources can be supplied from external oscillators, quartz-crystal resonators and ceramic resonators. In addition, the system clock source can be supplied from one of two internal oscillators and PLL circuits, with a choice of speeds selectable via software. Additional clock features include:

- Selectable system clock source between external or internal sources via software.
- Fail-Safe Clock Monitor (FSCM) designed to detect a failure of the external clock source (LP, XT, HS, ECH, ECM, ECL) and switch automatically to the internal oscillator.
- Oscillator Start-up Timer (OST) ensures stability of crystal oscillator sources.

The RSTOSC bits of Configuration Word 1 determine the type of oscillator that will be used when the device is reset, including when it is first powered-up.


The internal clock modes, LFINTOSC, HFINTOSC (set at 1 MHz), or HFINTOSC (set at 32 MHz) can be set through the RSTOSC bits.

If an external clock source is selected, the FEXTOSC bits of Configuration Word 1 must be used in conjunction with the RSTOSC bits to select the External Clock mode.

The external oscillator module can be configured in one of the following clock modes by setting the FEXTOSC<2:0> bits of Configuration Word 1:

- 1. ECL External Clock Low-Power mode (<= 100 kHz)
- 2. ECM External Clock Medium-Power mode (<= 8 MHz)
- 3. ECH External Clock High-Power mode (above 8 MHz)
- 4. LP 32 kHz Low-Power Crystal mode.
- 5. XT Medium Gain Crystal or Ceramic Resonator Oscillator mode (between 100 kHz and 4 MHz)
- 6. HS High Gain Crystal or Ceramic Resonator mode (above 4 MHz)

The ECH, ECM, and ECL Clock modes rely on an external logic level signal as the device clock source. The LP, XT, and HS Clock modes require an external crystal or resonator to be connected to the device. Each mode is optimized for a different frequency range. The INTOSC internal oscillator block produces low and high-frequency clock sources, designated LFINTOSC and HFINTOSC. (see Internal Oscillator Block, Figure 7-1).



PIC16(L)F18326/18346

FIGURE 7-1: SIMPLIFIED PIC® MCU CLOCK SOURCE BLOCK DIAGRAM

7.2 Clock Source Types

Clock sources can be classified as external or internal.

External clock sources rely on external circuitry for the clock source to function. Examples are: oscillator modules (ECH, ECM, ECL mode), quartz crystal resonators or ceramic resonators (LP, XT and HS modes).

There is also a secondary oscillator block which is optimized for a 32.768 kHz external clock source, which can be used as an alternate clock source.

There are two internal oscillator blocks:

- HFINTOSC
- LFINTOSC

The HFINTOSC can produce clock frequencies from 1-16 MHz. The LFINTOSC generates a 31 kHz clock frequency.

There is a PLL that can be used by the external oscillator. See **Section 7.2.1.4 "4x PLL**" for more details. Additionally, there is a PLL that can be used by the HFINTOSC at certain frequencies. See **Section 7.2.2.2 "2x PLL"** for more details.

7.2.1 EXTERNAL CLOCK SOURCES

An external clock source can be used as the device system clock by performing one of the following actions:

- Program the RSTOSC<2:0> bits in the Configuration Words to select an external clock source that will be used as the default system clock upon a device Reset.
- Write the NOSC<2:0> and NDIV<3:0> bits in the OSCCON1 register to switch the system clock source.

See **Section 7.3 "Clock Switching"** for more information.

7.2.1.1 EC Mode


The External Clock (EC) mode allows an externally generated logic level signal to be the system clock source. When operating in this mode, an external clock source is connected to the CLKIN input. OSC2/CLKOUT is available for general purpose I/O or CLKOUT. Figure 7-2 shows the pin connections for EC mode.

EC mode has three power modes to select from through Configuration Words:

- ECH High power, <= 32 MHz
- ECM Medium power, <= 8 MHz
- ECL Low power, <= 0.1 MHz

The Oscillator Start-up Timer (OST) is disabled when EC mode is selected. Therefore, there is no delay in operation after a Power-on Reset (POR) or wake-up from Sleep. Because the PIC[®] MCU design is fully static, stopping the external clock input will have the effect of halting the device while leaving all data intact. Upon restarting the external clock, the device will resume operation as if no time had elapsed.

FIGURE 7-2: EXTERNAL CLOCK (EC) MODE OPERATION




PIC16(L)F18326/18346


7.2.1.2 LP, XT, HS Modes

The LP, XT and HS modes support the use of quartz crystal resonators or ceramic resonators connected to OSC1 and OSC2 (Figure 7-3). The three modes select a low, medium or high gain setting of the internal inverter-amplifier to support various resonator types and speed.

- LP Oscillator mode selects the lowest gain setting of the internal inverter-amplifier. LP mode current consumption is the least of the three modes. This mode is designed to drive only 32.768 kHz tuning-fork type crystals (watch crystals) but can operate up to 100 kHz.
- XT Oscillator mode selects the intermediate gain setting of the internal inverter-amplifier. XT mode current consumption is the medium of the three modes. This mode is best suited to crystals and resonators with a frequency rang up to 4 MHz.
- HS Oscillator mode selects the highest gain setting of the internal inverter-amplifier. HS mode current consumption is the highest of the three modes. This mode is best suited for resonators that require operating frequencies up to 20 MHz.

Figure 7-3 and Figure 7-4 show typical circuits for quartz crystal and ceramic resonators, respectively.






Note 1: Quartz crystal characteristics vary according to type, package and manufacturer. The user must consult the manufacturer data sheets for specifications and recommended application.

- **2:** Always verify oscillator performance over the VDD and temperature range that is expected for the application.
- **3:** For oscillator design assistance, reference the following Microchip Application Notes:
 - AN826, Crystal Oscillator Basics and Crystal Selection for rfPIC[®] and PIC[®] Devices (DS00826)
 - AN849, Basic PIC[®] Oscillator Design (DS00849)
 - AN943, Practical PIC[®] Oscillator Analysis and Design (DS00943)
 - AN949, Making Your Oscillator Work (DS00949)



CERAMIC RESONATOR OPERATION (XT OR HS MODE)



7.2.1.3 Oscillator Start-up Timer (OST)

If the oscillator module is configured for LP, XT or HS modes, the Oscillator Start-up Timer (OST) counts 1024 oscillations from OSC1. This occurs following a Power-on Reset (POR), Brown-out Reset (BOR), or a wake-up from Sleep. The OST ensures that the oscillator circuit, using a quartz crystal resonator or ceramic resonator, has started and is providing a stable system clock to the oscillator module.

7.2.1.4 4x PLL

The oscillator module contains a PLL that can be used with external clock sources to provide a system clock source. The input frequency for the PLL must fall within specifications. See the PLL Clock Timing Specifications in Table 35-9.


The PLL may be enabled for use by one of two methods:

- 1. Program the RSTOSC bits in the Configuration Word 1 to enable the EXTOSC with 4x PLL.
- 2. Write the NOSC<2:0> bits in the OSCCON1 register to enable the EXTOSC with 4x PLL.

7.2.1.5 Secondary Oscillator

The secondary oscillator is a separate oscillator block that can be used as an alternate system clock source. The secondary oscillator is optimized for 32.768 kHz, and can be used with an external crystal oscillator connected to the SOSCI and SOSCO device pins, or an external clock source connected to the SOSCIN pin. The secondary oscillator can be selected during run-time using clock switching. Refer to **Section 7.3** "**Clock Switching**" for more information.

FIGURE 7-5: QUARTZ CRYSTAL OPERATION (SECONDARY OSCILLATOR)



- Note 1: Quartz crystal characteristics vary according to type, package and manufacturer. The user must consult the manufacturer data sheets for specifications and recommended application.
 - **2:** Always verify oscillator performance over the VDD and temperature range that is expected for the application.
 - **3:** For oscillator design assistance, reference the following Microchip Application Notes:
 - AN826, Crystal Oscillator Basics and Crystal Selection for rfPIC[®] and PIC[®] Devices (DS00826)
 - AN849, Basic PICmicro[®] Oscillator Design (DS00849)
 - AN943, Practical PICmicro[®] Oscillator Analysis and Design (DS00943)
 - AN949, Making Your Oscillator Work (DS00949)
 - TB097, Interfacing a Micro Crystal MS1V-T1K 32.768 kHz Tuning Fork Crystal to a PIC16F690/SS (DS91097)
 - AN1288, Design Practices for Low-Power External Oscillators (DS01288)

7.2.2 INTERNAL CLOCK SOURCES

The device may be configured to use the internal oscillator block as the system clock by performing one of the following actions:

- Program the RSTOSC<2:0> bits in Configuration Words to select the INTOSC clock source, which will be used as the default system clock upon a device Reset.
- Write the NOSC<2:0> bits in the OSCCON1 register to switch the system clock source to the internal oscillator during run-time. See Section 7.3 "Clock Switching" for more information.

The function of the OSC2/CLKOUT pin is determined by the CLKOUTEN bit in Configuration Words.

The internal oscillator block has two independent oscillators that can produce two internal system clock sources.

- 1. The HFINTOSC (High-Frequency Internal Oscillator) is factory-calibrated and operates up to 32 MHz.
- The LFINTOSC (Low-Frequency Internal Oscillator) is factory-calibrated and operates at 31 kHz.

7.2.2.1 HFINTOSC

The High-Frequency Internal Oscillator (HFINTOSC) is a precision digitally-controlled internal clock source that produces a stable clock up to 32 MHz. The HFINTOSC can be enabled through one of the following methods:

- Programming the RSTOSC<2:0> bits in Configuration Word 1 to '110' (1 MHz) or '000' (32 MHz) to set the oscillator upon device Power-up or Reset
- Write to the NOSC<2:0> bits of the OSCCON1 register during run-time

The HFINTOSC frequency can be selected by setting the HFFRQ<3:0> bits of the OSCFRQ register.

The NDIV<3:0> bits of the OSCCON1 register allow for division of the output of the selected clock source by a range between 1:1 and 1:512.

7.2.2.2 2x PLL

The oscillator module contains a PLL that can be used with the HFINTOSC clock source to provide a system clock source. The input frequency to the PLL is limited to 8, 12, or 16 MHz, which will yield a system clock source of 16, 24, or 32 MHz, respectively.

The PLL may be enabled for use by one of two methods:

- Program the RSTOSC bits in the Configuration Word 1 to '000' to enable the HFINTOSC (32 MHz). This setting configures the HFFRQ<3:0> bits to '110' (16 MHz) and activates the 2x PLL.
- Write '000' to the NOSC<2:0> bits in the OSCCON1 register to enable the 2x PLL, and write the correct value into the HFFRQ<3:0> bits of the OSCFRQ register to select the desired system clock frequency. See Register 7-6 for more information.

7.2.2.3 Internal Oscillator Frequency Adjustment

The HFINTOSC and LFINTOSC internal oscillators are both factory-calibrated. TH HFINTOSC oscillator can be adjusted in software by writing to the OSCTUNE register (Register 7-3). OSCTUNE does not affect the LFINTOSC frequency.

The default value of the OSCTUNE register is 00h. The value is a 6-bit two's complement number. A value of 1Fh will provide an adjustment to the maximum frequency. A value of 20h will provide an adjustment to the minimum frequency.

When the OSCTUNE register is modified, the HFINTOSC oscillator frequency will begin shifting to the new frequency. Code execution continues during this shift. There is no indication that the shift has occurred.

7.2.2.4 LFINTOSC

The Low-Frequency Internal Oscillator (LFINTOSC) is a factory-calibrated 31 kHz internal clock source.

The LFINTOSC is the clock source for the Power-up Timer (PWRT), Watchdog Timer (WDT) and Fail-Safe Clock Monitor (FSCM). The LFINTOSC can also be used as the system clock, or as a clock or input source to certain peripherals.

The LFINTOSC is selected as the clock source through one of the following methods:

- Programming the RSTOSC<2:0> bits of Configuration Word 1 to enable LFINTOSC.
- Write to the NOSC<2:0> bits of the OSCCON1 register.

7.2.2.5 Oscillator Status and Manual Enable

The 'ready' status of each oscillator is displayed in the OSCSTAT1 register (Register 7-4). The oscillators can also be manually enabled through the OSCEN register (Register 7-5). Manual enables make it possible to verify the operation of the EXTOSC or SOSC crystal oscillators. This can be achieved by enabling the selected oscillator, then watching the corresponding 'ready' state of the oscillator in the OSCSTAT1 register.

7.3 Clock Switching

The system clock source can be switched between external and internal clock sources via software using the New Oscillator Source (NOSC) and New Divider Selection Request (NDIV) bits of the OSCCON1 register. The following clock sources can be selected:

- External Oscillator (EXTOSC)
- High-Frequency Internal Oscillator (HFINTOSC)
- Low-Frequency Internal Oscillator (LFINTOSC)
- Secondary Oscillator (SOSC)
- EXTOSC with 4x PLL
- HFINTOSC with 2x PLL

7.3.1 NEW OSCILLATOR SOURCE (NOSC) AND NEW DIVIDER SELECTION REQUEST (NDIV) BITS

The New Oscillator Source (NOSC) and New Divider Selection Request (NDIV) bits of the OSCCON1 register select the system clock source and frequencies that are used for the CPU and peripherals.

When the new values of NOSC<2:0> and NDIV<3:0> are written to OSCCON1, the current oscillator selection will continue to operate as the system clock while waiting for the new source to indicate that it is stable and ready. In some cases, the newly requested source may already be in use, and is ready immediately. In the case of a divider-only change, the new and old sources are the same and are ready immediately. The device may enter Sleep while waiting for the switch as described in Section 7.3.3 "Clock Switch and Sleep".

When the new oscillator is ready, the New Oscillator is Ready (NOSCR) bit of OSCCON3 and the Clock Switch Interrupt Flag (CSWIF) bit of PIR3 become set (CSWIF = 1). If Clock Switch Interrupts are enabled (CSWIE = 1), an interrupt will be generated at that time. The Oscillator Ready (ORDY) bit of OSCCON3 can also be polled to determine when the oscillator is ready in lieu of an interrupt.

If the Clock Switch Hold (CSWHOLD) bit of OSCCON3 is clear, the oscillator switch will occur when the New Oscillator Ready bit (NOSCR) is set and the interrupt (if enabled) will be serviced at the new oscillator setting. If CSWHOLD is set, the oscillator switch is suspended, while execution continues using the current (old) clock source. When the NOSCR bit is set, software will:

- Set CSWHOLD = 0 so the switch can complete, or
- Copy COSC into NOSC<2:0> to abandon the switch.

If DOZE is in effect, the switch occurs on the next clock cycle, whether or not the CPU is operating during that cycle.

Changing the clock post-divider without changing the clock source (i.e., changing Fosc from 1 MHz to 2 MHz) is handled in the same manner as a clock source change, as described previously. The clock source will already be active, so the switch is relatively quick. CSWHOLD must be clear (CSWHOLD = 0) for the switch to complete.

The current COSC and CDIV are indicated in the OSCCON2 register up to the moment when the switch actually occurs, at which time OSCCON2 is updated and ORDY is set. NOSCR is cleared by hardware to indicate that the switch is complete.

7.3.2 PLL INPUT SWITCH

Switching between the PLL and any non-PLL source is managed as described above. The input to the PLL is established when NOSC<2:0> selects the PLL, and maintained by the COSC setting.

When NOSC<2:0> and COSC select the PLL with different input sources, the system continues to run using the COSC setting, and the new source is enabled per NOSC<2:0>. When the new oscillator is ready (and CSWHOLD = 0), system operation is suspended while the PLL input is switched and the PLL acquires lock.


7.3.3 CLOCK SWITCH AND SLEEP

If OSCCON1 is written with a new value and the device is put to Sleep before the switch completes, the switch will not take place and the device will enter Sleep mode.

When the device wakes from Sleep and the CSWHOLD bit is clear, the device will wake with the 'new' clock active, and the Clock Switch Interrupt Flag bit (CSWIF) will be set.

When the device wakes from Sleep and the CSWHOLD bit is set, the device will wake with the 'old' clock active and the new clock will be requested again.

PIC16(L)F18326/18346







FIGURE 7-7: CLOCK SWITCH (CSWHOLD = 1)


PIC16(L)F18326/18346



7.4 Fail-Safe Clock Monitor

The Fail-Safe Clock Monitor (FSCM) allows the device to continue operating should the external oscillator fail. The FSCM is enabled by setting the FCMEN bit in the Configuration Words. The FSCM is applicable to all external Oscillator modes (LP, XT, HS, ECL, ECM, ECH, and Secondary Oscillator).

FIGURE 7-9: FSCM BLOCK DIAGRAM



7.4.1 FAIL-SAFE DETECTION

The FSCM module detects a failed oscillator by comparing the external oscillator to the FSCM sample clock. The sample clock is generated by dividing the LFINTOSC by 64 (see Figure 7-9). Inside the fail detector block is a latch. The external clock sets the latch on each falling edge of the external clock. The sample clock clears the latch on each rising edge of the sample clock. A failure is detected when an entire half-cycle of the sample clock elapses before the external clock goes low.

FIGURE 7-10: FSCM TIMING DIAGRAM

7.4.2 FAIL-SAFE OPERATION


When the external clock fails, the FSCM switches the device clock to the HFINTOSC at 1 MHz clock frequency and sets the bit flag OSFIF of the PIR3 register. Setting this flag will generate an interrupt if the OSFIE bit of the PIE3 register is also set. The device firmware can then take steps to mitigate the problems that may arise from a failed clock. The system clock will continue to be sourced from the internal clock source until the device firmware successfully restarts the external oscillator and switches back to external operation, by writing to the NOSC<2:0> and NDIV<3:0>bits of the OSCCON1 register.

7.4.3 FAIL-SAFE CONDITION CLEARING

The Fail-Safe condition is cleared after a Reset, executing a SLEEP instruction or changing the NOSC<2:0> and NDIV<3:0> bits of the OSCCON1 register. When switching to the external oscillator or external oscillator with PLL, the OST is restarted. While the OST is running, the device continues to operate from the INTOSC selected in OSCCON1. When the OST times out, the Fail-Safe condition is cleared after successfully switching to the external clock source. The OSFIF bit must be cleared prior to switching to the external clock source. If the Fail-Safe condition still exists, the OSFIF flag will again be set by hardware.

7.4.4 RESET OR WAKE-UP FROM SLEEP

The FSCM is designed to detect an oscillator failure after the Oscillator Start-up Timer (OST) has expired. The OST is used after waking up from Sleep and after any type of Reset. The OST is not used with the EC Clock modes so that the external clock signal can be stopped if required. Therefore, the device will always be executing code while the OST is operating when using one of the EC modes.



7.5 Register Definitions: Oscillator Control

KEOISTEK /	-1. 0000							
U-0	R/W-f/f ⁽¹⁾	R/W-f/f ⁽¹⁾	R/W-f/f ⁽¹⁾	R/W-q/q ⁽⁴⁾	R/W-q/q ⁽⁴⁾	R/W-q/q ⁽⁴⁾	R/W-q/q ⁽⁴⁾	
—		NOSC<2:0> ^{(2,3}	3)	NDIV<3:0> ^(2,3)				
bit 7	-						bit 0	

REGISTER 7-1: OSCCON1: OSCILLATOR CONTROL REGISTER 1

Legend:					
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'			
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets			
'1' = Bit is set	'0' = Bit is cleared	f = determined by fuse setting			
q = Reset value is determined by hardware					

bit 7	Unimplemented: Read as '0

bit 6-4	NOSC<2:0>: New Oscillator Source Request bits
	The setting requests a source oscillator and PLL combination per Table 7-1. POR value = RSTOSC (Register 5-2).

- bit 3-0 NDIV<3:0>: New Divider Selection Request bits The setting determines the new postscaler division ratio per Table 7-2.
- Note 1: The default value (f/f) is set equal to the RSTOSC Configuration bits.
 - 2: If NOSC is written with a reserved value (Table 7-1), the HFINTOSC will be automatically selected as the clock source.
 - 3: When CSWEN = 0, this register is read-only and cannot be changed from the POR value.
 - 4: When RSTOSC = 110 (HFINTOSC 1 MHz) the NDIV bits will default to '0100' upon Reset; for all other NOSC settings, the NVID bits will default to '0000' upon Reset.

REGISTER 7-2: OSCCON2: OSCILLATOR CONTROL REGISTER 2

U-0	R-q/q ⁽¹⁾						
—		COSC<2:0>			CDIV	<3:0>	
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Reset value is determined by hardware

 bit 7
 Unimplemented: Read as '0'

 bit 6-4
 COSC<2:0>: Current Oscillator Source Select bits (read-only) Indicates the current source oscillator and PLL combination per Table 7-1.

 bit 3-0
 CDIV<3:0>: Current Divider Select bits (read-only)

Indicates the current postscaler division ratio per Table 7-2.

Note 1: The Reset value (q/q) will match the NOSC<2:0>/NDIV<3:0> bits.

NOSC<2:0> COSC<2:0>	Clock Source
111	EXTOSC ⁽¹⁾
110	HFINTOSC
101	Reserved
100	LFINTOSC
011	SOSC
010	Reserved
001	EXTOSC with 4xPLL ⁽¹⁾
000	HFINTOSC with 2x PLL (32 MHz)

TABLE 7-1: NOSC/COSC BIT SETTINGS

Note 1: EXTOSC configured by the FEXTOSC bits of Configuration Word 1 (Register 5-1).

TABLE 7-2: NDIV/CDIV BIT SETTINGS

NDIV<3:0> CDIV<3:0>	Clock Divider
1111-1010	Reserved
1001	512
1000	256
0111	128
0110	64
0101	32
0100	16
0011	8
0010	4
0001	2
0000	1

REGISTER 7-3: OSCCON3: OSCILLATOR CONTROL REGISTER 3

R/W/HC-0/0	R/W-0/0	R/W-0/0	R-0/0	R-0/0	U-0	U-0	U-0
CSWHOLD	SOSCPWR	SOSCBE	ORDY	NOSCR	—	—	—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Reset value is determined by hardware

bit 7	CSWHOLD: Clock Switch Hold bit
	 1 = Clock switch will hold (with interrupt) when the oscillator selected by NOSC is ready 0 = Clock switch may proceed when the oscillator selected by NOSC is ready; if this bit is set at the time that NOSCR becomes '1', the switch and interrupt will occur.
bit 6	SOSCPWR: Secondary Oscillator Power Mode Select bit
	If SOSCBE = 0
	 Secondary oscillator operating in High-Power mode
	0 = Secondary oscillator operating in Low-Power mode
	If SOSCBE = 1
	x = Bit is ignored
bit 5	SOSCBE: Secondary Oscillator Bypass Enable bit
	 1 = Secondary oscillator SOSCI is configured as an external clock input (ST-buffer); SOSCO is not used.
	0 = Secondary oscillator is configured as a crystal oscillator using SOSCO and SOSCI pins.
bit 4	ORDY: Oscillator Ready bit (read-only)
	1 = OSCCON1 = OSCCON2; the current system clock is the clock specified by NOSC
	0 = A clock switch is in progress
bit 3	NOSCR: New Oscillator is Ready bit (read-only)
	 1 = A clock switch is in progress and the oscillator selected by NOSC indicates a Ready condition 0 = A clock switch is not in progress, or the NOSC-selected oscillator is not yet ready
bit 2-0	Unimplemented: Read as '0'
-	

R-q/q	R-q/q	U-0	R-q/q	R-q/q	R-q/q	U-0	R-q/q			
EXTOR	HFOR		LFOR	SOR	ADOR		PLLR			
bit 7							bit 0			
Legend:										
R = Readable		W = Writable			mented bit, reac					
u = Bit is unc	hanged	x = Bit is unk	nown	-n/n = Value	at POR and BO	R/Value at all o	other Resets			
'1' = Bit is set	t	'0' = Bit is cle	ared	q = Reset va	lue is determine	d by hardware	;			
bit 7		TOSC (external		ady bit						
		cillator is ready cillator is not er		t vet ready to h						
bit 6				it yet ready to t						
DILO		<pre>HFOR: HFINTOSC Oscillator Ready bit 1 = The oscillator is ready to be used</pre>								
		cillator is not er		ot yet ready to b	be used.					
bit 5	Unimpleme	nted: Read as	0'							
bit 4	LFOR: LFIN	TOSC Oscillato	r Ready bit							
		cillator is ready								
	0 = The os	cillator is not er	nabled, or is no	ot yet ready to l	be used.					
bit 3		dary Oscillator								
		cillator is ready		t vot roodv to l	hausad					
h # 0		cillator is not er		or yet ready to i	be used.					
bit 2		ADOR: ADCRC Oscillator Ready bit 1 = The oscillator is ready to be used								
		cillator is not er		ot yet ready to l	be used					
bit 1		nted: Read as		, , , , , , , , , , , , , , , , , , ,						
bit 0	PLLR: PLL i									
-		L is ready to be	eused							
		L is not enable		input source is	s not ready or th	ne PLL is not re	vhee			

REGISTER 7-4: OSCSTAT1: OSCILLATOR STATUS REGISTER 1

R/W-0/0	R/W-0/0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	U-0	U-0
EXTOEN	HFOEN	—	LFOEN	SOSCEN	ADOEN	—	—
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
u = Bit is unch	anged	x = Bit is unkr	nown	-n/n = Value a	at POR and BC	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is clea	ared				
bit 7	1 = EXTOSC 0 = EXTOSC	ternal Oscillato is explicitly ena may be enable	abled, operatin ed by another r	g as specified nodule	by FEXTOSC		
bit 6	1 = HFINTOS	NTOSC Oscilla C is explicitly e C may be ena	enabled, opera	ting as specifie	ed by OSCFRQ	(Register 7-6)	
bit 5	Unimplemen	ted: Read as '	0'				
bit 4	1 = LFINTOS	ITOSC (31 kHz C is explicitly e C may be enat	nabled		Enable bit		
bit 3	1 = Secondar	condary Oscilla y Oscillator is e y Oscillator ma	explicitly enabl	ed			
bit 2		DSC (600 kHz) s explicitly enal	oled		Enable bit		
	0 7.00001	hay be enabled	i by another m	odule			

REGISTER 7-5: OSCEN: OSCILLATOR MANUAL ENABLE REGISTER

-n/n = Value at POR and BOR/Value at all other Resets

REGISTER /-	6: USCr	OSCERQ: HEINTOSC FREQUENCE SELECTION REGISTER								
U-0	U-0	U-0	U-0	R/W-0/0	R/W-1/1	R/W-1/1	R/W-0/0			
—		— — — HFFRQ<3:0>								
bit 7							bit 0			
Legend:										
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'						

bit 7-4 Unimplemented: Read as '0'

u = Bit is unchanged

'1' = Bit is set

bit 3-0 **HFFRQ<3:0>:** HFINTOSC Frequency Selection bits

x = Bit is unknown

'0' = Bit is cleared

HFFRQ<3:0>	Nominal Freq. (MHz) (NOSC = 110)	2x PLL Freq. (MHz) (NOSC = 000)
0000	1	
0001	2	Reserved
0010	Reserved	Reserved
0011	4	
0100	8	16
0101	12	24
0110	16	32
0111	32	Reserved
1xxx	32	Reserved

					D M M M M		D // 0 / 0
U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
	—			HFTU	N<5:0>		
bit 7							bit C
Legend:							
R = Readab	ole bit	W = Writable	bit	U = Unimpler	nented bit, rea	d as '0'	
u = Bit is un	changed	x = Bit is unki	nown	-n/n = Value a	at POR and BC	R/Value at all	other Resets
'1' = Bit is se	et	'0' = Bit is cle	ared				
bit 7-6	Unimpleme	ented: Read as '	0'				
bit 5-0	-	>: HFINTOSC F		ning hits			
		Maximum frequ		ing bits			
	01 1110	Maximan noqu	oney				
	•						
	•						
	•						
	00 0001						
		Center frequence	v Oscillator m	odule is runnin	n at the calibrat	ed frequency (default value)
	11 1111	Conter nequence	y. Oscillator fi		g at the calibrat	ed inequency (
	•						
	•						
	•						
	10 0000 =	Minimum freque	ncv				
	10 00000-						

REGISTER 7-7: OSCTUNE: HFINTOSC TUNING REGISTER

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
OSCCON1		N	OSC<2:0>			NDIV	<3:0>		89
OSCCON2	—	C	OSC<2:0>			CDIV	<3:0>		89
OSCCON3	CWSHOLD	SOSCPWR	SOSCBE	ORDY	NOSCR	_	_	_	90
OSCSTAT1	EXTOR	HFOR	—	LFOR	SOR	ADOR	_	PLLR	91
OSCEN	EXTOEN	HFOEN	_	LFOEN	SOSCEN	ADOEN	_	_	92
OSCFRQ	_	—	_	_		HFFRO	Q<3:0>		93
OSCTUNE		_			HFTUN	N<5:0>			94

TABLE 7-3: SUMMARY OF REGISTERS ASSOCIATED WITH CLOCK SOURCES

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by clock sources.

TABLE 7-4: SUMMARY OF CONFIGURATION WORD WITH CLOCK SOURCES

Name	Bits	Bit -/7	Bit -/6	Bit 13/5	Bit 12/4	Bit 11/3	Bit 10/2	Bit 9/1	Bit 8/0	Register on Page
	13:8	_	_	FCMEN		CSWEN	_		CLKOUTEN	
CONFIG1	7:0	_	RSTOSC2	RSTOSC1	RSTOSC0	_	FEXTOSC2	FEXTOSC1	FEXTOSC0	64

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by clock sources.


8.0 INTERRUPTS

The interrupt feature allows certain events to preempt normal program flow. Firmware is used to determine the source of the interrupt and act accordingly. Some interrupts can be configured to wake the MCU from Sleep mode.

Many peripherals produce interrupts. Refer to the corresponding chapters for details.

A block diagram of the interrupt logic is shown in Figure 8-1.

FIGURE 8-1: INTERRUPT LOGIC	FIGURE 8-1:	INTERRUPT LOGIC
-----------------------------	-------------	-----------------



8.1 Operation

Interrupts are disabled upon any device Reset. They are enabled by setting the following bits:

- The GIE bit of the INTCON register
- The Interrupt Enable bit(s) for the specific interrupt event(s)
- The PEIE bit of the INTCON register (if the Interrupt Enable bit of the interrupt event is contained in the PIEx registers).

The PIR1, PIR2, PIR3 and PIR4 registers record individual interrupts via interrupt flag bits. Interrupt flag bits will be set, regardless of the status of the GIE, PEIE and individual interrupt enable bits.

The following events happen when an interrupt event occurs while the GIE bit is set:

- Current prefetched instruction is flushed
- GIE bit is cleared
- Current Program Counter (PC) is pushed onto the stack
- Critical registers are automatically saved to the shadow registers (See "Section 8.5 "Automatic Context Saving")
- PC is loaded with the interrupt vector 0004h

The firmware within the Interrupt Service Routine (ISR) may determine the source of the interrupt by polling the interrupt flag bits. The interrupt flag bits must be cleared before exiting the ISR to avoid repeated interrupts. Because the GIE bit is cleared, any interrupt that occurs while executing the ISR will be recorded through its interrupt flag, but will not cause the processor to redirect to the interrupt vector.

The RETFIE instruction exits the ISR by popping the previous address from the stack, restoring the saved context from the shadow registers and setting the GIE bit.

For additional information on a specific interrupt's operation, refer to its peripheral chapter.

Note 1:	Individual	inte	rrupt	flag	bits	s are	e set,
	regardless		the	state	of	any	other
	enable bits	•					


2: All interrupts will be ignored while the GIE bit is cleared. Any interrupt occurring while the GIE bit is clear will be serviced when the GIE bit is set again.

8.2 Interrupt Latency

Interrupt latency is defined as the time from when the interrupt event occurs to the time code execution at the interrupt vector begins. The latency for synchronous interrupts is three or four instruction cycles. The interrupt is sampled during Q1 of the instruction cycle. The actual interrupt latency then depends on the instruction that is executing at the time the interrupt is detected. See Figure 8-2 and Figure 8-3 for more details.

PIC16(L)F18326/18346

FIGURE 8-	2:	INTE	ERRUPT L	ATENCY					
									Rev. 10-000289E 11/29/2017
OSC1					∫	22 Q3 Q4	01 02 03 04	01 02 03 04	
CLKOUT		\							
INT pin		Va	lid Interrupt	1 Сус	le Instru	ction at	PC		
Fetch	PC -	1	PC	PC + 1	I (PC = 0x0004	PC = 0x0005	PC = 0x0006
Execute	PC - 2		PC - 1	PC	χ	NOP	NOP	PC = 0x0004	PC = 0x0005
			ideterminate Latency ⁽²⁾			ency			
				y time during r any time dur			ow, the actual lat	ency can vary.	



8.3 Interrupts During Sleep

All interrupts can be used to wake from Sleep. To wake from Sleep, the peripheral must be able to operate without the system clock. The interrupt source must have the appropriate Interrupt Enable bit(s) set prior to entering Sleep.

On waking from Sleep, if the GIE bit is also set, the processor will branch to the interrupt vector. Otherwise, the processor will continue executing instructions after the SLEEP instruction. The instruction directly after the SLEEP instruction will always be executed before branching to the ISR. Refer to Section 9.0 "Power-Saving Operation Modes" for more details.

8.4 INT Pin

The INT pin can be used to generate an asynchronous edge-triggered interrupt. This interrupt is enabled by setting the INTE bit of the PIE0 register. The INTEDG bit of the INTCON register determines on which edge the interrupt will occur. When the INTEDG bit is set, the rising edge will cause the interrupt. When the INTEDG bit is clear, the falling edge will cause the interrupt. The INTF bit of the PIR0 register will be set when a valid edge appears on the INT pin. If the GIE and INTE bits are also set, the processor will redirect program execution to the interrupt vector.

8.5 Automatic Context Saving

Upon entering an interrupt, the return PC address is saved on the stack. Additionally, the following registers are automatically saved in the shadow registers:

- W register
- STATUS register (except for TO and PD)
- BSR register
- FSR registers
- PCLATH register

Upon exiting the Interrupt Service Routine, these registers are automatically restored. Any modifications to these registers during the ISR will be lost. If modifications to any of these registers are desired, the corresponding shadow register will be modified and the value will be restored when exiting the ISR. The shadow registers are available in Bank 31 and are readable and writable. Depending on the user's application, other registers may also need to be saved.

8.6 Register Definitions: Interrupt Control

		-					
R/W/HS/H	C R/W-0/0	U-0	U-0	U-0	U-0	U-0	R/W-1/1
GIE	PEIE		_	_	_	_	INTEDG
bit 7							bit 0
Legend:							
R = Readab	ole bit	W = Writable	bit	U = Unimpler	nented bit, read	d as '0'	
u = Bit is unchanged x = Bit is unknown				-n/n = Value a	at POR and BC	R/Value at all o	other Resets
'1' = Bit is se					ire set	HC = Hardwa	are clear
bit 7	GIE: Global I	nterrupt Enable	bit				
	1 = Enables a	all active interru	ipts				
	0 = Disables	all interrupts					
bit 6		eral Interrupt E					
		all active periph all peripheral in		i			
bit 5-1		ted: Read as '	•				
-	•						
bit 0		errupt Edge Sel on rising edge o					
		on falling edge					
	•		F				
Note:	nterrupt flag bits a	ire set when an	interrupt				
	condition occurs, r	U					
	ts corresponding						
	Enable (GIE) bit o		•				
	Jser software appropriate interru	must ensu Int flag bits are					
	prior to enabling a						
<u>۲</u>	and to onability a	n inton apt.					

REGISTER 8-1: INTCON: INTERRUPT CONTROL REGISTER

U-0	U-0	R/W/HS-0/0	R/W-0/0	U-0	U-0	U-0	R/W/HS-0/0
—		TMR0IE	IOCIE		—	—	INTE
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is uncha	anged	x = Bit is unkr	nown	-n/n = Value a	at POR and BOI	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared	HS = Hardwa	are set		
bit 7-6	Unimplemen	ted: Read as ')'				
bit 5	TMROIE: TM	R0 Overflow Int	errupt Enable	e bit			
		the TMR0 inte	•				
	0 = Disables	s the TMR0 inte	errupt				
bit 4		upt-on-Change	•	ble bit			
		the IOC chang the IOC chang	/ 1				
bit 3-1		ted: Read as '					
	•						
bit 0		ternal Interrupt	0				
		the INT extern					
		s the INT extern	•				
Mate di The	average internet						

REGISTER 8-2: PIE0: PERIPHERAL INTERRUPT ENABLE REGISTER 0

Note 1: The external interrupt GPIO pin is selected by INTPPS (Register 13-1).

REGISTER 8	3-3: PIE1:	PERIPHERA	L INTERRUI	PT ENABLE	REGISTER 1		
R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE
bit 7	•	•	•	•	•	•	bit 0
Lovendi							
Legend: R = Readable	• hit	W = Writable	bit	U = Unimpler	nented bit, read	las '0'	
u = Bit is unch		x = Bit is unkr		-	at POR and BO		other Resets
'1' = Bit is set	•	'0' = Bit is cle					
			urcu				
bit 7	TMR1GIE: Ti	mer1 Gate Inte	rrupt Enable l	bit			
		the Timer1 gate	-				
		the Timer1 gate					
bit 6	ADIE: Analog	g-to-Digital Con	verter (ADC)	Interrupt Enabl	e bit		
		the ADC interru					
		the ADC interru	•				
bit 5		RT Receive Int					
		the EUSART re					
bit 4		RT Transmit Int	•				
		the EUSART tra					
	0 = Disables	the EUSART tr	ansmit interru	ipt			
bit 3	•	chronous Seria	•) Interrupt Enal	ble bit		
		the MSSP inter					
h # 0		the MSSP inter	•	nabla bit			
bit 2		SP1 Bus Collisi is collision inter	•				
		is collision inter		led			
bit 1		R2 to PR2 Mat	•				
	1 = Enables t	the Timer2 to P	R2 match inte	errupt			
	0 = Disables	the Timer2 to F	R2 match inte	errupt			
bit 0		er1 Overflow Ir					
		the Timer1 over					
	0 = Disables	the Timer1 ove	mow interrupt	[
Note: Bit	PEIE of the IN		must be				
	t to enable any						

REGISTER 8-3: PIE1: PERIPHERAL INTERRUPT ENABLE REGISTER 1

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE
bit 7							bit (
Legend:						(0)	
R = Readable b		W = Writable			nented bit, read		
u = Bit is uncha	anged	x = Bit is unkr		-n/n = Value a	at POR and BO	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared				
bit 7	TMR6IF: TM	R6 to PR6 Mate	ch Interrupt Fi	nable bit			
		PR6 match inte	•				
		PR6 match is r	•				
bit 6	C2IE: Compa	arator C2 Interro	upt Enable bit				
	•	the Comparato	•				
	0 = Disables	the Comparate	or C2 interrupt	t			
bit 5	C1IE: Compa	arator C1 Interr	upt Enable bit				
		the Comparato the Comparato					
bit 4		Interrupt Enab		L			
DIL 4		sk complete int		d			
		rrupt not enable		-			
bit 3	SSP2IE: Hos	t Synchronous	Serial Port (N	1SSP2) Interrup	ot Enable bit		
		he MSSP2 inte					
		the MSSP2 inte	•				
bit 2		SP2 Bus Collisi s collision inter		nable bit			
		s collision inter		led			
bit 1		R4 to PR4 Mate	•				
		PR4 match inte					
	0 = TMR4 to	PR4 match is r	ot enabled				
bit 0	NCO1IE: NC	O Interrupt Ena	able bit				
	1 = NCO roll	• • •					
bit 0		over interrupt e over interrupt n					

REGISTER 8-4: PIE2: PERIPHERAL INTERRUPT ENABLE REGISTER 2

Note: Bit PEIE of the INTCON register must be set to enable any peripheral interrupt.

	8-5: PIE3: I			I LNADLL	REGISTER 3		
R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
OSFIE	CSWIE	TMR3GIE	TMR3IE	CLC4IE	CLC3IE	CLC2IE	CLC1IE
bit 7							bit 0
Legend:							
R = Readabl		W = Writable	bit	•	mented bit, read		
u = Bit is unc	changed	x = Bit is unkr	own	-n/n = Value a	at POR and BO	R/Value at all c	other Resets
'1' = Bit is se	t	'0' = Bit is clea	ared				
bit 7	1 = Enables	ator Fail Interru the Oscillator F the Oscillator F	ail interrupt				
bit 6	1 = The clock	k Switch Comp < switch module < switch module	e interrupt is e	enabled			
bit 5	1 = Timer3 Ga	mer3 Gate Inte ate interrupt is ate interrupt is	enabled	oit			
bit 4	1 = TMR3 ove	R3 Overflow Int erflow interrupt erflow interrupt	is enabled				
bit 3	1 = CLC4 inte	24 Interrupt Flag errupt is enable errupt is not ena	d				
bit 2	CLC3IE: CLC 1 = CLC3 inte	3 Interrupt Flag errupt is enable errupt is not ena	g bit d				
bit 1	1 = CLC2 inte	2 Interrupt Ena errupt enabled errupt disabled	ble bit				
bit 0		1 Interrupt Ena errupt enabled	ble bit				

REGISTER 8-5: PIE3: PERIPHERAL INTERRUPT ENABLE REGISTER 3

Note: Bit PEIE of the INTCON register must be set to enable any peripheral interrupt.

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
CWG2IE	CWG1IE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE
bit 7							bit
Legend:			,				
R = Readable		W = Writable			mented bit, read		
u = Bit is unch	anged	x = Bit is unknown			at POR and BO	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared	HS = Hardwa	are set		
bit 7	1 = CWG2 inf	/G 2 Interrupt E terrupt enabled terrupt not enal					
bit 6	1 = CWG1 i	/G 1 Interrupt E nterrupt enable nterrupt not ena	d				
bit 5	TMR5GIE: Timer5 Gate Interrupt Enable bit 1 = TMR5 Gate interrupt is enabled 0 = TMR5 Gate interrupt is not enabled						
bit 4	TMR5IE: TMR5 Overflow Interrupt Enable bit 1 = TMR5 overflow interrupt is enabled 0 = TMR5 overflow interrupt is not enabled						
bit 3	CCP4IE: CCP4 Interrupt Enable bit 1 = CCP4 interrupt is enabled 0 = CCP4 interrupt is not enabled						
bit 2	CCP3IE: CCP3 Interrupt Enable bit 1 = CCP3 interrupt is enabled 0 = CCP3 interrupt is not enabled						
bit 1	CCP2IE: CCP2 Interrupt Enable bit 1 = CCP2 interrupt is enabled 0 = CCP2 interrupt is not enabled						
bit 0	CCP1IE: CCF	P1 Interrupt En Interrupt is enab	able bit led				

REGISTER 8-6: PIE4: PERIPHERAL INTERRUPT ENABLE REGISTER 4

set to enable any peripheral interrupt.

						-			
U-0	U-0	R/W/HS-0/0	R-0	U-0	U-0	U-0	R/W/HS-0/0		
—	-	TMR0IF	IOCIF ⁽¹⁾	—	—	—	INTF		
bit 7	bit 7						bit 0		
Legend:									
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'					
u = Bit is unch	anged	x = Bit is unkn	iown	-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is clea	ared	HS= Hardware Set					
bit 7-6	Unimplemented: Read as '0'								
bit 5	TMROIF: TMF	R0 Overflow Int	errupt Flag bi	t					
	1 = TMR0 register has overflowed (must be cleared in software)								
	0 = TMR0 register did not overflow								
bit 4	IOCIF: Interrupt-on-Change Interrupt Flag bit (read-only)								
1 = An enabled edge was detected by the IOC module. One of the IOCF bits is set.									
0 = No enabled edge is was detected by the IOC module. None of the IOCF bits is set.						et.			
	Pins are individually masked via IOCxP and IOCxN.								

REGISTER 8-7: PIR0: PERIPHERAL INTERRUPT REQUEST REGISTER 0

bit 3-1	Unimplemented: Read as '0'			
bit 0	INTF: INT External Interrupt Flag			

- INTF: INT External Interrupt Flag bit
 - 1 = The INT external interrupt occurred (must be cleared in software)
 - 0 = The INT external interrupt did not occur
- Note 1: The IOCIF bit is the logical OR of all the IOCAF-IOCCF flags. Therefore, to clear the IOCIF flag, application firmware must clear all of the IOCAF-IOCCF register bits.

Note:	Interrupt flag bits are set when an interrupt								
	condition occurs, regardless of the state of								
	its corresponding enable bit or the Global								
	Enable (GIE) bit of the INTCON register.								
	User software must ensure the								
	appropriate interrupt flag bits are cleared								
	prior to enabling an interrupt.								

R/W/HS-0/0		R/HS/HC-0	R-0	R/W/HS-0/0	R/W/HS-0/0	1 R/W/HS-0/0	R/W/HS-0/0		
TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF		
bit 7	7.Dii	T COIL	1741		DOLIII		bit C		
Legend:									
R = Readable	e bit	W = Writable	bit	•	nented bit, reac				
u = Bit is uncl	0	x = Bit is unknown		-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is clea	ared	HS = Hardwa	ire set				
bit 7	1 = The Time	ner1 Gate Inter 1 gate has gor 1 gate has not	ne inactive (tl	ne gate is close	d)				
bit 6	1 = The A/D c	ADIF: Analog-to-Digital Converter (ADC) Interrupt Flag bit 1 = The A/D conversion completed 0 = The A/D conversion is not completed							
bit 5	1 = The EUSA	RCIF: EUSART Receive Interrupt Flag bit (read-only) 1 = The EUSART1 receive buffer is not empty 0 = The EUSART1 receive buffer is empty							
bit 4	TXIF : EUSART Transmit Interrupt Flag bit (read-only) 1 = The EUSART1 transmit buffer is empty 0 = The EUSART1 transmit buffer is not empty								
bit 3	 SSP1IF: Synchronous Serial Port (MSSP) Interrupt Flag bit 1 = The Transmission/Reception/Bus Condition is complete (must be cleared in software) 0 = Waiting for the Transmission/Reception/Bus Condition in progress 								
bit 2	BCL1IF: MSSP Bus Collision Interrupt Flag bit 1 = A bus collision was detected (must be cleared in software) 0 = No bus collision was detected								
bit 1	TMR2IF: Timer2 to PR2 Interrupt Flag bit								
		PR2 match occ to PR2 match		be cleared in so	oftware)				
bit 0	TMR1IF: Timer1 Overflow Interrupt Flag bit								
		erflow occurred overflow occu		eared in softwar	e)				
co its Er	terrupt flag bits a ndition occurs, re corresponding e nable (GIE) bit o ser software	egardless of the enable bit or th	e state of e Global register.						

REGISTER 8-8: PIR1: PERIPHERAL INTERRUPT REQUEST REGISTER 1

appropriate interrupt flag bits are cleared

prior to enabling an interrupt.

R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0			
TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF			
bit 7		1		1			bit (
Legend:										
R = Readable	bit	W = Writable bit			mented bit, read					
u = Bit is unch	nanged	x = Bit is unknown		-n/n = Value at POR and BOR/Value at all other Resets						
'1' = Bit is set		'0' = Bit is cleared		HS = Hardware set						
bit 7	TMR6IF: TMR6 to PR6 Match Interrupt Flag bit 1 = TMR6 to PR6 match occurred (must be cleared in software) 0 = No TMR6 to PR6 match occurred									
bit 6		C2IF: Comparator C2 Interrupt Flag bit								
	1 = Comparat	or 2 interrupt a	isserted							
bit 5	C1IF: Comparator C1 Interrupt Flag bit									
	1 = Comparator 1 interrupt asserted 0 = Comparator 1 interrupt not asserted									
bit 4	NVMIF: NVM Interrupt Flag bit 1 = The NVM has completed a programming task 0 = NVM interrupt not asserted									
bit 3	SSP2IF: Host Synchronous Serial Port (MSSP2) Interrupt Flag bit 1 = The Transmission/Reception/Bus Condition is complete (must be cleared in software) 0 = Waiting for the Transmission/Reception/Bus Condition in progress									
bit 2	BCL2IF: MSSP2 Bus Collision Interrupt Flag bit 1 = A bus collision was detected (must be cleared in software) 0 = No bus collision was detected									
bit 1	 TMR4IF: TMR4 to PR4 Match Interrupt Flag bit 1 = TMR4 to PR4 match occurred (must be cleared in software) 0 = No TMR4 to PR4 match occurred 									
bit 0	NCO1IF: NCO Interrupt Flag bit									
	 1 = The NCO has rolled over. 0 = No NCO interrupt is asserted. 									
	0 = NO NCO	interrupt is ass	erted.							
co its	errupt flag bits a ndition occurs, re corresponding e able (GIE) bit c	egardless of the	e state of le Global							

REGISTER 8-9: PIR2: PERIPHERAL INTERRUPT REQUEST REGISTER 2

Note: Interrupt flag bits are set when an interrupt condition occurs, regardless of the state of its corresponding enable bit or the Global Enable (GIE) bit of the INTCON register. User software must ensure the appropriate interrupt flag bits are cleared prior to enabling an interrupt.

	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0
OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF
bit 7							bit (
Legend:						(0)	
R = Readable I		W = Writable		•	nented bit, read		
u = Bit is uncha	inged	x = Bit is unkn			at POR and BO	R/Value at all c	ther Resets
1' = Bit is set		'0' = Bit is clea	ared	HS = Hardwa	ire set		
bit 7		otor Eqil Sofo I	ntorrunt Elog I	ait			
		ator Fail-Safe I Clock Monitor ı			Logoillator		
		scillator operat			i Oscillator		
bit 6		Switch Comp	•	-lag bit			
					vitch; new oscilla	ator is ready	
	0 = The clock	switch module	has not comp	oleted clock sw	vitch		
bit 5		ner3 Gate Inter					
		3 gate has gon					
		3 gate has not	-				
bit 4		R3 Overflow Int					
		erflow occurred	•	ared in softwar	e)		
		overflow occur					
bit 3		4 Interrupt Flag	-				
	1 = The CLC4 0 = No CLC4	OUT interrupt	condition has	been met			
bit 2		3 Interrupt Flag	n hit				
		Sout interrupt	-	heen met			
	0 = No CLC3	•	Condition nas	been met			
bit 1		2 Interrupt Flag	n bit				
		OUT interrupt	-	been met			
	0 = No CLC2						
bit 0	CLC1IF: CLC	1 Interrupt Flag	g bit				
	1 = The CLC1 0 = No CLC1	OUT interrupt	condition has	been met			

REGISTER 8-10: PIR3: PERIPHERAL INTERRUPT REQUEST REGISTER 3

Note:	Interrupt flag bits are set when an interrupt condition occurs, regardless of the state of its corresponding enable bit or the Global
	Enable (GIE) bit of the INTCON register.
	User software must ensure the
	appropriate interrupt flag bits are cleared
	prior to enabling an interrupt.

REGISTER 8-					UPT REQUES			
R/W/HS-0/0	R/W/H	S-0/0	R/W/HS-0/0	R/W/HS-0/	/0 R/W/HS-0/0	R/W/HS-0/	0 R/W/HS-0/0	R/W/HS-0/0
CWG2IF	CWG	1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF
bit 7								bit (
Legend:								
R = Readable	bit		W = Writable	bit	U = Unimpler	nented bit, re	ad as '0'	
u = Bit is uncha	anged		x = Bit is unkr	nown	-		3OR/Value at all c	other Resets
'1' = Bit is set	•		'0' = Bit is clea	ared	HS = Hardwa	are set		
bit 7 bit 6	1 = CW 0 = CW CWG1I	G2 has G2 is c F: CW0	G 2 Interrupt F s gone into shi operating norm G1 Interrupt FI	utdown nally, or intei lag bit	rrupt cleared			
bit 5	0 = CW TMR5G	G1 is c i lF: Tim 1 = The	s gone into shu operating norm ner5 Gate Intel e TMR5 gate h e TMR5 gate h	nally, or inter rrupt Flag b nas gone ina	it active (the gate i	s closed).		
bit 4 bit 3	TMR5IF	: Time 1 = TM 0 = No	r5 Overflow In	terrupt Flag occurred (mu w occurred		software)		
DIL O				g bit	ССРМ М			
	Value		Capture		COMM		PWI	И
	1		ire occurred be cleared in		Compare match (must be cleared	occurred	Output trailing ed (must be cleared	dge occurred
	0	Captu	ire did not occ	ur	Compare match occur	did not	Output trailing ed occur	lge did not
bit 2	CCP3IF	CCP	3 Interrupt Fla	g bit				
	Value				CCPM N	lode		
	Value		Capture		Compa	are	PWM	
	1		ire occurred be cleared in		Compare match (must be cleared		Output trailing e (must be cleared	
	-	1			_			

Compare match did not

occur

REGISTER 8-11: PIR4: PERIPHERAL INTERRUPT REQUEST REGISTER 4

0

Capture did not occur

Output trailing edge did not

occur

REGISTER 8-11: PIR4: PERIPHERAL INTERRUPT REQUEST REGISTER 4 (CONTINUED)

bit 1

CCP2IF: CCP2 Interrupt Flag bit

Value		CCPM Mode	
value	Capture	Capture Compare	
1	Capture occurred (must be cleared in software)	Compare match occurred (must be cleared in software)	Output trailing edge occurred (must be cleared in software)
0	Capture did not occur	Compare match did not occur	Output trailing edge did not occur

bit 0

CCP1IF: CCP1 Interrupt Flag bit

Value	CCPM Mode						
value	Capture	Compare	PWM				
1	Capture occurred (must be cleared in software)	Compare match occurred (must be cleared in software)	Output trailing edge occurred (must be cleared in software)				
0	Capture did not occur	Compare match did not occur	Output trailing edge did not occur				

Note: Interrupt flag bits are set when an interrupt condition occurs, regardless of the state of its corresponding enable bit or the Global Enable (GIE) bit of the INTCON register. User software must ensure the appropriate interrupt flag bits are cleared prior to enabling an interrupt.

TABLE 8-1: SUMMARY OF REGISTERS ASSOCIATED WITH INTERRUPTS

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
INTCON	GIE	PEIE	_					INTEDG	100
PIE0	—	_	TMR0IE	IOCIE	_	—	_	INTE	101
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103
PIE3	OSFIE	CSWIE	TMR3GIE	TMR3IE	CLC4IE	CLC3IE	CLC2IE	CLC1IE	104
PIE4	CWG2IE	CWG1IE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE	105
PIR0	—	_	TMR0IF	IOCIF	_	—	_	INTF	106
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108
PIR3	OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF	109
PIR4	CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	110

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by interrupts.

9.0 POWER-SAVING OPERATION MODES


The purpose of the Power-Down modes is to reduce power consumption. There are three Power-Down modes: Doze mode, Idle mode and Sleep mode.

9.1 Doze Mode

Doze mode allows for power savings by reducing CPU operation and program memory access, without affecting peripheral operation. Doze mode differs from Sleep mode because the system oscillators continue to operate, while only the CPU and program memory are affected. The reduced execution saves power by eliminating unnecessary operations within the CPU and memory.

When the Doze Enable (DOZEN) bit is set (DOZEN = 1), the CPU executes only one instruction cycle out of every N cycles as defined by the DOZE<2:0> bits of the CPUDOZE register. For example, if DOZE<2:0> = 100, the instruction cycle ratio is 1:32. The CPU and memory execute for one instruction cycle and then lay idle for 31 instruction cycles. During the unused cycles, the peripherals continue to operate at the system clock speed.





9.1.1 DOZE OPERATION

The Doze operation is illustrated in Figure 9-1. For this example:

- Doze enable (DOZEN) bit set (DOZEN = 1)
- DOZE<2:0> = 001 (1:4) ratio
- Recover-on-Interrupt (ROI) bit set (ROI = 1)

As with normal operation, the program memory fetches for the next instruction cycle. The instruction clocks to the peripherals continue throughout.

9.1.2 INTERRUPTS DURING DOZE

If an interrupt occurs and the Recover-on-Interrupt (ROI) bit is cleared (ROI = 0) at the time of the interrupt, the Interrupt Service Routine (ISR) continues to execute at the rate selected by DOZE<2:0>. Interrupt latency is extended by the DOZE<2:0> ratio.

If an interrupt occurs and the ROI bit is set (ROI = 1) at the time of the interrupt, the DOZEN bit is cleared and the CPU executes at full speed. The prefetched instruction is executed and then the interrupt vector sequence is executed. In Figure 9-1, the interrupt occurs during the 2nd instruction cycle of the Doze period, and immediately brings the CPU out of Doze. If the Doze-on-Exit (DOE) bit is set (DOE = 1) when the RETFIE operation is executed, DOZEN is set, and the CPU executes at the reduced rate based on the DOZE<2:0> ratio.

9.1.3 IDLE MODE

When the IDLE Enable (IDLEN) bit is cleared (IDLEN = 0), the SLEEP instruction will put the device into full Sleep mode (see Section 9.2 "Sleep Mode"). When IDLEN is set (IDLEN = 1), the SLEEP instruction will put the device into Idle mode. In Idle mode, the CPU and memory operations are halted, but the peripheral clocks continue to run. This mode is similar to Doze mode, except that in Idle both the CPU and program memory are shut off.

Note: Peripherals using FOSC will continue running while in Idle (but not in Sleep).

Note: If CLKOUT is enabled (CLKOUT = 0, Configuration Word 1), the output will continue operating while in Idle.

9.1.3.1 Idle and Interrupts

Idle mode ends when an interrupt occurs (even if GIE = 0), but IDLEN is not changed. The device can re-enter Idle by executing the SLEEP instruction.

If Recover-on-Interrupt is enabled (ROI = 1), the interrupt that brings the device out of Idle also restores full-speed CPU execution when Doze is also enabled.

9.1.3.2 Idle and WDT

When in Idle, the WDT Reset is blocked and will instead wake the device. The WDT wake-up is not an interrupt, therefore ROI does not apply.

Note: The WDT can bring the device out of Idle, in the same way it brings the device out of Sleep. The DOZEN bit is not affected.

9.2 Sleep Mode

Sleep mode is entered by executing the SLEEP instruction, while the Idle Enable (IDLEN) bit of the CPUDOZE register is cleared (IDLEN = 0). If the SLEEP instruction is executed while the IDLEN bit is set (IDLEN = 1), the CPU will enter the Idle mode (Section 9.2.3 "Low-Power Sleep Mode").

Upon entering Sleep mode, the following conditions exist:

- 1. Resets other than WDT are not affected by Sleep mode; WDT will be cleared but keeps running if enabled for operation during Sleep.
- 2. The \overline{PD} bit of the STATUS register is cleared.
- 3. The $\overline{\text{TO}}$ bit of the STATUS register is set.
- 4. The CPU and System clocks are disabled.
- 5. 31 kHz LFINTOSC, HFINTOSC and SOSC will remain enabled if any peripheral has requested them as a clock source or if the HFOEN, LFOEN, or SOSCEN bits of the OSCEN register are set.
- ADC is unaffected if the dedicated ADCRC oscillator is selected. When the ADC clock is something other than ADCRC, a SLEEP instruction causes the present conversion to be aborted and the ADC module is turned off, although the ADON bit remains active.
- 7. I/O ports maintain the status they had before SLEEP was executed (driving high, low, or high-impedance) only if no peripheral connected to the I/O port is active.

Refer to individual chapters for more details on peripheral operation during Sleep.

To minimize current consumption, consider the following conditions:

- I/O pins must not be floating
- External circuitry sinking current from I/O pins
- Internal circuitry sourcing current from I/O pins
- Current draw from pins with internal weak pull-ups
- Modules using any oscillator

I/O pins that are high-impedance inputs must be pulled to VDD or VSS externally to avoid switching currents caused by floating inputs.

Examples of internal circuitry that might be sourcing current include modules such as the DAC and FVR modules. See Section 24.0 "5-bit Digital-to-Analog Converter (DAC1) Module" and Section 16.0 "Fixed Voltage Reference (FVR)" for more information on these modules.

9.2.1 WAKE-UP FROM SLEEP

The device can wake-up from Sleep through one of the following events:

- 1. External Reset input on MCLR pin, if enabled
- 2. BOR Reset, if enabled.
- 3. POR Reset.
- 4. Watchdog Timer, if enabled
- 5. Interrupts by peripherals capable of running during Sleep (see individual peripheral for more information).

The first three events will cause a device Reset. The last two events are considered a continuation of program execution. To determine whether a device Reset or wake-up event occurred, refer to Section 6.11 "Determining the Cause of a Reset".

The WDT is cleared when the device wakes-up from Sleep, regardless of the source of wake-up.

9.2.2 WAKE-UP USING INTERRUPTS

When global interrupts are disabled (GIE cleared) and any interrupt source has both its interrupt enable bit and interrupt flag bit set, one of the following will occur:

- If the interrupt occurs **before** the execution of a SLEEP instruction
 - SLEEP instruction will execute as a NOP
 - <u>WD</u>T and WDT prescaler will not be cleared
 - TO bit of the STATUS register will not be set
 - PD bit of the STATUS register will not be cleared
- If the interrupt occurs **during or after** the execution of a **SLEEP** instruction
 - SLEEP instruction will be completely executed
 - Device will immediately wake-up from Sleep
 - WDT and WDT prescaler will be cleared
 - TO bit of the STATUS register will be set
 - PD bit of the STATUS register will be cleared

Even if the flag bits were checked before executing a SLEEP instruction, it may be possible for flag bits to become set before the SLEEP instruction completes. To determine whether a SLEEP instruction executed, test the PD bit. If the PD bit is set, the SLEEP instruction was executed as a NOP.

FIGURE 9-2	2: WAK	E-UP FROM	I SLEEP	THRC	UGH INTER	RUPT		
CLKIN ⁽¹⁾ CLKOUT ⁽²⁾		Q1 Q2 Q3 Q4 ~		Tost(3)		Q1 Q2 Q3 Q4 /~_/~_/~_/ //	Q1 Q2 Q3 Q4 ////////////////////////////////////	Q1 Q2 Q3 Q4 ~
Interrupt flag					Interrupt Laten	cy ⁽⁴⁾	· · · · · · · · · · · · · · · · · · · ·	
GIE bit (INTCON reg.).		Processor in					
nstruction Flow PC	, <u>χ ΡC</u>	(PC + 1	Х РС	+ 2	X PC + 2	X PC + 2	X 0004h	X 0005h
Instruction [Fetched	Inst(PC) = Sleep	Inst(PC + 1)	1 1 1		Inst(PC + 2)		Inst(0004h)	Inst(0005h)
Instruction { Executed {	Inst(PC - 1)	Sleep	1 1 1		Inst(PC + 1)	Forced NOP	Forced NOP	Inst(0004h)
2: 3:	External clock. Higl CLKOUT is shown Tost = 1024 Tosc. GIE = 1 assumed.	here for timing re This delay does	ference. not apply to E	C and IN			execution will con	tinue in-line.

9.2.3 LOW-POWER SLEEP MODE

The PIC16F18326/18346 device contains an internal Low Dropout (LDO) voltage regulator, which allows the device I/O pins to operate at voltages up to 5.5V while the internal device logic operates at a lower voltage. The LDO and its associated reference circuitry must remain active when the device is in Sleep mode.

The PIC16F18326/18346 allows the user to optimize the operating current in Sleep, depending on the application requirements.

Low-Power Sleep mode can be selected by setting the VREGPM bit of the VREGCON register. Depending on the configuration of this bit, the LDO and reference circuitry are placed in a Low-Power state when the device is in Sleep.

9.2.3.1 Sleep Current vs. Wake-up Time

In the default operating mode, the LDO and reference circuitry remain in the normal configuration while in Sleep. The device is able to exit Sleep mode quickly since all circuits remain active. In Low-Power Sleep mode, when waking-up from Sleep, an extra delay time is required for these circuits to return to the normal configuration and stabilize.

The Low-Power Sleep mode is beneficial for applications that stay in Sleep mode for long periods of time. The Normal mode is beneficial for applications that need to wake from Sleep quickly and frequently.

9.2.3.2 Peripheral Usage in Sleep

Some peripherals that can operate in Sleep mode will not operate properly with the Low-Power Sleep mode selected. The Low-Power Sleep mode is intended for use with these peripherals:

- Brown-out Reset (BOR)
- Watchdog Timer (WDT)
- External interrupt pin/Interrupt-on-change pins
- Timer 1 (with external clock source)

It is the responsibility of the end user to determine what is acceptable for their application when setting the VREGPM settings to ensure operation in Sleep.

Note: The PIC16LF18326/18346 does not have a configurable Low-Power Sleep mode. PIC16LF18326/18346 is an unregulated device and is always in the lowest power state when in Sleep, with no wake-up time penalty. This device has a lower maximum VDD and I/O voltage than the PIC16F18326/18346. See Section 35.0 "Electrical Specifications" for more information.

9.3 Register Definitions: Voltage Regulator Control

'0' = Bit is cleared

REGISTER 9-1: VREGCON: VOLTAGE REGULATOR CONTROL REGISTER⁽¹⁾

U-0	U-0	U-0	U-0	U-0	U-0	R/W-0/0	R/W-1/1
	—	—	_	—	—	VREGPM	Reserved
bit 7							bit 0
Legend:							
R = Readable bit		W = Writable bi	it	U = Unimplem	ented bit, read as	'0'	
u = Bit is unchanged x = Bit is unknown			-n/n = Value at POR and BOR/Value at all other Resets				

bit 7-2	Unimplemented: Read as '0'
bit 1	VREGPM: Voltage Regulator Power Mode Selection bit
	1 = Low-Power Sleep mode enabled in Sleep ⁽²⁾ ; Draws lowest current in Sleep, slower wake-up
	0 = Normal-Power Sleep mode enabled in Sleep ⁽²⁾ ; Draws higher current in Sleep, faster wake-up
bit 0	Reserved: Read as '1'. Maintain this bit set.

Note 1: PIC16F18326/18346 only.

'1' = Bit is set

2: See Section 35.0 "Electrical Specifications".

REGISTER 9-2: CPUDOZE: DOZE AND IDLE REGISTER

R/W-0/u	R/W/HC/HS-0/0	R/W-0/0	R/W-0/0	U-0	R/W-0/0	R/W-0/0	R/W-0/0
IDLEN	DOZEN ^(1,2)	ROI	DOE	—		DOZE<2:0>	
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7	IDLEN: Idle Enable bit 1 = A SLEEP instruction inhibits the CPU clock, but not the peripheral clock(s)
	0 = A SLEEP instruction places the device into Full-Sleep mode
bit 6	 DOZEN: Doze Enable bit^(1,2) 1 = The CPU executes instruction cycles according to Doze setting 0 = The CPU executes all instruction cycles (fastest, highest power operation)
bit 5	 ROI: Recover-on-Interrupt bit 1 = Entering the Interrupt Service Routine (ISR) makes DOZEN = 0 bit, bringing the CPU to full-speed operation. 0 = Interrupt entry does not change DOZEN
bit 4	 DOE: Doze-on-Exit bit 1 = Executing RETFIE makes DOZEN = 1, bringing the CPU to reduced speed operation. 0 = RETFIE does not change DOZEN
bit 3	Unimplemented: Read as '0'
bit 2-0	DOZE<2:0>: Ratio of CPU Instruction Cycles to Peripheral Instruction Cycles 111 = 1:256 110 = 1:128 101 = 1:64 100 = 1:32 011 = 1:16 010 = 1:8 001 = 1:4 000 = 1:2
Note 1: 2:	When ROI = 1 or DOE = 1, DOZEN is changed by hardware interrupt entry and/or exit. Entering ICD overrides DOZEN, returning the CPU to full execution speed; this bit is not affected.

	ABLE 9-1. SUMMART OF REGISTERS ASSOCIATED WITH FOWER-DOWN MODE									
Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page	
INTCON	GIE	PEIE	—	—	—			INTEDG	100	
PIE0	—		TMR0IE	IOCIE	—	_	_	INTE	101	
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102	
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103	
PIE3	OSFIE	CSWIE	TMR3GIE	TMR3IE	CLC4IE	CLC3IE	CLC2IE	CLC1IE	104	
PIE4	CWG2IE	CWG1IE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE	105	
PIR0	—	—	TMR0IF	IOCIF	_	_	_	INTF	106	
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107	
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108	
PIR3	OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF	109	
PIR4	CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	110	
IOCAP			IOCAP5	IOCAP4	IOCAP3	IOCAP2	IOCAP1	IOCAP0	174	
IOCAN	—		IOCAN5	IOCAN4	IOCAN3	IOCAN2	IOCAN1	IOCAN0	174	
IOCAF	_	_	IOCAF5	IOCAF4	IOCAF3	IOCAF2	IOCAF1	IOCAF0	175	
IOCBP ⁽¹⁾	IOCBP7	IOCBP6	IOCBP5	IOCBP4	—	_	_	_	175	
IOCBN ⁽¹⁾	IOCBN7	IOCBN6	IOCBN5	IOCBN4	—	_	_	_	176	
IOCBF ⁽¹⁾	IOCBF7	IOCBF6	IOCBF5	IOCBF4	—	_	_	_	176	
IOCCP	IOCCP7 ⁽¹⁾	IOCCP6 ⁽¹⁾	IOCCP5	IOCCP4	IOCCP3	IOCCP2	IOCCP1	IOCCP0	177	
IOCCN	IOCCN7 ⁽¹⁾	IOCCN6 ⁽¹⁾	IOCCN5	IOCCN4	IOCCN3	IOCCN2	IOCCN1	IOCCN0	177	
IOCCF	IOCCF7 ⁽¹⁾	IOCCF6 ⁽¹⁾	IOCCF5	IOCCF4	IOCCF3	IOCCF2	IOCCF1	IOCCF0	178	
STATUS				TO	PD	Z	DC	С	30	
VREGCON ⁽²⁾	_	_	_	—	_	—	VREGPM	—	117	
CPUDOZE	IDLEN	DOZEN	ROI	DOE	_	— DOZE<2:0>				
WDTCON	_	_		WDTPS<4:0> SWDTEN						

TABLE 9-1: SUMMARY OF REGISTERS ASSOCIATED WITH POWER-DOWN MODE

Legend: — = unimplemented location, read as '0'. Shaded cells are not used in Power-Down mode.

Note 1: PIC16(L)F18346 only.

2: PIC16F18326/18346 only.


10.0 WATCHDOG TIMER (WDT)

The Watchdog Timer is a system timer that generates a Reset if the firmware does not issue a CLRWDT instruction within the time-out period. The Watchdog Timer is typically used to recover the system from unexpected events.

The WDT has the following features:

- Independent clock source
- Multiple operating modes
- WDT is always ON
- WDT is OFF when in Sleep
- WDT is controlled by software
- WDT is always OFF
- Configurable time-out period is from 1 ms to 256 seconds (nominal)
- Multiple WDT clearing conditions
- Operation during Sleep

FIGURE 10-1: WATCHDOG TIMER BLOCK DIAGRAM



10.1 Independent Clock Source

The WDT derives its time base from the 31 kHz LFINTOSC internal oscillator. Time intervals in this chapter are based on a nominal interval of 1 ms. See Table 35-8 for the LFINTOSC specification.

10.2 WDT Operating Modes

The Watchdog Timer module has four operating modes controlled by the WDTE<1:0> bits in Configuration Words (see Table 10-1).

10.2.1 WDT IS ALWAYS ON

When the WDTE bits of Configuration Words are set to '11', the WDT is always ON.

WDT protection is active during Sleep.

10.2.2 WDT IS OFF IN SLEEP

When the WDTE bits of Configuration Words are set to '10', the WDT is on, except in Sleep.

WDT protection is not active during Sleep.

10.2.3 WDT CONTROLLED BY SOFTWARE

When the WDTE bits of Configuration Words are set to '01', the WDT is controlled by the SWDTEN bit of the WDTCON register.

WDT protection is unchanged by Sleep. See Table 10-1 for more details.

10.2.4 WDT IS ALWAYS OFF

When the WDTE bits are set to '00', the WDT is disabled, and the SWDTEN bit of the WDTCON is ignored.

WDTE<1:0>	SWDTEN	Device Mode	WDT Mode
11	Х	Х	Active
1.0		Awake	Active
10	Х	Sleep	Disabled
0.1	1		Active
01	0	Х	Disabled
00	Х	Х	Disabled

TABLE 10-1: WDT OPERATING MODES

TABLE 10-2: WDT CLEARING CONDITIONS

10.3 Time-out Period

The WDTPS<4:0> bits of the WDTCON register set the time-out period from 1 ms to 256 seconds (nominal). After a Reset, the default time-out period is two seconds.

10.4 Clearing the WDT

The WDT is cleared when any of the following conditions occur:

- Any Reset
- CLRWDT instruction is executed
- Device enters Sleep
- · Device wakes up from Sleep due to an interrupt
- Oscillator fail
- WDT is disabled
- Oscillator Start-up Timer (OST) is running

See Table 10-2 for more information.

10.5 Operation During Sleep

When the device enters Sleep, the WDT is cleared. If the WDT is enabled during Sleep, the WDT resumes counting.

When the device exits Sleep, the WDT is cleared again. The WDT remains clear until the OST, if enabled, completes. See **Section 7.0** "Oscillator **Module**" for more information on the OST.

When a WDT time-out occurs while the device is in Sleep, no Reset is generated. Instead, the device wakes up and resumes operation. The $\overline{\text{TO}}$ and $\overline{\text{PD}}$ bits in the STATUS register are changed to indicate the event. See STATUS Register (Register 4-1) for more information.

Conditions	WDT
WDTE = 00	Cleared and Disabled
WDTE = 01 and SWDTEN = 0	Cleared and Disabled
Exit Sleep due to a Reset + System Clock = XT, HS, LP	Cleared until the end of OST
Exit Sleep due to a Reset + System Clock = HFINTOSC, LFINTOSC, EC, SOSC	Cleared until the end of OST
Exit Sleep due to an interrupt	
Enter Sleep	
CLRWDT Command	Cleared
Oscillator Failure (see Section 7.4 "Fail-Safe Clock Monitor")	
System Reset	
Any clock switch or divider change (see Section 7.3 "Clock Switching")	Unaffected

Register Definitions: Watchdog Control 10.6

- -~ .

U-0	U-0	R/W-0/0	R/W-1/1	R/W-0/0	R/W-1/1	R/W-1/1	R/W-0/0				
				WDTPS<4:0>(1)		SWDTEN				
pit 7							bit C				
_egend:											
R = Readabl	e bit	W = Writable	bit	U = Unimplem	ented bit, rea	d as '0'					
u = Bit is unc	hanged	x = Bit is unkr	nown	•		OR/Value at all	other Resets				
'1' = Bit is se	0	'0' = Bit is clea	ared		-						
	-										
bit 7-6	Unimpleme	ented: Read as '	0'								
bit 5-1	WDTPS<4:	WDTPS<4:0>: Watchdog Timer Period Select bits ⁽¹⁾									
	Bit Value =	Bit Value = Prescale Rate									
	11111 = R	eserved. Result	s in minimum	interval (1:32)							
	•										
	•										
	•	• 10011 = Reserved. Results in minimum interval (1:32)									
	10011 – R										
	10010 = 1	:8388608 (2 ²³) (Interval 256s	nominal)							
	10001 = 1	$10001 = 1:4194304 (2^{22}) (Interval 128s nominal)$									
	10000 = 1	$10001 = 1:4194304 (2^{22}) (Interval 128s nominal) 10000 = 1:2097152 (2^{21}) (Interval 64s nominal) 01111 = 1:1048576 (2^{20}) (Interval 32s nominal) 01111 = 1:1048576 (2^{20}) (1nterval 32s nominal) 0111 = 1:1048576 (2^{20}) (1nterval 32s nominal) 011 = 1:1048576 (2^{20}) (1n$									
	01111 = 1	$01111 = 1:1048576 (2^{20}) (Interval 32s nominal)$									
	01110 = 1	$01110 = 1:524288 (2^{19}) (Interval 16s nominal) 01101 = 1:524288 (2^{19}) (Interval 16s nominal)$									
	$01101 = 1:262144 (2^{18})$ (Interval 8s nominal) $01100 = 1:124072 (2^{17})$ (Interval 4s nominal)										
	01100 = 1:131072 (2 ¹⁷) (Interval 4s nominal) 01011 = 1:65536 (Interval 2s nominal) (Reset value)										
		01011 = 1:65536 (Interval 2s nominal) (Reset value) 01010 = 1:32768 (Interval 1s nominal)									
		01001 = 1.32700 (interval 15 hominal) 01001 = 1.16384 (interval 512 ms nominal)									
		01000 = 1:8192 (Interval 256 ms nominal)									
		00111 = 1:4096 (Interval 128 ms nominal)									
		00110 = 1:2048 (Interval 64 ms nominal)									
		00101 = 1:1024 (Interval 32 ms nominal)									
		00100 = 1:512 (Interval 16 ms nominal) 00011 = 1:256 (Interval 8 ms nominal)									
		:128 (Interval 8 r :128 (Interval 4 r									
		:64 (Interval 2 m									
		:32 (Interval 1 m									
oit O		Software Enable/		/atchdog Timer b	bit						
	If WDTE<1:			5							
		is ignored.									
	If WDTE<1:										
		DT is turned on									
		DT is turned off									
	If WDTE<1:										
	i his bit	is ignored.									



IABLE IV V.								-11	
Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
STATUS	_		_	TO	PD	Z	DC	С	30
WDTCON	_			١	SWDTEN	121			

TABLE 10-3: SUMMARY OF REGISTERS ASSOCIATED WITH WATCHDOG TIMER

Legend: x = unknown, u = unchanged, – = unimplemented locations read as '0'. Shaded cells are not used by Watchdog Timer.

TABLE 10-4: SUMMARY OF CONFIGURATION WORD WITH WATCHDOG TIMER

Name	Bits	Bit -/7	Bit -/6	Bit 13/5	Bit 12/4	Bit 11/3	Bit 10/2	Bit 9/1	Bit 8/0	Register on Page
CONFIG2	13:8	_	—	DEBUG	STVREN	PPS1WAY		BORV		05
	7:0	BOREN1	BOREN0	LPBOREN	_	WDTE1	WDTE0	PWRTE	MCLRE	65

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by Watchdog Timer.

11.0 NONVOLATILE MEMORY (NVM) CONTROL

NVM is separated into two types: Program Flash Memory and Data EEPROM.

NVM is accessible by using both the FSR and INDF registers, or through the NVMREG register interface.

The write time is controlled by an on-chip timer. The write/erase voltages are generated by an on-chip charge pump rated to operate over the operating voltage range of the device.

NVM can be protected in two ways; by either code protection or write protection.

Code protection (\overline{CP} and \overline{CPD} bits in Configuration Word 4) disables access, reading and writing, to both the Program Flash Memory and EEPROM via external device programmers. Code protection does not affect the self-write and erase functionality. Code protection can only be Reset by a device programmer performing a Bulk Erase to the device, clearing all nonvolatile memory, Configuration bits, and User IDs.

Write protection prohibits self-write and erase to a portion or all of the Program Flash Memory, as defined by the WRT<1:0> bits of Configuration Word 3. Write protection does not affect a device programmer's ability to read, write, or erase the device.

11.1 Program Flash Memory

Program Flash Memory consists of 16,384 14-bit words as user memory, with additional words for User ID information, Configuration Words, and interrupt vectors. Program Flash Memory provides storage locations for:

- User program instructions
- User defined data

Program Flash Memory data can be read and/or written to through:

- CPU instruction fetch (read-only)
- FSR/INDF indirect access (read-only) (Section 11.3 "FSR and INDF Access")
- NVMREG access (Section 11.4 "NVMREG Access"
- In-Circuit Serial Programming[™] (ICSP[™])

Read operations return a single word of memory. When write and erase operations are done on a row basis, the row size is defined in Table 11-1. Program Flash Memory will erase to a logic '1' and program to a logic '0'.

TABLE 11-1:FLASH MEMORY
ORGANIZATION BY DEVICE

Device	Row Erase (words)	Write Latches (words)	
PIC16(L)F18326	32	32	
PIC16(L)F18346	52	52	

It is important to understand the Program Flash Memory structure for erase and programming operations. Program Flash Memory is arranged in rows. A row consists of 32 14-bit program memory words. A row is the minimum size that can be erased by user software.

All or a portion of a row can be programmed. Data to be written into the program memory row are written to 14-bit wide data write latches. These latches are not directly accessible to the user, but may be loaded via sequential writes to the NVMDATH:NVMDATL register pair.

Note:	To modify only a portion of a previously programmed row, then the contents of the entire row must be read and saved in RAM prior to the erase. Then, the new data and retained data can be written into the write latches to reprogram the row of Program Flash Memory. Any unprogrammed locations can be written without first erasing the row. In this case, it is not necessary to save and rewrite the
	it is not necessary to save and rewrite the other previously programmed locations

11.1.1 PROGRAM MEMORY VOLTAGES

The Program Flash Memory is readable and writable during normal operation over the full VDD range.

11.1.1.1 Programming Externally

The program memory cell and control logic support write and Bulk Erase operations down to the minimum device operating voltage.

11.1.1.2 Self-Programming

The program memory cell and control logic will support write and row erase operations across the entire VDD range. Bulk Erase is not supported when self-programming.

11.2 Data EEPROM

Data EEPROM consists of 256 bytes of user data memory. The EEPROM provides storage locations for 8-bit user defined data.

EEPROM can be read and/or written through:

- FSR/INDF indirect access (Section 11.3 "FSR and INDF Access")
- NVMREG access (Section 11.4 "NVMREG Access")
- In-Circuit Serial Programming (ICSP)

Unlike Program Flash Memory, which must be written to by row, EEPROM can be written to byte-by-byte.

11.3 FSR and INDF Access

The FSR and INDF registers allow indirect access to the Program Flash Memory or EEPROM.

11.3.1 FSR READ

With the intended address loaded into an FSR register, a MOVIW instruction or read of INDF will read data from the Program Flash Memory or EEPROM. The CPU operation is suspended during the read, and resumes immediately after. Read operations return a single word of memory. When the MSB of the FSR (ex: FSRxH) is set to 0x70, the lower 8-bit address value (in FSRxL) determines the EEPROM location that may be read from (through the INDF register). In other words, the EEPROM address range 0x00-0xFF is mapped into the FSR address space between 0x7000-0x70FF. Writing to the EEPROM cannot be accomplished via the FSR/INDF interface.

11.3.2 FSR WRITE

Writing/erasing the NVM through the FSR registers (ex. MOVWI instruction) is not supported in the PIC16(L)F18326/18346 devices.

11.4 NVMREG Access

The NVMREG interface allows read/write access to all the locations accessible by FSRs, and also read/write access to the User ID locations and EEPROM, and read-only access to the device identification, revision, and Configuration data.

Reading, writing, or erasing of NVM via the NVMREG interface is prevented when the device is code-protected.

11.4.1 NVMREG READ OPERATION

To read a NVM location using the NVMREG interface, the user must:

- Clear the NVMREGS bit of the NVMCON1 register if the user intends to access Program Flash Memory locations, or set NVMREGS if the user intends to access User ID, Configuration, or EEPROM locations.
- 2. Write the desired address into the NVMADRH:NVMADRL register pair (Table 11-2).
- 3. Set the RD bit of the NVMCON1 register to initiate the read.


Once the read control bit is set, the CPU operation is suspended during the read, and resumes immediately after. The data are available in the very next cycle, in the NVMDATH:NVMDATL register pair; therefore, it can be read as two bytes in the following instructions.

NVMDATH:NVMDATL register pair will hold this value until another read or until it is written to by the user.

Upon completion, the RD bit is cleared by hardware.

PIC16(L)F18326/18346

FIGURE 11-1: PROGRAM FLASH MEMORY READ FLOWCHART Start Read Operation Select Memory: Program Flash Memory, EEPROM, Config. Words, User ID (NVMREGS) Select Word Address (NVMADRH:NVMADRL)



EXAMPLE 11-1: PROGRAM FLASH MEMORY READ

```
* This code block will read 1 word of program
* memory at the memory address:
    PROG ADDR HI : PROG ADDR LO
    data will be returned in the variables;
*
    PROG_DATA_HI, PROG_DATA_LO
    BANKSELNVMADRL; Select Bank for NVMCON registersMOVLWPROG_ADDR_LO;MOVWFNVMADRL; Store LSB of addressMOVLWPROG_ADDR_HI;MOVWFNVMADRH; Store MSB of address
    BCF
                 NVMCON1, NVMREGS ; Do not select Configuration Space
               NVMCON1,RD ; Initiate read
    BSF
                NVMDATL,W ; Get LSB of word

PROG_DATA_LO ; Store in user location

NVMDATH,W ; Get MSB of word

PROG_DATA_HI ; Store in user
    MOVF
    MOVWF
    MOVF
    MOVWF
```

11.4.2 NVM UNLOCK SEQUENCE

The unlock sequence is a mechanism that protects the NVM from unintended self-write programming or erasing. The sequence must be executed and completed without interruption to successfully complete any of the following operations:

- Program Flash Memory Row Erase
- · Load of Program Flash Memory write latches
- Write of Program Flash Memory write latches to Program Flash Memory memory
- Write of Program Flash Memory write latches to User IDs
- Write to EEPROM


The unlock sequence consists of the following steps and must be completed in order:

- Write 55h to NVMCON2
- Write AAh to NMVCON2
- · Set the WR bit of NVMCON1

Once the WR bit is set, the processor will stall internal operations until the operation is complete and then resume with the next instruction.

Since the unlock sequence must not be interrupted, global interrupts must be disabled prior to the unlock sequence and re-enabled after the unlock sequence is completed.

FIGURE 11-2: NVM UNLOCK SEQUENCE FLOWCHART



EXAMPLE 11-2: NVM UNLOCK SEQUENCE

BANKSEL	NVMCON1	
BSF	NVMCON1,WREN	; Enable write/erase
MOVLW	55h	; Load 55h
BCF	INTCON, GIE	; Recommended so sequence is not interrupted
MOVWF	NVMCON2	; Step 1: Load 55h into NVMCON2
MOVLW	AAh	; Step 2: Load W with AAh
MOVWF	NVMCON2	; Step 3: Load AAh into NVMCON2
BSF	NVMCON1,WR	; Step 4: Set WR bit to begin write/erase
BSF	INTCON, GIE	; Re-enable interrupts

Note 1: Sequence begins when NVMCON2 is written; steps 1-4 must occur in the cycle-accurate order shown.

2: Opcodes shown are illustrative; any instruction that has the indicated effect may be used.

Note: The two NOP instructions after setting the WR bit, which were required in previous devices, are not required for PIC16(L)F18326/18346 devices. See Figure 11-2.

11.4.3 NVMREG WRITE TO EEPROM

Writing to the EEPROM is accomplished by the following steps:

- 1. Set the NVMREGS and WREN bits of the NVMCON1 register.
- Write the desired address (address +7000h) into the NVMADRH:NVMADRL register pair (Table 11-2).
- 3. Perform the unlock sequence as described in Section 11.4.2 "NVM Unlock Sequence".

A single EEPROM byte is written with NVMDATA. The operation includes an implicit erase cycle for that byte (it is not necessary to set the FREE bit), and requires many instruction cycles to finish. CPU execution continues in parallel and, when complete, WR is cleared by hardware, NVMIF is set, and an interrupt will occur if NVMIE is also set. Software must poll the WR bit to determine when writing is complete, or wait for the interrupt to occur. WREN will remain unchanged.

Once the EEPROM write operation begins, clearing the WR bit will have no effect; the operation will continue to run to completion.

11.4.4 NVMREG ERASE OF PROGRAM FLASH MEMORY

Program Flash Memory can only be erased one row at a time. No automatic erase occurs upon the initiation of the write to Program Flash Memory.

To erase a Program Flash Memory row:

- Clear the NVMREGS bit of the NVMCON1 register to erase Program Flash Memory locations, or set the NVMREGS bit to erase User ID locations.
- 2. Write the desired address into the NVMADRH:NVMADRL register pair (Table 11-2).
- 3. Set the FREE and WREN bits of the NVMCON1 register.
- 4. Perform the unlock sequence as described in Section 11.4.2 "NVM Unlock Sequence".


If the Program Flash Memory address is write-protected, the WR bit will be cleared and the erase operation will not take place.

While erasing Program Flash Memory, CPU operation is suspended, and resumes when the operation is complete. Upon completion, the NVMIF is set, and an interrupt will occur if the NVMIE bit is also set.

Write latch data are not affected by erase operations, and WREN will remain unchanged.

FIGURE 11-3: NVM ERASE

FLOWCHART



EXAMPLE 11-3: ERASING ONE ROW OF PROGRAM FLASH MEMORY

; This sample row erase routine assumes the following:									
; 1.A valid a	; 1.A valid address within the erase row is loaded in variables ADDRH:ADDRL								
; 2.ADDRH and	; 2.ADDRH and ADDRL are located in common RAM (locations 0x70 - 0x7F)								
BANKSEL	NVMADRL								
MOVF	ADDRL,W								
MOVWF	NVMADRL	; Load lower 8 bits of erase address boundary							
MOVF	ADDRH,W								
MOVWF	NVMADRH	; Load upper 6 bits of erase address boundary							
BCF	NVMCON1, NVMREGS	; Choose Program Flash Memory area							
BSF	NVMCON1, FREE	; Specify an erase operation							
BSF	NVMCON1,WREN	; Enable writes							
BCF	INTCON, GIE	; Disable interrupts during unlock sequence							
;		REQUIRED UNLOCK SEQUENCE:							
MOVLW	55h	; Load 55h to get ready for unlock sequence							
MOVWF	NVMCON2	; First step is to load 55h into NVMCON2							
MOVLW	AAh	; Second step is to load AAh into W							
MOVWF	NVMCON2	; Third step is to load AAh into NVMCON2							
BSF	NVMCON1,WR	; Final step is to set WR bit							
·									
,									
BSF	INTCON, GIE	; Re-enable interrupts, erase is complete							
BCF	NVMCON1,WREN	; Disable writes							
1									

TABLE 11-2: NVM ORGANIZATION AND ACCESS INFORMATION

Host Values			NV	MREG Acce	ss FSR Access			
Memory Function	Program Counter (PC), ICSP™ Address	Memory Type	NVMREGS bit (NVMCON1)	NVMADR <14:0>	Allowed Operations	FSR Address	FSR Programming Address	
Reset Vector	0000h		0	0000h		8000h		
User Memory	0001h	Program	0	0001h		8001h		
	0003h	Flash		0003h	READ	8003h		
INT Vector	0004h	Memory	0	0004h	WRITE	8004h	READ-ONLY	
User Memory	0005h		0	0005h		8005h		
	3FFFh			3FFFh		BFFFh		
User ID		Program	1	0000h				
		Flash Memory		0003h	READ			
Reserved		_	—	0004h	—			
Rev ID			1	0005h		No	Access	
Device ID	No PC Address		1	0006h		110	100000	
CONFIG1		Program Flash	1	0007h	READ			
CONFIG2		Memory	1	0008h				
CONFIG3		Memory		0009h				
CONFIG4				000Ah				
User Memory		EEPROM	1	7000h	READ	7000h	READ-ONLY	
				70FFh	WRITE	70FFh		

11.4.5 NVMREG WRITE TO PROGRAM FLASH MEMORY

Program memory is programmed using the following steps:

- 1. Load the address of the row to be programmed into NVMADRH:NVMADRL.
- 2. Load each write latch with data.
- 3. Initiate a programming operation.
- 4. Repeat steps 1 through 3 until all data are written.

Before writing to program memory, the word(s) to be written must be erased or previously unwritten. Program memory can only be erased one row at a time. No automatic erase occurs upon the initiation of the write.

Program memory can be written one or more words at a time. The maximum number of words written at one time is equal to the number of write latches. See Figure 11-4 (row writes to program memory with 32 write latches) for more details.


The write latches are aligned to the Flash row address boundary defined by the upper ten bits of NVMADRH:NVMADRL, (NVMADRH<6:0>:NVMADRL<7:5>) with the lower five bits of NVMADRL, (NVMADRL<4:0>) determining the write latch being loaded. Write operations do not cross these boundaries. At the completion of a program memory write operation, the data in the write latches are reset to contain 0x3FFF.

The following steps must be completed to load the write latches and program a row of program memory. These steps are divided into two parts. First, each write latch is loaded with data from the NVMDATH:NVMDATL using the unlock sequence with LWLO = 1. When the last word to be loaded into the write latch is ready, the LWLO bit is cleared and the unlock sequence executed. This initiates the programming operation, writing all the latches into Flash program memory.

Note: The special unlock sequence is required to load a write latch with data or initiate a Flash programming operation. If the unlock sequence is interrupted, writing to the latches or program memory will not be initiated.


- 1. Set the WREN bit of the NVMCON1 register.
- 2. Clear the NVMREGS bit of the NVMCON1 register.
- Set the LWLO bit of the NVMCON1 register. When the LWLO bit of the NVMCON1 register is '1', the write sequence will only load the write latches and will not initiate the write to Flash program memory.
- 4. Load the NVMADRH:NVMADRL register pair with the address of the location to be written.
- 5. Load the NVMDATH:NVMDATL register pair with the program memory data to be written.
- Execute the unlock sequence (Section 11.4.2 "NVM Unlock Sequence"). The write latch is now loaded.
- 7. Increment the NVMADRH:NVMADRL register pair to point to the next location.
- 8. Repeat steps 5 through 7 until all but the last write latch has been loaded.
- Clear the LWLO bit of the NVMCON1 register. When the LWLO bit of the NVMCON1 register is '0', the write sequence will initiate the write to Flash program memory.
- 10. Load the NVMDATH:NVMDATL register pair with the program memory data to be written.
- 11. Execute the unlock sequence (Section 11.4.2 "NVM Unlock Sequence"). The entire program memory latch content is now written to Flash program memory.
 - **Note:** The program memory write latches are reset to the blank state (0x3FFF) at the completion of every write or erase operation. As a result, it is not necessary to load all the program memory write latches. Unloaded latches will remain in the blank state.

An example of the complete write sequence is shown in Example 11-4. The initial address is loaded into the NVMADRH:NVMADRL register pair; the data are loaded using indirect addressing.



PIC16(L)F18326/18346

FIGURE 11-5: PROGRAM FLASH MEMORY WRITE FLOWCHART



PIC16(L)F18326/18346

EXAMPLE 11-4: WRITING TO PROGRAM FLASH MEMORY


EXAMPL	_E 11-4: V	RITING TO PROGRAM	FLASH MEMORY
; This	write routi	ne assumes the following	ng:
; 1. 32	2 words of d	ata are loaded, starti	ng at the address in DATA_ADDR
; 2. Ea	ach word of	data to be written is	made up of two adjacent bytes in DATA_ADDR,
; st	tored in lit	tle endian format	
; 3.A	valid start	ing address (the least	significant bits = 00000) is loaded in ADDRH:ADDRL
			on RAM (locations 0x70 - 0x7F)
; 5. NV	VM interrupt	s are not taken into a	ccount
	BANKSEL	NVMADRH	
	MOVF	ADDRH,W	
	MOVWF	NVMADRH	; Load initial address
	MOVF	ADDRL,W	
	MOVWF	NVMADRL	
	MOVLW	LOW DATA_ADDR	; Load initial data address
	MOVWF	FSROL	
	MOVLW	HIGH DATA_ADDR	
	MOVWF	FSROH	
	BCF	NVMCON1, NVMREGS	; Set Program Flash Memory as write location
	BSF	NVMCON1,WREN	; Enable writes
	BSF	NVMCON1,LWLO	; Load only write latches
LOOP			
	MOVIW	FSR0++	
	MOVWF	NVMDATL	; Load first data byte
	MOVIW	FSR0++	
	MOVWF	NVMDATH	; Load second data byte
	MOVF	NVMADRL,W	
	XORLW	0x20	; Check if lower bits of address are 00000
	ANDLW	0x20	; and if on last of 32 addresses
	BTFSC	STATUS,Z	; Last of 32 words?
	GOTO	START_WRITE	; If so, go write latches into memory
	CALL	UNLOCK_SEQ	; If not, go load latch
	INCF	NVMADRL, F	; Increment address
	GOTO	LOOP	
START	WRITE		
	BCF	NVMCON1, LWLO	; Latch writes complete, now write memory
	CALL	UNLOCK SEQ	; Perform required unlock sequence
	BCF	NVMCONI, LWLO	; Disable writes
UNLOCK	SEO		
ONTOCK	MOVLW	55h	
	BCF	INTCON, GIE	; Disable interrupts
	MOVWF	NVMCON2	; Begin unlock sequence
	MOVLW	AAh	,,
	MOVWF	NVMCON2	
	BSF	NVMCON1,WR	
	BSF	INTCON, GIE	; Unlock sequence complete, re-enable interrupts
	return	·	

11.4.6 MODIFYING PROGRAM FLASH MEMORY

When modifying existing data in a program memory row, and data within that row must be preserved, it must first be read and saved in a RAM image. Program memory is modified using the following steps:

- 1. Load the starting address of the row to be modified.
- 2. Read the existing data from the row into a RAM image.
- 3. Modify the RAM image to contain the new data to be written into program memory.
- 4. Load the starting address of the row to be rewritten.
- 5. Erase the program memory row.
- 6. Load the write latches with data from the RAM image.
- 7. Initiate a programming operation.

FIGURE 11-6: PROGRAM FLASH MEMORY MODIFY FLOWCHART



11.4.7 NVMREG EEPROM, USER ID, DEVICE ID AND CONFIGURATION WORD ACCESS

Instead of accessing Program Flash Memory, the EEPROM, the User ID's, Device ID/Revision ID and Configuration Words can be accessed when NVMREGS = 1 in the NVMCON1 register. This is the region that would be pointed to by PC<15> = 1, but not all addresses are accessible. Different access may exist for reads and writes. Refer to Table 11-3.

When read access is initiated on an address outside the parameters listed in Table 11-3, the NVMDATH: NVMDATL register pair is cleared, reading back '0's.


TABLE 11-3: EEPROM, USER ID, DEV/REV ID AND CONFIGURATION WORD ACCESS (NVMREGS = 1)

Address	Function	Read Access	Write Access
8000h-8003h	User IDs	Yes	Yes
8005h-8006h	Device ID/Revision ID	Yes	No
8007h-800Ah	Configuration Words 1-4	Yes	No
F000h-F0FFh	EEPROM	Yes	Yes

11.4.8 WRITE VERIFY

It is considered good programming practice to verify that program memory writes agree with the intended value. Since program memory is stored as a full row, then the stored program memory contents are compared with the intended data stored in RAM after the last write is complete.

FIGURE 11-7: PROGRAM FLASH MEMORY VERIFY FLOWCHART



11.4.9 WRERR BIT

The WRERR bit can be used to determine if a write error occurred.

WRERR will be set if one of the following conditions occurs:

- If WR is set while the NVMADRH:NMVADRL points to a write-protected address
- A Reset occurs while a self-write operation was in progress
- An unlock sequence was interrupted

The WRERR bit is normally set by hardware, but can be set by the user for test purposes. Once set, WRERR must be cleared in software.

TABLE 11-4: ACTIONS FOR PROGRAM FLASH MEMORY WHEN WR = 1

Free	LWLO	Actions for Program Flash Memory when WR = 1	Comments
0	0	Write the write latch data to Program Flash Memory row. See Section 11.4.4 "NVMREG Erase of Pro- gram Flash Memory"	 If WP is enabled, WR is cleared and WRERR is set Write latches are reset to 3FFh NVMDATH:NVMDATL is ignored
0	1	Copy NVMDATH:NVMDATL to the write latch corre- sponding to NVMADR LSBs. See Section 11.4.4 "NVMREG Erase of Program Flash Memory"	Write protection is ignoredNo memory access occurs
1	x	Erase the 32-word row of NVMADRH:NVMADRL location. See Section 11.4.3 "NVMREG Write to EEPROM"	 If WP is enabled, WR is cleared and WRERR is set All 32 words are erased NVMDATH:NVMDATL is ignored

11.5 Register Definitions: Program Flash Memory Control REGISTER 11-1: NVMDATL: NONVOLATILE MEMORY DATA LOW BYTE REGISTER

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
			NVME	AT<7:0>			
bit 7							bit 0
Legend:							
R = Readable b	it	W = Writable bi	it	U = Unimplem	ented bit, read as	s 'O'	
u = Bit is uncha	nged	x = Bit is unkno	own	-n/n = Value at	POR and BOR/	Value at all other	Resets
'1' = Bit is set		'0' = Bit is clear	ed				

bit 7-0

NVMDAT<7:0>: Read/Write Value for Least Significant bits of Program Memory

REGISTER 11-2: NVMDATH: NONVOLATILE MEMORY DATA HIGH BYTE REGISTER

U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
—	—	NVMDAT<13:8>					
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 Unimplemented: Read as '0'

bit 5-0	NVMDAT<13:8>: Read/Write Value for Most Significant bits of Program Memory ⁽¹⁾
	NUMBAL NOT

Note 1: This byte is ignored when writing to EEPROM.

REGISTER 11-3: NVMADRL: NONVOLATILE MEMORY ADDRESS LOW BYTE REGISTER

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
NVMADR<7:0>							
bit 7 bit							

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 NVMADR<7:0>: Specifies the Least Significant bits for Program Memory Address

REGISTER 11-4: NVMADRH: NONVOLATILE MEMORY ADDRESS HIGH BYTE REGISTER

U-1	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
—				NVMADR<14:8	}>		
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7 Unimplemented: Read as '1'

bit 6-0 NVMADR<14:8>: Specifies the Most Significant bits for Program Memory Address

U-0	R/W-0/0	R/W-0/0	R/W/HC-0/0	R/W/HC-x/q	R/W-0/0	R/S/HC-0/0	R/S/HC-0/0		
—	NVMREGS	LWLO	FREE	WRERR	WREN	WR	RD		
bit 7							bit (
Legend:									
R = Read		W = Writable		-	mented bit, read		4h D		
	an only be set	x = Bit is unk			at POR and BO		ther Resets		
'1' = Bit is	Sel	'0' = Bit is cle	ared	HC = BILIS C	eared by hardw	are			
bit 7	Unimplemen	ted: Read as	ʻ0'						
bit 6	•	Configuration S							
	1 = Access E	EEPROM, Con	figuration, Use	r ID and Devid	e ID registers				
		Program Flash	-						
bit 5	LWLO: Load When FREE	Write Latches	Only bit						
			d updates the w	vrite latch for tl	nis word within t	he row: no mer	norv operatio		
	is initiate					,	2 1		
			d writes data or	erases					
L:4 /		ne bit is ignore		hla hit					
bit 4			ory Erase Enal R points to a Pr		lemory location				
					and; the row co		icated addres		
			prepare for writi						
		-	e completed no	-					
bit 3			rror Flag bit ^{(1,2} ardware	.,0)					
		This bit is normally set by hardware. 1 = A write operation was interrupted by a Reset, interrupted unlock sequence, or WR was written to							
	one while	e NVMADR po	ints to a write-p	protected addr	ess.				
			operation comp	eleted normally	/				
bit 2	-	WREN: Program/Erase Enable bit 1 = Allows program/erase cycles							
			rasing of progra	am Flash					
bit 1	WR: Write Co								
	When NVMR	EG:NVMADR	points to a EEF						
		 1 = Initiates an erase/program cycle at the corresponding EEPROM location 0 = NVM program/erase operation is complete and inactive 							
		•			emory location:				
			ndicated by Tal						
	-		peration is com	plete and inac	tive				
bit 0	RD: Read Co								
					data to NVMDA omplete. The bit				
	in softwa				inplete. The bit	can only be se	t (not cleared		
	0 = NVM rea	d operation is	complete and i	nactive.					
Note 1:	Bit may change wh					'0' or '1').			
2:	Bit must be cleared								
3: 4:	Bit may be written This bit can only b					NVM Unlock S	equence"		
5:	Operations are sel	•	•	•					
6:	Once a write opera		-						
7:	Reading from EEP	'KOM loads or	NVMDALL<	/:U> (Register	· 11-1).				

REGISTER 11-5: NVMCON1: NONVOLATILE MEMORY CONTROL 1 REGISTER

7: Reading from EEPROM loads only NVMDATL<7:0> (Register 11-1).

W-0/0	W-0/0	W-0/0	W-0/0	W-0/0	W-0/0	W-0/0	W-0/0		
NVMCON2									
bit 7							bit 0		
Legend:									
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'									
S = Bit can only b	e set	x = Bit is unknov	vn	-n/n = Value at POR and BOR/Value at all other Reset					
'1' = Bit is set		'0' = Bit is cleare	ed						

REGISTER 11-6: NVMCON2: NONVOLATILE MEMORY CONTROL 2 REGISTER

bit 7-0 **NVMCON2<7:0>:** Flash Memory Unlock Pattern bits To unlock writes, a 55h must be written first, followed by an AAh, before setting the WR bit of the NVMCON1 register. The value written to this register is used to unlock the writes.

TABLE 11-5: SUMMARY OF REGISTERS ASSOCIATED WITH NONVOLATILE MEMORY (NVM)

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
INTCON	GIE	PEIE	—	—	—		—	INTEDG	100
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BLC2IF	TMR4IF	NCO1IF	108
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BLC2IE	TMR4IE	NCO1IE	103
NVMCON1	_	NVMREGS	LWLO	FREE	WRERR	WREN	WR	RD	138
NVMCON2	2 NVMCON2								139
NVMADRL	. NVMADR<7:0>							137	
NVMADRH	(1) NVMADR<14:8>							137	
NVMDATL	NVMDAT<7:0>							137	
NVMDATH	_	—			NVMDA	T<13:8>			137

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by NVM. **Note 1:** Unimplemented, read as '1'.

TABLE 11-6:	SUMMARY OF CONFIGURATION WORD WITH NONVOLATILE MEMORY (NVM	1)
-------------	--	----

Name	Bits	Bit -/7	Bit -/6	Bit 13/5	Bit 12/4	Bit 11/3	Bit 10/2	Bit 9/1	Bit 8/0	Register on Page
CONFIG3	13:8	—	—	LVP	—	—	—	_	—	66
	7:0	_	_	_	_	_	_	WRT	<1:0>	
CONFIG4	13:8	_	_	_	_	_	_	_	_	67
	7:0	—	_	_	_	_	_	CPD	CP	

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by NVM.

12.0 I/O PORTS

TABLE 12-1: PORT AVAILABILITY PER DEVICE

Device	PORTA	PORTB	PORTC
PIC16(L)F18326	•		•
PIC16(L)F18346	•	•	•

Each port has ten standard registers for its operation. These registers are:

- PORTx registers (reads the levels on the pins of the device)
- LATx registers (output latch)
- TRISx registers (data direction)
- ANSELx registers (analog select)
- WPUx registers (weak pull-up)
- INLVLx (input level control)
- SLRCONx registers (slew rate)
- ODCONx registers (open-drain)

Most PORT pins share functions with device peripherals, both analog and digital. In general, when a peripheral is enabled on a PORT pin, that pin cannot be used as a general purpose output; however, the pin can still be read.


The Data Latch (LATx registers) is useful for read-modify-write operations on the value that the I/O pins are driving.

A write operation to the LATx register has the same effect as a write to the corresponding PORTx register. A read of the LATx register reads of the values held in the I/O PORT latches, while a read of the PORTx register reads the actual I/O pin value.

Ports that support analog inputs have an associated ANSELx register. When an ANSEL bit is set, the digital input buffer associated with that bit is disabled.

Disabling the input buffer prevents analog signal levels on the pin between a logic high and low from causing excessive current in the logic input circuitry. A simplified model of a generic I/O port, without the interfaces to other peripherals, is shown in Figure 12-1.

FIGURE 12-1: GENERIC I/O PORT OPERATION



12.1 I/O Priorities

Each pin defaults to the PORT data latch after Reset. Other functions are selected with the peripheral pin select logic. See **Section 13.0 "Peripheral Pin Select** (**PPS**) **Module**" for more information.

Analog input functions, such as ADC and comparator inputs, are not shown in the peripheral pin select lists. These inputs are active when the I/O pin is set for Analog mode using the ANSELx register. Digital output functions may continue to control the pin when it is in Analog mode.

Analog outputs, when enabled, take priority over the digital outputs and force the digital output driver to the high-impedance state.

12.2 PORTA Registers

12.2.1 DATA REGISTER

PORTA is a 6-bit wide, bidirectional port. The corresponding data direction register is TRISA (Register 12-2). Setting a TRISA bit (= 1) will make the corresponding PORTA pin an input (i.e., disable the output driver). Clearing a TRISA bit (= 0) will make the corresponding PORTA pin an output (i.e., enables output driver and puts the contents of the output latch on the selected pin). The exception is RA3, which is input-only and its TRIS bit will always read as '1'. Example 12-1 shows how to initialize PORTA.

Reading the PORTA register (Register 12-1) reads the status of the pins, whereas writing to it will write to the PORT latch. All write operations are read-modify-write operations. Therefore, a write to a port implies that the PORT pins are read, this value is modified and then written to the PORT data latch (LATA).

The PORT data latch LATA (Register 12-3) holds the output port data, and contains the latest value of a LATA or PORTA write.

EXAMPLE 12-1: INITIALIZING PORTA

<pre>; This code example illustrates ; initializing the PORTA register. The ; other ports are initialized in the same ; manner.</pre>						
BANKSEL CLRF BANKSEL CLRF BANKSEL	PORTA LATA LATA ANSELA ANSELA TRISA B'00111000'	; ;Init PORTA ;Data Latch ; ;digital I/O ; ;Set RA<5:3> as inputs ;and set RA<2:0> as ;outputs				

12.2.2 DIRECTION CONTROL

The TRISA register (Register 12-2) controls the PORTA pin output drivers, even when they are being used as analog inputs. The user must ensure the bits in the TRISA register are maintained set when using them as analog inputs. I/O pins configured as analog inputs always read '0'.

12.2.3 OPEN-DRAIN CONTROL

The ODCONA register (Register 12-6) controls the open-drain feature of the port. Open-drain operation is independently selected for each pin. When an ODCONA bit is set, the corresponding port output becomes an open-drain driver capable of sinking current only. When an ODCONA bit is cleared, the corresponding port output pin is the standard push-pull drive capable of sourcing and sinking current.

Note:	It is not necessary to set open-drain control when using the pin for I ² C; the I ² C
	module controls the pin and makes the pin open-drain.

12.2.4 SLEW RATE CONTROL

The SLRCONA register (Register 12-7) controls the slew rate option for each PORT pin. Slew rate control is independently selectable for each PORT pin. When an SLRCONA bit is set, the corresponding PORT pin drive is slew rate limited. When an SLRCONA bit is cleared, The corresponding PORT pin drive slews at the maximum rate available.

12.2.5 INPUT THRESHOLD CONTROL

The INLVLA register (Register 12-8) controls the input voltage threshold for each of the available PORTA input pins. A selection between the Schmitt Trigger CMOS or the TTL Compatible thresholds is available. The input threshold is important in determining the value of a read of the PORTA register and also the level at which an interrupt-on-change occurs, if that feature is enabled. See Table 35-4 for more information on threshold levels.

Note:	Changing the input threshold selection may be performed while all peripheral
	modules are disabled. Changing the
	threshold level during the time a module is
	active may inadvertently generate a
	transition associated with an input pin,
	regardless of the actual voltage level on
	that pin.

12.2.6 ANALOG CONTROL

The ANSELA register (Register 12-4) is used to configure the Input mode of an I/O pin to analog. Setting the appropriate ANSELA bit high will cause all digital reads on the pin to be read as '0' and allow analog functions on the pin to operate correctly.

The state of the ANSELA bits has no effect on digital output functions. A pin with TRIS clear and ANSEL set will still operate as a digital output, but the Input mode will be analog. This can cause unexpected behavior when executing read-modify-write instructions on the affected port.

Note:	The ANSELA bits default to the Analog					
	mode after Reset. To use any pins as					
	digital general purpose or peripheral					
	inputs, the corresponding ANSEL bits					
	must be initialized to '0' by user software.					

12.2.7 WEAK PULL-UP CONTROL

The WPUA register (Register 12-5) controls the individual weak pull-ups for each PORT pin.

PORTA pin RA3 includes the $\overline{\text{MCLR}}/\text{VPP}$ input. The MCLR input allows the device to be reset, and can be disabled by the MCLRE bit of Configuration Word 2. A weak pull-up is present on the RA3 PORT pin. This weak pull-up is enabled when $\overline{\text{MCLR}}$ is enabled (MCLRE = 1) or the WPUA3 bit is set. The weak pull-up is disabled when the MCLR is disabled and the WPUA3 bit is cleared.

12.2.8 PORTA FUNCTIONS AND OUTPUT PRIORITIES

Each PORTA pin is multiplexed with other functions.

Each pin defaults to the PORT latch data after Reset. Other output functions are selected with the peripheral pin select logic. See **Section 13.0 "Peripheral Pin Select (PPS) Module"** for more information.

Analog input functions, such as ADC and comparator inputs are not shown in the peripheral pin select lists. Digital output functions may continue to control the pin when it is in Analog mode.

12.3 Register Definitions: PORTA

U-0	U-0	R/W-x/u	R/W-x/u	R-x/u	R/W-x/u	R/W-x/u	R/W-x/u	
—	_	RA5	RA4	RA3 ⁽²⁾	RA2	RA1	RA0	
bit 7							bit 0	
Legend:								
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unknown			-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set '0' = Bit is cleared								

REGISTER 12-1: PORTA: PORTA REGISTER

bit 7-6	Unimplemented: Read as '0	,
DIL 7-0	Uninplemented. Read as 0	1

bit 5-0 RA<5:0>: PORTA I/O Value bits⁽¹⁾ 1 = PORT pin is ≥ VIH 0 = PORT pin is ≤ VIL

- **Note 1:** Writes to PORTA are actually written to corresponding LATA register. Reads from PORTA register is return of actual I/O pin values.
 - 2: Bit RA3 is read-only, and will read '1' when MCLRE = 1 (Master Clear enabled).

REGISTER 12-2: TRISA: PORTA TRI-STATE REGISTER

U-0	U-0	R/W-1/1	R/W-1/1	U-1	R/W-1/1	R/W-1/1	R/W-1/1
—	—	TRISA5	TRISA4	—	TRISA2	TRISA1	TRISA0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	Unimplemented: Read as '0'
bit 5-4	TRISA<5:4>: PORTA Tri-State Control bit 1 = PORTA pin configured as an input (tri-stated) 0 = PORTA pin configured as an output
bit 3	Unimplemented: Read as '1'
bit 2-0	TRISA<2:0>: PORTA Tri-State Control bit 1 = PORTA pin configured as an input (tri-stated) 0 = PORTA pin configured as an output

U-0	U-0			U-0				
0-0	0-0	R/W-x/u	R/W-x/u	0-0	R/W-x/u	R/W-x/u	R/W-x/u	
_		LATA5	LATA4		LATA2	LATA1	LATA0	
bit 7							bit 0	
Legend:								
R = Readable bit		W = Writable bit		U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is u		x = Bit is unkn	iown	-n/n = Value at POR and BOR/Value at all other Resets				
'1' = Bit is set '0' = Bit is cleared		ared						
bit 7-6	Unimplemen	tad: Read as '(·،					
bit 5-4	5-4 LATA<5:4>: RA<5:4> Output Latch Value bits ⁽¹⁾							
bit 3	Unimplemented: Read as '0'							
bit 2-0 LATA<2:0>: RA<2:0> Output Latch Value bits ⁽¹⁾								

REGISTER 12-3: LATA: PORTA DATA LATCH REGISTER

Note 1: Writes to PORTA are actually written to corresponding LATA register. Reads from PORTA register is return of actual I/O pin values.

REGISTER 12-4: ANSELA: PORTA ANALOG SELECT REGISTER

U-0	U-0	R/W-1/1	R/W-1/1	U-0	R/W-1/1	R/W-1/1	R/W-1/1
—		ANSA5	ANSA4	—	ANSA2	ANSA1	ANSA0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	Unimplemented: Read as '0'
bit 5-4	 ANSA<5:4>: Analog Select between Analog or Digital Function on pins RA<5:4>, respectively 1 = Analog input. Pin is assigned as analog input⁽¹⁾. Digital input buffer disabled. 0 = Digital I/O. Pin is assigned to port or digital special function.
bit 3	Unimplemented: Read as '0'
bit 2-0	 ANSA<2:0>: Analog Select between Analog or Digital Function on pins RA<2:0>, respectively 1 = Analog input. Pin is assigned as analog input⁽¹⁾. Digital input buffer disabled. 0 = Digital I/O. Pin is assigned to port or digital special function.

Note 1: When setting a pin to an analog input, the corresponding TRIS bit must be set to Input mode to allow external control of the voltage on the pin.

U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
_	—	WPUA5	WPUA4	WPUA3 ⁽¹⁾	WPUA2	WPUA1	WPUA0		
bit 7							bit 0		
Legend:									
R = Readab	le bit	W = Writable	bit	U = Unimplemented bit, read as '0'					
u = Bit is une	changed	x = Bit is unknown		-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is se	et	'0' = Bit is clea	ared						
bit 7-6	Unimplemen	ted: Read as '	0'						
bit 5-0	it 5-0 WPUA<5:0>: Weak Pull-up Register bits ⁽²⁾								
	1 = Pull-up er	nabled							
	0 = Pull-up disabled								
Note 1: If MCLRE = 1, the weak pull-up in RA3 is always enabled; bit WPUA3 is not affected.									

REGISTER 12-5: WPUA: WEAK PULL-UP PORTA REGISTER

2: The weak pull-up device is automatically disabled if the pin is configured as an output.

REGISTER 12-6: ODCONA: PORTA OPEN-DRAIN CONTROL REGISTER

U-0	U-0	R/W-0/0	R/W-0/0	U-0	R/W-0/0	R/W-0/0	R/W-0/0
—	—	ODCA5	ODCA4	—	ODCA2	ODCA1	ODCA0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	Unimplemented: Read as '0'
bit 5-4	ODCA<5:4>: PORTA Open-Drain Enable bits For RA<5:4> pins, respectively 1 = PORT pin operates as open-drain drive (sink current only) 0 = PORT pin operates as standard push-pull drive (source and sink current)
bit 3	Unimplemented: Read as '0'
bit 2-0	ODCA<2:0>: PORTA Open-Drain Enable bits For RA<2:0> pins, respectively 1 = PORT pin operates as open-drain drive (sink current only) 0 = PORT pin operates as standard push-pull drive (source and sink current)

U-0	U-0	R/W-1/1	R/W-1/1	U-0	R/W-1/1	R/W-1/1	R/W-1/1
_	—	SLRA5	SLRA4	—	SLRA2	SLRA1	SLRA0
bit 7							bit 0
Legend:							
R = Readab	le bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is un	changed	x = Bit is unkr	nown	-n/n = Value a	at POR and BOI	R/Value at all c	other Resets
'1' = Bit is se	et	'0' = Bit is clea	ared				
bit 7-6	Unimplemen	ted: Read as '	0'				
bit 5-4	SLRA<5:4>:	PORTA Slew F	ate Enable b	its			
		pins, respectiv	2				
		slew rate is lin					
	•	slews at maxi					
bit 3	Unimplemen	Unimplemented: Read as '0'					
bit 2-0	SLRA<2:0>:	PORTA Slew F	ate Enable b	its			
		pins, respectiv					
	•	slew rate is lir					
	0 = PORT pin	slews at maxi	mum rate				

REGISTER 12-7: SLRCONA: PORTA SLEW RATE CONTROL REGISTER

REGISTER 12-8: INLVLA: PORTA INPUT LEVEL CONTROL REGISTER

U-0	U-0	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
—	—	INLVLA5	INLVLA4	INLVLA3	INLVLA2	INLVLA1	INLVLA0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	Unimplemented: Read as '0'
---------	----------------------------

bit 5-0 INLVLA<5:0>: PORTA Input Level Select bits

For RA<5:0> pins, respectively

1 = ST input used for PORT reads and interrupt-on-change

0 = TTL input used for PORT reads and interrupt-on-change

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
PORTA		—	RA5	RA4	RA3	RA2	RA1	RA0	143
TRISA	_	_	TRISA5	TRISA4	_	TRISA2	TRISA1	TRISA0	143
LATA	_	_	LATA5	LATA4	_	LATA2	LATA1	LATA0	144
ANSELA	_	_	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
WPUA	_	_	WPUA5	WPUA4	WPUA3	WPUA2	WPUA1	WPUA0	145
ODCONA	_	_	ODCA5	ODCA4	_	ODCA2	ODCA1	ODCA0	145
SLRCONA		_	SLRA5	SLRA4	_	SLRA2	SLRA1	SLRA0	146
INLVLA		_	INLVLA5	INLVLA4	INLVLA3	INLVLA2	INLVLA1	INLVLA0	146

TABLE 12-2: SUMMARY OF REGISTERS ASSOCIATED WITH PORTA

Legend: -= unimplemented locations read as '0'. Shaded cells are not used by PORTA.

TABLE 12-3: SUMMARY OF CONFIGURATION WORD WITH PORTA

Name	Bits	Bit -/7	Bit -/6	Bit 13/5	Bit 12/4	Bit 11/3	Bit 10/2	Bit 9/1	Bit 8/0	Register on Page
	13:8	—	—	DEBUG	STVREN	PPS1WAY	—	BORV	_	C.F.
CONFIG2	7:0	BOREN1	BOREN0	LPBOREN	_	WDTE1	WDTE0	PWRTE	MCLRE	65

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by PORTA.

12.4 PORTB Registers (PIC16(L)F18346 Only)

12.4.1 DATA REGISTER

PORTB is a 4-bit wide bidirectional port and is only available in the PIC16(L)F18346 devices. The corresponding data direction register is TRISB (Register 12-10). Setting a TRISB bit (= 1) will make the corresponding PORTB pin an input (i.e., put the corresponding output driver in a High-Impedance mode). Clearing a TRISB bit (= 0) will make the corresponding PORTB pin an output (i.e., enable the output driver and put the contents of the output latch on the selected pin). Example 12-1 shows how to initialize an I/O port.

Reading the PORTB register (Register 12-9) reads the status of the pins, whereas writing to it will write to the PORT latch. All write operations are read-modify-write operations. Therefore, a write to a port implies that the PORT pins are read; this value is modified and then written to the PORT data latch (LATB).

The PORT data latch LATB (Register 12-11) holds the output port data, and contains the latest value of a LATB or PORTB write.

12.4.2 DIRECTION CONTROL

The TRISB register (Register 12-10) controls the PORTB pin output drivers, even when they are being used as analog inputs. The user must ensure the bits in the TRISB register are maintained set when using them as analog inputs. I/O pins configured as analog inputs always read '0'.

12.4.3 INPUT THRESHOLD CONTROL

The INLVLB register (Register 12-16) controls the input voltage threshold for each of the available PORTB input pins. A selection between the Schmitt Trigger CMOS or the TTL Compatible thresholds is available. The input threshold is important in determining the value of a read of the PORTB register and also the level at which an interrupt-on-change occurs, if that feature is enabled. See Table 35-4 for more information on threshold levels.

Note: Changing the input threshold selection may be performed while all peripheral modules are disabled. Changing the threshold level during the time a module is active may inadvertently generate a transition associated with an input pin, regardless of the actual voltage level on that pin.

12.4.4 OPEN-DRAIN CONTROL

The ODCONB register (Register 12-14) controls the open-drain feature of the port. Open-drain operation is independently selected for each pin. When an ODCONB bit is set, the corresponding port output becomes an open-drain driver capable of sinking current only. When an ODCONB bit is cleared, the corresponding port output pin is the standard push-pull drive capable of sourcing and sinking current.

Note:	
	control when using the pin for I^2C ; the I^2C
	module controls the pin and makes the pin
	open-drain.

12.4.5 SLEW RATE CONTROL

The SLRCONB register (Register 12-15) controls the slew rate option for each PORT pin. Slew rate control is independently selectable for each PORT pin. When an SLRCONB bit is set, the corresponding PORT pin drive is slew rate limited. When an SLRCONB bit is cleared, the corresponding PORT pin drive slews at the maximum rate possible.

12.4.6 ANALOG CONTROL

The ANSELB register (Register 12-12) is used to configure the Input mode of an I/O pin to analog. Setting the appropriate ANSELB bit high will cause all digital reads on the pin to be read as '0' and allow analog functions on the pin to operate correctly.

The state of the ANSELB bits has no effect on digital output functions. A pin with TRIS clear and ANSELB set will still operate as a digital output, but the Input mode will be analog. This can cause unexpected behavior when executing read-modify-write instructions on the affected port.

The ANSELB bits default to the Analog mode after Reset. To use any pins as
digital general purpose or peripheral inputs, the corresponding ANSEL bits must be initialized to '0' by user software.

12.4.7 WEAK PULL-UP CONTROL

The WPUB register (Register 12-13) controls the individual weak pull-ups for each PORT pin.

12.4.8 PORTB FUNCTIONS AND OUTPUT PRIORITIES

Each pin defaults to the PORT latch data after Reset. Other output functions are selected with the peripheral pin select logic. See **Section 13.0 "Peripheral Pin Select (PPS) Module**" for more information.

Analog input functions, such as ADC and comparator inputs, are not shown in the peripheral pin select lists. Digital output functions may continue to control the pin when it is in Analog mode.

12.5 Register Definitions: PORTB

R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	U-0	U-0	U-0	U-0	
RB7	RB6	RB5	RB4	_	_	—		
bit 7							bit 0	
Legend:								
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unknown			nown	-n/n = Value at POR and BOR/Value at all other Resets				
'1' = Bit is set '0' = Bit is cleared								

REGISTER 12-9: PORTB: PORTB REGISTER

bit 7-4	RB<7:4>: PORTB I/O Value bits ⁽¹⁾
	1 = PORT pin is <u>></u> Vін
	0 = PORT pin is <u><</u> VIL

bit 3-0 Unimplemented: Read as '0'

Note 1: Writes to PORTB are actually written to corresponding LATB register. Reads from PORTB register return actual I/O pin values.

....

REGISTER 12-10: TRISB: PORTB TRI-STATE REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	U-0	U-0	U-0	U-0
TRISB7	TRISB6	TRISB5	TRISB4	—	—		—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4	TRISB<7:4>: PORTB I/O Tri-State Control bits
	1 = PORTB pin configured as an input (tri-stated)
	0 = PORTB pin configured as an output
bit 3-0	Unimplemented: Read as '0'

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	U-0	U-0	U-0	U-0	
LATB7	LATB6	LATB5	LATB4	—	—	—	—	
bit 7				·			bit 0	
Legend:								
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unknown			nown	-n/n = Value at POR and BOR/Value at all other Resets				
'1' = Bit is set		'0' = Bit is clea	ared					

REGISTER 12-11: LATB: PORTB DATA LATCH REGISTER

bit 7-4	LATB<7:4>: RB<5:4> Output Latch Value bits ⁽¹⁾
---------	---

bit 3-0 Unimplemented: Read as '0'

Note 1: Writes to LATB are equivalent with writes to the corresponding PORTB register. Reads from LATB register return register values, not I/O pin values.

REGISTER 12-12: ANSELB: PORTB ANALOG SELECT REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	U-0	U-0	U-0	U-0
ANSB7	ANSB6	ANSB5	ANSB4	—	—	_	—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 ANSB<7:4>: Analog Select between Analog or Digital Function

1 = Analog input. Pin is assigned as analog input⁽¹⁾. Digital input buffer disabled.

- 0 = Digital I/O. Pin is assigned to port or digital special function.
- bit 3-0 Unimplemented: Read as '0'
- **Note 1:** Setting ANSB[n] = 1 disables the digital input circuitry. Weak pull-ups, if available, are unaffected. The corresponding TRIS bit must be set to Input mode by the user to allow external control of the voltage on the pin.

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	U-0	U-0	U-0	U-0	
WPUB7	WPUB6	WPUB5	WPUB4	—	—	—	—	
bit 7							bit 0	
Legend:								
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unknown		nown	-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is clea	ared					

REGISTER 12-13: WPUB: WEAK PULL-UP PORTB REGISTER

bit 7-4	WPUB<7:4>: Weak Pull-up Register bits
	1 = Weak Pull-up enabled
	0 = Weak Pull-up disabled
bit 3-0	Unimplemented: Read as '0'

REGISTER 12-14: ODCONB: PORTB OPEN-DRAIN CONTROL REGISTER

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	U-0	U-0	U-0	U-0
ODCB7	ODCB6	ODCB5	ODCB4	—	—	—	—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 **ODCB<7:4>:** PORTB Open-Drain Configuration bits For RB<7:4> pins, respectively: 1 = PORT pin operates as open-drain drive (sink current only) 0 = PORT pin operates as standard push-pull drive (source and sink current)

bit 3-0 Unimplemented: Read as '0'

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	U-0	U-0	U-0	U-0
SLRB7	SLRB6	SLRB5	SLRB4	—	—	—	—
bit 7	·						bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is unchanged x = Bit is unknown		-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set '0' = Bit is cleared							

REGISTER 12-15: SLRCONB: PORTB SLEW RATE CONTROL REGISTER

bit 7-4	SLRB<7:4>: PORTB Slew Rate Control on pins RB<7:4>, respectively
	1 = Slew rate enabled
	0 = Slew rate disabled
	····

bit 3-0 Unimplemented: Read as '0'

REGISTER 12-16: INLVLB: PORTB INPUT LEVEL CONTROL REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	U-0	U-0	U-0	U-0
INLVLB7	INLVLB6	INLVLB5	INLVLB4	—	—	—	—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 INLVLB<7:4>: PORTB Input Level Select on pins RB<7:4>, respectively 1 = ST input used for PORT reads 0 = TTL input used for PORT reads

bit 3-0 Unimplemented: Read as '0'

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
PORTB	RB7	RB6	RB5	RB4					149
TRISB	TRISB7	TRISB6	TRISB5	TRISB4	_				149
LATB	LATB7	LATB6	LATB5	LATB4	_				150
ANSELB	ANSB7	ANSB6	ANSB5	ANSB4	_				150
WPUB	WPUB7	WPU6	WPUB5	WPUB4	_				151
ODCONB	ODCB7	ODCB6	ODCB5	ODCB4	_				151
SLRCONB	SLRB7	SLRB6	SLRB5	SLRB4					152
INLVLB	INLVLB7	INLVLB6	INLVLB5	INLVLB4	_	_	_		152

TABLE 12-4: SUMMARY OF REGISTERS ASSOCIATED WITH PORTB

Legend: x = unknown, u = unchanged, – = unimplemented locations read as '0'. Shaded cells are not used by PORTB.

12.6 PORTC Registers

12.6.1 DATA REGISTER

PORTC is a bidirectional port that is either 6-bit wide (PIC16(L)F18326) or 8-bit wide (PIC16(L)F18346). The corresponding data direction register is TRISC (Register 12-18). Setting a TRISC bit (= 1) will make the corresponding PORTC pin an input (i.e., put the corresponding output driver in a High-Impedance mode). Clearing a TRISC bit (= 0) will make the corresponding PORTC pin an output (i.e., enable the output driver and put the contents of the output latch on the selected pin). Example 12-1 shows how to initialize an I/O port.

Reading the PORTC register (Register 12-17) reads the status of the pins, whereas writing to it will write to the PORT latch. All write operations are read-modify-write operations. Therefore, a write to a port implies that the PORT pins are read, this value is modified and then written to the PORT data latch (LATC).

The PORT data latch LATC (Register 12-19) holds the output port data, and contains the latest value of a LATC or PORTC write.

12.6.2 DIRECTION CONTROL

The TRISC register (Register 12-18) controls the PORTC pin output drivers, even when they are being used as analog inputs. The user must ensure the bits in the TRISC register are maintained set when using them as analog inputs. I/O pins configured as analog inputs always read '0'.

12.6.3 INPUT THRESHOLD CONTROL

The INLVLC register (Register 12-24) controls the input voltage threshold for each of the available PORTC input pins. A selection between the Schmitt Trigger CMOS or the TTL Compatible thresholds is available. The input threshold is important in determining the value of a read of the PORTC register and also the level at which an interrupt-on-change occurs, if that feature is enabled. See Table 35-4 for more information on threshold levels.

Note: Changing the input threshold selection may be performed while all peripheral modules are disabled. Changing the threshold level during the time a module is active may inadvertently generate a transition associated with an input pin, regardless of the actual voltage level on that pin.

12.6.4 OPEN-DRAIN CONTROL

The ODCONC register (Register 12-22) controls the open-drain feature of the port. Open-drain operation is independently selected for each pin. When an ODCONC bit is set, the corresponding port output becomes an open-drain driver capable of sinking current only. When an ODCONC bit is cleared, the corresponding port output pin is the standard push-pull drive capable of sourcing and sinking current.

Note:	It is not necessary to set open-drain control when using the pin for I ² C; the I ² C
	module controls the pin and makes the pin open-drain.

12.6.5 SLEW RATE CONTROL

The SLRCONC register (Register 12-23) controls the slew rate option for each PORT pin. Slew rate control is independently selectable for each PORT pin. When an SLRCONC bit is set, the corresponding PORT pin drive is slew rate limited. When an SLRCONC bit is cleared, The corresponding PORT pin drive slews at the maximum rate possible.

12.6.6 ANALOG CONTROL

The ANSELC register (Register 12-20) is used to configure the Input mode of an I/O pin to analog. Setting the appropriate ANSELC bit high will cause all digital reads on the pin to be read as '0' and allow analog functions on the pin to operate correctly.

The state of the ANSELC bits has no effect on digital output functions. A pin with TRIS clear and ANSELC set will still operate as a digital output, but the Input mode will be analog. This can cause unexpected behavior when executing read-modify-write instructions on the affected port.

Note:	The ANSELC bits default to the Analog mode after Reset. To use any pins as
	digital general purpose or peripheral inputs, the corresponding ANSEL bits
	must be initialized to '0' by user software.

12.6.7 WEAK PULL-UP CONTROL

The WPUC register (Register 12-21) controls the individual weak pull-ups for each PORT pin.

12.6.8 PORTC FUNCTIONS AND OUTPUT PRIORITIES

Each pin defaults to the PORT latch data after Reset. Other functions are selected with the peripheral pin select logic. See **Section 13.0 "Peripheral Pin Select** (**PPS**) **Module**" for more information.

Analog output functions, such as ADC and comparator inputs, are not shown in the peripheral pin select lists. Digital output functions may continue to control the pin when it is in Analog mode.

12.7 Register Definitions: PORTC

REGISTER 12-17: PORTC: PORTC REGISTER

	-	-					
R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
RC7 ⁽¹⁾	RC6 ⁽¹⁾	RC5	RC4	RC3	RC2	RC1	RC0
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	l as '0'	
u = Bit is uncha	u = Bit is unchanged x = Bit is unknown -n/n = Value at POR and BOR/Value at all other			other Resets			
'1' = Bit is set		'0' = Bit is cle	ared				
		-					
bit 7-6	RC<7:6>: P(ORTC I/O Value	bits ^(1,2)				

DIL 7-0	
	1 = PORT pin is <u>></u> V IH
	0 = PORT pin is <u><</u> VIL
bit 5-0	RC<5:0>: PORTC General Purpose I/O Pin bits ⁽²⁾
	1 = PORT pin is <u>></u> V IH
	0 = PORT pin is <u><</u> VIL

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

2: Writes to PORTC are actually written to corresponding LATC register. Reads from PORTC register is return of actual I/O pin values.

REGISTER 12-18: TRISC: PORTC TRI-STATE REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	TRISC<7:6> : PORTC Tri-State Control bits ⁽¹⁾ 1 = PORTC pin configured as an input (tri-stated) 0 = PORTC pin configured as an output
bit 5-0	TRISC<5:0>: PORTC Tri-State Control bits 1 = PORTC pin configured as an input (tri-stated) 0 = PORTC pin configured as an output

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
LATC7 ⁽¹⁾	LATC6 ⁽¹⁾	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0
bit 7				-			bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, read	as '0'	
u = Bit is uncha	anged	x = Bit is unkn	iown	-n/n = Value a	at POR and BOI	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared				

REGISTER 12-19: LATC: PORTC DATA LATCH REGISTER

bit 7-6 LATC<7:6>: PORTC Output Latch Value bits⁽¹⁾

bit 5-0 LATC<5:0>: PORTC Output Latch Value bits

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0
				L		bit 0
bit	W = Writable	bit	U = Unimpler	nented bit, read	d as '0'	
anged	x = Bit is unkr	nown	-n/n = Value a	at POR and BC	R/Value at all	other Resets
	'0' = Bit is clea	ared				
	ANSC6 ⁽¹⁾	ANSC6 ⁽¹⁾ ANSC5bitW = Writableangedx = Bit is unkr	ANSC6 ⁽¹⁾ ANSC5 ANSC4 bit W = Writable bit	ANSC6 ⁽¹⁾ ANSC5 ANSC4 ANSC3 bit W = Writable bit U = Unimpler anged x = Bit is unknown -n/n = Value a	ANSC6 ⁽¹⁾ ANSC5ANSC4ANSC3ANSC2bitW = Writable bitU = Unimplemented bit, read anged $x = Bit$ is unknown $-n/n = Value$ at POR and BC	ANSC6 ⁽¹⁾ ANSC5ANSC4ANSC3ANSC2ANSC1bitW = Writable bitU = Unimplemented bit, read as '0'angedx = Bit is unknown-n/n = Value at POR and BOR/Value at all of the second sec

REGISTER 12-20: ANSELC: PORTC ANALOG SELECT REGISTER

bit 7-6	ANSC<7:6> : Analog Select between Analog or Digital Function on pins RC<7:6>, respectively ⁽¹⁾ 1 = Analog input. Pin is assigned as analog input ⁽²⁾ . Digital input buffer disabled. 0 = Digital I/O. Pin is assigned to port or digital special function.
bit 5-0	 ANSC<5:0>: Analog Select between Analog or Digital Function on pins RC<5:0>, respectively 1 = Analog input. Pin is assigned as analog input⁽²⁾. Digital input buffer disabled. 0 = Digital I/O. Pin is assigned to port or digital special function.

- Note 1: PIC16(L)F18346 only; otherwise read as '0'.
 - 2: When setting a pin to an analog input, the corresponding TRIS bit must be set to Input mode to allow external control of the voltage on the pin.

REGISTER 12-21: WPUC: WEAK PULL-UP PORTC REGISTER

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
WPUC7 ⁽¹⁾	WPUC6 ⁽¹⁾	WPUC5	WPUC4	WPUC3	WPUC2	WPUC1	WPUC0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	WPUC<7:6> ⁽¹⁾ : Weak Pull-up Register bits ⁽²⁾
	1 = Pull-up enabled
	0 = Pull-up disabled
bit 5-0	WPUC<5:0>: Weak Pull-up Register bits ⁽²⁾
	1 = Pull-up enabled
	0 = Pull-up disabled

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

2: The weak pull-up device is automatically disabled if the pin is configured as an output.

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
ODCC7 ⁽¹⁾	ODCC6 ⁽¹⁾	ODCC5	ODCC4	ODCC3	ODCC2	ODCC1	ODCC0
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is unch	anged	x = Bit is unkr	iown	-n/n = Value a	at POR and BO	R/Value at all o	ther Resets
'1' = Bit is set		'0' = Bit is clea	ared				
bit 7-6	bit 7-6 ODCC<7:6> : PORTC Open-Drain Enable bits ⁽¹⁾ For RC<7:6> pins, respectively 1 = PORT pin operates as open-drain drive (sink current only) 0 = PORT pin operates as standard push-pull drive (source and sink current)						
bit 5-0 ODCC<5:0>: PORTC Open-Drain Enable bits For RC<5:0> pins, respectively 1 = PORT pin operates as open-drain drive (sink current only) 0 = PORT pin operates as standard push-pull drive (source and sink current)							
	16/1) 19246 -	بمايد ملامم سيرامه					

REGISTER 12-22: ODCONC: PORTC OPEN-DRAIN CONTROL REGISTER

Note 1:	PIC16(L)F18346 only; otherwise read as '0'.	
---------	---	--

REGISTER 12-23: SLRCONC: PORTC SLEW RATE CONTROL REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
SLRC7 ⁽¹⁾	SLRC6 ⁽¹⁾	SLRC5	SLRC4	SLRC3	SLRC2	SLRC1	SLRC0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	SLRC<7:6>: PORTC Slew Rate Enable bits ⁽¹⁾ For RC<7:6> pins, respectively 1 = PORT pin slew rate is limited 0 = PORT pin slews at maximum rate
bit 5-0	SLRC<5:0>: PORTC Slew Rate Enable bits For RC<5:0> pins, respectively 1 = PORT pin slew rate is limited 0 = PORT pin slews at maximum rate

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

R/W-1/1 INLVLC7 ⁽¹⁾ bit 7	R/W-1/1 INLVLC6 ⁽¹⁾	R/W-1/1 INLVLC5	R/W-1/1 INLVLC4	R/W-1/1 INLVLC3	R/W-1/1	R/W-1/1	R/W-1/1			
	INLVLC6 ⁽¹⁾	INLVLC5	INLVLC4							
bit 7				INLVLCS	INLVLC2	INLVLC1	INLVLC0			
							bit 0			
Legend:										
R = Readable bi	t	W = Writable b	bit	U = Unimpler	nented bit, read	as '0'				
u = Bit is unchanged x = Bit is unknown				-n/n = Value at POR and BOR/Value at all other Resets						
'1' = Bit is set		'0' = Bit is clea	red							
bit 5-0	For RC<7:6> 1 = ST input u 2 = TTL input NLVLC<5:0> For RC<5:0> 1 = ST input u	: PORTC Input pins, respective used for PORT used for PORT PORTC Input pins, respective used for PORT	ely reads and into reads and in Level Select ely reads and into	errupt-on-chan terrupt-on-cha bits errupt-on-chan	nge ge					

REGISTER 12-24: INLVLC: PORTC INPUT LEVEL CONTROL REGISTER

Note 1: PIC16(L)F18346 only; otherwise read as '0'.

TABLE 12-5: SUMMARY OF REGISTERS ASSOCIATED WITH PORTC

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
PORTC	RC7 ⁽¹⁾	RC6 ⁽¹⁾	RC5	RC4	RC3	RC2	RC1	RC0	155
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
LATC	LATC7 ⁽¹⁾	LATC6 ⁽¹⁾	LATC5	LATC4	LATC3	LATC2	LATC1	LATC0	156
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
WPUC	WPUC7 ⁽¹⁾	WPUC6 ⁽¹⁾	WPUC5	WPUC4	WPUC3	WPUC2	WPUC1	WPUC0	157
ODCONC	ODCC7 ⁽¹⁾	ODCC6 ⁽¹⁾	ODCC5	ODCC4	ODCC3	ODCC2	ODCC1	ODCC0	158
SLRCONC	SLRC7 ⁽¹⁾	SLRC6 ⁽¹⁾	SLRC5	SLRC4	SLRC3	SLRC2	SLRC1	SLRC0	158
INLVLC	INLVLC7 ⁽¹⁾	INLVLC6 ⁽¹⁾	INLVLC5	INLVLC4	INLVLC3	INLVLC2	INLVLC1	INLVLC0	159

Each I/O pin has a PPS register with which the pin output source is selected. With few exceptions, the port

TRIS control associated with that pin retains control

over the pin output driver. Peripherals that control the

pin output driver as part of the peripheral operation will

override the TRIS control as needed. These

Although every pin has its own PPS peripheral selection register, the selections are identical for every

The notation "Rxy" is a place holder for the

pin identifier. For example, RA0PPS.

PPS Outputs

• EUSART1 (synchronous operation)

pin as shown in Register 13-2.

13.2

peripherals are:

MSSP (I²C)

Note:

13.0 PERIPHERAL PIN SELECT (PPS) MODULE

The Peripheral Pin Select (PPS) module connects peripheral inputs and outputs to the device I/O pins. Only digital signals are included in the selections. All analog inputs and outputs remain fixed to their assigned pins. Input and output selections are independent as shown in the simplified block diagram Figure 13-1.

13.1 PPS Inputs

Each peripheral has a PPS register with which the inputs to the peripheral are selected. Inputs include the device pins.

Although every peripheral has its own PPS input selection register, the selections are identical for every peripheral as shown in Register 13-1.

Note:	The notation "xxx" in the register name is
	a place holder for the peripheral identifier.
	For example, CLC1PPS.

FIGURE 13-1: SIMPLIFIED PPS BLOCK DIAGRAM

PPS Inputs RA0 PPS RA0 PPS RA0 PPS RA0 Peripheral abc Peripheral abc Peripheral xyz RC7⁽¹⁾ RA0 RxyPPS Rxy RC7⁽¹⁾ Rxy RC7⁽¹⁾ RC7⁽¹⁾ Rxy RC7⁽¹⁾ RC7⁽¹⁾ RC7⁽¹⁾

DS40001839F-page 160

13.3 Bidirectional Pins

PPS selections for peripherals with bidirectional signals on a single pin must be made so that the PPS input and PPS output select the same pin. This requires configuring both the appropriate xxxPPS input and RxyPPS output registers. For example, if the SCL1 line is routed to pin RC0, the SSP1SCLPPS input register will be set to '10000' (routes to RC0) and the RC0PPS output register will be set to '11000' (routes the SCL1 internal connection to RC0). Peripherals that have bidirectional signals are:

- EUSART1 (synchronous operation)
- MSSP (I²C)
 - Note: The I²C default input pins are I²C and SMBus compatible and are the only pins on the PIC16(L)F18326 with this compatibility. For the PIC16(L)F18346, in addition to the default pins as described above, RC0, RC1, RC4, and RC5 are also I²C and SMBus compatible. Clock and data signals can be routed to any pin, however pins without I²C compatibility will operate at standard TTL/ST logic levels as selected by the INVLV register.

13.4 PPSLOCKED Bit

The PPS includes a mode in which all input and output selections can be locked to prevent inadvertent changes. PPS selections are locked by setting the PPSLOCKED bit of the PPSLOCK register. Setting and clearing this bit requires a special sequence as an extra precaution against inadvertent changes. Examples of setting and clearing the PPSLOCKED bit are shown in Example 13-1.

EXAMPLE 13-1: PPS LOCK/UNLOCK SEQUENCE

;	suspend interrupts
	bcf INTCON,GIE
;	BANKSEL PPSLOCK ; set bank
;	required sequence, next 5 instructions
	movlw 0x55
	movwf PPSLOCK
	movlw 0xAA
	movwf PPSLOCK
;	Set PPSLOCKED bit to disable writes or
;	Clear PPSLOCKED bit to enable writes
	bsf PPSLOCK, PPSLOCKED
;	restore interrupts
	bsf INTCON,GIE
	bsf INTCON,GIE

13.5 PPS1WAY Bit

The PPS can be locked by setting the PPS1WAY bit of Configuration Word 2.

When the PPS1WAY bit is set, the PPSLOCKED bit of the PPSLOCK register can be cleared and set only one time after a device Reset. Once the PPS registers are configured, user software sets the PPSLOCKED bit, preventing any further writes to the PPS registers. the PPS registers can be read at any time, regardless of the PPS1WAY or PPSLOCKED settings.

When the PPS1WAY bit is clear, the PPSLOCKED bit of the PPSLOCK register can be cleared and set multiple times during code execution, but requires the PPS lock/unlock sequence to be performed each time modifications to the PPS registers are made.

13.6 Operation During Sleep

PPS input and output selections are unaffected by Sleep.

13.7 Effects of a Reset

A device Power-On-Reset (POR) clears all PPS input and output selections to their default values, and clears the PPSLOCKED bit of the PPSLOCK register. All other Resets leave the selections unchanged. Default input selections are shown in pin allocation Table 2 and Table 3.


13.8 Register Definitions: PPS Input Selection

REGISTER 13-1: xxxPPS: PERIPHERAL xxx INPUT SELECTION

U-0	U-0	U-0	R/W-q/u	R/W-q/u	R/W-q/u	R/W-q/u	R/W-q/u			
—	—	—			xxxPPS<4:0>					
bit 7							bit (
Legend:										
R = Readat	ole hit	W = Writable	hit	= Inimpler	nented bit, read	l as 'N'				
u = Bit is unchanged x = Bit is unknown					at POR and BO		ther Resets			
(1) = Bit is charged (1) = Bit is charged (1) = Bit is cleared (1) = B					pends on periph					
				<u> </u>						
bit 7-5	Unimpleme	ented: Read as	ʻ0 '							
bit 4-0		0>: Peripheral x	•	tion bits						
	11xxx = Re	eserved. Do not	use.							
	10111 = Peripheral input is RC7 ⁽¹⁾									
	10110 = Peripheral input is RC6 ⁽¹⁾									
		10101 = Peripheral input is RC5								
		ripheral input is								
		eripheral input is								
		10010 = Peripheral input is RC2 10001 = Peripheral input is RC1								
		10000 = Peripheral input is RC1 10000 = Peripheral input is RC0								
	01111 = P e	eripheral input is	RB7 ⁽¹⁾							
	01110 = Pe	eripheral input is	RB6(')							
	01101 = Peripheral input is RB5 ⁽¹⁾ 01100 = Peripheral input is RB4 ⁽¹⁾									
	01100 – Fe	inprierar input is	ND4' /							
		eserved. Do not	use.							
		ripheral input is								
	00100 = Pe	eripheral input is	RA4							
		eripheral input is								
		eripheral input is								
		eripheral input is								
	00000 = Pe	eripheral input is	RA0							

U-0	U-0	U-0	R/W-0/u	R/W-0/u	R/W-0/u	R/W-0/u	R/W-0/u					
_	_	_			RxyPPS<4:0>							
pit 7							bit					
Legend:												
R = Readabl	le bit	W = Writable	e bit	U = Unimpler	mented bit, read	l as '0'						
u = Bit is und		x = Bit is unl		•	at POR and BO		ther Resets					
'1' = Bit is se	-	'0' = Bit is cl										
1 - Dit 13 30	<i>.</i>		carcu									
bit 7-5	Unimplomo	ntad: Read as	'o'									
bit 4-0	-	Unimplemented: Read as '0'										
DIL 4-0	-	RxyPPS<4:0>: Pin Rxy Output Source Selection bits										
		11111 = Rxy source is DSM 11110 = Rxy source is CLKR										
		1110 = Rxy source is CLKR 1101 = Rxy source is NCO1										
		1101 = Rxy source is NCO1 1100 = Rxy source is TMR0										
		$1011 = \text{Rxy source is SDO2/SDA2}^{(1)}$										
		y source is SC										
		, y source is SD										
		, y source is SC										
		, y source is C2										
		y source is C1										
		y source is DT										
		y source is TX/										
		y source is CW										
		y source is CW										
		y source is CW										
		y source is CW										
		y source is CC										
		y source is CC										
		y source is CC										
		y source is CC										
		y source is CW										
		y source is CW y source is CW										
		y source is CW										
		y source is CV										
		y source is CL										
		y source is CL										
		y source is CL										
		y source is PW										
		y source is PW										
	00001 = Re	-	-									
	00000 = Re											

REGISTER 13-2: RxyPPS: PIN Rxy OUTPUT SOURCE SELECTION REGISTER



REGISTER 13-3: PPSLOCK: PPS LOCK REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0/0
—	—	—	—	—	_	—	PPSLOCKED
bit 7							bit 0
Legend:							

Logona.		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-1 Unimplemented: Read as '0'

bit 0 PPSLOCKED: PPS Locked bit 1= PPS is locked. PPS selections can not be changed. 0= PPS is not locked. PPS selections can be changed.

TABLE 13-1: SUMMARY OF REGISTERS ASSOCIATED WITH THE PPS MODULE

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on page
PPSLOCK		—		—	_		_	PPSLOCKED	164
INTPPS						INTPPS<	4:0>		162
T0CKIPPS						T0CKIPPS	<4:0>		162
T1CKIPPS						T1CKIPPS	<4:0>		162
T1GPPS						T1GPPS<	:4:0>		162
T3CKIPPS						T3CKIPPS	<4:0>		162
T3GPPS						T3GPPS<	:4:0>		162
T5CKIPPS						T5CKIPPS	<4:0>		162
T5GPPS						T5GPPS<	:4:0>		162
CCP1PPS		_				CCP1PPS	<4:0>		162
CCP2PPS						CCP2PPS	<4:0>		162
CCP3PPS						CCP3PPS	<4:0>		162
CCP4PPS						CCP4PPS	<4:0>		162
CWG1PPS						CWG1PPS	<4:0>		162
CWG2PPS						CWG2PPS	<4:0>		162
MDCIN1PPS					Ν	MDCIN1PP	S<4:0>		162
MDCIN2PPS					Ν	MDCIN2PP	S<4:0>		162
MDMINPPS						MDMINPPS	6<4:0>		162
SSP1CLKPPS					S	SP1CLKPF	PS<4:0>		162
SSP1DATPPS					S	SP1DATPF	°S<4:0>		162
SSP1SSPPS	_	—			S	SSP1SSPP	S<4:0>		162
SSP2CLKPPS	_	—			S	SP2CLKPF	PS<4:0>		162
SSP2DATPPS	_	—			S	SP2DATPF	PS<4:0>		162
SSP2SSPPS	_	—			S	SSP2SSPP	S<4:0>		162

Legend: — = unimplemented, read as '0'. Shaded cells are unused by the PPS module.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on page		
RXPPS	_	_			RXPPS<4:0>						
CLCIN0PPS		_			(CLCIN0PP	S<4:0>		162		
CLCIN1PPS	—	_	_		(CLCIN1PP	S<4:0>		162		
CLCIN2PPS	—	_	_		(CLCIN2PP	S<4:0>		162		
CLCIN3PPS	—	_	_		(CLCIN3PP	S<4:0>		162		
RA0PPS	—	_	_			RA0PPS<	:4:0>		163		
RA1PPS	—	_	_			RA1PPS<	:4:0>		163		
RA2PPS	—	_	_			RA2PPS<	:4:0>		163		
RA4PPS	—	_	_			RA4PPS<	:4:0>		163		
RA5PPS	—	_	_			RA5PPS<	:4:0>		163		
RB4PPS ⁽¹⁾		_				RB4PPS<	:4:0>		163		
RB5PPS ⁽¹⁾		_				RB5PPS<	:4:0>		163		
RB6PPS ⁽¹⁾		_				RB6PPS<	:4:0>		163		
RB7PPS ⁽¹⁾	—	_				RB7PPS<	:4:0>		163		
RC0PPS	—	_	_			RC0PPS<	:4:0>		163		
RC1PPS	—	_	_			RC1PPS<	:4:0>		163		
RC2PPS	—	_	_			RC2PPS<	:4:0>		163		
RC3PPS	—	_	_			RC3PPS<	:4:0>		163		
RC4PPS	—	—			RC4PPS<4:0>						
RC5PPS	—	—				RC5PPS<	:4:0>		163		
RC6PPS ⁽¹⁾	—	—				RC6PPS<	:4:0>		163		
RC7PPS ⁽¹⁾	—	—				RC7PPS<	:4:0>		163		

TABLE 13-1:	SUMMARY OF REGISTERS ASSOCIATED WITH THE PPS MODULE (CONTINUED)
-------------	---

Legend: — = unimplemented, read as '0'. Shaded cells are unused by the PPS module.

14.0 PERIPHERAL MODULE DISABLE

The PIC16(L)F18326/18346 provides the ability to disable selected modules, placing them into the lowest possible power mode.

For legacy reasons, all modules are ON by default following any Reset.

14.1 **Disabling a Module**

Disabling a module has the following effects:

- · All clock and control inputs to the module are suspended; there are no logic transitions, and the module will not function.
- · The module is held in Reset.
- Writing to the SFRs is disabled
- Reads return 00h
- · Analog outputs are disabled; Digital outputs read '∩'

14.2 **Enabling a Module**

When the register bit is cleared, the module is reenabled and will be in its Reset state; SFR data will reflect the POR Reset values.

Depending on the module, it may take up to one full instruction cycle for the module to become active. There must be no interaction with the module (e.g., writing to registers) for at least one instruction after it has been re-enabled.

14.3 System Clock Disable


Setting SYSCMD (PMD0, Register 14-1) disables the system clock (Fosc) distribution network to the peripherals. Not all peripherals make use of SYSCLK, so not all peripherals are affected. Refer to the specific peripheral description to see if it will be affected by this bit.

REGISTER 14-1: PMD0: PMD CONTROL REGISTER 0

R/W-0/0	R/W-0/0	U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0
SYSCMD	FVRMD	_	—	_	NVMMD	CLKRMD	IOCMD
7							0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Value depends on condition

bit 7	 SYSCMD: Disable Peripheral System Clock Network bit See description in Section 14.3 "System Clock Disable". 1 = System Clock network disabled (a.k.a. Fosc) 0 = System Clock network enabled
bit 6	FVRMD: Disable Fixed Voltage Reference FVR bit 1 = FVR module disabled 0 = FVR module enabled
bit 5-3	Unimplemented: Read as '0'
bit 2	 NVMMD: NVM Module Disable bit⁽¹⁾ 1 = Data EEPROM (a.k.a. user memory, EEPROM) reading and writing is disabled; NVMCON registers cannot be written; FSR access to EEPROM returns zero. 0 = NVM module enabled
bit 1	CLKRMD: Disable Clock Reference CLKR bit 1 = CLKR module disabled 0 = CLKR module enabled
bit 0	IOCMD: Disable Interrupt-on-Change bit, All Ports 1 = IOC module(s) disabled 0 = IOC module(s) enabled
Note 1	When enabling NVM a delay of up to 1 us may be required before accessing data



R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
NCOMD	TMR6MD	TMR5MD	TMR4MD	TMR3MD	TMR2MD	TMR1MD	TMR0MD
bit 7							bit (
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimplem	nented bit, read	l as '0'	
u = Bit is unc	hanged	x = Bit is unkr	iown	-n/n = Value a	t POR and BO	R/Value at all c	ther Resets
'1' = Bit is se	İ	'0' = Bit is clea	ared	q = Value dep	ends on condit	ion	
bit 7	1 = NCO1 m	able Numerical odule disabled odule enabled	y Control Osci	llator bit			
bit 6		sable Timer TM odule disabled odule enabled	R6 bit				
bit 5		sable Timer TM odule disabled odule enabled	R5 bit				
bit 4		sable Timer TM odule disabled odule enabled	R4 bit				
bit 3	TMR3MD: Disable Timer TMR3 bit 1 = TMR3 module disabled 0 = TMR3 module enabled						
bit 2	1 = TMR2 m	sable Timer TM odule disabled odule enabled	R2 bit				
bit 1	1 = TMR1 m	sable Timer TM odule disabled odule enabled	R1 bit				
bit 0		sable Timer TM odule disabled	R0 bit				

REGISTER 14-2: PMD1: PMD CONTROL REGISTER 1

U-0	R/W-0/0	R/W-0/0	U-0	U-0	R/W-0/0	R/W-0/0	U-0
	DACMD	ADCMD	—	_	CMP2MD	CMP1MD	—
bit 7							bit 0
Lovendi							
Legend: R = Readable	bit	W = Writable I	oit	U = Unimpler	nented bit, read	l as '0'	
u = Bit is unch	nanged	x = Bit is unkn	own	-n/n = Value a	t POR and BO	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared	q = Value dep	ends on condit	ion	
bit 7	Unimplemen	ted: Read as 'o)'				
bit 6	bit 6 DACMD: Disable DAC bit 1 = DAC module disabled 0 = DAC module enabled						
bit 5	ADCMD: Disa 1 = ADC mod 0 = ADC mod	dule disabled					
bit 4-3	Unimplemen	ted: Read as 'o)'				
bit 2	-						
bit 1	bit 1 CMP1MD: Disable Comparator C1 bit 1 = C1 module disabled 0 = C1 module enabled						
bit 0	Unimplemen	ted: Read as '()'				

REGISTER 14-3: PMD2: PMD CONTROL REGISTER 2

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
CWG2MD	CWG1MD	PWM6MD	PWM5MD	CCP4MD	CCP3MD	CCP2MD	CCP1MD
bit 7							bit
• • • • • •							
Legend:							
R = Readable	e bit	W = Writable		•	nented bit, read		
u = Bit is uncl	0	x = Bit is unkr		-n/n = Value a	t POR and BO	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is clea	ared	q = Value dep	ends on condit	ion	
bit 7		isable CWG2 b odule disabled odule enabled	it				
bit 6	CWG1MD: Di 1 = CWG1 m	isable CWG1 b odule disabled odule enabled	it				
bit 5	1 = PWM6 m	isable PWM6 b odule disabled odule enabled	it				
bit 4	1 = PWM5 m	isable PWM5 b odule disabled odule enabled	it				
bit 3	CCP4MD: Dis 1 = CCP4 mo 0 = CCP4 mo						
bit 2	CCP3MD: Disable CCP3 bit 1 = CCP3 module disabled 0 = CCP3 module enabled						
bit 1	CCP2MD: Disable CCP2 bit 1 = CCP2 module disabled 0 = CCP2 module enabled						
bit 0		sable CCP1 bit odule disabled					

REGISTER 14-4: PMD3: PMD CONTROL REGISTER 3

U-0	U-0	R/W-0/0	U-0	U-0	R/W-0/0	R/W-0/0	U-0
—	—	UART1MD	—	—	MSSP2MD	MSSP1MD	—
bit 7							bit 0
Legend:							
R = Readable	e bit	W = Writable I	bit	U = Unimplem	ented bit, read	as '0'	
u = Bit is unch	nanged	x = Bit is unkn	own	-n/n = Value a	t POR and BOP	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is clea	ared	q = Value dep	ends on conditi	on	
bit 7-6	Unimplement	t ed: Read as '0)'				
bit 5		isable EUSAR					
		1 module disab					
h:+ 4 0		1 module enabl					
bit 4-3	-	ted: Read as '0					
bit 2		isable MSSP2 nodule disablec					
		nodule enabled	-				
bit 1		isable MSSP1					
	1 = MSSP1 module disabled						
	0 = MSSP1 n	nodule enabled					
bit 0	Unimplement	ted: Read as '0)'				

REGISTER 14-5: PMD4: PMD CONTROL REGISTER 4

U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
_	_	_	CLC4MD	CLC3MD	CLC2MD	CLC1MD	DSMMD
bit 7							bit 0
Legend:							
R = Readab	ole bit	W = Writable	bit	U = Unimplen	nented bit, read	l as '0'	
u = Bit is un	ichanged	x = Bit is unkr	iown	-n/n = Value a	at POR and BO	R/Value at all c	other Resets
'1' = Bit is se	et	'0' = Bit is clea	ared	q = Value dep	ends on condit	ion	
bit 7-5	Unimpleme	nted: Read as ')'				
bit 4	1 = CLC4 m	isable CLC4 bit nodule disabled nodule enabled					
bit 3	1 = CLC3 m	isable CLC3 bit nodule disabled nodule enabled					
bit 2 CLC2MD: Disable CLC2 bit 1 = CLC2 module disabled 0 = CLC2 module enabled							
bit 1	CLC1MD: Disable CLC1 bit 1 = CLC1 module disabled 0 = CLC1 module enabled						
bit 0	1 = DSM m	sable Data Signa odule disabled odule enabled	al Modulator bi	t			

REGISTER 14-6: PMD5: PMD CONTROL REGISTER 5

15.0 INTERRUPT-ON-CHANGE

All pins on all ports can be configured to operate as Interrupt-On-Change (IOC) pins. An interrupt can be generated by detecting a signal that has either a rising edge or a falling edge. Any individual pin, or combination of pins, can be configured to generate an interrupt. The interrupt-on-change module has the following features:

- Interrupt-on-Change enable
- Rising and falling edge detection
- · Individual pin configuration
- Individual pin interrupt flags

Figure 15-1 is a block diagram of the IOC module.

15.1 Enabling the Module

To allow individual pins to generate an interrupt, the IOCIE bit of the PIE0 register must be set. If the IOCIE bit is disabled, the edge detection on the pin will still occur, but an interrupt will not be generated.

15.2 Individual Pin Configuration

For each pin, a rising edge detector and a falling edge detector are present. To enable a pin to detect a rising edge, the associated bit of the IOCxP register is set. To enable a pin to detect a falling edge, the associated bit of the IOCxN register is set.

A pin can be configured to detect rising and falling edges simultaneously by setting the associated bits in both of the IOCxP and IOCxN registers.

15.3 Interrupt Flags

The bits located in the IOCxF registers are status flags that correspond to the interrupt-on-change pins of each port. If an expected edge is detected on an appropriately enabled pin, then the status flag for that pin will be set, and an interrupt will be generated if the IOCIE bit is set. The IOCIF bit of the PIR0 register reflects the status of all IOCxF bits.

15.4 Clearing Interrupt Flags

The individual status flags (IOCxF register bits) can be cleared by resetting them to zero. If another edge is detected during this clearing operation, the associated status flag will be set at the end of the sequence, regardless of the value actually being written.

To ensure that no detected edge is lost while clearing flags, only AND operations masking out known changed bits may be performed. The following sequence is an example of what may be performed.


EXAMPLE 15-1: CLEARING INTERRUPT FLAGS (PORTA EXAMPLE)

MOVLW 0xff XORWF IOCAF, W ANDWF IOCAF, F

15.5 Operation in Sleep

The interrupt-on-change interrupt event will wake the device from Sleep mode, if the IOCIE bit is set.

If an edge is detected while in Sleep mode, the affected IOCxF register will be updated prior to the first instruction executed out of Sleep.



15.6 Register Definitions: Interrupt-on-Change Control

U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
				N/W-0/0	R/VV-0/0	R/W-0/U	
_	IOCAP5	IOCAP4	IOCAP3	IOCAP2	IOCAP1	IOCAP0	
						bit 0	
R = Readable bit W = Writable bit		bit	U = Unimplemented bit, read as '0'				
= Bit is unchanged x = Bit is unknown		-n/n = Value a	at POR and BO	R/Value at all o	ther Resets		
	'0' = Bit is clea	ared					
		anged x = Bit is unkr		anged x = Bit is unknown -n/n = Value a	anged x = Bit is unknown -n/n = Value at POR and BOI	anged x = Bit is unknown -n/n = Value at POR and BOR/Value at all o	

REGISTER 15-1: IOCAP: INTERRUPT-ON-CHANGE PORTA POSITIVE EDGE REGISTER

bit 7-6 Unimplemented: Read as '0'

bit 5-0 **IOCAP<5:0>:** Interrupt-on-Change PORTA Positive Edge Enable bits

- 1 = Interrupt-on-Change enabled on the pin for a positive going edge. IOCAFx bit and IOCIF flag will be set upon detecting an edge.
- 0 = Interrupt-on-change disabled for the associated pin

REGISTER 15-2: IOCAN: INTERRUPT-ON-CHANGE PORTA NEGATIVE EDGE REGISTER

U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
_	_	IOCAN5	IOCAN4	IOCAN3	IOCAN2	IOCAN1	IOCAN0	
bit 7		•					bit 0	
Legend:								
R = Readable bit W = Writable bit			hit	II = IInimplemented bit read as '0'				

R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 Unimplemented: Read as '0'

bit 5-0 IOCAN<5:0>: Interrupt-on-Change PORTA Negative Edge Enable bits

- 1 = Interrupt-on-Change enabled on the pin for a negative going edge. IOCAFx bit and IOCIF flag will be set upon detecting an edge.
- 0 = Interrupt-on-Change disabled for the associated pin

U-0	U-0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0
—	—	IOCAF5	IOCAF4	IOCAF3	IOCAF2	IOCAF1	IOCAF0
bit 7							bit 0
Legend:							
R = Readable bit W = Writable bit		bit	U = Unimpler	nented bit, read	l as '0'		
u = Bit is unchanged x = Bit is unknown		nown	-n/n = Value at POR and BOR/Value at all other Resets				

REGISTER 15-3: IOCAF: INTERRUPT-ON-CHANGE PORTA FLAG REGISTER

bit 7-6	Unimplemented: Read as '0'

'1' = Bit is set

bit 5-0

IOCAF<5:0>: Interrupt-on-Change PORTA Flag bits

'0' = Bit is cleared

1 = An enabled change was detected on the associated pin Set when IOCAPx = 1 and a rising edge was detected on RAx, or when IOCANx = 1 and a falling edge was detected on RAx.

HS - Bit is set in hardware

0 = No change was detected, or the user cleared the detected change.

REGISTER 15-4: IOCBP: INTERRUPT-ON-CHANGE PORTB POSITIVE EDGE REGISTER⁽¹⁾

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	U-0	U-0	U-0	U-0
IOCBP7	IOCBP6	IOCBP5	IOCBP4	—	—	—	—
bit 7	·						bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 **IOCBP<7:4>:** Interrupt-on-Change PORTB Positive Edge Enable bits

- 1 = Interrupt-on-Change enabled on the pin for a positive going edge. IOCAFx bit and IOCIF flag will be set upon detecting an edge.
- 0 = Interrupt-on-Change disabled for the associated pin

bit 3-0 Unimplemented: Read as '0'

R/W-0/0 OCBN6	R/W-0/0	R/W-0/0	U-0	U-0	U-0	U-0	
OCDINO	IOCBN5	IOCBN4		_	_	_	
						bit 0	
	W = Writable I	bit	U = Unimplemented bit, read as '0'				
d	x = Bit is unkn	iown	-n/n = Value at POR and BOR/Value at all other Resets				
'1' = Bit is set '0' = Bit is cleared		ared					
	d	d x = Bit is unkn		d $x = Bit is unknown$ -n/n = Value a	d x = Bit is unknown -n/n = Value at POR and BOI	x = Bit is unknown -n/n = Value at POR and BOR/Value at all o	

REGISTER 15-5: IOCBN: INTERRUPT-ON-CHANGE PORTB NEGATIVE EDGE REGISTER⁽¹⁾

bit 7-4	 IOCBN<7:4>: Interrupt-on-Change PORTB Negative Edge Enable bits 1 = Interrupt-on-Change enabled on the pin for a negative going edge. IOCAFx bit and IOCIF flag will be set upon detecting an edge. 0 = Interrupt-on-Change disabled for the associated pin
bit 3-0	Unimplemented: Read as '0'
Note 1: F	PIC16(L)F18346 only.

REGISTER 15-6: IOCBF: INTERRUPT-ON-CHANGE PORTB FLAG REGISTER⁽¹⁾

R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	U-0	U-0	U-0	U-0
IOCBF7	IOCBF6	IOCBF5	IOCBF4		—	—	—
bit 7 bit							

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	HS - Bit is set in hardware

bit 7-4 IOCBF<7:4>: Interrupt-on-Change PORTB Flag bits

1 = An enabled change was detected on the associated pin

Set when IOCBPx = 1 and a rising edge was detected on RBx, or when IOCBNx = 1 and a falling edge was detected on RBx.

0 = No change was detected, or the user cleared the detected change.

bit 3-0 Unimplemented: Read as '0'

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
IOCCP7 ⁽¹⁾	IOCCP6 ⁽¹⁾	IOCCP5	IOCCP4	IOCCP3	IOCCP2	IOCCP1	IOCCP0	
bit 7	•			•		•	bit 0	
Legend:								
R = Readable	bit	W = Writable	bit	U = Unimplemented bit, read as '0'				
u = Bit is unchanged x = Bit is unkn		iown	-n/n = Value a	at POR and BO	R/Value at all c	ther Resets		
'1' = Bit is set '0' = Bit is			ared					

REGISTER 15-7: IOCCP: INTERRUPT-ON-CHANGE PORTC POSITIVE EDGE REGISTER

bit 7-6	 IOCCP<7:6>: Interrupt-on-change PORTC Positive Edge Enable bits⁽¹⁾ 1 = Interrupt-on-change enabled on the pin for a positive going edge. IOCCFx bit and IOCIF flag will be set upon detecting an edge. 0 = Interrupt-on-change disabled for the associated pin
bit 5-0	 IOCCP<5:0>: Interrupt-on-change PORTC Positive Edge Enable bits 1 = Interrupt-on-change enabled on the pin for a positive going edge. IOCCFx bit and IOCIF flag will be set upon detecting an edge. 0 = Interrupt-on-change disabled for the associated pin

Note 1: PIC16(L)F18346 only.

REGISTER 15-8: IOCCN: INTERRUPT-ON-CHANGE PORTC NEGATIVE EDGE REGISTER

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
IOCCN7 ⁽¹⁾	IOCCN6 ⁽¹⁾	IOCCN5	IOCCN4	IOCCN3	IOCCN2	IOCCN1	IOCCN0
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	 IOCCN<7:6>: Interrupt-on-change PORTC Negative Edge Enable bits⁽¹⁾ 1 = Interrupt-on-change enabled on the pin for a negative going edge. IOCCFx bit and IOCIF flag will be set upon detecting an edge. 0 = Interrupt-on-change disabled for the associated pin
bit 5-0	 IOCCN<5:0>: Interrupt-on-change PORTC Negative Edge Enable bits 1 = Interrupt-on-Change enabled on the pin for a negative going edge. IOCCFx bit and IOCIF flag will be set upon detecting an edge. 0 = Interrupt-on-Change disabled for the associated pin
Noto 1:	

R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0	R/W/HS-0/0		
IOCCF7 ⁽¹⁾	IOCCF6 ⁽¹⁾	IOCCF5	IOCCF4	IOCCF3	IOCCF2	IOCCF1	IOCCF0		
bit 7							bit 0		
Legend:									
R = Readable	bit	W = Writable	bit	U = Unimplemented bit, read as '0'					
u = Bit is uncha	anged	x = Bit is unkr	iown	-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set '0' = Bit is cleared			ared	HS - Bit is set in hardware					
bit 7-6	OCCF<7:6>:	Interrupt-on-C	hange PORT(C Flag bits					

REGISTER 15-9: IOCCF: INTERRUPT-ON-CHANGE PORTC FLAG REGISTER

bit 7-6	 IOCCF<7:6>: Interrupt-on-Change PORTC Flag bits 1 = An enabled change was detected on the associated pin. Set when IOCCPx = 1 and a rising edge was detected on RCx, or when IOCCNx = 1 and a falling edge was detected on RCx. 0 = No change was detected, or the user cleared the detected change.
bit 5-0	 IOCCF<5:0>: Interrupt-on-Change PORTC Flag bits 1 = An enabled change was detected on the associated pin. Set when IOCCPx = 1 and a rising edge was detected on RCx, or when IOCCNx = 1 and a falling edge was detected on RCx.

0 = No change was detected, or the user cleared the detected change.

Note 1: PIC16(L)F18346 only.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
ANSELA	—	_	ANSA4	ANSA4		ANSA2	ANSA1	ANSA0	144
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	—	—	—	150
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
TRISA	—	—	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	—	—	—	149
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
INTCON	GIE	PEIE		_	_	—	—	INTEDG	100
PIE0	—	—	TMR0IE	IOCIE	_	—	—	INTE	101
IOCAP	—	—	IOCAP5	IOCAP4	IOCAP3	IOCAP2	IOCAP1	IOCAP0	174
IOCAN	—	—	IOCAN5	IOCAN4	IOCAN3	IOCAN2	IOCAN1	IOCAN0	174
IOCAF	_	—	IOCAF5	IOCAF4	IOCAF3	IOCAF2	IOCAF1	IOCAF0	175
IOCBP ⁽¹⁾	IOCBP7	IOCBP6	IOCBP5	IOCBP4	_	—	—	—	175
IOCBN ⁽¹⁾	IOCBN7	IOCBN6	IOCBN5	IOCBN4	_	_	_	_	176
IOCBF ⁽¹⁾	IOCBF7	IOCBF6	IOCBF5	IIOCBF4	_	_	_	_	176
IOCCP	IOCCP7 ⁽¹⁾	IOCCP6 ⁽¹⁾	IOCCP5	IOCCP4	IOCCP3	IOCCP2	IOCCP1	IOCCP0	177
IOCCN	IOCCN7 ⁽¹⁾	IOCCN6 ⁽¹⁾	IOCCN5	IOCCN4	IOCCN3	IOCCN2	IOCCN1	IOCCN0	177
IOCCF	IOCCF7 ⁽¹⁾	IOCCF6 ⁽¹⁾	IOCCF5	IOCCF4	IOCCF3	IOCCF2	IOCCF1	IOCCF0	178

TABLE 15-1: SUMMARY OF REGISTERS ASSOCIATED WITH INTERRUPT-ON-CHANGE

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by interrupt-on-change.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

16.0 FIXED VOLTAGE REFERENCE (FVR)

The Fixed Voltage Reference, or FVR, is a stable voltage reference, independent of VDD, with 1.024V, 2.048V or 4.096V selectable output levels. The output of the FVR subsystem can be configured to supply a reference voltage to the following:

- · ADC input channel
- ADC positive reference
- Comparator positive input
- Digital-to-Analog Converter (DAC)

The FVR can be enabled by setting the FVREN bit of the FVRCON register.

Note: Fixed Voltage Reference output cannot exceed VDD.

16.1 Independent Gain Amplifiers

The output of the FVR, which is supplied to the ADC, Comparators and DAC, is routed through two independent programmable gain amplifiers. Each amplifier can be programmed for a gain of 1x, 2x or 4x, to produce the three possible voltage levels.


The ADFVR<1:0> bits of the FVRCON register are used to enable and configure the gain amplifier settings for the reference supplied to the ADC module. Reference Section 22.0 "Analog-to-Digital Converter (ADC) Module" for additional information.

The CDAFVR<1:0> bits of the FVRCON register are used to enable and configure the gain amplifier settings for the reference supplied to the DAC and comparator module. Reference Section 24.0 "5-bit Digital-to-Analog Converter (DAC1) Module" and Section 19.0 "Comparator Module" for additional information.

16.2 FVR Stabilization Period

When the Fixed Voltage Reference module is enabled, it requires time for the reference and amplifier circuits to stabilize. See Table 35-16 for FVR start-up times.

FIGURE 16-1: VOLTAGE REFERENCE BLOCK DIAGRAM



16.3 Register Definitions: FVR Control

R/W-0/0	R-q/q	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
FVREN	FVRRDY ⁽¹⁾	TSEN ⁽³⁾	TSRNG ⁽³⁾	CDAF	VR<1:0>	ADFV	R<1:0>		
bit 7							bit (
Legend:									
R = Readable bit		W = Writable bit		U = Unimpler	mented bit read	las '0'			
u = Bit is unchanged		x = Bit is unknown		U = Unimplemented bit, read as '0' -n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is cleared		q = Value depends on condition					
bit 7	1 = Fixed Vo	d Voltage Refe Itage Referenc	e is enabled	bit					
bit 6	 0 = Fixed Voltage Reference is disabled FVRRDY: Fixed Voltage Reference Ready Flag bit⁽¹⁾ 1 = Fixed Voltage Reference output is ready for use 0 = Fixed Voltage Reference output is not ready or not enabled 								
bit 5	 TSEN: Temperature Indicator Enable bit⁽³⁾ 1 = Temperature Indicator is enabled 0 = Temperature Indicator is disabled 								
bit 4	TSRNG: Temperature Indicator Range Selection bit ⁽³⁾ 1 = VOUT = VDD - 4VT (High Range) 0 = VOUT = VDD - 2VT (Low Range)								
bit 3-2	CDAFVR<1:0>: Comparator FVR Buffer Gain Selection bits 11 = Comparator FVR Buffer Gain is 4x, (4.096V) ⁽²⁾ 10 = Comparator FVR Buffer Gain is 2x, (2.048V) ⁽²⁾ 01 = Comparator FVR Buffer Gain is 1x, (1.024V) 00 = Comparator FVR Buffer is off								
bit 1-0	ADFVR<1:0>: ADC FVR Buffer Gain Selection bit 11 = ADC FVR Buffer Gain is 4x, $(4.096V)^{(2)}$ 10 = ADC FVR Buffer Gain is 2x, $(2.048V)^{(2)}$ 01 = ADC FVR Buffer Gain is 1x, $(1.024V)$ 00 = ADC FVR Buffer is off								
2: Fix	RRDY is always ked Voltage Refe	erence output o							

REGISTER 16-1: FVRCON: FIXED VOLTAGE REFERENCE CONTROL REGISTER

3: See Section 17.0 "Temperature Indicator Module" for additional information.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on page
FVRCON	FVREN	FVRRDY	TSEN	TSRNG	CDAFV	′R<1:0>	ADFVI	R<1:0>	180
ADCON0			CHS<5:0>				GO/DONE	ADON	244
ADCON1	ADFM	A	ADCS<2:0>	•		ADNREF	ADPRE	245	
CMxCON1	CxINTP	CxINTN	C	xPCH<2:0	>		CxNCH<2:0>		197
DAC1CON0	DAC1EN	—	DAC10E	—	DAC1PI	PS<1:0>	_	DAC1NSS	263

TABLE 16-1: SUMMARY OF REGISTERS ASSOCIATED WITH FIXED VOLTAGE REFERENCE

Legend: Shaded cells are not used with the Fixed Voltage Reference.

17.0 TEMPERATURE INDICATOR MODULE

This family of devices is equipped with a temperature circuit designed to measure the operating temperature of the silicon die. The circuit's range of operating temperature falls between -40°C and +85°C. The output is a voltage that is proportional to the device temperature. The output of the temperature indicator is internally connected to the device ADC.

The circuit may be used as a temperature threshold detector or a more accurate temperature indicator, depending on the level of calibration performed. A one-point calibration allows the circuit to indicate a temperature closely surrounding that point. A two-point calibration allows the circuit to sense the entire range of temperature more accurately. Reference Application Note AN2092, *"Using the Temperature Indicator Module"* (DS00002092) for more details regarding the calibration process.

17.1 Circuit Operation

Figure 17-1 shows a simplified block diagram of the temperature circuit. The proportional voltage output is achieved by measuring the forward voltage drop across multiple silicon junctions.

Equation 17-1 describes the output characteristics of the temperature indicator.

EQUATION 17-1: VOUT RANGES

High Range: VOUT = VDD - 4VT

Low Range: VOUT = VDD - 2VT


The temperature sense circuit is integrated with the Fixed Voltage Reference (FVR) module. See **Section 16.0 "Fixed Voltage Reference (FVR)**" for more information.

The circuit is enabled by setting the TSEN bit of the FVRCON register. When disabled, the circuit draws no current.

The circuit operates in either high or low range. The high range, selected by setting the TSRNG bit of the FVRCON register, provides a wider output voltage. This provides more resolution over the temperature range. This range requires a higher bias voltage to operate and thus, a higher VDD is needed.

The low range is selected by clearing the TSRNG bit of the FVRCON register. The low range generates a lower voltage drop and thus, a lower VDD voltage is needed to operate the circuit. The low range is provided for low voltage operation.

FIGURE 17-1: TEMPERATURE CIRCUIT DIAGRAM



17.2 Minimum Operating VDD

When the temperature circuit is operated in low range, the device may be operated at any operating voltage that is within specifications.

When the temperature circuit is operated in high range, the device operating voltage, VDD, must be high enough to ensure that the temperature circuit is correctly biased.

Table 17-1 shows the recommended minimum VDD vs.range setting.

TABLE 17-1: RECOMMENDED VDD VS. RANGE

Min. VDD, TSRNG = 1	Min. VDD, TSRNG = 0
3.6V	1.8V

17.3 Temperature Output

The output of the circuit is measured using the internal Analog-to-Digital Converter. A channel is provided for the temperature circuit output. Refer to Section 22.0 "Analog-to-Digital Converter (ADC) Module" for detailed information.

17.4 ADC Acquisition Time

To ensure accurate temperature measurements, the user must wait at least 200 μs after the ADC input multiplexer is connected to the temperature indicator output before the conversion is performed.

TABLE 17-2: SUMMARY OF REGISTERS ASSOCIATED WITH THE TEMPERATURE INDICATOR

	Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on page
F	VRCON	FVREN	FVRRDY	TSEN	TSRNG	CDAFV	′R<1:0>	ADFV	R<1:0>	180

Legend: Shaded cells are unused by the temperature indicator module.

18.0 PULSE-WIDTH MODULATION (PWM)

The PWMx modules generate Pulse-Width Modulated (PWM) signals of varying frequency and duty cycle.


In addition to the CCP modules, the PIC16(L)F18326/18346 devices contain two PWM modules.

Pulse-Width Modulation (PWM) is a scheme that provides power to a load by switching quickly between fully on and fully off states. The PWM signal resembles a square wave where the high portion of the signal is considered the ON state (pulse width), and the low portion of the signal is considered the OFF state. The term duty cycle describes the proportion of the ON time to the OFF time and is expressed in percentages, where 0% is fully OFF and 100% is fully ON. A lower duty cycle corresponds to less power applied and a higher duty cycle corresponds to more power applied. The PWM period is defined as the duration of one complete cycle or the total amount of on and off time combined.

PWM resolution defines the maximum number of steps that can be present in a single PWM period. A higher resolution allows for more precise control of the pulse-width time and in turn the power that is applied to the load.

Figure 18-1 shows a typical waveform of the PWM signal.





18.1 Standard PWM Mode

The standard PWM mode generates a Pulse-Width Modulation (PWM) signal on the PWMx pin with up to ten bits of resolution. The period, duty cycle, and resolution are controlled by the following registers:

- TMR2, TMR4 or TMR6 registers
- PR2, PR4 or PR6 registers
- PWMxCON registers
- PWMxDCH registers
- PWMxDCL registers


Figure 29-2 shows a simplified block diagram of the PWM operation.

If PWMPOL = 0, the default state of the output is '0'. If PWMPOL = 1, the default state is '1'. If PWMEN = 0, the output will be the default state.

Note: The corresponding TRIS bit must be cleared to enable the PWM output on the PWMx pin

Note: The formulas and text refer to TMR2 and PR2, for simplicity. The same formulas and text apply to TMR4/6 and PR4/6. The timer sources can be selected in Register 18-4. For additional information on TMR2/4/6, refer to Section 28.0 "Timer2/4/6 Module"

FIGURE 18-2: SIMPLIFIED PWM BLOCK DIAGRAM



18.1.1 PWM PERIOD

Referring to Figure 18-1, the PWM output has a period and a pulse width. The frequency of the PWM is the inverse of the period (1/period).

The PWM period is specified by writing to the PR2 register. The PWM period can be calculated using the following formula:

EQUATION 18-1: PWM PERIOD

 $PWM Period = [(PR2) + 1] \bullet 4 \bullet TOSC \bullet$ (TMR2 Prescale Value) **Note:** TOSC = 1/FOSC

When TMR2 is equal to PR2, the following three events occur on the next increment cycle:

- TMR2 is cleared
- The PWMx pin is set (Exception: If the PWM duty cycle = 0%, the pin will not be set.)
- The PWM pulse width is latched from PWMxDC.

Note: If the pulse-width value is greater than the period, the assigned PWM pin(s) will remain unchanged.

18.1.2 PWM DUTY CYCLE

The PWM duty cycle is specified by writing a 10-bit value to the PWMxDC register. The PWMxDCH contains the eight MSbs and bits <7:6> of the PWMxDCL register contain the two LSbs.

The PWMDC register is double-buffered and can be updated at any time. This double buffering is essential for glitch-free PWM operation. New values take effect when TMR2 = PR2. Note that PWMDC is left-justified.

The 8-bit timer TMR2 register is concatenated with either the 2-bit internal system clock (FOSC), or two bits of the prescaler, to create the 10-bit time base. The system clock is used if the Timer2 prescaler is set to 1:1.

Equation 18-2 is used to calculate the PWM pulse width.

Equation 18-3 is used to calculate the PWM duty cycle ratio.

EQUATION 18-2: PULSE WIDTH

Pulse Width = (PWMxDC) • T_{OSC} •

• (TMR2 Prescale Value)

EQUATION 18-3: DUTY CYCLE RATIO

Duty Cycle Ratio = $\frac{(PWMxDC)}{4(PR2+1)}$

18.1.3 PWM RESOLUTION

PWM resolution, expressed in number of bits, defines the maximum number of discrete steps that can be present in a single PWM period. For example, a 10-bit resolution will result in 1024 discrete steps, whereas an 8-bit resolution will result in 256 discrete steps.

The maximum PWM resolution is ten bits when PR2 is 255. The resolution is a function of the PR2 register value as shown by Equation 18-4.

EQUATION 18-4: PWM RESOLUTION

 $Resolution = \frac{\log[4(PR2 + 1)]}{\log(2)} bits$

Note: If the pulse-width value is greater than the period, the assigned PWM pin(s) will remain unchanged.

18.1.4 OPERATION IN SLEEP MODE

In Sleep mode, the TMR2 register will not increment and the state of the module will not change. If the PWMx pin is driving a value, it will continue to drive that value. When the device wakes up, TMR2 will continue from its previous state.

18.1.5 CHANGES IN SYSTEM CLOCK FREQUENCY

The PWM frequency is derived from the system clock frequency. Any changes in the system clock frequency will result in changes to the PWM frequency. See **Section 7.0, Oscillator Module** for additional details.

18.1.6 EFFECTS OF RESET

Any Reset will force all ports to Input mode and the PWMx registers to their Reset states.

18.1.7 SETUP FOR PWM OPERATION

The following steps will be taken when configuring the module for using the PWMx outputs:

- 1. Disable the PWMx pin output driver(s) by setting the associated TRIS bit(s).
- 2. Configure the PWM output polarity by configuring the PWMxPOL bit of the PWMxCON register.
- 3. Load the PR2 register with the PWM period value, as determined by Equation 18-1.
- 4. Load the PWMxDCH register and bits <7:6> of the PWMxDCL register with the PWM duty cycle value, as determined by Equation 18-2.
- 5. Configure and start Timer2:
 - Clear the TMR2IF interrupt flag bit of the PIR1 register.
 - Select the Timer2 prescale value by configuring the T2CKPS bit of the T2CON register.
 - Enable Timer2 by setting the TMR2ON bit of the T2CON register.
- 6. Wait until the TMR2IF is set.
- 7. When the TMR2IF flag bit is set:
 - Clear the associated TRIS bit(s) to enable the output driver.
 - Route the signal to the desired pin by configuring the RxyPPS register.
 - Enable the PWMx module by setting the PWMxEN bit of the PWMxCON register.

In order to send a complete duty cycle and period on the first PWM output, the above steps must be followed in the order given. If it is not critical to start with a complete PWM signal, then the PWM module can be enabled during Step 2 by setting the PWMxEN bit of the PWMxCON register.

18.2 Register Definitions: PWM Control

R/W-0/0	U-0	R-0	R/W-0/0	U-0	U-0	U-0	U-0
PWMxEN	_	PWMxOUT	PWMxPOL		—	—	
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
u = Bit is unchanged x = Bit is unknown		nown	-n/n = Value	at POR and BO	R/Value at all c	other Resets	
'1' = Bit is set		'0' = Bit is clea	ared				
bit 7	PWMxEN: P	WM Module En	able bit				
	1 = PWM m	odule is enable	b				
	0 = PWM m	odule is disable	d				
bit 6	Unimplemer	nted: Read as '	0'				
bit 5	PWMxOUT:	PWM Module C	output Level w	hen bit is read.			
bit 4 PWMxPOL: PWMx Output Polarity Select bit							
	1 = PWM ou	itput is active-lo	W.				
	0 = PWM ou	itput is active-hi	gh.				
bit 3-0	Unimplemer	nted: Read as '	0'				

REGISTER 18-1: PWMxCON: PWM CONTROL REGISTER

REGISTER 18-2: PWMxDCH: PWM DUTY CYCLE HIGH BITS

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
			PWMxE)C<9:2>			
bit 7 bit 0							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0

PWMxDC<9:2>: PWM Duty Cycle Most Significant bits

These bits are the MSbs of the PWM duty cycle. The two LSbs are found in PWMxDCL Register.

REGISTER 18-3: PWMxDCL: PWM DUTY CYCLE LOW BITS

R/W-x/u	R/W-x/u	U-0	U-0	U-0	U-0	U-0	U-0
PWMxD0	C<1:0>	—	—	—	—	—	—
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 **PWMxDC<1:0>:** PWM Duty Cycle Least Significant bits

These bits are the LSbs of the PWM duty cycle. The MSbs are found in PWMxDCH Register.

bit 5-0 Unimplemented: Read as '0'

				<u> </u>	,	
PWM Frequency	1.22 kHz	4.88 kHz	19.53 kHz	78.12 kHz	156.3 kHz	208.3 kHz
Timer Prescale	16	4	1	1	1	1
PR2 Value	0xFF	0xFF	0xFF	0x3F	0x1F	0x17
Maximum Resolution (bits)	10	10	10	8	7	6.6

TABLE 18-1: EXAMPLE PWM FREQUENCIES AND RESOLUTIONS (Fosc = 20 MHz)

TABLE 18-2:EXAMPLE PWM FREQUENCIES AND RESOLUTIONS (Fosc = 8 MHz)

PWM Frequency	1.22 kHz	4.90 kHz	19.61 kHz	76.92 kHz	153.85 kHz	200.0 kHz
Timer Prescale	16	4	1	1	1	1
PR2 Value	0xFF	0xFF	0xFF	0x3F	0x1F	0x17
Maximum Resolution (bits)	10	10	10	8	7	6.6

REGISTER 18-4: PWMTMRS: PWM TIMERS CONTROL REGISTER

U-0	U-0	U-0	U-0	R/W-0/0	R/W-1/1	R/W-0/0	R/W-1/1
—	_	—	—	P6TSE	EL<1:0>	P5TSE	L<1:0>
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4	Unimplemented: Read as '0'
bit 3-2	P6TSEL<1:0>: PWM6 Mode Timer Selection bits
	00 = Reserved
	01 = PWM6 is based on TMR2
	10 = PWM6 is based on TMR4
	11 = PWM6 is based on TMR6
bit 1-0	P5TSEL<1:0>: PWM5 Mode Timer Selection bits
	00 = Reserved
	01 = PWM5 is based on TMR2
	10 = PWM5 is based on TMR4
	11 = PWM5 is based on TMR6

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA			TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	_		ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_	_		149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_			150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
PWM5CON	PWM5EN		PWM5OUT	PWM5POL	—	_	_	_	187
PWM5DCH				PWM5DC<	9:2>				187
PWM5DCL	PWM5	DC<1:0>	—	_	_	_	_		187
PWM6CON	PWM6EN	_	PWM6OUT	PWM6POL	_	_	_	_	187
PWM6DCH				PWM6DC<	9:2>				187
PWM6DCL	PWM6	DC<1:0>	—	_	_	_	_		187
PWMTMRS	_	_	_	_	P6TSE	L<1:0>	P5TSE	L<1:0>	188
INTCON	GIE	PEIE	_	_	_	_	_	INTEDG	100
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103
T2CON	_		T2OUTPS	S<3:0>		TMR2ON	T2CKP	'S<1:0>	299
T4CON	_		T4OUTPS	S<3:0>		TMR4ON	T4CKP	'S<1:0>	293
T6CON	_		T6OUTPS	S<3:0>		TMR6ON	T6CKP	'S<1:0>	293
TMR2				TMR2<7:0)>				300
TMR4				TMR4<7:0)>				300
TMR6				TMR6<7:0)>				300
PR2				PR2<7:0	>				300
PR4				PR4<7:0	>				300
PR6				PR6<7:0	>				300
CWGxDAT						DAT<	<3:0>		215
CLCxSELy				· · · · · · · · · · · · · · · · · · ·	LCxDyS<	5:0>			229
MDSRC		_	_	_		MDMS	3:0>		272
MDCARH		MDCHPOL	MDCHSYNC	_		MDCH	<3:0>		273
MDCARL	—	MDCLPOL	MDCLSYNC	—		MDCL	<3:0>		274

TABLE 18-3: SUMMARY OF REGISTERS ASSOCIATED WITH PWMx

Legend: - = Unimplemented locations, read as '0'. Shaded cells are not used by the PWM module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

19.0 COMPARATOR MODULE

Comparators are used to interface analog circuits to a digital circuit by comparing two analog voltages and providing a digital indication of their relative magnitudes. Comparators are very useful mixed signal building blocks because they provide analog functionality independent of program execution. The analog comparator module includes the following features:

- Programmable input selection
- Selectable voltage reference
- Programmable output polarity
- · Rising/falling output edge interrupts
- Wake-up from Sleep
- CWG Auto-shutdown source

19.1 Comparator Overview


A single comparator is shown in Figure 19-1 along with the relationship between the analog input levels and the digital output. When the analog voltage at VIN+ is less than the analog voltage at VIN-, the output of the comparator is a digital low level. When the analog voltage at VIN+ is greater than the analog voltage at VIN-, the output of the comparator is a digital high level.


The comparators available for this device are located in Table 19-1.

TABLE 19-1: AVAILABLE COMPARATORS

Device	C1	C2
PIC16(L)F18326	•	•
PIC16(L)F18346	•	•

FIGURE 19-1: SINGLE COMPARATOR





COMPARATOR MODULE SIMPLIFIED BLOCK DIAGRAM

19.2 Comparator Control

Each comparator has two control registers: CMxCON0 and CMxCON1.

The CMxCON0 register (see Register 19-1) contains Control and Status bits for the following:

- Enable
- Output
- Output polarity
- Hysteresis enable
- Timer1 output synchronization

The CMxCON1 register (see Register 19-2) contains Control bits for the following:

- Interrupt on positive/negative edge enables
- Positive input channel selection
- Negative input channel selection

19.2.1 COMPARATOR ENABLE

Setting the CxON bit of the CMxCON0 register enables the comparator for operation. Clearing the CxON bit disables the comparator resulting in minimum current consumption.

19.2.2 COMPARATOR OUTPUT

The output of the comparator can be monitored by reading either the CxOUT bit of the CMxCON0 register or the MCxOUT bit of the CMOUT register.

The comparator output can also be routed to an external pin through the RxyPPS register (Register 13-2). The corresponding TRIS bit must be clear to enable the pin as an output.

Note 1: The internal output of the comparator is latched with each instruction cycle. Unless otherwise specified, external outputs are not latched.

19.2.3 COMPARATOR OUTPUT POLARITY

Inverting the output of the comparator is functionally equivalent to swapping the comparator inputs. The polarity of the comparator output can be inverted by setting the CxPOL bit of the CMxCON0 register. Clearing the CxPOL bit results in a noninverted output.

Table 19-2showsthe outputstateversusinputconditions, including polarity control.

TABLE 19-2: COMPARATOR OUTPUT STATE VS. INPUT CONDITIONS

Input Condition	CxPOL	CxOUT
CxVN > CxVP	0	0
CxVN < CxVP	0	1
CxVN > CxVP	1	1
CxVN < CxVP	1	0

19.3 Comparator Hysteresis

A selectable amount of separation voltage can be added to the input pins of each comparator to provide a hysteresis function to the overall operation. Hysteresis is enabled by setting the CxHYS bit of the CMxCON0 register.

See Comparator Specifications in Table 35-14 for more information.

19.4 Timer1 Gate Operation

The output resulting from a comparator operation can be used as a source for gate control of Timer1. See **Section 27.6 "Timer1 Gate"** for more information. This feature is useful for timing the duration or interval of an analog event.

It is recommended that the comparator output be synchronized to Timer1. This ensures that Timer1 does not increment while a change in the comparator is occurring.

19.4.1 COMPARATOR OUTPUT SYNCHRONIZATION

The output from a comparator can be synchronized with Timer1 by setting the CxSYNC bit of the CMxCON0 register.

Once enabled, the comparator output is latched on the falling edge of the Timer1 source clock. This allows the timer/counter to synchronize with the CxOUT bit so that the software sees no ambiguity due to timing. See the Comparator Block Diagram (Figure 19-2) and the Timer1 Block Diagram (Figure 27-1) for more information.

19.5 Comparator Interrupt

An interrupt can be generated when either the rising edge or falling edge detector detects a change in the output value of each comparator.

When either edge detector is triggered and its associated enable bit is set (CxINTP and/or CxINTN bits of the CMxCON1 register), the Corresponding Interrupt Flag bit (CxIF bit of the PIR2 register) will be set.

To enable the interrupt, set the following bits:

- The CxON bit of the CMxCON0 register
- · The CxIE bit of the PIE2 register
- The CxINTP bit of the CMxCON1 register (for a rising edge detection)
- The CxINTN bit of the CMxCON1 register (for a falling edge detection)
- The PEIE and GIE bits of the INTCON register

The associated interrupt flag bit, CxIF bit of the PIR2 register, must be cleared in software. If another edge is detected while this flag is being cleared, the flag will still be set at the end of the sequence.

Note: Although a comparator is disabled, an interrupt can be generated by changing the output polarity with the CxPOL bit of the CMxCON0 register, or by switching the comparator on or off with the CxON bit of the CMxCON0 register.

19.6 Comparator Positive Input Selection

Configuring the CxPCH<2:0> bits of the CMxCON1 register directs an internal voltage reference or an analog pin to the noninverting input of the comparator:

- · CxIN0+ analog pin
- DAC output
- FVR (Fixed Voltage Reference)
- Vss (Ground)

See **Section 16.0 "Fixed Voltage Reference (FVR)"** for more information on the Fixed Voltage Reference module.

See Section 24.0 "5-bit Digital-to-Analog Converter (DAC1) Module" for more information on the DAC input signal.

Any time the comparator is disabled (CxON = 0), all comparator inputs are disabled.

19.7 Comparator Negative Input Selection

The CxNCH<2:0> bits of the CMxCON1 register direct an analog input pin and internal reference voltage or analog ground to the inverting input of the comparator:

- CxIN- pin
- FVR (Fixed Voltage Reference)
- Analog Ground

Note: To use CxINy+ and CxINy- pins as analog input, the appropriate bits must be set in the ANSEL register and the corresponding TRIS bits must also be set to disable the output drivers.

19.8 Comparator Response Time


The comparator output is indeterminate for a period of time after the change of an input source or the selection of a new reference voltage. This period is referred to as the response time. The response time of the comparator differs from the settling time of the voltage reference. Therefore, both of these times must be considered when determining the total response time to a comparator input change. See the Comparator and Voltage Reference Specifications in Table 35-14 for more details.

19.9 Analog Input Connection Considerations

A simplified circuit for an analog input is shown in Figure 19-3. Since the analog input pins share their connection with a digital input, they have reverse biased ESD protection diodes to VDD and Vss. The analog input, therefore, must be between Vss and VDD. If the input voltage deviates from this range by more than 0.6V in either direction, one of the diodes is forward biased and a latch-up may occur.

A maximum source impedance of $10 \text{ k}\Omega$ is recommended for the analog sources. Also, any external component connected to an analog input pin, such as a capacitor or a Zener diode, must have very little leakage current to minimize inaccuracies introduced.

- Note 1: When reading a PORT register, all pins configured as analog inputs will read as a '0'. Pins configured as digital inputs will provide an input based on their level as either a TTL or ST input buffer.
 - 2: Analog levels on any pin defined as a digital input, may cause the input buffer to consume more current than is specified.





19.10 CWG Auto-shutdown Source

The output of the comparator module can be used as an auto-shutdown source for the CWG module. When the output of the comparator is active and the corresponding ASxE is enabled, the CWG operation will be suspended immediately (Section 20.7.1.2 "External Input Source Shutdown").

19.11 Operation in Sleep Mode

The comparator module can operate during Sleep. The comparator clock source is based on the Timer1 clock source. If the Timer1 clock source is either the system clock (FOSC) or the instruction clock (FOSC/4), Timer1 will not operate during Sleep, and synchronized comparator outputs will not operate.

A comparator interrupt will wake the device from Sleep. The CxIE bits of the PIE2 register must be set to enable comparator interrupts.

19.12 Register Definitions: Comparator Control

R/W-0/0	R-0/0	U-0	R/W-0/0	U-0	R/W-1/1	R/W-0/0	R/W-0/0			
CxON	CxOUT		CxPOL	—	CxSP	CxHYS	CxSYNC			
bit 7							bit C			
Legend:										
R = Readable		W = Writable		•	mented bit, read					
u = Bit is unch	anged	x = Bit is unk		-n/n = Value	at POR and BC	R/Value at all	other Resets			
'1' = Bit is set		'0' = Bit is cle	eared							
bit 7	CxON: Com	parator Enable	bit							
		ator is enabled								
	0 = Compar	ator is disabled	and consumes	no active pov	ver					
bit 6	CxOUT: Co	mparator Outpu	t bit							
		1 (inverted pola	rity):							
	1 = CxVP <									
	0 = CxVP >	0 (noninverted)	oolarity):							
	1 = CxVP >		<u>Jolanty).</u>							
	0 = CxVP <									
bit 5	Unimpleme	nted: Read as	' O '							
bit 4	CxPOL: Co	mparator Outpu	it Polarity Selec	t bit						
	1 = Compar	ator output is in	verted							
	0 = Compar	ator output is n	ot inverted							
bit 3	Unimpleme	nted: Read as	'O'							
bit 2	CxSP: Com	parator Speed/	Power Select b	it						
		ator operates ir d. (do not use)	Normal-Power	r, High-Speed	mode					
bit 1	CxHYS: Comparator Hysteresis Enable bit									
		rator hysteresis								
		rator hysteresis								
bit 0	CxSYNC: C	omparator Out	out Synchronou	is Mode bit						
	1 = Compa	rator output to	Timer1 and I/C	pin is synchr	ronous to chang	ges on Timer1	clock source			
		updated on the								
	0 - Compa	rator output to 7	imor1 and I/O	nin ia aavnahr	onoulo					

REGISTER 19-1: CMxCON0: COMPARATOR Cx CONTROL REGISTER 0

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
CxINTP	CxINTN	CxINTN CxPCH<2:0>				CxNCH<2:0>	
bit 7							bit (
Lonordi							
Legend:	L		1. 14				
R = Readable		W = Writable		•	mented bit, rea		
u = Bit is uncl	•	x = Bit is unki		-n/n = value	at POR and BC	R/value at all	other Resets
'1' = Bit is set		'0' = Bit is cle	ared				
bit 7	CxINTP: Cor	mparator Interru	ıpt on Positive	Going Edge E	nable bits		
		F interrupt flag rupt flag will be					
bit 6	CxINTN: Cor	mparator Interru	upt on Negative	e Going Edge	Enable bits		
		F interrupt flag rupt flag will be					
bit 5-3	CxPCH<2:0>	-: Comparator	Positive Input (Channel Select	t bits		
		connects to Vs	-				
		connects to FV					
		connects to DA unconnected					
		unconnected					
		unconnected					
		unconnected connects to Cx	INO+ nin				
bit 2-0		 Comparator 	•	Channel Sele	ct bits		
5112 0		connects to Vs	•				
	110 = CxVN	connects to FV	/R Buffer 2				
		unconnected					
		unconnected connects to Cx	dN2 nin				
		connects to CX					
		connects to Cx					

REGISTER 19-2: CMxCON1: COMPARATOR Cx CONTROL REGISTER 1

REGISTER IS	9-3. CIVICO		AION OUTF		. N		
U-0	U-0	U-0	U-0	U-0	U-0	R-0/0	R-0/0
_	—	—	_	_	—	MC2OUT	MC10UT
bit 7					•	-	bit 0

REGISTER 19-3: CMOUT: COMPARATOR OUTPUT REGISTER

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-2 Unimplemented: Read as '0'

```
bit 1 MC2OUT: Mirror Copy of C2OUT bit
```

bit 0 MC10UT: Mirror Copy of C10UT bit

TABLE 19-3: SUMMARY OF REGISTERS ASSOCIATED WITH COMPARATOR MODULE

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
ANSELA	—	—	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_	—		150
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
TRISA		_	TRISA5	TRISA4	_	TRISA2	TRISA1	TRISA0	143
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	—	—	—	149
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
CMxCON0	CxON	CxOUT	_	CxPOL	_	CxSP	CxHYS	CxSYNC	196
CMxCON1	CxINTP	CxINTN		CxPCH<2:0	>		CxNCH<2:0	>	197
CMOUT	—	—	_	—	—	—	MC2OUT	MC1OUT	198
FVRCON	FVREN	FVRRDY	TSEN	TSRNG	CDAFV	′R<1:0>	ADF\	/R<1:0>	180
DACCON0	DAC1EN	—	DAC10E	_	DAC1PS	SS<1:0>	—	DAC1NSS	263
DACCON1	—	—	_			DAC1R<4:0	>		264
INTCON	GIE	PEIE	_	_	—	—	—	INTEDG	100
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BLC2IE	TMR4IE	NCO1IE	103
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BLC2IF	TMR4IF	NCO1IF	108
CLCINxPPS	—	—	_		С	LCINxPPS<4	:0>		162
MDMINPPS	—	—	_		N	1DMINPPS<4	:0>		162
T1GPPS		—	_			T1GPPS<4:0	>		162
CWGxAS1	—	_	-	AS4E	AS3E	AS2E	AS1E	AS0E	218

Legend: — = unimplemented location, read as '0'. Shaded cells are unused by the comparator module.

Note 1: PIC16(L)F18346 only.

20.0 COMPLEMENTARY WAVEFORM GENERATOR (CWG) MODULE

The Complementary Waveform Generator (CWGx) produces complementary waveforms with dead-band delay from a selection of input sources.

The CWGx module has the following features:

- · Selectable dead-band clock source control
- · Selectable input sources
- · Output enable control
- · Output polarity control
- Dead-band control with independent 6-bit rising and falling edge dead-band counters
- Auto-shutdown control with:
 - Selectable shutdown sources
 - Auto-restart enable
 - Auto-shutdown pin override control

20.1 Fundamental Operation

The CWG generates two output waveforms from the selected input source.

The off-to-on transition of each output can be delayed from the on-to-off transition of the other output, thereby, creating a time delay immediately where neither output is driven. This is referred to as dead time and is covered in **Section 20.6 "Dead-Band Control"**.

It may be necessary to guard against the possibility of circuit faults or a feedback event arriving too late or not at all. In this case, the active drive must be terminated before the Fault condition causes damage. This is referred to as auto-shutdown and is covered in **Section 20.7 "Auto-Shutdown Control"**.

20.2 Operating Modes

The CWGx module can operate in six different modes, as specified by the MODE<2:0> bits of the CWGxCON0 register:

- · Half-Bridge mode
- Push-Pull mode
- Asynchronous Steering mode
- Synchronous Steering mode
- Full-Bridge mode, Forward
- Full-Bridge mode, Reverse

All modes accept a single pulse data input, and provide up to four outputs as described in the following sections.

All modes include auto-shutdown control as described in Section 20.11 "Register Definitions: CWG Control"


Note: Except as noted for Full-bridge mode (Section 20.2.4 "Full-Bridge Modes") mode changes may only be performed while EN = 0 (Register 20-1).

20.2.1 HALF-BRIDGE MODE

In Half-Bridge mode, two output signals are generated as true and inverted versions of the input as illustrated in Figure 20-1. A nonoverlap (dead-band) time is inserted between the two outputs as described in **Section 20.6 "Dead-Band Control**". Steering modes are not used in Half-Bridge mode.

The unused outputs, CWGxC and CWGxD, drive similar signals with polarity independently controlled by POLC and POLD, respectively.

FIGURE 20-1: CWGx HALF-BRIDGE MODE OPERATION




20.2.2 PUSH-PULL MODE

In Push-Pull mode, two output signals are generated, alternating copies of the input as illustrated in Figure 20-2. This alternation creates the push-pull effect required for driving some transformer based power supply designs. Dead-band control is not used in Push-Pull mode. Steering modes are not used in Push-Pull mode.

The push-pull sequencer is reset whenever EN = 0 or if an auto-shutdown event occurs. The sequencer is clocked by the first input pulse, and the first output appears on CWGxA.

The unused outputs CWGxC and CWGxD drive copies of CWGxA and CWGxB, respectively, but with polarity controlled by POLC and POLD.





20.2.3 STEERING MODES

In both Synchronous and Asynchronous Steering modes, the modulated input signal can be steered to any combination of four CWG outputs and a fixed-value will be presented on all the outputs not used for the PWM output. Each output has independent polarity, steering, and shutdown options. Dead-band control is not used in either Steering mode.

When STRy = 0 (Register 20-5), the corresponding pin is held at the level defined by SDATy (Register 20-5). When STRy = 1, the pin is driven by the modulated input signal.

The POLy bits (Register 20-2) control the signal polarity only when STRy = 1.


The CWG auto-shutdown operation also applies to Steering modes as described in Section 20.11 "Register Definitions: CWG Control".

Note: Only the WGSTRy bits are synchronized; the WGSDATy (data) bits are not synchronized.

20.2.3.1 Synchronous Steering Mode

In Synchronous Steering mode (MODE<2:0> bits = 001, Register 20-1), changes to steering selection registers take effect on the next rising edge of the modulated data input (Figure 20-3). In Synchronous Steering mode, the output will always produce a complete waveform.






20.2.3.2 Asynchronous Steering Mode

In Asynchronous mode (MODE<2:0> bits = 000, Register 20-1), steering takes effect at the end of the instruction cycle that writes to WGxSTR. In Asynchronous Steering mode, the output signal may be an incomplete waveform (Register 20-4). This operation may be useful when the user firmware needs to immediately remove a signal from the output pin.

FIGURE 20-4: EXAMPLE OF ASYNCHRONOUS STEERING (MODE<2:0> = 000)



20.2.3.3 Start-up Considerations

The application hardware must use the proper external pull-up and/or pull-down resistors on the CWG output pins. This is required because all I/O pins are forced to high-impedance at Reset.

The POLy bits (Register 20-2) allow the user to choose whether the output signals are active-high or active-low.


20.2.4 FULL-BRIDGE MODES

In Forward and Reverse Full-Bridge modes, three outputs drive static values while the fourth is modulated by the data input. Dead-band control is described in Section 20.2.3 "Steering Modes" and Section 20.6 "Dead-Band Control". Steering modes are not used with either of the Full-Bridge modes.

The mode selection may be toggled between forward and reverse (changing MODE<2:0>) without clearing EN.

When connected as shown in Figure 20-5, the outputs are appropriate for a full-bridge motor driver. Each CWG output signal has independent polarity control, so the circuit can be adapted to high-active and low-active drivers.





Full-Bridge Reverse Mode

In Full-Bridge Reverse mode (MODE<2:0> = 011),

CWGxC is driven to its Active state and CWGxB is

modulated while CWGxA and CWGxD are driven to

their Inactive state, as illustrated at the bottom of


20.2.4.2

Figure 20-6.

20.2.4.1 Full-Bridge Forward Mode

In Full-Bridge Forward mode (MODE<2:0> = 010), CWGxA is driven to its Active state and CWGxD is modulated while CWGxB and CWGxC are driven to their Inactive state, as illustrated at the top of Figure 20-6.

FIGURE 20-6: EXAMPLE OF FULL-BRIDGE OUTPUT



20.2.4.3 Direction Change in Full-Bridge Mode

In Full-Bridge mode, changing MODE<2:0> controls the forward/reverse direction. Changes to MODE<2:0> change to the new direction on the next rising edge of the modulated input.

A direction change is initiated in software by changing the MODE<2:0> bits of the WGxCON0 register. The sequence is illustrated in Figure 20-7.

- The associated active output CWGxA and the inactive output CWGxC are switched to drive in the opposite direction.
- The previously modulated output CWGxD is switched to the inactive state, and the previously inactive output CWGxB begins to modulate.
- CWG modulation resumes after the direction-switch dead band has elapsed.

20.2.4.4 Dead-Band Delay in Full-Bridge Mode

Dead-band delay is important when either of the following conditions is true:

- 1. The direction of the CWG output changes when the duty cycle of the data input is at or near 100%, or
- 2. The turn-off time of the power switch, including the power device and driver circuit, is greater than the turn-on time.

The dead-band delay is inserted only when changing directions, and only the modulated output is affected. The statically-configured outputs (CWGxA and CWGxC) are not afforded dead band, and switch essentially simultaneously.

Figure 20-7 shows an example of the CWG outputs changing directions from forward to reverse, at near 100% duty cycle. In this example, at time t1, the output of CWGxA and CWGxD become inactive, while output CWGxC becomes active. Since the turn-off time of the power devices is longer than the turn-on time, a shootthrough current will flow through power devices QC and QD for the duration of 't'. The same phenomenon will occur to power devices QA and QB for the CWG direction change from reverse to forward.

If changing the CWG direction at high duty cycle is required for an application, two possible solutions for eliminating the shoot-through current are:

- 1. Reduce the CWG duty cycle for one period before changing directions.
- 2. Use switch drivers that can drive the switches off faster than they can drive them on.





FIGURE 20-7: EXAMPLE OF PWM DIRECTION CHANGE AT NEAR 100% DUTY CYCLE

PIC16(L)F18326/18346






FIGURE 20-10: SIMPLIFIED CWG BLOCK DIAGRAM (OUTPUT STEERING MODES)





FIGURE 20-11: SIMPLIFIED CWG BLOCK DIAGRAM (FORWARD AND REVERSE FULL-BRIDGE MODES)



20.3 Clock Source

The clock source is used to drive the dead-band timing circuits. The CWGx module allows the following clock sources to be selected:

- Fosc (system clock)
- HFINTOSC (16 MHz only)

When the HFINTOSC is selected the HFINTOSC will be kept running during Sleep. Therefore, CWG modes requiring dead band can operate in Sleep provided that the CWG data input is also active during Sleep. The clock sources are selected using the CS bit of the CWGxCLKCON register (Register 20-3).

20.4 Selectable Input Sources

The CWG generates the output waveforms from the input sources in Table 20-1.

Source Peripheral	Signal Name
CWGxPPS	CWG PPS input connection
C1OUT	Comparator 1 output
C2OUT	Comparator 2 output
CCP1	Capture/Compare/PWM output
CCP2	Capture/Compare/PWM output
CCP3	Capture/Compare/PWM output
CCP4	Capture/Compare/PWM output
PWM5	PWM5 output
PWM6	PWM6 output
NCO1	Numerically Controlled Oscillator (NCO) output
CLC1	Configurable Logic Cell 1 output
CLC2	Configurable Logic Cell 2 output
CLC3	Configurable Logic Cell 3 output
CLC4	Configurable Logic Cell 4 output

TABLE 20-1: SELECTABLE INPUT SOURCES

The input sources are selected using the DAT<3:0> bits in the CWGxDAT register (Register 20-4).

20.5 Output Control

Immediately after the CWG module is enabled, the complementary drive is configured with all output drives cleared.

20.5.1 CWGx OUTPUTS

Each CWG output can be routed to a Peripheral Pin Select (PPS) output via the RxyPPS register (see Section 13.0 "Peripheral Pin Select (PPS) Module").

20.5.2 POLARITY CONTROL

The polarity of each CWG output can be selected independently. When the output polarity bit is set, the corresponding output is active-low. Clearing the output polarity bit configures the corresponding output as active-high. However, polarity does not affect the override levels. Output polarity is selected with the POLy bits of the CWGxCON1 register.

20.6 Dead-Band Control

Dead-band control provides for nonoverlapping output signals to prevent current shoot-through in power switches. The CWGx modules contain two 6-bit dead-band counters. These counters can be loaded with values that will determine the length of the dead band initiated on either the rising or falling edges of the input source. Dead-band control is used in either Half-Bridge or Full-Bridge modes.

The rising-edge dead-band delay is determined by the rising dead-band count register (Register 20-8, CWGxDBR) and the falling-edge dead-band delay is determined by the falling dead-band count register (Register 20-9, CWGxDBF). Dead-band duration is established by counting the CWG clock periods from zero up to the value loaded into either the rising or falling dead-band counter registers. The dead-band counters are incremented on every rising edge of the CWG clock source.

20.6.1 RISING EDGE AND REVERSE DEAD BAND

In Half-Bridge mode, the rising edge dead band delays the turn-on of the CWGxA output after the rising edge of the CWG data input. In Full-Bridge mode, the reverse dead-band delay is only inserted when changing directions from Forward mode to Reverse mode, and only the modulated output CWGxB is affected.

The CWGxDBR register determines the duration of the dead-band interval on the rising edge of the input source signal. This duration is from 0 to 64 periods of the CWG clock.

Dead band is always initiated on the edge of the input source signal. A count of zero indicates that no dead band is present.

If the input source signal reverses polarity before the dead-band count is completed then no output will be seen on the respective output.

The CWGxDBR register value is double-buffered. If EN = 0 (Register 20-1), the buffer is loaded when CWGxDBR is written. If EN = 1, then the buffer will be loaded at the rising edge, following the first falling edge of the data input after the LD bit (Register 20-1) is set.

20.6.2 FALLING EDGE AND FORWARD DEAD BAND

In Half-Bridge mode, the falling edge dead band delays the turn-on of the CWGxB output at the falling edge of the CWGx data input. In Full-Bridge mode, the forward dead-band delay is only inserted when changing directions from Reverse mode to Forward mode, and only the modulated output CWGxD is affected.

The CWGxDBF register determines the duration of the dead-band interval on the falling edge of the input source signal. This duration is from zero to 64 periods of the CWG clock.

Dead band is always initiated on the edge of the input source signal. A count of zero indicates that no dead band is present.

If the input source signal reverses polarity before the dead-band count is completed, then no output will be seen on the respective output.

The CWGxDBF register value is double-buffered. When EN = 0 (Register 20-1), the buffer is loaded when CWGxDBF is written. If EN = 1, then the buffer will be loaded at the rising edge following the first falling edge of the data input after the LD (Register 20-1) is set.

20.6.3 DEAD-BAND JITTER

The CWG input data signal may be asynchronous to the CWG input clock, so some jitter may occur in the observed dead band in each cycle. The maximum jitter is equal to one CWG clock period. See Equation 20-1 for details and an example.

EQUATION 20-1: DEAD-BAND DELAY TIME CALCULATION

$$T_{DEAD-BAND_MIN} = \frac{1}{F_{CWG_CLOCK}} \bullet DBx < 4:0>$$

$$T_{DEAD-BAND_MAX} = \frac{1}{F_{CWG_CLOCK}} \bullet DBx < 4:0> + 1$$

$$T_{JITTER} = T_{DEAD-BAND_MAX} - T_{DEAD-BAND_MIN}$$

$$T_{JITTER} = \frac{1}{F_{CWG_CLOCK}}$$

$$T_{DEAD-BAND_MAX} = T_{DEAD-BAND_MIN} + T_{JITTER}$$
Example:
$$DBR < 4:0> = 0x0A = 10$$

$$F_{CWG_CLOCK} = 8 MHz$$

$$T_{JITTER} = \frac{1}{8 MHz}$$

$$T_{DEAD-BAND_MIN} = 125 \text{ ns } \bullet 10 = 1.25 \text{ } \mu \text{s}$$

$$T_{DEAD-BAND_MAX} = 1.25 \text{ } \mu \text{s} + 0.125 \text{ } \mu \text{s} = 1.37 \text{ } \mu \text{s}$$

20.7 Auto-Shutdown Control

Auto-shutdown is a method to immediately override the CWG output levels with specific overrides that allow for safe shutdown of the circuit. The shutdown state can be either cleared automatically or held until cleared by software.

20.7.1 SHUTDOWN

The shutdown state can be entered by either of the following two methods:

- Software generated
- External input

The SHUTDOWN bit indicates when a Shutdown condition exists. The bit may be set or cleared in software or by hardware.

20.7.1.1 Software-Generated Shutdown

Setting the SHUTDOWN bit of the CWGxAS0 register will force the CWG into the Shutdown state.

When auto-restart is disabled, the Shutdown state will persist as long as the SHUTDOWN bit is set.

When auto-restart is enabled, the SHUTDOWN bit will clear automatically and resume operation on the next rising edge event.

20.7.1.2 External Input Source Shutdown

Any of the auto-shutdown external inputs can be selected to suspend the CWG operation. These sources are individually enabled by the ASxE bits of the CWGxAS1 register (Register 20-7). When any of the selected inputs goes active (pins are active-low), the CWG outputs will immediately switch to the override levels selected by the LSBD<1:0> and LSAC<1:0> bits without any software delay (Section 20.7.1.3 "Pin Override Levels"). Any of the following external input sources can be selected to cause a Shutdown condition:

- Comparator C1
- Comparator C2
- CLC2
- CWGxPPS

Note: Shutdown inputs are level sensitive, not edge sensitive. The shutdown state cannot be cleared, except by disabling auto-shutdown, as long as the shutdown input level persists.

20.7.1.3 Pin Override Levels

The levels driven to the CWG outputs during an autoshutdown event are controlled by the LSBD<1:0> and LSAC<1:0> bits of the CWGxAS0 register (Register 20-6). The LSBD<1:0> bits control CWGxB/D output levels, while the LSAC<1:0> bits control the CWGxA/C output levels.

20.7.1.4 Auto-Shutdown Interrupts

When an auto-shutdown event occurs, either by software or hardware setting SHUTDOWN, the CWGxIF flag bit of the PIR4 register is set (Register 8-11).

20.8 Auto-Shutdown Restart

After an auto-shutdown event has occurred, there are two ways to resume operation:

- Software controlled
- Auto-restart

In either case, the shutdown source must be cleared before the restart can take place. That is, either the Shutdown condition must be removed, or the corresponding WGASxE bit must be cleared.

20.8.1 SOFTWARE-CONTROLLED RESTART

If the REN bit of the CWGxASD0 register is clear (REN = 0), the CWGx module must be restarted after an auto-shutdown event through software.

Once all auto-shutdown conditions are removed, the software must clear SHUTDOWN. Once SHUTDOWN is cleared, the CWG module will resume operation upon the first rising edge of the CWG data input.

Note: SHUTDOWN bit cannot be cleared in software if the auto-shutdown condition is still present.

20.8.2 AUTO-RESTART

If the REN bit of the CWGxASD0 register is set (REN = 1), the CWGx module will restart from the shutdown state automatically.

Once all auto-shutdown conditions are removed, the hardware will automatically clear SHUTDOWN. Once SHUTDOWN is cleared, the CWG module will resume operation upon the first rising edge of the CWG data input.

Note: SHUTDOWN bit cannot be cleared in software if the auto-shutdown condition is still present.

20.9 Operation During Sleep

The CWGx module will operate during Sleep, provided that the input sources remain active.

If the HFINTOSC is selected as the module clock source, dead-band generation will remain active. This will have a direct effect on the Sleep mode current.

20.10 Configuring the CWG

- Ensure that the TRIS control bits corresponding to CWG outputs are set so that all are configured as inputs, ensuring that the outputs are inactive during setup. External hardware may ensure that pin levels are held to safe levels.
- 2. Clear the EN bit, if not already cleared.
- Configure the MODE<2:0> bits of the CWGxCON0 register to set the output operating mode.
- 4. Configure the POLy bits of the CWGxCON1 register to set the output polarities.
- 5. Configure the DAT<3:0> bits of the CWGxDAT register to select the data input source.
- 6. If a Steering mode is selected, configure the STRy bits to select the desired output on the CWG outputs.
- Configure the LSBD<1:0> and LSAC<1:0> bits of the CWGxAS0 register to select the autoshutdown output override states (this is necessary even if not using auto-shutdown because start-up will be from a shutdown state).
- 8. If auto-restart is desired, set the REN bit of CWGxAS0.
- 9. If auto-shutdown is desired, configure the ASxE bits of the CWGxAS1 register to select the shutdown source.
- 10. Set the desired rising and falling dead-band times with the CWGxDBR and CWGxDBF registers.
- 11. Select the clock source in the CWGxCLKCON register.
- 12. Set the EN bit to enable the module.
- 13. Clear the TRIS bits that correspond to the CWG outputs to set them as outputs.
- 14. If auto-restart is to be used, set the REN bit and the SHUTDOWN bit will be cleared automatically. Otherwise, clear the SHUTDOWN bit in software to start the CWG.

20.11 Register Definitions: CWG Control

				LREGISTER	•		
R/W-0/0	R/W/HC-0/0	U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0
EN	LD ⁽¹⁾		—	—		MODE<2:0>	
bit 7							bit (
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, rea	d as '0'	
u = Bit is unch	nanged	x = Bit is unki	nown	-n/n = Value a	at POR and BC	R/Value at all o	ther Resets
'1' = Bit is set		'0' = Bit is cle	ared	HS/HC = Bit i	s set/cleared b	y hardware	
bit 7 bit 6	1 = Dead-bar this bit is 0 = Buffers re	enabled disabled ad Buffers bit ⁽¹ nd count buffer set. emain unchang	rs to be loade ged	d on CWG data	a rising edge fo	llowing first fall	ing edge afte
bit 5-3	Unimplemen	ted: Read as '	0'				
bit 2-0	111 = Reser 110 = Reser 101 = CWG 100 = CWG 011 = CWG 010 = CWG	ved outputs operat outputs operat outputs operat outputs operat	e in Push-Pul e in Half-Brido e in Reverse e in Forward I		de		

REGISTER 20-1: CWGxCON0: CWGx CONTROL REGISTER 0

Note 1: This bit can only be set after EN = 1; it cannot be set in the same cycle when EN is set.

U-0	U-0	R-x	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
_	_	IN	_	POLD	POLC	POLB	POLA
bit 7		·		•			bit
Legend:							
R = Readat	ole bit	W = Writable	bit	U = Unimpler	mented bit, reac	l as '0'	
u = Bit is un	changed	x = Bit is unk	nown	-n/n = Value a	at POR and BO	R/Value at all c	other Resets
'1' = Bit is s	et	'0' = Bit is cle	ared	q = Value dep	pends on condit	ion	
bit 7-6	Unimpleme	ented: Read as	0'				
bit 5	IN: CWGx [Data Input Signa	l (read-only)				
bit 4	Unimpleme	ented: Read as '	0'				
bit 3	POLD: WG	xD Output Polar	ity bit				
	•	output is inverted					
	0 = Signal o	output is normal	polarity				
bit 2		xC Output Polar	•				
	•	output is inverted					
	•	output is normal					
bit 1		xB Output Polar					
	-	output is inverted					
	•	output is normal					
bit 0		xA Output Polar	•				
	•	output is inverted					
	0 = Signal c	output is normal	polarity				

REGISTER 20-2: CWGxCON1: CWGx CONTROL REGISTER 1

REGISTER 20-3: CWGxCLKCON: CWGx CLOCK INPUT SELECTION REGISTER

U-0	U-0	U-0	U-0	U-0	U-0	U-0	R/W-0/0
—	_	_	_	_	_		CS
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Value depends on condition

bit 7-1 Unimplemented: Read as '0'

bit 0 CS: CWG Clock Source Selection Select bits

WGCLK	K Clock Source			
0	Fosc			
1	HFINTOSC (remains operating during Sleep)			

	0- 4 . 0110A			SELECTION				
U-0	U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
—					DAT<3:0>			
bit 7		·		·			bit 0	
Legend:								

REGISTER 20-4: CWGxDAT: CWGx DATA INPUT SELECTION REGISTER

Legena:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Value depends on condition

bit 7-4 Unimplemented: Read as '0'

bit 3-0 DAT<3:0>: CWG Data Input Selection bits

DAT	Data Source
0000	CWGxPPS
0001	C1OUT
0010	C2OUT
0011	CCP1
0100	CCP2
0101	CCP3
0110	CCP4
0111	PWM5
1000	PWM6
1001	NCO1
1010	CLC1
1011	CLC2
1100	CLC3
1101	CLC4
1110	Reserved
1111	Reserved

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0			
OVRD	OVRC	OVRB	OVRA	STRD ⁽²⁾	STRC ⁽²⁾	STRB ⁽²⁾	STRA ⁽²⁾			
bit 7				• •			bit 0			
										
Legend:										
R = Readable bit		W = Writable bit		U = Unimplemented bit, read as '0'						
u = Bit is und	changed	x = Bit is unkr	nown	wn -n/n = Value at POR and BOR/Value at all other Rese						
'1' = Bit is se	t	'0' = Bit is cleared q = Value depends on condition								
bit 7	OVRD: Stee	ring Data D bit								
bit 6	OVRC: Stee	ring Data C bit								
oit 5	OVRB: Stee	ring Data B bit								
bit 4	OVRA: Stee	ring Data A bit								
bit 3	STRD: Steer	STRD: Steering Enable bit D ⁽²⁾								
	1 = CWGxD	1 = CWGxD output has the CWGx data input waveform with polarity control from POLD bit								
	0 = CWGxD	output is assigr	ned to value of	OVRD bit						
bit 2	STRC: Steer	STRC: Steering Enable bit C ⁽²⁾								
	1 = CWGxC	1 = CWGxC output has the CWGx data input waveform with polarity control from POLC bit								
	0 = CWGxC	0 = CWGxC output is assigned to value of OVRC bit								
bit 1 STRB: Steering Enable bit B ⁽²⁾										
	1 = CWGxB	1 = CWGxB output has the CWGx data input waveform with polarity control from POLB bit								
	0 = CWGxB	0 = CWGxB output is assigned to value of OVRB bit								
bit 0	STRA: Steer	STRA: Steering Enable bit A ⁽²⁾								
	1 = CWGxA	1 = CWGxA output has the CWGx data input waveform with polarity control from POLA bit								
	0 = CWGxA	output is assign	ed to value of	OVRA bit						
Note 1: T	he bits in this reg	e bits in this register apply only when MODE<2:0> = $00x$ (Register 20-1, steering modes).								
2 : T	his bit is double-	buffered when I	MODE<2:0> =	001.						

REGISTER 20-5: CWGxSTR⁽¹⁾: CWG STEERING CONTROL REGISTER

2: This bit is double-buffered when MODE<2:0> = 001.

R/W/HS/SC-0/0	R/W-0/0	R/W-0/0	R/W-1/1	R/W-0/0	R/W-1/1	U-0	U-0	
SHUTDOWN	REN	LSBD)<1:0>	LSAC	><1:0>	—	—	
bit 7							bit 0	
Legend:								
R = Readable bit	t	W = Writable	bit	U = Unimplem	ented bit, read	as '0'		
u = Bit is unchan	ged	x = Bit is unki	nown	-n/n = Value at	t POR and BOR	:/Value at all o	ther Resets	
'1' = Bit is set		'0' = Bit is cle	ared	q = Value depe	ends on conditio	on		
				(1.0)				
bit 7		: Auto-Shutdov		ıs bit ^(1,2)				
		-shutdown stat						
		-shutdown eve		bd				
bit 6 REN: Auto-Restart Enable bit								
		start is enabled						
	• • • • • • • • •	start is disabled			o			
bit 5-4				Shutdown State (
				nen an auto-shut nen an auto-shut				
	-			an auto-shutdow				
			•	ding polarity, is utdown event oc	•	GxB/D after t	he required	
bit 3-2	LSAC<1:0>:	CWGxA and C	WGxC Auto-S	Shutdown State (Control bits			
	$11 = A \log i c'1'$ is placed on CWGxA/C when an auto-shutdown event occurs.							
	10 = A logic '0' is placed on CWGxA/C when an auto-shutdown event occurs.							
		-		an auto-shutdow				
			•	ding polarity, is utdown event oc	•	GXA/C after t	ne required	
bit 1-0	Unimplemen	ited: Read as '	0'					
Note 1: This b	oit may be writt	ten while EN =	0 (Register 20)-1), to place the	outputs into the	e shutdown co	onfiguration.	
	utouto will rom	ain in auta ahu	itdouuro ototo u	ntil the next risin	a adap of the C	WC data innu	it offer this	

REGISTER 20-6: CWGxAS0: CWG AUTO-SHUTDOWN CONTROL REGISTER 0

2: The outputs will remain in auto-shutdown state until the next rising edge of the CWG data input after this bit is cleared.

U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
	—	—	AS4E	AS3E	AS2E	AS1E	AS0E	
bit 7				·	·		bit 0	
Legend:								
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'		
u = Bit is unch	anged	x = Bit is unkr	nown	-n/n = Value at POR and BOR/Value at all other Reset				
'1' = Bit is set		'0' = Bit is clea	ared	q = Value de	pends on condit	ion		
bit 7-5	Unimplemented: Read as '0'							
bit 4	AS4E: CWG	Auto-Shutdowr	n Source 4 (CL	C4) Enable bit				
		utdown for CLC						
		utdown for CLC						
bit 3		Auto-Shutdowr utdown from Cl	(C2) Enable bit				
	- /	utdown from C		-				
bit 2	AS2E: CWG	Auto-Shutdowr	Source 2 (C2	2) Enable bit				
		utdown from Co	•	,				
	0 = Auto-sh	utdown from Co	omparator 2 is	disabled				
bit 1	AS1E: CWG	Auto-Shutdowr	n Source 1 (C1	l) Enable bit				
		utdown from C						
		utdown from Co	•					
bit 0		Auto-Shutdowr utdown from C'	(NGxPPS) Enat	de bit			
		utdown from C						

REGISTER 20-7: CWGxAS1: CWG AUTO-SHUTDOWN CONTROL REGISTER 1

REGISTER 20-8: CWGxDBR: CWGx RISING DEAD-BAND COUNT REGISTER

U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
—	—			DBR	<5:0>		
bit 7							bit 0
Legend:							

R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	q = Value depends on condition

bit 7-6 Unimplemented: Read as '0'

bit 5-0 DBR<5:0>: CWG Rising Edge Triggered Dead-Band Count bits 11 1111 = 63-64 CWG clock periods 11 1110 = 62-63 CWG clock periods . 00 0010 = 2-3 CWG clock periods 00 0001 = 1-2 CWG clock periods 00 0000 = 0 CWG clock periods. Dead-band generation is bypassed.

U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
_	_			DBF<5:0>					
bit 7							bit 0		
Legend:									
R = Readable bit W = Writable bit				U = Unimpler	nented bit, read	as '0'			
u = Bit is unchanged x = Bit is unknown			-n/n = Value a	at POR and BO	R/Value at all c	other Resets			
'1' = Bit is set '0' = Bit is cleared			q = Value depends on condition						
bit 7-6	Unimplemer	ited: Read as '	0'						
bit 5-0	DBF<5:0>: C	WG Falling Ed	ge Triggered	Dead-Band Coເ	int bits				
	11 1111 =	63-64 CWG clo	ock periods						
	11 1110 =	62-63 CWG clo	ock periods						
	•								
	•								
	•		(pariada						
		2-3 CWG clock 1-2 CWG clock							
				-hand generatio	n is hynassed				
	00 0000 = 0 CWG clock periods. Dead-band generation is bypassed.								

REGISTER 20-9: CWGxDBF: CWGx FALLING DEAD-BAND COUNT REGISTER

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	—	_	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	—		ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_	—	_	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_	_	_	150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
PIR4	CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	110
PIE4	CWG2IE	CWG1IE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE	105
CWG1CON0	EN	LD	_	_	_	Ν	/ODE<2:0	>	213
CWG1CON1	_	_	IN	_	POLD	POLC	POLB	POLA	214
CWG1CLKCON	—	_	_	_	_	_	_	CS	214
CWG1DAT	—	_	_	— DAT<3:0>				215	
CWG1STR	OVRD	OVRC	OVRB	OVRA	STRD	STRC	STRB	STRA	216
CWG1AS0	SHUTDOWN	REN	LSBD<	<1:0>	LSAC	<1:0>	_	_	217
CWG1AS1	—	_	_	AS4E AS3E AS2E AS1E AS0E				218	
CWG1DBR	—	_			DBR	<5:0>			218
CWG1DBF	—	_			DBF<	<5:0>			219
CWG1PPS	—	—	_		CV	VG1PPS<4	l:0>		162
CWG2CON0	EN	LD	_		_	Ν	/IODE<2:0	>	213
CWG2CON1	—	_	IN	_	POLD	POLC	POLB	POLA	214
CWG2CLKCON	—	_	_	_	_	_	—	CS	214
CWG2DAT	—	_	_	_		DAT	<3:0>		215
CWG2STR	OVRD	OVRC	OVRB	OVRA	STRD	STRC	STRB	STRA	216
CWG2AS0	SHUTDOWN	REN	LSBD<	<1:0>	LSAC	<1:0>	—	_	217
CWG2AS1	—			AS4E	AS3E	AS2E	AS1E	AS0E	218
CWG2DBR	_			-	DBR	<5:0>	-	-	218
CWG2DBF	—				DBF<	<5:0>			219
CWG2PPS					CV	VG2PPS<4	l:0>		162

TABLE 20-2: SUMMARY OF REGISTERS ASSOCIATED WITH CWGX	TABLE 20-2 :	SUMMARY OF REGISTERS ASSOCIATED WITH CWGx
---	---------------------	---

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '0'.

21.0 CONFIGURABLE LOGIC CELL (CLC)

The Configurable Logic Cell (CLCx) provides programmable logic that operates outside the speed limitations of software execution. The logic cell takes up to 36 input signals and, through the use of configurable gates, reduces the 36 inputs to four logic lines that drive one of eight selectable single-output logic functions.

Input sources are a combination of the following:

- I/O pins
- Internal clocks
- · Peripherals
- · Register bits

The output can be directed internally to peripherals and to an output pin.

Refer to Figure 21-1 for a simplified diagram showing signal flow through the CLCx.

Possible configurations include:

- · Combinatorial Logic
 - AND
 - NAND
 - AND-OR
 - AND-OR-INVERT
 - OR-XOR
 - OR-XNOR
- Latches
 - S-R
 - Clocked D with Set and Reset
- Transparent D with Set and Reset
- Clocked J-K with Reset




FIGURE 21-1: CLCx SIMPLIFIED BLOCK DIAGRAM

21.1 CLCx Setup

Programming the CLCx module is performed by configuring the four stages in the logic signal flow. The four stages are:

- Data selection
- Data gating
- Logic function selection
- Output polarity

Each stage is setup at run time by writing to the corresponding CLCx Special Function Registers. This has the added advantage of permitting logic reconfiguration on-the-fly during program execution.

21.1.1 DATA SELECTION

There are 36 signals available as inputs to the configurable logic.

Data selection is through four multiplexers as indicated on the left side of Figure 21-2. Data inputs in the figure are identified by 'LCx_in' signal name.

Table 21-1 correlates the input number to the actual signal for each CLC module. The column labeled 'LCxDyS<5:0> Value' indicates the MUX selection code for the selected data input. LCxDyS is an abbreviation for the MUX select input codes: LCxD1S<5:0> through LCxD4S<5:0>.

Data inputs are selected with CLCxSEL0 through CLCxSEL3 registers (Register 21-3 through Register 21-6).

TABLE 21-1: CLCx DATA INPUT SELECTION

LCxDyS<5:0> Value	CLCx Input Source
L00011 [35]	TMR6/PR6 match
L00010 [34]	TMR5 overflow
L00001 [33]	TMR4/PR4 match
L00000 [32]	TMR3 overflow
11111 [31]	Fosc
L1110 [30]	HFINTOSC
11101 [29]	LFINTOSC
11100 [28]	ADCRC
11011 [27]	IOCIF int flag bit
11010 [26]	TMR2/PR2 match
11001 [25]	TMR1 overflow
11000 [24]	TMR0 overflow
10111 [23]	EUSART1 (DT) output
L0110 [22]	EUSART1 (TX/CK) output
L0101 [21]	SDA2/SDO2
L0100 [20]	SCL2/SCK2
10011 [19]	SDA1/SDO1
10010 [18]	SCL1/SCK1
10001 [17]	PWM6 output
10000 [16]	PWM5 output
01111 [15]	CCP4 output
01110 [14]	CCP3 output
01101 [13]	CCP2 output
01100 [12]	CCP1 output
01011 [11]	CLKR output
01010 [10]	DSM output
01001 [9]	C2 output
01000 [8]	C1 output
00111 [7]	CLC4 output
00110 [6]	CLC3 output
00101 [5]	CLC2 output
00100 [4]	CLC1 output
00011 [3]	CLCIN3PPS
00010 [2]	CLCIN2PPS
00001 [1]	CLCIN1PPS
00000 [0]	CLCINOPPS

21.1.2 INPUT DATA SELECTION GATES

Outputs from the input multiplexers are directed to the desired logic function input through the data gating stage. Each data gate can direct any combination of the four selected inputs.

The gate can be configured to direct each input signal as inverted or noninverted data. The output of each gate can be inverted before going on to the logic function stage.

The gating is in essence a 1-to-4 input AND/NAND/OR/NOR gate. When every input is inverted and the output is inverted, the gate is an OR of all enabled data inputs. When the inputs and output are not inverted, the gate is an AND of all enabled inputs.

Table 21-2 summarizes the basic logic that can be obtained in gate 1 by using the Gate Logic Select bits and Gate Polarity bits. The table shows the logic of four input variables, but each gate can be configured to use less than four. If no inputs are selected, the output will be zero or one, depending on the Gate Output Polarity bit.

TABLE 21-2: DATA GATING LOGIC

CLCxGLSy	LCxGyPOL	Gate Logic
0x55	1	4-input AND
0x55	0	4-input NAND
0xAA	1	4-input NOR
0xAA	0	4-input OR
0x00	0	Logic 0
0x00	1	Logic 1

It is possible (but not recommended) to select both the true and negated values of an input. When this is done, the gate output is zero, regardless of the other inputs, but may emit logic glitches (transient-induced pulses). If the output of the channel must be zero or one, the recommended method is to set all gate bits to zero and use the Gate Polarity bit to set the desired level.

Data gating is configured with the logic gate select registers as follows:

- Gate 1: CLCxGLS0 (Register 21-7)
- Gate 2: CLCxGLS1 (Register 21-8)
- Gate 3: CLCxGLS2 (Register 21-9)
- Gate 4: CLCxGLS3 (Register 21-10)

Register number suffixes are different than the gate numbers because other variations of this module have multiple gate selections in the same register.

Data gating is indicated in the right side of Figure 21-2. Only one gate is shown in detail. The remaining three gates are configured identically with the exception that the data enables correspond to the enables for that gate.

21.1.3 LOGIC FUNCTION

There are eight available logic functions, including:

- AND-OR
- OR-XOR
- AND
- S-R Latch
- · D Flip-Flop with Set and Reset
- D Flip-Flop with Reset
- · J-K Flip-Flop with Reset
- · Transparent Latch with Set and Reset

Logic functions are shown in Figure 21-3. Each logic function has four inputs and one output. The four inputs are the four data gate outputs of the previous stage. The output is fed to the inversion stage and from there to other peripherals, an output pin, and back to the CLCx itself.

21.1.4 OUTPUT POLARITY

The last stage in the configurable logic cell is the output polarity. Setting the LCxPOL bit of the CLCxPOL register inverts the output signal from the logic stage. Changing the polarity while the interrupts are enabled will cause an interrupt for the resulting output transition.

21.2 CLCx Interrupts

An interrupt will be generated upon a change in the output value of the CLCx when the appropriate interrupt enables are set. A rising edge detector and a falling edge detector are present in each CLC for this purpose.

The CLCxIF bit of the associated PIR3 register will be set when either edge detector is triggered and its associated enable bit is set. The LCxINTP bit enables rising edge interrupts and the LCxINTN bit enables falling edge interrupts. Both are located in the CLCxCON register.

To fully enable the interrupt, set the following bits:

- The CLCxIE bit of the PIE3 register
- The LCxINTP bit of the CLCxCON register (for a rising edge detection)
- The LCxINTN bit of the CLCxCON register (for a falling edge detection)
- · The PEIE and GIE bits of the INTCON register

The CLCxIF bit of the PIR3 register, must be cleared in software as part of the interrupt service. If another edge is detected while this flag is being cleared, the flag will still be set at the end of the sequence.

21.3 Output Mirror Copies

Mirror copies of all LCxCON output bits are contained in the CLCDATA register. Reading this register samples the outputs of all CLCs simultaneously. This prevents any timing skew introduced by testing or reading the LCxOUT bits in the individual CLCxCON registers.

21.4 Effects of a Reset

The CLCxCON register is cleared to zero as the result of a Reset. All other selection and gating values remain unchanged.

21.5 Operation During Sleep

The CLC module operates independently from the system clock and will continue to run during Sleep, provided that the input sources selected remain active.

The HFINTOSC remains active during Sleep when the CLC module is enabled and the HFINTOSC is selected as an input source, regardless of the system clock source selected.

In other words, if the HFINTOSC is simultaneously selected as the system clock and as a CLC input source, when the CLC is enabled, the CPU will go Idle during Sleep, but the CLC will continue to operate and the HFINTOSC will remain active.


This will have a direct effect on the Sleep mode current.

21.6 CLCx Setup Steps


Follow these steps when setting up the CLCx:

- Disable CLCx by clearing the LCxEN bit.
- Select desired inputs using CLCxSEL0 through CLCxSEL3 registers (See Table 21-1).
- Clear any associated ANSEL bits.
- Set all TRIS bits associated with external CLC inputs.
- Enable the chosen inputs through the four gates using CLCxGLS0, CLCxGLS1, CLCxGLS2, and CLCxGLS3 registers.
- Select the gate output polarities with the LCxGyPOL bits of the CLCxPOL register.
- Select the desired logic function with the LCxMODE<2:0> bits of the CLCxCON register.
- Select the desired polarity of the logic output with the LCxPOL bit of the CLCxPOL register. (This step may be combined with the previous gate output polarity step).
- If driving a device pin, set the desired pin PPS control register and also clear the TRIS bit corresponding to that output.
- If interrupts are desired, configure the following bits:
- Set the LCxINTP bit in the CLCxCON register for rising event.
- Set the LCxINTN bit in the CLCxCON register for falling event.
- Set the CLCxIE bit of the PIE3 register.
- Set the GIE and PEIE bits of the INTCON register.
- Enable the CLCx by setting the LCxEN bit of the CLCxCON register.

PIC16(L)F18326/18346



PIC16(L)F18326/18346



21.7 Register Definitions: CLC Control

R/W-0/0	U-0	R-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
LCxEN		LCxOUT	LCxINTP	LCxINTN		LCxMODE<2:0>	
bit 7							bit (
Legend:							
R = Readab	le bit	W = Writable	bit	U = Unimplen	nented bit, rea	d as '0'	
u = Bit is un		x = Bit is unkr		•	,	DR/Value at all o	ther Resets
'1' = Bit is se	•	'0' = Bit is clea					
bit 7	LCxEN: Con	figurable Logic	Cell Enable b	it			
	Ų	able logic cell i		U 1	0		
L H O	•	able logic cell is		has logic zero	output		
bit 6	•	nted: Read as '					
bit 5		nfigurable Logi		•		Ŧ	
	•	gic cell output		· · ·			
bit 4		onfigurable Log		0 0		e bit	
		will be set wher will not be set	n a rising edge	e occurs on CL	CXOUT		
bit 3		onfigurable Log	ic Cell Negativ	ve Edge Going	Interrupt Enat	ole bit	
		will be set wher	-	• •			
	0 = CLCxIF	will not be set					
bit 2-0	LCxMODE<2	2:0>: Configura	ble Logic Cell	Functional Mo	de bits		
		s 1-input transpa		h S and R			
		J-K flip-flop wi					
		2-input D flip-f 1-input D flip-f					
	011 = Cell is		iop with 5 and				
	010 = Cell is						
	001 = Cell is	•					
	000 = Cell is						

REGISTER 21-1: CLCxCON: CONFIGURABLE LOGIC CELL CONTROL REGISTER

R/W-0/0	U-0	U-0	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u			
LCxPOL	. —	—	—	LCxG4POL	LCxG3POL	LCxG2POL	LCxG1POL			
bit 7							bit C			
Legend:										
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'										
u = Bit is unchanged x = Bit is unknown -n/n = Value at POR and BOR/Value at all other Re							other Resets			
'1' = Bit is s	et	'0' = Bit is clea	ared							
bit 7	LCxPOL: CLCxOUT Output Polarity Control bit									
		put of the logic o								
		0 = The output of the logic cell is not inverted								
bit 6-4	Unimpleme	nted: Read as '	0'							
bit 3		Gate 3 Output	•							
		put of gate 3 is i		n applied to the	logic cell					
		put of gate 3 is r								
bit 2		Gate 2 Output								
		put of gate 2 is i put of gate 2 is r		n applied to the	logic cell					
bit 1		Gate 1 Output		trol bit						
		put of gate 1 is i	,		logic cell					
		put of gate 1 is r			logic cell					
bit 0		Gate 0 Output		trol bit						
-		put of gate 0 is i	•		logic cell					
		put of gate 0 is r			0					

REGISTER 21-2: CLCxPOL: SIGNAL POLARITY CONTROL REGISTER

REGISTER 21-3: CLCxSEL0: GENERIC CLCx DATA 0 SELECT REGISTER

U-0	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
—	—			LCxD1	1S<5:0>		
bit 7							bit 0

Legend:R = Readable bitW = Writable bitU = Unimplemented bit, read as '0'u = Bit is unchangedx = Bit is unknown-n/n = Value at POR and BOR/Value at all other Resets'1' = Bit is set'0' = Bit is cleared

bit 7-6	Unimplemented: Read as '0'
---------	----------------------------

bit 5-0	LCxD1S<5:0>: CLCx Data 1 Input Selection bits
	See Table 21-1.

REGISTER 21-4: CLCxSEL1: GENERIC CLCx DATA 1 SELECT REGISTER

U-0	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
—	—			LCxD2	2S<5:0>		
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6	Unimplemented: Read as '0'
---------	----------------------------

bit 5-0 LCxD2S<5:0>: CLCx Data 2 Input Selection bits See Table 21-1.

REGISTER 21-5: CLCxSEL2: GENERIC CLCx DATA 2 SELECT REGISTER

U-0	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
—	—			LCxD3	3S<5:0>		
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 Unimplemented: Read as '0'

bit 5-0 LCxD3S<5:0>: CLCx Data 3 Input Selection bits See Table 21-1.

REGISTER 21-6: CLCxSEL3: GENERIC CLCx DATA 3 SELECT REGISTER

LCxD4S<5:0>	/-x/u
hit 7	
bit 7	bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 Unimplemented: Read as '0'

bit 5-0 LCxD4S<5:0>: CLCx Data 4 Input Selection bits See Table 21-1.

REGISTER 21-7: CLCxGLS0: GATE 0 LOGIC SELECT REGISTER

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
LCxG1D4T	LCxG1D4N	LCxG1D3T	LCxG1D3N	LCxG1D2T	LCxG1D2N	LCxG1D1T	LCxG1D1N
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7	LCxG1D4T: Gate 0 Data 4 True (noninverted) bit
	 1 = CLCIN3 (true) is gated into CLCx Gate 0 0 = CLCIN3 (true) is not gated into CLCx Gate 0
bit 6	LCxG1D4N: Gate 0 Data 4 Negated (inverted) bit
	1 = CLCIN3 (inverted) is gated into CLCx Gate 0
	0 = CLCIN3 (inverted) is not gated into CLCx Gate 0
bit 5	LCxG1D3T: Gate 0 Data 3 True (noninverted) bit
	1 = CLCIN2 (true) is gated into CLCx Gate 0
	0 = CLCIN2 (true) is not gated into CLCx Gate 0
bit 4	LCxG1D3N: Gate 0 Data 3 Negated (inverted) bit
	1 = CLCIN2 (inverted) is gated into CLCx Gate 0
	0 = CLCIN2 (inverted) is not gated into CLCx Gate 0
bit 3	LCxG1D2T: Gate 0 Data 2 True (noninverted) bit
	1 = CLCIN1 (true) is gated into CLCx Gate 0
	0 = CLCIN1 (true) is not gated into CLCx Gate 0
bit 2	LCxG1D2N: Gate 0 Data 2 Negated (inverted) bit
	1 = CLCIN1 (inverted) is gated into CLCx Gate 0
	0 = CLCIN1 (inverted) is not gated into CLCx Gate 0
bit 1	LCxG1D1T: Gate 0 Data 1 True (noninverted) bit
	1 = CLCIN0 (true) is gated into CLCx Gate 0
	0 = CLCIN0 (true) is not gated into CLCx Gate 0
bit 0	LCxG1D1N: Gate 0 Data 1 Negated (inverted) bit
	1 = CLCIN0 (inverted) is gated into CLCx Gate 0
	0 = CLCIN0 (inverted) is not gated into CLCx Gate 0

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
LCxG2D4T	LCxG2D4N	LCxG2D3T	LCxG2D3N	LCxG2D2T	LCxG2D2N	LCxG2D1T	LCxG2D1N
bit 7							bit C
Legend:							
R = Readable		W = Writable	bit	•	mented bit, read		
u = Bit is uncha	anged	x = Bit is unkr		-n/n = Value a	at POR and BO	R/Value at all c	ther Resets
'1' = Bit is set		'0' = Bit is clea	ared				
			. ,				
bit 7		Gate 1 Data 4 T	,	,			
		(true) is gated i (true) is not gat					
bit 6		Gate 1 Data 4 I					
bit o		(inverted) is ga	0 (,			
		(inverted) is no					
bit 5	LCxG2D3T: 0	Gate 1 Data 3 T	rue (noninver	ted) bit			
		(true) is gated i					
	0 = CLCIN2 ((true) is not gat	ed into CLCx	Gate 1			
bit 4		Gate 1 Data 3 I	•	,			
		(inverted) is ga					
bit 3		(inverted) is no	•				
DIL 3		Gate 1 Data 2 T (true) is gated i	,	,			
		(true) is not gat					
bit 2		Gate 1 Data 2 I					
		(inverted) is ga	•	,			
	0 = CLCIN1 (inverted) is no	t gated into Cl	Cx Gate 1			
bit 1	LCxG2D1T: O	Gate 1 Data 1 T	rue (noninver	ted) bit			
		(true) is gated i					
		(true) is not gat					
bit 0		Gate 1 Data 1 I	-	•			
		(inverted) is ga (inverted) is no					
	0 - CLUINU ((invented) is no	i galeu into Cl				

REGISTER 21-8: CLCxGLS1: GATE 1 LOGIC SELECT REGISTER

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
LCxG3D4T	LCxG3D4N	LCxG3D3T	LCxG3D3N	LCxG3D2T	LCxG3D2N	LCxG3D1T	LCxG3D1N
bit 7							bit 0
Legend:							
R = Readable		W = Writable		•	nented bit, read		
u = Bit is unch	anged	x = Bit is unkr		-n/n = Value a	at POR and BO	R/Value at all c	ther Resets
'1' = Bit is set		'0' = Bit is clea	ared				
			. ,				
bit 7		Gate 2 Data 4 1	,	,			
		(true) is gated i (true) is not gat					
bit 6		Gate 2 Data 4					
		(inverted) is ga	0 (,			
		(inverted) is no					
bit 5	LCxG3D3T: 0	Gate 2 Data 3 1	rue (noninver	ted) bit			
		(true) is gated i					
		(true) is not gat					
bit 4		Gate 2 Data 3 I	•	,			
		(inverted) is ga (inverted) is no					
bit 3		Gate 2 Data 2 1	•				
		(true) is gated i	,	,			
		(true) is not gat					
bit 2	LCxG3D2N:	Gate 2 Data 2	Negated (inve	rted) bit			
		(inverted) is ga					
		(inverted) is no	-				
bit 1		Gate 2 Data 1 1		,			
		(true) is gated i (true) is not gat					
bit 0		Gate 2 Data 1					
		(inverted) is ga	-	•			
		(inverted) is ga					

REGISTER 21-9: CLCxGLS2: GATE 2 LOGIC SELECT REGISTER

		-					
R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
LCxG4D4T	LCxG4D4N	LCxG4D3T	LCxG4D3N	LCxG4D2T	LCxG4D2N	LCxG4D1T	LCxG4D1N
bit 7		•				•	bit (
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, read	as '0'	
u = Bit is uncha	anged	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all c	ther Resets
'1' = Bit is set		'0' = Bit is clea	ared				
bit 7	LCxG4D4T: 0	Gate 3 Data 4 1	True (noninver	ted) bit			
		(true) is gated i					
		(true) is not gat					
bit 6		Gate 3 Data 4	•	,			
		(inverted) is ga (inverted) is no					
bit 5		Gate 3 Data 3 1	•				
2.1.0		(true) is gated i					
		(true) is not gat					
bit 4	LCxG4D3N:	Gate 3 Data 3	Negated (inve	rted) bit			
		(inverted) is ga					
		(inverted) is no	•				
bit 3		Gate 3 Data 2 1	•	,			
		(true) is gated i (true) is not gat					
bit 2		Gate 3 Data 2					
SR 2		(inverted) is ga					
		(inverted) is no					
bit 1	LCxG4D1T: 0	Gate 3 Data 1 1	True (noninver	ted) bit			
		(true) is gated i					
		(true) is not gat					
bit 0		Gate 3 Data 1	•	,			
		(inverted) is ga (inverted) is no					
	\cup – ULUNU(inveneuris no	голео шо Ст				

REGISTER 21-10: CLCxGLS3: GATE 3 LOGIC SELECT REGISTER

REGISTER 21-11: CLCDATA: CLC DATA OUTPUT

U-0	U-0	U-0	U-0	R-0	R-0	R-0	R-0
_	—	—	—	MLC4OUT	MLC3OUT	MLC2OUT	MLC1OUT
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4	Unimplemented: Read as '0'
bit 3	MLC4OUT: Mirror copy of LC4OUT bit
bit 2	MLC3OUT: Mirror copy of LC3OUT bit
bit 1	MLC2OUT: Mirror copy of LC2OUT bit
bit 0	MLC1OUT: Mirror copy of LC1OUT bit

TABLE 21-3: SUMMARY OF REGISTERS ASSOCIATED WITH CLCx

Name	Bit7	Bit6	Bit5	Bit4	Blt3	Bit2	Bit1	Bit0	Register on Page
ANSELA	_	_	ANSA5	ANSA4	—	ANSA2	ANSA1	ANSA0	144
TRISA	_	_	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	—	—	_	_	150
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	—	—		—	149
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
INTCON	GIE	PEIE	—	—	—	—	_	INTEDG	100
PIR3	OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF	109
PIE3	OSFIE	CSWIE	TMR3GIE	TMR3IE	CLC4IE	CLC3IE	CLC2IE	CLC1IE	104
CLC1CON	LC1EN	—	LC10UT	LC10UT LC1INTP LC1INTN LC1MODE<2:0>				>	227
CLC1POL	LC1POL	_	_	—	LC1G4POL	LC1G3POL	LC1G2POL	LC1G1POL	228
CLC1SEL0	_	_			LC1D1	S<5:0>			229
CLC1SEL1	—	_			LC1D2	2S<5:0>			229
CLC1SEL2	—	—			LC1D3	3S<5:0>			229
CLC1SEL3	—	—			LC1D4	IS<5:0>			230
CLC1GLS0	LC1G1D4T	LC1G1D4N	LC1G1D3T	LC1G1D3N	LC1G1D2T	LC1G1D2N	LC1G1D1T	LC1G1D1N	230
CLC1GLS1	LC1G2D4T	LC1G2D4N	LC1G2D3T	LC1G2D3N	LC1G2D2T	LC1G2D2N	LC1G2D1T	LC1G2D1N	231
CLC1GLS2	LC1G3D4T	LC1G3D4N	LC1G3D3T	LC1G3D3N	LC1G3D2T	LC1G3D2N	LC1G3D1T	LC1G3D1N	232
CLC1GLS3	LC1G4D4T	LC1G4D4N	LC1G4D3T	LC1G4D3N	LC1G4D2T	LC1G4D2N	LC1G4D1T	LC1G4D1N	233
CLC2CON	LC2EN	—	LC2OUT	LC2INTP	LC2INTN	L	C2MODE<2:0	>	227
CLC2POL	LC2POL	—	—	—	LC2G4POL	LC2G3POL	LC2G2POL	LC2G1POL	228
CLC2SEL0	—	_			LC2D1	S<5:0>		1	229
CLC2SEL1	-	—			LC2D2	2S<5:0>			229
CLC2SEL2	—	_			LC2D3	S<5:0>			229
CLC2SEL3	—	—		LC2D4S<5:0>					230

Name	Bit7	Bit6	Bit5	Bit4	Blt3	Bit2	Bit1	Bit0	Register on Page
CLC2GLS0	LC2G1D4T	LC2G1D4N	LC2G1D3T	LC2G1D3N	LC2G1D2T	LC2G1D2N	LC2G1D1T	LC2G1D1N	230
CLC2GLS1	LC2G2D4T	LC2G2D4N	LC2G2D3T	LC2G2D3N	LC2G2D2T	LC2G2D2N	LC2G2D1T	LC2G2D1N	231
CLC2GLS2	LC2G3D4T	LC2G3D4N	LC2G3D3T	LC2G3D3N	LC2G3D2T	LC2G3D2N	LC2G3D1T	LC2G3D1N	232
CLC2GLS3	LC2G4D4T	LC2G4D4N	LC2G4D3T	LC2G4D3N	LC2G4D2T	LC2G4D2N	LC2G4D1T	LC2G4D1N	233
CLC3CON	LC3EN	_	LC3OUT	LC3INTP	LC3INTN	L	C3MODE<2:0	>	227
CLC3POL	LC3POL	_	_	—	LC3G4POL	LC3G3POL	LC3G2POL	LC3G1POL	228
CLC3SEL0	—	_			LC3D1	S<5:0>			229
CLC3SEL1	_	_			LC3D2	S<5:0>			229
CLC3SEL2	—	_			LC3D3	S<5:0>			229
CLC3SEL3	_	_			LC3D4	S<5:0>			230
CLC3GLS0	LC3G1D4T	LC3G1D4N	LC3G1D3T	LC3G1D3N	LC3G1D2T	LC3G1D2N	LC3G1D1T	LC3G1D1N	230
CLC3GLS1	LC3G2D4T	LC3G2D4N	LC3G2D3T	LC3G2D3N	LC3G2D2T	LC3G2D2N	LC3G2D1T	LC3G2D1N	231
CLC3GLS2	LC3G3D4T	LC3G3D4N	LC3G3D3T	LC3G3D3N	LC3G3D2T	LC3G3D2N	LC3G3D1T	LC3G3D1N	232
CLC3GLS3	LC3G4D4T	LC3G4D4N	LC3G4D3T	LC3G4D3N	LC3G4D2T	LC3G4D2N	LC3G4D1T	LC3G4D1N	233
CLC4CON	LC4EN	_	LC4OUT	LC4INTP	LC4INTN	L	C4MODE<2:0	>	227
CLC4POL	LC4POL	_	—	—	LC4G4POL	LC4G3POL	LC4G2POL	LC4G1POL	228
CLC4SEL0	_	_			LC4D1	S<5:0>			229
CLC4SEL1	—	_			LC4D2	2S<5:0>			229
CLC4SEL2	_	_			LC4D3	S<5:0>			229
CLC4SEL3	—	_			LC4D4	S<5:0>			230
CLC4GLS0	LC4G1D4T	LC4G1D4N	LC4G1D3T	LC4G1D3N	LC4G1D2T	LC4G1D2N	LC4G1D1T	LC4G1D1N	230
CLC4GLS1	LC4G2D4T	LC4G2D4N	LC4G2D3T	LC4G2D3N	LC4G2D2T	LC4G2D2N	LC4G2D1T	LC4G2D1N	231
CLC4GLS2	LC4G3D4T	LC4G3D4N	LC4G3D3T	LC4G3D3N	LC4G3D2T	LC4G3D2N	LC4G3D1T	LC4G3D1N	232
CLC4GLS3	LC4G4D4T	LC4G4D4N	LC4G4D3T	LC4G4D3N	LC4G4D2T	LC4G4D2N	LC4G4D1T	LC4G4D1N	233
CLCDATA	_	_	_	—	MLC4OUT	MLC3OUT	MLC2OUT	MLC1OUT	234
CLCIN0PPS	_	_	_		CI	LCIN0PPS<4:	0>		162
CLCIN1PPS	—	—	—		C	LCIN1PPS<4:	0>		162
CLCIN2PPS	_	_	—	- CLCIN2PPS<4:0>				162	
CLCIN3PPS	_	_	—		C	LCIN3PPS<4:	0>		162
CLC10UTPPS	—	_	—		CL	C1OUTPPS<4	1:0>		162
CLC2OUTPPS	_	—	—		CL	C2OUTPPS<4	1:0>		162
CLC3OUTPPS	_	—	—		CL	C3OUTPPS<4	1:0>		162
CLC4OUTPPS	_	—	—		CL	C4OUTPPS<4	1:0>		162

Legend: — = unimplemented, read as '0'. Shaded cells are unused by the CLC module.


22.0 ANALOG-TO-DIGITAL CONVERTER (ADC) MODULE

The Analog-to-Digital Converter (ADC) allows conversion of an analog input signal to a 10-bit binary representation of that signal. This device uses analog inputs, which are multiplexed into a single sample and hold circuit. The output of the sample and hold is connected to the input of the converter. The converter generates a 10-bit binary result via successive approximation and stores the conversion result into the ADC result registers (ADRESH:ADRESL register pair). Figure 22-1 shows the block diagram of the ADC.

The ADC voltage reference is software selectable to be either internally generated or externally supplied.

FIGURE 22-1: ADC BLOCK DIAGRAM

The ADC can generate an interrupt upon completion of a conversion. This interrupt can be used to wake-up the device from Sleep.



22.1 ADC Configuration

When configuring and using the ADC the following functions must be considered:

- Port configuration
- · Channel selection
- ADC voltage reference selection
- ADC conversion clock source
- · Interrupt control
- · Result formatting

22.1.1 PORT CONFIGURATION

The ADC can be used to convert both analog and digital signals. When converting analog signals, the I/O pin will be configured for analog by setting the associated TRIS and ANSEL bits. Refer to **Section 12.0 "I/O Ports"** for more information.

Note:	Analog voltages on any pin that is defined
	as a digital input may cause the input
	buffer to conduct excess current.

22.1.2 CHANNEL SELECTION

There are several channel selections available:

- Five PORTA pins (RA0-RA2, RA4-RA5)
- Four PORTB pins (RB4-RB7, PIC16(L)F18346 only)
- Six PORTC pins (RC0-RC5, PIC16(L)F18326)
- Eight PORTC pins (RC0-RC7, PIC16(L)F18346 only)
- Temperature Indicator
- DAC output
- Fixed Voltage Reference (FVR)
- Vss (ground)

The CHS<5:0> bits of the ADCON0 register (Register 22-1) determine which channel is connected to the sample and hold circuit.

When changing channels, a delay is required before starting the next conversion. Refer to **Section 22.2 "ADC Operation**" for more information.

Note: It is recommended that when switching from an ADC channel of a higher voltage to a channel of a lower voltage, that the user selects the Vss channel before connecting to the channel with the lower voltage. If the ADC does not have a dedicated Vss input channel, the Vss selection (DAC1R<4:0> = b'00000') through the DAC output channel can be used. If the DAC is in use, a free input channel can be connected to Vss, and can be used in place of the DAC.

22.1.3 ADC VOLTAGE REFERENCE

The ADPREF<1:0> bits of the ADCON1 register provides control of the positive voltage reference. The positive voltage reference can be:

- VREF+ pin
- Vdd
- FVR 2.048V
- FVR 4.096V (Not available on LF devices)

The ADNREF bit of the ADCON1 register provides control of the negative voltage reference. The negative voltage reference can be:

- VREF- pin
- Vss

See Section 22.0 "Analog-to-Digital Converter (ADC) Module" for more details on the Fixed Voltage Reference.

22.1.4 CONVERSION CLOCK

The source of the conversion clock is software selectable via the ADCS<2:0> bits of the ADCON1 register. There are seven possible clock options:

- Fosc/2
- Fosc/4
- Fosc/8
- Fosc/16
- Fosc/32
- Fosc/64
- ADCRC (dedicated RC oscillator)

The time to complete one bit conversion is defined as TAD. One full 10-bit conversion requires 11 TAD periods as shown in Figure 22-2.

For correct conversion, the appropriate TAD specification must be met. Refer to Table 35-13 for more information. Table 22-1 gives examples of appropriate ADC clock selections.

Note: Unless using the ADCRC, any changes in the system clock frequency will change the ADC clock frequency, which may adversely affect the ADC result.

ADC Clock Period (TAD)		Device Frequency (Fosc)						
ADC Clock Source	ADCS<2:0>	32 MHz	20 MHz	16 MHz	8 MHz	4 MHz	1 MHz	
Fosc/2	000	62.5ns ⁽²⁾	100 ns ⁽²⁾	125 ns ⁽²⁾	250 ns ⁽²⁾	500 ns ⁽²⁾	2.0 μs	
Fosc/4	100	125 ns ⁽²⁾	200 ns ⁽²⁾	250 ns ⁽²⁾	500 ns ⁽²⁾	1.0 μs	4.0 μs	
Fosc/8	001	0.5 μs ⁽²⁾	400 ns ⁽²⁾	0.5 μs ⁽²⁾	1.0 μs	2.0 μs	8.0 μs ⁽³⁾	
Fosc/16	101	800 ns	800 ns	1.0 μs	2.0 μs	4.0 μs	16.0 μs ⁽³⁾	
Fosc/32	010	1.0 μs	1.6 μs	2.0 μs	4.0 μs	8.0 μs ⁽³⁾	32.0 μs ⁽²⁾	
Fosc/64	110	2.0 μs	3.2 μs	4.0 μs	8.0 μs ⁽³⁾	16.0 μs ⁽²⁾	64.0 μs ⁽²⁾	
ADCRC	x11	1.0-6.0 μs ^(1,4)						

TABLE 22-1: ADC CLOCK PERIOD (TAD) Vs. DEVICE OPERATING FREQUENCIES

Legend: Shaded cells are outside of recommended range.


Note 1: See TAD parameter for ADCRC source typical TAD value.

2: These values violate the required TAD time.

3: Outside the recommended TAD time.

4: The ADC clock period (TAD) and total ADC conversion time can be minimized when the ADC clock is derived from the system clock FOSC. However, the ADCRC oscillator source must be used when conversions are to be performed with the device in Sleep mode.

FIGURE 22-2: ANALOG-TO-DIGITAL CONVERSION TAD CYCLES



22.1.5 INTERRUPTS

The ADC module allows for the ability to generate an interrupt upon completion of an Analog-to-Digital conversion. The ADC Interrupt Flag is the ADIF bit in the PIR1 register. The ADC Interrupt Enable is the ADIE bit in the PIE1 register. The ADIF bit must be cleared in software.

Note 1:	The ADIF bit is set at the completion of
	every conversion, regardless of whether
	or not the ADC interrupt is enabled.

2: The ADC operates during Sleep only when the ADCRC oscillator is selected.


This interrupt can be generated while the device is operating or while in Sleep. If the device is in Sleep, the interrupt will wake-up the device. Upon waking from Sleep, the next instruction following the SLEEP instruction is always executed. If the user is attempting to wake-up from Sleep and resume in-line code execution, the ADIE bit of the PIE1 register and the PEIE bit of the INTCON register must both be set and the GIE bit of the INTCON register must be cleared. If all three of these bits are set, the execution will switch to the Interrupt Service Routine (ISR).

22.1.6 RESULT FORMATTING

The 10-bit ADC conversion result can be supplied in two formats, left justified or right justified. The ADFM bit of the ADCON1 register controls the output format.

Figure 22-3 shows the two output formats.

FIGURE 22-3: 10-BIT ADC CONVERSION RESULT FORMAT



22.2 ADC Operation

22.2.1 STARTING A CONVERSION

To enable the ADC module, the ADON bit of the ADCON0 register must be set to a '1'. Setting the GO/DONE bit of the ADCON0 register to a '1' will start the Analog-to-Digital conversion.

Note:	The GO/DONE bit will not be set in the
	same instruction that turns on the ADC.
	Refer to Section 22.2.5 "ADC Conver-
	sion Procedure".

22.2.2 COMPLETION OF A CONVERSION

When the conversion is complete, the ADC module will:

- Clear the GO/DONE bit
- Set the ADIF Interrupt Flag bit
- Update the ADRESH and ADRESL registers with new conversion result

Note: A device Reset forces all registers to their Reset state. Thus, the ADC module is turned off and any pending conversion is terminated.

22.2.3 ADC OPERATION DURING SLEEP

The ADC module can operate during Sleep. This requires the ADC clock source to be set to the ADCRC option. When the ADCRC oscillator source is selected, the ADC waits one additional instruction before starting the conversion. This allows the SLEEP instruction to be executed, which can reduce system noise during the conversion. If the ADC interrupt is enabled, the device will wake-up from Sleep when the conversion completes. If the ADC interrupt is disabled, the ADC module is turned off after the conversion completes, although the ADON bit remains set.

When the ADC clock source is something other than ADCRC, a SLEEP instruction causes the present conversion to be aborted and the ADC module is turned off, although the ADON bit remains set.

Note: The auto-conversion feature is not available while the device is in Sleep mode.

22.2.4 AUTO-CONVERSION TRIGGER

The Auto-conversion Trigger allows periodic ADC measurements without software intervention. When a rising edge of the selected source occurs, the GO/DONE bit is set by hardware.

The Auto-conversion Trigger source is selected with the ADACT<4:0> bits of the ADACT register.

See Table 22-2 for auto-conversion sources.

TABLE 22-2: ADC AUTO-CONVERSION TABLE

Source Peripheral	Description
TMR0	Timer0 Overflow condition
TMR1	Timer1 Overflow condition
TMR3	Timer3 Overflow condition
TMR5	Timer5 Overflow condition
TMR2	Match between Timer2 and PR2
TMR4	Match between Timer4 and PR4
TMR6	Match between Timer6 and PR6
C1	Comparator C1 output
C2	Comparator C2 output
CLC1	CLC1 output
CLC2	CLC2 output
CLC3	CLC3 output
CLC4	CLC4 output
CCP1	CCP1 output
CCP2	CCP2 output
CCP3	CCP3 output
CCP4	CCP4 output

22.2.5 ADC CONVERSION PROCEDURE

This is an example procedure for using the ADC to perform an Analog-to-Digital conversion:

- 1. Configure Port:
 - Disable pin output driver (Refer to the TRIS register)
 - Configure pin as analog (Refer to the ANSEL register)
- 2. Configure the ADC module:
 - Select ADC conversion clock
 - Select voltage reference
 - Select ADC input channel
 - Turn on ADC module
- 3. Configure ADC interrupt (optional):
 - Clear ADC interrupt flag
 - Enable ADC interrupt
 - Enable peripheral interrupt
 - Enable global interrupt⁽¹⁾
- 4. Wait the required acquisition time⁽²⁾.
- 5. Start conversion by setting the GO/DONE bit.
- 6. Wait for ADC conversion to complete by one of the following:
 - Polling the GO/DONE bit
 - Waiting for the ADC interrupt
- 7. Read ADC Result.
- 8. Clear the ADC interrupt flag (required if interrupt is enabled).
 - **Note 1:** The global interrupt can be disabled if the user is attempting to wake-up from Sleep and resume in-line code execution.
 - 2: Refer to Section 22.3 "ADC Acquisition Requirements".

EXAMPLE 22-1: ADC CONVERSION

;This code block configures the ADC ; for polling, Vdd and Vss references, ADCRC ;oscillator and ANO input. ;Conversion start & polling for completion ; are included. BANKSEL ADCON1 B'11110000' MOVLW ;Right justify, ADCRC ;oscillator MOVWF ADCON1 ;Vdd and Vss Vref BANKSEL TRISA TRISA,0 ;Set RA0 to input BSF BANKSEL ANSELA ; ;Set RAO to analog BSF ANSELA,0 BANKSEL ADCON0 ; MOVLW B'00000001' ;Select channel ANO MOVWF ADCON0 ;Turn ADC On SampleTime CALL ;Acquisiton delay BSF ADCON0, ADGO ;Start conversion ADCON0, ADGO ; Is conversion done? BTFSC GOTO \$-1 ;No, test again ADRESH BANKSEL ; MOVF ADRESH,W ;Read upper 2 bits MOVWF RESULTHI ;store in GPR space BANKSEL ADRESL MOVF ADRESL,W ;Read lower 8 bits MOVWF RESULTLO ;Store in GPR space

22.3 **ADC Acquisition Requirements**

For the ADC to meet its specified accuracy, the charge holding capacitor (CHOLD) must be allowed to fully charge to the input channel voltage level. The Analog Input model is shown in Figure 22-4. The source impedance (Rs) and the internal sampling switch (Rss) impedance directly affect the time required to charge the capacitor CHOLD. The sampling switch (Rss) impedance varies over the device voltage (VDD), refer to Figure 22-4. The maximum recommended impedance for analog sources is 10 k Ω .

As the source impedance is decreased, the acquisition time may be decreased. After the analog input channel is selected (or changed), an ADC acquisition must be done before the conversion can be started. To calculate the minimum acquisition time, Equation 22-1 may be used. This equation assumes that 1/2 LSb error is used (1,024 steps for the ADC). The 1/2 LSb error is the maximum error allowed for the ADC to meet its specified resolution.

EQUATION 22-1: ACQUISITION TIME EXAMPLE

Assumptions: Temperature =
$$50^{\circ}C$$
 and external impedance of $10k\Omega 5.0V VDD$
 $TACQ = Amplifier Settling Time + Hold Capacitor Charging Time + Temperature Coefficient$
 $= TAMP + TC + TCOFF$
 $= 2\mu s + TC + [(Temperature - 25^{\circ}C)(0.05\mu s/^{\circ}C)]$
The value for TC can be approximated with the following equations:
 $V_{APPLIED}\left(1 - \frac{1}{(2^{n+1}) - 1}\right) = V_{CHOLD}$;[1] VCHOLD charged to within 1/2 lsb

$$V_{APPLIED}\left(1-e^{\frac{-TC}{RC}}\right) = V_{CHOLD}$$

;[2] VCHOLD charge response to VAPPLIED

$$V_{APPLIED}\left(1-e^{\frac{-Tc}{RC}}\right) = V_{APPLIED}\left(1-\frac{1}{(2^{n+1})-1}\right) \quad (combining [1] and [2])$$

Note: Where n = number *of bits of the ADC.*

Solving for TC:

$$TC = -C_{HOLD}(RIC + RSS + RS) \ln(1/2047)$$

= $-10pF(1k\Omega + 7k\Omega + 10k\Omega) \ln(0.0004885)$
= $1.37\mu s$

Therefore:


$$TACQ = 2\mu s + 892ns + [(50^{\circ}C - 25^{\circ}C)(0.05\mu s/^{\circ}C)]$$

= 4.62\mu s


Note 1: The reference voltage (VREF) has no effect on the equation, since it cancels itself out.

- 2: The charge holding capacitor (CHOLD) is not discharged after each conversion.
- **3:** The maximum recommended impedance for analog sources is 10 k Ω . This is required to meet the pin leakage specification.

PIC16(L)F18326/18346







22.4 Register Definitions: ADC Control

REGISTER 22-1: ADCON0: ADC CONTROL REGISTER 0

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
		CHS<	:5:0>			GO/DONE	ADON
pit 7							bit
o a o a d i							
Legend:						(0)	
R = Readable		W = Writable b		•	ented bit, read a		
u = Bit is unc	hanged	x = Bit is unkno	wn	-n/n = Value at	POR and BOR/	Value at all other	Resets
'1' = Bit is set	t	ʻ0' = Bit is clear	ed				
bit 7-2	CHS<5:0>:	Analog Channel Se	lect bits				
	111111 =	FVR (Fixed Voltag					
	111110 =	DAC1 output ⁽¹⁾					
	111101 =	Temperature Indic	ator ⁽³⁾				
	111100 =	Vss					
	111011 =	Reserved. No cha	nnel connected				
	•						
	010111 =	ANC7 ⁽⁴⁾					
	010110 =	ANC6 ⁽⁴⁾					
	010101 =	ANC5					
	010100 =	ANC4					
	010011 =	ANC3					
	010010 =	ANC2					
	010001 =	ANC1					
	010000 =	ANCO					
	001111 =	ANB7 ⁽⁴⁾ ANB6 ⁽⁴⁾					
	001110 = 001101 =	ANB5 ⁽⁴⁾					
	001101 =	ANB4 ⁽⁴⁾					
	001011 =	Reserved. No cha	nnel connected				
	•			•			
	•						
	•						
	000101 =	ANA5					
	000100 =	ANA4					
	000011 =	Reserved. No cha	nnel connected				
	000010 =	ANA2					
	000001 = 000000 =	ANA1 ANA0					
bit 1		ADC Conversion St					
		version cycle in pro					
		s automatically clean version completed			conversion has	completed.	
bit 0	ADON: ADO	Enable bit					
-	1 = ADC is e						
		lisabled and consur	nes no operatir	ng current			
		"5-bit Digital-to-A				ormation.	
		"Fixed Voltage R					
		"Temperature Inc	licator Module	" tor more informa	ation.		
4 : F	PIC16(L)F18346	only.					

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	U-0	R/W-0/0	R/W-0/0	R/W-0/0		
ADFM		ADCS<2:0>		—	ADNREF	ADPRE	F<1:0>		
bit 7							bit (
Logondy									
Legend: R = Readabl	o hit	W = Writable	hit		monted hit read	l aa 'O'			
				•	emented bit, read		ath an Daaata		
u = Bit is und	•	x = Bit is unkr		-n/n = value	at POR and BO	R/value at all o	olner Resels		
'1' = Bit is se	t	'0' = Bit is clea	ared						
bit 7	1 = Right ju loaded.	tified. Six Least	Significant bi		H are set to '0' w . are set to '0' w				
bit 6-4	ADCS<2:0>: ADC Conversion Clock Select bits 111 = ADCRC (dedicated RC oscillator) 110 = Fosc/64 101 = Fosc/16 100 = Fosc/4 011 = ADCRC (dedicated RC oscillator) 010 = Fosc/32 001 = Fosc/8 000 = Fosc/2								
bit 3	Unimpleme	nted: Read as '	כ'						
bit 2	ADNREF: A/D Negative Voltage Reference Configuration bit When ADON = 0, all multiplexer inputs are disconnected. 0 = VREF- is connected to AVss 1 = VREF- is connected to external VREF-								
bit 1-0	ADPREF<1:0>: ADC Positive Voltage Reference Configuration bits 11 = VREF+ is connected to internal Fixed Voltage Reference (FVR) module ⁽¹⁾ 10 = VREF+ is connected to external VREF+ pin ⁽¹⁾ 01 = Reserved 00 = VREF+ is connected to VDD								

REGISTER 22-2: ADCON1: ADC CONTROL REGISTER 1

Note 1: When selecting the VREF+ pin as the source of the positive reference, be aware that a minimum voltage specification exists. See Table 35-13 for details.

U-0	U-0	0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
—	_		—			ADACT<4:0>		
bit 7			•					bit
Legend:								
R = Readabl	e bit		W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
u = Bit is und	changed		x = Bit is unkr	nown	-n/n = Value a	at POR and BC	R/Value at all	other Resets
'1' = Bit is set			'0' = Bit is cle	ared				
bit 7-5	Unimp	leme	ented: Read as '	0'				
bit 4-0	-		0>: Auto-Conver		election bits ⁽¹⁾			
	1111	=	CCP4	55				
	1110	=	CCP3					
	1101	=	CCP2					
	1100	=	CCP1					
	1011	=	CLC4					
	1010	=	CLC3					
	1001	=	CLC2					
	1000	=	CLC1					
	0111	=	Comparator C2	2				
	0110	=	Comparator C1	1				
	0101	=	Timer2-PR2 m	atch				
	0100	=	Timer1 overflov					
	0011	=	Timer0 overflov	_N (2)				
	0010	=	Timer6-PR6 m	atch				
	0001	=	Timer4-PR4 m	atch				
	0000	=	No auto-conve		elected			
	10000	=	Timer3 overflov	_N (2)				
	10001	-	Timer5 overflov	_{^/} (2)				

REGISTER 22-3: ADACT: A/D AUTO-CONVERSION TRIGGER

2: Trigger corresponds to when the peripheral's interrupt flag is set.

REGISTER 22-4: ADRESH: ADC RESULT REGISTER HIGH (ADRESH) ADFM = 0

R/W-x/u R/W-x/u <t< th=""><th></th></t<>	
	-x/u R/W-x/u
bit 7	
	bit 0
Legend:	
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'	
u = Bit is unchanged x = Bit is unknown -n/n = Value at POR and BOR/Value	at all other Resets
'1' = Bit is set '0' = Bit is cleared	

bit 7-0 **ADRES<9:2>**: ADC Result Register bits Upper eight bits of 10-bit conversion result

REGISTER 22-5: ADRESL: ADC RESULT REGISTER LOW (ADRESL) ADFM = 0

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
ADRES<1:0>		—	—	—	—	—	—
bit 7							bit 0

Legend:

Logona.		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-6 ADRES<1:0>: ADC Result Register bits

Lower two bits of 10-bit conversion result

bit 5-0 **Reserved**: Do not use.

	R/W-x/u	R/W-x/u									
		—	—	—	—	—	ADRES<9:8>				
k	oit 7							bit 0			

REGISTER 22-6: ADRESH: ADC RESULT REGISTER HIGH (ADRESH) ADFM = 1

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-2 Reserved: Do not use.

bit 1-0	ADRES<9:8>: ADC Result Register bits
	Upper two bits of 10-bit conversion result

REGISTER 22-7: ADRESL: ADC RESULT REGISTER LOW (ADRESL) ADFM = 1

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	
ADRES<7:0>								
bit 7	bit 7 bit 0							

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 ADRES<7:0>: ADC Result Register bits Lower eight bits of 10-bit conversion result

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page	
INTCON	GIE	PEIE	_	—	_	_	_	INTEDG	100	
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102	
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107	
TRISA	—	—	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143	
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_	_	_	149	
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155	
ANSELA	—	_	ANSA5	ANSA4		ANSA2	ANSA1	ANSA0	144	
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_	_	_	150	
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157	
ADCON0	CHS<5:0> GO/DONE ADON								244	
ADCON1	ADFM	ADCS<2:0>				ADNREF	ADPREI	F<1:0>	245	
ADACT	—	_		ADACT<4:0>					246	
ADRESH	ADRESH<7:0>								247	
ADRESL	ADRESL<7:0>								247	
FVRCON	FVREN	FVRRDY	TSEN	TSRNG	NG CDAFVR<1:0> ADFVR<1:0>				180	
DAC1CON1					DAC1R<4:0>					
OSCSTAT1	EXTOR	HFOR		LFOR	SOR	ADOR		PLLR	91	

 TABLE 22-3:
 SUMMARY OF REGISTERS ASSOCIATED WITH ADC

Legend: -= unimplemented read as '0'. Shaded cells are not used for the ADC module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

23.0 NUMERICALLY CONTROLLED OSCILLATOR (NCO1) MODULE

The Numerically Controlled Oscillator (NCO1) module is a timer that uses the overflow from the addition of an increment value to divide the input frequency. The advantage of the addition method over simple counter-driven timer is that the output frequency resolution does not vary with the divider value. The NCO1 is most useful for applications that require frequency accuracy and fine resolution at a fixed duty cycle.

Features of the NCO1 include:

- 20-bit increment function
- Fixed Duty Cycle (FDC) mode
- Pulse Frequency (PF) mode
- Output pulse-width control
- · Multiple clock input sources
- Output polarity control
- Interrupt capability

Figure 23-1 is a simplified block diagram of the NCO1 module.




FIGURE 23-1: NUMERICALLY CONTROLLED OSCILLATOR MODULE SIMPLIFIED BLOCK DIAGRAM

Note 1: The increment registers are double-buffered to allow for value changes to be made without first disabling the NCO1 module. They are shown for reference only and are not user accessible.

23.1 NCO1 Operation

The NCO1 operates by repeatedly adding a fixed value to an accumulator. Additions occur at the input clock rate. The accumulator will overflow with a carry periodically, which is the raw NCO1 output (NCO_overflow). This effectively reduces the input clock by the ratio of the addition value to the maximum accumulator value. See Equation 23-1.

The NCO1 output can be further modified by stretching the pulse or toggling a flip-flop. The modified NCO1 output is then distributed internally to other peripherals and can optionally be output to a pin. The accumulator overflow also generates an interrupt (NCO_interrupt).

The NCO1 period changes in discrete steps to create an average frequency.

EQUATION 23-1: NCO1 OPERATION

 $FOVERFLOW = \frac{NCO1 \ Clock \ Frequency \times Increment \ Value}{2^{20}}$

23.1.1 NCO1 CLOCK SOURCES

Clock sources available to the NCO1 include:

- HFINTOSC
- Fosc
- LC1_out

The NCO1 clock source is selected by configuring the N1CKS<1:0> bits in the NCO1CLK register.

23.1.2 ACCUMULATOR

The accumulator is a 20-bit register. Read and write access to the accumulator is available through three registers:

- NCO1ACCL
- NCO1ACCH
- NCO1ACCU

23.1.3 ADDER

The NCO1 adder is a full adder, which operates independently from the system clock. The addition of the previous result and the increment value replaces the accumulator value on the rising edge of each input clock.

23.1.4 INCREMENT REGISTERS

The increment value is stored in three registers making up a 20-bit increment. In order of LSB to MSB they are:

- NCO1INCL
- NCO1INCH
- NCO1INCU

When the NCO1 module is enabled, the NCO1INCU and NCO1INCH registers must be written first, then the NCO1INCL register. Writing to the NCO1INCL register initiates the increment buffer registers to be loaded simultaneously on the second rising edge of the NCO_clk signal.

The registers are readable and writable. The increment registers are double-buffered to allow value changes to be made without first disabling the NCO1 module.

When the NCO1 module is disabled, the increment buffers are loaded immediately after a write to the increment registers.

Note: The increment buffer registers are not user-accessible.

23.2 Fixed Duty Cycle (FDC) Mode

In Fixed Duty Cycle (FDC) mode, every time the accumulator overflows (NCO_overflow), the output is toggled. This provides a 50% duty cycle with a constant frequency, provided that the increment value remains constant.

The FDC frequency can be calculated using Equation 23-2. The FDC frequency is half of the overflow frequency since it takes two overflow events to generate one FDC clock period. For more information, see Figure 23-2.

EQUATION 23-2: FDC FREQUENCY

$$F_{fdc} = F_{overflow}/2$$

The FDC mode is selected by clearing the N1PFM bit in the NCO1CON register.

23.3 Pulse Frequency (PF) Mode

In Pulse Frequency (PF) mode, every time the accumulator overflows (NCO_overflow), the output becomes active for one or more clock periods. Once the clock period expires, the output returns to an inactive state. This provides a pulsed output. The output becomes active on the rising clock edge immediately following the overflow event. For more information, see Figure 23-2.

The value of the active and inactive states depends on the polarity bit, N1POL, in the NCO1CON register.

The PF mode is selected by setting the N1PFM bit in the NCO1CON register.

23.3.1 OUTPUT PULSE-WIDTH CONTROL

When operating in PF mode, the active state of the output can vary in width by multiple clock periods. Various pulse widths are selected with the N1PWS<2:0> bits in the NCO1CLK register.

When the selected pulse width is greater than the accumulator overflow time frame, the output of the NCO1 does not toggle.


23.4 Output Polarity Control

The last stage in the NCO1 module is the output polarity. The N1POL bit in the NCO1CON register selects the output polarity. Changing the polarity while the interrupts are enabled will cause an interrupt for the resulting output transition.

The NCO1 output can be used internally by source code or other peripherals. Accomplish this by reading the N1OUT (read-only) bit of the NCO1CON register.

The NCO1 output signal is available to the following peripherals:

• CWG



C16(L)F18326/18346

U

23.5 Interrupts

When the accumulator overflows (NCO_overflow), the NCO1 Interrupt Flag bit, NCO1IF, of the PIR2 register is set. To enable the interrupt event (NCO_interrupt), the following bits must be set:

- The N1EN bit of the NCO1CON register
- The NCO1IE bit of the PIE2 register
- The PEIE bit of the INTCON register
- The GIE bit of the INTCON register

The interrupt must be cleared by software by clearing the NCO1IF bit in the Interrupt Service Routine.

23.6 Effects of a Reset

All of the NCO1 registers are cleared to zero as the result of a Reset.

23.7 Operation in Sleep

The NCO1 module operates independently from the system clock and will continue to run during Sleep, provided that the clock source selected remains active.

The HFINTOSC remains active during Sleep when the NCO1 module is enabled and the HFINTOSC is selected as the clock source, regardless of the system clock source selected.

In other words, if the HFINTOSC is simultaneously selected as the system clock and the NCO1 clock source, when the NCO1 is enabled, the CPU will go Idle during Sleep, but the NCO1 will continue to operate and the HFINTOSC will remain active.

This will have a direct effect on the Sleep mode current.

23.8 NCO1 Control Registers

R/W-0/0	U-0	R-0/0	R/W-0/0	U-0	U-0	U-0	R/W-0/0
N1EN		N1OUT	N1POL				N1PFM
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, read	l as '0'	
u = Bit is unch	nanged	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all	other Resets
'1' = Bit is set		'0' = Bit is cle	ared				
bit 7 bit 6 bit 5	0 = NCO1 mc Unimplemen N1OUT: NCC	odule is enable odule is disable I ted : Read as ' 01 Output bit current output v	o'	CO1 module			
bit 4		01 Polarity bit tput signal is ir tput signal is n					
bit 3-1	Unimplemen	ted: Read as '	0'				
bit 0	1 = NCO1 op	01 Output Divid erates in Pulse erates in Fixed	Frequency m	ode ode, divide by 3	2		

REGISTER 23-1: NCO1CON: NCO1 CONTROL REGISTER

R/W-0/0) R/W-0/0	R/W-0/0	U-0	U-0	U-0	R/W-0/0	R/W-0/0
	N1PWS<2:0>					N1CK	S<1:0>
bit 7							bit (
Legend:							
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'							
u = Bit is u	unchanged	x = Bit is unkr	iown	-n/n = Value a	t POR and BO	R/Value at all o	other Resets
'1' = Bit is	set	'0' = Bit is clea	ared				
bit 4-2	110 = NCO 101 = NCO 100 = NCO 011 = NCO 010 = NCO 001 = NCO 000 = NCO	1 output is activ 1 output is activ	e for 64 input e for 32 input e for 16 input e for 8 input c e for 4 input c e for 2 input c e for 1 input c	clock periods clock periods clock periods lock periods lock periods lock periods			
Note 1: 2:	N1CKS<1:0> 11 =Reserve 10 = CLC1OU 01 = Fosc	: NCO1 Clock s d JT DSC (16 MHz) only when opera	Source Select ating in Pulse	Frequency mod		does not togg	le.

REGISTER 23-2: NCO1CLK: NCO1 INPUT CLOCK CONTROL REGISTER

REGISTER 23-3: NCO1ACCL: NCO1 ACCUMULATOR REGISTER – LOW BYTE

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0				
	NCO1ACC<7:0>										
bit 7							bit 0				
Legend:											
R = Readable	bit	W = Writable I	oit	U = Unimplen	nented bit, read	d as '0'					
u = Bit is unch	u = Bit is unchanged x = Bit is unknown -n/n = Value at POR and B0				at POR and BC	OR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is clea	red								

bit 7-0 NCO1ACC<7:0>: NCO1 Accumulator, low byte

REGISTER 23-4: NCO1ACCH: NCO1 ACCUMULATOR REGISTER – HIGH BYTE

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0			
NCO1ACC<15:8>										
bit 7							bit 0			
Legend:										
R = Readable bi	t	W = Writable bit		U = Unimplemented bit, read as '0'						
u = Bit is unchan	nged	x = Bit is unknown -n/n = Value at POR and BOR/Value at all of				her Resets				
'1' = Bit is set		'0' = Bit is cleare	d							

bit 7-0 NCO1ACC<15:8>: NCO1 Accumulator, high byte

REGISTER 23-5: NCO1ACCU: NCO1 ACCUMULATOR REGISTER – UPPER BYTE⁽¹⁾

U-0	U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
—	—	—	_	NCO1ACC<19:16>					
bit 7							bit 0		

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 Unimplemented: Read as '0'

bit 3-0 NCO1ACC<19:16>: NCO1 Accumulator, upper byte

Note 1: The accumulator spans registers NCO1ACCU:NCO1ACCH:NCO1ACCL. The 24 bits are reserved but not all are used. This register updates in real-time, asynchronously to the CPU; there is no provision to ensure atomic access to this 24-bit space using an 8-bit bus. Writing to this register while the module is operating will produce undefined results.

REGISTER 23-6: NCO1INCL^(1,2): NCO1 INCREMENT REGISTER – LOW BYTE

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-1/1		
NCO1INC<7:0>									
bit 7 bit									

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 NCO1INC<7:0>: NCO1 Increment, low byte

Note 1: The logical increment spans NCO1INCU:NCO1INCH:NCO1INCL.

2: NCO1INC is double-buffered as INCBUF; INCBUF is updated on the next falling edge of NCOCLK after writing to NCO1INCL;NCO1INCU and NCO1INCH must be written prior to writing NCO1INCL.

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0			
NCO1INC<15:8>										
bit 7	bit 7 bit 0									
Legend:										
R = Readable	bit	W = Writable b	oit	U = Unimplen	nented bit, read	l as '0'				
u = Bit is unch	anged	x = Bit is unkn	own	-n/n = Value at POR and BOR/Value at all other Res						
'1' = Bit is set		'0' = Bit is clea	ired							

REGISTER 23-7: NCO1INCH⁽¹⁾: NCO1 INCREMENT REGISTER – HIGH BYTE

bit 7-0 NCO1INC<15:8>: NCO1 Increment, high byte

Note 1: The logical increment spans NCO1INCU:NCO1INCH:NCO1INCL.

REGISTER 23-8: NCO1INCU⁽¹⁾: NCO1 INCREMENT REGISTER – UPPER BYTE

U-0	U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	
				NC01INC<19:16>				
bit 7							bit 0	

Legend:

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 Unimplemented: Read as '0'

bit 3-0 NCO1INC<19:16>: NCO1 Increment, upper byte

Note 1: The logical increment spans NCO1INCU:NCO1INCH:NCO1INCL.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	_	-	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	_	_	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	—	—	_	—	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	—	—	—	—	150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103
INTCON	GIE	PEIE	_	_	_	_	_	INTEDG	100
NCO1CON	N1EN	_	N1OUT	N1POL	_	_	_	N1PFM	256
NCO1CLK		N1PWS<2:0)>	_			N1CK	S<1:0>	257
NCO1ACCL			NC	O1ACC <7	:0>				257
NCO1ACCH			NC	01ACC <15	5:8>				258
NCO1ACCU	_					NCO1AC	C <19:16>	•	258
NCO1INCL			N	CO1INC<7:	0>				258
NCO1INCH			NC	O1INC<15	:8>				259
NCO1INCU	_		_			NCO1IN	C<19:16>		259
CWG1DAT	_		_	_		DAT	<3:0>		215
MDSRC	—	_	_			MDM	S<3:0>		272
MDCARH	_	MDCHPOL	MDCHSYNC	_		MDCH	H<3:0>		273
MDCARL	_	MDCLPOL	MDCLSYNC	_		MDCI	L<3:0>		274
CCPxCAP	_	_	_			CCPxC	TS<3:0>		310

TABLE 23-1 :	SUMMARY OF REGISTERS ASSOCIATED WITH NCO1

Legend: -= unimplemented read as '0'. Shaded cells are not used for NCO1 module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

24.0 5-BIT DIGITAL-TO-ANALOG CONVERTER (DAC1) MODULE

The Digital-to-Analog Converter supplies a variable voltage reference, ratiometric with the input source, with 32 selectable output levels.

The input of the DAC can be connected to:

- External VREF pins
- VDD supply voltage
- FVR (Fixed Voltage Reference)

The output of the DAC can be configured to supply a reference voltage to the following:

- Comparator positive input
- ADC input channel
- DAC1OUT pin

The Digital-to-Analog Converter (DAC) is enabled by setting the DAC1EN bit of the DAC1CON0 register.

EQUATION 24-1: DAC OUTPUT VOLTAGE

24.1 Output Voltage Selection

The DAC has 32 voltage level ranges. The 32 levels are set with the DAC1R<4:0> bits of the DAC1CON1 register.

The DAC output voltage is determined by Equation 24-1:

$$V_{OUT} = \left((V_{SOURCE+} - V_{SOURCE-}) \times \frac{DACIR\langle 4:0 \rangle}{2^5} \right) + (V_{SOURCE-})$$
$$V_{SOURCE+} = V_{DD} \text{ or } V_{REF+} \text{ or } FVR$$
$$V_{SOURCE-} = V_{SS} \text{ or } V_{REF-}$$

24.2 Ratiometric Output Level

The DAC output value is derived using a resistor ladder with each end of the ladder tied to a positive and negative voltage reference input source. If the voltage of either input source fluctuates, a similar fluctuation will result in the DAC output value.

The value of the individual resistors within the ladder can be found in Table 35-15.

24.3 DAC Voltage Reference Output

The DAC voltage can be output to the DAC1OUT pin by setting the DAC1OE bit of the DAC1CON0 register. Selecting the DAC reference voltage for output on the DAC1OUT pin automatically overrides the digital output buffer and digital input threshold detector functions, it disables the weak pull-up and the constant-current drive function of that pin. Reading the DAC1OUT pin when it has been configured for DAC reference voltage output will always return a '0'.

Due to the limited current drive capability, a buffer must be used on the DAC voltage reference output for external connections to the DAC1OUT pin. Figure 24-2 shows an example buffering technique.





FIGURE 24-2: VOLTAGE REFERENCE OUTPUT BUFFER EXAMPLE



24.4 Operation During Sleep

The DAC continues to function during Sleep. When the device wakes up from Sleep through an interrupt or a Watchdog Timer time-out, the contents of the DAC1CON0 register are not affected.

24.6 Register Definitions: DAC Control

24.5 Effects of a Reset

A device Reset affects the following:

- DAC is disabled.
- DAC output voltage is removed from the DAC10UT pin.
- The DAC1R<4:0> range select bits are cleared.

REGISTER 24-1: DACCON0: VOLTAGE REFERENCE CONTROL REGISTER 0

R/W-0/0	U-0	R/W-0/0	U-0	R/W-0/0	R/W-0/0	U-0	R/W-0/0
DAC1EN	—	DAC10E	—	DAC1PSS<1:0>		—	DAC1NSS
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7	DAC1EN: DAC1 Enable bit 1 = DAC is enabled 0 = DAC is disabled
bit 6	Unimplemented: Read as '0'
bit 5	DAC1OE: DAC1 Voltage Output 1 Enable bit 1 = DAC voltage level is output on the DAC1OUT pin 0 = DAC voltage level is disconnected from the DAC1OUT pin
bit 4	Unimplemented: Read as '0'
bit 3-2	DAC1PSS<1:0>: DAC1 Positive Source Select bits 11 = Reserved, do not use 10 = FVR output 01 = VREF+ pin 00 = VDD
bit 1	Unimplemented: Read as '0'
bit 0	DAC1NSS: DAC1 Negative Source Select bits 1 = VREF- pin 0 = Vss

REGISTER 24-2:	DACCON1: VOLTAGE REFERENCE CONTROL REGISTER 1
----------------	---

			-	-					
U-0	U-0	U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
_	_	—		DAC1R<4:0>					
bit 7			•				bit 0		
Legend:									
R = Readable bit W = Writable bit			bit	U = Unimplemented bit, read as '0'					
u = Bit is unchanged x = Bit is unknown		nown	-n/n = Value at POR and BOR/Value at all other Resets						
'1' = Bit is set		'0' = Bit is cle	eared						

bit 7-5 Unimplemented: Read as '0'

bit 4-0 DAC1R<4:0>: DAC1 Voltage Output Select bits VOUT = (VSRC+ - VSRC-)*(DAC1R<4:0>/32) + VSRC

TABLE 24-1: SUMMARY OF REGISTERS ASSOCIATED WITH THE DAC1 MODULE

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on page
DACCON0	DAC1EN	—	DAC10E	— DAC1PSS<1:0>			—	DAC1NSS	263
DACCON1	_	_	_	— DAC1R<4:0>					264
CMxCON1	CxINTP	CxINTN	CxPCH<2:0>			CxNCH<2:0>			197
ADCON0		CHS<5:0> GO/DONE ADON						244	

Legend: — = Unimplemented location, read as '0'. Shaded cells are not used with the DAC module.

25.0 DATA SIGNAL MODULATOR (DSM) MODULE

The Data Signal Modulator (DSM) is a peripheral which allows the user to mix a data stream, also known as a modulator signal, with a carrier signal to produce a modulated output.

Both the carrier and the modulator signals are supplied to the DSM module either internally from the output of a peripheral, or externally through an input pin.

The modulated output signal is generated by performing a logical "AND" operation of both the carrier and modulator signals and then provided to the MDOUT pin.

The carrier signal is comprised of two distinct and separate signals. A carrier high (CARH) signal and a carrier low (CARL) signal. During the time in which the modulator (MOD) signal is in a logic high state, the DSM mixes the carrier high signal with the modulator signal. When the modulator signal is in a logic low state, the DSM mixes the carrier low signal with the modulator signal.


Using this method, the DSM can generate the following types of key modulation schemes:

- Frequency-Shift Keying (FSK)
- Phase-Shift Keying (PSK)
- On-Off Keying (OOK)

Additionally, the following features are provided within the DSM module:

- Carrier Synchronization
- Carrier Source Polarity Select
- Carrier Source Pin Disable
- Programmable Modulator Data
- Modulator Source Pin Disable
- Modulated Output Polarity Select
- Slew Rate Control

Figure 25-1 shows a simplified block diagram of the Data Signal Modulator peripheral.



25.1 DSM Operation

The DSM module can be enabled by setting the MDEN bit in the MDCON register. Clearing the MDEN bit in the MDCON register, disables the DSM module by automatically switching the carrier high and carrier low signals to the Vss signal source. The modulator signal source is also switched to the MDBIT in the MDCON register. This not only assures that the DSM module is inactive, but that it is also consuming the least amount of current.

The values used to select the carrier high, carrier low, and modulator sources held by the Modulation Source, Modulation High Carrier, and Modulation Low Carrier control registers are not affected when the MDEN bit is cleared and the DSM module is disabled. The values inside these registers remain unchanged while the DSM is inactive. The sources for the carrier high, carrier low and modulator signals will once again be selected when the MDEN bit is set and the DSM module is again enabled and active.

The modulated output signal can be disabled without shutting down the DSM module. The DSM module will remain active and continue to mix signals, but the output value will not be sent to the DSM pin. During the time that the output is disabled, the DSM pin will remain low. The modulated output can be disabled by clearing the MDEN bit in the MDCON register.

25.2 Modulator Signal Sources

The modulator signal can be supplied from the following sources:

- CCP1 Output
- CCP2 Output
- PWM5 Output
- PWM6 Output
- MSSP1 SDO1 (SPI mode only)
- MSSP2 SDO2 (SPI mode only)
- Comparator C1 Output
- Comparator C2 Output
- EUSART1 TX Output
- External Signal on MDMIN pin
- NCO1 Output
- CLC1 Output
- CLC2 Output
- CLC3 Output
- CLC4 Output
- MDBIT bit in the MDCON register

The modulator signal is selected by configuring the MDMS <3:0> bits in the MDSRC register.

25.3 Carrier Signal Sources

The carrier high signal and carrier low signal can be supplied from the following sources:

- CCP1 Output
- CCP2 Output
- PWM5 Output
- PWM6 Output
- NCO1 Output
- · Fosc (System Clock)
- HFINTOSC
- CLC1 Output
- CLC2 Output
- CLC3 Output
- CLC4 Output
- CLKR
- External Signal on MDCIN1 pin
- External Signal on MDCIN2 pin
- Vss

The carrier high signal is selected by configuring the MDCH <3:0> bits in the MDCARH register. The carrier low signal is selected by configuring the MDCL <3:0> bits in the MDCARL register.

25.4 Carrier Synchronization

During the time when the DSM switches between carrier high and carrier low signal sources, the carrier data in the modulated output signal can become truncated. To prevent this, the carrier signal can be synchronized to the modulator signal. When the modulator signal transitions away from the synchronized carrier, the unsynchronized carrier source is immediately active, while the synchronized carrier remains active until its next falling edge. When the modulator signal transitions back to the synchronized carrier, the unsynchronized carrier is immediately disabled, and the modulator waits until the next falling edge of the synchronized carrier before the synchronized carrier becomes active.

Synchronization is enabled separately for the carrier high and carrier low signal sources. Synchronization for the carrier high signal is enabled by setting the MDCHSYNC bit in the MDCARH register. Synchronization for the carrier low signal is enabled by setting the MDCLSYNC bit in the MDCARL register.

Figure 25-1 through Figure 25-6 show timing diagrams of using various synchronization methods.

PIC16(L)F18326/18346




FIGURE 25-3: NO SYNCHRONIZATION (MDSHSYNC = 0, MDCLSYNC = 0)





FIGURE 25-4: CARRIER HIGH SYNCHRONIZATION (MDSHSYNC = 1, MDCLSYNC = 0)

Carrier High (CARH)		- - -
Carrier Low (CARL)	mmmmmm	, , , ,
Modulator (MOD)		-
MDCHSYNC = 1 MDCLSYNC = 0		, , ,
Active Carrier State	CARH / both CARL / CARH / both CARL	- - -

PIC16(L)F18326/18346

FIGURE 25-5:	CARRIER LOW SYNCHRONIZATION (MDSHSYNC = 0, MDCLSYNC = 1)
Carrier High (CARH)	
Carrier Low (CARL)	
Modulator (MOD)	
MDCHSYNC = 0 MDCLSYNC = 1	
Active Carrier State -	



25.5 Carrier Source Polarity Select

The signal provided from any selected input source for the carrier high and carrier low signals can be inverted. Inverting the signal for the carrier high source is enabled by setting the MDCHPOL bit of the MDCARH register. Inverting the signal for the carrier low source is enabled by setting the MDCLPOL bit of the MDCARL register.

25.6 Programmable Modulator Data

The MDBIT of the MDCON register can be selected as the source for the modulator signal. This gives the user the ability to program the value used for modulation.

25.7 Modulated Output Polarity

The modulated output signal provided on the DSM pin can also be inverted. Inverting the modulated output signal is enabled by setting the MDOPOL bit of the MDCON register.

25.8 Slew Rate Control

The slew rate limitation on the output PORT pin can be disabled. The slew rate limitation can be removed by clearing the SLR bit of the SLRCON register associated with that pin. For example, clearing the slew rate limitation for pin RA5 would require clearing the SLRA5 bit of the SLRCONA register.

25.9 Operation in Sleep Mode

The DSM module is not affected by Sleep mode. The DSM can still operate during Sleep, if the Carrier and Modulator input sources are also still operable during Sleep.

25.10 Effects of a Reset

Upon any device Reset, the DSM module is disabled. The user's firmware is responsible for initializing the module before enabling the output. The registers are reset to their default values.

25.11 Register Definitions: Modulation Control

REGISTER Z								
R/W-0/0	U-0	U-0	R/W-0/0	R-0/0	U-0	U-0	R/W-0/0	
MDEN	—	—	MDOPOL	MDOUT	—	_	MDBIT ⁽²⁾	
bit 7	·						bit 0	
Legend:								
R = Readable bit W = Writable bit U = Unimplemented bit, read as '0'								
u = Bit is uncha	anged	x = Bit is unkr	iown	-n/n = Value	at POR and BOI	R/Value at all o	ther Resets	
'1' = Bit is set		'0' = Bit is clea	ared					
bit 7	1 = Modulato	lator Module E r module is en r module is dis	abled and mix	• • •	als			
bit 6-5	Unimplemen	ted: Read as '	כ'					
bit 4	MDOPOL: Mo	odulator Outpu	t Polarity Sele	ct bit				
		r output signal r output signal						
bit 3		ulator Output k		, i				
		current output v		odulator modu	le ⁽¹⁾			
bit 2-1		ted: Read as '						
bit 0	MDBIT: Allow	s software to n	nanually set m	odulation sou	rce input to mod	ule ⁽²⁾		
			•	•	onous from the o odulator or carrie		tes this	

REGISTER 25-1: MDCON: MODULATION CONTROL REGISTER

2: MDBIT must be selected as the modulation source in the MDSRC register for this operation.

U-0	U-0	U-0	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	
_	_	—	_		MDMS	S<3:0>		
bit 7	·			·			bit (
Legend:								
R = Readable bit W = Writable bit U = Unimplemented bit, read				l as '0'				
u = Bit is un	changed	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all o	other Resets	
'1' = Bit is se	et	'0' = Bit is cle	ared					
bit 7-4	Unimpleme	nted: Read as '	0'					
bit 3-0	•	 Modulation So 		n hits				
	1111 = CL							
	1110 = CL	•						
	1101 = CL							
	1100 = CL							
	1011 = NC							
		= EUSART1 TX output						
	1001 = MS	SP2 SDO2 outp	out					
	1000 = MS	SP1 SDO1 outp	out					
	0111 = C2	(Comparator 2)	output					
		(Comparator 1)	output					
	0101 = PW							
	0100 = PW	•						
		P2 output (PWN						
		P1 output (PWN	I Output mod	de only)				
	0001 = MD							
	0000 = MD	BLI DIT OF MDCO	JN register is	s modulation sou	lice			

REGISTER 25-2: MDSRC: MODULATION SOURCE CONTROL REGISTER

U-0	R/W-x/u	R/W-x/u	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u			
_	MDCHPOL	MDCHSYNC	_		MDCH	<3:0> ⁽¹⁾				
bit 7							bit			
Legend:										
R = Readabl	e bit	W = Writable bi	it	U = Unimpler	mented bit, read	d as '0'				
u = Bit is und	changed	x = Bit is unkno	wn	-n/n = Value a	at POR and BO	R/Value at all o	other Resets			
'1' = Bit is se	t	ʻ0' = Bit is clear	ed							
bit 7	Unimplomor	ted: Bood on 'o'								
	-	nted: Read as '0'								
bit 6		Modulator High C		-						
		 1 = Selected high carrier signal is inverted 0 = Selected high carrier signal is not inverted 								
		U								
bit 5		: Modulator High	•							
		lulator waits for a falling edge on the high time carrier signal before allowing a switch to the								
		low time carrier 0 = Modulator output is not synchronized to the high time carrier signal ⁽¹⁾								
				d to the high tim	e carrier signal	(•)				
bit 4	-	nted: Read as '0'								
bit 3-0	MDCH<3:0>	MDCH<3:0> Modulator Data High Carrier Selection bits ⁽¹⁾								
	1111 = CLC	1111 = CLC4 output								
	1110 = CLC	110 = CLC3 output								
		1 = CLC2 output								
) = CLC1 output								
	1011 = HFI	11 = HFINTOSC								
	1010 = Fos	1010 = Fosc								
		1001 = Reserved. No channel connected.								
	1000 = NC	•								
		0111 = PWM6 output								
		PWM5 output								
		P2 output (PWM								
		P1 output (PWM								
		erence clock mod	ule signal	(CLKR)						
	0010 = MD									
	0001 = MD									
	0000 = Vss									

REGISTER 25-3: MDCARH: MODULATION HIGH CARRIER CONTROL REGISTER

Note 1: Narrowed carrier pulse widths or spurs may occur in the signal stream if the carrier is not synchronized.

U-0	R/W-x/u	R/W-x/u	U-0	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
	MDCLPOL	MDCLSYNC			MDCL	<3:0> ⁽¹⁾	
bit 7	·	· · · · ·					bit
Legend:							
R = Readable	e bit	W = Writable bi	it	U = Unimpler	mented bit, read	d as '0'	
u = Bit is uncl	hanged	x = Bit is unkno	wn	-n/n = Value a	at POR and BC	R/Value at all o	other Resets
'1' = Bit is set	-	ʻ0' = Bit is clear	ed				
L:1 7	Unimulan	atad: Daad as (o)					
bit 7	-	nted: Read as '0'					
bit 6		Modulator Low C		•			
		low carrier signa					
		low carrier signa					
bit 5		: Modulator Low	-				
		or waits for a fallir	ng edge on	the low time car	rier signal befor	e allowing a sw	itch to the hig
	time car			-1 4 - 4 1 - · · · 4 · · · -		n	
		or output is not sy		a to the low time	e carrier signal	,	
bit 4	•	nted: Read as '0'					
bit 3-0	MDCL<3:0>	Modulator Data H	High Carrie	r Selection bits	(1)		
	1111 = CLC						
	1110 = CLC						
	1101 = CLC						
	1100 = CLC	•					
	1011 = HFI						
	1010 = Fos		al connect	ad			
	1001 - Res 1000 = NC	served. No chann	er connecte	eu.			
	0111 = PW						
	0110 = PW						
		P2 output (PWM)	Output mod	de onlv)			
		P1 output (PWM)					
		erence clock mod					
	0010 = MD		0	. ,			
	0.001 - MD						
	0001 = MD	CIN1PPS					

REGISTER 25-4: MDCARL: MODULATION LOW CARRIER CONTROL REGISTER

Note 1: Narrowed carrier pulse widths or spurs may occur in the signal stream if the carrier is not synchronized.

TABLE 23-1.			JISTERS AS	SOCIALE				DULAIU	
Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	_		TRISA5	TRISA4	_(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	_	_	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
SLRCONA	_	_	SLRA5	SLRA4		SLRA2	SLRA1	SLRA0	146
INLVLA	_	_	INLVLA5	INLVLA4	INLVLA3	INLVLA2	INLVLA1	INLVLA0	146
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	—	—	_	—	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_	_	—	150
SLRCONB ⁽¹⁾	SLRB7	SLRB6	SLRB5	SLRB4	_	_	_	_	152
INLVLB ⁽¹⁾	INLVLB7	INLVLB6	INLVLB5	INLVLB4	_	_	_	—	152
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
SLRCONC	SLRC7 ⁽¹⁾	SLRC6 ⁽¹⁾	SLRC5	SLRC4	SLRC3	SLRC2	SLRC1	SLRC0	158
INLVLC	INLVLC7 ⁽¹⁾	INLVLC6 ⁽¹⁾	INLVLC5	INLVLC4	INLVLC3	INLVLC2	INLVLC1	INLVLC0	159
MDCON	MDEN	_	_	MDOPOL	MDOUT	—	_	MDBIT	271
MDSRC	_	_	_	_		MDMS	\$<3:0>		272
MDCARH	_	MDCHPOL	MDCHSYNC	_		MDCH	1<3:0>		273
MDCARL		MDCLPOL	MDCLSYNC			MDCL	<3:0>		274
MDCIN1PPS	_	—	—		MDC	XIN1PPS<4	l:0>		162
MDCIN2PPS	—	—	—		MDC	N2PPS<4	l:0>		162
MDMINPPS			_		MDI	MINPPS<4	:0>		162

TABLE 25-1: SUMMARY OF REGISTERS ASSOCIATED WITH DATA SIGNAL MODULATOR MODE

Legend: — = unimplemented, read as '0'. Shaded cells are not used in the Data Signal Modulator mode.

Note 1: PIC16(L)F18346 only.

2: Unimplemented. Read as '1'.

26.0 TIMER0 MODULE

The Timer0 module is an 8/16-bit timer/counter with the following features:

- 16-bit timer/counter
- 8-bit timer/counter with programmable period
- Synchronous or asynchronous operation
- Selectable clock sources
- Programmable prescaler (independent of Watchdog Timer)
- Programmable postscaler
- Operation during Sleep mode
- Interrupt on match or overflow
- Output on I/O pin (via PPS) or to other peripherals

26.1 Timer0 Operation

Timer0 can operate as either an 8-bit timer/counter or a 16-bit timer/counter. The mode is selected with the T016BIT bit of the T0CON register.

When used with an Fosc/4 clock source, the module is a timer and increments on every instruction cycle. When used with any other clock source, the module can be used as either a timer or a counter and increments on every rising edge of the external source.

26.1.1 16-BIT MODE

In normal operation, TMR0 increments on the rising edge of the clock source. A 15-bit prescaler on the clock input gives several prescale options (see prescaler control bits, T0CKPS<3:0> in the T0CON1 register).

26.1.1.1 Timer0 Reads and Writes in 16-bit Mode

TMR0H is not the actual high byte of Timer0 in 16-bit mode. It is actually a buffered version of the real high byte of Timer0, which is neither directly readable nor writable (see Figure 26-1). TMR0H is updated with the contents of the high byte of Timer0 during a read of TMR0L. This provides the ability to read all 16 bits of Timer0 without having to verify that the read of the high and low byte was valid, due to a rollover between successive reads of the high and low byte.

Similarly, a write to the high byte of Timer0 must also take place through the TMR0H Buffer register. The high byte is updated with the contents of TMR0H when a write occurs to TMR0L. This allows all 16 bits of Timer0 to be updated at once.

26.1.2 8-BIT MODE

In normal operation, TMR0 increments on the rising edge of the clock source. A 15-bit prescaler on the clock input gives several prescale options (see prescaler control bits, T0CKPS<3:0> in the T0CON1 register).

In 8-bit mode, TMR0H no longer functions as the Timer0 high byte, but instead functions as the Period Register (PR). The value of TMR0L is compared to that of TMR0H on each clock cycle. When the two values match, the following events happen:

- TMR0_out goes high for one prescaled clock period
- TMR0L is reset
- The contents of TMR0H are copied to the period buffer

In 8-bit mode, the TMR0L and TMR0H registers are both directly readable and writable. The TMR0L register is cleared on any device Reset, while the TMR0H register initializes at FFh.

Both the prescaler and postscaler counters are cleared on the following events:

- A write to the TMR0L register
- A write to either the T0CON0 or T0CON1 registers.
- <u>Any device Reset</u> Power-on Reset (POR), MCLR Reset, Watchdog Timer Reset (WDTR) or Brown-out Reset (BOR)

26.1.3 COUNTER MODE

In Counter mode, the prescaler is normally disabled by setting the T0CKPS bits of the T0CON1 register to '0000'. Each rising edge of the clock input (or the output of the prescaler if the prescaler is used) increments the counter by '1'.

26.1.4 TIMER MODE

In Timer mode, the Timer0 module will increment every instruction cycle as long as there is a valid clock signal and the T0CKPS bits of the T0CON1 register (Register 26-4) are set to '0000'. When a prescaler is added, the timer will increment at the rate based on the prescaler value.

26.1.5 ASYNCHRONOUS MODE

When the T0ASYNC bit of the T0CON1 register is set (T0ASYNC = 1), the counter increments with each rising edge of the input source (or output of the prescaler, if used). Asynchronous mode allows the counter to continue operation during Sleep mode provided that the clock also continues to operate during Sleep.

26.1.6 SYNCHRONOUS MODE

When the T0ASYNC bit of the T0CON1 register is clear (T0ASYNC = 0), the counter clock is synchronized to the system oscillator (Fosc/4). When operating in Synchronous mode, the counter clock frequency cannot exceed Fosc/4.

26.2 Clock Source Selection

The T0CS<2:0> bits of the T0CON1 register are used to select the clock source for Timer0. Register 26-4 displays the clock source selections.

26.2.1 INTERNAL CLOCK SOURCE

When the internal clock source is selected, Timer0 operates as a timer and will increment on multiples of the clock source, as determined by the Timer0 prescaler.

26.2.2 EXTERNAL CLOCK SOURCE

When an external clock source is selected, Timer0 can operate as either a timer or a counter. Timer0 will increment on multiples of the rising edge of the external clock source, as determined by the Timer0 prescaler.

26.3 **Programmable Prescaler**

A software programmable prescaler is available for exclusive use with Timer0. There are 16 prescaler options for Timer0 ranging in powers of two from 1:1 to 1:32768. The prescaler values are selected using the T0CKPS<3:0> bits of the T0CON1 register.

The prescaler is not directly readable or writable. Clearing the prescaler register can be done by writing to the TMR0L register, the T0CON0 register, or the T0CON1 register.

26.4 Programmable Postscaler

A software programmable postscaler (output divider) is available for exclusive use with Timer0. There are 16 postscaler options for Timer0 ranging from 1:1 to 1:16. The postscaler values are selected using the T0OUTPS<3:0> bits of the T0CON0 register.

The postscaler is not directly readable or writable. Clearing the postscaler register can be done by writing to the TMR0L register, the T0CON0 register, or the T0CON1 register. In the 16-bit mode, if the postscaler option is selected to a ratio other than 1:1, the reload of the TMR0H and TMR0L registers is not possible inside the Interrupt Service Routine. The timer period must be calculated with the prescaler and postscaler factors selected.

26.5 Operation During Sleep

When operating synchronously, Timer0 will halt. When operating asynchronously, Timer0 will continue to increment and wake the device from Sleep (if Timer0 interrupts are enabled) provided that the input clock source is active.

26.6 Timer0 Interrupts

The Timer0 Interrupt Flag (TMR0IF) bit is set when either of the following conditions occur:

- 8-bit TMR0L matches the TMR0H value
- 16-bit TMR0 rolls over from FFFFh

When the postscaler bits (T0OUTPS<3:0>) are set to 1:1 operation (no division), the T0IF Flag bit will be set with every TMR0 match or rollover. In general, the TMR0IF Flag bit will be set every T0OUTPS +1 matches or rollovers.


If Timer0 interrupts are enabled (the TMR0IE bit of the PIE0 register = 1), the CPU will be interrupted and the device may wake from Sleep (see Section 26.5 "Operation During Sleep" for more details).

26.7 Timer0 Output

The Timer0 output can be routed to any I/O pin via the RxyPPS output selection register (see Section 13.0 "Peripheral Pin Select (PPS) Module" for additional information). The Timer0 output can also be used by other peripherals, such as the auto-conversion trigger of the Analog-to-Digital Converter. Finally, the Timer0 output can be monitored through software via the Timer0 Output (T0OUT) bit of the T0CON0 register (Register 26-3).

TMR0_out will be one postscaled clock period when a match occurs between TMR0L and TMR0H in 8-bit mode, or when TMR0 rolls over in 16-bit mode. When a match condition occurs, the Timer0 output will toggle every T0OUTPS + 1 match. The total Timer0 period takes two match events to occur, and creates a 50% duty cycle output.

PIC16(L)F18326/18346



26.8 Register Definitions: Timer0 Register

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
			TMRC	L<7:0>			
bit 7							bit 0
Legend:							
R = Readable I	bit	W = Writable bit		U = Unimpler	nented bit, read	l as '0'	
u = Bit is uncha	anged	x = Bit is unknown		-n/n = Value a	at POR and BO	R/Value at all c	ther Resets
'1' = Bit is set		'0' = Bit is clea	ared				

REGISTER 26-1: TMR0L: TIMER0 COUNT REGISTER

bit 7-0 TMR0L<7:0>:TMR0 Counter bits 7..0

REGISTER 26-2: TMR0H: TIMER0 PERIOD REGISTER

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
		-	TMR0H<7:0> o	or TMR0<15:8>	>		
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 When T016BIT = 0 TMR0H<7:0>:TMR0 Period Register Bits 7..0 When T016BIT = 1 TMR0<15:8>: TMR0 Counter bits 15..8

R/W-0/0	U-0	R-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
TOEN	—	T0OUT	T016BIT		TOOUTI	PS<3:0>	
bit 7							bit
Legend:							
R = Readable bit		W = Writable	bit	U = Unimpler	mented bit, read	l as '0'	
u = Bit is unchang	ed	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all c	other Resets
'1' = Bit is set		'0' = Bit is cle	ared				
1		ule is enabled		l vest Power mo	de		
bit 6 Ur	nimplemen	ted: Read as '	0'				
	OUT:TMR0) Output (read- bit	only)				
1	= TMR0 is		as 16-bit Time	r Select bit			
11 11 11 11 11 10 10 10 10 01 01 01 01 0	<pre>1 = TMR0 is a 16-bit timer 0 = TMR0 is an 8-bit timer T0OUTPS<3:0>: TMR0 Output Postscaler (divider) Select bits 1111 = 1:16 Postscaler 1100 = 1:15 Postscaler 1001 = 1:14 Postscaler 1000 = 1:13 Postscaler 1011 = 1:12 Postscaler 1001 = 1:10 Postscaler 1000 = 1:9 Postscaler 0101 = 1:10 Postscaler 0111 = 1:8 Postscaler 0110 = 1:7 Postscaler 0101 = 1:6 Postscaler 0101 = 1:6 Postscaler 0101 = 1:5 Postscaler 0111 = 1:4 Postscaler 0011 = 1:4 Postscaler 0010 = 1:3 Postscaler 0010 = 1:2 Postscaler 0001 = 1:2 Postscaler</pre>						

REGISTER 26-3: T0CON0: TIMER0 CONTROL REGISTER 0

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
	T0CS<2:0>		T0ASYNC		T0CKF	PS<3:0>	
bit 7			·				bit (
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
u = Bit is unch	nanged	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is cle	ared				
bit 7-5	111 = CLC1 110 = SOSC 101 = Reserv 100 = LFINT 011 = HFINT 010 = Fosc/4	ved OSC ⁻ OSC 4 PPS (Inverted)		its			
bit 4	1 = The inpu	MR0 Input Asy at to the TMR0 o at to the TMR0 o	counter is not	synchronized t	to system clock osc/4	S	
bit 3-0	TOCKPS<3:0 1111 = 1:327 1110 = 1:163 1101 = 1:819 1001 = 1:409 1011 = 1:202 1010 = 1:102 1001 = 1:512 1000 = 1:256 0111 = 1:126 0110 = 1:64 0101 = 1:32 0100 = 1:16 0011 = 1:2 0000 = 1:1	384 92 96 48 24 2 5	ate Select bit				

REGISTER 26-4: T0CON1: TIMER0 CONTROL REGISTER 1

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA		-	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	_	_	ANSA5	ANSA4	—	ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	—	_		_	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_			—	150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
TMR0L	TMR0L<7:0>						279		
TMR0H	TMR0H<7:0> or TMR0<15:8>				279				
T0CON0	T0EN	—	T0OUT	T016BIT	Т	00UTPS<	:3:0>		280
T0CON1	٦	F0CS<2:0>		TOASYNC		T0CKPS<	3:0>		281
T0CKIPPS	_	_	_		T0CKIF	PS<4:0>			162
TMR0PPS	_	—	_		TMR0P	PS<4:0>			162
ADACT	_	-	_		ADAC	T<4:0>			246
CLCxSELy	_	_			LCxDyS<5:	0>			229
T1GCON	TMR1GE	T1GPOL	T1GTM	T1GSPM	T1GGO/DONE	T1GVAL	T1GSS	S<1:0>	294
INTCON	GIE	PEIE	—	_	—	—	_	INTEDG	100
PIR0	_	—	TMR0IF	IOCIF	—	_		INTF	106
PIE0	_	_	TMR0IE	IOCIE				INTE	101

TABLE 26-1: SUMMARY OF REGISTERS ASSOCIATED WITH TIMER0

Legend: — = Unimplemented location, read as '0'. Shaded cells are not used by the Timer0 module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.


27.0 TIMER1/3/5 MODULE WITH GATE CONTROL

Timer1/3/5 modules are 16-bit timers/counters, each with the following features:

- 16-bit timer/counter register pair (TMR1H:TMR1L)
- Programmable internal or external clock source
- 2-bit prescaler
- Clock source for optional comparator synchronization
- Multiple Timer1 gate (count enable) sources
- Interrupt on overflow
- Wake-up on overflow (external clock, Asynchronous mode only)
- Time base for the Capture/Compare function with the CCP modules
- Auto-Conversion Trigger (with CCP)
- · Selectable Gate Source Polarity
- · Gate Toggle mode
- Gate Single-Pulse mode
- Gate Value Status
- Gate Event Interrupt

Figure 27-1 is a block diagram of the Timer1 module.

- **Note 1:** In devices with more than one Timer module, it is very important to pay close attention to the register names used. A number placed after the module acronym is used to distinguish between separate modules. For example, the T1CON and T3CON control the same operational aspects of two completely different Timer modules.
 - 2: Throughout this section, generic references to Timer1 module in any of its operating modes may be interpreted as being equally applicable to Timerx module. Register names, module signals, I/O pins and bit names may use the generic designator 'x' to indicate the use of a numeral to distinguish a particular module, when required.



27.1 Timer1 Operation

The Timer1 module is a 16-bit incrementing counter which is accessed through the TMR1H:TMR1L register pair. Writes to TMR1H or TMR1L directly update the counter.

The module can be used with either internal or external clock sources, and has the Timer1 Gate Enable function. When Timer1 is used with the Timer1 Gate Enable, the timer can measure time intervals or count signal pulses between two points of interest. When used without the Timer1 Gate Enable, the timer simply measures time intervals.

Timer1 is enabled by configuring the TMR1ON and TMR1GE bits in the T1CON and T1GCON registers, respectively. Table 27-1 displays the Timer1 enable selections.

TABLE 27-1: TIMER1 ENABLE SELECTIONS

TMR10N	TMR1GE	Timer1 Operation
0	0	Off
0	1	Off
1	0	Always On
1	1	Count Enabled

27.2 Clock Source Selection

The TMR1CS<1:0> and T1OSC bits of the T1CON register are used to select the clock source for Timer1. Table 27-2 displays the clock source selections. The TMR1H:TMR1L register pair will increment on multiples of the clock source as determined by the Timer1 prescaler.

When either the Fosc or LFINTOSC clock source is selected, the TMR1H:TMR1L register pair will increment every rising clock edge. Reading from the TMR1H:TMR1L register pair when either the Fosc or LFINTOSC is the clock source will cause a 2 LSb loss in resolution, which can be mitigated by using an asynchronous input signal to gate the Timer1 clock input (see Section 26.5 "Operation During Sleep" for more information on the Timer1 Gate Enable).

When the Fosc/4 clock source is selected, the TMR1H:TMR1L register pair increments every instruction cycle (once every four Fosc pulses).

In addition to the internal clock sources, Timer1 has a dedicated external clock input pin, T1CKI. T1CKI can be either synchronized to the system clock or can run asynchronously via the T1SYNC bit of the T1CON register. When the T1CKI pin is used as the clock source, the TMR1H:TMR1L register pair increments on the rising edge of the T1CKI clock input.

Note:	When using Timer1 to count events, a falling edge must be registered by the counter prior to the first incrementing rising edge after any one or more of the
	following conditions:

- Timer1 enabled after POR
- Write to TMR1H or TMR1L
- · Timer1 is disabled
- Timer1 is disabled (TMR1ON = 0) when T1CKI is high then Timer1 is enabled (TMR1ON=1) when T1CKI is low.

TABLE 27-2: CLOCK SOURCE SELECTIONS

TMR1CS<1:0>	Clock Source
11	LFINTOSC
10	External Clocking on T1CKI Pin
01	System Clock (Fosc)
00	Instruction Clock (Fosc/4)

27.2.1 TIMER1 (SECONDARY) OSCILLATOR

A dedicated low-power 32.768 kHz oscillator circuit is built-in between pins SOSCI (input) and SOSCO (amplifier output). This internal circuit is designed to be used in conjunction with an external 32.768 kHz crystal.

The oscillator circuit is enabled by setting the T1SOSC bit of the T1CON register. The oscillator will continue to run during Sleep.

Note: The oscillator requires a start-up and stabilization time before use. Thus, T1SOSC must be set and a suitable delay observed prior to using Timer1. A suitable delay similar to the OST delay can be implemented in software by clearing the bit then presettina TMR1IF the TMR1H:TMR1L register pair to FC00h. The TMR1IF flag will be set when 1024 clock cycles have elapsed, thereby indicating that the oscillator is running and reasonably stable.

27.3 Timer1 Prescaler

Timer1 has four prescaler options allowing 1, 2, 4 or 8 divisions of the clock input. The T1CKPS bits of the T1CON register control the prescale counter. The prescale counter is not directly readable or writable; however, the prescaler counter is cleared upon a write to TMR1H or TMR1L.

27.4 Timer1 16-Bit Read/Write Mode

Timer1 can be configured for 16-bit reads and writes. A read from TMR1L loads the contents of the high byte of Timer1 into the Timer1 High Byte Buffer register. This provides the user with the ability to accurately read all 16 bits of Timer1 without having to determine whether a read of the high byte, followed by a read of the low byte, has become invalid due to a rollover between reads.

A write to the high byte of Timer1 must also take place through the TMR1H Buffer register. The Timer1 high byte is updated with the contents of TMR1H when a write occurs to TMR1L. This allows a user to write all 16 bits at once to both the high and low bytes of Timer1. The high byte of Timer1 is not directly readable or writable in this mode.

All reads and writes must take place through the Timer1 High Byte Buffer register. Writes to TMR1H do not clear the Timer1 prescaler. The prescaler is only cleared on writes to TMR1L.




FIGURE 27-2: BODY DIAGRAM

27.5 Timer1 Operation in Asynchronous Mode

If the control bit T1SYNC of the T1CON register is set, the external clock input is not synchronized. The timer increments asynchronously to the internal phase clocks. If the external clock source is selected, then the timer will continue to run during Sleep and can generate an interrupt on overflow, which will wake-up the processor. However, special precautions in software are needed to read/write the timer (see Section 27.5.1 "Reading and Writing Timer1 in Asynchronous Mode").

Note: When switching from synchronous to asynchronous operation, it is possible to skip an increment. When switching from asynchronous to synchronous operation, it is possible to produce an additional increment.

27.5.1 READING AND WRITING TIMER1 IN ASYNCHRONOUS MODE

Reading TMR1H or TMR1L while the timer is running from an external asynchronous clock will ensure a valid read (taken care of in hardware). However, reading the 16-bit timer in two 8-bit values itself poses certain problems, since the timer may overflow between the reads.

For writes, it is recommended that the user simply stop the timer and write the desired values. A write contention may occur by writing to the timer registers, while the register is incrementing. This may produce an unpredictable value in the TMR1H:TMR1L register pair.

27.6 Timer1 Gate

Timer1 can be configured to count freely or the count can be enabled and disabled using Timer1 gate circuitry. This is also referred to as Timer1 Gate Enable.

Timer1 gate can also be driven by multiple selectable sources.

27.6.1 TIMER1 GATE ENABLE

The Timer1 Gate Enable mode is enabled by setting the TMR1GE bit of the T1GCON register. The polarity of the Timer1 Gate Enable mode is configured using the T1GPOL bit of the T1GCON register.

When Timer1 Gate Enable mode is enabled, Timer1 will increment on the rising edge of the Timer1 clock source. When Timer1 Gate Enable mode is disabled, no incrementing will occur and Timer1 will hold the current count. See Figure 27-4 for timing details.

TABLE 27-3 :	TIMER1 GATE ENABLE
	SELECTIONS

T1CLK	T1GPOL	T1G	Timer1 Operation
\uparrow	0	0	Counts
\uparrow	0	1	Holds Count
\uparrow	1	0	Holds Count
\uparrow	1	1	Counts

27.6.2 TIMER1 GATE SOURCE SELECTION

Timer1 gate source selections are shown in Table 27-4. Source selection is controlled by the T1GSS bits of the T1GCON register. The polarity of the selected input is configurable. Polarity selection is controlled by the T1GPOL bit of the T1GCON register.

TABLE 27-4: TIMER1 GATE SOURCES

T1GSS	Timer1 Gate Source		
00	Timer1 Gate Pin		
01	Overflow of Timer0 (TMR0 increments from FFh to 00h)		
10	Comparator 1 Output (optionally Timer1 synchronized output)		
11	Comparator 2 Output (optionally Timer1 synchronized output)		

27.6.2.1 T1G Pin Gate Operation

The T1G pin is one source for Timer1 gate control. It can be used to supply an external source to the Timer1 gate circuitry.

27.6.2.2 Timer0 Overflow Gate Operation

When Timer0 increments from FFh to 00h, a low-to-high pulse will automatically be generated and internally supplied to the Timer1 gate circuitry.

27.6.2.3 Comparator C1 Gate Operation

The output resulting from a Comparator 1 operation can be selected as a source for Timer1 gate control. The Comparator 1 output can be synchronized to the Timer1 clock or left asynchronous. For more information see Section 19.4.1 "Comparator Output Synchronization".

27.6.2.4 Comparator C2 Gate Operation

The output resulting from a Comparator 2 operation can be selected as a source for Timer1 gate control. The Comparator 2 output can be synchronized to the Timer1 clock or left asynchronous. For more information see Section 19.4.1 "Comparator Output Synchronization".

27.6.3 TIMER1 GATE TOGGLE MODE

When Timer1 Gate Toggle mode is enabled, it is possible to measure the full period of a Timer1 gate signal, as opposed to the duration of a single level pulse.

The Timer1 gate source is routed through a flip-flop that changes state on every incrementing edge of the signal. See Figure 27-5 for timing details.

Timer1 Gate Toggle mode is enabled by setting the T1GTM bit of the T1GCON register. When the T1GTM bit is cleared, the flip-flop is cleared and held clear. This is necessary to control which edge is measured.

Note: Enabling Toggle mode at the same time as changing the gate polarity may result in indeterminate operation.

27.6.4 TIMER1 GATE SINGLE-PULSE MODE

When Timer1 Gate Single-Pulse mode is enabled, it is possible to capture a single-pulse gate event. Timer1 Gate Single-Pulse mode is first enabled by setting the T1GSPM bit in the T1GCON register. Next, the T1GGO/DONE bit in the T1GCON register must be set. The Timer1 will be fully enabled on the next incrementing edge of the Timer1 gate signal. On the next trailing edge of the Timer1 gate signal, the T1GGO/DONE bit will automatically be cleared. No other gate events will be allowed to increment Timer1 until the T1GGO/DONE bit is once again set in software. See Figure 27-6 for timing details.

If the Single-Pulse Gate mode is disabled by clearing the T1GSPM bit in the T1GCON register, the T1GGO/DONE bit must also be cleared.

Enabling the Toggle mode and the Single-Pulse mode simultaneously will permit both sections to work together. This allows the period of the Timer1 gate source to be measured. See Figure 27-7 for timing details.

27.6.5 TIMER1 GATE VALUE STATUS

When Timer1 Gate Value Status is utilized, it is possible to read the most current level of the gate control value. The value is stored in the T1GVAL bit in the T1GCON register. The T1GVAL bit is valid even when the Timer1 gate is not enabled (TMR1GE bit is cleared).

27.7 Timer1 Interrupt

The Timer1 register pair (TMR1H:TMR1L) increments to FFFFh and rolls over to 0000h. When Timer1 rolls over, the Timer1 interrupt flag bit of the PIR1 register is set. To enable the interrupt on rollover, set these bits:

- The TMR1ON bit of the T1CON register
- The TMR1IE bit of the PIE1 register
- The PEIE bit of the INTCON register
- The GIE bit of the INTCON register

The interrupt is cleared by clearing the TMR1IF bit in the Interrupt Service Routine.

Note: The TMR1H:TMR1L register pair and the TMR1IF bit must be cleared before enabling interrupts.

27.7.1 TIMER1 GATE EVENT INTERRUPT

When Timer1 Gate Event Interrupt is enabled, it is possible to generate an interrupt upon the completion of a gate event. When the falling edge of T1GVAL occurs, the TMR1GIF flag bit in the PIR1 register will be set. If the TMR1GIE bit in the PIE1 register is set, then an interrupt will be recognized.

The TMR1GIF flag bit operates even when the Timer1 gate is not enabled (TMR1GE bit is cleared).

27.8 Timer1 Operation During Sleep

Timer1 can only operate during Sleep when setup in Asynchronous mode. In this mode, an external crystal or clock source can be used to increment the timer. To set up the timer to wake the device:

- The TMR1ON bit of the T1CON register must be set
- The TMR1IE bit of the PIE1 register must be set
- The PEIE bit of the INTCON register must be set
- The T1SYNC bit of the T1CON register must be set
- The TMR1CS bits of the T1CON register must be configured
- The T1SOSC bit of the T1CON register must be configured

The device will wake-up on an overflow and execute the next instructions. If the GIE bit of the INTCON register is set, the device will call the Interrupt Service Routine.

Secondary oscillator will continue to operate in Sleep regardless of the $\overline{T1SYNC}$ bit setting.

27.9 CCP Capture/Compare Time Base

The CCP modules use the TMR1H:TMR1L register pair as the time base when operating in Capture or Compare mode.

In Capture mode, the value in the TMR1H:TMR1L register pair is copied into the CCPR1H:CCPR1L register pair on a configured event.

In Compare mode, an event is triggered when the value CCPR1H:CCPR1L register pair matches the value in the TMR1H:TMR1L register pair. This event can be an Auto-conversion Trigger.

For more information, see Section 29.0 "Capture/Compare/PWM Modules".

27.10 CCP Auto-Conversion Trigger

When any of the CCP's are configured to trigger an auto-conversion, the trigger will clear the TMR1H:TMR1L register pair. This auto-conversion does not cause a Timer1 interrupt. The CCP module may still be configured to generate a CCP interrupt.


In this mode of operation, the CCPR1H:CCPR1L register pair becomes the period register for Timer1.

Timer1 must be synchronized and FOSC/4 must be selected as the clock source to utilize the Auto-conversion Trigger. Asynchronous operation of Timer1 can cause an Auto-conversion Trigger to be missed.

In the event that a write to TMR1H or TMR1L coincides with an Auto-conversion Trigger from the CCP, the write will take precedence.


For more information, see Section 29.3.3 "Auto-Conversion Trigger".

PIC16(L)F18326/18346



2: In Counter mode, a falling edge must be registered by the counter prior to the first incrementing rising edge of the clock.

FIGURE 27-4: TIMER1 GATE ENABLE MODE



PIC16(L)F18326/18346




FIGURE 27-6: TIMER1 GATE SINGLE-PULSE MODE




FIGURE 27-7: TIMER1 GATE SINGLE-	PULSE AND TOGGLE COMBINED MODE
TMR1GE	
T1GPOL	
T1GSPM	
T1GTM	
T1GGO/ Set by software DONE Counting enabled or rising edge of T1G	Cleared by hardware on falling edge of T1GVAL
t1g_in	
т1СКІ	
T1GVAL	
Timer1 N	<u>N + 1</u> <u>N + 2</u> <u>N + 3</u> <u>N + 4</u>
TMR1GIF Cleared by software	Set by hardware on Cleared by falling edge of T1GVAL — software

27.11 Register Definitions: Timer1/3/5 Control

R/W-0/u	R/W-0/u	R/W-0/u R/W-0/u		R/W-0/u	R/W-0/u	U-0	R/W-0/u
TMRxCS<1:0>		TxCKPS<	<1:0>	TxSOSC	TxSYNC	_	TMRxON
bit 7					1		bit (
Legend:							
R = Readab	le bit	W = Writable bit		U = Unimpler	mented bit, read	as '0'	
u = Bit is un	changed	x = Bit is unknow	vn	-n/n = Value a	at POR and BOF	R/Value at all	other Resets
'1' = Bit is se	et	'0' = Bit is cleare	d				
bit 7-6	11 = Timerx 10 = Timerx <u>If TxSO</u> Externa <u>If TxSO</u> Clock fr 01 = Timerx	0>: Timerx Clock source is Ll clock source is pi SC = 0: I clock from TxCK SC = 1: om SOSC, either clock source is sy clock source is in	FINTOSC n or oscillato IPPS pin (or crystal oscill rstem clock	or: n the rising edg lator on TxSOS (Fosc)	,	ins, or SOSC	CIN input
oit 5-4	TxCKPS<1:	0>: Timerx Input C	lock Presca	ale Select bits			
	11 = 1:8 Pre 10 = 1:4 Pre 01 = 1:2 Pre 00 = 1:1 Pre	scale value scale value					
bit 3	TxSOSC: LF	P Oscillator Enable	Control bit				
		equested as the cl nabled as the cloc					
bit 2	TMRxCS<1: 1 = Do not s 0 = Synchro TMRxCS<1:	synchronize extern nize external cloc 0> = 0x	al clock inp (input with	ut system clock	additional synch	ronization is	performed.
bit 1	This bit is ignored. Timer1 uses the internal clock and no additional synchronization is p Unimplemented: Read as '0'						
bit 0	TMRxON: Ti						
-	1 = Enables						

REGISTER 27-1: TxCON⁽¹⁾: TIMERx CONTROL REGISTER

R/W-0/u	R/W-0/u	R/W-0/u	R/W-0/u	R/W/HC-0/u	R-x/x	R/W-0/u	R/W-0/u
TMRxGE	TxGPOL	TxGTM	TxGSPM	TxGGO/DONE	TxGVAL	TxGSS	S<1:0>
bit 7							bit
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimplement	-		
u = Bit is unch	anged	x = Bit is unkr	nown	-n/n = Value at P0	OR and BOR/∖	/alue at all ot	ner Resets
'1' = Bit is set		'0' = Bit is clea	ared	HC = Bit is cleare	d by hardware	•	
bit 7	TMRxGE: Tir	ner1 Gate Ena	ble bit				
		ored 1:		ïmer1 gate function			
bit 6		nerx Gate Pola	-				
				unts when gate is h nts when gate is lov			
bit 5	TxGTM: Time	erx Gate Toggle	e Mode bit				
	0 = Timerx G	Sate Toggle mo Sate Toggle mo lip-flop toggles	de is disabled	and toggle flip-flop q edge	is cleared		
bit 4	-	nerx Gate Sing	-				
	1 = Timerx G	•	se mode is en	abled and is contro	lling Timerx ga	te	
bit 3	TxGGO/DON	E: Timerx Gate	e Single-Pulse	Acquisition Status	bit		
	0 = Timerx g	ate single-puls	e acquisition h	s ready, waiting for has completed or ha TxGSPM is cleared	is not been sta	irted	
bit 2	TxGVAL: Tim	nerx Gate Value	e Status bit				
	Indicates the current state of the Timerx gate, latched at Q1, provided to TMRxH:TMRxL Unaffected by Timerx Gate Enable (TMRxGE)						
bit 1-0	TxGSS<1:0>	: Timerx Gate	Source Select	bits			
	10 = Compar	ator 2 optional ator 1 optional overflow output gate pin	y synchronize				
		~ I					

REGISTER 27-2: TxGCON⁽¹⁾: TIMERx GATE CONTROL REGISTER

REGISTER 27-3: TMRxL⁽¹⁾: TIMERx LOW BYTE REGISTER

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
			TMRx	L<7:0>			
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable I	bit	U = Unimpler	nented bit, read	d as '0'	
u = Bit is unch	anged	x = Bit is unkn	nown	-n/n = Value a	at POR and BC	R/Value at all	other Resets
'1' = Bit is set		'0' = Bit is clea	ared				

bit 7-0 TMRxL<7:0>: TMRx Low Byte bits

Note 1: 'x' refers to either '1', '3' or '5' for the respective Timer1/3/5 registers.

REGISTER 27-4: TMRxH⁽¹⁾: TIMERx HIGH BYTE REGISTER

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u
			TMRxH	 <7:0>			
bit 7							bit 0

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 TMRxH<7:0>: TMRx High Byte bits

Note 1: 'x' refers to either '1', '3' or '5' for the respective Timer1/3/5 registers.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA		—	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA		_	ANSA5	ANSA4	_	ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_		_	—	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_		_	_	150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
INTCON	GIE	PEIE	_	_	_		_	INTEDG	100
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
PIR3	OSFIF	CSWIF	TMR3GIF	TMR3IF	CLC4IF	CLC3IF	CLC2IF	CLC1IF	109
PIE3	OSFIE	CSWIE	TMR3GIE	TMR3IE	CLC4IE	CLC3IE	CLC2IE	CLC1IE	104
PIR4	CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	110
PIE4	CWG2IE	CWG1IE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE	105
T1CON	TMR1C	S<1:0>	T1CKP	S<1:0>	T1SOSC	T1SYNC	_	TMR10N	293
T1GCON	TMR1GE	T1GPOL	T1GTM	T1GSPM	T1GGO/DONE	T1GVAL	T1GS	S<1:0>	294
TMR1L		TMR1L<7:0>							295
TMR1H				TMR	1H<7:0>				295
T1CKIPPS	_	_	_	– T1CKIPPS<4:0>					162
T1GPPS	_	_	_	– T1GPPS<4:0>					162
T3CON	TMR3C	S<1:0>	T3CKP	S<1:0>	T3SOSC	T3SYNC	—	TMR3ON	293
T3GCON	TMR3GE	T3GPOL	T3GTM	T3GSPM	T3GGO/DONE	T3GVAL	T3GS	S<1:0>	294
TMR3L				TMR	3L<7:0>				295
TMR3H				TMR	3H<7:0>				295
T3CKIPPS	_	—	—		ТЗСК	IPPS<4:0>			162
T3GPPS	_	_	_		T3G	PPS<4:0>			162
T5CON	TMR5C	:S<1:0>	T5CKP	S<1:0>	T5SOSC	T5SYNC	_	TMR5ON	293
T5GCON	TMR5GE	T5GPOL	T5GTM	T5GSPM	T5GGO/DONE	T5GVAL	T5GS	S<1:0>	294
TMR5L				TMR	5L<7:0>				295
TMR5H				TMR	5H<7:0>				295
T5CKIPPS	_	_	_		T5CK	IPPS<4:0>			162
T5GPPS	_	_	_		T5G	PPS<4:0>			162
T0CON0	T0EN	_	TOOUT	T016BIT		T0OUTPS-	<3:0>		280
CMxCON0	CxON	CxOUT	_	CxPOL	_	CxSP	CxHYS	CxSYNC	196
CCPTMRS	C4TSE	L<1:0>	C3TSE	L<1:0>	C2TSEL<	1:0>	C1TSE	L<1:0>	312
CCPxCON	CCPxEN	_	CCPxOUT	CCPxFMT		CCPxMODE	<3:0>		309
CLCxSELy		—			LCxDyS<5	:0>			229
ADACT		_			ADA	ACT<4:0>			246

Legend: — = unimplemented location, read as '0'. Shaded cells are not used by the Timer1 module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

PIC16(L)F18326/18346

28.0 TIMER2/4/6 MODULE

Timer2/4/6 modules are 8-bit timers that incorporate the following features:

- 8-bit Timer and Period registers (TMR2/4/6 and PR2/4/6, respectively)
- Readable and writable (both registers)
- Software programmable prescaler (1:1, 1:4, 1:16, and 1:64)
- Software programmable postscaler (1:1 to 1:16)
- Interrupt on TMR2/4/6 match with PR2/4/6
- Optional use as the shift clock for the MSSPx module

See Figure 28-1 for a block diagram of Timer2/4/6.

- **Note 1:** In devices with more than one Timer module, it is very important to pay close attention to the register names used. A number placed after the module acronym is used to distinguish between separate modules. For example, the T2CON and T4CON control the same operational aspects of two completely different Timer modules.
 - 2: Throughout this section, generic references to Timer2 module in any of its operating modes may be interpreted as being equally applicable to Timerx module. Register names, module signals, I/O pins and bit names may use the generic designator 'x' to indicate the use of a numeral to distinguish a particular module, when required.




FIGURE 28-1: TIMER2/4/6 BLOCK DIAGRAM

28.1 Timer2 Operation

The clock input to the Timer2 modules is the system instruction clock (Fosc/4).

A 4-bit counter/prescaler on the clock input allows direct input, divide-by-4 and divide-by-16 prescale options. These options are selected by the prescaler control bits, T2CKPS<1:0> of the T2CON register. The value of TMR2 is compared to that of the Period register, PR2, on each clock cycle. When the two values match, the comparator generates a match signal as the timer output. This signal also resets the value of TMR2 to 00h on the next cycle and drives the output counter/postscaler (see Section 28.2 "Timer2 Interrupt").

The TMR2 and PR2 registers are both directly readable and writable. The TMR2 register is cleared on any device Reset, whereas the PR2 register initializes to FFh. Both the prescaler and postscaler counters are cleared on the following events:

- A write to the TMR2 register
- A write to the T2CON register
- Power-on Reset (POR)
- <u>Brown</u>-out Reset (BOR)
- MCLR Reset
- Watchdog Timer (WDT) Reset
- Stack Overflow Reset
- Stack Underflow Reset
- RESET Instruction

Note: TMR2 is not cleared when T2CON is written.

28.2 Timer2 Interrupt

Timer2 can also generate an optional device interrupt. The Timer2 output signal (TMR2-to-PR2 match) provides the input for the 4-bit counter/postscaler. This counter generates the TMR2 match interrupt flag which is latched in TMR2IF of the PIR1 register. The interrupt is enabled by setting the TMR2 Match Interrupt Enable bit, TMR2IE, of the PIE1 register.

A range of 16 postscale options (from 1:1 through 1:16 inclusive) can be selected with the postscaler control bits, T2OUTPS<3:0>, of the T2CON register.

28.3 Timer2 Output

The unscaled output of TMR2 is available primarily to the CCP modules, where it is used as a time base for operations in PWM mode.

Timer2 can be optionally used as the shift clock source for the MSSPx module operating in SPI mode. Additional information is provided in Section 30.0 "Host Synchronous Serial Port (MSSPx) Module"

28.4 Timer2 Operation During Sleep

The Timer2 timers cannot be operated while the processor is in Sleep mode. The contents of the TMR2 and PR2 registers will remain unchanged while the processor is in Sleep mode.

28.5 Register Definitions: Timer2/4/6 Control

U-0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
_	- TxOUTPS<3:0>				TMRxON	TxCKP	S<1:0>
bit 7							bit (
Legend:							
R = Readab		W = Writable		•	mented bit, read		
u = Bit is un	changed	x = Bit is unkr	nown	-n/n = Value a	at POR and BO	R/Value at all	other Resets
'1' = Bit is se	et	'0' = Bit is clea	ared				
bit 7	Unimpleme	ented: Read as '	0'				
bit 6-3	TxOUTPS<	3:0>: Timerx Ou	tput Postscale	er Select bits			
	1111 = 1:1 0	6 Postscaler					
	1110 = 1:1	5 Postscaler					
		4 Postscaler					
		3 Postscaler					
		2 Postscaler					
		1 Postscaler					
	1001 = 1.10 1000 = 1.9) Postscaler					
	0111 = 1:8						
	0110 = 1 : 7						
	0101 = 1:6						
	0100 = 1:5	Postscaler					
	0011 = 1:4	Postscaler					
	0010 = 1:3	Postscaler					
	0001 = 1:2						
	0000 = 1:1						
bit 2	-	Fimer2 On bit					
	1 = Timerx 0 = Timerx						
bit 1-0		:0>: Timerx Cloc	k Dragonia Sa	laat hita			
			k Prescale Se	elect bits			
	11 = Presca 10 = Presca						
	10 = Presca						
	01 = Presca						
	00 = 10000						

REGISTER 28-1: TxCON⁽¹⁾: TIMERx CONTROL REGISTER

REGISTER 28-2: TMRx⁽¹⁾: **TIMERx COUNT REGISTER**

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
			TMR>	<7:0>			
bit 7							bit 0
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, read	d as '0'	
u = Bit is unch	anged	x = Bit is unkn	iown	-n/n = Value a	at POR and BC	R/Value at all	other Resets
'1' = Bit is set		'0' = Bit is clea	ared				

bit 7-0 TMRx<7:0>: TMRx Counter bits 7..0

Note 1: 'x' refers to either '2,' 4' or '6' for the respective Timer2/4/6 registers.

REGISTER 28-3: PRx: TIMERx PERIOD REGISTER⁽¹⁾

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1
			PRx<	:7:0>			
bit 7							bit 0
Legend:							

R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 PRx<7:0>: TMRx Counter bits 7..0

When TMRx = PRx, the next clock will reset the counter; counter period is (PRx+1)

Note 1: 'x' refers to either '2,' 4' or '6' for the respective Timer2/4/6 registers.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
INTCON	GIE	PEIE	_	—	—	—	_	INTEDG	100
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103
T2CON	—		T2OUTPS<3:0> TMR2ON T2CKPS<1:0>						299
TMR2		TMR2<7:0>							300
PR2		PR2<7:0>							300
T4CON	_		T4OUTPS<3:0> TMR4ON T4CKPS<1:0>						
TMR4		TMR4<7:0>							300
PR4		PR4<7:0>							300
T6CON	—		T6OUTPS<3:0> TMR6ON T6CKPS<1:0>						
TMR6		TMR6<7:0>							300
PR6		PR6<7:0>							300
ADACT	—	—	— — ADACT<4:0>						246
PWMTMRS	—	_	_	—	P6TSE	L<1:0>	P5TSE	L<1:0>	188
CLCxSELy	_	_			LCxDyS	6<5:0>			229

TABLE 28-1: SUMMARY OF REGISTERS ASSOCIATED WITH TIMER2/4/6

Legend: — = unimplemented location, read as '0'. Shaded cells are not used for Timer2/4/6 module.

29.0 CAPTURE/COMPARE/PWM MODULES

The Capture/Compare/PWM module is a peripheral that allows the user to time and control different events and to generate Pulse-Width Modulation (PWM) signals. In Capture mode, the peripheral allows the timing of the duration of an event. The Compare mode allows the user to trigger an external event when a predetermined amount of time has expired. The PWM mode can generate Pulse-Width Modulated signals of varying frequency and duty cycle.

This family of devices contains four standard Capture/Compare/PWM modules (CCP1, CCP2, CCP3 and CCP4).

The Capture and Compare functions are identical for all CCP modules.

29.1 CCP/PWM Clock Selection

The PIC16(L)F18326/18346 devices allow each individual CCP and PWM module to select the timer source that controls the module. Each module has an independent selection.

As there are up to three 8-bit timers with auto-reload (Timer2, Timer4, and Timer6), PWM mode on the CCP and PWM modules can use any of these timers.

The CCPTMRS register is used to select which timer is used.

- Note 1: In devices with more than one CCP module, it is very important to pay close attention to the register names used. A number placed after the module acronym is used to distinguish between separate modules. For example, the CCP1CON and CCP2CON control the same operational aspects of two completely different CCP modules.
 - 2: Throughout this section, generic references to a CCP module in any of its operating modes may be interpreted as being equally applicable to CCPx module. Register names, module signals, I/O pins, and bit names may use the generic designator 'x' to indicate the use of a numeral to distinguish a particular module, when required.

29.2 Capture Mode

Capture mode makes use of either the 16-bit Timer0 or Timer1 resource. When an event occurs on the capture source, the 16-bit CCPRxH:CCPRxL register pair captures and stores the 16-bit value of the TMR0H:TMR0L or TMR1H:TMR1L register pair, respectively. An event is defined as one of the following and is configured by the CCPxMODE<3:0> bits of the CCPxCON register:

- · Every falling edge
- Every rising edge
- Every 4th rising edge
- Every 16th rising edge

When a capture is made, the Interrupt Request Flag bit CCPxIF of the PIR4 register is set. The interrupt flag must be cleared in software. If another capture occurs before the value in the CCPRxH, CCPRxL register pair is read, the old captured value is overwritten by the new captured value.

Figure 29-1 shows a simplified diagram of the capture operation.

29.2.1 CAPTURE SOURCES


In Capture mode, the CCPx pin may be configured as an input by setting the associated TRIS control bit.

Note: If the CCPx pin is configured as an output, a write to the port can cause a Capture condition.

The capture source is selected by configuring the CCPxCTS<3:0> bits of the CCPxCAP register. The following sources can be selected:

- CCPxPPS input
- C1_output
- C2_output
- NCO_output
- IOC_interrupt
- LC1_output
- LC2_output
- LC3_output
- LC4_output

FIGURE 29-1: CAPTURE MODE OPERATION BLOCK DIAGRAM



DS40001839F-page 303

29.2.2 TIMER1/3/5 MODE RESOURCE

Timer1/3/5 must be running in Timer mode or Synchronized Counter mode for the CCP module to use the capture feature. In Asynchronous Counter mode, the capture operation may not work.

See Section 27.0 "Timer1/3/5 Module with Gate Control" for more information on configuring Timer1/3/5.

Note: Clocking Timer1/3/5 from the system clock (Fosc) may not be used in Capture mode. In order for Capture mode to recognize the trigger event on the CCPx pin, Timer1/3/5 must be clocked from the instruction clock (Fosc/4) or from an external clock source.

29.2.3 SOFTWARE INTERRUPT MODE

When the Capture mode is changed, a false capture interrupt may be generated. The user must keep the CCPxIE interrupt enable bit of the PIE4 register clear to avoid false interrupts. Additionally, the user must clear the CCPxIF interrupt flag bit of the PIR4 register following any change in Operating mode.

29.2.4 CCP PRESCALER

There are four prescaler settings specified by the CCPxMODE<3:0> bits of the CCPxCON register. Whenever the CCP module is turned off, or the CCP module is not in Capture mode, the prescaler counter is cleared. Any Reset will clear the prescaler counter.

Switching from one capture prescaler to another does not clear the prescaler and may generate a false interrupt. To avoid this unexpected operation, turn the module off by clearing the CCPxCON register before changing the prescaler. Example 29-1 demonstrates the code to perform this function.

EXAMPLE 29-1: CHANGING BETWEEN CAPTURE PRESCALERS

BANKSEL	CCPxCON	;Set Bank bits to point
		;to CCPxCON
CLRF	CCPxCON	;Turn CCP module off
MOVLW	NEW CAPT PS	;Load the W reg with
		;the new prescaler
		;move value and CCP ON
MOVWF	CCPxCON	;Load CCPxCON with this
		;value
1		

29.2.5 CAPTURE DURING SLEEP

Capture mode depends upon the Timer1/3/5 module for proper operation. There are two options for driving the Timer1/3/5 module in Capture mode. It can be driven by the instruction clock (Fosc/4), or by an external clock source.

When Timer1/3/5 is clocked by Fosc/4, Timer1/3/5 will not increment during Sleep. When the device wakes from Sleep, Timer1/3/5 will continue from its previous state.

Capture mode will operate during Sleep when Timer1/3/5 is clocked by an external clock source.

29.3 Compare Mode

Compare mode makes use of the 16-bit Timer1/3/5 resource. The 16-bit value of the CCPRxH:CCPRxL register pair is constantly compared against the 16-bit value of the TMR1/3/5H:TMR1/3/5L register pair. When a match occurs, one of the following events can occur:

- Toggle the CCPx output
- · Set the CCPx output
- · Clear the CCPx output
- Generate an Auto-conversion Trigger
- Generate a Software Interrupt


The action on the pin is based on the value of the CCPxMODE<3:0> control bits of the CCPxCON register. At the same time, the interrupt flag CCPxIF bit is set, and an ADC conversion can be triggered, if selected.

All Compare modes can generate an interrupt and trigger an ADC conversion.

Figure 29-2 shows a simplified diagram of the compare operation.

Note: When the CCP is configured in Compare mode using the 'toggle output on match' setting (CCPxMODE<3:0> bits = 0010) and the reference timer is set for an input clock prescale other than 1:1, the output of the CCP will toggle multiple times until finally settling a '0' logic level. To avoid this, the timer input clock prescale select bits must be set to a 1:1 ratio (TxCKPS = 00).

FIGURE 29-2: COMPARE MODE OPERATION BLOCK DIAGRAM



29.3.1 CCPX PIN CONFIGURATION

The user must configure the CCPx pin as an output by clearing the associated TRIS bit and defining the appropriate output pin through the RxyPPS registers. See Section 13.0 "Peripheral Pin Select (PPS) Module" for more details.

Note: Clearing the CCPxCON register will force the CCPx compare output latch to the default low level. This is not the PORT I/O data latch.

29.3.2 TIMER1/3/5 MODE RESOURCE

In Compare mode, Timer1/3/5 must be running in either Timer mode or Synchronized Counter mode. The compare operation may not work in Asynchronous Counter mode.

See Section 27.0 "Timer1/3/5 Module with Gate Control" for more information on configuring Timer1/3/5.

Note:	Clocking Timer1/3/5 from the system clock (Fosc) may not be used in Compare		
	mode. In order for Compare mode to		
	recognize the trigger event on the CCPx		
	pin, Timer1/3/5 must be clocked from the		
	instruction clock (Fosc/4) or from an		
	external clock source.		

29.3.3 AUTO-CONVERSION TRIGGER

All CCPx modes set the CCP interrupt flag (CCPxIF). When this flag is set as a match occurs, an auto-conversion trigger can occur if the CCP module is selected as the conversion trigger source.

Refer to **Section 22.2.4 "Auto-Conversion Trigger"** for more information.

Note:	Removing the Match condition by			
	changing the contents of the CCPRxH			
	and CCPRxL register pair, between the			
	clock edge that generates the			
	Auto-conversion Trigger and the clock			
	edge that generates the Timer Reset, will			
	preclude the Reset from occurring.			

29.3.4 COMPARE DURING SLEEP

Since Fosc is shut down during Sleep mode, the Compare mode will not function properly during Sleep, unless the timer is running. The device will wake on interrupt (if enabled).

29.3.5 COMPARE INTERRUPTS

The CCPxIF interrupt flag will be set when a match between the CCPRxH:CCPRxL register pair and the TMR1/3/5H:TMR1/3/5L register pair occurs. If the device is in Sleep and interrupts are enabled (CCPxIE = 1), the device will wake up, assuming Timer1 is operating during Sleep.

29.4 PWM Overview

Pulse-Width Modulation (PWM) is a scheme that provides power to a load by switching quickly between fully on and fully off states. The PWM signal resembles a square wave where the high portion of the signal is considered the ON state and the low portion of the signal is considered the OFF state. The high portion, also known as the pulse width, can vary in time and is defined in steps. A larger number of steps applied, which lengthens the pulse width, also supplies more power to the load. Lowering the number of steps applied, which shortens the pulse width, supplies less power. The PWM period is defined as the duration of one complete cycle or the total amount of on and off time combined.

PWM resolution defines the maximum number of steps that can be present in a single PWM period. A higher resolution allows for more precise control of the pulse-width time and in turn the power that is applied to the load.

The term duty cycle describes the proportion of the on time to the off time and is expressed in percentages, where 0% is fully off and 100% is fully on. A lower duty cycle corresponds to less power applied and a higher duty cycle corresponds to more power applied.

Figure 29-3 shows a typical waveform of the PWM signal.

29.4.1 STANDARD PWM OPERATION

The standard PWM mode generates a Pulse-Width Modulation (PWM) signal on the CCPx pin with up to 10 bits of resolution. The period, duty cycle, and resolution are controlled by the following registers:

- PR2/4/6 registers
- T2/4/6CON registers
- CCPRxL registers
- CCPxCON registers

Figure 29-4 shows a simplified block diagram of PWM operation.

Note: The corresponding TRIS bit must be cleared to enable the PWM output on the CCPx pin.

FIGURE 29-3: CCP PWM OUTPUT SIGNAL





FIGURE 29-4: SIMPLIFIED PWM BLOCK DIAGRAM



29.4.2 SETUP FOR PWM OPERATION

The following steps must be taken when configuring the CCP module for standard PWM operation:

- Use the desired output pin RxyPPS control to select CCPx as the source and disable the CCPx pin output driver by setting the associated TRIS bit.
- 2. Load the PR2 register with the PWM period value.
- Configure the CCP module for the PWM mode by loading the CCPxCON register with the appropriate values.
- 4. Load the CCPRxL register and the CCPRxH register bits, with the PWM duty cycle value and configure the CCPxFMT bit of the CCPxCON register to set the proper register alignment.
- 5. Configure and start Timer2, 4 or 6.
 - Clear the TMR2/4/6IF interrupt flag bits of the PIR4 register. See Note below.
 - Configure the T2/4/6CKPS bits of the T2/4/6CON register with the Timer prescale value.
 - Enable the Timer by setting the TMR2/4/6ON bit of the T2/4/6CON register.
- 6. Enable PWM output pin:
 - Wait until the Timer overflows and the TMR2/4/6IF bits of the PIR4 register is set. See the Note below.
 - Enable the CCPx pin output driver by clearing the associated TRIS bit
 - **Note:** To send a complete duty cycle and period on the first PWM output, the above steps must be included in the setup sequence. If it is not critical to start with a complete PWM signal on the first output, then step 6 may be ignored.

29.4.3 TIMER2/4/6 TIMER RESOURCE

The PWM standard mode makes use of the 8-bit Timer2/4/6 timer resources to specify the PWM period.

29.4.4 PWM PERIOD

The PWM period is specified by the PRx register of Timer2/4/6. The PWM period can be calculated using the formula of Equation 29-1.

EQUATION 29-1: PWM PERIOD

 $PWM Period = [(PR2x) + 1] \bullet 4 \bullet TOSC \bullet$ (TMR2/4/6 Prescale Value)

Note: Tosc = 1/Fosc

When TMR2/4/6 is equal to PR2/4/6, the following three events occur on the next increment cycle:

- TMR2/4/6 is cleared
- The CCPx pin is set. (Exception: If the PWM duty cycle = 0%, the pin will not be set.)
- The PWM duty cycle is transferred from the CCPRxL/H register pair into a 10-bit buffer.

Note: The Timer postscaler (see Section 28.1 "Timer2 Operation") is not used in the determination of the PWM frequency.


29.4.5 PWM DUTY CYCLE

The PWM duty cycle is specified by writing a 10-bit value to the CCPRxH:CCPRxL register pair. The alignment of the 10-bit value is determined by the CCPRxFMT bit of the CCPxCON register (see Figure 29-5). The CCPRxH:CCPRxL register pair can be written to at any time; however, the duty cycle value is not latched into the 10-bit buffer until after a match between PR2/4/6 and TMR2/4/6.

Equation 29-2 is used to calculate the PWM pulse width.

Equation 29-3 is used to calculate the PWM duty cycle ratio.

FIGURE 29-5: PWM 10-BIT ALIGNMENT BLOCK DIAGRAM



EQUATION 29-2: PULSE WIDTH

Pulse Width =	CCPRxH:CCPRxL registe	er pair) 🔹
		1 17 1

TOSC • (TMR2 Prescale Value)

EQUATION 29-3: DUTY CYCLE RATIO

$$Duty Cycle Ratio = \frac{(CCPRxH:CCPRxL register pair)}{4(PR2 + 1)}$$

The CCPRxH:CCPRxL register pair and a 2-bit internal latch are used to double buffer the PWM duty cycle. This double buffering provides glitchless PWM operation.

The 8-bit timer TMR2/4/6 register is concatenated with either the 2-bit internal system clock (Fosc), or two bits of the prescaler, to create the 10-bit time base. The system clock is used if the Timer2/4/6 prescaler is set to 1:1.

When the 10-bit time base matches the CCPRxH:CCPRxL register pair, then the CCPx pin is cleared (see Figure 29-4).

29.4.6 PWM RESOLUTION

PWM resolution, expressed in number of bits, defines the maximum number of discrete steps that can be present in a single PWM period. For example, a 10-bit resolution will result in 1024 discrete steps, whereas an 8-bit resolution will result in 256 discrete steps.

The maximum PWM resolution is ten bits when PRx is 255. The resolution is a function of the PRx register value as shown by Equation 29-4.

EQUATION 29-4: PWM RESOLUTION

Resolution =
$$\frac{\log[4(PRx + 1)]}{\log(2)}$$
 bits

Note: If the pulse-width value is greater than the period the assigned PWM pin(s) will remain unchanged.

TABLE 29-1.	EXAMPLE PWM FREQUENCIES AND RESOLUTIONS (Fosc = 20 MHz)	
IADLL 23-1.		

PWM Frequency	1.22 kHz	4.88 kHz	19.53 kHz	78.12 kHz	156.3 kHz	208.3 kHz
Timer Prescale	16	4	1	1	1	1
PRx Value	0xFF	0xFF	0xFF	0x3F	0x1F	0x17
Maximum Resolution (bits)	10	10	10	8	7	6.6

TABLE 29-2: EXAMPLE PWM FREQUENCIES AND RESOLUTIONS (Fosc = 8 MHz)

PWM Frequency	1.22 kHz	4.90 kHz	19.61 kHz	76.92 kHz	153.85 kHz	200.0 kHz
Timer Prescale	16	4	1	1	1	1
PRx Value	0x65	0x65	0x65	0x19	0x0C	0x09
Maximum Resolution (bits)	8	8	8	6	5	5

29.4.7 OPERATION IN SLEEP MODE

In Sleep mode, the TMR2/4/6 register will not increment and the state of the module will not change. If the CCPx pin is driving a value, it will continue to drive that value. When the device wakes up, TMR2/4/6 will continue from its previous state.

29.4.8 CHANGES IN SYSTEM CLOCK FREQUENCY

The PWM frequency is derived from the system clock frequency. Any changes in the system clock frequency will result in changes to the PWM frequency. See **Section 7.0 "Oscillator Module"** for additional details.

29.4.9 EFFECTS OF RESET

Any Reset will force all ports to Input mode and the CCP registers to their Reset states.

29.5 Register Definitions: CCP Control

R/W-0/0) U-0	R-x/x	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
CCPxEN	v —	CCPxOUT	CCPxFMT		CCPxMC	DE<3:0>			
bit 7							bit (
Legend:									
R = Reada	ble bit	W = Writable	bit	U = Unimpler	nented bit, rea	d as '0'			
u = Bit is u	nchanged	x = Bit is unkr	nown	-n/n = Value a	at POR and BC	R/Value at all	other Reset		
'1' = Bit is s	set	'0' = Bit is clea	ared						
bit 7	-	CP Module Ena	ble bit						
	1 = CCP is e 0 = CCP is e								
bit 6	Unimpleme	nted: Read as '	0'						
bit 5	-	CCPx Output Da		bit					
bit 4	CCPxFMT:	CCPW (pulse wi	dth) Alignment	t bit					
		<u>= = Capture mod</u>	le						
	-	Unused <u>CCPxMODE = Compare mode</u>							
		Unused							
		<u>E = PWM mode</u>							
	1 = Left-alig	ned format igned format							
bit 3-0	•	E<3:0>: CCPx N	lada Salaat hit	_~ (1)					
DIL J-U	1111 = PW		IDde Gelect bit	5. /					
	1110 = Res								
	1101 = Res								
	1100 = Res	erved							
	1011 = Con	npare mode: out	put will pulse	-1-0; Clears T	MR1/3/5				
	1010 = Con	npare mode: out	put will pulse 0	-1-0					
		npare mode: clea		•					
	1000 = Con	npare mode: set	output on com	pare match					
	0111 = Cap	ture mode: ever	y 16th rising e	dge of CCPx in	put				
		0110 = Capture mode: every 4th rising edge of CCPx input							
		1 = Capture mode: every rising edge of CCPx input 00 = Capture mode: every falling edge of CCPx input							
	0100 = Cap	ture mode: ever	y falling edge o	of CCPX input					
	0011 = Cap	ture mode: ever	y edge of CCP	'x input					
		npare mode: tog							
		npare mode: tog ture/Compare/P							
	All modes will se trigger source.	•	•		•	is selected as	the ADC		

REGISTER 29-1: CCPxCON: CCPx CONTROL REGISTER

	REGISTER 29-2:	CCPxCAP: CAPTURE INPUT SELECTION REGISTER
--	----------------	---

U-0	U-0	U-0	U-0	R/W-0/x	R/W-0/x	R/W-0/x	R/W-0/x
—	—	—	—		CCPxC	TS<3:0>	
bit 7	•		•	•			bit 0
Legend:							

Legenu.		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Reset
'1' = Bit is set	'0' = Bit is cleared	

bit 7-4 Unimplemented: Read as '0'

bit 3-0 CCPxCTS<3:0>: CCPx Capture Mode Data Select bits

CCAP<3:0>	CCP1CAP CAPTURE INPUT	CCP2CAP CAPTURE INPUT	CCP3CAP CAPTURE INPUT	CCP4CAP CAPTURE INPUT			
0000	CCP1PPS	CCP2PPS	CCP3PPS	CCP4PPS			
0001		C1OUT					
0010		C20	DUT				
0011		NC	O1				
0100		IOC_interrupt					
0101	LC1_output						
0110		LC2_output					
0111		LC3_output					
1000		LC4_c	output				
1001							
 1111		Rese	erved				

R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x
			CCPR	xL<7:0>			
bit 7							bit (
Legend:							
R = Readable b	oit	W = Writable bi	it	U = Unimpler	nented bit, read	d as '0'	
u = Bit is unchanged x = Bit is unknown			wn	-n/n = Value a	at POR and BC	R/Value at all	other Reset
'1' = Bit is set		'0' = Bit is clear	ed				

REGISTER 29-3: CCPRxL REGISTER: CCPx REGISTER LOW BYTE

bit 7-0	CCPxMODE = Capture mode
	CCPRxL<7:0>: Captured value of TMR1/3/5L
	CCPxMODE = Compare mode
	CCPRxL<7:0>: LS Byte compared to TMR1/3/5L
	CCPxMODE = PWM modes when CCPxFMT = 0
	CCPRxL<7:0>: CCPW<7:0> – Pulse-width Least Significant eight bits
	CCPxMODE = PWM modes when CCPxFMT = 1
	CCPRxL<7:6>: CCPW<1:0> – Pulse-width Least Significant two bits
	CCPRxL<5:0>: Not used.

REGISTER 29-4: CCPRxH REGISTER: CCPx REGISTER HIGH BYTE

R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	R/W-x/x	
CCPRxH<7:0>								
bit 7	bit 7							

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Reset
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0	CCPxMODE = Capture mode
	CCPRxH<7:0>: Captured value of TMR1/3/5H
	CCPxMODE = Compare mode
	CCPRxH<7:0>: MS Byte compared to TMR1/3/5H
	CCPxMODE = PWM modes when CCPxFMT = 0
	CCPRxH<7:2>: Not used
	CCPRxH<1:0>: CCPW<9:8> – Pulse-width Most Significant two bits
	CCPxMODE = PWM modes when CCPxFMT = 1
	CCPRxH<7:0>: CCPW<9:2> – Pulse-width Most Significant eight bits

R/W-1/1

R/W-0/0

R/W-1/1

C4T	SEL<1:0>	C3TSEL<1:0>	C2TSEL<1:0>	C1TSEL<1:0>					
bit 7				bit 0					
Legend:									
R = Readal	ole bit	W = Writable bit	U = Unimplemented bit, rea	U = Unimplemented bit, read as '0'					
u = Bit is unchanged x		x = Bit is unknown	-n/n = Value at POR and B	-n/n = Value at POR and BOR/Value at all other Reset					
'1' = Bit is set '0'		'0' = Bit is cleared							
bit 7-6	C4TSEL<1	:0>: CCP4 Capture, Compa	are and PWM mode Timer Select	tion bits					
Selection as show in Table 29-4.									
bit 5-4 C3TSEL<1:0>: CCP3 Capture, Compare			are and PWM mode Timer Select	tion bits					
	Selection as	s show in Table 29-4.							
bit 3-2		• •	are and PWM mode Timer Select	tion bits					
	Selection as	s show in Table 29-4.							
bit 1-0			are and PWM mode Timer Select	tion bits					
	Selection as	s show in Table 29-4.							

R/W-0/0

R/W-1/1

REGISTER 29-5: CCPTMRS: CCP TIMERS CONTROL REGISTER

R/W-0/0

TABLE 29-3: TIMER SELECTIONS

R/W-1/1

R/W-0/0

CxTSEL<1:0>	Operating mode based on CCPxMODE<3:0>					
	Capture Compare	PWM				
00	TMR0	TMR2				
01	TMR1	T MIRZ				
10	TMR3	TMR4				
11	TMR5	TMR6				

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	—	_	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA	—	_	ANSA5	ANSA4		ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_	_	_	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4	_	_	_		150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
INTCON	GIE	PEIE	_	_	_	_	_	INTEDG	100
PIR4	CWG2IF	CWG1IF	TMR5GIF	TMR5IF	CCP4IF	CCP3IF	CCP2IF	CCP1IF	110
PIE4	CWG2IE	CWGIE	TMR5GIE	TMR5IE	CCP4IE	CCP3IE	CCP2IE	CCP1IE	105
CCPxCON	CCPxEN	_	CCPxOUT	CCPxFMT CCPxMODE<3:0>					
CCPxCAP	—	_	—	_	- CCPxCTS<3:0>				
CCPRxL				CCPRx<7:0>					
CCPRxH				CCPRx<1	5:8>				311
CCPTMRS	C4TSI	EL<1:0>	C3TSEL	.<1:0>	C2TSE	EL<1:0>	C1TSE	L<1:0>	312
CCP1PPS	_	_	_		С	CP1PPS<4:0	>		162
CCP2PPS	_	_	_		С	CP2PPS<4:0	>		162
CCP3PPS	_	_	_		С	CP3PPS<4:0	>		162
CCP4PPS	_	_	_	CCP4PPS<4:0>					
RxyPPS	_	_	_	RxyPPS<4:0>					
ADACT	—	—	—			ADACT<4:0>			246
CLCxSELy	_	—			LCxDyS-	<5:0>			229
CWGxDAT	_	_	—			DAT<	:3:0>		215
MDSRC		_				MDMS	s<3:0>		272
MDCARH		MDCHPOL	MDCHSYNC			MDCH	<3:0>		273
MDCARL	_	MDCLPOL	MDCLSYNC	_		MDCL	<3:0>		274

TABLE 29-4: SUMMARY OF REGISTERS ASSOCIATED WITH CCPx

Legend: — = Unimplemented location, read as '0'. Shaded cells are not used by the CCP module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

30.0 HOST SYNCHRONOUS SERIAL PORT (MSSPx) MODULE

30.1 MSSPx Module Overview

The Host Synchronous Serial Port (MSSPx) module is a serial interface useful for communicating with other peripheral or microcontroller devices. These peripheral devices may be serial EEPROMs, shift registers, display drivers, A/D Converters, etc. The MSSPx module can operate in one of two modes:

- Serial Peripheral Interface (SPI)
- Inter-Integrated Circuit (I²C)


The SPI interface supports the following modes and features:

- Host mode
- Client mode
- · Clock Polarity
- Client Select Synchronization (Client mode only)
- · Daisy-chain connection of client devices

Figure 30-1 is a block diagram of the SPI interface module.

- Note 1: In devices with more than one MSSP module, it is very important to pay close attention to the register names used. A number placed after the module acronym is used to distinguish between separate modules. For example, the SSP1STAT and SSP2STAT control the same operational aspects of two completely different MSSP modules.
 - 2: Throughout this section, generic references to the MSSP1 module in any of its operating modes may be interpreted as being equally applicable to MSSPx module. Register names, module signals, I/O pins, and bit names may use the generic designator 'x' to indicate the use of a numeral to distinguish a particular module, when required.

FIGURE 30-1: MSSP BLOCK DIAGRAM (SPI MODE)





The I^2C interface supports the following modes and features:

- Host mode
- Client mode
- Byte NACKing (Client mode)
- Limited multi-host support
- 7-bit and 10-bit addressing
- Start and Stop interrupts
- Interrupt masking
- Clock stretching
- Bus collision detection
- General call address matching
- Address masking
- Selectable SDA hold times

Figure 30-2 is a block diagram of the I^2C interface module in Host mode. Figure 30-3 is a diagram of the I^2C interface module in Client mode.

FIGURE 30-2: MSSP BLOCK DIAGRAM (I²C HOST MODE)





30.2 SPI Mode Overview

The Serial Peripheral Interface (SPI) bus is a synchronous serial data communication bus that operates in Full-Duplex mode. Devices communicate in a host/client environment where the host device initiates the communication. A client device is controlled through a Chip Select known as Client Select.

The SPI bus specifies four signal connections:

- Serial Clock (SCK)
- Serial Data Out (SDO)
- Serial Data In (SDI)
- Client Select (SS)

Figure 30-1 shows the block diagram of the MSSPx module when operating in SPI mode.

The SPI bus operates with a single host device and one or more client devices. When multiple client devices are used, an independent Client Select connection can be used to address each client individually.

Figure 30-4 shows a typical connection between a host device and multiple client devices.

The host selects only one client at a time. Most client devices have tri-state outputs so their output signal appears disconnected from the bus when they are not selected.

Transmissions involve two shift registers, eight bits in size, one in the host and one in the client. Data are always shifted out one bit at a time, with the Most Significant bit (MSb) shifted out first. At the same time, a new Least Significant bit (LSb) is shifted into the same register.

Figure 30-5 shows a typical connection between two processors configured as host and client devices.

Data are shifted out of both shift registers on the programmed clock edge and latched on the opposite edge of the clock.

The host device transmits information out on its SDO output pin which is connected to, and received by, the client's SDI input pin. The client device transmits information out on its SDO output pin, which is connected to, and received by, the host's SDI input pin.

To begin communication, the host device first sends out the clock signal. Both the host and the client devices may be configured for the same clock polarity.

The host device starts a transmission by sending out the MSb from its shift register. The client device reads this bit from that same line and saves it into the LSb position of its shift register. During each SPI clock cycle, a full-duplex data transmission occurs. This means that while the host device is sending out the MSb from its shift register (on its SDO pin) and the client device is reading this bit and saving it as the LSb of its shift register, that the client device is also sending out the MSb from its shift register (on its SDO pin) and the host device is reading this bit and saving it as the LSb of its shift register.

After eight bits have been shifted out, the host and client have exchanged register values.

If there are more data to exchange, the shift registers are loaded with new data and the process repeats itself.


Whether the data are meaningful or not (dummy data), depends on the application software. This leads to three scenarios for data transmission:

- Host sends useful data and client sends dummy data.
- Host sends useful data and client sends useful data.
- Host sends dummy data and client sends useful data.

Transmissions must be performed in multiples of eight clock pulses. When there is no more data to be transmitted, the host stops sending the clock signal and it deselects the client.

Every client device connected to the bus that has not been selected through its client select line must disregard the clock and transmission signals and must not transmit out any data of its own.





30.2.1 SPI MODE REGISTERS

The MSSPx module has five registers for SPI mode operation. These are:

- MSSPx STATUS register (SSPxSTAT)
- MSSPx Control register 1 (SSPxCON1)
- MSSPx Control register 3 (SSPxCON3)
- MSSPx Data Buffer register (SSPxBUF)
- MSSPx Address register (SSPxADD)
- MSSPx Shift register (SSPxSR)
- (Not directly accessible)

SSPxCON1 and SSPSTAT are the control and STATUS registers in SPI mode operation. The SSPxCON1 register is readable and writable. The lower six bits of the SSPxSTAT are read-only. The upper two bits of the SSPxSTAT are read/write.

In one SPI Host mode, SSPxADD can be loaded with a value used in the Baud Rate Generator. More information on the Baud Rate Generator is available in Section 30.7 "Baud Rate Generator".

SSPxSR is the shift register used for shifting data in and out. SSPxBUF provides indirect access to the SSPxSR register. SSPxBUF is the buffer register to which data bytes are written, and from which data bytes are read.

In receive operations, SSPxSR and SSPxBUF together create a buffered receiver. When SSPxSR receives a complete byte, it is transferred to SSPxBUF and the SSPxIF interrupt is set.

During transmission, the SSPxBUF is not buffered. A write to SSPxBUF will write to both SSPxBUF and SSPxSR.

30.2.2 SPI MODE OPERATION

When initializing the SPI, several options need to be specified. This is done by programming the appropriate control bits (SSPxCON1<5:0> and SSPxSTAT<7:6>). These control bits allow the following to be specified:

- · Host mode (SCK is the clock output)
- Client mode (SCK is the clock input)
- Clock Polarity (Idle state of SCK)
- Data Input Sample Phase (middle or end of data output time)
- Clock Edge (output data on rising/falling edge of SCK)
- Clock Rate (Host mode only)
- Client Select mode (Client mode only)


To enable the serial port, SSP Enable bit, SSPEN of the SSPxCON1 register, must be set. To reset or reconfigure SPI mode, clear the SSPEN bit, re-initialize the SSPxCONy registers and then set the SSPEN bit. This configures the SDI, SDO, SCK and SS pins as serial PORT pins. For the pins to behave as the serial port function, some must have their data direction bits (in the TRIS register) appropriately programmed as follows:

- · SDI must have corresponding TRIS bit set
- SDO must have corresponding TRIS bit cleared
- SCK (Host mode) must have corresponding TRIS bit cleared
- SCK (Client mode) must have corresponding
 TRIS bit set
- SS must have corresponding TRIS bit set

Any serial port function that is not desired may be overridden by programming the corresponding data direction (TRIS) register to the opposite value. The MSSPx consists of a transmit/receive shift register (SSPxSR) and a buffer register (SSPxBUF). The SSPxSR shifts the data in and out of the device, MSb first. The SSPxBUF holds the data that were written to the SSPxSR until the received data are ready. Once the eight bits of data have been received, that byte is moved to the SSPxBUF register. Then, the Buffer Full Detect bit, BF of the SSPxSTAT register, and the interrupt flag bit, SSPxIF, are set. Any write to the SSPxBUF register during transmission/reception of data will be ignored and the write collision detect bit, WCOL, of the SSPxCON1 register, will be set. User software must clear the WCOL bit to allow the following write(s) to the SSPxBUF register to complete successfully.

When the application software is expecting to receive valid data, the SSPxBUF must be read before the next byte of data to transfer is written to the SSPxBUF. The Buffer Full bit, BF of the SSPxSTAT register, indicates when SSPxBUF has been loaded with the received data (transmission is complete). When the SSPxBUF is read, the BF bit is cleared. This data may be irrelevant if the SPI is only a transmitter. Generally, the MSSP interrupt is used to determine when the transmission/reception has completed. If the interrupt method is not going to be used, then software polling can be done to ensure that a write collision does not occur.

The SSPxSR is not directly readable or writable and can only be accessed by addressing the SSPxBUF register.





30.2.3 SPI HOST MODE

The host can initiate the data transfer at any time because it controls the SCK line. The host determines when the client (Processor 2, Figure 30-5) is to broadcast data by the software protocol.

In Host mode, the data is transmitted/received as soon as the SSPxBUF register is written to. If the SPI is only going to receive, the SDO output can be disabled (programmed as an input). The SSPxSR register will continue to shift in the signal present on the SDI pin at the programmed clock rate. As each byte is received, it will be loaded into the SSPxBUF register as if a normal received byte (interrupts and Status bits appropriately set). The clock polarity is selected by appropriately programming the CKP bit of the SSPxCON1 register and the CKE bit of the SSPxSTAT register. Then, this will give waveforms for SPI communication as shown in Figure 30-6, Figure 30-8, Figure 30-9 and Figure 30-10, where the MSB is transmitted first. In Host mode, the SPI clock rate (bit rate) is user programmable to be one of the following:

- Fosc/4 (or Tcy)
- Fosc/16 (or 4 * Tcy)
- Fosc/64 (or 16 * Tcy)
- Timer2 output/2
- Fosc/(4 * (SPPxADD + 1))

Figure 30-6 shows the waveforms for Host mode.

When the CKE bit is set, the SDO data are valid before there is a clock edge on SCK. The change of the input sample is shown based on the state of the SMP bit. The time when the SSPxBUF is loaded with the received data are shown.




FIGURE 30-6: SPI MODE WAVEFORM (HOST MODE)

30.2.4 SPI CLIENT MODE

In Client mode, the data are transmitted and received as external clock pulses appear on SCK. When the last bit is latched, the SSPxIF Interrupt Flag bit is set.

Before enabling the module in SPI Client mode, the clock line must match the proper Idle state. The clock line can be observed by reading the SCK pin. The Idle state is determined by the CKP bit of the SSPxCON1 register.

While in Client mode, the external clock is supplied by the external clock source on the SCK pin. This external clock must meet the minimum high and low times as specified in the electrical specifications.

While in Sleep mode, the client can transmit/receive data. The shift register is clocked from the SCK pin input and when a byte is received, the device will generate an interrupt. If enabled, the device will wake-up from Sleep.

30.2.4.1 Daisy-Chain Configuration

The SPI bus can sometimes be connected in a daisy-chain configuration. The first client output is connected to the second client input, the second client output is connected to the third client input, and so on. The final client output is connected to the host input. Each client sends out, during a second group of clock pulses, an exact copy of what was received during the first group of clock pulses. The whole chain acts as one large communication shift register. The daisy-chain feature only requires a single Client Select line from the host device.

Figure 30-7 shows the block diagram of a typical daisy-chain connection when operating in SPI mode.

In a daisy-chain configuration, only the most recent byte on the bus is required by the client. Setting the BOEN bit of the SSPxCON3 register will enable writes to the SSPxBUF register, even if the previous byte has not been read. This allows the software to ignore data that may not apply to it.

30.2.5 CLIENT SELECT SYNCHRONIZATION

The Client Select can also be used to synchronize communication. The Client Select line is held high until the host device is ready to communicate. When the Client Select line is pulled low, the client knows that a new transmission is starting.

If the client fails to receive the communication properly, it will be reset at the end of the transmission, when the Client Select line returns to a high state. The client is then ready to receive a new transmission when the Client Select line is pulled low again. If the Client Select line is not used, there is a risk that the client will eventually become out of sync with the host. If the client misses a bit, it will always be one bit off in future transmissions. Use of the Client Select line allows the client and host to align themselves at the beginning of each transmission.

The \overline{SS} pin allows a Synchronous Client mode. The SPI must be in Client mode with \overline{SS} pin control enabled (SSPxCON1<3:0> = 0100).

When the \overline{SS} pin is low, transmission and reception are enabled and the SDO pin is driven.


When the \overline{SS} pin goes high, the SDO pin is no longer driven, even if in the middle of a transmitted byte and becomes a floating output. External pull-up/pull-down resistors may be desirable depending on the application.


- Note 1: When the SPI is in Client mode with \overline{SS} pin control enabled (SSPxCON1<3:0> = 0100), the SPI module will reset if the \overline{SS} pin is set to VDD.
 - 2: When the SPI is used in Client mode with CKE set; the user must enable SS pin control.
 - **3:** While operated in SPI Client mode, the SMP bit of the SSPxSTAT register must remain clear.

When the SPI module resets, the bit counter is forced to '0'. This can be done by either forcing the SS pin to a high level or clearing the SSPEN bit.

PIC16(L)F18326/18346











FIGURE 30-10: SPI MODE WAVEFORM (CLIENT MODE WITH CKE = 1)



30.2.6 SPI OPERATION IN SLEEP MODE

In SPI Host mode, when the Sleep mode is selected, all module clocks are halted and the transmission/reception will remain in that state until the device wakes. After the device returns to Run mode, the module will resume transmitting and receiving data.

In SPI Client mode, the SPI Transmit/Receive Shift register operates asynchronously to the device. This allows the device to be placed in Sleep mode and data to be shifted into the SPI Transmit/Receive Shift register. When all eight bits have been received, the MSSP interrupt flag bit will be set and if enabled, will wake the device.

30.3 I²C Mode Overview

The Inter-Integrated Circuit (I^2C) bus is a multi-host serial data communication bus. Devices communicate in a host/client environment where the host devices initiate the communication. A client device is controlled through addressing.

The I²C bus specifies two signal connections:

- Serial Clock (SCL)
- Serial Data (SDA)

Figure 30-11 shows the block diagram of the MSSPx module when operating in I^2C mode.

Both the SCL and SDA connections are bidirectional open-drain lines, each requiring pull-up resistors for the supply voltage. Pulling the line to ground is considered a logical zero and letting the line float is considered a logical one.

Figure 30-2 and Figure 30-3 show a typical connection between two processors configured as host and client devices.

The I²C bus can operate with one or more host devices and one or more client devices.

There are four potential modes of operation for a given device:


- Host Transmit mode
 (host is transmitting data to a client)
- Host Receive mode (host is receiving data from a client)
- Client Transmit mode
 (client is transmitting data to a host)
- Client Receive mode (client is receiving data from the host)

To begin communication, the host device sends out a Start condition followed by the address byte of the client it intends to communicate with. This is followed by a single Read/Write bit, which determines whether the host intends to transmit to or receive data from the client device.

If the requested client exists on the bus, it will respond with an Acknowledge bit, otherwise known as an ACK. The host then continues in either transmit or receive data from the client device.

FIGURE 30-11: I²C HOST/

CLIENT CONNECTION



On the last byte of data communicated, the host device may end the transmission by sending a Stop <u>bit</u>. If the host device is in <u>Receive</u> mode, it sends a <u>NACK</u> in place of the last ACK bit. A Stop bit is indicated by a low-to-high transition of the SDA line while the SCL line is held high.

In some cases, the host may want to maintain control of the bus and re-initiate another transmission. If so, the host device may send a Restart condition in place of the Stop bit or last ACK bit when it is in Receive mode.

The I²C bus specifies three message protocols;

- Single message where a host writes data to a client.
- Single message where a host reads data from a client.
- Combined message where a host initiates a minimum of two writes, or two reads, or a combination of writes and reads, to one or more clients.

30.3.1 CLOCK STRETCHING

When a client device has not completed processing data, it can delay the transfer of more data through the process of clock stretching. An addressed client device may hold the SCL clock line low after receiving or sending a bit, indicating that it is not yet ready to continue. The host that is communicating with the client will attempt to raise the SCL line in order to transfer the next bit, but will detect that the clock line has not yet been released. Because the SCL connection is open-drain, the client has the ability to hold that line low until it is ready to continue communicating.

Clock stretching allows receivers that cannot keep up with a transmitter to control the flow of incoming data.

30.3.2 ARBITRATION

Each host device must monitor the bus for Start and Stop bits. If the device detects that the bus is busy, it cannot begin a new message until the bus returns to an Idle state.

However, two host devices may try to initiate a transmission on or about the same time. When this occurs, the process of arbitration begins. Each transmitter checks the level of the SDA data line and compares it to the level that it expects to find. The first transmitter to observe that the two levels do not match, loses arbitration, and must stop transmitting on the SDA line.

For example, if one transmitter holds the SDA line to a logical one (lets it float) and a second transmitter holds it to a logical zero (pulls it low), the result is that the SDA line will be low. The first transmitter then observes that the level of the line is different than expected and concludes that another transmitter is communicating.

The first transmitter to notice this difference is the one that loses arbitration and must stop driving the SDA line. If this transmitter is also a host device, it also must stop driving the SCL line. It then can monitor the lines for a Stop condition before trying to reissue its transmission. In the meantime, the other device that has not noticed any difference between the expected and actual levels on the SDA line continues with its original transmission.

Client Transmit mode can also be arbitrated, when a host addresses multiple clients, but this is less common.

30.4 I²C MODE OPERATION

All MSSP I²C communication is byte oriented and shifted out MSb first. Six SFR registers and two interrupt flags interface the module with the PIC[®] microcontroller and user software. Two pins, SDA and SCL, are exercised by the module to communicate with other external I²C devices.

30.4.1 BYTE FORMAT

All communication in I^2C is done in 9-bit segments. A byte is sent from a host to a client or vice-versa, followed by an Acknowledge bit sent back. After the eighth falling edge of the SCL line, the device outputting data on the SDA changes that pin to an input and reads in an acknowledge value on the next clock pulse.

The clock signal, SCL, is provided by the host. Data are valid to change while the SCL signal is low, and sampled on the rising edge of the clock. Changes on the SDA line while the SCL line is high define special conditions on the bus, explained below.

30.4.2 DEFINITION OF I²C TERMINOLOGY

There is language and terminology in the description of I^2C communication that have definitions specific to I^2C . That word usage is defined below and may be used in the rest of this document without explanation. This table was adapted from the Philips I^2C specification.

30.4.3 SDA AND SCL PINS

When selecting any I²C mode, the SCL and SDA pins may be set by the user to inputs by setting the appropriate TRIS bits.

Note: Any device pin can be selected for SDA and SCL functions with the PPS peripheral. These functions are bidirectional. The SDA input is selected with the SSPDATPPS registers. The SCL input is selected with the SSPCLKPPS registers. Outputs are selected with the RxyPPS registers. It is the user's responsibility to make the selections so that both the input and the output for each function is on the same pin.

30.4.4 SDA HOLD TIME

The hold time of the SDA pin is selected by the SDAHT bit of the SSPxCON3 register. Hold time is the time SDA is held valid after the falling edge of SCL. Setting the SDAHT bit selects a longer 300 ns minimum hold time and may help on buses with large capacitance.

TABLE 30-1: I ²	² C BUS TERMS
----------------------------	--------------------------

TABLE 30-1.	
TERM	Description
Transmitter	The device which shifts data out onto the bus.
Receiver	The device which shifts data in from the bus.
Host	The device that initiates a transfer, generates clock signals and terminates a transfer.
Client	The device addressed by the host.
Multi-host	A bus with more than one device that can initiate data transfers.
Arbitration	Procedure to ensure that only one host at a time controls the bus. Winning arbitration ensures that the message is not corrupted.
Synchronization	Procedure to synchronize the clocks of two or more devices on the bus.
Idle	No host is controlling the bus, and both SDA and SCL lines are high.
Active	Any time one or more host devices are controlling the bus.
Addressed Client	Client device that has received a matching address and is actively being clocked by a host.
Matching Address	Address byte that is clocked into a client that matches the value stored in SPPxADD.
Write Request	Client receives a matching address with R/W bit clear, and is ready to clock in data.
Read Request	Host sends an address byte with the R/\overline{W} bit set, indicating that it wishes to clock data out of the client. These data are the next and all following bytes until a Restart or Stop.
Clock Stretching	When a device on the bus hold SCL low to stall communication.
Bus Collision	Any time the SDA line is sampled low by the module while it is out- putting and expected high state.

30.4.5 START CONDITION

The I^2C specification defines a Start condition as a transition of SDA from a high to a low state while SCL line is high. A Start condition is always generated by the host and signifies the transition of the bus from an Idle to an Active state. Figure 30-12 shows wave forms for Start and Stop conditions.

30.4.6 STOP CONDITION

A Stop condition is a transition of the SDA line from low-to-high state while the SCL line is high.

Note: At least one SCL low time must appear before a Stop is valid, therefore, if the SDA line goes low then high again while the SCL line stays high, only the Start condition is detected.

30.4.7 RESTART CONDITION


A Restart is valid any time that a Stop is valid. A host can issue a Restart if it wishes to hold the bus after terminating the current transfer. A Restart has the same effect on the client that a Start would, resetting all client logic and preparing it to clock in an address. The host may want to address the same or another client. Figure 30-13 shows the wave form for a Restart condition.

In 10-bit Addressing Client mode a Restart is required for the host to clock data out of the addressed client. Once a client has been fully addressed, matching both high and low address bytes, the host can issue a Restart and the high address byte with the R/W bit set. The client logic will then hold the clock and prepare to clock out data.


30.4.8 START/STOP CONDITION INTERRUPT MASKING

The SCIE and PCIE bits of the SSPxCON3 register can enable the generation of an interrupt in Client modes that do not typically support this function. Client modes where interrupt on Start and Stop detect are already enabled, these bits will have no effect.

FIGURE 30-12: I²C START AND STOP CONDITIONS







30.4.9 ACKNOWLEDGE SEQUENCE

The ninth SCL pulse for any transferred byte in I^2C is dedicated as an Acknowledge. It allows receiving devices to respond back to the transmitter by pulling the SDA line low. The transmitter must release control of the line during this time to shift in the response. The Acknowledge (ACK) is an active-low signal, pulling the SDA line low indicates to the transmitter that the device has received the transmitted data and is ready to receive more.

The result of an \overline{ACK} is placed in the ACKSTAT bit of the SSPxCON2 register.

Client software, when the AHEN and DHEN bits are set, the clock is stretched, allowing the client time to change the ACK value before it is sent back to the transmitter. The ACKDT bit of the SSPxCON2 register is set/cleared to determine the response.

There are certain conditions where an ACK will not be sent by the client. If the BF bit of the SSPxSTAT register or the SSPOV bit of the SSPxCON1 register are set when a byte is received.

When the module is addressed, after the eighth falling edge of SCL on the bus, the ACKTIM bit of the SSPxCON3 register is set. The ACKTIM bit indicates the acknowledge time of the active bus. The ACKTIM Status bit is only active when the AHEN bit or DHEN bit is enabled.

30.5 I²C CLIENT MODE OPERATION

The MSSP Client mode operates in one of four modes selected by the SSPM bits of SSPxCON1 register. The modes can be divided into 7-bit and 10-bit Addressing mode. 10-bit Addressing modes operate the same as 7-bit with some additional overhead for handling the larger addresses.

Modes with Start and Stop bit interrupts operate the same as the other modes with SSPxIF additionally getting set upon detection of a Start, Restart, or Stop condition.

30.5.1 CLIENT MODE ADDRESSES

The SSPxADD register (Register 30-6) contains the Client mode address. The first byte received after a Start or Restart condition is compared against the value stored in this register. If the byte matches, the value is loaded into the SSPxBUF register and an interrupt is generated. If the value does not match, the module goes Idle and no indication is given to the software that anything happened.

The SSP Mask register (Register 30-5) affects the address matching process. See **Section 30.5.9** "SSP **Mask Register**" for more information.

30.5.1.1 I²C Client 7-bit Addressing Mode

In 7-bit Addressing mode, the LSb of the received data byte is ignored when determining if there is an address match.

30.5.1.2 I²C Client 10-bit Addressing Mode

In 10-bit Addressing mode, the first received byte is compared to the binary value of '1 1 1 1 0 A9 A8 0'. A9 and A8 are the two MSb's of the 10-bit address and stored in bits 2 and 1 of the SSPxADD register.

After the acknowledge of the high byte the UA bit is set and SCL is held low until the user updates SSPxADD with the low address. The low address byte is clocked in and all eight bits are compared to the low address value in SSPxADD. Even if there is not an address match; SSPIF and UA are set, and SCL is held low until SSPxADD is updated to receive a high byte again. When SSPxADD is updated the UA bit is cleared. This ensures the module is ready to receive the high address byte on the next communication.

A high and low address match as a write request is required at the start of all 10-bit addressing communication. A transmission can be initiated by issuing a Restart once the client is addressed, and clocking in the high address with the R/W bit set. The client hardware will then acknowledge the read request and prepare to clock out data. This is only valid for a client after it has received a complete high and low address byte match.

30.5.2 CLIENT RECEPTION

When the R/W bit of a matching received address byte is clear, the R/W bit of the SSPxSTAT register is cleared. The received address is loaded into the SSPxBUF register and acknowledged.

When the Overflow condition exists for a received address, then not Acknowledge is given. An Overflow condition is defined as either bit BF of the SSPxSTAT register is set, or bit SSPOV of the SSPxCON1 register is set. The BOEN bit of the SSPxCON3 register modifies this operation. For more information see Register 30-4.

An MSSP interrupt is generated for each transferred data byte. Flag bit, SSPxIF, must be cleared by software.

When the SEN bit of the SSPxCON2 register is set, SCL will be held low (clock stretch) following each received byte. The clock must be released by setting the CKP bit of the SSPxCON1 register.

30.5.2.1 7-bit Addressing Reception

This section describes a standard sequence of events for the MSSPx module configured as an I^2C client in 7-bit Addressing mode. Figure 30-14 and Figure 30-15 is used as a visual reference for this description.

This is a step-by-step process of what typically must be done to accomplish I^2C communication.

- 1. Start bit detected.
- 2. The S bit of SSPxSTAT is set; SSPxIF is set if interrupt on Start detect is enabled.
- 3. Matching address with R/\overline{W} bit clear is received.
- 4. The client pulls SDA low sending an ACK to the host, and sets SSPxIF bit.
- 5. Software clears the SSPxIF bit.
- 6. Software reads received address from SSPxBUF clearing the BF flag.
- 7. If SEN = 1; Client software sets CKP bit to release the SCL line.
- 8. The host clocks out a data byte.
- 9. Client drives SDA low sending an ACK to the host, and sets SSPxIF bit.
- 10. Software clears SSPxIF.
- 11. Software reads the received byte from SSPxBUF clearing BF.
- 12. Steps 8-12 are repeated for all received bytes from the host.
- 13. Host sends Stop condition, setting P bit of SSPx-STAT, and the bus goes Idle.

30.5.2.2 7-bit Reception with AHEN and DHEN

Client device reception with AHEN and DHEN set operate the same as without these options with extra interrupts and clock stretching added after the eighth falling edge of SCL. These additional interrupts allow time for the client software to decide whether it wants to \overline{ACK} the receive address or data byte.


This list describes the steps that need to be taken by client software to use these options for I^2C communication. Figure 30-16 displays a module using both address and data holding. Figure 30-17 includes the operation with the SEN bit of the SSPxCON2 register set.

- 1. The S bit of SSPxSTAT is set; SSPxIF is set if interrupt on Start detect is enabled.
- Matching address with R/W bit clear is clocked in. SSPxIF is set and CKP cleared after the eighth falling edge of SCL.
- 3. Client clears the SSPxIF.
- Client can look at the ACKTIM bit of the SSPxCON3 register to <u>determine</u> if the SSPxIF was after or before the ACK.
- 5. Client reads the address value from SSPxBUF, clearing the BF flag.
- 6. Client sets ACK value clocked out to the host by setting ACKDT.
- 7. Client releases the clock by setting CKP.
- 8. SSPxIF is set after an ACK, not after a NACK.
- 9. If SEN = 1 the client hardware will stretch the clock after the ACK.


10. Client clears SSPxIF.

Note: SSPxIF is still set after the ninth falling edge of SCL even if there is no clock stretching and BF has been cleared. Only if NACK is sent to host is SSPIF not set

- 11. SSPxIF set and CKP cleared after eighth falling edge of SCL for a received data byte.
- 12. Client looks at ACKTIM bit of SSPxCON3 to determine the source of the interrupt.
- 13. Client reads the received data from SSPxBUF clearing BF.
- 14. Steps 7-14 are the same for each received data byte.
- 15. Communication is ended by either the client sending an ACK = 1, or the host sending a Stop condition. If a Stop is sent and Interrupt on Stop Detect is disabled, the client will only know by polling the P bit of the SSPxSTAT register.



I²C CLIENT, 7-BIT ADDRESS, RECEPTION (SEN = 0, AHEN = 0, DHEN = 0) **FIGURE 30-14:**



DS40001839F-page 331

age 331





FIGURE 30-16: I²C CLIENT, 7-BIT ADDRESS, RECEPTION (SEN = 0, AHEN = 1, DHEN = 1)



on 8th falling edge of SCL

s

Р

30.5.3 CLIENT TRANSMISSION

When the R/W bit of the incoming address byte is set and an address match occurs, the R/W bit of the SSPxSTAT register is set. The received address is loaded into the SSPxBUF register, and an ACK pulse is sent by the client on the ninth bit.

Following the ACK, client hardware clears the CKP bit and the SCL pin is held low (see Section 30.5.6 "Clock Stretching" for more details). By stretching the clock, the host will be unable to assert another clock pulse until the client is done preparing the transmit data.

The transmit data must be loaded into the SSPxBUF register which also loads the SSPxSR register. Then, the SCL pin may be released by setting the CKP bit of the SSPxCON1 register. The eight data bits are shifted out on the falling edge of the SCL input. This ensures that the SDA signal is valid during the SCL high time.

The \overline{ACK} pulse from the host-receiver is latched on the rising edge of the ninth SCL input pulse. This \overline{ACK} value is copied to the ACKSTAT bit of the SSPxCON2 register. If ACKSTAT is set (not \overline{ACK}), then the data transfer is complete. When the not \overline{ACK} is latched by the client, the client goes Idle and waits for another occurrence of the Start bit. If the SDA line was low (\overline{ACK}), the next transmit data must be loaded into the SSPxBUF register. Again, the SCL pin must be released by setting bit CKP.

An MSSP interrupt is generated for each data transfer byte. The SSPxIF bit must be cleared by software and the SSPxSTAT register is used to determine the status of the byte. The SSPxIF bit is set on the falling edge of the ninth clock pulse.

30.5.3.1 Client Mode Bus Collision

A client receives a Read request and begins shifting data out on the SDA line. If a bus collision is detected and the SBCDE bit of the SSPxCON3 register is set, the BCLIF bit of the PIR register is set. Once a bus collision is detected, the client goes Idle and waits to be addressed again. User software can use the BCLIF bit to handle a client bus collision.

30.5.3.2 7-bit Transmission


A host device can transmit a read request to a client, and then clock data out of the client. The list below outlines what software for a client will need to do to accomplish a standard transmission. Figure 30-18 can be used as a reference to this list.

- 1. Host sends a Start condition on SDA and SCL.
- 2. The S bit of SSPxSTAT is set; SSPxIF is set if interrupt on Start detect is enabled.
- 3. Matching address with R/W bit set is received by the Client setting SSPxIF bit.
- 4. Client hardware generates an ACK and sets SSPxIF.
- 5. SSPxIF bit is cleared by user.
- 6. Software reads the received address from SSPxBUF, clearing BF.
- 7. R/\overline{W} is set so CKP was automatically cleared after the ACK.
- 8. The client software loads the transmit data into SSPxBUF.
- 9. CKP bit is set releasing SCL, allowing the host to clock the data out of the client.
- 10. SSPxIF is set after the \overline{ACK} response from the host is loaded into the ACKSTAT register.
- 11. SSPxIF bit is cleared.
- 12. The client software checks the ACKSTAT bit to see if the host wants to clock out more data.

Note 1:		the retch		ACKs	the	clock	will	be
2:	ris	ACKSTAT is the only bit updated on the rising edge of SCL (9th) rather than the falling.						

- 13. Steps 9-13 are repeated for each transmitted byte.
- 14. If the host sends a not ACK; the clock is not held, but SSPxIF is still set.
- 15. The host sends a Restart condition or a Stop.
- 16. The client is no longer addressed.





30.5.3.3 7-bit Transmission with Address Hold Enabled

Setting the AHEN bit of the SSPxCON3 register enables additional clock stretching and interrupt generation after the eighth falling edge of a received matching address. Once a matching address has been clocked in, CKP is cleared and the SSPxIF interrupt is set.


Figure 30-19 displays a standard waveform of a 7-bit address client transmission with AHEN enabled.

- 1. Bus starts Idle.
- Host sends Start condition; the S bit of SSPxSTAT is set; SSPxIF is set if interrupt on Start detect is enabled.
- Host sends matching address with R/W bit set. After the eighth falling edge of the SCL line the CKP bit is cleared and SSPxIF interrupt is generated.
- 4. Client software clears SSPxIF.
- Client software reads ACKTIM bit of SSPxCON3 register, and R/W and D/A of the SSPxSTAT register to determine the source of the interrupt.
- 6. Client reads the address value from the SSPxBUF register clearing the BF bit.
- Client software decides from this information if it wishes to ACK or not ACK and sets the ACKDT bit of the SSPxCON2 register accordingly.
- 8. Client sets the CKP bit releasing SCL.
- 9. Host clocks in the \overline{ACK} value from the client.
- 10. Client hardware automatically clears the CKP bit and sets SSPxIF after the ACK if the R/W bit is set.
- 11. Client software clears SSPxIF.
- 12. Client loads value to transmit to the host into SSPxBUF setting the BF bit.

Note: <u>SSPxBUF</u> cannot be loaded until after the ACK.

- 13. Client sets the CKP bit releasing the clock.
- 14. Host clocks out the data from the client and sends an ACK value on the ninth SCL pulse.
- 15. Client hardware copies the ACK value into the ACKSTAT bit of the SSPxCON2 register.
- 16. Steps 10-15 are repeated for each byte transmitted to the host from the client.
- 17. If the host sends a not ACK the client releases the bus allowing the host to send a Stop and end the communication.

Note: Host must send a not ACK on the last byte to ensure that the client releases the SCL line to receive a Stop.



ACKTIM is cleared

on 9th rising edge of SCL

C16(L)F18326/18346

ACKTIM

R/W D/A ACKTIM is set on 8th falling

edge of SCL

30.5.4 CLIENT MODE 10-BIT ADDRESS RECEPTION

This section describes a standard sequence of events for the MSSPx module configured as an I^2C client in 10-bit Addressing mode.

Figure 30-20 is used as a visual reference for this description.

This is a step-by-step process of what must be done by client software to accomplish I^2C communication.

- 1. Bus starts Idle.
- Host sends Start condition; S bit of SSPxSTAT is set; SSPxIF is set if interrupt on Start detect is enabled.
- 3. Host sends matching high address with R/W bit clear; UA bit of the SSPxSTAT register is set.
- 4. Client sends ACK and SSPxIF is set.
- 5. Software clears the SSPxIF bit.
- 6. Software reads received address from SSPxBUF clearing the BF flag.
- 7. Client loads low address into SSPxADD, releasing SCL.
- 8. Host sends matching low address byte to the client; UA bit is set.

Note: Updates to the SSPxADD register are not allowed until after the ACK sequence.

9. Client sends ACK and SSPxIF is set.


Note: If the low address does not match, SSPxIF and UA are still set so that the client software can set SSPxADD back to the high address. BF is not set because there is no match. CKP is unaffected.

- 10. Client clears SSPxIF.
- 11. Client reads the received matching address from SSPxBUF clearing BF.
- 12. Client loads high address into SSPxADD.
- Host clocks a data byte to the client and clocks out the clients ACK on the ninth SCL pulse; SSPxIF is set.
- 14. If SEN bit of SSPxCON2 is set, CKP is cleared by hardware and the clock is stretched.
- 15. Client clears SSPxIF.
- 16. Client reads the received byte from SSPxBUF clearing BF.
- 17. If SEN is set the client sets CKP to release the SCL.
- 18. Steps 13-17 repeat for each received byte.
- 19. Host sends Stop to end the transmission.

30.5.5 10-BIT ADDRESSING WITH ADDRESS OR DATA HOLD

Reception using 10-bit addressing with AHEN or DHEN set is the same as with 7-bit modes. The only difference is the need to update the SSPxADD register using the UA bit. All functionality, specifically when the CKP bit is cleared and SCL line is held low are the same. Figure 30-21 can be used as a reference of a client in 10-bit addressing with AHEN set.

Figure 30-22 shows a standard waveform for a client transmitter in 10-bit Addressing mode.



When SEN = 1;-

CKP is cleared after

9th falling edge of received byte

Set by software, releasing SCL

DS40001839F-page 339

CKP





FIGURE 30-21: I²C CLIENT, 10-BIT ADDRESS, RECEPTION (SEN = 0, AHEN = 1, DHEN = 0)



30.5.6 CLOCK STRETCHING

Clock stretching occurs when a device on the bus holds the SCL line low, effectively pausing communication. The client may stretch the clock to allow more time to handle data or prepare a response for the host device. A host device is not concerned with stretching as anytime it is active on the bus and not transferring data it is stretching. Any stretching done by a client is invisible to the host software and handled by the hardware that generates SCL.

The CKP bit of the SSPxCON1 register is used to control stretching in software. Any time the CKP bit is cleared, the module will wait for the SCL line to go low and then hold it. Setting CKP will release SCL and allow more communication.

30.5.6.1 Normal Clock Stretching

Following an ACK if the R/W bit of SSPxSTAT is set, a read request, the client hardware will clear CKP. This allows the client time to update SSPxBUF with data to transfer to the host. If the SEN bit of SSPxCON2 is set, the client hardware will always stretch the clock after the ACK sequence. Once the client is ready; CKP is set by software and communication resumes.

30.5.6.2 10-bit Addressing Mode

In 10-bit Addressing mode, when the UA bit is set, the clock is always stretched. This is the only time the SCL is stretched without CKP being cleared. SCL is released immediately after a write to SSPxADD.

Note: Previous versions of the module did not stretch the clock if the second address byte did not match.

30.5.6.3 Byte NACKing


When the AHEN bit of SSPxCON3 is set; CKP is cleared by hardware after the eighth falling edge of SCL for a received matching address byte. When the DHEN bit of SSPxCON3 is set; CKP is cleared after the eighth falling edge of SCL for received data.

Stretching after the eighth falling edge of SCL allows the client to look at the received address or data and decide if it wants to ACK the received data.

30.5.7 CLOCK SYNCHRONIZATION AND THE CKP BIT

Any time the CKP bit is cleared, the module will wait for the SCL line to go low and then hold it. However, clearing the CKP bit will not assert the SCL output low until the SCL output is already sampled low. Therefore, the CKP bit will not assert the SCL line until an external I^2C host device has already asserted the SCL line. The SCL output will remain low until the CKP bit is set and all other devices on the I^2C bus have released SCL. This ensures that a write to the CKP bit will not violate the minimum high time requirement for SCL (see Figure 30-23).

FIGURE 30-23: CLOCK SYNCHRONIZATION TIMING



30.5.8 GENERAL CALL ADDRESS SUPPORT

The addressing procedure for the I^2C bus is such that the first byte after the Start condition usually determines which device will be the client addressed by the host device. The exception is the general call address which can address all devices. When this address is used, all devices might, in theory, respond with an acknowledge.


The general call address is a reserved address in the I^2C protocol, defined as address 0x00. When the GCEN bit of the SSPxCON2 register is set, the client module will automatically ACK the reception of this address regardless of the value stored in SSPxADD. After the client clocks in an address of all zeros with

the R/\overline{W} bit clear, an interrupt is generated and client software can read SSPxBUF and respond. Figure 30-24 shows a general call reception sequence.

In 10-bit Address mode, the UA bit will not be set on the reception of the general call address. The client will prepare to receive the second byte as data, just as it would in 7-bit mode.

If the AHEN bit of the SSPxCON3 register is set, just as with any other address reception, the client hardware will stretch the clock after the eighth falling edge of SCL. The client must then set its ACKDT value and release the clock with communication progressing.

FIGURE 30-24: CLIENT MODE GENERAL CALL ADDRESS SEQUENCE



30.5.9 SSP MASK REGISTER

An SSP Mask (SPPxMSK) register (Register 30-5) is available in I²C Client mode as a mask for the value held in the SSPxSR register during an address comparison operation. A zero ('0') bit in the SSPxMSK register has the effect of making the corresponding bit of the received address a "don't care".

This register is reset to all '1's upon any Reset condition and, therefore, has no effect on standard SSP operation until written with a mask value.

The SSP Mask register is active during:

- 7-bit Address mode: address compare of A<7:1>.
- 10-bit Address mode: address compare of A<7:0> only. The SSP mask has no effect during the reception of the first (high) byte of the address.

30.6 I²C Host Mode

Host mode is enabled by setting and clearing the appropriate SSPM<3:0> bits in the SSPxCON1 register and by setting the SSPEN bit. In Host mode, the SDA and SCK pins must be configured as inputs. The MSSP peripheral hardware will override the output driver TRIS controls when necessary to drive the pins low.

Host mode of operation is supported by interrupt generation on the detection of the Start and Stop conditions. The Stop (P) and Start (S) bits are cleared from a Reset or when the MSSPx module is disabled. Control of the I^2C bus may be taken when the P bit is set, or the bus is Idle.

In Firmware Controlled Host mode, user code conducts all I²C bus operations based on Start and Stop bit condition detection. Start and Stop condition detection is the only active circuitry in this mode. All other communication is done by the user software directly manipulating the SDA and SCL lines.

The following events will cause the SSP Interrupt Flag bit, SSPxIF, to be set (SSP interrupt, if enabled):

- Start condition generation
- Stop condition generation
- Data transfer byte transmitted/received
- Acknowledge transmitted/received
- · Repeated Start generated
 - **Note 1:** The MSSPx module, when configured in I²C Host mode, does not allow queuing of events. For instance, the user is not allowed to initiate a Start condition and immediately write the SSPxBUF register to initiate transmission before the Start condition is complete. In this case, the SSPxBUF will not be written to and the WCOL bit will be set, indicating that a write to the SSPxBUF did not occur
 - 2: When in Host mode, Start/Stop detection is masked and an interrupt is generated when the SEN/PEN bit is cleared and the generation is complete.

30.6.1 I²C HOST MODE OPERATION

The host device generates all of the serial clock pulses and the Start and Stop conditions. A transfer is ended with a Stop condition or with a Repeated Start condition. Since the Repeated Start condition is also the beginning of the next serial transfer, the I^2C bus will not be released.

In Host Transmitter mode, serial data are output through SDA, while SCL outputs the serial clock. The first byte transmitted contains the client address of the receiving device (7 bits) and the Read/Write (R/W) bit. In this case, the R/W bit will be logic '0'. Serial data are transmitted eight bits at a time. After each byte is transmitted, an Acknowledge bit is received. Start and Stop conditions are output to indicate the beginning and the end of a serial transfer.


In Host Receive mode, the first byte transmitted contains the client address of the transmitting device (7 bits) and the R/W bit. In this case, the R/W bit will be logic '1'. Thus, the first byte transmitted is a 7-bit client address followed by a '1' to indicate the receive bit. Serial data are received via SDA, while SCL outputs the serial clock. Serial data are received eight bits at a time. After each byte is received, an Acknowledge bit is transmitted. Start and Stop conditions indicate the beginning and end of transmission.

A Baud Rate Generator is used to set the clock frequency output on SCL. See Section 30.7 "Baud Rate Generator" for more details.

30.6.2 CLOCK ARBITRATION

Clock arbitration occurs when the host, during any receive, transmit or Repeated Start/Stop condition, releases the SCL pin (SCL allowed to float high). When the SCL pin is allowed to float high, the Baud Rate Generator (BRG) is suspended from counting until the SCL pin is actually sampled high. When the SCL pin is sampled high, the Baud Rate Generator is reloaded with the contents of SSPxADD<7:0> and begins counting. This ensures that the SCL high time will always be at least one BRG rollover count in the event that the clock is held low by an external device (Figure 30-25).

FIGURE 30-25: BAUD RATE GENERATOR TIMING WITH CLOCK ARBITRATION



30.6.3 WCOL STATUS FLAG

If the user writes the SSPxBUF when a Start, Restart, Stop, Receive or Transmit sequence is in progress, the WCOL is set and the contents of the buffer are unchanged (the write does not occur). Any time the WCOL bit is set it indicates that an action on SSPxBUF was attempted while the module was not Idle.


Note: Because queuing of events is not allowed, writing to the lower five bits of SSPxCON2 is disabled until the Start condition is complete.

30.6.4 I²C HOST MODE START CONDITION TIMING

To initiate a Start condition (Figure 30-26), the user sets the Start Enable bit, SEN bit of the SSPxCON2 register. If the SDA and SCL pins are sampled high, the Baud Rate Generator is reloaded with the contents of SSPxADD<7:0> and starts its count. If SCL and SDA are both sampled high when the Baud Rate Generator times out (TBRG), the SDA pin is driven low. The action of the SDA being driven low while SCL is high is the Start condition and causes the S bit of the SSPxSTAT register to be set. Following this, the Baud Rate Generator is reloaded with the contents of SSPxADD<7:0> and resumes its count. When the Baud Rate Generator times out (TBRG), the SEN bit of the SSPxCON2 register will be automatically cleared by hardware; the Baud Rate Generator is suspended, leaving the SDA line held low and the Start condition is complete.

- Note 1: If at the beginning of the Start condition, the SDA and SCL pins are already sampled low, or if during the Start condition, the SCL line is sampled low before the SDA line is driven low, a bus collision occurs, the Bus Collision Interrupt Flag, BCLIF, is set, the Start condition is aborted and the l²C module is reset into its idle state.
 - **2:** The Philips I²C specification states that a bus collision cannot occur on a Start.

FIGURE 30-26: FIRST START BIT TIMING




30.6.5 I²C HOST MODE REPEATED START CONDITION TIMING

A Repeated Start condition (Figure 30-27) occurs when the RSEN bit of the SSPxCON2 register is programmed high and the host state machine is no longer active. When the RSEN bit is set, the SCL pin is asserted low. When the SCL pin is sampled low, the Baud Rate Generator is loaded and begins counting. The SDA pin is released (brought high) for one Baud Rate Generator count (TBRG). When the Baud Rate Generator times out, if SDA is sampled high, the SCL pin will be deasserted (brought high). When SCL is sampled high, the Baud Rate Generator is reloaded and begins counting. SDA and SCL must be sampled high for one TBRG. This action is then followed by assertion of the SDA pin (SDA = 0) for one TBRG while SCL is high. SCL is asserted low. Following this, the RSEN bit of the SSPxCON2 register will be automatically cleared and the Baud Rate Generator will not be reloaded, leaving the SDA pin held low. As soon as a Start condition is detected on the SDA and SCL pins, the S bit of the SSPxSTAT register will be set. The SSPxIF bit will not be set until the Baud Rate Generator has timed out.

Note 1:	If RSEN is programmed while any other					
	event is in progress, it will not take effect.					

- **2:** A bus collision during the Repeated Start condition occurs if:
 - SDA is sampled low when SCL goes from low-to-high.
 - SCL goes low before SDA is asserted low. This may indicate that another host is attempting to transmit a data '1'.

FIGURE 30-27: REPEATED START CONDITION WAVEFORM



30.6.6 I²C HOST MODE TRANSMISSION

Transmission of a data byte, a 7-bit address or the other half of a 10-bit address is accomplished by simply writing a value to the SSPxBUF register. This action will set the Buffer Full flag bit, BF, and allow the Baud Rate Generator to begin counting and start the next transmission. Each bit of address/data will be shifted out onto the SDA pin after the falling edge of SCL is asserted. SCL is held low for one Baud Rate Generator rollover count (TBRG). Data must be valid before SCL is released high. When the SCL pin is released high, it is held that way for TBRG. The data on the SDA pin must remain stable for that duration and some hold time after the next falling edge of SCL. After the eighth bit is shifted out (the falling edge of the eighth clock), the BF flag is cleared and the host releases SDA. This allows the client device being addressed to respond with an ACK bit during the ninth bit time if an address match occurred, or if data were received properly. The status of ACK is written into the ACKSTAT bit on the rising edge of the ninth clock. If the host receives an Acknowledge, the Acknowledge Status bit, ACKSTAT, is cleared. If not, the bit is set. After the ninth clock, the SSPIF bit is set and the host clock (Baud Rate Generator) is suspended until the next data byte is loaded into the SSPxBUF, leaving SCL low and SDA unchanged (Figure 30-28).

After the write to the SSPxBUF, each bit of the address will be shifted out on the falling edge of SCL until all seven address bits and the R/W bit are completed. On the falling edge of the eighth clock, the host will release the SDA pin, allowing the client to respond with an Acknowledge. On the falling edge of the ninth clock, the host will sample the SDA pin to see if the address was recognized by a client. The status of the ACK bit is loaded into the ACKSTAT Status bit of the SSPxCON2 register. Following the falling edge of the ninth clock transmission of the address, the SSPxIF is set, the BF flag is cleared and the Baud Rate Generator is turned off until another write to the SSPxBUF takes place, holding SCL low and allowing SDA to float.

30.6.6.1 BF Status Flag

In Transmit mode, the BF bit of the SSPxSTAT register is set when the CPU writes to SSPxBUF and is cleared when all eight bits are shifted out.

30.6.6.2 WCOL Status Flag

If the user writes the SSPxBUF when a transmit is already in progress (i.e., SSPxSR is still shifting out a data byte), the WCOL bit is set and the contents of the buffer are unchanged (the write does not occur).

WCOL must be cleared by software before the next transmission.


30.6.6.3 ACKSTAT Status Flag

In Transmit mode, the ACKSTAT bit of the SSPxCON2 register is cleared when the client has sent an Acknowledge ($\overline{ACK} = 0$) and is set when the client does not Acknowledge ($\overline{ACK} = 1$). A client sends an Acknowledge when it has recognized its address (including a general call), or when the client has properly received its data.

30.6.6.4 Typical Transmit Sequence

- 1. The user generates a Start condition by setting the SEN bit of the SSPxCON2 register.
- 2. SSPxIF is set by hardware on completion of the Start.
- 3. SSPxIF is cleared by software.
- 4. The MSSPx module will wait the required start time before any other operation takes place.
- 5. The user loads the SSPxBUF with the client address to transmit.
- 6. Address is shifted out the SDA pin until all eight bits are transmitted. Transmission begins as soon as SSPxBUF is written to.
- 7. The MSSPx module shifts in the ACK bit from the client device and writes its value into the ACKSTAT bit of the SSPxCON2 register.
- 8. The MSSPx module generates an interrupt at the end of the ninth clock cycle by setting the SSPxIF bit.
- 9. The user loads the SSPxBUF with eight bits of data.
- 10. Data are shifted out the SDA pin until all eight bits are transmitted.
- 11. The MSSPx module shifts in the ACK bit from the client device and writes its value into the ACKSTAT bit of the SSPxCON2 register.
- 12. Steps 8-11 are repeated for all transmitted data bytes.
- 13. The user generates a Stop or Restart condition by setting the PEN or RSEN bits of the SSPxCON2 register. Interrupt is generated once the Stop/Restart condition is complete.

FIGURE 30-28: I²C HOST MODE WAVEFORM (TRANSMISSION, 7 OR 10-BIT ADDRESS)



30.6.7 I²C HOST MODE RECEPTION

Host mode reception (Figure 30-29) is enabled by programming the Receive Enable bit, RCEN bit of the SSPxCON2 register.

Note:	The MSSPx module must be in an Idle				
	state before the RCEN bit is set or the				
	RCEN bit will be disregarded.				

The Baud Rate Generator begins counting and on each rollover, the state of the SCL pin changes (high-to-low/low-to-high) and data are shifted into the SSPxSR. After the falling edge of the eighth clock, the receive enable flag is automatically cleared, the contents of the SSPxSR are loaded into the SSPxBUF, the BF flag bit is set, the SSPxIF flag bit is set and the Baud Rate Generator is suspended from counting, holding SCL low. The MSSPx is now in Idle state awaiting the next command. When the buffer is read by the CPU, the BF flag bit is automatically cleared. The user can then send an Acknowledge bit at the end of reception by setting the Acknowledge Sequence Enable, ACKEN bit of the SSPxCON2 register.

30.6.7.1 BF Status Flag

In receive operation, the BF bit is set when an address or data byte is loaded into SSPxBUF from SSPxSR. It is cleared when the SSPxBUF register is read.

30.6.7.2 SSPOV Status Flag

In receive operation, the SSPOV bit is set when eight bits are received into the SSPxSR and the BF flag bit is already set from a previous reception.


30.6.7.3 WCOL Status Flag

If the user writes the SSPxBUF when a receive is already in progress (i.e., SSPxSR is still shifting in a data byte), the WCOL bit is set and the contents of the buffer are unchanged (the write does not occur).

30.6.7.4 Typical Receive Sequence:

- 1. The user generates a Start condition by setting the SEN bit of the SSPxCON2 register.
- 2. SSPxIF is set by hardware on completion of the Start.
- 3. SSPxIF is cleared by software.
- 4. User writes SSPxBUF with the client address to transmit and the R/W bit set.
- 5. Address is shifted out the SDA pin until all eight bits are transmitted. Transmission begins as soon as SSPxBUF is written to.
- 6. The MSSPx module shifts in the ACK bit from the client device and writes its value into the ACKSTAT bit of the SSPxCON2 register.
- 7. The MSSPx module generates an interrupt at the end of the ninth clock cycle by setting the SSPxIF bit.
- 8. User sets the RCEN bit of the SSPxCON2 register and the host clocks in a byte from the client.
- 9. After the eighth falling edge of SCL, SSPxIF and BF are set.
- 10. Host clears SSPxIF and reads the received byte from SSPxBUF, clears BF.
- 11. Host sets ACK value sent to client in ACKDT bit of the SSPxCON2 register and initiates the ACK by setting the ACKEN bit.
- 12. Host's ACK is clocked out to the client and SSPxIF is set.
- 13. User clears SSPIF.
- 14. Steps 8-13 are repeated for each received byte from the client.
- 15. Host sends a not ACK or Stop to end communication.

FIGURE 30-29: I²C HOST MODE WAVEFORM (RECEPTION, 7-BIT ADDRESS)



30.6.8 ACKNOWLEDGE SEQUENCE TIMING

An Acknowledge sequence is enabled by setting the Acknowledge Sequence Enable bit, ACKEN bit of the SSPxCON2 register. When this bit is set, the SCL pin is pulled low and the contents of the Acknowledge data bit are presented on the SDA pin. If the user wishes to generate an Acknowledge, then the ACKDT bit must be cleared. If not, the user must set the ACKDT bit before starting an Acknowledge sequence. The Baud Rate Generator then counts for one rollover period (TBRG) and the SCL pin is deasserted (pulled high). When the SCL pin is sampled high (clock arbitration), the Baud Rate Generator counts for TBRG. The SCL pin is then pulled low. Following this, the ACKEN bit is automatically cleared, the Baud Rate Generator is turned off and the MSSPx module then goes into Idle mode (Figure 30-30).

30.6.8.1 WCOL Status Flag

If the user writes the SSPxBUF when an Acknowledge sequence is in progress, then WCOL bit is set and the contents of the buffer are unchanged (the write does not occur).

30.6.9 STOP CONDITION TIMING

A Stop bit is asserted on the SDA pin at the end of a receive/transmit by setting the Stop Sequence Enable bit, PEN bit of the SSPxCON2 register. At the end of a receive/transmit, the SCL line is held low after the falling edge of the ninth clock. When the PEN bit is set, the host will assert the SDA line low. When the SDA line is sampled low, the Baud Rate Generator is reloaded and counts down to '0'. When the Baud Rate Generator times out, the SCL pin will be brought high and one TBRG (Baud Rate Generator rollover count) later, the SDA pin will be deasserted. When the SDA pin is sampled high while SCL is high, the P bit of the SSPxSTAT register is set. A TBRG later, the PEN bit is cleared and the SSPxIF bit is set (Figure 30-31).

30.6.9.1 WCOL Status Flag

If the user writes the SSPxBUF when a Stop sequence is in progress, then the WCOL bit is set and the contents of the buffer are unchanged (the write does not occur).

FIGURE 30-30: ACKNOWLEDGE SEQUENCE WAVEFORM





FIGURE 30-31: STOP CONDITION RECEIVE OR TRANSMIT MODE



30.6.10 SLEEP OPERATION

While in Sleep mode, the I²C client module can receive addresses or data and when an address match or complete byte transfer occurs, wake the processor from Sleep (if the MSSP interrupt is enabled).

30.6.11 EFFECTS OF A RESET

A Reset disables the MSSPx module and terminates the current transfer.

30.6.12 MULTI-HOST MODE

In Multi-Host mode, the interrupt generation on the detection of the Start and Stop conditions allows the determination of when the bus is free. The Stop (P) and Start (S) bits are cleared from a Reset or when the MSSPx module is disabled. Control of the I²C bus may be taken when the P bit of the SSPxSTAT register is set, or the bus is Idle, with both the S and P bits clear. When the bus is busy, enabling the SSP interrupt will generate the interrupt when the Stop condition occurs.

In multi-host operation, the SDA line must be monitored for arbitration to see if the signal level is the expected output level. This check is performed by hardware with the result placed in the BCL1IF bit.

The states where arbitration can be lost are:

- · Address Transfer
- Data Transfer
- · A Start Condition
- A Repeated Start Condition
- An Acknowledge Condition

30.6.13 MULTI-HOST COMMUNICATION, BUS COLLISION AND BUS ARBITRATION

Multi-Host mode support is achieved by bus arbitration. When the host outputs address/data bits onto the SDA pin, arbitration takes place when the host outputs a '1' on SDA, by letting SDA float high and another host asserts a '0'. When the SCL pin floats high, data may be stable. If the expected data on SDA are a '1' and the data sampled on the SDA pin are '0', then a bus collision has taken place. The host will set the Bus Collision Interrupt Flag, BCLIF and reset the I²C port to its Idle state (Figure 30-32).

If a transmit was in progress when the bus collision occurred, the transmission is halted, the BF flag is cleared, the SDA and SCL lines are deasserted and the SSPxBUF can be written to. When the user services the bus collision Interrupt Service Routine and if the l^2C bus is free, the user can resume communication by asserting a Start condition.


If a Start, Repeated Start, Stop or Acknowledge condition was in progress when the bus collision occurred, the condition is aborted, the SDA and SCL lines are deasserted and the respective control bits in the SSPxCON2 register are cleared. When the user services the bus collision Interrupt Service Routine and if the I^2C bus is free, the user can resume communication by asserting a Start condition.

The host will continue to monitor the SDA and SCL pins. If a Stop condition occurs, the SSPxIF bit will be set.

A write to the SSPxBUF will start the transmission of data at the first data bit, regardless of where the transmitter left off when the bus collision occurred.

In Multi-Host mode, the interrupt generation on the detection of Start and Stop conditions allows the determination of when the bus is free. Control of the I^2C bus can be taken when the P bit is set in the SSPxSTAT register, or the bus is Idle and the S and P bits are cleared.

FIGURE 30-32: BUS COLLISION TIMING FOR TRANSMIT AND ACKNOWLEDGE



PIC16(L)F18326/18346

30.6.13.1 Bus Collision During a Start Condition

During a Start condition, a bus collision occurs if:

- a) SDA or SCL are sampled low at the beginning of the Start condition (Figure 30-33).
- b) SCL is sampled low before SDA is asserted low (Figure 30-34).

During a Start condition, both the SDA and the SCL pins are monitored.

If the SDA pin is already low, or the SCL pin is already low, then all of the following occur:


- · the Start condition is aborted,
- the BCL1IF flag is set and
- the MSSPx module is reset to its Idle state (Figure 30-33).

The Start condition begins with the SDA and SCL pins deasserted. When the SDA pin is sampled high, the Baud Rate Generator is loaded and counts down. If the SCL pin is sampled low while SDA is high, a bus collision occurs because it is assumed that another host is attempting to drive a data '1' during the Start condition.


If the SDA pin is sampled low during this count, the BRG is reset and the SDA line is asserted early (Figure 30-35). If, however, a '1' is sampled on the SDA pin, the SDA pin is asserted low at the end of the BRG count. The Baud Rate Generator is then reloaded and counts down to zero; if the SCL pin is sampled as '0' during this time, a bus collision does not occur. At the end of the BRG count, the SCL pin is asserted low.

Note: The reason that bus collision is not a factor during a Start condition is that no two bus hosts can assert a Start condition at the exact same time. Therefore, one host will always assert SDA before the other. This condition does not cause a bus collision because the two hosts must be allowed to arbitrate the first address following the Start condition. If the address is the same, arbitration must be allowed to continue into the data portion, Repeated Start or Stop conditions.














30.6.13.2 Bus Collision During a Repeated Start Condition

During a Repeated Start condition, a bus collision occurs if:

- a) A low level is sampled on SDA when SCL goes from low level to high level (Case 1).
- b) SCL goes low before SDA is asserted low, indicating that another host is attempting to transmit a data '1' (Case 2).

When the user releases SDA and the pin is allowed to float high, the BRG is loaded with SSPxADD and counts down to zero. The SCL pin is then deasserted and when sampled high, the SDA pin is sampled. If SDA is low, a bus collision has occurred (i.e., another host is attempting to transmit a data '0', Figure 30-36). If SDA is sampled high, the BRG is reloaded and begins counting. If SDA goes from high-to-low before the BRG times out, no bus collision occurs because no two hosts can assert SDA at exactly the same time.

If SCL goes from high-to-low before the BRG times out and SDA has not already been asserted, a bus collision occurs. In this case, another host is attempting to transmit a data '1' during the Repeated Start condition, see Figure 30-37.

If, at the end of the BRG time-out, both SCL and SDA are still high, the SDA pin is driven low and the BRG is reloaded and begins counting. At the end of the count, regardless of the status of the SCL pin, the SCL pin is driven low and the Repeated Start condition is complete.

FIGURE 30-36: BUS COLLISION DURING A REPEATED START CONDITION (CASE 1)





FIGURE 30-37: BUS COLLISION DURING REPEATED START CONDITION (CASE 2)



30.6.13.3 Bus Collision During a Stop Condition

Bus collision occurs during a Stop condition if:

- a) After the SDA pin has been deasserted and allowed to float high, SDA is sampled low after the BRG has timed out (Case 1).
- b) After the SCL pin is deasserted, SCL is sampled low before SDA goes high (Case 2).

The Stop condition begins with SDA asserted low. When SDA is sampled low, the SCL pin is allowed to float. When the pin is sampled high (clock arbitration), the Baud Rate Generator is loaded with SSPxADD and counts down to zero. After the BRG times out, SDA is sampled. If SDA is sampled low, a bus collision has occurred. This is due to another host attempting to drive a data '0' (Figure 30-38). If the SCL pin is sampled low before SDA is allowed to float high, a bus collision occurs. This is another case of another host attempting to drive a data '0' (Figure 30-39).

FIGURE 30-38: BUS COLLISION DURING A STOP CONDITION (CASE 1)





FIGURE 30-39: BUS COLLISION DURING A STOP CONDITION (CASE 2)



30.7 Baud Rate Generator

The MSSPx module has a Baud Rate Generator available for clock generation in both I²C and SPI Host modes. The Baud Rate Generator (BRG) reload value is placed in the SSPxADD register (Register 30-6). When a write occurs to SSPxBUF, the Baud Rate Generator will automatically begin counting down.

Once the given operation is complete, the internal clock will automatically stop counting and the clock pin will remain in its last state.


An internal signal "Reload" in Figure 30-40 triggers the value from SSPxADD to be loaded into the BRG counter. This occurs twice for each oscillation of the module clock line. The logic dictating when the reload signal is asserted depends on the mode the MSSPx is being operated in.

Table 30-4demonstratesclockratesbasedoninstructioncyclesandtheBRGvalueloadedintoSPPxADD.

EQUATION 30-1: BAUD RATE GENERATOR

$$FCLOCK = \frac{FOSC}{(SSPxADD + 1)(4)}$$

FIGURE 30-40: BAUD RATE GENERATOR BLOCK DIAGRAM



Note: Values of 0x00, 0x01 and 0x02 are not valid for SSPxADD when used as a Baud Rate Generator for I²C. This is an implementation limitation.

Fosc	Fcy	BRG Value	FcLock (2 Rollovers of BRG)
32 MHz	8 MHz	13h	400 kHz
32 MHz	8 MHz	19h	308 kHz
32 MHz	8 MHz	4Fh	100 kHz
16 MHz	4 MHz	09h	400 kHz
16 MHz	4 MHz	0Ch	308 kHz
16 MHz	4 MHz	27h	100 kHz
4 MHz	1 MHz	09h	100 kHz

TABLE 30-2: MSSP CLOCK RATE W/BRG

Note: Refer to the I/O port electrical specifications in Table 35-4 to ensure the system is designed to support IOL requirements.

30.8 Register Definitions: MSSP Control

REGISTE	REGISTER 30-1: SSPxSTAT: SSP STATUS REGISTER							
R/W-0/0	R/W-0/0	R/HS/HC-0/0	R/HS/HC-0/0	R/HS/HC-0/0	R/HS/HC-0/0	R/HS/HC-0/0	R/HS/HC-0/0	
SMP	CKE ⁽¹⁾	D/A	P ⁽²⁾	S ⁽²⁾	R/W	UA	BF	
bit 7						·	bit 0	
Legend:						(-)		
R = Readab		W = Writable b		•	ented bit, read as		– <i>i</i>	
u = Bit is ur	•	x = Bit is unkno			t POR and BOR/	Value at all other	Resets	
'1' = Bit is s	et	ʻ0' = Bit is clea	red	HS/HC = Hard	lware set/clear			
bit 7	<u>SPI Host mod</u> 1 = Input data 0 = Input data <u>SPI Client mo</u> SMP must be <u>In I²C Host or</u> 1 = Slew rate	sampled at end sampled at midd	of data output ti lle of data outpu Pl is used in Clie for Standard Sj	ut time ent mode peed mode (100)		
bit 6	CKE : SPI Clo In SPI Host or 1 = Transmit of 0 = Transmit of In 1^2 C mode of 1 = Enable inp	ck Edge Select b <u>r Client mode:</u> occurs on transitio occurs on transitio	it (SPI mode on on from active to on from Idle to a nresholds are o	ly) ⁽¹⁾ o Idle clock state active clock state	e	'n		
bit 5	1 = Indicates	dress bit (I ² C moo that the last byte that the last byte	received or trar					
bit 4	1 = Indicates	P: Stop bit ⁽²⁾ (I ² C mode only. This bit is cleared when the MSSP module is disabled, SSPEN is cleared.) 1 = Indicates that a Stop bit has been detected last (this bit is '0' on Reset) 0 = Stop bit was not detected last						
bit 3	1 = Indicates	S: Start bit ⁽²⁾ (I ² C mode only. This bit is cleared when the MSSP module is disabled, SSPEN is cleared.) 1 = Indicates that a Start bit has been detected last (this bit is '0' on Reset) 0 = Start bit was not detected last						
bit 2	R/W : Read/W This bit holds match to the r $\ln 1^2 C$ Client n 1 = Read 0 = Write $\ln 1^2 C$ Host me 1 = Transmit 0 = Transmit	rite bit information the R/W bit infor next Start bit, Stop node:	n (I ² C mode on mation follo <u>win</u> o bit, or not ACP	g the last addre				
bit 1	UA: Update A 1 = Indicates 1	UA: Update Address bit (10-bit I ² C mode only) 1 = Indicates that the user needs to update the address in the SPPxADD register 0 = Address does not need to be updated						
bit 0	<u>Receive (SPI</u> 1 = Receive c 0 = Receive n <u>Transmit (I</u> ² C 1 = Data trans	 BF: Buffer Full Status bit <u>Receive (SPI and I²C modes):</u> Receive complete, SSPxBUF is full Receive not complete, SSPxBUF is empty <u>Transmit (I²C mode only):</u> Data transmit in progress (does not include the ACK and Stop bits), SPPxBUF is full Data transmit complete (does not include the ACK and Stop bits), SPPxBUF is empty 						
Note 1: 2:	Polarity of clock sta This bit is cleared o			-				

R/C/HS-0/0	R/C/HS-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
WCOL	SSPOV ⁽¹⁾	SSPEN	CKP		SSPM	<3:0>	
bit 7	•		1				bit (
Legend:							
R = Readable	bit	W = Writable	bit	U = Unimplen	nented bit, read	as '0'	
u = Bit is unch	anged	x = Bit is unk			at POR and BO		
'1' = Bit is set		'0' = Bit is cle	ared	HS = Bit is se	t by hardware	C = User clea	ired
bit 7		-			nitting the previo	ous word (mus	t be cleared i
bit 6	$\frac{\text{In SPI mode:}}{1 = \text{Anew byt}}$ the data in the SPPx is not set (must be 0 = No overfil In I ² C mode: 1 = A byte is	n SSPSR are lo BUF, even if or since each nev cleared in softv ow received while fransmit mode	nile the SPPxB st. Overflow ca ly transmitting v reception (an vare). the SPPxBUF	n only occur in C data, to avoid s d transmission)	Il holding the prev Client mode. In Cl etting overflow. I is initiated by wr holding the prev).	lient mode, the (n Host mode, th iting to the SPF	user must rea ne overflow bi PxBUF registe
bit 5	 SSPEN: Synchronous Serial Port Enable bit In both modes, when enabled, the following pins must be properly configured as input or output In <u>SPI mode</u>: 1 = Enables serial port and configures SCK, SDO, SDI and SS as the source of the serial PORT pins⁽¹⁾ 0 = Disables serial port and configures these pins as I/O PORT pins <u>In I²C mode</u>: 1 = Enables the serial port and configures the SDA and SCL pins as the source of the serial PORT pins 0 = Disables serial port and configures these pins as I/O PORT pins 						PORT pins ⁽²⁾
bit 4	$\frac{\text{In SPI mode:}}{1 = \text{Idle state}}$ $0 = \text{Idle state}$ $\frac{\text{In I}^2 \text{C Client n}}{\text{SCL release of }}$ $1 = \text{Enable closed}$	control ock ck low (clock s ode:	igh level ow level	to ensure data	setup time.)		

REGISTER 30-2: SSPxCON1: SSP CONTROL REGISTER 1 (CONTINUED)

- bit 3-0 SSPM<3:0>: Synchronous Serial Port Mode Select bits 1111 = I^2C Client mode, 10-bit address with Start and Stop bit interrupts enabled 1110 = I^2C Client mode, 7-bit address with Start and Stop bit interrupts enabled 1101 = Reserved 1100 = Reserved $1011 = I^2C$ firmware controlled Host mode (client idle) 1010 = SPI Host mode, clock = Fosc/(4 * (SPPxADD+1))⁽⁵⁾ 1001 = Reserved $1000 = I^2C$ Host mode, clock = Fosc / (4 * (SPPxADD+1))⁽⁴⁾ $0111 = I^2C$ Client mode, 10-bit address $0110 = I^2C$ Client mode, 7-bit address 0101 = SPI Client mode, clock = SCK pin, SS pin control disabled, SS can be used as I/O pin 0100 = SPI Client mode, clock = SCK pin, \overline{SS} pin control enabled 0011 = SPI Host mode, clock = T2 match/2 0010 = SPI Host mode, clock = Fosc/64 0001 = SPI Host mode, clock = Fosc/16 0000 = SPI Host mode, clock = Fosc/4
- **Note 1:** In Host mode, the overflow bit is not set since each new reception (and transmission) is initiated by writing to the SPPxBUF register.
 - **2:** When enabled, these pins must be properly configured as input or output. Use SSP1SSPPS, SSP1CLKPPS, SSP1DATPPS, and RxyPPS to select the pins.
 - **3:** When enabled, the SDA and SCL pins must be configured as inputs. Use SSPxCLKPPS, SSPxDATPPS, and RxyPPS to select the pins.
 - 4: SPPxADD values of 0, 1 or 2 are not supported for I²C mode.
 - 5: SPPxADD value of 0 is not supported. Use SSPM = 0000 instead.

R/W-0/0	R/HS/HC-0	R/W-0/0	R/S/HC-0/0	R/S/HC-0/0	R/S/HC-0/0	R/S/HC-0/0	R/S/HC-0/0	
GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	
bit 7				•			bit C	
Legend:								
R = Readab	le hit	W = Writable	bit	II – Unimpler	nented bit, read	1 26 'O'		
u = Bit is un		x = Bit is unk		-	at POR and BO		thar Pasata	
(1) = Bit is set	0	0' = Bit is cle			d by hardware			
1 - Dit 13 30	<i></i>		aleu		a by naroware	0 – 03el 3el		
bit 7	1 = Enable in		general call a	ent mode only) ddress (0x00 d	or 00h) is receiv	red in the SSPS	SR	
bit 6	1 = Acknowle	ACKSTAT: Acknowledge Status bit (in I ² C mode only) 1 = Acknowledge was not received 0 = Acknowledge was received						
bit 5	ACKDT: Ackr	nowledge Data	bit (in I ² C mod	de only)				
	In Receive me Value transmi 1 = Not Ackno 0 = Acknowle	itted when the owledge	user initiates a	an Acknowledg	e sequence at t	the end of a rec	ceive	
bit 4	<u>In Host Recei</u> 1 = Initiate <i>A</i> Automati	ve mode:	sequence on y hardware.	bit (in I ² C Hosi SDA and S	t mode only) CL pins, and	transmit ACk	(DT data bit	
bit 3	RCEN: Recei	ve Enable bit	(in I ² C Host mo	ode only)				
	1 = Enables F 0 = Receive i	Receive mode dle	for I ² C	.,				
bit 2	PEN: Stop Co	ondition Enable	e bit (in I ² C Ho	st mode only)				
	1 = Initiate St 0 = Stop cond		n SDA and SC	L pins. Automa	atically cleared	by hardware.		
bit 1	RSEN: Repea	ated Start Con	dition Enable b	oit (in I ² C Host	mode only)			
		 1 = Initiate Repeated Start condition on SDA and SCL pins. Automatically cleared by hardware. 0 = Repeated Start condition Idle 						
bit 0	SEN: Start Condition Enable/Stretch Enable bit							
	0 = Start cond	art condition o dition Idle	n SDA and SC	L pins. Automa	atically cleared	by hardware.		
				ent transmit ar	nd client receive	e (stretch enabl	ed)	
	or bits ACKEN, R et (no spooling) a				is not in the idle	e state, these bi	ts may not be	

REGISTER 30-3: SSPxCON2: SSPx CONTROL REGISTER 2 (I²C MODE ONLY)⁽¹⁾

REGISTE	ER 30-4: SSPx	CON3: SSP C							
R-0/0		R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0		
ACKTIN	A ⁽³⁾ PCIE	SCIE	BOEN	SDAHT	SBCDE	AHEN	DHEN		
bit 7							bit (
Legend:									
R = Read	lable bit	W = Writable	bit	U = Unimpler	nented bit, read	as '0'			
	unchanged	x = Bit is unkr			at POR and BO		ther Resets		
'1' = Bit is	•	'0' = Bit is clea							
		-							
bit 7	ACKTIM: Ac	knowledge Time	e Status bit (l ²	² C mode only) ⁽	3)				
	1 = Indicates	s the I ² C bus is i	n an Acknowle	edge sequence	e, set on eighth		SCL clock		
		cknowledge sec	-			clock			
bit 6		Condition Interru	•		()				
		nterrupt on deten ection interrupts							
bit 5	•	Condition Interru			()				
DI U		nterrupt on dete	-		•				
		ection interrupts							
bit 4	BOEN: Buffe	er Overwrite Ena	able bit						
	In SPI Client								
		xBUF updates of w byte is recei							
		CON1 register i							
		node and SPI H	<u>ost mode:</u>						
	This bit i <u>In I²C Client</u>	s ignored.							
		PxBUF is update	ed and \overline{ACK} is	s generated fo	r a received ad	dress/data byte	e, ignoring th		
	state	e of the SSPOV	bit only if the	BF bit = 0.		,	, 0 0		
		PxBUF is only up			-				
bit 3		A Hold Time Sel	•						
		n of 300 ns hold		0	U U				
bit 2			 0 = Minimum of 100 ns hold time on SDA after the falling edge of SCL SBCDE: Client Mode Bus Collision Detect Enable bit (I²C Client mode only) 						
Dit L			ollision Detect	•	•	nlv)			
		ing edge of SCI		t Enable bit (I ²	C Client mode o	• /	high state the		
	BCL1IF bit o	ing edge of SCI f the PIR1 regis	L, SDA is san	t Enable bit (l ² 0 npled low whe	C Client mode on the module is	• /	nigh state, the		
			L, SDA is san ter is set, and	t Enable bit (l ² 0 npled low whe	C Client mode on the module is	• /	nigh state, the		
	1 = Enable c 0 = Client bu	f the PIR1 regis lient bus collisic ls collision interr	L, SDA is san ter is set, and on interrupts rupts are disat	t Enable bit (I ² npled low whe bus goes idle bled	C Client mode on the module is	• /	nigh state, th		
bit 1	1 = Enable c 0 = Client bu AHEN: Addr	f the PIR1 regis lient bus collisic is collision interr ess Hold Enable	L, SDA is san ter is set, and on interrupts upts are disat e bit (I ² C Clier	t Enable bit (l ² npled low whe bus goes idle bled nt mode only)	C Client mode c n the module is	s outputting a h	-		
bit 1	1 = Enable c 0 = Client bu AHEN: Addr 1 = Followin	f the PIR1 regis lient bus collisic is collision interr ess Hold Enable g the eighth fal	L, SDA is san ter is set, and on interrupts upts are disat e bit (I ² C Clier ling edge of S	t Enable bit (I ² npled low whe bus goes idle bled ht mode only) SCL for a mate	C Client mode c n the module is ching received a	s outputting a h	-		
bit 1	1 = Enable c 0 = Client bu AHEN: Addr 1 = Followin SSPCO	f the PIR1 regis lient bus collisic is collision interr ess Hold Enable g the eighth fal N1 register will l	L, SDA is san ter is set, and on interrupts upts are disat be bit (I ² C Clier ling edge of S be cleared and	t Enable bit (I ² npled low whe bus goes idle bled ht mode only) SCL for a mate	C Client mode c n the module is ching received a	s outputting a h	-		
	1 = Enable c 0 = Client bu AHEN: Addr 1 = Followin SSPCO 0 = Address	f the PIR1 regis lient bus collisic is collision interr ess Hold Enable g the eighth fal N1 register will I holding is disab	L, SDA is san ter is set, and on interrupts rupts are disat e bit (I ² C Clier ling edge of S oe cleared and led	t Enable bit (I ² npled low whe bus goes idle bled ht mode only) SCL for a mate d the SCL will I	C Client mode c n the module is ching received a	s outputting a h	-		
bit 1 bit 0	1 = Enable c 0 = Client bu AHEN: Addre 1 = Followin SSPCO 0 = Address DHEN: Data	f the PIR1 regis lient bus collisic is collision interr ess Hold Enable g the eighth fal N1 register will l	L, SDA is san ter is set, and on interrupts upts are disat bit (I ² C Clier ling edge of S be cleared and led t (I ² C Client m	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mato d the SCL will I	C Client mode c n the module is ching received a be held low.	address byte; (CKP bit of th		
	 1 = Enable of 0 = Client but AHEN: Address 1 = Following 0 = Address DHEN: Data 1 = Following bit of the 	f the PIR1 regis lient bus collisio is collision interr ess Hold Enable g the eighth fal N1 register will I holding is disab Hold Enable bit g the eighth falli SSPCON1 reg	L, SDA is san ter is set, and on interrupts upts are disate bit (I ² C Clier ling edge of S be cleared and led t (I ² C Client m ng edge of SC	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mate d the SCL will I node only) CL for a receive	C Client mode c n the module is ching received a be held low.	address byte; (CKP bit of the		
	 1 = Enable of 0 = Client but AHEN: Address 1 = Following 0 = Address DHEN: Data 1 = Following bit of the 	f the PIR1 regis dient bus collision is collision interr ess Hold Enable g the eighth fal N1 register will h holding is disab Hold Enable bit g the eighth falli	L, SDA is san ter is set, and on interrupts upts are disate bit (I ² C Clier ling edge of S be cleared and led t (I ² C Client m ng edge of SC	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mate d the SCL will I node only) CL for a receive	C Client mode c n the module is ching received a be held low.	address byte; (CKP bit of th		
	 1 = Enable of 0 = Client but AHEN: Address 1 = Following SSPCO 0 = Address DHEN: Data 1 = Following bit of the 0 = Data hole For daisy-chained 	f the PIR1 regis lient bus collisio is collision interr ess Hold Enable g the eighth fall holding is disab Hold Enable bit g the eighth falli e SSPCON1 reg ding is disabled	L, SDA is san ter is set, and on interrupts upts are disate bit (I ² C Clien ling edge of So be cleared and led t (I ² C Client m ng edge of SO ister and SCL allows the use	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mato d the SCL will I node only) CL for a receive is held low.	C Client mode c n the module is ching received a be held low. ed data byte; cli but the last rece	address byte; (ent hardware c	CKP bit of the lears the CKI		
bit 0	 1 = Enable of 0 = Client but AHEN: Address 1 = Following SSPCO 0 = Address DHEN: Data 1 = Following bit of the 0 = Data hole For daisy-chained when a new byte 	f the PIR1 regis lient bus collisio is collision interr ess Hold Enable g the eighth fall holding is disab Hold Enable bit g the eighth falli e SSPCON1 reg ding is disabled	L, SDA is san ter is set, and on interrupts upts are disate bit (I ² C Clien ling edge of So be cleared and led t (I ² C Client m ng edge of SO ister and SCL allows the use	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mato d the SCL will I node only) CL for a receive is held low.	C Client mode c n the module is ching received a be held low. ed data byte; cli but the last rece	address byte; (ent hardware c	CKP bit of the lears the CKI		
bit 0	 1 = Enable of 0 = Client but AHEN: Address 1 = Following SSPCO 0 = Address DHEN: Data 1 = Following bit of the 0 = Data hole For daisy-chained 	f the PIR1 regis lient bus collisio is collision interr ess Hold Enable g the eighth fal holding is disab Hold Enable bit g the eighth falli e SSPCON1 reg ding is disabled I SPI operation; is received and	L, SDA is san ter is set, and on interrupts upts are disate bit (I ² C Clien ling edge of So be cleared and led t (I ² C Client m ng edge of SO jister and SCL allows the use BF = 1, but ha	t Enable bit (I ² npled low whe bus goes idle bled nt mode only) SCL for a mato d the SCL will I node only) CL for a receive is held low.	C Client mode of n the module is ching received a be held low. ed data byte; cli out the last rece ues to write the	address byte; (ent hardware c ived byte. SSP most recent by	CKP bit of the lears the CKI OV is still set te to		

REGISTER 30-4: SSPxCON3: SSP CONTROL REGISTER 3

R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1	R/W-1/1		
			SSPxM	ISK<7:0>					
bit 7							bit 0		
Legend:									
R = Readable bit W = Writable bit				U = Unimplen	nented bit, read	l as '0'			
u = Bit is unchanged x = Bit is unknown				-n/n = Value at POR and BOR/Value at all other Resets					
'1' = Bit is set		'0' = Bit is cle	ared						
bit 7-1		7:1>: Mask bits				0 -			
	1 = The rec	eived address b	it n is compar	ed to SPPxADI	D <n> to detect</n>	I [∠] C address m	atch		
	• • • • • • • •	eived address b							
bit 0 SSPxMSK<0>: Mask bit for I ² C Client mode, 10-bit Address									
I ² <u>C Client mode, 10-bit addres</u> s (SSPM<3:0> = 0111 or 1111):									
		eived address b				I ² C address ma	atch		
	0 = The rec	eived address b	it 0 is not use	d to detect I ² C	address match				
	<u>l²C Client m</u>	ode, 7-bit addre	<u>ss:</u>						

REGISTER 30-5: SSPxMSK: SSP MASK REGISTER

/W-0/0 R	/W-0/0 R/	/W-0/0 F	R/W-0/0 I	R/W-0/0	R/W-0/0	R/W-0/0	
SSPxADD<7:0>							
bit 7 bit 0							
/							

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

Host mode:

bit 7-0	SSPxADD<7:0>: Baud Rate Clock Divider bits
	SCL pin clock period = ((ADD<7:0> + 1) *4)/Fosc

10-bit Client mode – Most Significant Address Byte:

MSK0 bit is ignored.

- bit 7-3 **Not used:** Unused for Most Significant Address Byte. Bit state of this register is a "don't care". Bit pattern sent by host is fixed by I²C specification and must be equal to '11110'. However, those bits are compared by hardware and are not affected by the value in this register.
- bit 2-1 SSPxADD<2:1>: Two Most Significant bits of 10-bit address
- bit 0 Not used: Unused in this mode. Bit state is a "don't care".

10-bit Client mode – Least Significant Address Byte:

bit 7-0 SSPxADD<7:0>: Eight Least Significant bits of 10-bit address

7-bit Client mode:

bit 0 Not used: Unused in this mode. Bit state is a "don't care".

REGISTER 30-7: SSPxBUF: MSSP BUFFER REGISTER

R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	R/W-x/u	
TV/VV-A/U	TV VV-A/U	T (/ V V-A/U			TV/V-A/U	TV/VV-A/U	TV/VV-A/U	
			SSPxB	UF<7:0>				
bit 7							bit 0	
Legend:								
R = Readable	bit	W = Writable	bit	U = Unimpler	nented bit, read	as '0'		
u = Bit is unchanged x = Bit is unknown			nown	-n/n = Value at POR and BOR/Value at all other Resets				

bit 7-0 SSPxBUF<7:0>: MSSP Buffer bits

'1' = Bit is set

TABLE 30-3: SUMMARY OF REGISTERS ASSOCIATED WITH MSSPx

'0' = Bit is cleared

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	—	_	TRISA5	TRISA4	_(3)	TRISA2	TRISA1	TRISA0	143
ANSELA	_	_	ANSA5	ANSA4	—	ANSA2	ANSA1	ANSA0	144
INLVLA ⁽¹⁾	_	_	INLVLA5	INLVLA4	INLVLA3	INLVLA2	INLVLA1	INLVLA0	146
TRISB ⁽²⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_		—	149
ANSELB ⁽²⁾	ANSB7	ANSB6	ANSB5	ANSB4	—	_	_	—	150
INLVLB ⁽²⁾	INLVLB7	INLVLB6	INLVLB5	INLVLB4	_	_	_	_	152
TRISC	TRISC7 ⁽²⁾	TRISC6 ⁽²⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽²⁾	ANSC6 ⁽²⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
INLVLC ⁽¹⁾	INLVLC7 ⁽²⁾	INLVLC6 ⁽²⁾	INLVLC5	INLVLC4	INLVLC3	INLVLC2	INLVLC1	INLVLC0	159
INTCON	GIE	PEIE	_	_	—	—	_	INTEDG	100
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
PIR2	TMR6IF	C2IF	C1IF	NVMIF	SSP2IF	BCL2IF	TMR4IF	NCO1IF	108
PIE2	TMR6IE	C2IE	C1IE	NVMIE	SSP2IE	BCL2IE	TMR4IE	NCO1IE	103
SSPxSTAT	SMP	CKE	D/Ā	Р	S	R/W	UA	BF	360
SSPxCON1	WCOL	SSPOV	SSPEN	CKP		SSPN	<3:0>		361
SSPxCON2	GCEN	ACKSTAT	ACKDT	ACKEN	RCEN	PEN	RSEN	SEN	363
SSPxCON3	ACKTIM	PCIE	SCIE	BOEN	SDAHT	SBCDE	AHEN	DHEN	364
SSPxMSK				SSPxMS	K<7:0>				365
SSPxADD				SSPxAD	D<7:0>				365
SSPxBUF				SSPxBU	F<7:0>				366
SSPxCLKPPS	—	_			SSF	xCLKPPS<	4:0>		162
SSPxDATPPS	_	—	_		SSF	xDATPPS<	4:0>		162
SSPxSSPPS	_	—	_		SSI	PxSSPPS<4	:0>		162

Legend: — = Unimplemented location, read as '0'. Shaded cells are not used by the MSSP module

Note 1: When using designated I^2C pins, the associated pin values in INLVLx will be ignored.

2: PIC16(L)F18346 only.

3: Unimplemented, read as '1'.

31.0 ENHANCED UNIVERSAL SYNCHRONOUS ASYNCHRONOUS RECEIVER TRANSMITTER (EUSART1)

The Enhanced Universal Synchronous Asynchronous Receiver Transmitter (EUSART1) module is a serial I/O communications peripheral. It contains all the clock generators, shift registers and data buffers necessary to perform an input or output serial data transfer independent of device program execution. The EUSART1, also known as a Serial Communications Interface (SCI), can be configured as a full-duplex asynchronous system or half-duplex synchronous system. **Full-Duplex** mode is useful for communications with peripheral systems, such as CRT terminals and personal computers. Half-Duplex Synchronous mode is intended for communications with peripheral devices, such as A/D or D/A integrated circuits, serial EEPROMs or other microcontrollers. These devices typically do not have internal clocks for baud rate generation and require the external clock signal provided by a host synchronous device.

The EUSART1 module includes the following capabilities:

- · Full-duplex asynchronous transmit and receive
- Two-character input buffer
- One-character output buffer
- Programmable 8-bit or 9-bit character length
- Address detection in 9-bit mode
- Input buffer overrun error detection
- · Received character framing error detection
- · Half-duplex synchronous host
- Half-duplex synchronous client
- Programmable clock polarity in synchronous modes
- Sleep operation

The EUSART1 module implements the following additional features, making it ideally suited for use in Local Interconnect Network (LIN) bus systems:


- Automatic detection and calibration of the baud rate
- Wake-up on Break reception
- 13-bit Break character transmit

Block diagrams of the EUSART1 transmitter and receiver are shown in Figure 31-1 and Figure 31-2.

The EUSART1 transmit output (TX_out) is available to the TX/CK pin and internally to the following peripherals:


• Configurable Logic Cell (CLC)

FIGURE 31-1: EUSART1 TRANSMIT BLOCK DIAGRAM



PIC16(L)F18326/18346





The operation of the EUSART1 module is controlled through three registers:

- Transmit Status and Control (TX1STA)
- Receive Status and Control (RC1STA)
- Baud Rate Control (BAUD1CON)

These registers are detailed in Register 31-1, Register 31-2 and Register 31-3, respectively.

The RX and CK input pins are selected with the RXPPS and CKPPS registers, respectively. TX, CK, and DT output pins are selected with each pin's RxyPPS register. Since the RX input is coupled with the DT output in Synchronous mode, it is the user's responsibility to select the same pin for both of these functions when operating in Synchronous mode. The EUSART1 control logic will control the data direction drivers automatically.

31.1 EUSART1 Asynchronous Mode

The EUSART1 transmits and receives data using the standard non-return-to-zero (NRZ) format. NRZ is implemented with two levels: a VOH Mark state which represents a '1' data bit, and a VoL Space state which represents a '0' data bit. NRZ refers to the fact that consecutively transmitted data bits of the same value stay at the output level of that bit without returning to a neutral level between each bit transmission. An NRZ transmission port idles in the Mark state. Each character transmission consists of one Start bit followed by eight or nine data bits and is always terminated by one or more Stop bits. The Start bit is always a space and the Stop bits are always marks. The most common data format is eight bits. Each transmitted bit persists for a period of 1/(Baud Rate). An on-chip dedicated 8-bit/16-bit Baud Rate Generator is used to derive standard baud rate frequencies from the system oscillator. See Table 31-3 for examples of baud rate configurations.

The EUSART1 transmits and receives the LSb first. The EUSART1's transmitter and receiver are functionally independent, but share the same data format and baud rate. Parity is not supported by the hardware, but can be implemented in software and stored as the ninth data bit.

31.1.1 EUSART1 ASYNCHRONOUS TRANSMITTER

The EUSART1 transmitter block diagram is shown in Figure 31-1. The heart of the transmitter is the serial Transmit Shift Register (TSR), which is not directly accessible by software. The TSR obtains its data from the transmit buffer, which is the TX1REG register.

31.1.1.1 Enabling the Transmitter

The EUSART1 transmitter is enabled for asynchronous operations by configuring the following three control bits:

- TXEN = 1
- SYNC = 0
- SPEN = 1

All other EUSART1 control bits are assumed to be in their default state.

Setting the TXEN bit of the TX1STA register enables the transmitter circuitry of the EUSART1. Clearing the SYNC bit of the TX1STA register configures the EUSART1 for asynchronous operation. Setting the SPEN bit of the RC1STA register enables the EUSART1 and automatically configures the TX/CK I/O pin as an output. If the TX/CK pin is shared with an analog peripheral, the analog I/O function must be disabled by clearing the corresponding ANSEL bit.

Note: The TXIF Transmitter Interrupt flag is set when the TXEN Enable bit is set.

31.1.1.2 Transmitting Data

A transmission is initiated by writing a character to the TX1REG register. If this is the first character, or the previous character has been completely flushed from the TSR, the data in the TX1REG are immediately transferred to the TSR register. If the TSR still contains all or part of a previous character, the new character data are held in the TX1REG until the Stop bit of the previous character has been transmitted. The pending character in the TX1REG is then transferred to the TSR in one TCY immediately following the Stop bit sequence commences immediately following the transfer of the data to the TSR from the TX1REG.

31.1.1.3 Transmit Data Polarity

The polarity of the transmit data can be controlled with the SCKP bit of the BAUD1CON register. The default state of this bit is '0' which selects high true transmit ldle and data bits. Setting the SCKP bit to '1' will invert the transmit data resulting in low true ldle and data bits. The SCKP bit controls transmit data polarity in Asynchronous mode only. In Synchronous mode, the SCKP bit has a different function. See Section 31.4.1.2 "Clock Polarity".

31.1.1.4 Transmit Interrupt Flag

The TXIF Interrupt Flag bit of the PIR1 register is set whenever the EUSART1 transmitter is enabled and no character is being held for transmission in the TX1REG. In other words, the TXIF bit is only clear when the TSR is busy with a character and a new character has been queued for transmission in the TX1REG. The TXIF Flag bit is not cleared immediately upon writing TX1REG. TXIF becomes valid in the second instruction cycle following the write execution. Polling TXIF immediately following the TX1REG write will return invalid results. The TXIF bit is read-only, it cannot be set or cleared by software.

The TXIF interrupt can be enabled by setting the TXIE Interrupt Enable bit of the PIE1 register. However, the TXIF Flag bit will be set whenever the TX1REG is empty, regardless of the state of TXIE Enable bit.

To use interrupts when transmitting data, set the TXIE bit only when there are more data to send. Clear the TXIE Interrupt Enable bit upon writing the last character of the transmission to the TX1REG.

31.1.1.5 TSR Status

The TRMT bit of the TX1STA register indicates the status of the TSR register. This is a read-only bit. The TRMT bit is set when the TSR register is empty and is cleared when a character is transferred to the TSR register from the TX1REG. The TRMT bit remains clear until all bits have been shifted out of the TSR register. No interrupt logic is tied to this bit, so the user has to poll this bit to determine the TSR status.

Note:	The TSR register is not mapped in data
	memory, so it is not available to the user.

31.1.1.6 Transmitting 9-bit Characters

The EUSART1 supports 9-bit character transmissions. When the TX9 bit of the TX1STA register is set, the EUSART1 will shift nine bits out for each character transmitted. The TX9D bit of the TX1STA register is the ninth, and Most Significant data bit. When transmitting 9-bit data, the TX9D data bit must be written before writing the eight Least Significant bits into the TX1REG. All nine bits of data will be transferred to the TSR shift register immediately after the TX1REG is written.

A special 9-bit Address mode is available for use with multiple receivers. See **Section 31.1.2.7** "Address **Detection**" for more information on the Address mode.

31.1.1.7 Asynchronous Transmission Setup

- Initialize the SP1BRGH, SP1BRGL register pair and the BRGH and BRG16 bits to achieve the desired baud rate (see Section 31.3 "EUSART1 Baud Rate Generator (BRG)").
- 2. Enable the asynchronous serial port by clearing the SYNC bit and setting the SPEN bit.
- 3. If 9-bit transmission is desired, set the TX9 control bit. A set ninth data bit will indicate that the eight Least Significant data bits are an address when the receiver is set for address detection.
- 4. Set SCKP bit if inverted transmit is desired.
- 5. Enable the transmission by setting the TXEN control bit. This will cause the TXIF interrupt bit to be set.
- If interrupts are desired, set the TXIE Interrupt Enable bit of the PIE1 register. An interrupt will occur immediately provided that the GIE and PEIE bits of the INTCON register are also set.
- 7. If 9-bit transmission is selected, the ninth bit may be loaded into the TX9D data bit.
- 8. Load 8-bit data into the TX1REG register. This will start the transmission.





FIGURE 31-3: ASYNCHRONOUS TRANSMISSION



31.1.2 EUSART1 ASYNCHRONOUS RECEIVER

The Asynchronous mode is typically used in RS-232 systems. The receiver block diagram is shown in Figure 31-2. The data are received on the RX/DT pin and drives the data recovery block. The data recovery block is actually a high-speed shifter operating at 16 times the baud rate, whereas the serial Receive Shift Register (RSR) operates at the bit rate. When all eight or nine bits of the character have been shifted in, they are immediately transferred to a two character First-In First-Out (FIFO) memory. The FIFO buffering allows reception of two complete characters and the start of a third character before software must start servicing the EUSART1 receiver. The FIFO and RSR registers are not directly accessible by software. Access to the received data is via the RC1REG register.

31.1.2.1 Enabling the Receiver

The EUSART1 receiver is enabled for asynchronous operation by configuring the following three control bits:

- CREN = 1
- SYNC = 0
- SPEN = 1

All other EUSART1 control bits are assumed to be in their default state.

Setting the CREN bit of the RC1STA register enables the receiver circuitry of the EUSART1. Clearing the SYNC bit of the TX1STA register configures the EUSART1 for asynchronous operation. Setting the SPEN bit of the RC1STA register enables the EUSART1. The programmer must set the corresponding TRIS bit to configure the RX/DT I/O pin as an input.

Note: If the RX/DT function is on an analog pin, the corresponding ANSEL bit must be cleared for the receiver to function.

31.1.2.2 Receiving Data

The receiver data recovery circuit initiates character reception on the falling edge of the first bit. The first bit, also known as the Start bit, is always a zero. The data recovery circuit counts one-half bit time to the center of the Start bit and verifies that the bit is still a zero. If it is not a zero, then the data recovery circuit aborts character reception, without generating an error, and resumes looking for the falling edge of the Start bit. If the Start bit zero verification succeeds, then the data recovery circuit counts a full bit time to the center of the next bit. The bit is then sampled by a majority detect circuit and the resulting '0' or '1' is shifted into the RSR. This repeats until all data bits have been sampled and shifted into the RSR. One final bit time is measured and the level sampled. This is the Stop bit, which is always a '1'. If the data recovery circuit samples a '0' in the Stop bit position then a framing error is set for this character, otherwise the framing error is cleared for this character. See Section 31.1.2.4 "Receive Framing Error" for more information on framing errors.

Immediately after all data bits and the Stop bit have been received, the character in the RSR is transferred to the EUSART1 receive FIFO and the RCIF Interrupt Flag bit of the PIR1 register is set. The top character in the FIFO is transferred out of the FIFO by reading the RC1REG register.

Note:	If the receive FIFO is overrun, no additional
	characters will be received until the
	Overrun condition is cleared. See
	Section 31.1.2.5 "Receive Overrun
	Error" for more information on overrun
	errors.

31.1.2.3 Receive Interrupts

The RCIF Interrupt Flag bit of the PIR1 register is set whenever the EUSART1 receiver is enabled and there is an unread character in the receive FIFO. The RCIF Interrupt Flag bit is read-only, it cannot be set or cleared by software.

RCIF interrupts are enabled by setting all of the following bits:

- RCIE, Interrupt Enable bit of the PIE1 register
- PEIE, Peripheral Interrupt Enable bit of the INTCON register
- GIE, Global Interrupt Enable bit of the INTCON register

The RCIF Interrupt Flag bit will be set when there is an unread character in the FIFO, regardless of the state of interrupt enable bits.

31.1.2.4 Receive Framing Error

Each character in the receive FIFO buffer has a corresponding framing error Status bit. A framing error indicates that a Stop bit was not seen at the expected time. The framing error status is accessed via the FERR bit of the RC1STA register. The FERR bit represents the status of the top unread character in the receive FIFO. Therefore, the FERR bit must be read before reading the RC1REG.

The FERR bit is read-only and only applies to the top unread character in the receive FIFO. A framing error (FERR = 1) does not preclude reception of additional characters. It is not necessary to clear the FERR bit. Reading the next character from the FIFO buffer will advance the FIFO to the next character and the next corresponding framing error.

The FERR bit can be forced clear by clearing the SPEN bit of the RC1STA register which resets the EUSART1. Clearing the CREN bit of the RC1STA register does not affect the FERR bit. A framing error by itself does not generate an interrupt.

Note: If all receive characters in the receive FIFO have framing errors, repeated reads of the RC1REG will not clear the FERR bit.

31.1.2.5 Receive Overrun Error

The receive FIFO buffer can hold two characters. An overrun error will be generated if a third character, in its entirety, is received before the FIFO is accessed. When this happens the OERR bit of the RC1STA register is set. The characters already in the FIFO buffer can be read but no additional characters will be received until the error is cleared. The error must be cleared by either clearing the CREN bit of the RC1STA register or by resetting the EUSART1 by clearing the SPEN bit of the RC1STA register.

31.1.2.6 Receiving 9-bit Characters

The EUSART1 supports 9-bit character reception. When the RX9 bit of the RC1STA register is set the EUSART1 will shift nine bits into the RSR for each character received. The RX9D bit of the RC1STA register is the ninth and Most Significant data bit of the top unread character in the receive FIFO. When reading 9-bit data from the receive FIFO buffer, the RX9D data bit must be read before reading the eight Least Significant bits from the RC1REG.

31.1.2.7 Address Detection

A special Address Detection mode is available for use when multiple receivers share the same transmission line, such as in RS-485 systems. Address detection is enabled by setting the ADDEN bit of the RC1STA register.

Address detection requires 9-bit character reception. When address detection is enabled, only characters with the ninth data bit set will be transferred to the receive FIFO buffer, thereby setting the RCIF interrupt bit. All other characters will be ignored.

Upon receiving an address character, user software determines if the address matches its own. Upon address match, user software must disable address detection by clearing the ADDEN bit before the next Stop bit occurs. When user software detects the end of the message, determined by the message protocol used, software places the receiver back into the Address Detection mode by setting the ADDEN bit.

31.1.2.8 Asynchronous Reception Setup

- Initialize the SP1BRGH, SP1BRGL register pair and the BRGH and BRG16 bits to achieve the desired baud rate (see Section 31.3 "EUSART1 Baud Rate Generator (BRG)").
- 2. Clear the ANSEL bit for the RX pin (if applicable).
- 3. Enable the serial port by setting the SPEN bit. The SYNC bit must be clear for asynchronous operation.
- If interrupts are desired, set the RCIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- 5. If 9-bit reception is desired, set the RX9 bit.
- 6. Enable reception by setting the CREN bit.
- 7. The RCIF Interrupt Flag bit will be set when a character is transferred from the RSR to the receive buffer. An interrupt will be generated if the RCIE Interrupt Enable bit was also set.
- 8. Read the RC1STA register to get the error flags and, if 9-bit data reception is enabled, the ninth data bit.
- 9. Get the received eight Least Significant data bits from the receive buffer by reading the RC1REG register.
- 10. If an overrun occurred, clear the OERR flag by clearing the CREN Receiver Enable bit.

ASYNCHRONOUS RECEPTION

FIGURE 31-5:

31.1.2.9 9-bit Address Detection Mode Setup

This mode is typically used in RS-485 systems. To set up an Asynchronous Reception with Address Detect Enable:

- Initialize the SP1BRGH, SP1BRGL register pair and the BRGH and BRG16 bits to achieve the desired baud rate (see Section 31.3 "EUSART1 Baud Rate Generator (BRG)").
- 2. Clear the ANSEL bit for the RX pin (if applicable).
- 3. Enable the serial port by setting the SPEN bit. The SYNC bit must be clear for asynchronous operation.
- If interrupts are desired, set the RCIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- 5. Enable 9-bit reception by setting the RX9 bit.
- 6. Enable address detection by setting the ADDEN bit.
- 7. Enable reception by setting the CREN bit.
- 8. The RCIF Interrupt Flag bit will be set when a character with the ninth bit set is transferred from the RSR to the receive buffer. An interrupt will be generated if the RCIE Interrupt Enable bit was also set.
- 9. Read the RC1STA register to get the error flags. The ninth data bit will always be set.
- 10. Get the received eight Least Significant data bits from the receive buffer by reading the RC1REG register. Software determines if this is the device's address.
- 11. If an overrun occurred, clear the OERR flag by clearing the CREN receiver enable bit.
- 12. If the device has been addressed, clear the ADDEN bit to allow all received data into the receive buffer and generate interrupts.

	bit / bit 0 / bit 1 / \int	bit 7/8/ Stop bit / bit 0 bit	$\begin{array}{c} \begin{array}{c} \begin{array}{c} \\ \end{array} \\ \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \begin{array}{c} \\ \end{array} \begin{array}{c} \\ \end{array} \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \end{array} \begin{array}{c} \\ \end{array} \begin{array}{c} \\ \end{array} \end{array} \end{array} \end{array} \begin{array}{c} \\ \end{array} \end{array} \end{array} \end{array} \begin{array}{c} \\ \end{array} \end{array} \end{array} \end{array} \end{array} \begin{array}{c} \\ \end{array} $	bitXbit 7	7/8/ Stop bit
Rcv Shift Reg	(7		(I
Rcv Buffer Reg.	<u>)</u>)	Word 1 RC1REG)) Word 2))	
RCIDL -		RC1REG	RC1REG	7	¦
		; L			4
Read Rcv Buffer Reg.				(
RC1REG	<u>)</u>)		<u>)</u>)	<u>)</u>)	:)
RCIF	(((
(Interrupt Flag)	<u>)</u>)		<u>)</u>)	<u> </u>	
OERR bit _	((((
CREN	$\frac{1}{1}$			$\frac{1}{1}$	5
-))		<u>)</u>)	<u>)</u>)	/
Note: This ti	ming diagram shows three word	Is appearing on the RX input	The RC1REG (receive buff	fer) is read after th	ne third word

31.2 Clock Accuracy with Asynchronous Operation

The factory calibrates the internal oscillator block output (INTOSC). However, the INTOSC frequency may drift as VDD or temperature changes, and this directly affects the asynchronous baud rate. Two methods may be used to adjust the baud rate clock, but both require a reference clock source of some kind.

The first (preferred) method uses the OSCTUNE register to adjust the INTOSC output. Adjusting the value in the OSCTUNE register allows for fine resolution changes to the system clock source. See Section 7.2.2.3 "Internal Oscillator Frequency Adjustment" for more information.

The other method adjusts the value in the Baud Rate Generator. This can be done automatically with the Auto-Baud Detect feature (see Section 31.3.1 "Auto-Baud Detect"). There may not be fine enough resolution when adjusting the Baud Rate Generator to compensate for a gradual change in the peripheral clock frequency.

31.3 EUSART1 Baud Rate Generator (BRG)

The Baud Rate Generator (BRG) is an 8-bit or 16-bit timer that is dedicated to the support of both the asynchronous and synchronous EUSART1 operation. By default, the BRG operates in 8-bit mode. Setting the BRG16 bit of the BAUD1CON register selects 16-bit mode.

The SP1BRGH, SP1BRGL register pair determines the period of the free running baud rate timer. In Asynchronous mode the multiplier of the baud rate period is determined by both the BRGH bit of the TX1STA register and the BRG16 bit of the BAUD1CON register. In Synchronous mode, the BRGH bit is ignored.

Table 31-1 contains the formulas for determining the baud rate. Example 31-1 provides a sample calculation for determining the baud rate and baud rate error.

Typical baud rates and error values for various asynchronous modes have been computed for the user's convenience and are shown in Table 31-3. It may be advantageous to use the high baud rate (BRGH = 1), or the 16-bit BRG (BRG16 = 1) to reduce the baud rate error. The 16-bit BRG mode is used to achieve slow baud rates for fast oscillator frequencies.

Writing a new value to the SP1BRGH, SP1BRGL register pair causes the BRG timer to be reset (or cleared). This ensures that the BRG does not wait for a timer overflow before outputting the new baud rate.


If the system clock is changed during an active receive operation, a receive error or data loss may result. To avoid this problem, check the status of the RCIDL bit to make sure that the receive operation is Idle before changing the system clock.

EXAMPLE 31-1: CALCULATING BAUD RATE ERROR

For a device with Fosc of 16 MHz, desired baud rate of 9600, Asynchronous mode, 8-bit SPR1BRG:

 $Desired Baud Rate = \frac{FOSC}{64([SPBRGH:SPBRGL] + 1)}$

Solving for SP1BRGH:SP1BRGL:



31.3.1 AUTO-BAUD DETECT

The EUSART1 module supports automatic detection and calibration of the baud rate.

In the Auto-Baud Detect (ABD) mode, the clock to the BRG is reversed. Rather than the BRG clocking the incoming RX signal, the RX signal is timing the BRG. The Baud Rate Generator is used to time the period of a received 55h (ASCII "U") which is the Sync character for the LIN bus. The unique feature of this character is that it has five rising edges including the Stop bit edge.

Setting the ABDEN bit of the BAUD1CON register starts the auto-baud calibration sequence. While the ABD sequence takes place, the EUSART1 state machine is held in Idle. On the first rising edge of the receive line, after the Start bit, the SPBRG begins counting up using the BRG counter clock as shown in Figure 31-6. The fifth rising edge will occur on the RX pin at the end of the eighth bit period. At that time, an accumulated value totaling the proper BRG period is left in the SP1BRGH, SP1BRGL register pair, the ABDEN bit is automatically cleared and the RCIF interrupt flag is set. The value in RC1REG needs to be read to clear the RCIF interrupt. RC1REG content must be discarded. When calibrating for modes that do not use the SP1BRGH register the user can verify that the SP1BRGL register did not overflow by checking for 00h in the SP1BRGH register.

The BRG auto-baud clock is determined by the BRG16 and BRGH bits as shown in Table 31-1. During ABD, both the SP1BRGH and SP1BRGL registers are used as a 16-bit counter, independent of the BRG16 bit setting. While calibrating the baud rate period, the SP1BRGH and SP1BRGL registers are clocked at 1/8th the BRG base clock rate. The resulting byte measurement is the average bit time when clocked at full speed.


- Note 1: If the WUE bit is set with the ABDEN bit, auto-baud detection will occur on the byte following the Break character (see Section 31.3.3 "Auto-Wake-up on Break").
 - 2: It is up to the user to determine that the incoming character baud rate is within the range of the selected BRG clock source. Some combinations of oscillator frequency and EUSART1 baud rates are not possible.
 - 3: During the auto-baud process, the auto-baud counter starts counting at one. Upon completion of the auto-baud sequence, to achieve maximum accuracy, subtract 1 from the SP1BRGH:SP1BRGL register pair.

TABLE 31-1: BRG COUNTER CL	_OCK RATES
----------------------------	-------------------

BRG16	BRGH	BRG Base Clock	BRG ABD Clock
0	0	Fosc/64	Fosc/512
0	1	Fosc/16	Fosc/128
1	0	Fosc/16	Fosc/128
1	1	Fosc/4	Fosc/32

Note: During the ABD sequence, SP1BRGL and SP1BRGH registers are both used as a 16-bit counter, independent of the BRG16 setting.

FIGURE 31-6: AUTOMATIC BAUD RATE CALIBRATION



31.3.2 AUTO-BAUD OVERFLOW

During the course of automatic-baud detection, the ABDOVF bit of the BAUDxCON register will be set if the baud rate counter overflows before the fifth rising edge is detected on the RX pin. The ABDOVF bit indicates that the counter has exceeded the maximum count that can fit in the 16 bits of the SPxBRGH:SPxBRGL register pair. The Overflow condition will set the RCIF flag. The counter continues to count until the fifth rising edge is detected on the RX pin. The RCIDL bit will remain false ('0') until the fifth rising edge at which time the RCIDL bit will be set. If the RCREG is read after the overflow occurs but before the fifth rising edge, then the fifth rising edge will set the RCIF again.

Terminating the auto-baud process early to clear an Overflow condition will prevent proper detection of the sync character fifth rising edge. If any falling edges of the sync character have not yet occurred when the ABDEN bit is cleared, then those will be falsely detected as Start bits. The following steps are recommended to clear the Overflow condition:

- 1. Read RCREG to clear RCIF
- 2. If RCIDL is zero, then wait for RCIF and repeat step 1
- 3. Clear the ABDOVF bit

31.3.3 AUTO-WAKE-UP ON BREAK

During Sleep mode, all clocks to the EUSART1 are suspended. Because of this, the Baud Rate Generator is inactive and a proper character reception cannot be performed. The Auto-Wake-up feature allows the controller to wake up due to activity on the RX/DT line. This feature is available only in Asynchronous mode.

The Auto-Wake-up feature is enabled by setting the WUE bit of the BAUD1CON register. Once set, the normal receive sequence on RX/DT is disabled, and the EUSART1 remains in an Idle state, monitoring for a wake-up event independent of the CPU mode. A wake-up event consists of a high-to-low transition on the RX/DT line. (This coincides with the start of a Sync Break or a wake-up signal character for the LIN protocol.)

The EUSART1 module generates an RCIF interrupt coincident with the wake-up event. The interrupt is generated synchronously to the Q clocks in normal CPU operating modes (Figure 31-7), and asynchronously if the device is in Sleep mode (Figure 31-8). The Interrupt condition is cleared by reading the RC1REG register.

The WUE bit is automatically cleared by the low-to-high transition on the RX line at the end of the Break. This signals to the user that the Break event is over. At this point, the EUSART1 module is in Idle mode waiting to receive the next character.

31.3.3.1 Special Considerations

Break Character

To avoid character errors or character fragments during a wake-up event, the wake-up character must be all zeros.

When the wake-up is enabled the function works independent of the low time on the data stream. If the WUE bit is set and a valid nonzero character is received, the low time from the Start bit to the first rising edge will be interpreted as the wake-up event. The remaining bits in the character will be received as a fragmented character and subsequent characters can result in framing or overrun errors.

Therefore, the initial character in the transmission must be all '0's. This must be ten or more bit times, 13-bit times recommended for LIN bus, or any number of bit times for standard RS-232 devices.

Oscillator Start-up Time


Oscillator start-up time must be considered, especially in applications using oscillators with longer start-up intervals (i.e., LP, XT or HS/PLL mode). The Sync Break (or wake-up signal) character must be of sufficient length, and be followed by a sufficient interval, to allow enough time for the selected oscillator to start and provide proper initialization of the EUSART1.


WUE Bit


The wake-up event causes a receive interrupt by setting the RCIF bit. The WUE bit is cleared in hardware by a rising edge on RX/DT. The Interrupt condition is then cleared in software by reading the RC1REG register and discarding its contents.

To ensure that no actual data are lost, check the RCIDL bit to verify that a receive operation is not in process before setting the WUE bit. If a receive operation is not occurring, the WUE bit may then be set just prior to entering the Sleep mode.









31.3.4 BREAK CHARACTER SEQUENCE

The EUSART1 module has the capability of sending the special Break character sequences that are required by the LIN bus standard. A Break character consists of a Start bit, followed by 12 $^{\circ}$ bits and a Stop bit.

To send a Break character, set the SENDB and TXEN bits of the TX1STA register. The Break character transmission is then initiated by a write to the TX1REG. The value of data written to TX1REG will be ignored and all '0's will be transmitted.

The SENDB bit is automatically reset by hardware after the corresponding Stop bit is sent. This allows the user to preload the transmit FIFO with the next transmit byte following the Break character (typically, the Sync character in the LIN specification).

The TRMT bit of the TX1STA register indicates when the transmit operation is Active or Idle, just as it does during normal transmission. See Figure 31-9 for the timing of the Break character sequence.

31.3.4.1 Break and Sync Transmit Sequence

The following sequence will start a message frame header made up of a Break, followed by an auto-baud Sync byte. This sequence is typical of a LIN bus host.

- 1. Configure the EUSART1 for the desired mode.
- 2. Set the TXEN and SENDB bits to enable the Break sequence.
- 3. Load TX1REG with a dummy character to initiate transmission (the value is ignored).
- 4. Write '55h' to TX1REG to load the Sync character into the transmit FIFO buffer.
- 5. After the Break has been sent, the SENDB bit is reset by hardware and the Sync character is then transmitted.

When the TX1REG becomes empty, as indicated by the TXIF, the next data byte can be written to TX1REG.

31.3.5 RECEIVING A BREAK CHARACTER

The Enhanced EUSART1 module can receive a Break character in two ways.

The first method to detect a Break character uses the FERR bit of the RC1STA register and the received data as indicated by RC1REG. The Baud Rate Generator is assumed to have been initialized to the expected baud rate.


A Break character has been received when:

- · RCIF bit is set
- FERR bit is set
- RC1REG = 00h

The second method uses the Auto-Wake-up feature described in **Section 31.3.3** "**Auto-Wake-up on Break**". By enabling this feature, the EUSART1 will sample the next two transitions on RX/DT, cause an RCIF interrupt, and receive the next data byte followed by another interrupt.

Note that following a Break character, the user will typically want to enable the Auto-Baud Detect feature. For both methods, the user can set the ABDEN bit of the BAUD1CON register before placing the EUSART1 in Sleep mode.





31.4 EUSART1 Synchronous Mode

Synchronous serial communications are typically used in systems with a single host and one or more clients. The host device contains the necessary circuitry for baud rate generation and supplies the clock for all devices in the system. Client devices can take advantage of the host clock by eliminating the internal clock generation circuitry.

There are two signal lines in Synchronous mode: a bidirectional data line and a clock line. Clients use the external clock supplied by the host to shift the serial data into and out of their respective receive and transmit shift registers. Since the data line is bidirectional, synchronous operation is half-duplex only. Half-duplex refers to the fact that host and client devices can receive and transmit data but not both simultaneously. The EUSART1 can operate as either a host or client device.

Start and Stop bits are not used in synchronous transmissions.

31.4.1 SYNCHRONOUS HOST MODE

The following bits are used to configure the EUSART1 for synchronous host operation:

- SYNC = 1
- CSRC = 1
- SREN = 0 (for transmit); SREN = 1 (for receive)
- CREN = 0 (for transmit); CREN = 1 (for receive)
- SPEN = 1

Setting the SYNC bit of the TX1STA register configures the device for synchronous operation. Setting the CSRC bit of the TX1STA register configures the device as a host. Clearing the SREN and CREN bits of the RC1STA register ensures that the device is in the Transmit mode, otherwise the device will be configured to receive. Setting the SPEN bit of the RC1STA register enables the EUSART1.

31.4.1.1 Host Clock

Synchronous data transfers use a separate clock line, which is synchronous with the data. A device configured as a host transmits the clock on the TX/CK line. The TX/CK pin output driver is automatically enabled when the EUSART1 is configured for synchronous transmit or receive operation. Serial data bits change on the leading edge to ensure they are valid at the trailing edge of each clock. One clock cycle is generated for each data bit. Only as many clock cycles are generated as there are data bits.

31.4.1.2 Clock Polarity

A clock polarity option is provided for Microwire compatibility. Clock polarity is selected with the SCKP bit of the BAUD1CON register. Setting the SCKP bit sets the clock Idle state as high. When the SCKP bit is set, the data change on the falling edge of each clock. Clearing the SCKP bit sets the Idle state as low. When the SCKP bit is cleared, the data change on the rising edge of each clock.

31.4.1.3 Synchronous Host Transmission

Data are transferred out of the device on the RX/DT pin. The RX/DT and TX/CK pin output drivers are automatically enabled when the EUSART1 is configured for synchronous host transmit operation.

A transmission is initiated by writing a character to the TX1REG register. If the TSR still contains all or part of a previous character, the new character data is held in the TX1REG until the last bit of the previous character has been transmitted. If this is the first character, or the previous character has been completely flushed from the TSR, the data in the TX1REG are immediately transferred to the TSR. The transmission of the character commences immediately following the transfer of the data to the TSR from the TX1REG.

Each data bit changes on the leading edge of the host clock and remains valid until the subsequent leading clock edge.

Note: The TSR register is not mapped in data memory, so it is not available to the user.

31.4.1.4 Synchronous Host Transmission Setup

- Initialize the SP1BRGH, SP1BRGL register pair and the BRGH and BRG16 bits to achieve the desired baud rate (see Section 31.3 "EUSART1 Baud Rate Generator (BRG)").
- 2. Enable the synchronous host serial port by setting bits SYNC, SPEN and CSRC.
- 3. Disable Receive mode by clearing bits SREN and CREN.
- 4. Enable Transmit mode by setting the TXEN bit.
- 5. If 9-bit transmission is desired, set the TX9 bit.
- 6. If interrupts are desired, set the TXIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- 7. If 9-bit transmission is selected, the ninth bit may be loaded in the TX9D bit.
- 8. Start transmission by loading data to the TX1REG register.





FIGURE 31-11: SYNCHRONOUS TRANSMISSION (THROUGH TXEN)



31.4.1.5 Synchronous Host Reception

Data are received at the RX/DT pin. The RX/DT pin output driver is automatically disabled when the EUSART1 is configured for synchronous host receive operation.

In Synchronous mode, reception is enabled by setting either the Single Receive Enable bit (SREN of the RC1STA register) or the Continuous Receive Enable bit (CREN of the RC1STA register).

When SREN is set and CREN is clear, only as many clock cycles are generated as there are data bits in a single character. The SREN bit is automatically cleared at the completion of one character. When CREN is set, clocks are continuously generated until CREN is cleared. If CREN is cleared in the middle of a character, the CK clock stops immediately and the partial character is discarded. If SREN and CREN are both set, then SREN is cleared at the completion of the first character and CREN takes precedence. To initiate reception, set either SREN or CREN. Data are sampled at the RX/DT pin on the trailing edge of the TX/CK clock pin and are shifted into the Receive Shift Register (RSR). When a complete character is received into the RSR, the RCIF bit is set and the character is automatically transferred to the two character receive FIFO. The Least Significant eight bits of the top character in the receive FIFO are available in RC1REG. The RCIF bit remains set as long as there are unread characters in the receive FIFO.

Note: If the RX/DT function is on an analog pin, the corresponding ANSEL bit must be cleared for the receiver to function.

31.4.1.6 **Client Clock**

Synchronous data transfers use a separate clock line, which is synchronous with the data. A device configured as a client receives the clock on the TX/CK line. The TX/CK pin output driver is automatically disabled when the device is configured for synchronous client transmit or receive operation. Serial data bits change on the leading edge to ensure they are valid at the trailing edge of each clock. One data bit is transferred for each clock cycle. Only as many clock cycles may be received as there are data bits.

Note:	If the device is configured as a client and
	the TX/CK function is on an analog pin, the
	corresponding ANSEL bit must be cleared.

31.4.1.7 Receive Overrun Error

The receive FIFO buffer can hold two characters. An overrun error will be generated if a third character, in its entirety, is received before RC1REG is read to access the FIFO. When this happens the OERR bit of the RC1STA register is set. Previous data in the FIFO will not be overwritten. The two characters in the FIFO buffer can be read, however, no additional characters will be received until the error is cleared. The OERR bit can only be cleared by clearing the Overrun condition. If the overrun error occurred when the SREN bit is set and CREN is clear, then the error is cleared by reading RC1REG. If the overrun occurred when the CREN bit is set, then the Error condition is cleared by either clearing the CREN bit of the RC1STA register or by clearing the SPEN bit which resets the EUSART1.

31.4.1.8 **Receiving 9-bit Characters**

The EUSART1 supports 9-bit character reception. When the RX9 bit of the RC1STA register is set the EUSART1 will shift nine bits into the RSR for each character received. The RX9D bit of the RC1STA register is the ninth, and Most Significant, data bit of the top unread character in the receive FIFO. When reading 9-bit data from the receive FIFO buffer, the RX9D data bit must be read before reading the eight Least Significant bits from the RC1REG.

31.4.1.9 Synchronous Host Reception Setup

- Initialize the SP1BRGH, SP1BRGL register pair 1. for the appropriate baud rate. Set or clear the BRGH and BRG16 bits, as required, to achieve the desired baud rate.
- 2. Clear the ANSEL bit for the RX pin (if applicable).
- 3. Enable the synchronous host serial port by setting bits SYNC, SPEN and CSRC.
- 4. Ensure bits CREN and SREN are clear.
- 5. If interrupts are desired, set the RCIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- If 9-bit reception is desired, set bit RX9. 6.
- Start reception by setting the SREN bit or for 7. continuous reception, set the CREN bit.
- Interrupt Flag bit RCIF will be set when recep-8 tion of a character is complete. An interrupt will be generated if the Enable bit RCIE was set.
- Read the RC1STA register to get the ninth bit (if 9. enabled) and determine if any error occurred during reception.
- 10. Read the 8-bit received data by reading the RC1REG register.
- 11. If an overrun error occurs, clear the error by either clearing the CREN bit of the RC1STA register or by clearing the SPEN bit which resets the EUSART1.




FIGURE 31-12: SYNCHRONOUS RECEPTION (HOST MODE, SREN)

31.4.2 SYNCHRONOUS CLIENT MODE

The following bits are used to configure the EUSART1 for synchronous client operation:

- SYNC = 1
- CSRC = 0
- SREN = 0 (for transmit); SREN = 1 (for receive)
- CREN = 0 (for transmit); CREN = 1 (for receive)
- SPEN = 1

Setting the SYNC bit of the TX1STA register configures the device for synchronous operation. Clearing the CSRC bit of the TX1STA register configures the device as a client. Clearing the SREN and CREN bits of the RC1STA register ensures that the device is in the Transmit mode, otherwise the device will be configured to receive. Setting the SPEN bit of the RC1STA register enables the EUSART1.

31.4.2.1 EUSART1 Synchronous Client Transmit

The operation of the Synchronous Host and Client modes are identical (see Section 31.4.1.3 "Synchronous Host Transmission"), except in the case of the Sleep mode.

If two words are written to the TX1REG and then the SLEEP instruction is executed, the following will occur:

- 1. The first character will immediately transfer to the TSR register and transmit.
- 2. The second word will remain in the TX1REG register.
- 3. The TXIF bit will not be set.
- After the first character has been shifted out of TSR, the TX1REG register will transfer the second character to the TSR and the TXIF bit will now be set.
- 5. If the PEIE and TXIE bits are set, the interrupt will wake the device from Sleep and execute the next instruction. If the GIE bit is also set, the program will call the Interrupt Service Routine.

31.4.2.2 Synchronous Client Transmission Setup

- 1. Set the SYNC and SPEN bits and clear the CSRC bit.
- 2. Clear the ANSEL bit for the CK pin (if applicable).
- 3. Clear the CREN and SREN bits.
- 4. If interrupts are desired, set the TXIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- 5. If 9-bit transmission is desired, set the TX9 bit.
- 6. Enable transmission by setting the TXEN bit.
- 7. If 9-bit transmission is selected, insert the Most Significant bit into the TX9D bit.
- 8. Start transmission by writing the Least Significant eight bits to the TX1REG register.

31.4.2.3 EUSART1 Synchronous Client Reception

The operation of the Synchronous Host and Client modes is identical (Section 31.4.1.5 "Synchronous Host Reception"), with the following exceptions:

- Sleep
- CREN bit is always set, therefore the receiver is never Idle
- · SREN bit, which is a "don't care" in Client mode

A character may be received while in Sleep mode by setting the CREN bit prior to entering Sleep. Once the word is received, the RSR register will transfer the data to the RC1REG register. If the RCIE Enable bit is set, the interrupt generated will wake the device from Sleep and execute the next instruction. If the GIE bit is also set, the program will branch to the interrupt vector.

31.4.2.4 Synchronous Client Reception Setup

- 1. Set the SYNC and SPEN bits and clear the CSRC bit.
- 2. Clear the ANSEL bit for both the CK and DT pins (if applicable).
- If interrupts are desired, set the RCIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- 4. If 9-bit reception is desired, set the RX9 bit.
- 5. Set the CREN bit to enable reception.
- The RCIF bit will be set when reception is complete. An interrupt will be generated if the RCIE bit was set.
- 7. If 9-bit mode is enabled, retrieve the Most Significant bit from the RX9D bit of the RC1STA register.
- 8. Retrieve the eight Least Significant bits from the receive FIFO by reading the RC1REG register.
- 9. If an overrun error occurs, clear the error by either clearing the CREN bit of the RC1STA register or by clearing the SPEN bit which resets the EUSART1.

31.5 EUSART1 Operation During Sleep

The EUSART1 will remain active during Sleep only in the Synchronous Client mode. All other modes require the system clock and therefore cannot generate the necessary signals to run the Transmit or Receive Shift registers during Sleep.

Synchronous Client mode uses an externally generated clock to run the Transmit and Receive Shift registers.

31.5.1 SYNCHRONOUS RECEIVE DURING SLEEP

To receive during Sleep, all the following conditions must be met before entering Sleep mode:

- RC1STA and TX1STA Control registers must be configured for Synchronous Client Reception (see Section 31.4.2.4 "Synchronous Client Reception Setup").
- If interrupts are desired, set the RCIE bit of the PIE1 register and the GIE and PEIE bits of the INTCON register.
- The RCIF interrupt flag must be cleared by reading RC1REG to unload any pending characters in the receive buffer.

Upon entering Sleep mode, the device will be ready to accept data and clocks on the RX/DT and TX/CK pins, respectively. When the data word has been completely clocked in by the external device, the RCIF Interrupt Flag bit of the PIR1 register will be set. Thereby, waking the processor from Sleep.

Upon waking from Sleep, the instruction following the SLEEP instruction will be executed. If the Global Interrupt Enable (GIE) bit of the INTCON register is also set, then the Interrupt Service Routine at address 004h will be called.

31.5.2 SYNCHRONOUS TRANSMIT DURING SLEEP

To transmit during Sleep, all the following conditions must be met before entering Sleep mode:

- The RC1STA and TX1STA Control registers must be configured for synchronous client transmission (see Section 31.4.2.2 "Synchronous Client Transmission Setup").
- The TXIF Interrupt flag must be cleared by writing the output data to the TX1REG, thereby filling the TSR and transmit buffer.
- If interrupts are desired, set the TXIE bit of the PIE1 register and the PEIE bit of the INTCON register.
- Interrupt Enable bits TXIE of the PIE1 register and PEIE of the INTCON register must set.

Upon entering Sleep mode, the device will be ready to accept clocks on TX/CK pin and transmit data on the RX/DT pin. When the data word in the TSR has been completely clocked out by the external device, the pending byte in the TX1REG will transfer to the TSR and the TXIF flag will be set. Thereby, waking the processor from Sleep. At this point, the TX1REG is available to accept another character for transmission, which will clear the TXIF flag.

Upon waking from Sleep, the instruction following the SLEEP instruction will be executed. If the Global Interrupt Enable (GIE) bit is also set, then the Interrupt Service Routine at address 0004h will be called.

Register Definitions: EUSART1 Control 31.6

R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0	R-1/1	R/W-0/0
CSRC	TX9	TXEN ⁽¹⁾	SYNC	SENDB	BRGH	TRMT	TX9D
bit 7	•	·	•	• 			bit (
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimpler	mented bit, read	as '0'	
u = Bit is uncł	nanged	x = Bit is unkr	nown	-n/n = Value a	at POR and BOF	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is cle	ared				
bit 7	Asynchronou Unused in thi Synchronous 1 = Host mo	s mode – value	e ignored rated internal				
bit 6	1 = Selects	ansmit Enable I 9-bit transmiss 8-bit transmiss	ion				
bit 5	TXEN: Trans 1 = Transmit 0 = Transmit)				
bit 4	SYNC: EUSA 1 = Synchror 0 = Asynchror		ect bit				
bit 3	Asynchronou 1 = Send SY bit; clean 0 = SYNCH Synchronous	NCH BREAK of ed by hardware BREAK transm	on next transr e upon comple ission disable	etion	bit, followed by	12 '0' bits, fol	lowed by Sto
bit 2	BRGH: High Asynchronou 1 = High spe 0 = Low spe Synchronous	Baud Rate Sel <u>s mode</u> : ed ed	ect bit				
bit 1	TRMT: Trans 1 = TSR emp 0 = TSR full	mit Shift Regist oty	er Status bit				
bit 0	TX9D: Ninth Can be addre	bit of Transmit					

Note 1: SREN/CREN overrides TXEN in Sync mode.

R/W-0/0		R/W-0/0	R/W-0/0	R/W-0/0	R-0/0	R-0/0	R-x/x
SPEN ⁽¹⁾) RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D
bit 7							bit (
Legend:							
R = Reada		W = Writable		•	nented bit, read		
u = Bit is u	•	x = Bit is unki		-n/n = Value a	at POR and BOI	R/Value at all o	ther Resets
'1' = Bit is s	set	'0' = Bit is cle	ared				
bit 7	SPEN: Seria	l Port Enable b	(1)				
	1 = Serial po						
bit 6		eceive Enable b					
		9-bit reception 8-bit reception					
bit 5	SREN: Singl	e Receive Enal	ole bit				
	<u>Asynchronou</u>	<u>is mode</u> :					
		is mode – value <u>mode – Host</u> :	eignored				
		single receive single receive					
		ared after rece		ete.			
	-	<u>mode – Client</u>					
bit 4		is mode – value nuous Receive	•				
DIL 4	Asynchronou						
	•		eive until Ena	ble bit CREN is	cleared		
	0 = Disables <u>Synchronous</u>	continuous ree <u>mode</u> :	ceive	-			
		continuous rec continuous rec		ble bit CREN is	cleared (CREN	l overrides SR	EN)
bit 3	ADDEN: Add	lress Detect En	able bit				
	Asynchronou	is mode 9-bit (F	RX9 = <u>1</u>):				
	the rece	ive buffer is set		-	ad of the receive		
	Asynchronou	is mode 8-bit (F	RX9 = 0):	are received a	nd ninth bit can	be used as pai	rity bit
		is mode – value	e ignored				
bit 2	FERR: Fram	-					
	1 = Framing 0 = No frami		ipdated by rea	ading RC1REG	register and rec	ceive next valio	l byte)
bit 1	OERR: Over	run Error bit					
	1 = Overrun 0 = No overr	•	leared by clea	aring bit CREN))		
bit 0		bit of Received	l Data				
	i nis can be a	address/data bi	t or a paritv bi	t and must be o	alculated by us	er firmware.	

REGISTER 31-2: RC1STA: RECEIVE STATUS AND CONTROL REGISTER

R-0/0	R-1/1	U-0	R/W-0/0	R/W-0/0	U-0	R/W-0/0	R/W-0/0		
ABDOVF	RCIDL	—	SCKP	BRG16	—	WUE	ABDEN		
bit 7							bit C		
Legend:									
R = Readable		W = Writable			mented bit, rea				
u = Bit is unch	nanged	x = Bit is unkr		-n/n = Value	at POR and BC	R/Value at all c	ther Resets		
'1' = Bit is set		'0' = Bit is cle	ared						
bit 7	ABDOVF: A	uto-Baud Detec	t Overflow bit						
	Asynchronou								
	1 = Auto-bau	ıd timer overflov							
		id timer did not	overflow						
	<u>Synchronous</u> Don't care	<u>s mode</u> :							
bit 6		eive Idle Flag bi	t						
	Asynchronou	-	·						
	1 = Receiver								
		has been receiv	red and the re	ceiver is receiv	/ing				
	Synchronous Don't care	<u>s mode</u> :							
bit 5		nted: Read as '	0'						
bit 4	-	<br √ Transmit Pola							
	Asynchronou		,						
	1 = Idle state for transmit (TX) is a low level								
	0 = Idle state	e for transmit (T	X) is a high le	vel					
	Synchronous								
		e for clock (CK) e for clock (CK)							
bit 3		bit Baud Rate G							
bit 0		aud Rate Gener							
		ud Rate Genera							
bit 2	Unimpleme	nted: Read as '	0'						
bit 1	WUE: Wake	-up Enable bit							
	<u>Asynchronou</u>	<u>is mode</u> :							
				Rx pin – interru	pt generated o	n falling edge; b	it cleared in		
		on following ris		dataatad					
	Synchronous	ot monitored no s mode:	i fising edge o	delected					
	-	is mode – value	e ianored						
bit 0		o-Baud Detect I	0						
	Asynchronou	<u>is mode</u> :							
	-		surement on t	the next chara	acter – requires	reception of a	SYNCH field		
	(55h);cle	eared in hardwa	ire upon comp	oletion	-				
	0 = Baud ra Synchronous	te measuremen	t disabled or o	completed					
		S 111000							

REGISTER 31-3: BAUD1CON: BAUD RATE CONTROL REGISTER

REGISTER 31-4: RC1REG⁽¹⁾: RECEIVE DATA REGISTER

R-0	R-0	R-0	R-0	R-0	R-0	R-0	R-0		
RC1REG<7:0>									
bit 7							bit 0		
Legend:									
R = Readable b	bit	W = Writable b	it	U = Unimplemented bit, read as '0'					
u = Bit is uncha	anged	x = Bit is unkno	own	-n/n = Value at POR and BOR/Value at all other Resets					

bit 7-0 RC1REG<7:0>: Lower eight bits of the received data; read-only; see also RX9D (Register 31-2)

Note 1: RC1REG (including the ninth bit) is double buffered, and data are available while new data are being received.

REGISTER 31-5: TX1REG⁽¹⁾: TRANSMIT DATA REGISTER

'0' = Bit is cleared

1' = Bit is set

'1' = Bit is set

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
TX1REG<7:0>									
bit 7							bit 0		

Legend:		
R = Readable bit	W = Writable bit	U = Unimplemented bit, read as '0'
u = Bit is unchanged	x = Bit is unknown	-n/n = Value at POR and BOR/Value at all other Resets
'1' = Bit is set	'0' = Bit is cleared	

bit 7-0 **TX1REG<7:0>:** Lower eight bits of the received data; read-only; see also RX9D (Register 31-1)

Note 1: TX1REG (including the ninth bit) is double buffered, and can be written when previous data have started shifting.

REGISTER 31-6: SP1BRGL⁽¹⁾: BAUD RATE GENERATOR REGISTER

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0		
			SP1B	RG<7:0>					
bit 7							bit 0		
Legend:									
R = Readable b	Readable bit W = Writable bit				U = Unimplemented bit, read as '0'				
u = Bit is uncha	nged	x = Bit is unknow	vn	-n/n = Value at POR and BOR/Value at all other Resets					

bit 7-0 SP1BRG<7:0>: Lower eight bits of the Baud Rate Generator

'0' = Bit is cleared

Note 1: Writing to SP1BRG resets the BRG counter.

R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0	R/W-0
			SP1B	RG<15:8>			
bit 7							bit 0
Legend:							
R = Readable I	bit	W = Writable bit		U = Unimpler	nented bit, read	l as '0'	
u = Bit is uncha	anged	x = Bit is unknov	vn	-n/n = Value a	at POR and BO	R/Value at all o	other Resets
'1' = Bit is set		'0' = Bit is cleare	ed				

REGISTER 31-7: SP1BRGH^(1, 2): BAUD RATE GENERATOR HIGH REGISTER

bit 7 SP1BRG<15:8>: Upper eight bits of the Baud Rate Generator

Note 1: SP1BRGH value is ignored for all modes unless BAUD1CON<BRG16> is active.

2: Writing to SP1BRGH resets the BRG counter.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	—	_	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
ANSELA		_	ANSA5	ANSA4		ANSA2	ANSA1	ANSA0	144
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4		_	_	_	149
ANSELB ⁽¹⁾	ANSB7	ANSB6	ANSB5	ANSB4		_	_		150
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
ANSELC	ANSC7 ⁽¹⁾	ANSC6 ⁽¹⁾	ANSC5	ANSC4	ANSC3	ANSC2	ANSC1	ANSC0	157
INTCON	GIE	PEIE	_	—	—	_		INTEDG	100
PIR1	TMR1GIF	ADIF	RCIF	TXIF	SSP1IF	BCL1IF	TMR2IF	TMR1IF	107
PIE1	TMR1GIE	ADIE	RCIE	TXIE	SSP1IE	BCL1IE	TMR2IE	TMR1IE	102
RC1STA	SPEN	RX9	SREN	CREN	ADDEN	FERR	OERR	RX9D	385
TX1STA	CSRC	TX9	TXEN	SYNC	SENDB	BRGH	TRMT	TX9D	384
BAUD1CON	ABDOVF	RCIDL	—	SCKP	BRG16	-	WUE	ABDEN	386
RC1REG				RC1RE	G<7:0>				387
TX1REG				TX1RE	G<7:0>				387
SP1BRGL				SP1BR	G<7:0>				387
SP1BRGH				SP1BR0	G<15:8>				388
RXPPS	—	—			F	RXPPS<4:0	>		162
CLCxSELy	—	—			L	.CxDyS<4:0	>		229
MDSRC	_	_		—		MDMS	S<3:0>		272

TABLE 31-2: SUMMARY OF REGISTERS ASSOCIATED WITH EUSART1

Legend: — = unimplemented location, read as '0'. Shaded cells are not used for the EUSART1 module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

C	onfiguration B	its		Baud Rate Formula
SYNC	BRG16	BRGH	BRG/EUSART1 Mode	Baud Rate Formula
0	0	0	8-bit/Asynchronous	Fosc/[64 (n+1)]
0	0	1	8-bit/Asynchronous	
0	1	0	16-bit/Asynchronous	Fosc/[16 (n+1)]
0	1	1	16-bit/Asynchronous	
1	0	х	8-bit/Synchronous	Fosc/[4 (n+1)]
1	1	х	16-bit/Synchronous	

TABLE 31-3:BAUD RATE FORMULAS

Legend: x = Don't care, n = value of SP1BRGH, SP1BRGL register pair.

TABLE 31-4: BAUD RATE FOR ASYNCHRONOUS MODES

					SYNC	; = 0, BRG	l = 0, BRG	616 = 0				
BAUD	Foso	: = 32.00	0 MHz	Fosc	= 20.00	0 MHz	Fosc	= 18.43	2 MHz	Fosc	= 11.059	2 MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	_			_		_	_		_	_		
1200	—	—	—	1221	1.73	255	1200	0.00	239	1200	0.00	143
2400	2404	0.16	207	2404	0.16	129	2400	0.00	119	2400	0.00	71
9600	9615	0.16	51	9470	-1.36	32	9600	0.00	29	9600	0.00	17
10417	10417	0.00	47	10417	0.00	29	10286	-1.26	27	10165	-2.42	16
19.2k	19.23k	0.16	25	19.53k	1.73	15	19.20k	0.00	14	19.20k	0.00	8
57.6k	55.55k	-3.55	3	—	_	_	57.60k	0.00	7	57.60k	0.00	2
115.2k	—	_		_	_	_		_	_		_	_

					SYNC	; = 0, BRGH	l = 0, BRG	616 = 0				
BAUD	Fos	c = 8.000) MHz	Fos	c = 4.000) MHz	Fosc	: = 3.686	4 MHz	Fos	c = 1.000) MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300			_	300	0.16	207	300	0.00	191	300	0.16	51
1200	1202	0.16	103	1202	0.16	51	1200	0.00	47	1202	0.16	12
2400	2404	0.16	51	2404	0.16	25	2400	0.00	23	—	_	_
9600	9615	0.16	12	_	_	_	9600	0.00	5	—	_	_
10417	10417	0.00	11	10417	0.00	5	—	_	_	—	_	_
19.2k	—	_	_	_	_	_	19.20k	0.00	2	_	_	_
57.6k	—	_	_	—	_	_	57.60k	0.00	0	—	_	_
115.2k	_	_	—	_	_	—	_	_	—	_	_	—

					SYNC	C = 0, BRG	I = 1, BRO	G16 = 0				
BAUD	Fosc	= 32.00	0 MHz	Fosc	= 20.00	0 MHz	Foso	: = 18.43	2 MHz	Fosc	= 11.059	2 MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	—		_	_		_		_	—			_
1200	—		—	—		—	—	—	—	—		—
2400	—	_	—	_		—	—	_	—	—		_
9600	9615	0.16	207	9615	0.16	129	9600	0.00	119	9600	0.00	71
10417	10417	0.00	191	10417	0.00	119	10378	-0.37	110	10473	0.53	65
19.2k	19.23k	0.16	103	19.23k	0.16	64	19.20k	0.00	59	19.20k	0.00	35
57.6k	57.14k	-0.79	34	56.82k	-1.36	21	57.60k	0.00	19	57.60k	0.00	11
115.2k	117.64k	2.12	16	113.64k	-1.36	10	115.2k	0.00	9	115.2k	0.00	5

TABLE 31-4: BAUD RATE FOR ASYNCHRONOUS MODES (CONTINUED)

					SYNC	C = 0, BRG	l = 1, BRC	616 = 0				
BAUD	Fos	c = 8.000) MHz	Fos	c = 4.000) MHz	Fosc	: = 3.686	4 MHz	Fos	c = 1.000) MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	_	_	_	_		_	_	_	_	300	0.16	207
1200	—	—	—	1202	0.16	207	1200	0.00	191	1202	0.16	51
2400	2404	0.16	207	2404	0.16	103	2400	0.00	95	2404	0.16	25
9600	9615	0.16	51	9615	0.16	25	9600	0.00	23	—	_	_
10417	10417	0.00	47	10417	0.00	23	10473	0.53	21	10417	0.00	5
19.2k	19231	0.16	25	19.23k	0.16	12	19.2k	0.00	11	_	_	_
57.6k	55556	-3.55	8	—	_	_	57.60k	0.00	3	—	_	_
115.2k	—		_	_	_	_	115.2k	0.00	1	—		—

					SYNC	C = 0, BRG	I = 0, BRO	616 = 1				
BAUD	Foso	: = 32.00	0 MHz	Fosc	= 20.00	0 MHz	Foso	: = 18.43	2 MHz	Fosc	= 11.059	92 MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	300.0	0.00	6666	300.0	-0.01	4166	300.0	0.00	3839	300.0	0.00	2303
1200	1200	-0.02	3332	1200	-0.03	1041	1200	0.00	959	1200	0.00	575
2400	2401	-0.04	832	2399	-0.03	520	2400	0.00	479	2400	0.00	287
9600	9615	0.16	207	9615	0.16	129	9600	0.00	119	9600	0.00	71
10417	10417	0.00	191	10417	0.00	119	10378	-0.37	110	10473	0.53	65
19.2k	19.23k	0.16	103	19.23k	0.16	64	19.20k	0.00	59	19.20k	0.00	35
57.6k	57.14k	-0.79	34	56.818	-1.36	21	57.60k	0.00	19	57.60k	0.00	11
115.2k	117.6k	2.12	16	113.636	-1.36	10	115.2k	0.00	9	115.2k	0.00	5

					SYNC	; = 0, BRG	l = 0, BRG	616 = 1				
BAUD	Fos	c = 8.000) MHz	Fos	c = 4.000) MHz	Fosc	: = 3.686	4 MHz	Fos	c = 1.000) MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	299.9	-0.02	1666	300.1	0.04	832	300.0	0.00	767	300.5	0.16	207
1200	1199	-0.08	416	1202	0.16	207	1200	0.00	191	1202	0.16	51
2400	2404	0.16	207	2404	0.16	103	2400	0.00	95	2404	0.16	25
9600	9615	0.16	51	9615	0.16	25	9600	0.00	23	_	_	_
10417	10417	0.00	47	10417	0.00	23	10473	0.53	21	10417	0.00	5
19.2k	19.23k	0.16	25	19.23k	0.16	12	19.20k	0.00	11	—	_	_
57.6k	55556	-3.55	8	—	_	_	57.60k	0.00	3	—	_	_
115.2k	_	_	_	—		_	115.2k	0.00	1	—	_	_

TABLE 31-4: BAUD RATE FOR ASYNCHRONOUS MODES (CONTINUED)

				SYNC = 0	, BRGH	= 1, BRG16	i = 1 or Sγ	'NC = 1,	BRG16 = 1			
BAUD	Foso	= 32.00	0 MHz	Fosc	= 20.00	0 MHz	Foso	: = 18.43	2 MHz	Fosc	= 11.059	92 MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	300.0	0.00	26666	300.0	0.00	16665	300.0	0.00	15359	300.0	0.00	9215
1200	1200	0.00	6666	1200	-0.01	4166	1200	0.00	3839	1200	0.00	2303
2400	2400	0.01	3332	2400	0.02	2082	2400	0.00	1919	2400	0.00	1151
9600	9604	0.04	832	9597	-0.03	520	9600	0.00	479	9600	0.00	287
10417	10417	0.00	767	10417	0.00	479	10425	0.08	441	10433	0.16	264
19.2k	19.18k	-0.08	416	19.23k	0.16	259	19.20k	0.00	239	19.20k	0.00	143
57.6k	57.55k	-0.08	138	57.47k	-0.22	86	57.60k	0.00	79	57.60k	0.00	47
115.2k	115.9k	0.64	68	116.3k	0.94	42	115.2k	0.00	39	115.2k	0.00	23

				SYNC = 0	, BRGH	= 1, BRG16	i = 1 or Sγ	'NC = 1,	BRG16 = 1			
BAUD	Fos	c = 8.000) MHz	Fos	c = 4.000) MHz	Foso	: = 3.686	4 MHz	Fos	c = 1.000) MHz
RATE	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)	Actual Rate	% Error	SPBRG value (decimal)
300	300.0	0.00	6666	300.0	0.01	3332	300.0	0.00	3071	300.1	0.04	832
1200	1200	-0.02	1666	1200	0.04	832	1200	0.00	767	1202	0.16	207
2400	2401	0.04	832	2398	0.08	416	2400	0.00	383	2404	0.16	103
9600	9615	0.16	207	9615	0.16	103	9600	0.00	95	9615	0.16	25
10417	10417	0	191	10417	0.00	95	10473	0.53	87	10417	0.00	23
19.2k	19.23k	0.16	103	19.23k	0.16	51	19.20k	0.00	47	19.23k	0.16	12
57.6k	57.14k	-0.79	34	58.82k	2.12	16	57.60k	0.00	15	—	_	_
115.2k	117.6k	2.12	16	111.1k	-3.55	8	115.2k	0.00	7	—	_	_

32.0 REFERENCE CLOCK OUTPUT MODULE

The Reference Clock Output module provides the ability to send a clock signal to the clock reference output pin (CLKR). The Reference Clock Output can also be used as a signal for other peripherals, such as the Data Signal Modulator (DSM).

The Reference Clock Output module has the following features:

- · System clock is the module source clock
- Programmable clock divider
- Selectable duty cycle

32.1 Clock Source

The Reference Clock Output module uses the system clock (Fosc) as the clock source. Any device clock switching will be reflected in the clock output.

32.1.1 CLOCK SYNCHRONIZATION

Once the reference clock enable (CLKREN) is set, the module is ensured to be glitch-free at start-up.

When the Reference Clock Output is disabled, the output signal will be disabled immediately.

Clock dividers and clock duty cycles can be changed while the module is enabled, but glitches may occur on the output. To avoid possible glitches, clock dividers and clock duty cycles may be changed only when the CLKREN is clear.

32.2 Programmable Clock Divider

The module takes the system clock input and divides it based on the value of the CLKRDIV<2:0> bits of the CLKRCON register (Register 32-1).

The following configurations can be made based on the CLKRDIV<2:0> bits:

- · Base Fosc value
- Fosc divided by 2
- Fosc divided by 4
- Fosc divided by 8
- Fosc divided by 16
- Fosc divided by 32
- Fosc divided by 64
- Fosc divided by 128

The clock divider values can be changed while the module is enabled; however, in order to prevent glitches on the output, the CLKRDIV<2:0> bits may only be changed when the module is disabled (CLKREN = 0).

32.3 Selectable Duty Cycle

The CLKRDC<1:0> bits of the CLKRCON register can be used to modify the duty cycle of the output clock. A duty cycle of 25%, 50%, or 75% can be selected for all clock rates, with the exception of the undivided base Fosc value.


The duty cycle can be changed while the module is enabled; however, to prevent glitches on the output, the CLKRDC<1:0> bits may only be changed when the module is disabled (CLKREN = 0).

Note: The CLKRDC1 bit is reset to '1'. This makes the default duty cycle 50%.


32.4 Operation in Sleep Mode

The Reference Clock Output module clock is based on the system clock. When the device goes to Sleep, the module outputs will remain in their current state. This will have a direct effect on peripherals using the Reference Clock Output as an input signal.









R/W-0/0	U-0	U-0	R/W-1/1	R/W-0/0	R/W-0/0	R/W-0/0	R/W-0/0
CLKREN	_	_	CLKRI	DC<1:0>		CLKRDIV<2:0>	
bit 7							bit
Legend:							
R = Readable	e bit	W = Writable	bit	U = Unimpler	mented bit, read	d as '0'	
u = Bit is unc	hanged	x = Bit is unkr	iown	-n/n = Value	at POR and BC	R/Value at all o	other Resets
'1' = Bit is set	t	'0' = Bit is clea	ared				
bit 7	CLKREN: Re	eference Clock	Module Enabl	e bit			
	1 = Referen	nce clock modul	le enabled				
	0 = Referen	nce clock modul	e is disabled				
bit 6-5	Unimplemen	ted: Read as '	כ'				
bit 4-3	CLKRDC<1:0	0>: Reference (Clock Duty Cy	cle bits ⁽¹⁾			
	11 = Clock ou	utputs duty cycl	e of 75%				
	10 = Clock o	utputs duty cycl	e of 50%				
		utputs duty cycl					
	00 = Clock ou	utputs duty cycl	e of 0%				
bit 2-0	CLKRDIV<2:	0>: Reference	Clock Divider	bits			
	111 = Fosc o	divided by 128					
	110 = Fosc c						
	101 = Fosc c	•					
	100 = Fosc c	•					
	011 = Fosc c						
	010 = Fosc o 001 = Fosc o	•					
	000 = Fosc						
Noto 1. Bi	ts are valid for P	oforonoo Clook	, dividor voluo	a of two or lorg	or the base ale	ak aannat ha fi	urthor divido

REGISTER 32-1: CLKRCON: REFERENCE CLOCK CONTROL REGISTER

Note 1: Bits are valid for Reference Clock divider values of two or larger, the base clock cannot be further divided.

Name	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Register on Page
TRISA	_	_	TRISA5	TRISA4	(2)	TRISA2	TRISA1	TRISA0	143
TRISB ⁽¹⁾	TRISB7	TRISB6	TRISB5	TRISB4	_	_	_	—	149
TRISC	TRISC7 ⁽¹⁾	TRISC6 ⁽¹⁾	TRISC5	TRISC4	TRISC3	TRISC2	TRISC1	TRISC0	155
CLKRCON	CLKREN	_	—	CLKRD	CLKRDC<1:0> CLKRDIV<2:0>				227
CLCxSELy	—	_	LCxDyS<5:0>						229
MDCARH	—	MDCHPOL	MDCHSYNC	—	MDCH<3:0>				273
MDCARL	—	MDCLPOL	MDCLSYNC	_	MDCL<3:0>				274

Legend: — = unimplemented, read as '0'. Shaded cells are not used by the CLKR module.

Note 1: PIC16(L)F18346 only.

2: Unimplemented, read as '1'.

33.0 IN-CIRCUIT SERIAL PROGRAMMING™ (ICSP™)

ICSP[™] programming allows customers to manufacture circuit boards with unprogrammed devices. Programming can be done after the assembly process, allowing the device to be programmed with the most recent firmware or a custom firmware. Five pins are needed for ICSP programming:

- ICSPCLK
- ICSPDAT
- MCLR/VPP
- VDD
- Vss

In Program/Verify mode, the program memory, data EEPROM, User IDs and the Configuration Words are programmed through serial communications. The ICSPDAT pin is a bidirectional I/O used for transferring the serial data and the ICSPCLK pin is the clock input. For more information on ICSP, refer to the "*PIC16(L)F183XX Memory Programming Specification*" (DS40001738).

33.1 High-Voltage Programming Entry Mode

The device is placed into High-Voltage Programming Entry mode by holding the ICSPCLK and ICSPDAT pins low then raising the voltage on MCLR/VPP to VIHH.

33.2 Low-Voltage Programming Entry Mode

The Low-Voltage Programming Entry mode allows the PIC[®] Flash MCUs to be programmed using VDD only, without high voltage. When the LVP bit of Configuration Words is set to '1', the low-voltage ICSP programming entry is enabled. To disable the Low-Voltage ICSP mode, the LVP bit must be programmed to '0'. The LVP bit can only be reprogrammed to '0' by using the High-Voltage Programming mode.

Entry into the Low-Voltage Programming Entry mode requires the following steps:

- 1. MCLR is brought to VIL.
- 2. A 32-bit key sequence is presented on ICSPDAT, while clocking ICSPCLK.


Once the key sequence is complete, $\overline{\text{MCLR}}$ must be held at VIL for as long as Program/Verify mode is to be maintained.

If low-voltage programming is enabled (LVP = 1), the MCLR Reset function is automatically enabled and cannot be disabled. See **Section 6.4** "MCLR" for more information.

33.3 Common Programming Interfaces

Connection to a target device is typically done through an ICSP[™] header. A commonly found connector on development tools is the RJ-11 in the 6P6C (6-pin, 6-connector) configuration. See Figure 33-1.






Another connector often found in use with the PICkit[™] programmers is a standard 6-pin header with 0.1 inch spacing. Refer to Figure 33-2.


For additional interface recommendations, refer to the specific device programmer manual prior to PCB design.

It is recommended that isolation devices be used to separate the programming pins from other circuitry. The type of isolation is highly dependent on the specific application and may include devices such as resistors, diodes, or even jumpers. See Figure 33-3 for more information.









34.0 INSTRUCTION SET SUMMARY

Each instruction is a 14-bit word containing the operation code (opcode) and all required operands. The opcodes are broken into three broad categories.

- Byte Oriented
- Bit Oriented
- Literal and Control

The literal and control category contains the most varied instruction word format.

Table 34-3 lists the instructions recognized by the MPASM^T assembler.

All instructions are executed within a single instruction cycle, with the following exceptions, which may take two or three cycles:

- Subroutine entry takes two cycles (CALL, CALLW)
- Returns from interrupts or subroutines take two cycles (RETURN, RETLW, RETFIE)
- Program branching takes two cycles (GOTO, BRA, BRW, BTFSS, BTFSC, DECFSZ, INCSFZ)
- One additional instruction cycle will be used when any instruction references an indirect file register and the file select register is pointing to program memory.

One instruction cycle consists of 4 oscillator cycles; for an oscillator frequency of 4 MHz, this gives a nominal instruction execution rate of 1 MHz.

All instruction examples use the format '0xhh' to represent a hexadecimal number, where 'h' signifies a hexadecimal digit.

34.1 Read-Modify-Write Operations

Any WRITE instruction that specifies a file register as part of the instruction performs a Read-Modify-Write (R-M-W) operation. The register is read, the data are modified, and the result is stored according to either the working (W) register, or the originating file register, depending on the state of the destination designator 'd' (see Table 34-1 for more information). A read operation is performed on a register even if the instruction writes to that register.

TABLE 34-1: OPCODE FIELD DESCRIPTIONS

Field	Description
f	Register file address (0x00 to 0x7F)
W	Working register (accumulator)
b	Bit address within an 8-bit file register
k	Literal field, constant data or label
x	Don't care location (= 0 or 1). The assembler will generate code with x = 0 . It is the recommended form of use for compatibility with all Microchip software tools.
d	Destination select; d = 0: store result in W, d = 1: store result in file register f.
n	FSR or INDF number. (0-1)
mm	Pre-post increment-decrement mode selection

TABLE 34-2: ABBREVIATION DESCRIPTIONS

Field	Description
PC	Program Counter
TO	Time-Out bit
С	Carry bit
DC	Digit Carry bit
Z	Zero bit
PD	Power-Down bit

FIGURE 34-1: GENERAL FORMAT FOR INSTRUCTIONS

Byte-oriented file register operations
OPCODE d f (FILE #)
d = 0 for destination W d = 1 for destination f f = 7-bit file register address
Bit-oriented file register operations
OPCODE b (BIT #) f (FILE #)
b = 3-bit bit address f = 7-bit file register address
Literal and control operations
General
OPCODE k (literal)
k = 8-bit immediate value
CALL and GOTO instructions only
<u>13 11 10 0</u>
OPCODE k (literal)
k = 11-bit immediate value
MOVLP instruction only 13 7 6 0
OPCODE k (literal)
k = 7-bit immediate value
MOVLB instruction only
OPCODE k (literal)
k = 5-bit immediate value
BRA instruction only
13 9 8 0 OPCODE k (literal)
k = 9-bit immediate value
FSR Offset instructions
OPCODE n k (literal)
n = appropriate FSR k = 6-bit immediate value
FSR Increment instructions 13 3 2 1 0
OPCODE n m (mode)
n = appropriate FSR m = 2-bit mode value
OPCODE only
13 0 OPCODE
OFCODE

Mnemonic,		Description			14-bit	Opcode	Status		
Oper	ands	Description	Cycles	MSb			LSb	Affected	Note
		BYTE-ORIENTED FILE		RATIC	ONS				
ADDWF	f, d	Add W and f	1	00	0111	dfff	ffff	C, DC, Z	2
ADDWFC	f, d	Add with Carry W and f	1	11	1101	dfff	ffff	C, DC, Z	2
ANDWF	f, d	AND W with f	1	00	0101	dfff	ffff	Z	2
ASRF	f, d	Arithmetic Right Shift	1	11	0111	dfff	ffff	C, Z	2
LSLF	f, d	Logical Left Shift	1	11	0101	dfff	ffff	C, Z	2
LSRF	f, d	Logical Right Shift	1	11	0110	dfff	ffff	C, Z	2
CLRF	f	Clear f	1	00	0001	lfff	ffff	Z	2
CLRW	_	Clear W	1	00	0001	0000	00xx	Z	
COMF	f, d	Complement f	1	00	1001	dfff	ffff	Z	2
DECF	f, d	Decrement f	1	00	0011	dfff	ffff	Z	2
INCF	f, d	Increment f	1	00	1010	dfff	ffff	Z	2
IORWF	f, d	Inclusive OR W with f	1	00	0100	dfff	ffff	Z	2
MOVF	f, d	Move f	1	00	1000	dfff	ffff	Z	2
MOVWF	f	Move W to f	1	00	0000	1fff	ffff		2
RLF	f, d	Rotate Left f through Carry	1	00	1101	dfff	ffff	С	2
RRF	f, d	Rotate Right f through Carry	1	00	1100	dfff	ffff	С	2
SUBWF	f, d	Subtract W from f	1	00	0010	dfff	ffff	C, DC, Z	2
SUBWFB	f, d	Subtract with Borrow W from f	1	11	1011	dfff	ffff	C, DC, Z	2
SWAPF	f, d	Swap nibbles in f	1	00	1110	dfff	ffff		2
XORWF	f, d	Exclusive OR W with f	1	0.0	0110	dfff	ffff	z	2
		BYTE ORIENTED		ONS				1	
DECFSZ	f, d	Decrement f, Skip if 0	1(2)	00	1011	dfff	ffff		1, 2
INCFSZ	f, d	Increment f, Skip if 0	1(2)	00	1111	dfff	ffff		1, 2
		BIT-ORIENTED FILE R	EGISTER OPER	RATIO	NS				
BCF	f, b	Bit Clear f	1	01	00bb	bfff	ffff		2
BSF	f, b	Bit Set f	1	01	01bb	bfff	ffff		2
		BIT-ORIENTED S		NS					
BTFSC	f, b	Bit Test f, Skip if Clear	1 (2)	01	10bb	bfff	ffff		1, 2
BTFSS	f, b	Bit Test f, Skip if Set	1 (2)	01		bfff			1, 2
	., 2		PERATIONS	01	1100	~			., _
ADDLW	k	Add literal and W	1	11	1110	kkkk	kkkk	C, DC, Z	
ANDLW	k	AND literal with W	1	11	1001		kkkk	Z	
IORLW	k	Inclusive OR literal with W	1	11	1000		kkkk	z	
MOVLB	k	Move literal to BSR	1	00		001k		-	
MOVLP	k	Move literal to PCLATH	1	11	0001	1kkk			
MOVLW	k	Move literal to W	1	11		kkkk			
SUBLW	k	Subtract W from literal	1	11	1100		kkkk	C, DC, Z	
XORLW	k	Exclusive OR literal with W	1	11		kkkk		Z	
			OPERATIONS	1	1010			1-	I
BRA	k	Relative Branch	2	11	001k	kkkk	kkkk		
BRW	_	Relative Branch with W	2	00		0000			
CALL	k	Call Subroutine	2	10		kkkk			
CALLW	_	Call Subroutine with W	2	00		0000			
GOTO	k	Go to address	2	10		kkkk			
RETFIE	k	Return from interrupt	2	00	0000				
RETLW	k	Return with literal in W	2	11		kkkk			
RETURN	_	Return from Subroutine	2	00		0000			
			1-	1				1	1

TABLE 34-3: PIC16(L)F18326/18346 INSTRUCTION SET

Note 1: If the Program Counter (PC) is modified, or a conditional test is true, the instruction requires two cycles. The second cycle is executed as a NOP.

2: If this instruction addresses an INDF register and the MSb of the corresponding FSR is set, this instruction will require one additional instruction cycle.

3: See Section 34.2 "Instruction Descriptions" for detailed MOVIW and MOVWI instruction descriptions.

TABLE 34-3:	PIC16(L)F18326/18346 INSTRUCTION SET ((CONTINUED))
-------------	--	-------------	---

Mnemonic, Operands		Description	Cycles	14-bit Opcode				Status	Nataa
		Description		MSb			LSb	Affected	Notes
		INHERENT OPERA	TIONS						
CLRWDT	_	Clear Watchdog Timer	1	00	0000	0110	0100	TO, PD	
NOP	_	No Operation	1	00	0000	0000	0000		
RESET	_	Software device Reset	1	00	0000	0000	0001		
SLEEP	_	Go into Standby mode	1	00	0000	0110	0011	TO, PD	
TRIS	f	Load TRIS register with W	1	00	0000	0110	Offf		
		C-COMPILER OPT	IMIZED						
ADDFSR	n, k	Add Literal k to FSRn	1	11	0001	0nkk	kkkk		
MOVIW	n mm	Move Indirect FSRn to W with pre/post inc/dec	1	00	0000	0001	0nmm	Z	2, 3
		modifier, mm							
	k[n]	Move INDFn to W, Indexed Indirect.	1	11	1111	0nkk	kkkk	Z	2
MOVWI	n mm	Move W to Indirect FSRn with pre/post inc/dec	1	00	0000	0001	1nmm		2, 3
		modifier, mm							
	k[n]	Move W to INDFn, Indexed Indirect.	1	11	1111	1nkk	kkkk		2

Note 1: If the Program Counter (PC) is modified, or a conditional test is true, the instruction requires two cycles. The second cycle is executed as a NOP.

2: If this instruction addresses an INDF register and the MSb of the corresponding FSR is set, this instruction will require one additional instruction cycle.

3: See Section 34.2 "Instruction Descriptions" for detailed MOVIW and MOVWI instruction descriptions.

34.2 Instruction Descriptions

ADDFSR	Add Literal to FSRn
Syntax:	[label] ADDFSR FSRn, k
Operands:	-32 ≤ k ≤ 31 n ∈ [0, 1]
Operation:	$FSR(n) + k \rightarrow FSR(n)$
Status Affected:	None
Description:	The signed 6-bit literal 'k' is added to the contents of the FSRnH:FSRnL register pair.
	FSRn is limited to the range 0000h-FFFFh. Moving beyond these bounds will cause the FSR to

ANDLW	AND literal with W
Syntax:	[<i>label</i>] ANDLW k
Operands:	$0 \leq k \leq 255$
Operation:	(W) .AND. (k) \rightarrow (W)
Status Affected:	Z
Description:	The contents of W register are AND'ed with the 8-bit literal 'k'. The result is placed in the W register.

ADDLW	Add literal and W
Syntax:	[label] ADDLW k
Operands:	$0 \leq k \leq 255$
Operation:	$(W) + k \to (W)$
Status Affected:	C, DC, Z
Description:	The contents of the W register are added to the 8-bit literal 'k' and the result is placed in the W register.

wrap-around.

ANDWF	AND W with f
Syntax:	[<i>label</i>] ANDWF f,d
Operands:	$0 \le f \le 127$ $d \in [0,1]$
Operation:	(W) .AND. (f) \rightarrow (destination)
Status Affected:	Z
Description:	AND the W register with register 'f'. If 'd' is '0', the result is stored in the W register. If 'd' is '1', the result is stored back in register 'f'.

ADDWF	Add W and f		
Syntax:	[<i>label</i>] ADDWF f,d		
Operands:	$0 \le f \le 127$ $d \in [0,1]$		
Operation:	(W) + (f) \rightarrow (destination)		
Status Affected:	C, DC, Z		
Description:	Add the contents of the W register with register 'f'. If 'd' is '0', the result is stored in the W register. If 'd' is '1', the result is stored back in register 'f'.		

ASRF	Arithmetic Right Shift
Syntax:	[<i>label</i>]ASRF f{,d}
Operands:	$\begin{array}{l} 0\leq f\leq 127\\ d\in[0,1] \end{array}$
Operation:	(f<7>)→ dest<7> (f<7:1>) → dest<6:0>, (f<0>) → C,
Status Affected:	C, Z
Description:	The contents of register 'f' are shifted one bit to the right through the Carry flag. The MSb remains unchanged. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is stored back in

register 'f'.



ADDWFC ADD W and CARRY bit to f

Syntax:	[<i>label</i>] ADDWFC f {,d}
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	$(W) + (f) + (C) \rightarrow dest$
Status Affected:	C, DC, Z
Description:	Add W, the Carry flag and data mem- ory location 'f'. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is placed in data memory location 'f'.

BCF	Bit Clear f
Syntax:	[<i>label</i>]BCF f,b
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ 0 \leq b \leq 7 \end{array}$
Operation:	$0 \rightarrow (f \le b >)$
Status Affected:	None
Description:	Bit 'b' in register 'f' is cleared.

BTFSC	Bit Test f, Skip if Clear
Syntax:	[label] BTFSC f,b
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ 0 \leq b \leq 7 \end{array}$
Operation:	skip if (f) = 0
Status Affected:	None
Description:	If bit 'b' in register 'f' is '1', the next instruction is executed. If bit 'b', in register 'f', is '0', the next instruction is discarded, and a NOP is executed instead, making this a two-cycle instruction.

BRA	Relative Branch	BTFSS	Bit Test f, Skip if Set
Syntax:	[<i>label</i>]BRA label	Syntax:	[label] BTFSS f,b
	[<i>label</i>]BRA \$+k	Operands:	$0 \le f \le 127$
Operands:	$-256 \le label - PC + 1 \le 255$		0 ≤ b < 7
	$-256 \le k \le 255$	Operation:	skip if (f) = 1
Operation:	$(PC) + 1 + k \rightarrow PC$	Status Affected:	None
Status Affected:	None	Description:	If bit 'b' in register 'f' is '0', the next
Description:	Add the signed 9-bit literal 'k' to the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 1 + k. This instruction is a two-cycle instruction. This branch has a limited range.		instruction is executed. If bit 'b' is '1', then the next instruction is discarded and a NOP is executed instead, making this a two-cycle instruction.

BRW	Relative Branch	with	w

Syntax:	[<i>label</i>] BRW
Operands:	None
Operation:	$(PC) + (W) \rightarrow PC$
Status Affected:	None
Description:	Add the contents of W (unsigned) to the PC. Since the PC will have incremented to fetch the next instruction, the new address will be PC + 1 + (W). This instruction is a two-cycle instruction.

BSF	Bit Set f
Syntax:	[<i>label</i>]BSF f,b
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ 0 \leq b \leq 7 \end{array}$
Operation:	$1 \rightarrow (f \le b >)$
Status Affected:	None
Description:	Bit 'b' in register 'f' is set.

CALL	Call Subroutine
Syntax:	[<i>label</i>] CALL k
Operands:	$0 \leq k \leq 2047$
Operation:	$\begin{array}{l} (PC)+1 \rightarrow TOS, \\ k \rightarrow PC<10:0>, \\ (PCLATH<6:3>) \rightarrow PC<14:11> \end{array}$
Status Affected:	None
Description:	Call Subroutine. First, return address (PC + 1) is pushed onto the stack. The 11-bit immediate address is loaded into PC bits <10:0>. The upper bits of the PC are loaded from PCLATH. CALL is a two-cycle instruction.

CLRWDT	Clear Watchdog Timer
Syntax:	[label] CLRWDT
Operands:	None
Operation:	$\begin{array}{l} \text{O0h} \rightarrow \text{WDT} \\ 0 \rightarrow \text{WDT} \text{ prescaler,} \\ 1 \rightarrow \overline{\text{TO}} \\ 1 \rightarrow \overline{\text{PD}} \end{array}$
Status Affected:	TO, PD
Description:	CLRWDT instruction resets the Watch- dog Timer. It also resets the prescaler of the WDT. Status bits \overline{TO} and \overline{PD} are set.

CALLW	Subroutine Call With W	COMF	Complement
Syntax:	[label] CALLW	Syntax:	[label] COMF
Operands:	None	Operands:	0≤f≤127 d∈[0,1]
Operation:	(PC) +1 → TOS, (W) → PC<7:0>, (PCLATH<6:0>) → PC<14:8>	Operation: Status Affected:	$(f) \rightarrow (destination)$
Status Affected: Description:	None Subroutine call with W. First, the return address (PC + 1) is pushed onto the return stack. Then, the contents of W is loaded into PC<7:0>, and the contents of PCLATH into PC<14:8>. CALLW is a two-cycle instruction.	Description:	The contents of complemented. stored in W. If 'd stored back in re

MF	Complement f
tax:	[<i>label</i>] COMF f,d
erands:	$0 \le f \le 127$ $d \in [0,1]$
eration:	$(\overline{f}) \rightarrow (destination)$
us Affected:	Z
cription:	The contents of register 'f' are complemented. If 'd' is '0', the result is stored in W. If 'd' is '1', the result is stored back in register 'f'.

CLRF	Clear f
Syntax:	[label] CLRF f
Operands:	$0 \leq f \leq 127$
Operation:	$\begin{array}{l} 00h \rightarrow (f) \\ 1 \rightarrow Z \end{array}$
Status Affected:	Z
Description:	The contents of register 'f' are cleared and the Z bit is set.

DECF	Decrement f
Syntax:	[<i>label</i>] DECF f,d
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	(f) - 1 \rightarrow (destination)
Status Affected:	Z
Description:	Decrement register 'f'. If 'd' is '0', the result is stored in the W register. If 'd' is '1', the result is stored back in register 'f'.

CLRW	Clear W
Syntax:	[<i>label</i>] CLRW
Operands:	None
Operation:	$\begin{array}{l} 00h \rightarrow (W) \\ 1 \rightarrow Z \end{array}$
Status Affected:	Z
Description:	W register is cleared. Zero (Z) bit is set.

DECFSZ	Decrement f, Skip if 0
Syntax:	[<i>label</i>] DECFSZ f,d
Operands:	$0 \le f \le 127$ $d \in [0,1]$
Operation:	(f) - 1 \rightarrow (destination); skip if result = 0
Status Affected:	None
Description:	The contents of register 'f' are decre- mented. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed back in register 'f'. If the result is '1', the next instruction is executed. If the result is '0', then a NOP is executed instead, making it a two-cycle instruction.

GOTO	Unconditional Branch
Syntax:	[<i>label</i>] GOTO k
Operands:	$0 \leq k \leq 2047$
Operation:	$k \rightarrow PC<10:0>$ PCLATH<6:3> \rightarrow PC<14:11>
Status Affected:	None
Description:	GOTO is an unconditional branch. The 11-bit immediate value is loaded into PC bits <10:0>. The upper bits of PC are loaded from PCLATH<4:3>. GOTO is a two-cycle instruction.

INCFSZ	Increment f, Skip if 0
Syntax:	[<i>label</i>] INCFSZ f,d
Operands:	$\begin{array}{l} 0\leq f\leq 127\\ d\in [0,1] \end{array}$
Operation:	(f) + 1 \rightarrow (destination), skip if result = 0
Status Affected:	None
Description:	The contents of register 'f are incre- mented. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed back in register 'f'. If the result is '1', the next instruction is executed. If the result is '0', a NOP is executed instead, making it a two-cycle instruction.

IORLW	Inclusive OR literal with W
Syntax:	[<i>label</i>] IORLW k
Operands:	$0 \leq k \leq 255$
Operation:	(W) .OR. $k \rightarrow$ (W)
Status Affected:	Z
Description:	The contents of the W register are OR'ed with the 8-bit literal 'k'. The result is placed in the W register.

INCF	Increment f
Syntax:	[<i>label</i>] INCF f,d
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	(f) + 1 \rightarrow (destination)
Status Affected:	Z
Description:	The contents of register 'f' are incre- mented. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed back in register 'f'.

IORWF	Inclusive OR W with f
Syntax:	[<i>label</i>] IORWF f,d
Operands:	$0 \le f \le 127$ $d \in [0,1]$
Operation:	(W) .OR. (f) \rightarrow (destination)
Status Affected:	Z
Description:	Inclusive OR the W register with regis- ter 'f'. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed back in register 'f'.

LSLF	Logical Left Shift
Syntax:	[<i>label</i>]LSLF f{,d}
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	$(f<7>) \rightarrow C$ $(f<6:0>) \rightarrow dest<7:1>$ $0 \rightarrow dest<0>$
Status Affected:	C, Z
Description:	The contents of register 'f are shifted one bit to the left through the Carry flag. A '0' is shifted into the LSb. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is stored back in register 'f'.
	C ← register f ←0

LSRF	Logical Right Shift
Syntax:	[<i>label</i>] LSRF f {,d}
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	$\begin{array}{l} 0 \rightarrow \text{dest<7>} \\ (\text{f<7:1>}) \rightarrow \text{dest<6:0>}, \\ (\text{f<0>}) \rightarrow \text{C}, \end{array}$
Status Affected:	C, Z
Description:	The contents of register 'f are shifted one bit to the right through the Carry flag. A '0' is shifted into the MSb. If 'd' is '0', the result is placed in W. If 'd' is '1', the result is stored back in register 'f'.
	0 → register f → C

MOVF	Move f
Syntax:	[<i>label</i>] MOVF f,d
Operands:	$0 \le f \le 127$ $d \in [0,1]$
Operation:	$(f) \rightarrow (dest)$
Status Affected:	Z
Description:	The contents of register f is moved to a destination dependent upon the status of d. If d = 0, destination is W register. If d = 1, the destination is file register f itself. d = 1 is useful to test a file register since status flag Z is affected.
Words:	1
Cycles:	1
Example:	MOVF FSR, 0
	After Instruction W = value in FSR register Z = 1

ΜΟνιω	Move INDFn to W
Syntax:	[<i>label</i>] MOVIW ++FSRn [<i>label</i>] MOVIWFSRn [<i>label</i>] MOVIW FSRn++ [<i>label</i>] MOVIW FSRn [<i>label</i>] MOVIW k[FSRn]
Operands:	n ∈ [0,1] mm ∈ [00,01,10,11] -32 ≤ k ≤ 31
Operation:	$\begin{split} &\text{INDFn} \rightarrow W \\ &\text{Effective address is determined by} \\ &\text{FSR + 1 (preincrement)} \\ &\text{FSR - 1 (predecrement)} \\ &\text{FSR + k (relative offset)} \\ &\text{After the Move, the FSR value will be} \\ &\text{either:} \\ &\text{FSR + 1 (all increments)} \\ &\text{FSR - 1 (all decrements)} \\ &\text{Unchanged} \end{split}$
Status Affected:	Z

Mode	Syntax	mm
Preincrement	++FSRn	00
Predecrement	FSRn	01
Postincrement	FSRn++	10
Postdecrement	FSRn	11

Description:

This instruction is used to move data between W and one of the indirect registers (INDFn). Before/after this move, the pointer (FSRn) is updated by pre/post incrementing/decrementing it.

Note: The INDFn registers are not physical registers. Any instruction that accesses an INDFn register actually accesses the register at the address specified by the FSRn.

FSRn is limited to the range 0000h -FFFFh. Incrementing/decrementing it beyond these bounds will cause it to wrap-around.

Syntax:	[<i>label</i>]MOVLB k
Operands:	$0 \leq k \leq 31$
Operation:	$k \rightarrow BSR$
Status Affected:	None
Description:	The 5-bit literal 'k' is loaded into the Bank Select Register (BSR).

MOVLP	Move literal to PCLATH
Syntax:	[<i>label</i>] MOVLP k
Operands:	$0 \le k \le 127$
Operation:	$k \rightarrow PCLATH$
Status Affected:	None
Description:	The 7-bit literal 'k' is loaded into the PCLATH register.
MOVLW	Move literal to W
Syntax:	[<i>label</i>] MOVLW k
Operands:	$0 \le k \le 255$
Operation:	$k \rightarrow (W)$
Status Affected:	None
Description:	The 8-bit literal 'k' is loaded into W reg- ister. The "don't cares" will assemble as '0's.
Words:	1
Cycles:	1
Example:	MOVLW 0x5A
	After Instruction W = 0x5A
MOVWF	Move W to f
Syntax:	[<i>label</i>] MOVWF f
Operands:	$0 \le f \le 127$
Operation:	$(W) \rightarrow (f)$
Status Affected:	None
Description:	Move data from W register to register 'f.
Words:	1
Cycles:	1
Example:	MOVWF OPTION_REG
	Before Instruction OPTION_REG = 0xFF W = 0x4F After Instruction OPTION_REG = 0x4F W = 0x4F

ΜΟΥΨΙ	Move W to INDFn
Syntax:	[<i>label</i>] MOVWI ++FSRn [<i>label</i>] MOVWIFSRn [<i>label</i>] MOVWI FSRn++ [<i>label</i>] MOVWI FSRn [<i>label</i>] MOVWI k[FSRn]
Operands:	n ∈ [0,1] mm ∈ [00,01,10,11] -32 ≤ k ≤ 31
Operation:	 W → INDFn Effective address is determined by FSR + 1 (preincrement) FSR - 1 (predecrement) FSR + k (relative offset) After the Move, the FSR value will be either: FSR + 1 (all increments) FSR - 1 (all decrements) Unchanged
Status Affected:	None

Mode	Syntax	mm
Preincrement	++FSRn	00
Predecrement	FSRn	01
Postincrement	FSRn++	10
Postdecrement	FSRn	11

Description:

This instruction is used to move data between W and one of the indirect registers (INDFn). Before/after this move, the pointer (FSRn) is updated by pre/post incrementing/decrementing it.

Note: The INDFn registers are not physical registers. Any instruction that accesses an INDFn register actually accesses the register at the address specified by the FSRn.

FSRn is limited to the range 0000h-FFFFh. Incrementing/decrementing it beyond these bounds will cause it to wrap-around.

The increment/decrement operation on FSRn WILL NOT affect any Status bits.

NOP	No Operation
Syntax:	[<i>label</i>] NOP
Operands:	None
Operation:	No operation
Status Affected:	None
Description:	No operation.
Words:	1
Cycles:	1
Example:	NOP

RESET	Software Reset
Syntax:	[label] RESET
Operands:	None
Operation:	Execute a device Reset. Resets the RI flag of the PCON register.
Status Affected:	None
Description:	This instruction provides a way to execute a hardware Reset by software.

RETFIE	Return from Interrupt	
Syntax:	[<i>label</i>] RETFIE k	
Operands:	None	
Operation:	$TOS \rightarrow PC,$ 1 \rightarrow GIE	
Status Affected:	None	
Description:	Return from Interrupt. Stack is POPed and Top-of-Stack (TOS) is loaded in the PC. Interrupts are enabled by setting Global Interrupt Enable (GIE) bit (INTCON<7>). This is a two-cycle instruction.	
Words:	1	
Cycles:	2	
Example:	RETFIE	
	After Interrupt PC = TOS GIE = 1	

RETLW	Return with literal in W	
Syntax:	[<i>label</i>] RETLW k	
Operands:	$0 \le k \le 255$	
Operation:	$k \rightarrow (W);$ TOS \rightarrow PC	
Status Affected:	None	
Description:	The W register is loaded with the 8-bit literal 'k'. The program counter is loaded from the top of the stack (the return address). This is a two-cycle instruction.	
Words:	1	
Cycles:	2	
Example:	CALL TABLE;W contains table ;offset value • ;W now has table value	
TABLE	• • ADDWF PC ;W = offset RETLW k1 ;Begin table RETLW k2 ; • • • RETLW kn ; End of table	

Before Instruction		
W =	0x07	
After Instruction		
W =	value of k8	

RETURN Return from Subroutine

Syntax:	[label] RETURN
Operands:	None
Operation:	$TOS \rightarrow PC$
Status Affected:	None
Description:	Return from subroutine. The stack is POPed and the top of the stack (TOS) is loaded into the program counter. This is a two-cycle instruction.

RLF	Rotate Left f through Carry		
Syntax:	[<i>label</i>] RLF f,d		
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$		
Operation:	See description below		
Status Affected:	С		
Description:	The contents of register 'f' are rotated one bit to the left through the Carry flag. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is stored back in register 'f'.		
Words:	1		
Cycles:	1		
Example:	RLF REG1,0		
	Before Instruction		
	REG1 = 1110 0110		
	C = 0		
	After Instruction		
	REG1 = 1110 0110		
	$W = 1100 \ 1100$		
	C = 1		

RRF	Rotate Right f through Carry
Syntax:	[<i>label</i>] RRF f,d
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	See description below
Status Affected:	С
Description:	The contents of register 'f' are rotated one bit to the right through the Carry flag. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed back in register 'f'.



SLEEP	Enter Sleep mode
Syntax:	[label] SLEEP
Operands:	None
Operation:	$\begin{array}{l} \text{O0h} \rightarrow \text{WDT,} \\ 0 \rightarrow \text{WDT prescaler,} \\ 1 \rightarrow \overline{\text{TO}}, \\ 0 \rightarrow \text{PD} \end{array}$
Status Affected:	TO, PD
Description:	The power-down Status bit, \overline{PD} is cleared. Time-out Status bit, \overline{TO} is set. Watchdog Timer and its prescaler are cleared. See Section 9.2 "Sleep Mode" for more information.

SUBWF	Subtract W	/ from f	
Syntax:	[label] SL	JBWF f,d	
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$		
Operation:	(f) - (W) \rightarrow (c	lestination)	
Status Affected:	C, DC, Z		
Description:	Subtract (2's complement method) W register from register 'f'. If 'd' is '0', the result is stored in the W register. If 'd' is '1', the result is stored back in register 'f.		
	C = 0	W > f	
	C = 1	$W \leq f$	
	DC = 0	W<3:0> > f<3:0>	
	DC = 1	W<3:0> ≤ f<3:0>	

SUBWFB	Subtract W from f with Borrow
Syntax:	SUBWFB f {,d}
Operands:	$\begin{array}{l} 0\leq f\leq 127\\ d\in [0,1] \end{array}$
Operation:	$(f) - (W) - (\overline{B}) \rightarrow dest$
Status Affected:	C, DC, Z
Description:	Subtract W and the BORROW flag (CARRY) from register 'f' (2's complement method). If 'd' is '0', the result is stored in W. If 'd' is '1', the result is stored back in register 'f'.

SUBLW	Subtract W from literal		
Syntax:	[label] SL	IBLW k	
Operands:	$0 \leq k \leq 255$		
Operation:	$k \text{-} (W) \rightarrow (W)$		
Status Affected:	C, DC, Z		
Description:	The W register is subtracted (2's complement method) from the 8-bit literal 'k'. The result is placed in the W register.		
	C = 0	W > k	
	C = 1	$W \leq k$	
	DC = 0	W<3:0> > k<3:0>	

 $W<3:0> \le k<3:0>$

DC = 1

SWAPF	Swap Nibbles in f
Syntax:	[<i>label</i>] SWAPF f,d
Operands:	$\begin{array}{l} 0 \leq f \leq 127 \\ d \in [0,1] \end{array}$
Operation:	$(f<3:0>) \rightarrow (destination<7:4>),$ $(f<7:4>) \rightarrow (destination<3:0>)$
Status Affected:	None
Description:	The upper and lower nibbles of register 'f' are exchanged. If 'd' is '0', the result is placed in the W register. If 'd' is '1', the result is placed in register 'f'.

TRIS	Load TRIS Register with W
Syntax:	[<i>label</i>] TRIS f
Operands:	$5 \leq f \leq 7$
Operation:	(W) \rightarrow TRIS register 'f'
Status Affected:	None
Description:	Move data from W register to TRIS register. When 'f' = 5, TRISA is loaded. When 'f' = 6, TRISB is loaded. When 'f' = 7, TRISC is loaded.

XORLW	Exclusive OR literal with W		
Syntax:	[<i>label</i>] XORLW k		
Operands:	$0 \leq k \leq 255$		
Operation:	(W) .XOR. $k \rightarrow (W)$		
Status Affected:	Z		
Description:	The contents of the W register are XOR'ed with the 8-bit literal 'k'. The result is placed in the W register.		

XORWF	Exclusive OR W with f		
Syntax:	[<i>label</i>] XORWF f,d		
Operands:	$0 \le f \le 127$ $d \in [0,1]$		
Operation:	(W) .XOR. (f) \rightarrow (destination)		
Status Affected:	Z		
Description:	Exclusive OR the contents of the W register with register 'f'. If 'd' is '0', the result is stored in the W register. If 'd' is '1', the result is stored back in register 'f'.		

35.0 ELECTRICAL SPECIFICATIONS

35.1 Absolute Maximum Ratings^(†)

Ambient temperature under bias	40°C to +125°C
Storage temperature	65°C to +150°C
Voltage on pins with respect to Vss	
on VDD pin	
PIC16F18326/18346	0.3V to +6.5V
PIC16LF18326/18346	
on MCLR pin	0.3V to +9.0V
on all other pins	
Maximum current	
on Vss pin ⁽¹⁾	
-40°C \leq Ta \leq +85°C	350 mA
+85°C < Ta \leq +125°C	120 mA
on VDD pin ⁽¹⁾ for 28L-Pin Devices	
-40°C \leq Ta \leq +85°C	250 mA
+85°C < Ta \leq +125°C	120 mA
on any I/O pin	±50 mA
Clamp current, Iк (VPIN < 0 or VPIN > VDD)	±20 mA
Total power dissipation ⁽²⁾	800 mW


Note 1: Maximum current rating requires even load distribution across I/O pins. Maximum current rating may be limited by the device package power dissipation characterizations, see Table 35-3 to calculate device specifications. See technical brief TBxxxx for more details on maximum current requirements.

2: Power dissipation is calculated as follows: PDIS = VDD x {IDD $- \sum IOH$ } + $\sum {(VDD - VOH) x IOH}$ + $\sum (VOL x IOL)$.


† NOTICE: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure above maximum rating conditions for extended periods may affect device reliability.

35.2 Standard Operating Conditions

The standard operating co	onditions for any device are defined as:	
Operating Voltage: Operating Temperature:	$ \begin{array}{l} V \text{DDMIN} \leq V \text{DD} \leq V \text{DDMAX} \\ T \text{A}_\text{MIN} \leq T \text{A} \leq T \text{A}_\text{MAX} \end{array} $	
VDD — Operating Supply	y Voltage ⁽¹⁾	
PIC16LF18326/183	346	
VDDMIN (F	Fosc ≤ 16 MHz)	+1.8V
VDDMIN (F	Fosc ≤ 32 MHz)	+2.5V
VDDMAX		+3.6V
PIC16F18326/1834	46	
VDDMIN (F	Fosc ≤ 16 MHz)	+2.3V
VDDMIN (F	Fosc ≤ 32 MHz)	+2.5V
VDDMAX		+5.5V
TA — Operating Ambient	t Temperature Range	
Industrial Temperat	ture	
TA_MIN		-40°C
Та_мах		+85°C
Extended Temperat	ture	
TA_MIN		-40°C
Та_мах		+125°C
Note 1: See Paramete	er D002, DC Characteristics: Supply Voltage.	







35.3 DC Characteristics

TABLE 35-1:SUPPLY VOLTAGE


PIC16LF	C16LF18326/18346 Standard Operating Conditions (unless otherwi						ns (unless otherwise stated)			
PIC16F1	8326/183	46	Standard Operating Conditions (unless otherwise stated							
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions			
Supply Voltage										
D002	Vdd		1.8 2.5	-	3.6 3.6	V V	Fosc ≤ 16 MHz Fosc > 16 MHz			
D002	VDD		2.3 2.5		5.5 5.5	V V	Fosc ≤ 16 MHz Fosc > 16 MHz			
RAM Data Retention ⁽¹⁾										
D003	Vdr		1.5	_	—	V	Device in Sleep mode			
D003	Vdr		1.7		—	V	Device in Sleep mode			
Power-c	on Reset F	Release Voltage ⁽²⁾								
D004	VPOR		_	1.6	_	V	BOR and LPBOR disabled ⁽³⁾			
D004	VPOR		—	1.6		V	BOR and LPBOR disabled ⁽³⁾			
Power-c	on Reset F	ReARM Voltage ⁽²⁾								
D005	VPORR		_	0.8		V	BOR and LPBOR disabled ⁽³⁾			
D005	VPORR		—	1.5		V	BOR and LPBOR disabled ⁽³⁾			
VDD Ris	e Rate to	ensure Internal Power-on	Reset Si	ignal ⁽²⁾			•			
D006	SVDD		0.05	_		V/ms	BOR and LPBOR disabled ⁽³⁾			
D006	SVDD		0.05	—		V/ms	BOR and LPBOR disabled ⁽³⁾			

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: This is the limit to which VDD can be lowered in Sleep mode or during a device Reset, without losing RAM data.

2: See Figure 35-3, POR and POR ReARM with Slow Rising VDD.

3: See Table 35-11 for BOR and LPBOR trip point information.



PIC16LF1	8326/18346	Standard Operating Conditions	Standard Operating Conditions (unless otherwise stated) Standard Operating Conditions (unless otherwise stated)								
PIC16F18	326/18346	Standard Operating Conditions									
Param.	Cumhal	Device Characteristics	Min	Тур.	Мах	Lin:to	Conditions				
No.	Symbol	Device Characteristics		†	•	Units	Vdd	Note			
D100	IDDXT4	XT = 4 MHz		321	455	uA	3.0V				
D100	IDDXT4	XT = 4 MHz		332	479	uA	3.0V				
D101	IDDHF016	HFO = 16 MHz	—	1.3	1.8	mA	3.0V				
D101	IDDHF016	HFO = 16 MHz		1.4	1.9	mA	3.0V				
D102	IDDHFOPLL	HFO = 32 MHz		2.2	2.8	mA	3.0V				
D102	IDDHFOPLL	HFO = 32 MHz		2.3	2.9	mA	3.0V	32 MHz PIC16			
D103	IDDHSPLL32	HS+PLL = 32 MHz		2.2	2.8	mA	3.0V				
D103	IDDHSPLL32	HS+PLL = 32 MHz		2.3	2.9	mA	3.0V				
D104	IDDIDLE	Idle Mode, HFINTOSC = 16 MHz	_	804	128 3	uA	3.0V				
D104	IDDIDLE	Idle Mode, HFINTOSC = 16 MHz	_	816	128 4	uA	3.0V				
D105	IDDDOZE ⁽³⁾	Doze mode, HFO = 16 MHz, DOZE Ratio = 16	_	863	_	uA	3.0V	Typical value only, no			
D105	IDDDOZE ⁽³⁾	Doze mode, HFO = 16 MHz, DOZE Ratio = 16	_	875		uA	3.0V	maximum value required.			

TABLE 35-2: SUPPLY CURRENT (IDD)^(1,2)

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: The test conditions for all IDD measurements in active operation mode are: OSC1 = external square wave, from rail-to-rail; all I/O pins tri-stated, pulled to VDD; MCLR = VDD; WDT disabled.

- **2:** The supply current is mainly a function of the operating voltage and frequency. Other factors, such as I/O pin loading and switching rate, oscillator type, internal code execution pattern and temperature, also have an impact on the current consumption.
- 3: IDDDOZE = [IDDIDLE*(N-1)/N] + IDDHF016/N where N = DOZE Ration (see Register 9-2).

4: PMD bits are all in the default state, no modules are disabled.

PIC16LF	-18326/1834	6	Stand	ard Ope	erating	Conditio	ns (unl	ess ot	herwise stated)	
PIC16F1	18326/18346		Standard Operating Conditions (unless otherwise stated) VREGPM = 1						herwise stated)	
Param.	Symbol	Device Characteristics	Min.	Tun +	Max.	Max.	Units	Conditions		
No.	Symbol	Device Characteristics	wiin.	Тур.†	+85°C	+125°C	Units	VDD	Note	
D200	IPD	IPD Base	—	0.05	2	5.5	μA	3.0V		
D200	IPD	IPD Base		0.4	2.5	6	μA	3.0V		
D200A			—	13	22	27	μA	3.0V	VREGPM = 0	
D201	IPD_WDT	Low-Frequency Internal Oscillator/WDT	—	0.9	2.9	6	μA	3.0V		
D201	IPD_WDT	Low-Frequency Internal Oscillator/WDT	—	1.1	3.3	6.6	μA	3.0V		
D202	IPD_SOSC	Secondary Oscillator (SOSC)	_	2.7	4	9.6	μA	3.0V		
D202	IPD_SOSC	Secondary Oscillator (SOSC)	_	3.0	6.8	10	μΑ	3.0V		
D203	IPD_FVR	FVR	—	40	76	76	μΑ	3.0V		
D203	IPD_FVR	FVR	_	33	76	76	μΑ	3.0V		
D204	IPD_BOR	Brown-out Reset (BOR)	—	12	17	19	μA	3.0V		
D204	IPD_BOR	Brown-out Reset (BOR)	—	12	21	23	μΑ	3.0V		
D205	IPD_LPBOR	Low Power Brown-out Reset (LPBOR)	_	1.0	5	13	μA	3.0V		
D205	IPD_LPBOR	Low Power Brown-out Reset (LPBOR)	—	1.2	5	13	μA	3.0V		
D206	IPD_ADCA	ADC - Non converting	—	0.9	5.0	13	μA	3.0V		
D206	IPD_ADCA	ADC - Non converting	—	0.9	5.0	13	μA	3.0V		
D207	IPD_ADCA	ADC - Active		0.9	5	13	μA	3.0V	ADC is converting ⁽⁴⁾	
D207	IPD_ADCA	ADC - Active	—	0.9	5	13	μA	3.0V	ADC is converting ⁽⁴⁾	
D208	IPD_CMP	Comparator	—	35	45	50	μA	3.0V	High-Power Mode	
D208	IPD_CMP	Comparator	—	36	44	50	μA	3.0V	High-Power Mode	

TABLE 35-3: POWER-DOWN CURRENTS (IPD)^(1,2,3)

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: The peripheral current is the sum of the base IPD and the additional current consumed when this peripheral is enabled. The peripheral ∆ current can be determined by subtracting the base IDD or IPD current from this limit. Max values may be used when calculating total current consumption.

2: The power-down current in Sleep mode does not depend on the oscillator type. Power-down current is measured with the part in Sleep mode, with all I/O pins in high-impedance state and tied to Vss.

3: All peripheral currents listed are on a per-peripheral basis if more than one instance of a peripheral is available.

4: ADC clock source is ADCRC.

DC CHA	RACTI	ERISTICS	Standard Oper	Standard Operating Conditions (unless otherwise stated)						
Param. No.	Sym.	Characteristic	Min.	Тур.†	Max.	Units	Conditions			
	VIL	Input Low Voltage								
		I/O PORT:								
D300		with TTL buffer		_	0.8	V	$4.5V \leq V\text{DD} \leq 5.5V$			
D301				_	0.15 Vdd	V	$1.8V \leq V\text{DD} \leq 4.5V$			
D302		with Schmitt Trigger buffer		_	0.2 Vdd	V	$2.0V \leq V\text{DD} \leq 5.5V$			
D303		with I ² C levels	—	_	0.3 Vdd	V				
D304		with SMBus levels	—	_	0.8	V	$2.7V \leq V\text{DD} \leq 5.5V$			
D305		MCLR		_	0.2 Vdd	V				
	VIH	Input High Voltage								
		I/O PORT:								
D320		with TTL buffer	2.0	_	_	V	$4.5V \leq V\text{DD} \leq 5.5V$			
D321			0.25 VDD + 0.8	_	_	V	$1.8V \leq V\text{DD} \leq 4.5V$			
D322		with Schmitt Trigger buffer	0.8 Vdd	_	_	V	$2.0V \leq V\text{DD} \leq 5.5V$			
D323		with I ² C levels	0.7 Vdd	_	—	V				
D324		with SMBus levels	2.1	_	—	V	$2.7V \leq V\text{DD} \leq 5.5V$			
D325		MCLR	0.7 Vdd		—	V				
	lı∟	Input Leakage Current ⁽²⁾								
D340		I/O Ports	_	± 5	± 125	nA	Vss ≤ VPIN ≤ VDD, Pin at high-impedance, 85°C			
D341			_	± 5	± 1000	nA	$\label{eq:VSS} \begin{split} VSS &\leq V PIN \leq V DD, \\ Pin \ at \ high-impedance, \ 125^\circ C \end{split}$			
D342		MCLR ⁽²⁾	_	± 50	± 200	nA	Vss ≤ VPIN ≤ VDD, Pin at high-impedance, 85°C			
	IPUR	Weak Pull-up Current								
D350			25	120	200	μA	VDD = 3.0V, VPIN = VSS			
	Vol	Output Low Voltage ⁽³⁾								
D360		I/O ports	—	_	0.6	V	IOL = 10.0 mA, VDD = 3.0V			
	Vон	Output High Voltage ⁽³⁾								
D370		I/O ports	Vdd - 0.7	_	_	V	ЮН = 6.0 mA, VDD = 3.0V			
D380	Сю	All I/O pins	_	5	50	pF				

TABLE 35-4: I/O PORTS⁽¹⁾

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: Negative current is defined as current sourced by the pin.

2: The leakage current on the MCLR pin is strongly dependent on the applied voltage level. The specified levels represent normal operating conditions. Higher leakage current may be measured at different input voltages.

Standar	d Operatir	ng Conditions (unless otherwise s	stated)				
Param. No.	Sym.	Characteristic	Min.	Тур.†	Max.	Units	Conditions
High Vol	tage Entr	y Programming Mode Specification	ons				
MEM01	Vінн	Voltage on MCLR/VPP pin to enter Programming mode	8	—	9	V	(2)
MEM02	IPPGM	Current on MCLR/VPP pin during Programming mode	_	_	600	uA	(2)
Program	ming Mo	de Specifications				•	
MEM10	VBE	VDD for Bulk Erase		2.7		V	
MEM11	IDDPGM	Supply Current during Programming Operation	_	_	3	mA	
Data EE	PROM Me	mory Specifications				•	
MEM20	ED	DataEE Byte Endurance	100k	_		E/W	$-40^\circ C \le T A \le 85^\circ C$
MEM22	TD_REF	Total Erase/Write Cycles before Refresh	_	40	_	Year	Provided no other specifications are violated
MEM23	VD_RW	VDD for Read or Erase/Write Operation	VDDMIN	_	VDDMAX	V	
MEM24	TD_BEW	Byte Erase and Write Cycle Time		4.0	5.0	ms	
Program	Flash Me	emory Specifications					
MEM30	Eр	Flash Memory Cell Endurance	10k	_	_	E/W	$\begin{array}{l} -40^{\circ}C \leq TA \leq 85^{\circ}C \\ \textbf{(1)} \end{array}$
MEM31	EPHEF	High-Endurance Flash Memory Cell Endurance	100k	_	_	E/W	TBD
MEM32	TP_RET	Characteristic Retention	_	40	_	Year	Provided no other specifications are violated
MEM33	VP_RD	VDD for Read Operation	VDDMIN	_	VDDMAX	V	
MEM34	VP_REW	VDD for Row Erase or Write Operation	VDDMIN		VDDMAX	V	
MEM35	TP_REW	Self-Timed Row Erase or Self-Timed Write		2.0	2.5	ms	

TABLE 35-5: I/O AND CLOCK TIMING SPECIFICATIONS

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: Flash Memory Cell Endurance for the Flash memory is defined as: One Row Erase operation and one Self-Timed Write.

2: Required only if CONFIG3.LVP is disabled.


Standa	rd Operating	g Conditions (unless otherwise s	stated)		
Param. No.	Sym.	Characteristic	Тур.	Units	Conditions
TH01	θJA	Thermal Resistance Junction to	70.0	°C/W	14-pin PDIP package
		Ambient	95.3	°C/W	14-pin SOIC package
			100.0	°C/W	14-pin TSSOP package
			51.5	°C/W	16-pin UQFN/QFN/VQFN 4x4 mm package
			62.2	°C/W	20-pin PDIP package
			87.3	°C/W	20-pin SSOP package
			77.7	°C/W	20-pin SOIC package
			43.0	°C/W	20-pin UQFN 4x4 mm package
			40.0	°C/W	20-pin QFN/VQFN 4x4 mm package
TH02	θJC	Thermal Resistance Junction to	32.75	°C/W	14-pin PDIP package
		Case	31.0	°C/W	14-pin SOIC package
			24.4	°C/W	14-pin TSSOP package
			5.4	°C/W	16-pin UQFN/QFN/VQFN 4x4 mm package
			27.5	°C/W	20-pin PDIP package
			31.1	°C/W	20-pin SSOP package
			23.1	°C/W	20-pin SOIC package
			5.3	°C/W	20-pin UQFN 4x4 mm package
			21.7	°C/W	20-pin QFN/VQFN 4x4 mm package
TH03	Тјмах	Maximum Junction Temperature	150	°C	
TH04	PD	Power Dissipation	0.800	W	PD = PINTERNAL + PI/O
TH05	PINTERNAL	Internal Power Dissipation		W	PINTERNAL = IDD x VDD ⁽¹⁾
TH06	PI/O	I/O Power Dissipation	-	W	$PI/O = \Sigma (IOL * VOL) + \Sigma (IOH * (VDD - VOH))$
TH07	Pder	Derated Power	—	W	Pder = PDmax (Τj - Τa)/θja ⁽²⁾

TABLE 35-6: THERMAL CHARACTERISTICS


Note 1: IDD is current to run the chip alone without driving any load on the output pins.

2: TA = Ambient Temperature, TJ = Junction Temperature

35.4 AC Characteristics







		Conditions (unless otherwise	_				
	u Operating		e stated)	,		1	1
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions
ECL Os	cillator						
OS1	FECL	Clock Frequency	_	—	500	kHz	
OS2	TECL_DC	Clock Duty Cycle	40	—	60	%	
ECM Os	cillator						
OS3	FECM	Clock Frequency	_	—	4	MHz	
OS4	TECM_DC	Clock Duty Cycle	40		60	%	
ECH Os	cillator		•	•		•	
OS5	Fech	Clock Frequency	_	—	32	MHz	
OS6	TECH_DC	Clock Duty Cycle	40		60	%	
LP Osci	llator		L				
OS7	Flp	Clock Frequency	_	—	100	kHz	Note 4
XT Osci	llator						
OS8	Fxt	Clock Frequency		_	4	MHz	Note 4
HS Osci	illator	-					•
OS9	FHS	Clock Frequency	_	_	20	MHz	
System	Clock	•		•		•	•
OS20	Fosc	System Clock Frequency	—	—	32	MHz	Note 2, Note 3
OS21	FCY	Instruction Frequency	—	Fosc/4	_	MHz	
OS22	Тсү	Instruction Period	125	1/Fcy	_	ns	

TABLE 35-7: EXTERNAL CLOCK/OSCILLATOR TIMING REQUIREMENTS⁽¹⁾

These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

- **Note 1:** Instruction cycle period (TCY) equals four times the input oscillator time base period. All specified values are based on characterization data for that particular oscillator type under standard operating conditions with the device executing code. Exceeding these specified limits may result in an unstable oscillator operation and/or higher than expected current consumption. All devices are tested to operate at "min" values with an external clock applied to OSC1 pin. When an external clock input is used, the "max" cycle time limit is "DC" (no clock) for all devices.
 - 2: The system clock frequency (Fosc) is selected by the "main clock switch controls" as described in Section 7.3 "Clock Switching".
 - **3:** The system clock frequency (FOSC) must meet the voltage requirements defined in the **Section 35.2 "Standard Operating Conditions"**.
 - **4:** LP, XT and HS oscillator modes require an appropriate crystal or resonator to be connected to the device. For clocking the device with an external square wave, one of the EC mode selections must be used.

Standard	Operating	Conditions (unless otherwise stated)				
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions
OS50	FHFOSC	Precision Calibrated HFINTOSC Frequency		4 8 12 16 32		MHz	(2)
OS50	FHFOSC	Precision Calibrated HFINTOSC Frequency	3.92	4	4.08	MHz	25°C
OS51	FHFOSCLP	Low-Power Optimized HFINTOSC Frequency	0.93 1.86	1 2	1.07 2.14	MHz MHz	
OS52	FMFOSC	Internal Calibrated MFINTOSC Fre- quency	—	500	—	kHz	(3)
OS53	FLFOSC	Internal LFINTOSC Frequency	1 —	31		kHz	
OS54	THFOSCST	HFINTOSC Wake-up from Sleep Start-up Time	—	11 50	20 —	μs μs	VREGPM = 0 VREGPM = 1
OS56	TLFOSCST	LFINTOSC Wake-up from Sleep Start-up Time	—	0.2		ms	


* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: To ensure these oscillator frequency tolerances, VDD and VSS must be capacitively decoupled as close to the device as possible. $0.1 \ \mu$ F and $0.01 \ \mu$ F values in parallel are recommended.

2: See Figure 35-6: Precision Calibrated HFINTOSC/MFINTOSC Frequency Accuracy Over Device VDD and Temperature.

FIGURE 35-6: PRECISION CALIBRATED HFINTOSC FREQUENCY ACCURACY OVER DEVICE VDD AND TEMPERATURE




Standar	Standard Operating Conditions (unless otherwise stated)								
Param. No.	Sym.	Characteristic	Min.	Тур.†	Max.	Units	Conditions		
PLL01	FPLLIN	PLL Input Frequency Range	4		8	MHz	PIC16		
PLL02	FPLLOUT	PLL Output Frequency Range	16	_	32	MHz	(Note 1) PIC16		
PLL03	TPLLST	PLL Lock -Time from Start-up		200	_	μs			
PLL04	FPLLJIT	PLL Output Frequency Stability (Jitter)	-0.25		0.25	%			

TABLE 35-9: PLL CLOCK TIMING SPECIFICATIONS

Note 1: The output frequency of the PLL must meet the FOSC requirements listed in Parameter D002.







Standar	d Operating	Conditions (unless otherwise stat	ed)				
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions
IO1*	TCLKOUTH	CLKOUT rising edge delay (rising edge Fosc (Q1 cycle) to falling edge CLKOUT	_	—	70	ns	
IO2*	TCLKOUTL	CLKOUT falling edge delay (rising edge Fosc (Q3 cycle) to rising edge CLKOUT	_	—	72	ns	
IO3*	TIO_VALID	Port output valid time (rising edge Fosc (Q1 cycle) to port valid)	_	50	70	ns	
IO4*	TIO_SETUP	Port input setup time (Setup time before rising edge Fosc - Q2 cycle)	20	—	_	ns	
IO5*	TIO_HOLD	Port input hold time (Hold time after rising edge Fosc - Q2 cycle)	50	—	—	ns	
IO6*	TIOR_SLREN	Port I/O rise time, slew rate enabled	—	25	—	ns	VDD = 3.0V
IO7*	TIOR_SLRDIS	Port I/O rise time, slew rate disabled	—	5	—	ns	VDD = 3.0V
IO8*	TIOF_SLREN	Port I/O fall time, slew rate enabled	—	25	—	ns	VDD = 3.0V
109*	TIOF_SLRDIS	Port I/O fall time, slew rate disabled	—	5	—	ns	VDD = 3.0V
IO10*	TINT	INT pin high or low time to trigger an interrupt	25	—	—	ns	
IO11*	TIOC	Interrupt-on-Change minimum high or low time to trigger interrupt	25	—	—	ns	

TABLE 35-10: CLKOUT AND I/O TIMING SPECIFICATIONS

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated.










TABLE 35-11: RESET, WATCHDOG TIMER, OSCILLATOR, START-UP TIMER, POWER-UP TIMER, BROWN-OUT RESET AND LOW-POWER BROWN-OUT RESET SPECIFICATIONS

Standard Operating Conditions (unless otherwise stated)									
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions		
RST01	TMCLR	MCLR Pulse Width Low to ensure Reset	2	—		μS			
RST02	Tioz	I/O high-impedance from Reset detection	—	—	2	μS			
RST03	TWDT	Watchdog Timer Time-out Period	—	16		ms	16 ms Nominal Reset Time		
RST04*	TPWRT	Power-up Timer Period	—	65	—	ms			
RST05	Tost	Oscillator Start-up Timer Period ^(1,2)	—	1024		Tosc			
RST06	VBOR	Brown-out Reset Voltage ⁽⁴⁾	2.55 2.30 1.80	2.70 2.45 1.90	2.85 2.60 2.05	V V V	BORV = 0 BORV = 1 (PIC16F18326/18346) BORV = 1 (PIC16LF18326/18346)		
RST07	VBORHYS	Brown-out Reset Hysteresis	—	40		mV			
RST08	TBORDC	Brown-out Reset Response Time	—	3	_	μS			
RST09	VLPBOR	Low-Power Brown-out Reset Voltage	2.3	2.45	2.7	V	PIC16LF18326/18346		

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: By design, the Oscillator start-up timer (OST) counts the first 1024 cycles, independent of frequency.

2: To ensure these voltage tolerances, VDD and Vss must be capacitively decoupled as close to the device as possible. 0.1 µF values in parallel are recommended.

Standard Operating Conditions (unless otherwise stated) VDD = 3.0V, TA = 25°C									
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions		
AD01	NR	Resolution	—	_	10	bit			
AD02	EIL	Integral Error		±0.1	±1.0	LSb	ADCREF+ = 3.0V, ADCREF- = 0V		
AD03	Edl	Differential Error		±0.1	±1.0	LSb	ADCREF+ = 3.0V, ADCREF-= 0V		
AD04	EOFF	Offset Error		0.5	2	LSb	ADCREF+ = 3.0V, ADCREF- = 0V		
AD05	Egn	Gain Error		±0.2	±1.0	LSb	ADCREF+ = 3.0V, ADCREF- = 0V		
AD06	VADREF	ADC Reference Voltage (ADREF+) ⁽³⁾	1.8	_	Vdd	V			
AD07	VAIN	Full-Scale Range	ADREF-	_	ADREF+	V			
AD08	ZAIN	Recommended Impedance of Analog Voltage Source	—	10	—	kΩ			
AD09	Rvref	ADC Voltage Reference Ladder Impedance	—	50		kΩ	Note 3		

TABLE 35-12: ANALOG-TO-DIGITAL CONVERTER (ADC) CHARACTERISTICS^(1,2)

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: Total Absolute Error is the sum of the offset, gain and integral nonlinearity (INL) errors.

2: The ADC conversion result never decreases with an increase in the input and has no missing codes.

3: This is impedance seen by the VREF pads when the external reference pads are selected.


TABLE 35-13: ANALOG-TO DIGITAL CONVERTER (ADC) CONVERSION TIMING SPECIFICATIONS

Standar	Standard Operating Conditions (unless otherwise stated)									
Param. No.	Sym.	Characteristic	Min.	Typ.†	Max.	Units	Conditions			
AD20	TAD	ADC Clock Period	1	_	9	μs	This requirement is to set ADCCS correctly to produce this period/frequency			
AD21			1	2	6	μs	Using FRC as the ADC clock source; ADOSC = 1			
AD22	TCNV	Conversion Time	—	11	_	TAD	Set of GO/DONE bit to Clear of GO/DONE bit			
AD23	TACQ	Acquisition Time	—	2	_	μs				
AD24	Тнср		—	—	—	μs	Fosc based clock source			
		Disconnect Time	_	—	_	μs	FRC based clock source			

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

FIGURE 35-10: ADC CONVERSION TIMING (ADC CLOCK Fosc-BASED)






TABLE 35-14: COMPARATOR SPECIFICATIONS

VDD = 3.0	V, TA = 25°C	and AC Characteristics Graphs		<mark>arts</mark> " fo	r operati	ng chara	acterization.		
Param No.Sym.CharacteristicsMin.Typ.Max.UnitsComments									
CM01	VIOFF	Input Offset Voltage	—		±50	mV	VICM = VDD/2		
CM02	VICM	Input Common Mode Range	GND	_	Vdd	V			
CM03	CMRR	Common Mode Input Rejection Ratio	_	50	_	dB			
CM04	CHYST	Comparator Hysteresis	15	25	35	mV			
CM05	TRESP ⁽¹⁾	Response Time, Rising Edge		300	600	ns			
		Response Time, Falling Edge		220	500	ns			
CM06*	Тмсv2vo ⁽²⁾	Mode Change to Valid Output		_	10	μs			

* These parameters are characterized but not tested.

Note 1: Response time measured with one comparator input at VDD/2, while the other input transitions from Vss to VDD.

2: A mode change includes changing any of the control register values, including module enable.

TABLE 35-15: DIGITAL-TO-ANALOG CONVERTER (DAC) SPECIFICATIONS

Standard Operating Conditions (unless otherwise stated) VDD = 3.0V, TA = 25°C										
Param No.	Sym.	Characteristics	Min.	Typ.†	Max.	Units	Comments			
D5B01	VLSB	Step Size	_	(Vda- cref+/-Vda- cref-)/32	_	V				
D5B02	VACC	Absolute Accuracy	_	—	±0.5	LSb				
D5B03*	RUNIT	Unit Resistor Value	_	5000	_	Ω				
D5B04*	Тѕт	Settling Time ⁽¹⁾	—	—	10	μs				

* These parameters are characterized but not tested.

† Data in "Typ" column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: Settling time measured while DACR<4:0> transitions from '00000' to '01111'.

TABLE 35-16: FIXED VOLTAGE REFERENCE (FVR) SPECIFICATIONS

Standard Operating Conditions (unless otherwise stated)									
Param. No.	Symbol	Characteristic	Min.	Тур.	Max.	Units	Conditions		
FVR01	VFVR1	1x Gain (1.024V)	-4	_	+4	%	VDD ≥ 2.5 V, -40°C to 85°C		
FVR02	VFVR2	2x Gain (2.048V)	-4	_	+4	%	VDD ≥ 2.5 V, -40°C to 85°C		
FVR03	VFVR4	4x Gain (4.096V)	-5	_	+5	%	VDD \ge 4.75V, -40°C to 85°C		
FVR04	TFVRST	FVR Start-up Time	_	25	_	μs			
Note 1: Available only on PIC16F153xx.									

FIGURE 35-12: TIMER0 AND TIMER1 EXTERNAL CLOCK TIMINGS




TABLE 35-17: TIMER0 AND TIMER1 EXTERNAL CLOCK REQUIREMENTS

		g Conditions (un re -40°C ≤ Ta ≤ +12		se stated)					
Param. No.	Sym.	с	haracteristic		Min.	Typ.†	Max.	Units	Conditions
40*	Тт0Н	T0CKI High Pulse	Width	No Prescaler	0.5 Tcy + 20	_	_	ns	
				With Prescaler	10		_	ns	
41*	TT0L	T0CKI Low Pulse	Width	No Prescaler	0.5 Tcy + 20		_	ns	
				With Prescaler	10		_	ns	
42*	TT0P	T0CKI Period				—	—	ns	N = prescale value (2, 4,, 256)
45*	T⊤1H	T1CKI High Time Synchrono		s, No Prescaler	0.5 Tcy + 20			ns	
			Synchronous, with Prescaler		15			ns	
			Asynchrono	us	30			ns	
46*	T⊤1L	T1CKI Low Time	Synchronou	s, No Prescaler	0.5 Tcy + 20			ns	
			Synchronou	s, with Prescaler	15			ns	
			Asynchrono	us	30			ns	
47*	T⊤1P	T1CKI Input Period	Synchronou	s	Greater of: 30 or (Tcy + 40)* N	_	_	ns	
			Asynchrono	us	60			ns	
48	F⊤1		tor Input Frequency Range I by setting bit T1OSCEN)		32.4	32.768	33.1	kHz	
49*	TCKEZTMR1	Delay from Extern Increment	al Clock Edg	e to Timer	2 Tosc	—	7 Tosc	—	Timers in Sync mode

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

FIGURE 35-13: CAPTURE/COMPARE/PWM TIMINGS (CCP)




TABLE 35-18: CAPTURE/COMPARE/PWM CHARACTERISTICS (CCP)

	Standard Operating Conditions (unless otherwise stated) Operating temperature -40°C ≤ TA ≤ +125°C									
Param. No.	Sym.	Character	istic	Min.	Тур.†	Max.	Units	Conditions		
CC01*	TccL	CCPx Input Low Time	No Prescaler	0.5 Tcy + 20			ns			
			With Prescaler	20	—	—	ns			
CC02*	ТссН	CCPx Input High Time	No Prescaler	0.5 Tcy + 20	—		ns			
			With Prescaler	20	_		ns			
CC03*	TccP	CCPx Input Period		<u>(</u> 3 Tcy + 40)* N	_		ns	N = prescale value (1, 4 or 16)		

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.




TABLE 35-19: CONFIGURABLE LOGIC CELL (CLC) CHARACTERISTICS

Standard Operating Conditions (unless otherwise stated) Operating temperature -40°C ≤ TA ≤ +125°C									
Param. No.	Sym.	Characteristic Min. Typ.† Max. Units Condi							
CLC01*	TCLCIN	CLC input time (CKCxIN[n]) to CKC module Input select (LCx_in[n]) propagation time		7	105	ns	(Note 1)		
CLC02*	TCLC	CLC module input to output propagation delay		24 12		ns ns	VDD = 1.8V VDD > 3.6V		
CLC03*	TCLCOUT	CLC output time Rise Time		107			Rise Time (Note 1)		
		Fall Time	_	108			Fall Time (Note 1)		
CLC04* FCLCMAX CLC maximum switching frequency - 32 FOSC MHz									

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.

Note 1: See Table 35-10 for rise and fall times.

FIGURE 35-15: EUSART SYNCHRONOUS TRANSMISSION (HOST/CLIENT) TIMING




TABLE 35-20: EUSART SYNCHRONOUS TRANSMISSION CHARACTERISTICS

Standaro Operatin						
Param. No.	Symbol	Conditions				
US120	ТскH2dtV	SYNC XMIT (Host and Client)	—	80	ns	3.0V – 5.5V
		Clock high to data-out valid	_	100	ns	1.8V – 5.5V
US121	TCKRF	Clock out rise time and fall time	_	45	ns	3.0V – 5.5V
		(Host mode)		50	ns	1.8V – 5.5V
US122	TDTRF	Data-out rise time and fall time	—	45	ns	3.0V – 5.5V
				50	ns	1.8V – 5.5V

FIGURE 35-16: EUSART SYNCHRONOUS RECEIVE (HOST/CLIENT) TIMING




TABLE 35-21: EUSART SYNCHRONOUS RECEIVE CHARACTERISTICS

Standard Operating Conditions (unless otherwise stated) Operating temperature -40°C \leq TA \leq +125°C							
Param. No. Symbol Characteristic Min. Max. Units Conditions							
US125	TDTV2CKL	SYNC RCV (Host and Client) Data-hold before CK ↓ (DT hold time)	10	_	ns		
US126	TCKL2DTL	Data-hold after CK \downarrow (DT hold time)	15	—	ns		







FIGURE 35-18: SPI HOST MODE TIMING (CKE = 1, SMP = 1)









Standard Operating Conditions (unless otherwise stated)									
Param. No.	Symbol	Characteristic	Min.	Typ.†	Max.	Units	Conditions		
SP70*	TssL2scH, TssL2scL	$\overline{SS}\downarrow$ to SCK \downarrow or SCK \uparrow	2.25*Tcy	—	_	ns			
SP71*	TscH	SCK input high time (Client mode)	Tcy + 20	—	—	ns			
SP72*	TscL	SCK input low time (Client mode)	Tcy + 20	_	_	ns			
SP73*	TDIV2scH, TDIV2scL	Setup time of SDI data input to SCK edge	100	—	_	ns			
SP74*	TscH2dlL, TscL2dlL	Hold time of SDI data input to SCK edge	100	—	—	ns			
SP75*	TDOR	SDO data output rise time	_	10	25	ns	3.0V - 5.5V		
				25	50	ns	1.8V – 5.5V		
SP76*	TDOF	SDO data output fall time	_	10	25	ns			
SP77*	TssH2doZ	SS↑ to SDO output high-impedance	10	—	50	ns			
SP78*	TscR	SCK output rise time		10	25	ns	3.0V – 5.5V		
		(Host mode)	_	25	50	ns	1.8V – 5.5V		
SP79*	TscF	SCK output fall time (Host mode)	_	10	25	ns			
SP80*	TscH2doV,	SDO data output valid after SCK	_	—	50	ns	3.0V - 5.5V		
	TscL2DoV	edge	_	—	145	ns	1.8V – 5.5V		
SP81*	TDOV2scH, TDOV2scL	SDO data output setup to SCK edge	1 Tcy	—	_	ns			
SP82*	TssL2doV	SDO data output valid after $\overline{SS}\downarrow$ edge	_		50	ns			
SP83*	TscH2ssH, TscL2ssH	SS ↑ after SCK edge	1.5 Tcy + 40	—	_	ns			

* These parameters are characterized but not tested.

† Data in "Typ." column are at 3.0V, 25°C unless otherwise stated. These parameters are for design guidance only and are not tested.





TABLE 35-23: I²C BUS START/STOP BITS CHARACTERISTICS

Standard Operating Conditions (unless otherwise stated)									
Param. No.	Symbol	Charac	teristic	Min.	Тур.	Max.	Units	Conditions	
SP90*	TSU:STA	Start condition	100 kHz mode	4700	—	—	ns	Only relevant for Repeated	
		Setup time	400 kHz mode	600	_	—		Start condition	
SP91*	THD:STA	Start condition	100 kHz mode	4000	-	—	ns	After this period, the first	
		Hold time	400 kHz mode	600	-	—		clock pulse is generated	
SP92*	Tsu:sto	Stop condition	100 kHz mode	4700	—	—	ns		
		Setup time	400 kHz mode	600	_	—			
SP93	THD:STO	Stop condition	100 kHz mode	4000	—	—	ns		
		Hold time	400 kHz mode	600					

* These parameters are characterized but not tested.

FIGURE 35-22: I²C BUS DATA TIMING



Param. No.	Symbol	Charact	eristic	Min.	Max.	Units	Conditions
SP100*	Тнідн	Clock high time	100 kHz mode	4.0		μs	Device must operate at a minimum of 1.5 MHz
			400 kHz mode	0.6	-	μS	Device must operate at a minimum of 10 MHz
			SSP module	1.5 TCY	_		
SP101*	TLOW	Clock low time	100 kHz mode	4.7	-	μS	Device must operate at a minimum of 1.5 MHz
			400 kHz mode	1.3		μS	Device must operate at a minimum of 10 MHz
			SSP module	1.5 TCY	_		
SP102*	TR	SDA and SCL rise	100 kHz mode	—	1000	ns	
		time	400 kHz mode	20 + 0.1 Св	300	ns	CB is specified to be from 10-400 pF
SP103*	TF	SDA and SCL fall	100 kHz mode	_	250	ns	
		time	400 kHz mode	20 + 0.1 Св	250	ns	CB is specified to be from 10-400 pF
SP106*	THD:DAT	Data input hold	100 kHz mode	0		ns	
		time	400 kHz mode	0	0.9	μs	
SP107*	TSU:DAT	Data input setup	100 kHz mode	250	_	ns	(Note 2)
		time	400 kHz mode	100	_	ns	
SP109*	ΤΑΑ	Output valid from	100 kHz mode	—	3500	ns	(Note 1)
		clock	400 kHz mode	—		ns	
SP110*	TBUF	Bus free time	100 kHz mode	4.7	_	μS	Time the bus must be free
			400 kHz mode	1.3	—	μS	before a new transmissior can start
SP111	Св	Bus capacitive load	ing	_	400	pF	

TABLE 35-24: I²C BUS DATA CHARACTERISTICS

Note 1: As a transmitter, the device must provide this internal minimum delay time to bridge the undefined region (min. 300 ns) of the falling edge of SCL to avoid unintended generation of Start or Stop conditions.

2: A Fast mode (400 kHz) I²C bus device can be used in a Standard mode (100 kHz) I²C bus system, but the requirement TSU:DAT \ge 250 ns must then be met. This will automatically be the case if the device does not stretch the low period of the SCL signal. If such a device does stretch the low period of the SCL signal, it must output the next data bit to the SDA line TR max. + TSU:DAT = 1000 + 250 = 1250 ns (according to the Standard mode I²C bus specification), before the SCL line is released.

36.0 DC AND AC CHARACTERISTICS GRAPHS AND CHARTS

The graphs and tables provided in this section are for **design guidance** and are **not tested**.

In some graphs or tables, the data presented are **outside specified operating range** (i.e., outside specified VDD range). This is for **information only** and devices are ensured to operate properly only within the specified range.

Unless otherwise noted, all graphs apply to both the L and LF devices.

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore, outside the warranted range.

"Typical" represents the mean of the distribution at 25°C. "Maximum", "Max.", "Minimum" or "Min." represents (mean + 3σ) or (mean - 3σ) respectively, where σ is a standard deviation, over each temperature range.




FIGURE 36-1: WDT Time-Out Period (PIC16F18326/46 only)




FIGURE 36-2: WDT Time-Out Period (PIC16LF18326/46 only)




FIGURE 36-3: IPD Base, Low-Power Sleep Mode (PIC16LF18326/46 only)




FIGURE 36-4: IPD, Watchdog Timer (WDT) (PIC16LF18326/46 only)






FIGURE 36-5: IPD, Watchdog Timer (WDT) (PIC16F18326/46 only)



Reference (FVR) (PIC16LF18326/46 only)

Note: Unless otherwise noted, VIN = 5V, FOSC = 300 kHz, CIN = 0.1 µF, TA = 25°C.



Reference (FVR) (PIC16F18326/46 only)




FIGURE 36-8: IPD, Brown-Out Reset (BOR), BORV = 1 (PIC16LF18326/46 only)




FIGURE 36-9: IPD, Brown-Out Reset (BOR), BORV = 1 (PIC16F18326/46 only)

1.2

1.0

0.6

0.4

0.2

0.0

2.0

2.5

(10.8 O.8

đ





FIGURE 36-10: IPD. Low-Power Brown-Out *Reset* (*LPBOR* = 1)(*PIC16LF18326*/46 only)



Max Typical 2.0 2.2 2.4 2.6 2.8 3.0 3.2 3.4 3.6 3.8 VDD (V) FIGURE 36-12: IPD, Comparator

(PIC16LF18326/46 only)




FIGURE 36-13: IPD, Comparator (PIC16F18326/46 only)




FIGURE 36-14: IPD Base, VREGPM = 0, (PIC16F18326/46 only)




FIGURE 36-15: IPD Base, VREGPM = 1, (PIC16F18326/46 only)




FIGURE 36-16: IDD, XT Oscillator 4 MHz (PIC16LF18326/46 only)




FIGURE 36-17: IDD, XT Oscillator 4 MHz (PIC16F18326/46 only)




FIGURE 36-18: IDD, HS Oscillator 32 MHz (PIC16LF18326/46 only)




FIGURE 36-19: IDD, HS Oscillator 32 MHz (PIC16F18326/46 only)




FIGURE 36-20: IDD, HFINTOSC Mode, Fosc = 32 MHz (PIC16LF18326/46 only)




FIGURE 36-21: IDD, HFINTOSC Mode, Fosc = 32 MHz (PIC16F18326/46 only)




FIGURE 36-22: IDD, HFINTOSC Mode, Fosc = 16 MHz (PIC16LF18326/46 only)




FIGURE 36-23: IDD, HFINTOSC Mode Fosc = 16 MHz (PIC16F18326/46 only)




FIGURE 36-24: IDD, HFINTOSC Idle Mode, Fosc = 16 MHz (PIC16LF18326/46 only)




FIGURE 36-25: IDD, HFINTOSC Idle Mode, Fosc = 16 MHz (PIC16F18326/46 only)




FIGURE 36-26: IDD, HFINTOSC Doze Mode, Fosc = 16 MHz (PIC16LF18326/46 only)




FIGURE 36-27: IDD, HFINTOSC Doze Mode, Fosc = 16 MHz (PIC16F18326/46 only)




FIGURE 36-29: LFINTOSC Frequency (PIC16F18326/46 only)




FIGURE 36-28: LFINTOSC Frequency (PIC16LF18326/46 only)




FIGURE 36-30: HFINTOSC Typical Frequency Error (PIC16LF18326/46 only)




FIGURE 36-31: HFINTOSC Typical Frequency Error (PIC16F18326/46 only)




FIGURE 36-32: HFINTOSC Frequency Error VDD = 3V (All devices)




FIGURE 36-33: Weak Pull-Up Current (PIC16F18326/46 only)





FIGURE 36-34: Weak Pull-Up Current (PIC16LF18326/46 only)



Overtemperature, VDD = 5.5V (PIC16LF18326/46 only)




FIGURE 36-36: VoL vs. IoL Overtemperature, VDD = 5.5V (PIC16F18326/46 only)




FIGURE 36-37: VOH vs. IOH Overtemperature, VDD = 3.0V (All devices)




FIGURE 36-38: VOL vs. IOL Overtemperature, VDD = 3.0V (All devices)




FIGURE 36-39: VOH vs. IOH Overtemperature, VDD = 1.8V (PIC16LF18326/46 only)




FIGURE 36-41: Brown-Out Reset Voltage, Trip Point (BORV = 0) (All devices)




FIGURE 36-40: VOL vs. IOL Overtemperature, VDD = 1.8V (PIC16LF18326/46 only)




FIGURE 36-42: Brown-Out Reset Hysteresis, Trip Point (BORV = 0) (All devices)




FIGURE 36-43: Brown-Out Reset Voltage, *Trip Point (BORV = 1) (PIC16LF18326/46 only)*





FIGURE 36-45: Brown-Out Reset Voltage, *Trip Point (BORV = 1) (PIC16F18326/46 only)*






FIGURE 36-44: Brown-Out Reset Hysteresis, Trip Point (BORV = 1) (PIC16LF18326/46 only)





FIGURE 36-46: Brown-Out Reset Hysteresis, Trip Point (BORV = 1) (PIC16F18326/46 only)



(All devices)




FIGURE 36-49: BOR Response Time (PIC16LF18326/46 only)




FIGURE 36-50: BOR Response Time (PIC16F18326/46 only)




FIGURE 36-51: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, VREF = 3.0V, TAD = 1μ s, 25C (All devices)




FIGURE 36-53: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, VREF = 3.0V, TAD = $8 \mu s$, 25C (All devices)






FIGURE 36-52: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, VREF = 3.0V, TAD = 4 μ s, 25C (All devices)








FIGURE 36-55: ADC 10-Bit Mode, Single-Ended INL, VDD = 3.0V, VREF = 3.0V, TAD = $4 \mu s$, 25C (All devices)




FIGURE 36-56: ADC 10-Bit Mode, Single-Ended INL, VDD = 3.0V, VREF = 3.0V, TAD = $8 \mu s$, 25C (All devices)




FIGURE 36-57: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, VREF = 3.0V (All devices)




FIGURE 36-59: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, TAD = $1 \mu s$ (All devices)




FIGURE 36-58: ADC 10-Bit Mode, Single-Ended INL, VDD = 3.0V, VREF = 3.0V (All devices)




FIGURE 36-60: ADC 10-Bit Mode, Single-Ended INL, VDD = 3.0V, TAD = 1μ s (All devices)




FIGURE 36-61: ADC 10-Bit Mode, Single-Ended Gain Error, VDD = 3.0V, TAD = 1 μs (All devices)




FIGURE 36-63: ADC 10-Bit Mode, Single-Ended DNL, VDD = 3.0V, TAD = $4 \mu s$ (All devices)




FIGURE 36-65: ADC 10-Bit Mode, Single-Ended Gain Error, VDD = 3.0V, TAD = $4 \mu s$ (All devices)




FIGURE 36-62: ADC 10-Bit Mode, Single-Ended Offset Error, VDD = 3.0V, TAD = 1 μ s (All devices)




FIGURE 36-64: ADC 10-Bit Mode, Single-Ended INL, VDD = 3.0V, TAD = 4μ s (All devices)




FIGURE 36-66: ADC 10-Bit Mode, Single-Ended Offset Error, VDD = 3.0V, TAD = 4 μ s (All devices)




FIGURE 36-67: ADC 10-Bit Mode, Single-Ended Gain Error, VDD = 3.0V, VREF = 3.0V, -40°C to 85°C(All devices)




FIGURE 36-68: ADC 10-Bit Mode, Single-Ended Offset Error, VDD = 3.0V, VREF = 3.0V, -40°C to 85°C(All devices)




FIGURE 36-69: ADC RC Oscillator Period (PIC16LF18326/46 only)






FIGURE 36-70: ADC RC Oscillator Period (PIC16F18326/46 only)





= 3.0V, VREF = External 3V (All devices)




FIGURE 36-73: Typical DAC INL Error, VDD = 5.0V, VREF = External 5V (PIC16F18326/46 only)




FIGURE 36-75: DAC INL Error, VDD = 3.0V (PIC16LF18326/46 only)






FIGURE 36-74: Typical DAC INL Error, VDD = 5.0V, VREF = External 5V (PIC16F18326/46 only)








FIGURE 36-77: Absolute Value of DAC INL Error, VDD = 3.0V, VREF = VDD (All devices)




FIGURE 36-78: Absolute Value of DAC DNL Error, VDD = 5.0V, VDD = 5.0V, VREF = VDD (PIC16F18326/46 only)




FIGURE 36-79: Absolute Value of DAC INL Error, VDD = 5.0V, VREF = VDD (PIC16F18326/46 only)




FIGURE 36-81: Comparator Offset, Normal Power Mode (CxSP = 1), VDD = 3.0V, Typical Measured Values at 25°C




FIGURE 36-83: Comparator Hysteresis, Normal Power Mode (CxSP = 1), VDD = 5.5V, Typical Measured Values




FIGURE 36-80: Comparator Hysteresis, Normal Power Mode (CxSP = 1), VDD = 3.0V, Typical Measured Values




FIGURE 36-82: Comparator Offset, Normal Power Mode (CxSP = 1), VDD = 3.0V, Typical Measured Values from -40°C to 125°C




FIGURE 36-84: Comparator Offset, Normal Power Mode (CxSP = 1), VDD = 5.0V, Typical Measured Values at 25°C




FIGURE 36-85: Comparator Offset, Normal Power Mode (CxSP = 1), VDD = 5.5V, Typical Measured Values from -40°C to 125°C




FIGURE 36-87: Comparator Response Time Overvoltage, Normal Power Mode (CxSP = 1), Typical Measured Values




FIGURE 36-89: Comparator Output Filter Delay Time Overtemperature, Normal Power Mode (CxSP), Typical Measured Values




FIGURE 36-86: Comparator Response Time Overvoltage, Normal Power Mode (CxSP = 1), Typical Measured Values




FIGURE 36-88: Comparator Output Filter Delay Time Overtemperature, Normal Power Mode (CxSP), Typical Measured Values




FIGURE 36-90: Comparator Response Time Falling Edge (PIC16LF18326/46 only)




FIGURE 36-91: Comparator Response Time Falling Edge (PIC16F18326/46 only)




FIGURE 36-92: Comparator Response Time Rising Edge (PIC16LF18326/46 only)





FIGURE 36-93: Comparator Response Time Rising Edge (PIC16F18326/46 only)










FIGURE 36-94: Band Gap Ready Time (PIC16LF18326/46 only)














FIGURE 36-100: FVR Voltage Error 4x (PIC16F18326/46 only)









FIGURE 36-103: Input Level TTL



Control Enabled




FIGURE 36-105: Fall Time, Slew Rate Control Enabled







FIGURE 36-106: Rise Time, Slew Rate Control Disabled



Control Disabled








FIGURE 36-110: POR Rearm Voltage, Normal Power Mode






FIGURE 36-111: PWRT Period (PIC16F18326/46 only)








FIGURE 36-113: Wake From Sleep, VREGPM = 0, HFINTOSC = 4 MHz (PIC16F18326/46 only)




FIGURE 36-114: Wake From Sleep, VREGPM = 1, HFINTOSC = 4 MHz (PIC16F18326/46 only)




FIGURE 36-115: Wake From Sleep, VREGPM = 1, HFINTOSC = 16 MHz (PIC16F18326/46 only)




FIGURE 36-116: Wake From Sleep, VREGPM = 1, HFINTOSC = 16 MHz (PIC16F18326/46 only)




FIGURE 36-117: Wake From Sleep, VREGPM = 1 (PIC16F18326/46 only)




FIGURE 36-118: Wake From Sleep (PIC16LF18326/46 only)

37.0 DEVELOPMENT SUPPORT

Move a design from concept to production in record time with Microchip's award-winning development tools. Microchip tools work together to provide state of the art debugging for any project with easy-to-use Graphical User Interfaces (GUIs) in our free MPLAB[®] X and Atmel Studio Integrated Development Environments (IDEs), and our code generation tools. Providing the ultimate ease-of-use experience, Microchip's line of programmers, debuggers and emulators work seamlessly with our software tools. Microchip development boards help evaluate the best silicon device for an application, while our line of third party tools round out our comprehensive development tool solutions.

Microchip's MPLAB X and Atmel Studio ecosystems provide a variety of embedded design tools to consider, which support multiple devices, such as $PIC^{@}$ MCUs, $AVR^{@}$ MCUs, SAM MCUs and $dsPIC^{@}$ DSCs. MPLAB X tools are compatible with Windows[®], Linux[®] and Mac[®] operating systems while Atmel Studio tools are compatible with Windows.

Go to the following website for more information and details:


https://www.microchip.com/development-tools/

Example


38.0 PACKAGING INFORMATION


38.1 Marking Information

14-Lead PDIP (300 mil)




Marking Information (Continued)






Legend	: XXX Y YY WW NNN (63) *	Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC [®] designator for Matte Tin (Sn) This is Pb-free. The Pb-free JEDEC designator () (e3) can be found on the outer packaging for this .
Note:	be carrie	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available s for customer-specific information.



Legend:	XXX Y YY WW NNN @3 *	Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC [®] designator for Matte Tin (Sn) This is Pb-free. The Pb-free JEDEC designator () (e3) can be found on the outer packaging for this .
	be carrie	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available s for customer-specific information.




38.2 Details

The following sections give the technical details of the packages.

14-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	INCHES						
	Dimension Limits	MIN	NOM	MAX				
Number of Pins	N		14					
Pitch	e		.100 BSC					
Top to Seating Plane	A	-	-	.210				
Molded Package Thickness	A2	.115	.130	.195				
Base to Seating Plane	A1	.015	-	-				
Shoulder to Shoulder Width	E	.290	.310	.325				
Molded Package Width	E1	.240	.250	.280				
Overall Length	D	.735	.750	.775				
Tip to Seating Plane	L	.115	.130	.150				
Lead Thickness	С	.008	.010	.015				
Upper Lead Width	b1	.045	.060	.070				
Lower Lead Width	b	.014	.018	.022				
Overall Row Spacing §	eB	_	-	.430				

Notes:

1. Pin 1 visual index feature may vary, but must be located with the hatched area.

2. § Significant Characteristic.

3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.


4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


Microchip Technology Drawing C04-005B


14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



TOP VIEW









Microchip Technology Drawing No. C04-065C Sheet 1 of 2

14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging





VIEW C

Units		MILLIMETERS			
Dimension Lin	nits	MIN	NOM	MAX	
Number of Pins	N	14			
Pitch	е		1.27 BSC		
Overall Height	Α	-	-	1.75	
Molded Package Thickness	A2	1.25	-	-	
Standoff §	A1	0.10	-	0.25	
Overall Width	E	6.00 BSC			
Molded Package Width	E1	3.90 BSC			
Overall Length	D	8.65 BSC			
Chamfer (Optional)	h	0.25	-	0.50	
Foot Length	L	0.40	-	1.27	
Footprint	L1		1.04 REF		
Lead Angle	Θ	0°	-	-	
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.10	-	0.25	
Lead Width	b	0.31	-	0.51	
Mold Draft Angle Top	α	5°	-	15°	
Mold Draft Angle Bottom	β	5°	-	15°	


Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic
- Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- Dimensioning and tolerancing per ASME Y14.5M
 BSC: Basic Dimension. Theoretically exact value shown without tolerances.
 BEE: Reference Dimension, usually without tolerance for information purposes only
 - REF: Reference Dimension, usually without tolerance, for information purposes only.
- 5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-065C Sheet 2 of 2

14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units		MILLIMETERS		
Dimensior	Dimension Limits		NOM	MAX	
Contact Pitch	E	1.27 BSC			
Contact Pad Spacing	С		5.40		
Contact Pad Width	X			0.60	
Contact Pad Length	Y			1.50	
Distance Between Pads	Gx	0.67			
Distance Between Pads	G	3.90			

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2065A

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-087C Sheet 1 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Number of Pins	N		14	•
Pitch	е		0.65 BSC	
Overall Height	A	-	-	1.20
Molded Package Thickness	A2	0.80	1.00	1.05
Standoff	A1	0.05	-	0.15
Overall Width	E	6.40 BSC		
Molded Package Width	E1	4.30	4.40	4.50
Molded Package Length	D	4.90	5.00	5.10
Foot Length	L	0.45	0.60	0.75
Footprint	(L1)	1.00 REF		
Foot Angle	φ	0°	-	8°
Lead Thickness	С	0.09	-	0.20
Lead Width	b	0.19	-	0.30

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or

protrusions shall not exceed 0.15mm per side.

3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing No. C04-087C Sheet 2 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		Ν	MILLIMETERS		
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	E	0.65 BSC			
Contact Pad Spacing	C1		5.90		
Contact Pad Width (X14)	X1			0.45	
Contact Pad Length (X14)	Y1			1.45	
Distance Between Pads	G	0.20			


Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2087A


16-Lead Ultra Thin Plastic Quad Flat, No Lead Package (JQ) - 4x4x0.5 mm Body [UQFN]



Microchip Technology Drawing C04-257A Sheet 1 of 2

16-Lead Ultra Thin Plastic Quad Flat, No Lead Package (JQ) - 4x4x0.5 mm Body [UQFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Number of Pins	N		16	
Pitch	е		0.65 BSC	
Overall Height	Α	0.45	0.50	0.55
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.127 REF		
Overall Width	E	4.00 BSC		
Exposed Pad Width	E2	2.50	2.60	2.70
Overall Length	D		4.00 BSC	
Exposed Pad Length	D2	2.50	2.60	2.70
Terminal Width	b	0.25	0.30	0.35
Terminal Length	L	0.30	0.40	0.50
Terminal-to-Exposed-Pad	К	0.20	-	-

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-257A Sheet 2 of 2

16-Lead Ultra Thin Plastic Quad Flat, No Lead Package (JQ) - 4x4x0.5 mm Body [UQFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		MILLIMETERS			
			······································	-	
Dimensio	n Limits	MIN	NOM	MAX	
Contact Pitch	Е		0.65 BSC		
Optional Center Pad Width	X2			2.70	
Optional Center Pad Length	Y2			2.70	
Contact Pad Spacing	C1		4.00		
Contact Pad Spacing	C2		4.00		
Contact Pad Width (X16)	X1			0.35	
Contact Pad Length (X16)	Y1			0.80	

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2257A

16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-127D Sheet 1 of 2

16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension Limits		MIN	NOM	MAX
Number of Pins	Ν		16	
Pitch	е		0.65 BSC	
Overall Height	Α	0.80	0.90	1.00
Standoff	A1	0.00	0.02	0.05
Contact Thickness	A3	0.20 REF		
Overall Width	E	4.00 BSC		
Exposed Pad Width	E2	2.50	2.65	2.80
Overall Length	D		4.00 BSC	
Exposed Pad Length	D2	2.50	2.65	2.80
Contact Width	b	0.25	0.30	0.35
Contact Length	L	0.30	0.40	0.50
Contact-to-Exposed Pad	K	0.20	-	-

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.


- 2. Package is saw singulated
- 3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-127D Sheet 2 of 2

16-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4x0.9mm Body [QFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	E		•		
Optional Center Pad Width	W2			2.50	
Optional Center Pad Length	T2			2.50	
Contact Pad Spacing	C1		4.00		
Contact Pad Spacing	C2		4.00		
Contact Pad Width (X28)	X1			0.35	
Contact Pad Length (X28)	Y1			0.80	
Distance Between Pads	G	0.30			

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2127A

16-Lead Plastic Quad Flat, No Lead Package (7N) - 4x4x1.0 mm Body [VQFN] Wettable Flanks (Stepped), 0.40 mm Terminal Length


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-403C Sheet 1 of 2

16-Lead Plastic Quad Flat, No Lead Package (7N) - 4x4x1.0 mm Body [VQFN] Wettable Flanks (Stepped), 0.40 mm Terminal Length

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	Ν	MILLIMETERS		
Dimension	Limits	MIN	NOM	MAX	
Number of Terminals	N		16		
Pitch	е		0.65 BSC		
Overall Height	A	0.80	0.90	1.00	
Standoff	A1	0.00	0.02	0.05	
Terminal Thickness	A3		0.20 REF		
Step Height	A4	0.05	0.12	0.19	
Overall Width	E		4.00 BSC		
Exposed Pad Width	E2	2.50	2.60	2.70	
Overall Length	D		4.00 BSC		
Exposed Pad Length	D2	2.50	2.60	2.70	
Terminal Width	b	0.25	0.30	0.35	
Terminal Length	L	0.30	0.40	0.50	
Step Length	L1	0.035	0.060	0.085	
Terminal-to-Exposed Pad	K	0.30	-	-	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated

3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-403C Sheet 2 of 2

16-Lead Plastic Quad Flat, No Lead Package (7N) - 4x4x1.0 mm Body [VQFN] Wettable Flanks (Stepped), 0.40 mm Terminal Length

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		0.65 BSC	
Optional Center Pad Width	X2			2.70
Optional Center Pad Length	Y2			2.70
Contact Pad Spacing	C1		4.00	
Contact Pad Spacing	C2		4.00	
Contact Pad Width (X16)	X1			0.30
Contact Pad Length (X16)	Y1			0.80
Contact Pad to Center Pad (X16)	G1	0.20		
Contact Pad to Contact Pad (X12)	G2	0.35		
Thermal Via Diameter	V		0.30	
Thermal Via Pitch	EV		1.00	


Notes:

- 1. Dimensioning and tolerancing per ASME Y14.5M
- BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- 2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2403B

20-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		INCHES		
Dimensio	n Limits	MIN	NOM	MAX	
Number of Pins	Ν		20		
Pitch	е		.100 BSC		
Top to Seating Plane	Α	-	-	.210	
Molded Package Thickness	A2	.115	.130	.195	
Base to Seating Plane	A1	.015	_	-	
Shoulder to Shoulder Width	Е	.300	.310	.325	
Molded Package Width	E1	.240	.250	.280	
Overall Length	D	.980	1.030	1.060	
Tip to Seating Plane	L	.115	.130	.150	
Lead Thickness	С	.008	.010	.015	
Upper Lead Width	b1	.045	.060	.070	
Lower Lead Width	b	.014	.018	.022	
Overall Row Spacing §	eB	_	-	.430	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. § Significant Characteristic.

3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.


4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


Microchip Technology Drawing C04-019B


20-Lead Plastic Small Outline (SO) - Wide, 7.50 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging











VIEW A-A

Microchip Technology Drawing C04-094C Sheet 1 of 2

20-Lead Plastic Small Outline (SO) - Wide, 7.50 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging





Units		MILLIMETERS			
Dimension Lim	nits	MIN	NOM	MAX	
Number of Pins	N		20		
Pitch	е		1.27 BSC		
Overall Height	A	-	-	2.65	
Molded Package Thickness	A2	2.05	-	-	
Standoff §	A1	0.10	-	0.30	
Overall Width	E	10.30 BSC			
Molded Package Width	E1	7.50 BSC			
Overall Length	D	12.80 BSC			
Chamfer (Optional)	h	0.25	-	0.75	
Foot Length	L	0.40	-	1.27	
Footprint	L1		1.40 REF		
Lead Angle	Θ	0°	-	-	
Foot Angle	φ	0° - 8		8°	
Lead Thickness	С	0.20 - 0.33			
Lead Width	b	0.31	-	0.51	
Mold Draft Angle Top	α	5°	-	15°	
Mold Draft Angle Bottom	β	5°	-	15°	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.


2. § Significant Characteristic

- 3. Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- Dimensioning and tolerancing per ASME Y14.5M BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.
- 5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-094C Sheet 2 of 2

20-Lead Plastic Small Outline (SO) - Wide, 7.50 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units		MILLIMETERS			
Dimension	Dimension Limits		NOM	MAX		
Contact Pitch	E 1.27 BSC					
Contact Pad Spacing	С		9.40			
Contact Pad Width (X20)	Х			0.60		
Contact Pad Length (X20)	Y			1.95		
Distance Between Pads	Gx	0.67				
Distance Between Pads	G	7.45				

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2094A

20-Lead Plastic Shrink Small Outline (SS) – 5.30 mm Body [SSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS			
	Dimension Limits	MIN	NOM	MAX		
Number of Pins	N	20				
Pitch	е		0.65 BSC			
Overall Height	А	-	-	2.00		
Molded Package Thickness	A2	1.65	1.75	1.85		
Standoff	A1	0.05	-	_		
Overall Width	E	7.40	7.80	8.20		
Molded Package Width	E1	5.00	5.30	5.60		
Overall Length	D	6.90	7.20	7.50		
Foot Length	L	0.55	0.75	0.95		
Footprint L1		1.25 REF				
Lead Thickness	С	0.09	-	0.25		
Foot Angle	¢	0°	4°	8°		
Lead Width	b	0.22	-	0.38		

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.20 mm per side.


- 3. Dimensioning and tolerancing per ASME Y14.5M.
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-072B

20-Lead Plastic Shrink Small Outline (SS) - 5.30 mm Body [SSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units		MILLIMETERS			
Dimension	Dimension Limits		NOM	MAX		
Contact Pitch	E	0.65 BSC				
Contact Pad Spacing	С		7.20			
Contact Pad Width (X20)	X1			0.45		
Contact Pad Length (X20)	Y1			1.75		
Distance Between Pads	G	0.20				


Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2072B


20-Lead Ultra Thin Plastic Quad Flat, No Lead Package (GZ) - 4x4x0.5 mm Body [UQFN]



Microchip Technology Drawing C04-255A Sheet 1 of 2

20-Lead Ultra Thin Plastic Quad Flat, No Lead Package (GZ) - 4x4x0.5 mm Body [UQFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS			
Dimension	Limits	MIN	NOM	MAX		
Number of Terminals	N	20				
Pitch	е		0.50 BSC			
Overall Height	Α	0.45	0.50	0.55		
Standoff	A1	0.00	0.02	0.05		
Terminal Thickness	A3	0.127 REF				
Overall Width	E	4.00 BSC				
Exposed Pad Width	E2	2.60 2.70 2.80				
Overall Length	D	4.00 BSC				
Exposed Pad Length	D2	2.60 2.70 2.80				
Terminal Width		0.20	0.25	0.30		
Terminal Length	L	0.30	0.40	0.50		
Terminal-to-Exposed-Pad	K	0.20	-	-		

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-255A Sheet 2 of 2

20-Lead Ultra Thin Plastic Quad Flat, No Lead Package (GZ) - 4x4x0.5 mm Body [UQFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Contact Pitch E		0.50 BSC			
Optional Center Pad Width	X2	2.80			
Optional Center Pad Length	Y2			2.80	
Contact Pad Spacing			4.00		
Contact Pad Spacing	C2		4.00		
Contact Pad Width (X20)	X1			0.30	
Contact Pad Length (X20)	Y1			0.80	
Contact Pad to Center Pad (X20)	G1	0.20			

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-2255A

20-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4 mm Body [QFN] Also called VQFN


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-126 Rev C Sheet 1 of 2

20-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4 mm Body [QFN] Also called VQFN

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension	Limits	MIN	NOM	MAX	
Number of Terminals	Ν		20		
Pitch	е		0.50 BSC		
Overall Height	Α	0.80	0.90	1.00	
Standoff	A1	A1 0.00 0.02 0.0		0.05	
Terminal Thickness	A3	0.20 REF			
Overall Length	D	4.00 BSC			
Exposed Pad Length	D2	2.60 2.70 2.80			
Overall Width	E	4.00 BSC			
Exposed Pad Width	E2	2.60	2.70	2.80	
Terminal Width	b	b 0.18 0.25 0.		0.30	
Terminal Length	L	0.30	0.40	0.50	
Terminal-to-Exposed-Pad	K	0.20	-	-	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated


3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-126 Rev C Sheet 2 of 2

20-Lead Plastic Quad Flat, No Lead Package (ML) - 4x4 mm Body [QFN] Also called VQFN

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		MILLIMETERS				
Dimension	Dimension Limits		NOM	MAX		
Contact Pitch	ontact Pitch E		0.50 BSC			
Optional Center Pad Width	X2	2.80				
Optional Center Pad Length	1 Y2 2.8			2.80		
Contact Pad Spacing	C1		4.00			
Contact Pad Spacing C			4.00			
Contact Pad Width (X20)	X1	0.3		0.30		
Contact Pad Length (X20)	Y1			0.80		
Contact Pad to Center Pad (X16)	G1	0.20				
Thermal Via Diameter	V		0.30			
Thermal Via Pitch EV			1.00			

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2126 Rev B

APPENDIX A: DATA SHEET REVISION HISTORY

Revision F (03/2022)

Updated terminology used throughout the data sheet: "master" replaced by "host", and "slave" replaced by "client".

Updated Table 3, Figures 7-1, 35-9, 35-10 and 35-11, and Sections 7.5, 27.4 and 36.0 DC and AC Characteristics Graphs and Charts. Other minor corrections. Added the 16-Lead QFN (ML) package drawing.

Revision E (12/2019)

Added the 16-Lead VQFN (7N) package drawing.

Revision D (12/2018)

Updated Register 8-1, Table 35-6. Added the QFN/VQFN package. Other minor corrections.

Revision C (07/2018)

Updated Section 35.0 Electrical Specifications. Added Section 36.0 DC and AC Characteristics Graphs and Charts. Other minor corrections.

Revision B (04/2017)

Updated pin diagrams. Minor corrections to Table 1-1. Added the **"Guidelines for Getting Started With PIC16(L)F183XX"** chapter. Updated Figure 2-1. Added Section 4.1.1.3 NVMREG Access; Section 4.2.1. BANK SELECTION. Updated ADACT Register. Added new Figure 4-8; Section 4.5.4 DATA EEPROM MEMORY. Updated Figure 18-2. Minor changes to all chapters.

Revision A (04/2016)

Initial release of the document.

THE MICROCHIP WEBSITE

Microchip provides online support via our WWW site at www.microchip.com. This website is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the website contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip website at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

CUSTOMER SUPPORT

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Field Application Engineer (FAE)
- Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the website at: http://microchip.com/support

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. Device	Ť	Reel Temperature	XXX Pattern	,	PIC16 Exten PDIP	6LF18326- E/P ded temperature
Device:		18326, PIC16LF18326, 18346, PIC16LF18346.		,		SLF18346- E/SO ded temperature,
Tape and Reel Option:	Blank T	= Standard packaging (tube or tray) = Tape and Reel ⁽¹⁾				
Temperature Range:	l E	= -40° C to $+85^{\circ}$ C (Industrial) = -40° C to $+125^{\circ}$ C (Extended)				
Package: ⁽²⁾	JQ 7N GZ P ST SL SO SS ML	= 16-lead UQFN (4x4) = 16-lead VQFN (4X4) = 16-lead QFN (4X4) = 20-lead UQFN (4x4) = 14 and 20-lead PDIP = TSSOP = 14-lead SOIC = 20-lead SOIC = SSOP = 20-lead QFN/VQFN		Note	1: 2:	Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device . Check with your Microchip Sales Office for availabil- ity with the Tape and Reel option. Small form-factor packaging options may be available. Check www.microchip.com/packaging for
Pattern:		QTP, Code or Special Requirements otherwise)				small-form factor availability, or contact your local Sales Office.

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to
 continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at https:// www.microchip.com/en-us/support/design-help/client-supportservices.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSE-QUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

 $\ensuremath{\textcircled{\sc 0}}$ 2016-2022, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-5224-9904-6

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

Netherlands - Drunen

Tel: 31-416-690399 Fax: 31-416-690340

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

 PIC16LF18346-I/SO
 PIC16LF18326-I/ST
 PIC16LF18326-I/SL
 PIC16F18346-I/SO
 PIC16F18346-I/GZ

 PIC16F18326T-I/JQ
 PIC16LF18326T-I/ST
 PIC16F18346T-I/GZ
 PIC16F18346-E/SS
 PIC16LF18346-E/SO

 PIC16LF18326T-I/JQ
 PIC16F18326T-I/ST
 PIC16LF18326E-E/JQ
 PIC16F18326T-I/SL
 PIC16LF18346-E/SS

 PIC16LF18326T-I/JQ
 PIC16F18326T-I/ST
 PIC16LF18326E-E/JQ
 PIC16F18326T-I/SL
 PIC16LF18346-E/SS

 PIC16LF18326T-I/JQ
 PIC16F18326T-I/ST
 PIC16LF18326E-E/JQ
 PIC16LF18326T-I/SL
 PIC16LF18326E-E/SL

 PIC16LF18326-E/SL
 PIC16F18326E-E/SL
 PIC16LF18346T-I/SO
 PIC16LF18346E-E/P
 PIC16LF18346T-I/SO

 PIC16LF18346T-I/SS
 PIC16F18346T-I/SO
 PIC16F18326-I/ST
 PIC16LF18326E-E/P
 PIC16LF18346-E/P

 PIC16LF18326-I/SL
 PIC16F18326-I/SS
 PIC16F18326-I/SC
 PIC16LF18326-I/GZ
 PIC16LF18346T-I/GZ

 PIC16F18326-I/SL
 PIC16F18326-I/SL
 PIC16F18326-I/SL
 PIC16LF18326-I/SL
 PIC16LF18326-I/SL

 PIC16F18326-I/SL
 PIC16F18326-I/SL
 PIC16LF18326-I/SL
 PIC16LF18326-I/SL
 PIC16LF18326-I/SL

 PIC16F18326-E/SL
 PIC16F18326-I/SL
 PIC16F18326-I/