

## Hole Saw Arbors

Four standard models are available, each one furnished with a choice of 6.35mm (1/4") high speed steel or carbide tipped pilot drills. The set-screw in the body allows for easy replacement of the pilot drill. Quick-Hitch™ arbors permit instant change of hole saws without tools and without removing the arbor from the chuck.

A1, A4, A10 and A17-38 type arbors are suitable for use with the Quick Change Connector - Cat AQCDH.



ARBORS SUPPLIED WITH HIGH SPEED STEEL PILOT DRILLS				
CAT NO	FITS HOLE SAW DIAMETER	FITS CHUCK SIZE	SHANK SIZE	SCREW THREAD
A1	14-30mm (9/16" - 1 3/16")	9.5mm (3/8")	8.75mm (11/32") Hex	1/2"-20
A2 QUICK-HITCH	32-210mm (1 1/4" - 8 9/32")	13mm (1/2")	11mm (7/16") Hex	5/8"-18
A4	14-30mm (9/16" - 1 3/16")	6.5mm (1/4")	6.5mm (1/4") Hex	1/2"-20
A10 QUICK-HITCH	32-210mm (1 1/4" - 8 9/32")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18
ARBORS SUPPLIED WITH CARBIDE TIPPED PILOT DRILLS				
XA1	14-30mm (9/16" - 1 3/16")	9.5mm (3/8")	8.75mm (11/32") Hex	1/2"-20
XA2 QUICK HITCH	32-210mm (1 1/4" - 8 9/32")	13mm (1/2")	11mm (7/16") Hex	5/8"-18
XA4C	14-30mm (9/16" - 1 3/16")	6.5mm (1/4")	6.5mm (1/4") Hex	1/2"-20
XA10 QUICK HITCH	32-210mm (1 1/4" - 8 9/32")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18

## Locking Arbors

Ideal for use with saws 32mm - 210mm (1 1/4" - 8 9/32") diameter, the arbor locks tightly on the saw eliminating vibration and is invaluable on exceptionally tough jobs and production runs. Fitted with a 6.35mm (1/4") high speed steel or carbide tipped pilot drill.



LOCKING ARBORS WITH HIGH SPEED STEEL PILOT DRILL				
CAT NO	FITS HOLE SAW DIAMETER	FITS CHUCK SIZE	SHANK SIZE	SCREW THREAD
A17-38	32-210mm (1 1/4" - 8 9/32")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18
LOCKING ARBORS WITH CARBIDE TIPPED PILOT DRILL				
XA17-38	32-210mm (1 1/4" - 8 9/32")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18

## Special Purpose SDS Plus Shank Arbors

The SDS-plus shank allows the arbors to be used in SDS-plus rotary hammer drills with the hammer action facility turned off. Fitted with a 6.35mm (1/4") pilot drill.



SDS PLUS SHANK ARBORS WITH HIGH SPEED STEEL PILOT DRILL				
CAT NO	FITS HOLE SAW DIAMETER	FITS CHUCK SIZE	SHANK SIZE	SCREW THREAD
A1-1	14-30mm (9/16" - 1 3/16")	SDS Plus	SDS Plus	1/2"-20
A2-1	32-152mm (1 1/4 - 6")	SDS Plus	SDS Plus	5/8"-18

## Fast Cut Multi Purpose Hole Saw Arbors

Fast Cut Multi Purpose Hole Saw Arbors have exactly the same specification as our standard arbor range, except that the pilot drill is replaced by a 13mm (1/2") longer pilot drill, suitable for use with the extended cutting depth of our Fast Cut Multi Purpose Hole Saws.



FAST CUT MULTI PURPOSE HOLE SAW ARBORS WITH EXTRA LENGTH HIGH SPEED STEEL PILOT DRILLS				
CAT NO	FITS HOLE SAW DIAMETER	FITS CHUCK SIZE	SHANK SIZE	SCREW THREAD
A1E	14-30mm (9/16" - 1 3/16")	9.5mm (3/8")	8.75mm (11/32") Hex	1/2"-20
A2E QUICK-HITCH	32-159mm (1 1/4" - 6 1/4")	13mm (1/2")	11mm (7/16") Hex	5/8"-18
A4E	14-30mm (9/16" - 1 3/16")	6.5mm (1/4")	6.5mm (1/4") Hex	1/2"-20
A10E QUICK-HITCH	32-159mm (1 1/4" - 6 1/4")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18
FAST CUT MULTI PURPOSE HOLE SAW LOCKING ARBOR WITH EXTRA LENGTH HIGH SPEED STEEL PILOT DRILL				
A17-38E	32-159mm (1 1/4" - 6 1/4")	9.5mm (3/8")	8.75mm (11/32") Hex	5/8"-18
FAST CUT MULTI PURPOSE HOLE SAW SDS PLUS SHANK ARBORS WITH EXTRA LENGTH HIGH SPEED STEEL PILOT DRILLS				
CAT NO	FITS HOLE SAW DIAMETER	FITS CHUCK SIZE	SHANK SIZE	SCREW THREAD
A1-1E	14-30mm (9/16" - 1 3/16")	SDS Plus	SDS Plus	1/2"-20
A2-1E	32-152mm (1 1/4 - 6")	SDS Plus	SDS Plus	5/8"-18