


REV	REV.LIR	BEFORE REVISION	AFTER REVISION	SIGN	DATE
A/0					2022/12/5



Pin Assignment

P1	Color	P2
1	White	1
3	Red	3
2	Drain	2
4	White	4
6	Green	6
5	Drain	5
7	White	7
9	Blue	9
8	Drain	8
10	White	10
12	Brown	12
11	Drain	11
13	White	13
14	White	14
19	Black	19
17	Drain	17
15	Orange	15
16	Yellow	16
18	Red	18
SHELL	Drain	SHELL

TABLE A

P/No.	Length of finished product	Impedance of conduction
GC860-1.5	1500±20mm	3Ω
GC860-2.0	2000±30mm	4Ω

NOTES:
 1.100% OPEN,SHORT & MISWIRE TESE
 2.CONDUCTIVE RESISTANCE:TABLE A/MAX
 3.INSULATION RESISTANCE:10MΩ/MIN.AT DC300V/10ms
 4.Testing requirements: 8K 60Hz

Unit	mm	The general tolerance							
Scale	5:1	xx.:±0.3	5	shell	H02-0092	Zinc alloy shell, 38.6mm (L) ×14.5mm (W) ×10.2mm (H), gun color, printing: HDMI, VCOM, laser: 8K	2	pcs	
			4	PVC	SPVBK-003	PVC 45Pa Black UL94V-0	N/A	g	
			3	PE	SPETRO0001	PE Low density	N/A	g	
			2	CONN	CHDM019IGAM001	HDMI type A/M 2.1V PIN:G/F SHELL:G/F Insulator:Black, Three piece connector	2	pcs	
			1	WIRE	WUB54930A1-026	30AWG(1/0.254B*1P+D+AL+HM)*5C+30AWG*1/0.254B*4C+F+ADB16/9/0.12AL OD:6.0mm Black	ABLE A	mm	
		.xx.:±0.05	NO.	NAME	PAPT NO	SPECIFICATIONS	QTY	UNIT	

APPROVED BY	CHECKED BY	DRAWN BY
XIANG		CHEN



DESCRIPTION:	HDMI A/M TO HDMI A/M 2.1V
P/N:	CG860
DRAWN NO:	