ROHS COMPLIANT

Vishay General Semiconductor

Schottky Barrier Rectifier



| PRIMARY CHARACTERISTICS | | | | | | |
|-------------------------|----------------|--|--|--|--|--|
| I _{F(AV)} | 5.0 A | | | | | |
| V _{RRM} | 20 V to 60 V | | | | | |
| I _{FSM} | 220 A | | | | | |
| V _F | 0.48 V, 0.65 V | | | | | |
| T _J max. | 150 °C | | | | | |

FEATURES

- Guardring for overvoltage protection
- Extremely fast switching
- Low forward voltage drop
- High forward surge capability
- High frequency operation
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, dc-to-dc converters, and polarity protection applications.

MECHANICAL DATA

Case: DO-201AD

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS compliant, commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: Color band denotes the cathode end

| MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted) | | | | | | | |
|---|--------------------|------------------------|-------|-------|-------|-------|------|
| PARAMETER | SYMBOL | SB520 | SB530 | SB540 | SB550 | SB560 | UNIT |
| Maximum repetitive peak reverse voltage | V _{RRM} | 20 | 30 | 40 | 50 | 60 | V |
| Maximum RMS voltage | V _{RMS} | 14 | 21 | 28 | 35 | 42 | V |
| Maximum DC blocking voltage | V _{DC} | 20 | 30 | 40 | 50 | 60 | V |
| Maximum average forward rectified current at 0.375" (9.5 mm) lead length (fig. 1) | I _{F(AV)} | I _{F(AV)} 5.0 | | | | | A |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load | I _{FSM} | I _{FSM} 220 | | | | A | |
| Operating junction temperature range | TJ | - 65 to + 150 | | | | °C | |
| Storage temperature range | T _{STG} | - 65 to + 150 | | | | °C | |

| ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | | | |
|---|-------|-------------------------|-------------------------------|-------|-------|-------|-------|-------|------|
| PARAMETER | TEST | CONDITIONS | SYMBOL | SB520 | SB530 | SB540 | SB550 | SB560 | UNIT |
| Maximum instantaneous forward voltage | 5.0 A | | V _F ⁽¹⁾ | 0.48 | | 0.65 | | V | |
| Maximum instantaneous reverse current at rated | | T _A = 25 °C | I _B ⁽¹⁾ | 0.5 | | | mA | | |
| DC blocking voltage | | T _A = 100 °C | 'R \'' | | 50 | | 2 | 5 | ШA |

Note

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

Document Number: 88721 Revision: 19-Oct-09

For technical questions within your region, please contact one of the following: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u>



Vishay General Semiconductor



| THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted) | | | | | | | |
|--|---------------------------------|-------|-------|-------|-------|-------|------|
| PARAMETER | SYMBOL | SB520 | SB530 | SB540 | SB550 | SB560 | UNIT |
| Typical thermal registerion | R _{0JA} ⁽¹⁾ | 25 | | | | °C/W | |
| Typical thermal resistance | R _{0JL} ⁽¹⁾ | 8 | | | | | C/W |

Note

⁽¹⁾ Thermal resistance from junction to lead vertical P.C.B. mounting, 0.375" (9.5 mm) lead length

| ORDERING INFORMATION (Example) | | | | | | | | |
|--------------------------------|-----------------|------------------------|---------------|----------------------------------|--|--|--|--|
| PREFERRED P/N | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE | | | | |
| SB540-E3/54 | 1.09 | 54 | 1400 | 13" diameter paper tape and reel | | | | |
| SB540-E3/73 | 1.09 | 73 | 1000 | Ammo pack packaging | | | | |

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)






Fig. 1 - Forward Current Derating Curve










Fig. 3 - Typical Instantaneous Forward Characteristics






For technical questions within your region, please contact one of the following: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com



SB520 thru SB560


Vishay General Semiconductor













Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.