



Part Number : [2042236006](#)

Product Description : Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 6 Circuit Housing, Circuit #6 Voided

Series Number : 204223

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 2042236006_sd.pdf](#)

3D Models and Design Files

[3D Model 2042236006_stp.zip](#)

Specifications

[Application Specification 2042200000-AS-000.pdf](#)

[Packaging Specification 2042230000-PK-000.pdf](#)

[Product Specification 2042200000-PS-000.pdf](#)

[Product Specification 2042200000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	204223
Description	Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 6 Circuit Housing, Circuit #6 Voided
Application	Power, Signal, Wire-to-Wire
Product Family	Squba Sealed Wire-to-Wire Connectors
Product Name	Squba
UPC	191128757898

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.340/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba Sealed Single Row Receptacle Assemblies	<u>204220</u>

Use with Part(s)

Description	Part Number
Squba Plug Terminal, Matte Tin Plating, 22-24 AWG	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/2042261001.html</u>