MORNSUN®

Wide input voltage Non-Isolated and Regulated Single Output









FEATURES

- High efficiency up to 96%
- No-load input current as low as 0.1mA
- Operating ambient temperature range -40 $^{\circ}\mathrm{C}$ to +85 $^{\circ}\mathrm{C}$
- Support the negative output
- Output short-circuit protection
- Pin compatible with LM78xx series
- IEC60950, UL60950, EN62368 Approval

K78xx-1000R3(L) series are high efficiency switching regulators and ideal substitutes for LM78xx series three-terminal linear regulators. The converters feature high efficiency, low loss, short circuit protection, positive or negative output voltage, and there is no need for a heat sink. These product are widely used in applications such as industrial control, instrumentation and electric power.

Selection	Selection Guide									
		Input Voltage (VDC) [©]	O	utput	Full Load	Max.				
Certification	Part No.	Nominal (Range)	Voltage (VDC)	Current (mA) Max.	Efficiency (%) Vin Min. / Vin Max.	Capacitive Load (µF)				
	K7803-1000R3(L)	24 (6-36)	3.3	1000	90/81	680				
	K7805-1000R3(L)	24 (8-36)	5	1000	93/86	680				
		12 (8-27)	-5	-500	86/82	330				
UL/CE/CB	K7809-1000R3(L)	24 (13-36)	9	1000	95/90	680				
	K7812-1000R3(L) K7815-1000R3(L)	24 (16-36)	12	1000	96/93	680				
		12 (8-20)	-12	-300	89/88	330				
		24 (20-36)	15	1000	96/94	680				
		12 (8-18)	-15	-300	89/89	330				

Note:

② L-suffix: Add L-suffix for horizontal mount with 90 degree angled pins (K78xx-1000R3L).

Input Specifications						
Item	Operating Conditions	Min.	Тур.	Max.	Unit	
No-load Input Current	Positive output	-	0.1	1	mA	
Reverse Polarity Input		Forbidden				
Input Filter		Capacitance filter				

Output Specifications								
Item	Operating Conditions	Operating Conditions		Тур.	Max.	Unit		
Voltage Appurativ	F. II I a sel !	K7803-1000R3(L)		±2	±2 ±4			
Voltage Accuracy	Full load, input voltage range Others		±2	±3	ov.			
Linear Regulation	Full load, input voltage range	Full load, input voltage range		±0.2	±0.4	%		
Load Regulation	Nominal input,10% -100% load			±0.4	±0.6			
Ripple & Noise*	20MHz bandwidth, nominal input, 20%-100% load			20	75	mVp-p		

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

①For input voltage exceeding 30 VDC, an input capacitor of 22uF/50V is required;

DC/DC Converter K78xx-1000R3(L) Series

MORNSUN®

Temperature Coefficient	Operating ambient temperature -40 $^{\circ}\!$		-	±0.03	%/ ℃
Transient Response Deviation	Naminalization typitasa 050/ land the above		50	300	mV
Transient Recovery Time	Nominal input voltage, 25% load step change		0.1	1	ms
Short-circuit Protection	Nominal input	Continuous, self-recovery			

*Note: 1. The "parallel cable" method is used for Ripple and noise test, please refer to *DC-DC Converter Application Notes* for specific information;
2. With light loads at or below 20%, Ripple & Noise for 3.3/5V output parts increases to 100mVp-p max, and for 9V/12V/15V output parts to 2%Vo max.

General Specifications								
Item	Operating Condition		Min.	Тур.	Max.	Unit		
Operating Temperature*	Derating if the temperature ≥71°C (see Fig. 1)		-40		85			
Storage Temperature			-55		125	~c		
Pin Soldering Resistance Temperature	Soldering time: 10 seconds		-		260			
Storage Humidity	Non-condensing		5		95	%RH		
Switching Frequency	100% load, input voltage	K7803-1000R3(L)/K7805-1 000R3(L)	420	520	620	kHz		
, and the same of	range	Other output	580	680	780			
MTBF	MIL-HDBK-217F@25℃		2000	-	-	k hours		
Note: *The K7803-2000 (L) part requires an	Note: *The K7803-2000 (L) part requires an input voltage ≥5V for operation at -40°C.							

Mechanical Specifications						
Case Material		Black plastic; flame-retardant and heat-resistant (UL94 V-0)				
Dimensions	K78xx-1000R3	11.50 x 9.00 x 17.50 mm				
Diffierisions	K78xx-1000R3L	19.00 x 11.50 x 9.00 mm				
		3.8g (Typ.)				
		Free air convection				

Electron	Electromagnetic Compatibility (EMC)								
Emissions	CE	CISPR32/EN55032	CLASS B (see Fig. 4-2) for recommended circuit)						
RE		CISPR32/EN55032	2 CLASS B (see Fig. 4-2) for recommended circuit)						
	ESD	IEC/EN 61000-4-2	Contact ±4KV	perf. Criteria B					
	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A					
Immunity	EFT	IEC/EN 61000-4-4	±1KV (see Fig. 4-1) for recommended circuit)	perf. Criteria B					
	Surge	IEC/EN 61000-4-5	line to line ±1KV(see Fig. 4-① for recommended circuit)	perf. Criteria B					
	CS	IEC/EN 61000-4-6	3Vr.m.s	perf. Criteria A					

Typical Characteristic Curves








Fig. 1






Negative output Efficiency Vs input voltage (full load)






Design Reference

1. Typical application



Positive output application circuit



Negative output application circuit

Fig. 2 Typical application circuit




Fig. 3 Positive and I	Negat	ive out	tput app	licatio	n circuit

	Table 1	
Part No.	C1/C3 (ceramic capacitor)	C2/C4 (ceramic capacitor)
K7803-1000R3(L)		22µF/10V
K7805-1000R3(L)		22µF/10V
K7809-1000R3(L)	<u> </u>	22µF/16V
K7812-1000R3(L)		22µF/25V
K7815-1000R3(L)		22μF/25V

Note:

- 1. The required capacitors C1 and C2 (C3 and C4) must be connected as close as possible to the terminals of the module;
- 2. Refer to Table 1 for C1 and C2 (C3 and C4) capacitor values. For certain applications, increased values for C2 and C4 and/or tantalum or low ESR electrolytic capacitors may also be used instead;
- 3. When using configurations as shown in figure 3, we recommended to add an inductor (LDM) with a value of up to 10µH which helps reducing mutual interference;
- 4. Converter cannot be used for hot swap and with output in parallel.

2. EMC compliance circuit




Fig. 4 EMC recommended circuit


FUSE	MOV	LDM1	C0	C1/C2	C5	LDM2
Select fuse value according to actual input current	S20K30	82µH	680µF /50V	Refer to table 1	4.7µF /50V	12µH

Note: Part ① in Fig. 4 shows EMS compliance filter and part ② filter for EMI compliance; depending on requirement both filters ① and ② can be used in series as shown.

3. For additional information please refer to DC-DC converter application notes on

www.mornsun-power.com

Dimensions and Recommended Layout



Notes:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging bag number: 58210021 (K78xx-1000R3), 58210027 (K78xx-1000R3L);
- 2. The maximum capacitive load offered were tested at nominal input voltage and full load;
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 4. All index testing methods in this datasheet are based on our company corporate standards;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

MORNSUN Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail: info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.