

PTC thermistors for overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ...
230 V

Series/Type:

Date: August 2014

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Applications

- Overcurrent protection
- Short circuit protection

Features

- Qualification based on AEC-Q200 rev. D for type A407, A607 and A907
- Thermistor chip with lead-free tinned terminations
- Small size
- Short response times
- Suitable for reflow soldering only
- Suitable for automatic placement
- UL approval for selected types (case size 1210)
- RoHS-compatible

Delivery mode

- Blister tape (case size 1210) or cardboard tape (case sizes 0402 and 0603), 180-mm reel with 8-mm tape, taping to IEC 60286-3

General technical data


Switching cycles		N	100	
Tolerance of R_R	(except A907)	ΔR_R	± 25	%
Tolerance of R_R	(for A907)	ΔR_R	± 35	%
Operating temperature range	($V = 0$)	T_{op}	$-40/+125$	$^{\circ}\text{C}$
Operating temperature range	($V \leq V_{max}$, except A407 and A907)	T_{op}	$-20/+85$	$^{\circ}\text{C}$
Operating temperature range	($V \leq V_{max}$, for A407)	T_{op}	$-40/+125$	$^{\circ}\text{C}$
Operating temperature range	($V \leq V_{max}$, for A907)	T_{op}	$-40/+85$	$^{\circ}\text{C}$

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Electrical specifications and ordering codes

Type	$I_R^{1)}$ mA	$I_S^{1)}$ mA	I_{Smax} ($V = V_{max}$) A	R_R Ω	R_{min} Ω	EIA case size	Approvals 	Ordering code
$V_{max} = 30$ V DC or V AC, $V_R = 24$ V DC or V AC								
A606	90	180	0.5	27	17	1210	X	B59606A0110A062
A607	70	130	0.4	55	30	1210	X	B59607A0120A062
$V_{max} = 32$ V DC or V AC, $V_R = 24$ V DC or V AC								
A407	13	32	0.12	470	265	0402	–	B59407A0115A062
$V_{max} = 60$ V DC or V AC, $V_R = 42$ V DC or V AC								
A622	20	40	0.22	220	150	0603	–	B59622A0090A062
$V_{max} = 80$ V DC or V AC, $V_R = 63$ V DC or V AC								
A623	13	25	0.15	470	300	0603	–	B59623A0090A062
A707	50	90	0.3	125	75	1210	X	B59707A0120A062
$V_{max} = 265$ V DC or V AC, $V_R = 230$ V DC or V AC								
A807	15	40	0.2	400	200	1210	X	B59807A0090A062
A907	12	22	0.15	1500	640	1210	X	B59907A0120B062
$V_{max} = 400$ V DC or V AC, $V_R = 230$ V DC or V AC								
A907	12	22	0.15	1500	640	1210	–	B59907A0120A062

1) Measured on component soldered to standardized PCB


Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Dimensional drawings in mm


EIA case size 0402




Solder pad




EIA case size 0603




Solder pad



EIA case size 1210



Solder pad



Recommended maximum dimensions (mm)

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Reliability data

Test	Standard	Test conditions	$ \Delta R_{25}/R_{25} $
Electrical endurance, cycling	IEC 60738-1	Room temperature, I_{Smax}, V_{max} Number of cycles: 100	< 25% < 10% ¹⁾
Electrical endurance, constant	IEC 60738-1	Storage at $V_{max}/T_{op,max}$ (V_{max}) Test duration: 1000 h	< 25% < 20% ¹⁾
Damp heat	IEC 60738-1	Temperature of air: 40 °C Relative humidity of air: 93% Duration: 56 days Test according to IEC 60068-2-78	< 10%
Rapid change of temperature	IEC 60738-1	$T_1 = T_{op,min}$ (0 V), $T_2 = T_{op,max}$ (0 V) Number of cycles: 5 Test duration: 30 min Test according to IEC 60068-2-14, test Na	< 10%
Vibration	IEC 60738-1	Frequency range: 10 - 55 - 10 Hz Displacement amplitude: 0.75 mm Test duration: 3 × 2 h Test according to IEC 60068-2-6, test Fc	< 5% < 10% ¹⁾
Shock	IEC 60738-1	Pulse shape: half-sine Acceleration: 400 m/s ² Pulse duration: 6 ms; 6 × 5000 pulses Test according to IEC 60068-2-27, test Ea	< 5% < 10% ¹⁾
Climatic sequence	IEC 60738-1	Dry heat: $T = T_{op,max}$ (0 V) Test duration: 16 h Damp heat first cycle Cold: $T = T_{op,min}$ (0 V) Test duration: 2 h Damp heat 5 cycles Tests performed according to IEC 60068-2-30	< 10%
Bending test	IEC 60738-1	Components reflow-soldered to test board Maximum bending: 2 mm Test according to IEC 60068-2-21, test Ue	< 10%
Adhesive strength on PCB		Shearing of the component soldered on PCB by a force of 5 N normal to components longitudinal axis	No visible damage

1) For type A407, B59407A0115A062


Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Characteristics (typical) for A407

PTC resistance R_{PTC} versus
PTC temperature T_{PTC}
(measured at low signal voltage)



Rated current I_R versus ambient temperature T_A
(measured in still air)




Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Characteristics (typical) for A606, A607 and A707


PTC resistance R_{PTC} versus
PTC temperature T_{PTC}
(measured at low signal voltage)



Switching time t_S versus switching current I_S
(measured at 25 $^{\circ}\text{C}$ in still air)



Rated current I_R versus ambient temperature T_A
(measured in still air)




Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Characteristics (typical) for A807


PTC resistance R_{PTC} versus
PTC temperature T_{PTC}
(measured at low signal voltage)



Switching time t_s versus switching current I_s
(measured at 25 $^{\circ}\text{C}$ in still air)



Rated current I_R versus ambient temperature T_A
(measured in still air)



Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Characteristics (typical) for A907

PTC resistance R_{PTC} versus


PTC temperature T_{PTC}

(measured at low signal voltage)




Switching time t_s versus switching current I_s

(measured at 25 °C in still air)



Rated current I_R versus ambient temperature T_A

(measured in still air)



Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V


SMD

Characteristics (typical) for A622 and A623

PTC resistance R_{PTC} versus


PTC temperature T_{PTC}

(measured at low signal voltage)




Switching time t_S versus switching current I_S

(measured at 25 °C in still air)



Rated current I_R versus ambient temperature T_A

(measured in still air)



Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Cautions and warnings

General

- EPCOS thermistors are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with EPCOS during the design-in-phase.
- Ensure suitability of thermistor through reliability testing during the design-in phase. The thermistors should be evaluated taking into consideration worst-case conditions.

Storage

- Store thermistors only in original packaging. Do not open the package before storage.
- Storage conditions in original packaging: storage temperature $-25\text{ }^{\circ}\text{C} \dots +45\text{ }^{\circ}\text{C}$, relative humidity $\leq 75\%$ annual mean, maximum 95%, dew precipitation is inadmissible.
- Avoid contamination of thermistors surface during storage, handling and processing.
- Avoid storage of thermistor in harmful environment with effect on function on long-term operation (examples given under operation precautions).
- Use thermistor within the following period after delivery:
 - Through-hole devices (housed and leaded PTCs): 24 months
 - Motor protection sensors, glass-encapsulated sensors and probe assemblies: 24 months
 - Telecom pair and quattro protectors (TPP, TQP): 24 months
 - Leadless PTC thermistors for pressure contacting: 12 months
 - Leadless PTC thermistors for soldering: 6 months
 - SMDs in EIA sizes 3225 and 4032, and for PTCs with metal tags: 24 months
 - SMDs in EIA sizes 0402, 0603, 0805 and 1210: 12 months

Handling

- PTCs must not be dropped. Chip-offs must not be caused during handling of PTCs.
- Components must not be touched with bare hands. Gloves are recommended.
- Avoid contamination of thermistor surface during handling.

Soldering (where applicable)

- Use rosin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended.
- Complete removal of flux is recommended.
- Standard PTC heaters are not suitable for soldering.

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Mounting

- Electrode must not be scratched before/during/after the mounting process.
- Contacts and housing used for assembly with thermistor have to be clean before mounting. Especially grease or oil must be removed.
- When PTC thermistors are encapsulated with sealing material, the precautions given in chapter "Mounting instructions", "Sealing and potting" must be observed.
- When the thermistor is mounted, there must not be any foreign body between the electrode of the thermistor and the clamping contact.
- The minimum force of the clamping contacts pressing against the PTC must be 10 N.
- During operation, the thermistor's surface temperature can be very high. Ensure that adjacent components are placed at a sufficient distance from the thermistor to allow for proper cooling at the thermistors.
- Ensure that adjacent materials are designed for operation at temperatures comparable to the surface temperature of thermistor. Be sure that surrounding parts and materials can withstand this temperature.
- Avoid contamination of thermistor surface during processing.

Operation

- Use thermistors only within the specified temperature operating range.
- Use thermistors only within the specified voltage and current ranges.
- Environmental conditions must not harm the thermistors. Use thermistors only in normal atmospheric conditions. Avoid use in deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas etc), corrosive agents, humid or salty conditions. Contact with any liquids and solvents should be prevented.
- Be sure to provide an appropriate fail-safe function to prevent secondary product damage caused by abnormal function (e.g. use VDR for limitation of overvoltage condition).

This listing does not claim to be complete, but merely reflects the experience of EPCOS AG.

Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.epcos.com/orderingcodes

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

Symbols and terms

Symbol	Term
A	Area
C	Capacitance
C_{th}	Heat capacity
f	Frequency
I	Current
I_{max}	Maximum current
I_R	Rated current
I_{res}	Residual current
I_{PTC}	PTC current
I_r	Residual current
$I_{r,oil}$	Residual current in oil (for level sensors)
$I_{r,air}$	Residual current in air (for level sensors)
I_{RMS}	Root-mean-square value of current
I_S	Switching current
I_{Smax}	Maximum switching current
LCT	Lower category temperature
N	Number (integer)
N_c	Operating cycles at V_{max} , charging of capacitor
N_f	Switching cycles at V_{max} , failure mode
P	Power
P_{25}	Maximum power at 25 °C
P_{el}	Electrical power
P_{diss}	Dissipation power
R_G	Generator internal resistance
R_{min}	Minimum resistance
R_R	Rated resistance
ΔR_R	Tolerance of R_R
R_P	Parallel resistance
R_{PTC}	PTC resistance
R_{ref}	Reference resistance
R_S	Series resistance
R_{25}	Resistance at 25 °C
$R_{25,match}$	Resistance matching per reel/ packing unit at 25 °C
ΔR_{25}	Tolerance of R_{25}
T	Temperature
t	Time
T_A	Ambient temperature

Overcurrent protection

SMDs, EIA sizes 0402, 0603, and 1210, 24 V ... 230 V

SMD

t_a	Thermal threshold time
T_C	Ferroelectric Curie temperature
t_E	Settling time (for level sensors)
T_R	Rated temperature
T_{sense}	Sensing temperature
T_{op}	Operating temperature
T_{PTC}	PTC temperature
t_R	Response time
T_{ref}	Reference temperature
T_{Rmin}	Temperature at minimum resistance
t_S	Switching time
T_{surf}	Surface temperature
UCT	Upper category temperature
V or V_{el}	Voltage (with subscript only for distinction from volume)
$V_{c(max)}$	Maximum DC charge voltage of the surge generator
$V_{F,max}$	Maximum voltage applied at fault conditions in protection mode
V_{RMS}	Root-mean-square value of voltage
V_{BD}	Breakdown voltage
V_{ins}	Insulation test voltage
$V_{link,max}$	Maximum link voltage
V_{max}	Maximum operating voltage
$V_{max,dyn}$	Maximum dynamic (short-time) operating voltage
V_{meas}	Measuring voltage
$V_{meas,max}$	Maximum measuring voltage
V_R	Rated voltage
V_{PTC}	Voltage drop across a PTC thermistor
α	Temperature coefficient
Δ	Tolerance, change
δ_{th}	Dissipation factor
τ_{th}	Thermal cooling time constant
λ	Failure rate
e	Lead spacing (in mm)

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.