

Shrink sleeve - WMS 9,5 (EX16)R BK - 0800421

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shrink sleeve, Roll, black, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK W: without print, unperforated, mounting type: slide-on, cable diameter range: 3.2 ... 9.5 mm, lettering field size: 16 x 20000 mm

Your advantages

- ✓ Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- ✓ The shrink sleeves are automatically perforated or cut to the required length during the printing process
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- ✓ MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ Individual markers can be cut to any length up to 1 m

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 626194
GTIN	4046356626194

Technical data

Dimensions

Length (b)	20 m
Width (a)	16 mm
Cable diameter	3.2 mm ... 9.5 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	black
Base element material	polyolefine

Shrink sleeve - WMS 9,5 (EX16)R BK - 0800421

Technical data

General

Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
Shrink rate	3:1
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC001530

Shrink sleeve - WMS 9,5 (EX16)R BK - 0800421

Classifications

ETIM

ETIM 7.0	EC001530
----------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals




Approvals

CSA / UL Recognized



Ex Approvals



Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	---	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	---	---	---------------

Accessories

Accessories

Ink ribbon

Shrink sleeve - WMS 9,5 (EX16)R BK - 0800421

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Ink ribbon - TM-RIBBON 110 WH 100 - 0804661



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing the material off the roll product groups: EML..., EMLP ..., EMLF..., PML-M..., PML-T... and US material product groups: US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-WMT..., US-WMTB ..., US-PML-M..., US-EMLF..., width: 110 mm, color: white

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0800421](#)