

# Product Data Sheet

DIN 41612 Male 90°, type H11,  
Part No. 113-40010




Illustration similar



Perpendicular



Through Hole



Power



Rugged

- Termination length 3.5 mm
- 11 contacts
- solder
- performance level 2



» to product on [www.ept.de](http://www.ept.de)



» to product group [DIN 41612](#)

# Product Data Sheet

DIN 41612 Male 90°, type H11,  
Part No. 113-40010



## Technical Specifications

### Basics

Specification	IEC 60603-2 (DIN 41612)
Performance Level	2
No. of Contacts	11
Termination Technology	solder
Termination Length	3.5 mm
Operating Temperature Range	-55°C to +125°C

### Material

Insulator Material	PBT glass filled UL 94 V-0
CTI value <i>IEC 60112</i>	200
Contact Material	Copper alloy

### Mechanical

Pitch	7.62 mm
Mating Force	< 80 N
Separating Force per Pin	> 0.2 N
Durability	400 mating cycles

### Electrical

Operational Current	15 A
Contact Resistance	<8 mΩ
Clearance and Creepage	cr: ≥ 8.0 mm, cl: ≥ 4.5 mm
Insulation Resistance	> 10 <sup>6</sup> MΩ
Test Voltage	3100 V

### Processing

Soldering Temperature	to 260°C
-----------------------	----------

### Approval / Compliance


Environment	RoHS compliant
-------------	----------------

# Product Data Sheet

DIN 41612 Male 90°, type H11,  
Part No. 113-40010



## Derating Diagram



### Type H

20 °C	15 A
70 °C	11 A
100 °C	8 A

# Product Data Sheet

DIN 41612 Male 90°, type H11,  
Part No. 113-40010

---



## Modifications

Available on request

- Pre-mating and late-mating contacts
- Contact arrangement

## Drawings

Component data in 2D and 3D format you can download here:

[» PDF](#)

[» 3D IGES](#)

[» 3D STEP](#)

[» 3D PDF](#)