




Technical Data:
Electrical
 Pitch: 3.5mm
 Voltage rating: 300V
 Current rating: 12 Amps
 Withstanding Voltage: 2500VAC(1min)
Mechanical:
 Operating temperature: -40°C to +105°C
 Soldering temperature:
 Temperature= 250°C±10°C / 5 seconds max
 Safety approval: 
 RoHS Compliance


Part No.: **OSTOQXX1251**

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
... ..	3: Orange
24 24 Poles	4: Yellow
	5: Green (Standard)
	6: Blue
	8: Grey


Nonstandard colors
 Mins could apply



N=Number of contacts



P.C.B. LAYOUT



2	Pin	Copper Alloy	Tin plated	1xN
1	Body	PA66-30%GF UL94V		1
ITEM NAME OF PART		MATERIAL		Q'TY
DWG.	DATE	UNITS:	MM	SHEET: 1 OF 1
CHK.	DATE	SCALE:	NONE 4:1 ()	REV: A
APP.	DATE	TITLE:	OSTOQ SERIES 3.5MM RIGHT ANGLE TRIANGLE KEY LOCK	X. ±0.50 X.X ±0.30 X.XX ±0.10 X* ±1°
		PART NO. OSTOQXX1251		
		DWG NO. OSTOQXX1251.DWG		



ON-SHORE TECHNOLOGY, INC.

REV	SIGN	DESCRIPTION	CHK	DATE