Evaluates: MAX31343

General Description

The MAX31343 SHIELD is a fully assembled and tested PCB to evaluate the MAX31343, low-cost, extremely accurate, real-time clock (RTC) with I²C interface and power management. The shield operates from a single supply, either from USB or external power supply, and the integrated microelectromechanical systems (MEMS) resonator enhances the long-term accuracy and eliminates the external crystal requirement in the system. This device is accessed through an I²C serial interface provided by a MAX32625 PICO board.

The MAX31343 shield provides the hardware and software user interface (GUI) necessary to evaluate the MAX31343. The kit includes a MAX31343EKA+T. It connects to the PC through a MAX32625 PICO board and a micro-USB cable.

Features

- Easy Evaluation of the MAX31343
- +1.6V to +5.5V Single-Supply Operation
- Proven PCB Layout
- Fully Assembled and Tested

Shield Photo



Windows is a registered trademark and registered service mark of Microsoft Corporation.

Shield Contents

- Assembled MAX32625 PICO controller board
- Micro-USB cable
- Assembled circuit board including MAX31343EKA+T


Quick Start

Required Equipment

- One pico ammeter for measuring the current
- One oscilloscope and one oscilloscope probe
- One PC or laptop with Microsoft Windows® 7 or later
- One USB A male to micro B male cable
- One assembled and programmed MAX32625 PICO board
- One MAX31343 shield

Ordering Information appears at end of data sheet.

PICO Board Photo





Evaluates: MAX31343

Procedure

The shield is fully assembled and tested. Use the following steps to verify board operation.

- 1) Place the MAX31343 shield on a nonconductive surface to ensure that nothing on the PCB gets shorted to the workspace.
- 2) Verify that all jumpers are in their default position as shown on Table 1.
- 3) Connect the MAX32625 PICO board to the shield at the location shown as MAX32625 PICO (Figure 1).
- 4) Connect the USB A male to micro B male cable between the MAX32625 PICO board and PC/Laptop.
- Go to the MAX31343 shield product page to download and install the latest version of MAX31343 RTC SHIELD software.
- 6) Open the MAX31343 RTC SHIELD software, shown as Figure 2.




Figure 1. Connection and Setup

Table 1. Jumper Settings

JUMPER	SHUNT POSITION	DESCRIPTION				
JU1	1-2*	Connects clock output to pin 6 of P2 Arduino [®] /Mbed [®] connector				
JU 1	Open	Disconnects clock output from Arduino/Mbed connector				
	1-2	Connects backup supply to external DC supply				
11.12	1-3	Connects backup supply to super capacitor				
JU2	1-4*	Connects backup supply to ground				
	Open	Disconnects backup supply				
JU3	1-2*	Connects interrupt signal to pin 3 of P2 Arduino/Mbed connector				
103	Open	Disconnects interrupt signal from Arduino/Mbed connector				
	1-2	Connects VCC supply to +1.8V on board supply				
	1-3*	Connects VCC supply to +3.3V on board supply				
JU4	1-4	Connects VCC supply to +5.0V on board supply				
	1-5	Connects VCC supply to external DC supply				
	Open	Disconnects VCC				
JU5	1-2*	Connects VCC to MAX31343 IC WLP package (U1)				
102	Open	Disconnects VCC from MAX31343 IC WLP package (U1)				
JU8	1-2*	Connects square wave output to pin 4 of P2 Arduino/Mbed connector				
108	Open	Disconnects square wave output from Arduino/Mbed connector				
11.14.0	1-2*	Sets MAX31343 WLP package (U1) IC under test				
JU10	2-3	Sets MAX31343 TDFN package (U2) IC under test				
11.144	1-2*	Connects VCC to MAX31343 IC TDFN package (U2)				
JU11	Open	Disconnects VCC from MX31343 IC TDFN package (U2)				
11.14.0	1-2*	Connects VBAT to MAX31343 IC WLP package (U1)				
JU12	Open	Disconnects VBAT from MAX31343 IC WLP package (U1)				
11.14.2	1-2*	Connects VBAT to MAX31343 IC TDFN package (U2)				
JU13	Open	Disconnects VBAT from MAX31343 IC TDFN package (U2)				

*Default position

Arduino is a registered trademark of Arduino, LLC. Mbed is a trademark Arm Limited (or its subsidiaries) in the US and/or elsewhere.

onfiguration & Time Alarms & Timer Registers	RAM		Real Time Monitoring	
te/Time Configuration	RTC Configuration		Continuous Read	Temp
Day (Sun-Sat) Sunday (1)	Oscillator Enable	SQW	January	00:00:10 01, 2000, Sunday
Hour (0-23) Min (0-59) Sec (0-59)	Data Retention	SQW Frequeny	Interrupts & Flags	
Month (1-12) Date (1-31) Year (0-199)	Soft Reset	CLKO Frequeny 32 KHz *	Interrupts	Flags
Set Read	CLKOUT	Read	Alarm1 Interrupt	Alarm 1 Alarm 2
wer Mode Configuration	Temperature Configuration		Timer Interrupt	Timer
ower supply mode Power fail threshold • Auto 2.40V Manual Use VCC	Ter	26.25°C	Power Fail Temp sense flag	Power fail Temp sense flag OSF
Kohm + Schottky diode Trickle Charger Read	One Shot	Read	Read	Read
ıs Log Idresses found: 0xD0 XX31343 I2C slave detected.				Log To File Clear Log

Figure 2. MAX31343 RTC SHIELD Software—Configuration & Time Page

l

Detailed Description

The MAX31343 shield is a low-cost, extremely accurate real-time clock (RTC). It is driven by an internal temperaturecompensated microelectromechanical systems (MEMS) resonator. The oscillator provides a stable and accurate reference clock and maintains the RTC to within ± 0.432 seconds-per-day accuracy from -40°C to +85°C. The RTC device is accessed through an I²C serial interface.

The RTC maintains seconds, minutes, hours, day, date, month, year, and century information. The date at the end of the month is automatically adjusted for months with fewer than 31 days, including corrections for leap year up to the year 2199. The clock operates in the 24-hour format. Other features including two programmable timeof-day alarms, interrupt output, uncompensated programmable clock output, and temperature compensated programmable square-wave output. A voltage reference and comparator circuit monitor the status of VCC to detect power failures and automatically switch to the backup supply when necessary.

Detailed Description of Software and Functional Test Procedure

Real Time Monitoring

To monitor the time and date, on **Configuration & Time** page, under the **RTC Configuration** group box, enable **Oscillator Enable toggle** button, and under **Real Time Monitoring** group box, check **Continuous Read** checkbox for continuous reading.

Current Draw at Time-Keeping Mode

To measure the current draw under normal real-time clock conditions, without any interrupt or CLKO output:

- 1) Remove the jumper from JU5.
- With the output set to +3.3V and disabled, connect the negative terminal of the pico ammeter to the pin 1 of the JU5 (marked as a white dot) and the positive terminal to pin 2 of JU5.
- 3) On the Configuration & Time tab, in the Date/Time Configuration group box, press the Read button. In the RTC Configuration group box, disable the CLKOUT toggle button, and select 1Hz in SQW Frequency drop-down list. In the Real Time Monitoring group box, uncheck the Continuous Read check box.
- 4) The reading in the pico ammeter is the current consumed by MAX31343 IC only. It should be around 940nA.

CLKOUT Frequency

On the **Configuration & Time** tab of the software, under the **RTC Configuration** group box, enable the **CLKOUT** toggle button and select the desired frequency. The clock output can be monitored using an oscilloscope connected to CLKO test point (TP7). A frequency counter can also be used to measure the clock frequency accurately.

Alarm and Timer Configuration

Use the **Alarm & Timer Configuration** tab to configure Alarm 1, Alarm 2, and timer. (Figure 3)

For more details on using the software, refer to the *MAX31343 Shield Software User Guide*.

onfiguration & Time Alarm	s & Timer Registers	RAM			Real Time Monitoring	
arm 1 Configuration		Alarm 2 Con	figuration		Continuous Read	Temp
Repetition Rate		Repet	tition Rate			00:00:42
Date, Month, Year, Time	e Match 👻	Da	te, Hr, Min Match	w	January	01, 2000, Sunday
Hour (0-23) Min (0-59)	Sec (0-59)	Hour (0-	23) Min (0-59)		Interrupts & Flags	
	: 00 -	00			INT Disabled	
Month (1-12) Date (1-31)	Year (0-99)	Date (1-			Interrupts	Flags
					Alarm1 Interrupt	Alarm 1
	Read			Read	Alarm2 Interrupt	Alarm 2
mer Configuration					Timer Interrupt	Timer
Timer Enable	Timer Frequency		Timer Init (0-255)	0 👻	Power Fail	Power fail
Pause	 1024Hz 	256Hz			Temp sense flag	Temp sense flag
Repeat	64Hz	16Hz	Timer Count	0	Disable OSF	OSF
				Read	Read	Read
us Log						
idresses found: 0xD0 AX31343 I2C slave detected.						^
						Log To File

Figure 3. MAX31343 RTC SHIELD Software—Alarms & Timer Page

Evaluates: MAX31343

Registers Tab

Write and read the MAX31343 IC register map in the **Register** tab. (Figure 4)

For more details on using the software, refer to the *MAX31343 Shield Software User Guide*.

figur	ation & Time	Alarms & Timer	Registers	RAM				Real Time Monitoring	
Regis	ter Map							Continuous Read	Temp
Г	Addr	Reg Name	R/W	Value	Desel All	^			00:00:42
	0x00	status	RC	0x00					
	0x01	Int_en	R/W	0x00				January	01, 2000, Sunday
	0x02	RTC_reset	R/W	0x00				Interrupts & Flags	
	0x03	RTC_config1	R/W	0x0A				INT	
	0x04	RTC_config2	R/W	0x40				Disabled	
	0x05	Timer_config	R/W	0x04					
	0x06	Seconds	R/W	0x42				Interrupts	Flags
	0x07	Minutes	R/W	0x00					
	0x08	Hours	R/W	0x00				Alarm1 Interrupt	Alarm 1
	0x09	Day	R/W	0x01				Alarm2 Interrupt	Alarm 2
	0x0A	Date	R/W	0x01				Times laternet	
	0x0B	Month	R/W	0x01				Timer Interrupt	Timer
	0x0C	Year	R/W	0x00				Power Fail	Power fail
	0x0D	Alm1_sec	R/W	0x00	\checkmark			Tomp sopes flag	
	0x0E	Alm1_min	R/W	0x00				Temp sense flag	Temp sense flag
	0x0F	Alm1_hrs	R/W	0x00			Read	Disable OSF	OSF
	0x10	Alm1day_date	R/W	0x00					
	0x11	Alm1_mon	R/W	0x00		v	Write	Read	Read
Log									
	es found: 0xD0 43 I2C slave de								^
									Log To File

Figure 4. MAX31343 RTC SHIELD Software—Registers Page

Ordering Information

PART	ТҮРЕ
MAX31343SHLD#	Shield

#Denotes RoHS compliance.


Evaluates: MAX31343

MAX31343 SHIELD Bill of Materials


ITEM	REF_DES	DNI/DNP	QTY	MFG PART #	MANUFACTURER	VALUE	DESCRIPTION
1	C1, C3, C5, C7, C12, C14, C16, C23	-	8	C0402C103J3RAC	KEMET	0.01UF	CAPACITOR; SMT (0402); CERAMIC CHIP; 0.01UF; 25V; TOL=5%; TG=-55 DEGC TO +125 DEGC; TC=X7R
2	C2, C4, C6, C8, C10, C13, C15, C17, C20-C22, C24, C25	-	13	C1005X7R1C104K050BC;ATC530L104KT16; 0402YC104KAT2A;CGA2B1X7R1C104K050BC; GCM155R71C104KA55;C0402X7R160-104KNE; CL05B104KO5NNNC;GRM155R71C104KA88; C1005X7R1C104K;CC0402KRX7R7BB104; EMK10587104KV;CL05B104K05	TDK;AMERICAN TECHNICAL CERAMICS; AVK;TDK;MURATA;VENKEL LTD.; SAMSUNG ELECTRONICS;MURATA; TDK;YAGEO PHICOMP;TAIYO YUDEN; SAMSUNG ELECTRONICS	0.1UF	CAPACITOR; SMT (0402); CERAMIC CHIP; 0.1UF; 16V; TOL=10%; TG=-55 DEGC TO +125 DEGC; TC=X7R
3	C9, C19	-	2	CL05B105KQ5NQNC; GRM155R70J105KA12	SAMSUNG ELECTRONICS;MURATA	1UF	CAPACITOR; SMT (0402); CERAMIC CHIP; 1UF; 6.3V; TOL=10%; TG=-55 DEGC TO +125 DEGC; TC=X7R
4	C11, C18	-	2	GRM155R61A106ME44;GRM155R61A106ME11; 0402ZD106MAT2A;CL05A106MP5NUNC	MURATA;MURATA;AVX;SAMSUNG	10UF	CAPACITOR; SMT (0402); CERAMIC CHIP; 10UF; 10V; TOL=20%; TG=-55 DEGC TO +85 DEGC; TC=X5R
5	JU1, JU3, JU5-JU8, JU11-JU13	-	9	PCC02SAAN	SULLINS	PCC02SAAN	CONNECTOR; MALE; THROUGH HOLE; BREAKAWAY; STRAIGHT THROUGH; 2PINS; -65 DEGC TO +125 DEGC
6	JU2	-	1	PEC04SAAN	SULLINS ELECTRONICS CORP.	PEC04SAAN	CONNECTOR; MALE; THROUGH HOLE; BREAKAWAY; STRAIGHT; 4PINS
7	JU4	-	1	TSW-105-07-L-S	SAMTEC	TSW-105-07-L-S	EVKIT PART-CONNECTOR; THROUGH HOLE; TSW SERIES; SINGLE ROW; STRAIGHT; 5PINS
8	JU10	-	1	PBC03SAAN	SULLINS	PBC03SAAN	CONNECTOR; MALE; THROUGH HOLE; BREAKAWAY; STRAIGHT; 3PINS; -65 DEGC TO +125 DEGC
9	P1	-	1	SSQ-110-04-G-S	SAMTEC	SSQ-110-04-G-S	CONNECTOR; FEMALE; THROUGH HOLE; .025IN SQ POST SOCKET; STRAIGHT; 10PINS ;
10	P2, P4	-	2	SSQ-108-04-G-S	SAMTEC	SSQ-108-04-G-S	CONNECTOR; FEMALE; THROUGH HOLE; .025IN SQ POST SOCKET; STRAIGHT; 8PINS ;
11	P3	-	1	SSQ-106-04-G-S	SAMTEC	SSQ-106-04-G-S	CONNECTOR; FEMALE; THROUGH HOLE; .025IN SQ POST SOCKET; STRAIGHT; 6PINS ;
12	P5, P6	-	2	PPPC101LFBN-RC	SULLINS ELECTRONICS CORP.	PPPC101LFBN-RC	CONNECTOR; FEMALE; THROUGH HOLE; HEADER CONNECTOR; STRAIGHT; 10PINS
13	R1-R4, R7-R11	-	9	ERJ-2GEJ103	PANASONIC	10K	RESISTOR; 0402; 10K OHM; 5%; 200PPM; 0.10W; THICK FILM
14	R5	-	1	ERJ-2GE0R00	PANASONIC	0	RESISTOR; 0402; 0 OHM; 0%; JUMPER; 0.10W; THICK FILM
15	SUPER_CAP	-	1	KW-5R5C334-R	EATON POWERING BUSINESS WORLDWIDE	0.33F	CAP; THROUGH HOLE-RADIAL LEAD; 0.33F; +80%/-20%; 5.5V; ALUMINUM-ELECTROLYTIC ;
16	TP1, TP4	-	2	5011	KEYSTONE	N/A	TEST POINT; PIN DIA=0.125IN; TOTAL LENGTH=0.445IN; BOARD HOLE=0.063IN; BLACK; PHOSPHOR BRONZE WIRE SILVER PLATE FINISH;
17	TP2, TP3	-	2	5010	KEYSTONE	N/A	TEST POINT; PIN DIA=0.125IN; TOTAL LENGTH=0.445IN; BOARD HOLE=0.063IN; RED; PHOSPHOR BRONZE WIRE SIL;
18	TP5-TP9	-	5	5012	KEYSTONE	N/A	TEST POINT; PIN DIA=0.125IN; TOTAL LENGTH=0.445IN; BOARD HOLE=0.063IN; WHITE; PHOSPHOR BRONZE WIRE SILVER PLATE FINISH;
19	U1	-	1	MAX31343EKA+	MAXIM	MAX31343EKA+	EVKIT PART-IC; MAX31343EKA+; +/-4PPM; I2C REAL-TIME CLOCK WITH INTEGRATED MEMS OSCILLATOR; PACKAGE OUTLINE: 21-100336; PACKAGE CODE: K82A2+1
20	U2	DNI	1	MAX31343ETAY+	махім	MAX31343ETAY+	EVKIT PART-IC; MAX31343ETAY+; +/-4PPM; I2C REAL-TIME CLOCK WITH INTEGRATED MEMS OSCILLATOR; PACKAGE OUTLINE: 21-100322; PACKAGE LAND PATTERN: 90-100121; PACKAGE CODE: T834MKY+1
21	U3, U5	-	2	NLSX4373MUTAG	ON SEMICONDUCTOR	NLSX4373MUTAG	IC; TRANS; 2-BIT 20 MB/S DUAL-SUPPLY LEVEL TRANSLATOR; UDFN8
22	U4	-	1	NLSX4401MU1TCG	ON SEMICONDUCTOR	NLSX4401MU1TCG	IC; TRANS; 1-BIT 20 MB/S DUAL-SUPPLY LEVEL TRANSLATOR; UDFN6
23	U6-U8	-	3	MAX14689AETB+	МАХІМ	MAX14689AETB+	IC; ASW; ULTRA-SMALL LOW-RON BEYOND-THE-RAILS DPDT ANALOG SWITCHES; TDFN10-EP
24	PCB	-	1	MAX31343SHIELD	MAXIM	PCB	PCB:MAX31343SHIELD
25	P7	DNP	0	SSQ-103-03-G-D	SAMTEC	SSQ-103-03-G-D	CONNECTOR; FEMALE; THROUGH HOLE; SSQ SERIES ; STRAIGHT; 6PINS
26	R6	DNP	0	N/A	N/A	OPEN	PACKAGE OUTLINE 0402 RESISTOR
TOTAL			72	1			

Evaluates: MAX31343

MAX31343 SHIELD Schematics




MAX31343 SHIELD Schematics (continued)



Evaluates: MAX31343


00000000 00000000 R1 R2 maxim integrated... 29 U3 58 00 MAX31343_SHIELD_EVKIT_C UUU 7 0 0 0 0 000000000 00 R6 200 MAX32625 PICO USB 00000000000 P6 R5 100 JU12 Ο 000 40 JU2 0 0 C20 0 TP4 GND C18 SUPER CAP C18 SUPER CAP VBAT_EXT P3 + SUPER_CAP VBAT

MAX31343 SHIELD PCB Layouts




MAX31343 SHIELD PCB Layout—Top

MAX31343 SHIELD Component Placement Guide—Top Silkscreen



MAX31343 SHIELD PCB Layout—Bottom



MAX31343 SHIELD Component Placement Guide—Bottom Silkscreen

Evaluates: MAX31343

Revision History

REVISION	REVISION	DESCRIPTION	PAGES
NUMBER	DATE		CHANGED
0	4/20	Initial release	—

For pricing, delivery, and ordering information, please visit Maxim Integrated's online storefront at https://www.maximintegrated.com/en/storefront/storefront.html.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time.