



**Part Number :** [5051104096](#)

**Product Description :** Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 40 Circuits, 150°C Operating Temperature, Gold over Nickel Plating

**Series Number :** 505110

**Status :** Active

**Product Category :** FFC / FPC Connectors



---

## Documents & Resources

### Drawings

[Drawing 5051104096\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 5051104096\\_stp.zip](#)

### Specifications

[Packaging Specification 5051109200-200.pdf](#)

[Product Specification 5051100008-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	FFC / FPC Connectors
Series	505110
Description	Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 40 Circuits, 150°C Operating Temperature, Gold over Nickel Plating
Series Name	FD19
Comments	Black Actuator
Product Family	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	889056535571

### Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

### Physical

Actuator Type	Front Flip
Circuits (Loaded)	40
Color - Resin	Beige
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	1.90mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold

Material - Resin	Liquid Crystal Polymer
Net Weight	305.300/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.051µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C
Wire/Cable Type	FFC/FPC