LITEON LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

FEATURES

- *0.3 inch (7.62 mm) DIGIT HEIGHT
- *CONTINUOUS UNIFORM SEGMENTS
- ***LOW POWER REQUIREMENT**
- *EXCELLENT CHARACTERS APPEARANCE
- *HIGH BRIGHTNESS & HIGH CONTRAST
- ***WIDE VIEWING ANGLE**
- *** SOLID STATE RELIABILITY**
- *CATEGORIZED FOR LUMINOUS INTENSITY

DESCRIPTION

The LTS-312AP is a 0.3 inch (7.62 mm) digit height single digit seven-segment display. This device uses BRIGHT RED LED chips (GaP epi on GaP substrate). The display has a black face and red segments.

DEVICE


PART NO.	DESCRIPTION			
Bright Red	Common Anode			
LTS-312AP	Rt. & Lt. Hand Decimal			

PAGE: PART NO.: LTS-312AP 1 of 5

LITE-ON TECHNOLOGY CORPORATION


Property of Lite-On Only

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PART NO.: LTS-312AP PAGE: 2 of 5



LITEON LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

PIN CONNECTION

No.	CONNECTION					
1	CATHODE A					
2	CATHODE F					
3	COMMON ANODE					
4	NO PIN					
5	NO PIN					
6	CATHODE LDP					
7	CATHODE E					
8	CATHODE D					
9	CATHODE RDP					
10	CATHODE C					
11	CATHODE G					
12	NO PIN					
13	CATHODE B					
14	COMMON ANODE					

PAGE: 3 of 5 PART NO.: LTS-312AP



LITEON LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	MAXIMUM RATING	UNIT			
Power Dissipation Per Segment	40	mW			
Peak Forward Current Per Segment (Frequency 1Khz, 10% duty cycle)	60*	mA			
Continuous Forward Current Per Segment	15	mA			
Derating Linear From 25°C Per Segment	0.2	mA/°C			
Reverse Voltage Per Segment	5	V			
Operating Temperature Range	-35°C to +85°C				
Storage Temperature Range -35°C to +85°C					
Solder Temperature: max 260°C for max 3sec at 1.6mm below seating plane.					

^{*} see figure 5 to establish pulsed condition

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C


PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	Iv	340	750		μcd	I _F =10mA
Peak Emission Wavelength	λр		697		nm	I _F =20mA
Spectral Line Half-Width	Δλ		90		nm	I _F =20mA
Dominant Wavelength	λd		657		nm	I _F =20mA
Forward Voltage Per Segment	V_{F}		2.1	2.6	V	I _F =20mA
Reverse Current Per Segment	Ir			100	μA	V _R =5V
Luminous Intensity Matching Ratio	Iv-m			2:1		I _F =10mA


Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.


PART NO.: LTS-312AP PAGE: 4 of 5 Property of Lite-On Only

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)











Fig3. Relative Luminous Intensity vs. DC Forward Current



NOTE: P=BRIGHT RED

PART NO.: LTS-312AP PAGE: 5 of 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lite-On: