


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A2		REVISED PER ECO-11-004820	11MAR11	RK	HMR





SPECIFICATIONS:
MATERIALS:
 CASE-HIGH TEMPERATURE POLYESTER, BLACK
 ACTUATOR-POLYESTER, UL94V-0, BLACK
 FRAME- STEEL, TIN PLATE
 MOVING CONTACT-COPPER ALLOY, GOLD OVER NICKEL PLATE
 FIXED CONTACT-COPPER ALLOY, GOLD OVER NICKEL PLATE
 TERMINAL-COPPER ALLOY, TIN OVER NICKEL PLATE

ELECTRICAL:
 CURRENT RATING: 0.4 VA MAX. 20 V MAX. (AC/DC).
 INITIAL CONTACT RESISTANCE: 40 MILLIOHMS MAX.
 @ 100 M.V. AND 1 M.A. VOLTAGE WITHSTAND: 1000 VAC BETWEEN
 TERMINALS AND CASE GROUND FOR 1 MINUTE.
 LIFE: 60,000 - 80,000 CYCLES.

MECHANICAL:
 ACTUATION FORCE: 150-600 GRAMS

ENVIRONMENTAL:
 OPERATING TEMPERATURE: -4°F TO + 176°F (-20°C TO +80°C)
 STORAGE TEMPERATURE: -4°F TO + 176°F (-20°C TO +80°C)
 SOLDER HEAT RESISTANCE PER EIA-364-56A, PROCEDURE 3, COND. B
 SOLDERABILITY PER EID 364-52, CLASS 2 CATEGORY 1

1. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).



P/N	Alco P/N	Actuator Flush/ Extended	Position	Type			
					1 2 3 4 5 6	1 2 3 4 5 6	1 2 3 4 5 6
1571984-1	TSS11DGRA04	Extended	2	SPDT	1,2	None	2,3
1571984-2	TSS11EGRA04	Extended	3	SPDT	1,2	Off	2,3
1571984-3	TSS21NGRA04	Extended	2	DPDT	1-2, 4-5	None	2-3, 5-6
1571984-4	TSS21PGRA04	Extended	3	DPDT	1-2, 4-5	Off	2-3, 5-6

THIS DRAWING IS A CONTROLLED DOCUMENT. 28FEB06

DWN M.BINNER
 CHK M.SARVER
 APVD M.SARVER
 PRODUCT SPEC

TE Connectivity

NAME: SLIDE SWITCH RA

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 1571984 RESTRICTED TO: -

MATERIAL: SEE SPECIFICATION FINISH: - WEIGHT: - SCALE: 4:1 SHEET: 1 OF 1 REV: A2

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSS11DGRA04](#)