

FEATURES


- Quick punch removal with the push of a button for fast and easy tooling change
- Applicator designed to industry standard mounting and shut height 135.80mm (5.346")
- Quick set-up time; plus the crimp height, track and feed adjustments can be set without removing the applicator from the press
- Fine adjustment allows users to achieve target with little effort by adjusting in increments of .015mm (.0006") for conductor crimp height and .063mm (.0025") for insulation height
- Independent adjustment rings allow users to quickly adjust the conductor or insulation crimp height without affecting each other
- Directly adapts to most automatic wire processing machines

SCOPE

Products: RAST5 Normal Force (HNF) Female Crimp Terminal, 18-20 AWG.

Terminal	Terminal	Wire Size			Insulation	Strin Longth				
Series No.	Order No.			IPC/WHMA-A60 (1)		Termi	nal (2)	Strip Length		
Series No.		AWG	mm²	mm	ln.	mm	ln.	mm	ln.	
94518	94518-0100	18	0.80	2.20-2.80	.087110	2.20-2.80	.087110	5.00-5.50	.197216	
94516	94518-0101	20	0.50							
(1) To achieve optimum IPC-A620 Class 2 insulation crimps, use this insulation OD.										
(2) Ove	(2) Overall insulation OD specification for terminal.									

DEFINITION OF TERMS



The above terminal drawing is a generic terminal representation. It is not an image of any terminal listed in the scope.

Release Date: 03-23-10 Revision Date: 09-03-10 **UNCONTROLLED COPY**

CRIMP SPECIFICATION

Terminal Series No.	Bell n	nouth	Cut-off Tab	o Maximum	Conductor Brush	
renninai Series No.	mm	ln.	mm	In.	mm	ln.
94518	0.20-0.40	.008016	0.60	.024	0.50-1.50	.020059

	Bend up Bend down		Twist	Roll	Punch Width (Ref)				Seam	
Terminal Series No.	Bella up	Bena down	IWISU	ROII	Conductor		Insulation		Seam shall not be	
	Degree		Degree		mm	In	mm	In	open and no wire allowed	
94518	3 °	3 °	4 °	8 °	2.15	.085	2.80	.110	out of the crimping area	

After crimping, the crimp profiles should measure the following:

Tomainal	Wire Size		Conductor				Insulation					Pull Force	
Terminal Series No.			Crimp Height		Crimp Width (Ref)		Crimp Height (Ref)		Crimp Width (Ref)		Minimum		
Series No.	AWG	mm ²	mm	In.	mm	In.	mm	In.	mm	In.	Ν	Lb.	
	18	0.80	1.50-1.57	.059062	2.20-2.30	.087091	3.00-3.10	.118122	2.80-3.00	.110118	117.7	26.5	
94518	20	0.50	1.25-1.35	.049053	2.20-2.30	.087091	2.90-3.00	.114118	2.80-3.00	.110118	78.2	17.6	
		1.00	1.57-1.67	.062066	2.20-2.30	.087091	3.10-3.20	.122126	2.80-3.00	.110118	157.0	35.3	


Tool Qualification Notes:

- 1. Pull Force should be measured with no influence from the insulation crimp.
- 2. The above specifications are guidelines to an optimum crimp.

PARTS LIST

	FineAdjust Applicator 63901-9700									
ltem	Order No	Engineering No.	Description	Quantity						
Perishable Tooling										
	63901-9770	63901-9770	Tool Kit (All "Y" Items)	REF						
1	63457-0071	63457-0071	Conductor Punch	1 Y						
2	63832-0102	63832-0102	Conductor Anvil	1 Y						
3	63454-0116	63454-0116	Insulation Punch	1 Y						
4	63445-2841	63445-2841	Insulation Anvil	1 Y						
5	63443-0002	63443-0002	Cut-Off Plunger Front	1 Y						
6	63443-0012	63443-0012	Plunger Retainer Front	1 Y						
Other Components										
7	11-17-0022	1739-21	Hold-Down Spring	1						
8	11-18-4083	60707-8	Front Cover	1						
9	11-24-1067	4996-4	Cut-off Plunger Spring	1						
10	63443-0009	63443-0009	Scrap Chute Front	1						
11	63443-0024	63443-0024	Lower Tooling Key	1						
12	63443-0090	63443-0090	Wire Stop	1						
13	63443-0093	63443-0093	Shank	1						
14	63443-1718	63443-1718	18.80mm Height Spacer	1						
15	63443-2201	63443-2201	1.0mm Coarse Spacer	1						
16	63443-2213	63443-2213	13.0mm Coarse Spacer	1						
17	63443-2310	63443-2310	3.50mm Fine Spacer	1						
18	63443-2805	63443-2805	Plunger Striker Front	1						
19	63443-2912	63443-2912	Wire Hold-Down Plunger	1						
20	63443-6123	63443-6123	Rear Cover	1						
21	63600-1057	63600-1057	Wire Hold-Down Spring	1						
22	63890-0094	63890-0094	Terminal Hold-Down	1						
Frame										
23	63800-4901	63800-4901	Тор	1						
24	63801-3281	63801-3281	Base	1						
25	63801-4650	63801-4650	Track	1						
		Н	lardware							
26	N/A	N/A	M3 by 6 Long FHCS	1**						
27	N/A	N/A	M3 by 6 Long SHCS	2**						
28	N/A	N/A	M3 by 8 Long SHCS	1**						
29	N/A	N/A	M4 by 6 Long SHCS	2**						
30	N/A	N/A	M4 by 12 Long BHCS	2**						
31	N/A	N/A	M4 by 50 Long SHCS	2**						
32	N/A	N/A	M5 by 12 Long SHCS	1**						
33	N/A	N/A	#10-32 by 3/8"Long Flat Point SSS	1**						
34	N/A	N/A	#10-32 Hex Jam Nut	1**						
**	** Available from an industrial supply company such as MSC (1-800-645-7270).									

Release Date: 03-23-10 Revision Date: 09-03-10 **UNCONTROLLED COPY**



NOTES

- 1. Molex recommends an extra perishable tooling kit be maintained at your facility.
- 2. Verify tooling alignment by manually cycling the press and Applicator before crimping under power. Check that all screws are tight.
- 3. Slugs, Terminals, Dirt and Oil should be kept clear of work area.
- 4. Wear safety glasses at all times.
- 5. For recommended maintenance refer to the FineAdjust Manual.

CAUTION: This applicator should only be used in a press with a shut height of 135.80 mm (5.346"). Tooling damage could result at a lower setting.

CAUTION: To prevent injury never operate this Applicator without the guards supplied with the press or wire-processing machine in place. Reference the press or wire processing manufacturer's instruction manual.

CAUTION: Molex crimp specifications are valid only when used with Molex terminals, applicators and tooling.

http://www.molex.com

Release Date: 03-23-10 Revision Date: 09-03-10 **UNCONTROLLED COPY**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex: 63901-9770